

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **206-8LED3036-12-XX-OSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-35)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 206-8LED3036-12-XX-OSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK, OVERALL SPREAD LENS
Light Source: (1) SORAA 3000K 95 CRI LED
SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	299.2 lumens	Max Intensity:	826.2 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	38.9 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	34.5°H x 34.5°V	Field Angle (10%):	58°H x 58°V
Beam Lumens:	167.8 lumens	Field Lumens:	277.1 lumens
Beam Efficiency:	56.1%	Field Efficiency:	92.6%
Input Watts (W):	7.7		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 206-8LED3036-12-XX-OSL

Iso-Candela Plot






REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

Lumen Table

90	0.0															
80	0.0															
70	0.0															
60	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50	0.0															
40	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30	0.0															
20	0.0	0.0	0.0	0.1	0.7	2.6	4.8	4.8	2.6	0.7	0.1	0.0	0.0	0.0	0.0	0.0
10	0.0															
0	0.0	0.0	0.1	0.5	4.4	13.4	21.7	21.7	13.4	4.4	0.5	0.1	0.0	0.0	0.0	0.0
-10	0.0															
-20	0.0	0.0	0.0	0.3	2.5	8.2	13.8	13.8	8.2	2.5	0.3	0.0	0.0	0.0	0.0	0.0
-30	0.0															
-40	0.0	0.0	0.0	0.0	0.1	0.4	0.7	0.7	0.4	0.1	0.0	0.0	0.0	0.0	0.0	0.0
-50	0.0															
-60	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-70	0.0															
-80	0.0															
-90	0.0															


REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 206-8LED3036-12-XX-OSL

Luminous Intensity Polar Plot



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

Luminous Intensity Plot



Beam:
 H Angle: 34.5°
 V Angle: 34.5°
 Lumens: 167.8
 Efficiency: 56.1%

Field:
 H Angle: 58°
 V Angle: 58°
 Lumens: 277.1
 Efficiency: 92.6%

Spill:
 Lumens: 22.1
 Efficiency: 7.4%

- Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	1
45°	0	0	0	0	0	0	0	0	1	1	1
42.5°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
37.5°	0	0	0	0	0	0	1	1	1	1	1
35°	0	0	0	0	0	1	1	1	1	1	1
32.5°	0	0	0	0	0	1	1	1	1	1	2
30°	0	0	0	0	1	1	1	1	1	1	2
27.5°	0	0	0	0	1	1	1	1	1	2	3
25°	0	0	0	0	1	1	1	1	2	2	3
22.5°	0	0	0	1	1	1	1	1	2	3	3
20°	0	0	0	1	1	1	1	1	2	3	4
17.5°	0	0	0	1	1	1	1	2	3	3	5
15°	0	0	0	1	1	1	1	2	3	4	6
12.5°	0	0	1	1	1	1	1	2	3	4	7
10°	0	0	1	1	1	1	2	2	3	5	8
7.5°	0	0	1	1	1	1	2	3	3	6	9
5°	0	0	1	1	1	1	2	3	3	6	9
2.5°	0	0	1	1	1	1	2	3	3	6	10
0°	0	0	1	1	1	1	2	3	4	6	10
-2.5°	0	0	1	1	1	1	2	3	3	6	10
-5°	0	0	1	1	1	1	2	3	3	6	9
-7.5°	0	0	1	1	1	1	2	3	3	6	9
-10°	0	0	1	1	1	1	2	2	3	5	8
-12.5°	0	0	1	1	1	1	1	2	3	4	7
-15°	0	0	0	1	1	1	1	2	3	4	6
-17.5°	0	0	0	1	1	1	1	2	3	3	5
-20°	0	0	0	1	1	1	1	1	2	3	4



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	0	1	1	1	1	1	2	3	3
-25°	0	0	0	0	1	1	1	1	2	2	3
-27.5°	0	0	0	0	1	1	1	1	1	2	3
-30°	0	0	0	0	1	1	1	1	1	1	2
-32.5°	0	0	0	0	0	1	1	1	1	1	2
-35°	0	0	0	0	0	1	1	1	1	1	1
-37.5°	0	0	0	0	0	0	1	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	1	1	1	1
-45°	0	0	0	0	0	0	0	0	1	1	1
-47.5°	0	0	0	0	0	0	0	0	0	0	1
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	1	1
55°	0	0	0	0	0	1	1	1	1	1	1
52.5°	0	0	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	2
45°	1	1	1	1	1	1	1	2	2	2	2
42.5°	1	1	1	1	2	2	2	3	3	3	3
40°	1	1	1	2	2	3	3	3	4	4	5
37.5°	1	2	2	3	3	3	4	5	6	7	8
35°	2	2	3	3	4	5	7	8	10	12	14
32.5°	2	3	3	4	6	8	10	13	16	20	24
30°	3	3	5	6	9	12	16	22	28	35	45
27.5°	3	4	6	9	13	18	26	35	51	64	78
25°	4	6	9	13	19	28	43	61	82	104	125
22.5°	5	8	12	18	28	46	68	95	124	152	178
20°	7	10	16	26	43	68	99	135	171	207	243
17.5°	8	13	22	35	61	95	135	177	223	270	313
15°	10	16	28	51	82	124	171	223	279	336	388
12.5°	12	20	35	64	104	152	207	270	336	400	457
10°	14	24	45	78	125	178	243	313	388	457	523
7.5°	16	28	53	91	142	201	272	351	430	507	582
5°	17	30	59	101	155	219	296	380	463	547	629
2.5°	17	31	63	108	163	231	311	398	484	573	658
0°	18	32	64	110	166	235	316	404	491	582	668
-2.5°	17	31	63	108	163	231	311	398	484	573	658
-5°	17	30	59	101	155	219	296	380	463	547	629
-7.5°	16	28	53	91	142	201	272	351	430	507	582
-10°	14	24	45	78	125	178	243	313	388	457	523
-12.5°	12	20	35	64	104	152	207	270	336	400	457
-15°	10	16	28	51	82	124	171	223	279	336	388
-17.5°	8	13	22	35	61	95	135	177	223	270	313
-20°	7	10	16	26	43	68	99	135	171	207	243



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	5	8	12	18	28	46	68	95	124	152	178
-25°	4	6	9	13	19	28	43	61	82	104	125
-27.5°	3	4	6	9	13	18	26	35	51	64	78
-30°	3	3	5	6	9	12	16	22	28	35	45
-32.5°	2	3	3	4	6	8	10	13	16	20	24
-35°	2	2	3	3	4	5	7	8	10	12	14
-37.5°	1	2	2	3	3	3	4	5	6	7	8
-40°	1	1	1	2	2	3	3	3	4	4	5
-42.5°	1	1	1	1	2	2	2	3	3	3	3
-45°	1	1	1	1	1	1	1	2	2	2	2
-47.5°	1	1	1	1	1	1	1	1	1	1	2
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	0	0	1	1	1	1	1	1	1	1	1
-55°	0	0	0	0	0	1	1	1	1	1	1
-57.5°	0	0	0	0	0	0	0	0	0	1	1
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	1	1	1	1	1	1	1	0	0
55°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	2	2	2	2	2	2	2	1	1	1
45°	3	3	3	3	3	3	3	2	2	2	2
42.5°	3	3	3	4	3	3	3	3	3	3	3
40°	6	6	6	6	6	6	6	5	4	4	3
37.5°	9	9	10	10	10	9	9	8	7	6	5
35°	16	17	17	18	17	17	16	14	12	10	8
32.5°	28	30	31	32	31	30	28	24	20	16	13
30°	53	59	63	64	63	59	53	45	35	28	22
27.5°	91	101	108	110	108	101	91	78	64	51	35
25°	142	155	163	166	163	155	142	125	104	82	61
22.5°	201	219	231	235	231	219	201	178	152	124	95
20°	272	296	311	316	311	296	272	243	207	171	135
17.5°	351	380	398	404	398	380	351	313	270	223	177
15°	430	463	484	491	484	463	430	388	336	279	223
12.5°	507	547	573	582	573	547	507	457	400	336	270
10°	582	629	658	668	658	629	582	523	457	388	313
7.5°	648	698	729	739	729	698	648	582	507	430	351
5°	698	749	777	786	777	749	698	629	547	463	380
2.5°	729	777	800	808	800	777	729	658	573	484	398
0°	739	786	808	826	808	786	739	668	582	491	404
-2.5°	729	777	800	808	800	777	729	658	573	484	398
-5°	698	749	777	786	777	749	698	629	547	463	380
-7.5°	648	698	729	739	729	698	648	582	507	430	351
-10°	582	629	658	668	658	629	582	523	457	388	313
-12.5°	507	547	573	582	573	547	507	457	400	336	270
-15°	430	463	484	491	484	463	430	388	336	279	223
-17.5°	351	380	398	404	398	380	351	313	270	223	177
-20°	272	296	311	316	311	296	272	243	207	171	135



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	201	219	231	235	231	219	201	178	152	124	95
-25°	142	155	163	166	163	155	142	125	104	82	61
-27.5°	91	101	108	110	108	101	91	78	64	51	35
-30°	53	59	63	64	63	59	53	45	35	28	22
-32.5°	28	30	31	32	31	30	28	24	20	16	13
-35°	16	17	17	18	17	17	16	14	12	10	8
-37.5°	9	9	10	10	10	9	9	8	7	6	5
-40°	6	6	6	6	6	6	6	5	4	4	3
-42.5°	3	3	3	4	3	3	3	3	3	3	3
-45°	3	3	3	3	3	3	3	2	2	2	2
-47.5°	2	2	2	2	2	2	2	2	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	1	1	0	0	0	0	0	0	0	0	0
52.5°	1	1	1	1	1	0	0	0	0	0	0
50°	1	1	1	1	1	1	1	0	0	0	0
47.5°	1	1	1	1	1	1	1	1	0	0	0
45°	1	1	1	1	1	1	1	1	1	1	0
42.5°	2	2	2	1	1	1	1	1	1	1	1
40°	3	3	2	2	1	1	1	1	1	1	1
37.5°	4	3	3	3	2	2	1	1	1	1	1
35°	7	5	4	3	3	2	2	1	1	1	1
32.5°	10	8	6	4	3	3	2	2	1	1	1
30°	16	12	9	6	5	3	3	2	1	1	1
27.5°	26	18	13	9	6	4	3	3	2	1	1
25°	43	28	19	13	9	6	4	3	2	2	1
22.5°	68	46	28	18	12	8	5	3	3	2	1
20°	99	68	43	26	16	10	7	4	3	2	1
17.5°	135	95	61	35	22	13	8	5	3	3	2
15°	171	124	82	51	28	16	10	6	4	3	2
12.5°	207	152	104	64	35	20	12	7	4	3	2
10°	243	178	125	78	45	24	14	8	5	3	2
7.5°	272	201	142	91	53	28	16	9	6	3	3
5°	296	219	155	101	59	30	17	9	6	3	3
2.5°	311	231	163	108	63	31	17	10	6	3	3
0°	316	235	166	110	64	32	18	10	6	4	3
-2.5°	311	231	163	108	63	31	17	10	6	3	3
-5°	296	219	155	101	59	30	17	9	6	3	3
-7.5°	272	201	142	91	53	28	16	9	6	3	3
-10°	243	178	125	78	45	24	14	8	5	3	2
-12.5°	207	152	104	64	35	20	12	7	4	3	2
-15°	171	124	82	51	28	16	10	6	4	3	2
-17.5°	135	95	61	35	22	13	8	5	3	3	2
-20°	99	68	43	26	16	10	7	4	3	2	1



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	68	46	28	18	12	8	5	3	3	2	1
-25°	43	28	19	13	9	6	4	3	2	2	1
-27.5°	26	18	13	9	6	4	3	3	2	1	1
-30°	16	12	9	6	5	3	3	2	1	1	1
-32.5°	10	8	6	4	3	3	2	2	1	1	1
-35°	7	5	4	3	3	2	2	1	1	1	1
-37.5°	4	3	3	3	2	2	1	1	1	1	1
-40°	3	3	2	2	1	1	1	1	1	1	1
-42.5°	2	2	2	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	0
-47.5°	1	1	1	1	1	1	1	1	0	0	0
-50°	1	1	1	1	1	1	1	0	0	0	0
-52.5°	1	1	1	1	1	0	0	0	0	0	0
-55°	1	1	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	1	0	0	0	0	0	0	0	0	0	0
35°	1	1	0	0	0	0	0	0	0	0	0
32.5°	1	1	0	0	0	0	0	0	0	0	0
30°	1	1	1	0	0	0	0	0	0	0	0
27.5°	1	1	1	0	0	0	0	0	0	0	0
25°	1	1	1	0	0	0	0	0	0	0	0
22.5°	1	1	1	1	0	0	0	0	0	0	0
20°	1	1	1	1	0	0	0	0	0	0	0
17.5°	1	1	1	1	0	0	0	0	0	0	0
15°	1	1	1	1	0	0	0	0	0	0	0
12.5°	1	1	1	1	1	0	0	0	0	0	0
10°	2	1	1	1	1	0	0	0	0	0	0
7.5°	2	1	1	1	1	0	0	0	0	0	0
5°	2	1	1	1	1	0	0	0	0	0	0
2.5°	2	1	1	1	1	0	0	0	0	0	0
0°	2	1	1	1	1	0	0	0	0	0	0
-2.5°	2	1	1	1	1	0	0	0	0	0	0
-5°	2	1	1	1	1	0	0	0	0	0	0
-7.5°	2	1	1	1	1	0	0	0	0	0	0
-10°	2	1	1	1	1	0	0	0	0	0	0
-12.5°	1	1	1	1	1	0	0	0	0	0	0
-15°	1	1	1	1	0	0	0	0	0	0	0
-17.5°	1	1	1	1	0	0	0	0	0	0	0
-20°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	1	1	1	1	0	0	0	0	0	0	0
-25°	1	1	1	0	0	0	0	0	0	0	0
-27.5°	1	1	1	0	0	0	0	0	0	0	0
-30°	1	1	1	0	0	0	0	0	0	0	0
-32.5°	1	1	0	0	0	0	0	0	0	0	0
-35°	1	1	0	0	0	0	0	0	0	0	0
-37.5°	1	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: P246987 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 206-8LED3036-12-XX-OSL

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)