

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **206-8LED4010-12-XX-LVR**

Test Date: 04/06/18

**Test Information**

Test Method: LM-79-08  
Report Number: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
Test Lab: INNOVATION CENTER(G2)  
Test Date: 04/06/18  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 206-8LED4010-12-XX-LVR  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 10 DEGREE SPOT OPTIC,  
REGRESSED HOOD BLACK, HEX CELL LOUVER  
Light Source: (1) SORAA 4000K 95 CRI 10°NSP LED  
SM16-07-10D-940-03  
Ballast/Driver: CHROMA POWER SUPPLY IN0004


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	2H x 2V
Luminaire Lumens:	233.5 lumens	Max Intensity:	4838 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	29.2 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	12°H x 12°V	Field Angle (10%):	19.2°H x 19.2°V
Beam Lumens:	108.8 lumens	Field Lumens:	187.7 lumens
Beam Efficiency:	46.6%	Field Efficiency:	80.4%
Input Watts (W):	8		
Input Voltage (V):	12.0		
Input Current (Ain):	0.709		
Voltage Rise (V):	NR		
Power Factor:	0.9468		
Total Harmonic Distortion (THDi):	27.5		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	9 HR		
Ambient Temperature (°C):	24.9		
Test Distance:	25 FT		



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 206-8LED4010-12-XX-LVR

### Iso-Candela Plot






REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

### Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
40		0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.1	0.1	0.0	0.0	0.0	0.0			
30	0.0	0.0	0.0	0.1	0.2	0.3	0.5	0.5	0.3	0.2	0.1	0.0	0.0	0.0	0.0		
20		0.0	0.0	0.1	0.3	1.1	3.0	3.0	1.1	0.3	0.1	0.0	0.0	0.0			
10	0.0	0.0	0.0	0.2	0.5	2.9	48.4	48.4	2.9	0.5	0.2	0.0	0.0	0.0	0.0		
0		0.0	0.0	0.2	0.5	2.9	48.4	48.4	2.9	0.5	0.2	0.0	0.0	0.0			
-10	0.0	0.0	0.0	0.1	0.3	1.1	3.0	3.0	1.1	0.3	0.1	0.0	0.0	0.0	0.0		
-20		0.0	0.0	0.1	0.2	0.3	0.5	0.5	0.3	0.2	0.1	0.0	0.0	0.0			
-30	0.0	0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0		
-40		0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0			
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	

REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 206-8LED4010-12-XX-LVR


### Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg      - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

### Luminous Intensity Plot



**Beam:**  
 H Angle: 12°  
 V Angle: 12°  
 Lumens: 108.8  
 Efficiency: 46.6%

**Field:**  
 H Angle: 19.2°  
 V Angle: 19.2°  
 Lumens: 187.7  
 Efficiency: 80.4%

**Spill:**  
 Lumens: 45.8  
 Efficiency: 19.6%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	1
42.5°	0	0	0	0	0	0	0	0	0	1	1
40°	0	0	0	0	0	0	0	0	1	1	1
37.5°	0	0	0	0	0	0	0	1	1	1	1
35°	0	0	0	0	0	0	0	1	1	1	1
32.5°	0	0	0	0	0	0	1	1	1	1	1
30°	0	0	0	0	0	1	1	1	1	1	1
27.5°	0	0	0	0	0	1	1	1	1	1	2
25°	0	0	0	0	0	1	1	1	1	2	2
22.5°	0	0	0	0	1	1	1	1	1	2	2
20°	0	0	0	0	1	1	1	1	2	2	2
17.5°	0	0	0	0	1	1	1	1	2	2	3
15°	0	0	0	0	1	1	1	1	2	2	3
12.5°	0	0	0	1	1	1	1	1	2	2	4
10°	0	0	0	1	1	1	1	2	2	3	4
7.5°	0	0	0	1	1	1	1	2	2	3	4
5°	0	0	0	1	1	1	1	2	2	3	5
2.5°	0	0	0	1	1	1	1	2	2	3	5
0°	0	0	0	1	1	1	1	2	2	3	5
-2.5°	0	0	0	1	1	1	1	2	2	3	5
-5°	0	0	0	1	1	1	1	2	2	3	5
-7.5°	0	0	0	1	1	1	1	2	2	3	4
-10°	0	0	0	1	1	1	1	2	2	3	4
-12.5°	0	0	0	1	1	1	1	1	2	2	4
-15°	0	0	0	0	1	1	1	1	2	2	3
-17.5°	0	0	0	0	1	1	1	1	2	2	3
-20°	0	0	0	0	1	1	1	1	2	2	2



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	0	0	1	1	1	1	1	2	2
-25°	0	0	0	0	0	1	1	1	1	2	2
-27.5°	0	0	0	0	0	1	1	1	1	1	2
-30°	0	0	0	0	0	1	1	1	1	1	1
-32.5°	0	0	0	0	0	0	1	1	1	1	1
-35°	0	0	0	0	0	0	0	1	1	1	1
-37.5°	0	0	0	0	0	0	0	1	1	1	1
-40°	0	0	0	0	0	0	0	0	1	1	1
-42.5°	0	0	0	0	0	0	0	0	0	1	1
-45°	0	0	0	0	0	0	0	0	0	0	1
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	1	1
52.5°	0	0	0	0	0	1	1	1	1	1	1
50°	0	0	1	1	1	1	1	1	1	1	1
47.5°	0	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	2
42.5°	1	1	1	1	1	1	2	2	2	2	2
40°	1	1	1	1	2	2	2	2	2	2	3
37.5°	1	1	1	2	2	2	2	3	3	4	4
35°	1	1	2	2	2	3	3	4	5	5	6
32.5°	1	2	2	2	3	4	5	5	6	6	7
30°	2	2	2	3	4	5	6	7	7	8	9
27.5°	2	2	3	5	5	6	7	8	9	10	11
25°	2	3	4	5	6	7	9	10	11	13	14
22.5°	3	4	5	6	7	9	10	12	14	16	18
20°	3	5	6	7	9	10	12	15	18	21	25
17.5°	4	5	7	8	10	12	15	18	23	30	38
15°	5	6	7	9	11	14	18	23	32	43	58
12.5°	5	6	8	10	13	16	21	30	43	61	81
10°	6	7	9	11	14	18	25	38	58	81	115
7.5°	6	7	9	12	15	21	31	48	72	104	157
5°	6	8	10	13	16	23	35	55	83	131	249
2.5°	6	8	10	13	17	24	37	60	90	149	310
0°	6	8	10	13	17	24	38	62	93	155	332
-2.5°	6	8	10	13	17	24	37	60	90	149	310
-5°	6	8	10	13	16	23	35	55	83	131	249
-7.5°	6	7	9	12	15	21	31	48	72	104	157
-10°	6	7	9	11	14	18	25	38	58	81	115
-12.5°	5	6	8	10	13	16	21	30	43	61	81
-15°	5	6	7	9	11	14	18	23	32	43	58
-17.5°	4	5	7	8	10	12	15	18	23	30	38
-20°	3	5	6	7	9	10	12	15	18	21	25



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	3	4	5	6	7	9	10	12	14	16	18
-25°	2	3	4	5	6	7	9	10	11	13	14
-27.5°	2	2	3	5	5	6	7	8	9	10	11
-30°	2	2	2	3	4	5	6	7	7	8	9
-32.5°	1	2	2	2	3	4	5	5	6	6	7
-35°	1	1	2	2	2	3	3	4	5	5	6
-37.5°	1	1	1	2	2	2	2	3	3	4	4
-40°	1	1	1	1	2	2	2	2	2	2	3
-42.5°	1	1	1	1	1	1	2	2	2	2	2
-45°	1	1	1	1	1	1	1	1	1	1	2
-47.5°	0	1	1	1	1	1	1	1	1	1	1
-50°	0	0	1	1	1	1	1	1	1	1	1
-52.5°	0	0	0	0	0	1	1	1	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	1	1	1	1	1	1	1	1	1	0	0
52.5°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	2	2	2	2	2	2	2	2	1	1	1
42.5°	2	2	2	2	2	2	2	2	2	2	2
40°	3	3	3	3	3	3	3	3	2	2	2
37.5°	4	5	5	5	5	5	4	4	4	3	3
35°	6	6	6	6	6	6	6	6	5	5	4
32.5°	7	8	8	8	8	8	7	7	6	6	5
30°	9	10	10	10	10	10	9	9	8	7	7
27.5°	12	13	13	13	13	13	12	11	10	9	8
25°	15	16	17	17	17	16	15	14	13	11	10
22.5°	21	23	24	24	24	23	21	18	16	14	12
20°	31	35	37	38	37	35	31	25	21	18	15
17.5°	48	55	60	62	60	55	48	38	30	23	18
15°	72	83	90	93	90	83	72	58	43	32	23
12.5°	104	131	149	155	149	131	104	81	61	43	30
10°	157	249	310	332	310	249	157	115	81	58	38
7.5°	290	556	1053	1314	1053	556	290	157	104	72	48
5°	556	1594	2708	3140	2708	1594	556	249	131	83	55
2.5°	1053	2708	3996	4422	3996	2708	1053	310	149	90	60
0°	1314	3140	4422	4838	4422	3140	1314	332	155	93	62
-2.5°	1053	2708	3996	4422	3996	2708	1053	310	149	90	60
-5°	556	1594	2708	3140	2708	1594	556	249	131	83	55
-7.5°	290	556	1053	1314	1053	556	290	157	104	72	48
-10°	157	249	310	332	310	249	157	115	81	58	38
-12.5°	104	131	149	155	149	131	104	81	61	43	30
-15°	72	83	90	93	90	83	72	58	43	32	23
-17.5°	48	55	60	62	60	55	48	38	30	23	18
-20°	31	35	37	38	37	35	31	25	21	18	15



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	21	23	24	24	24	23	21	18	16	14	12
-25°	15	16	17	17	17	16	15	14	13	11	10
-27.5°	12	13	13	13	13	13	12	11	10	9	8
-30°	9	10	10	10	10	10	9	9	8	7	7
-32.5°	7	8	8	8	8	8	7	7	6	6	5
-35°	6	6	6	6	6	6	6	6	5	5	4
-37.5°	4	5	5	5	5	5	4	4	4	3	3
-40°	3	3	3	3	3	3	3	3	2	2	2
-42.5°	2	2	2	2	2	2	2	2	2	2	2
-45°	2	2	2	2	2	2	2	2	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	1	1	0	0	0	0	0	0	0	0	0
50°	1	1	1	1	1	0	0	0	0	0	0
47.5°	1	1	1	1	1	1	0	0	0	0	0
45°	1	1	1	1	1	1	1	1	0	0	0
42.5°	2	1	1	1	1	1	1	1	1	0	0
40°	2	2	2	1	1	1	1	1	1	1	0
37.5°	2	2	2	2	1	1	1	1	1	1	1
35°	3	3	2	2	2	1	1	1	1	1	1
32.5°	5	4	3	2	2	2	1	1	1	1	1
30°	6	5	4	3	2	2	2	1	1	1	1
27.5°	7	6	5	5	3	2	2	2	1	1	1
25°	9	7	6	5	4	3	2	2	2	1	1
22.5°	10	9	7	6	5	4	3	2	2	1	1
20°	12	10	9	7	6	5	3	2	2	2	1
17.5°	15	12	10	8	7	5	4	3	2	2	1
15°	18	14	11	9	7	6	5	3	2	2	1
12.5°	21	16	13	10	8	6	5	4	2	2	1
10°	25	18	14	11	9	7	6	4	3	2	2
7.5°	31	21	15	12	9	7	6	4	3	2	2
5°	35	23	16	13	10	8	6	5	3	2	2
2.5°	37	24	17	13	10	8	6	5	3	2	2
0°	38	24	17	13	10	8	6	5	3	2	2
-2.5°	37	24	17	13	10	8	6	5	3	2	2
-5°	35	23	16	13	10	8	6	5	3	2	2
-7.5°	31	21	15	12	9	7	6	4	3	2	2
-10°	25	18	14	11	9	7	6	4	3	2	2
-12.5°	21	16	13	10	8	6	5	4	2	2	1
-15°	18	14	11	9	7	6	5	3	2	2	1
-17.5°	15	12	10	8	7	5	4	3	2	2	1
-20°	12	10	9	7	6	5	3	2	2	2	1



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	10	9	7	6	5	4	3	2	2	1	1
-25°	9	7	6	5	4	3	2	2	2	1	1
-27.5°	7	6	5	5	3	2	2	2	1	1	1
-30°	6	5	4	3	2	2	2	1	1	1	1
-32.5°	5	4	3	2	2	2	1	1	1	1	1
-35°	3	3	2	2	2	1	1	1	1	1	1
-37.5°	2	2	2	2	1	1	1	1	1	1	1
-40°	2	2	2	1	1	1	1	1	1	1	0
-42.5°	2	1	1	1	1	1	1	1	1	0	0
-45°	1	1	1	1	1	1	1	1	0	0	0
-47.5°	1	1	1	1	1	1	0	0	0	0	0
-50°	1	1	1	1	1	0	0	0	0	0	0
-52.5°	1	1	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	1	0	0	0	0	0	0	0	0	0	0
30°	1	1	0	0	0	0	0	0	0	0	0
27.5°	1	1	0	0	0	0	0	0	0	0	0
25°	1	1	0	0	0	0	0	0	0	0	0
22.5°	1	1	1	0	0	0	0	0	0	0	0
20°	1	1	1	0	0	0	0	0	0	0	0
17.5°	1	1	1	0	0	0	0	0	0	0	0
15°	1	1	1	0	0	0	0	0	0	0	0
12.5°	1	1	1	1	0	0	0	0	0	0	0
10°	1	1	1	1	0	0	0	0	0	0	0
7.5°	1	1	1	1	0	0	0	0	0	0	0
5°	1	1	1	1	0	0	0	0	0	0	0
2.5°	1	1	1	1	0	0	0	0	0	0	0
0°	1	1	1	1	0	0	0	0	0	0	0
-2.5°	1	1	1	1	0	0	0	0	0	0	0
-5°	1	1	1	1	0	0	0	0	0	0	0
-7.5°	1	1	1	1	0	0	0	0	0	0	0
-10°	1	1	1	1	0	0	0	0	0	0	0
-12.5°	1	1	1	1	0	0	0	0	0	0	0
-15°	1	1	1	0	0	0	0	0	0	0	0
-17.5°	1	1	1	0	0	0	0	0	0	0	0
-20°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	1	1	1	0	0	0	0	0	0	0	0
-25°	1	1	0	0	0	0	0	0	0	0	0
-27.5°	1	1	0	0	0	0	0	0	0	0	0
-30°	1	1	0	0	0	0	0	0	0	0	0
-32.5°	1	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-26 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 206-8LED4010-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)