

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: LUMIERE

Report Number: P277817

Luminaire Tested: 696-8LED2710-12-BK-OSL

Issue Date: 3/3/2020

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-2019
 Report Number: P277817
 Test Lab: INNOVATION CENTER(G2)
 Issue Date: 3/3/2020
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: LUMIERE
 Catalog Number: 696-8LED2710-12-BK-OSL
 Description: BOCA 696, 8 W, 2700K CCT, 10 DEGREE SPOT OPTIC,
 FLUSH HOOD BLACK, OVERALL SPREAD LENS
 Light Source: (1) SORAA 2700K 90 CRI LED
 SM16-07-10D-927-03
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 320.6 lumens
 Efficiency: N/A
 Efficacy: 40.6 lumens/watt
 N/A
 Luminous Opening: Circular (Dia: 0.17' x H: 0')
 CIE Type: Indirect

Input Watts (W): 7.9
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 24 FT




Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P277817

CATALOG NUMBER: 696-8LED2710-12-BK-OSL

Luminous Intensity Polar Plot



TEST NUMBER: P277817

CATALOG NUMBER: 696-8LED2710-12-BK-OSL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°
95°	5445
100°	2733
105°	5500
110°	7088
115°	9114
120°	9601
125°	10941
130°	11978
135°	12902
140°	14459
145°	15839
150°	20032
155°	27637
160°	46636
165°	171921
170°	521084
175°	820096

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 0°
 Luminance: 0 cd/sqm

TEST NUMBER: P277817

CATALOG NUMBER: 696-8LED2710-12-BK-OSL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.7	0.2
100°-110°	3.1	1.0
110°-120°	7.6	2.4
120°-130°	11.4	3.5
130°-140°	14.6	4.5
140°-150°	17.1	5.3
150°-160°	24.5	7.6
160°-170°	104.7	32.7
170°-180°	137.0	42.7
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	11.3	3.5
90°-150°	54.3	16.9
90°-180°	321.0	100.1
0°-180°	320.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
90°	0	
95°	1	1
105°	3	3
115°	8	8
125°	13	11
135°	18	15
145°	26	17
155°	51	25
165°	337	105
175°	1656	137
180°	1645	

TEST NUMBER: P277817

CATALOG NUMBER: 696-8LED2710-12-BK-OSL

CANDELA DISTRIBUTION (FULL):

	0°
90°	0.0
92.5°	0.0
95°	1.0
97.5°	1.0
100°	1.0
102.5°	1.9
105°	2.9
107.5°	4.0
110°	4.9
112.5°	6.8
115°	7.8
117.5°	8.8
120°	9.7
122.5°	11.8
125°	12.7
127.5°	13.7
130°	15.6
132.5°	17.5
135°	18.5
137.5°	20.5
140°	22.5
142.5°	24.4
145°	26.3
147.5°	30.2
150°	35.2
151°	38.1
152°	40.9
153°	43.9
154°	46.8
155°	50.8
156°	55.6
157°	61.5
158°	68.3
159°	77.1
160°	88.8
161°	105.4
162°	132.8
163°	176.6
164°	243.9
165°	336.6
166°	452.8
167°	588.4
168°	737.6
169°	886.0
170°	1040.1

TEST NUMBER: P277817
CATALOG NUMBER: 696-8LED2710-12-BK-OSL

CANDELA DISTRIBUTION (continued):

	0°
171°	1193.4
172°	1337.8
173°	1470.4
174°	1578.7
175°	1655.9
176°	1696.8
177°	1700.8
178°	1681.2
179°	1655.9
180°	1645.1

(END OF REPORT)