

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: LUMIERE

Report Number: P27782[\_3000K

Luminaire Tested: 696-8LED2736-12-BK

Issue Date: 3/3/2020

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-2019  
 Report Number: P27782[\_3000K  
 Test Lab: INNOVATION CENTER(G2)  
 Issue Date: 3/3/2020  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: LUMIERE  
 Catalog Number: 696-8LED2736-12-BK  
 Description: BOCA 696, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,  
 FLUSH HOOD BLACK  
 Light Source: (1) SORAA 3000K 90 CRI LED  
 SM16-07-36D-930-03  
 Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 413.7 lumens  
 Efficiency: N/A  
 Efficacy: 53.7 lumens/watt  
 N/A  
 Luminous Opening: Circular (Dia: 0.17' x H: 0')  
 CIE Type: Indirect


Input Watts (W): 7.7  
 Input Voltage (V): NR  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 24 FT



Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	P3	10/30/2015	4/30/2016
Power Meter	IN0214	1/12/2016	1/12/2017
AC Power Source	IN0062	1/12/2016	1/12/2017
DC Power Supply	--	--	--
Room Thermometer	IN0145	1/13/2016	1/13/2017

TEST NUMBER: P27782\_3000K  
CATALOG NUMBER: 696-8LED2736-12-BK

### Luminous Intensity Polar Plot



TEST NUMBER: P27782[\_3000K  
 CATALOG NUMBER: 696-8LED2736-12-BK

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0																												
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0																												
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0																												
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0																												
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0																												
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0																												
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0																												
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0																												
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0																												
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0																												
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
95°	0
100°	0
105°	1893
110°	2880
115°	3490
120°	4042
125°	3523
130°	4676
135°	5644
140°	9133
145°	16410
150°	33383
155°	94672
160°	218212
165°	369798
170°	485849
175°	549361

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 0°  
 Luminance: 0 cd/sqm

TEST NUMBER: P27782[\_3000K

CATALOG NUMBER: 696-8LED2736-12-BK

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	1.3	0.3
110°-120°	3.0	0.7
120°-130°	4.1	1.0
130°-140°	6.8	1.6
140°-150°	18.4	4.4
150°-160°	85.3	20.6
160°-170°	193.2	46.7
170°-180°	101.6	24.6
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	4.3	1.0
90°-150°	33.5	8.1
90°-180°	414.0	100.1
0°-180°	413.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
90°	0	
95°	0	0
105°	1	1
115°	3	3
125°	4	4
135°	8	7
145°	27	18
155°	174	85
165°	724	193
175°	1109	102
180°	1157	

TEST NUMBER: P27782[\_3000K  
CATALOG NUMBER: 696-8LED2736-12-BK

**CANDELA DISTRIBUTION (FULL):**

	0°
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	1.0
105°	1.0
107.5°	2.0
110°	2.0
112.5°	3.0
115°	3.0
117.5°	3.0
120°	4.1
122.5°	4.1
125°	4.1
127.5°	5.1
130°	6.1
132.5°	7.1
135°	8.1
137.5°	10.1
140°	14.2
142.5°	19.2
145°	27.2
147.5°	37.4
150°	58.6
151°	72.8
152°	92.0
153°	115.3
154°	142.6
155°	173.9
156°	209.4
157°	251.8
158°	301.3
159°	355.9
160°	415.6
161°	478.3
162°	543.0
163°	606.7
164°	667.4
165°	724.0
166°	775.6
167°	827.1
168°	876.7
169°	924.3
170°	969.8

TEST NUMBER: P27782[\_3000K  
CATALOG NUMBER: 696-8LED2736-12-BK

**CANDELA DISTRIBUTION (continued):**

	0°
171°	1008.1
172°	1042.6
173°	1071.9
174°	1093.1
175°	1109.2
176°	1122.4
177°	1132.5
178°	1141.6
179°	1150.8
180°	1156.7

(END OF REPORT)