

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P246979

Luminaire Tested: **203-SS-8LED3025-12-CS-DIFF**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246979
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-40)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3025-12-CS-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, DIFFUSED LENS
Light Source: (1) SORAA 3000K 90 CRI LED
SM16-07-25D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 249.5 lumens
Efficiency: N/A
Efficacy: 32.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246979
CATALOG NUMBER: 203-SS-8LED3025-12-CS-DIFF

Luminous Intensity Polar Plot





TEST NUMBER: P246979

CATALOG NUMBER: 203-SS-8LED3025-12-CS-DIFF

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	89
3	105	99	94	91	103	98	93	90	95	92	89		93	90	87		90	88	86	85
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83	80	78	76
6	92	85	79	76	91	84	79	75	82	78	75		81	77	74		80	77	74	73
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77	73	71	69
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74	70	68	66
9	82	74	69	65	81	73	69	65	73	68	65		72	68	65		71	67	65	64
10	79	71	66	63	78	71	66	63	70	65	62		69	65	62		68	65	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	314924
5°	291958
10°	235816
15°	172951
20°	116822
25°	74308
30°	43412
35°	22948
40°	12559
45°	6838
50°	4759
55°	3785
60°	2664
65°	2101
70°	1298
75°	1716
80°	2557
85°	0



TEST NUMBER: P246979

CATALOG NUMBER: 203-SS-8LED3025-12-CS-DIFF

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	21.0
10°-20°	92.8	37.2
20°-30°	63.1	25.3
30°-40°	25.6	10.3
40°-50°	8.5	3.4
50°-60°	3.9	1.6
60°-70°	2.0	0.8
70°-80°	1.0	0.4
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	208.3	83.5
0°-40°	233.9	93.8
0°-60°	246.4	98.8
0°-90°	249.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	249.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	638	
5°	590	52
15°	339	93
25°	136	63
35°	38	26
45°	10	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P246979

CATALOG NUMBER: 203-SS-8LED3025-12-CS-DIFF

CANDELA DISTRIBUTION (FULL):

0°	
0°	638.3
1°	633.8
2°	626.8
3°	617.0
4°	605.5
5°	589.5
6°	570.9
7°	548.7
8°	523.9
9°	497.3
10°	470.7
11°	442.4
12°	415.8
13°	389.2
14°	363.5
15°	338.6
16°	312.9
17°	289.0
18°	265.9
19°	244.7
20°	222.5
21°	202.1
22°	184.4
23°	166.7
24°	150.7
25°	136.5
26°	122.3
27°	109.9
28°	98.4
29°	86.9
30°	76.2
32.5°	54.1
35°	38.1
37.5°	27.5
40°	19.5
42.5°	14.2
45°	9.8
47.5°	8.0
50°	6.2
52.5°	5.3
55°	4.4
57.5°	3.5
60°	2.7
62.5°	2.7
65°	1.8



TEST NUMBER: P246979
CATALOG NUMBER: 203-SS-8LED3025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.8
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)