

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-34

Luminaire Tested: **203-SS-8LED4036-12-BK-LVR**

Test Date: 04/06/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-34
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-34)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4036-12-BK-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK, HEX CELL LOUVER
Light Source: (1) SORAA 4000K 95 CRI LED
SM16-07-36D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 252.1 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.48
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.8
Input Voltage (V): 12.0
Input Current (Ain): 0.680
Voltage Rise (V): NR
Power Factor: 0.9908
Total Harmonic Distortion (THDi): 27.3%
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): 24.9
Test Distance: 25 FT



TEST NUMBER: G2-1802-569-34
CATALOG NUMBER: 203-SS-8LED4036-12-BK-LVR

Luminous Intensity Polar Plot





TEST NUMBER: G2-1802-569-34

CATALOG NUMBER: 203-SS-8LED4036-12-BK-LVR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	83	79	77	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	74	80	76	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	491406
5°	444252
10°	355202
15°	238025
20°	121810
25°	40284
30°	11394
35°	4818
40°	2576
45°	1395
50°	768
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: G2-1802-569-34

CATALOG NUMBER: 203-SS-8LED4036-12-BK-LVR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	31.6
10°-20°	125.2	49.7
20°-30°	39.7	15.8
30°-40°	5.6	2.2
40°-50°	1.6	0.6
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	244.7	97.1
0°-40°	250.3	99.3
0°-60°	252.1	100.0
0°-90°	252.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	252.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	996	
5°	897	80
15°	466	125
25°	74	40
35°	8	6
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: G2-1802-569-34

CATALOG NUMBER: 203-SS-8LED4036-12-BK-LVR

CANDELA DISTRIBUTION (FULL):

0°	
0°	996
1°	985
2°	965
3°	943
4°	921
5°	897
6°	869
7°	837
8°	797
9°	754
10°	709
11°	660
12°	609
13°	560
14°	512
15°	466
16°	420
17°	373
18°	325
19°	278
20°	232
21°	190
22°	154
23°	123
24°	95
25°	74
26°	58
27°	43
28°	34
29°	25
30°	20
32.5°	12
35°	8
37.5°	5
40°	4
42.5°	3
45°	2
47.5°	1
50°	1
52.5°	0
55°	0
57.5°	0
60°	0
62.5°	0
65°	0



TEST NUMBER: G2-1802-569-34

CATALOG NUMBER: 203-SS-8LED4036-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)