

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED2710-12-CS**

Issue Date: 3/3/2020

Test Information


Test Method: LM-79-08
Report Number: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (Pxxxxxx)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2710-12-CS
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER
Light Source: (1) SORAA 2700K 95 CRI 10°NSP LED
SM16-07-10D-927-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	2H x 2V
Luminaire Lumens:	269.8 lumens	Max Intensity:	4611.9 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	36.0 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	12.5°H x 12.5°V	Field Angle (10%):	19.2°H x 19.2°V
Beam Lumens:	125.7 lumens	Field Lumens:	186.5 lumens
Beam Efficiency:	46.6%	Field Efficiency:	69.1%
Input Watts (W):	7.5		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-CS

Iso-Candela Plot




REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.1	0.2	0.3	0.3	0.4	0.4	0.3	0.3	0.2	0.1	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.3	0.4	0.5	0.6	0.6	0.5	0.4	0.3	0.1	0.0	0.0		
30	0.0	0.0	0.1	0.2	0.4	0.5	0.7	0.9	0.9	0.7	0.5	0.4	0.2	0.1	0.0	0.0	
20		0.0	0.1	0.3	0.4	0.7	1.4	3.5	3.5	1.4	0.7	0.4	0.3	0.1	0.0		
10	0.0	0.0	0.1	0.3	0.5	0.8	3.4	49.1	49.1	3.4	0.8	0.5	0.3	0.1	0.0	0.0	
0		0.0	0.1	0.3	0.5	0.8	3.4	49.1	49.1	3.4	0.8	0.5	0.3	0.1	0.0		
-10	0.0	0.0	0.1	0.3	0.4	0.7	1.4	3.5	3.5	1.4	0.7	0.4	0.3	0.1	0.0	0.0	
-20		0.0	0.1	0.2	0.4	0.5	0.7	0.9	0.9	0.7	0.5	0.4	0.2	0.1	0.0		
-30	0.0	0.0	0.0	0.1	0.3	0.4	0.5	0.6	0.6	0.5	0.4	0.3	0.1	0.0	0.0	0.0	
-40		0.0	0.0	0.1	0.2	0.3	0.3	0.4	0.4	0.3	0.3	0.2	0.1	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	


REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-CS

Luminous Intensity Polar Plot



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

Luminous Intensity Plot



Beam:
 H Angle: 12.5°
 V Angle: 12.5°
 Lumens: 125.7
 Efficiency: 46.6%

Field:
 H Angle: 19.2°
 V Angle: 19.2°
 Lumens: 186.5
 Efficiency: 69.1%

Spill:
 Lumens: 83.3
 Efficiency: 30.9%

— Vertical Distribution through 0-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	1
48.75°	0	0	0	0	0	0	0	0	0	0	1
47.5°	0	0	0	0	0	0	0	0	0	1	1
46.25°	0	0	0	0	0	0	0	0	0	1	1
45°	0	0	0	0	0	0	0	0	1	1	1
43.75°	0	0	0	0	0	0	0	0	1	1	1
42.5°	0	0	0	0	0	0	0	0	1	1	1
41.25°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
38.75°	0	0	0	0	0	0	1	1	1	1	1
37.5°	0	0	0	0	0	0	1	1	1	1	1
36.25°	0	0	0	0	0	0	1	1	1	1	1
35°	0	0	0	0	0	0	1	1	1	1	1



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	1	1	1	1	1	1
32.5°	0	0	0	0	0	1	1	1	1	1	1
31.25°	0	0	0	0	0	1	1	1	1	1	1
30°	0	0	0	0	0	1	1	1	1	1	1
28.75°	0	0	0	0	0	1	1	1	1	1	1
27.5°	0	0	0	0	1	1	1	1	1	1	1
26.25°	0	0	0	0	1	1	1	1	1	1	1
25°	0	0	0	0	1	1	1	1	1	1	1
23.75°	0	0	0	0	1	1	1	1	1	1	1
22.5°	0	0	0	0	1	1	1	1	1	1	1
21.25°	0	0	0	0	1	1	1	1	1	1	1
20°	0	0	0	1	1	1	1	1	1	1	1
18.75°	0	0	0	1	1	1	1	1	1	1	1
17.5°	0	0	0	1	1	1	1	1	1	1	1
16.25°	0	0	0	1	1	1	1	1	1	1	1
15°	0	0	0	1	1	1	1	1	1	1	1
13.75°	0	0	0	1	1	1	1	1	1	1	1
12.5°	0	0	0	1	1	1	1	1	1	1	1
11.25°	0	0	0	1	1	1	1	1	1	1	1
10°	0	0	0	1	1	1	1	1	1	1	1
8.75°	0	0	0	1	1	1	1	1	1	1	1
7.5°	0	0	0	1	1	1	1	1	1	1	1
6.25°	0	0	0	1	1	1	1	1	1	1	1
5°	0	0	0	1	1	1	1	1	1	1	1
3.75°	0	0	0	1	1	1	1	1	1	1	1
2.5°	0	0	0	1	1	1	1	1	1	1	1
1.25°	0	0	0	1	1	1	1	1	1	1	1
0°	0	0	0	1	1	1	1	1	1	1	1
-1.25°	0	0	0	1	1	1	1	1	1	1	1
-2.5°	0	0	0	1	1	1	1	1	1	1	1
-3.75°	0	0	0	1	1	1	1	1	1	1	1
-5°	0	0	0	1	1	1	1	1	1	1	1
-6.25°	0	0	0	1	1	1	1	1	1	1	1
-7.5°	0	0	0	1	1	1	1	1	1	1	1
-8.75°	0	0	0	1	1	1	1	1	1	1	1
-10°	0	0	0	1	1	1	1	1	1	1	1
-11.25°	0	0	0	1	1	1	1	1	1	1	1
-12.5°	0	0	0	1	1	1	1	1	1	1	1
-13.75°	0	0	0	1	1	1	1	1	1	1	1
-15°	0	0	0	1	1	1	1	1	1	1	1
-16.25°	0	0	0	1	1	1	1	1	1	1	1
-17.5°	0	0	0	1	1	1	1	1	1	1	1
-18.75°	0	0	0	1	1	1	1	1	1	1	1
-20°	0	0	0	1	1	1	1	1	1	1	1
-21.25°	0	0	0	0	1	1	1	1	1	1	1



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	1	1	1	1	1	1	1
-23.75°	0	0	0	0	1	1	1	1	1	1	1
-25°	0	0	0	0	1	1	1	1	1	1	1
-26.25°	0	0	0	0	1	1	1	1	1	1	1
-27.5°	0	0	0	0	1	1	1	1	1	1	1
-28.75°	0	0	0	0	0	1	1	1	1	1	1
-30°	0	0	0	0	0	1	1	1	1	1	1
-31.25°	0	0	0	0	0	1	1	1	1	1	1
-32.5°	0	0	0	0	0	1	1	1	1	1	1
-33.75°	0	0	0	0	0	1	1	1	1	1	1
-35°	0	0	0	0	0	0	1	1	1	1	1
-36.25°	0	0	0	0	0	0	1	1	1	1	1
-37.5°	0	0	0	0	0	0	1	1	1	1	1
-38.75°	0	0	0	0	0	0	1	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	0	1	1	1
-43.75°	0	0	0	0	0	0	0	0	1	1	1
-45°	0	0	0	0	0	0	0	0	1	1	1
-46.25°	0	0	0	0	0	0	0	0	0	1	1
-47.5°	0	0	0	0	0	0	0	0	0	1	1
-48.75°	0	0	0	0	0	0	0	0	0	0	1
-50°	0	0	0	0	0	0	0	0	0	0	1
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	1
62.5°	0	0	0	0	0	0	0	0	0	1	1
61.25°	0	0	0	0	0	0	0	1	1	1	1
60°	0	0	0	0	0	0	1	1	1	1	1
58.75°	0	0	0	0	0	1	1	1	1	1	1
57.5°	0	0	0	0	1	1	1	1	1	1	1
56.25°	0	0	0	1	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	1	1
53.75°	0	1	1	1	1	1	1	1	1	1	1
52.5°	0	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	2
43.75°	1	1	1	1	1	1	1	1	1	2	2
42.5°	1	1	1	1	1	1	1	1	2	2	2
41.25°	1	1	1	1	1	1	1	1	2	2	2
40°	1	1	1	1	1	1	1	2	2	2	3
38.75°	1	1	1	1	1	1	1	2	2	2	3
37.5°	1	1	1	1	1	1	2	2	2	3	3
36.25°	1	1	1	1	1	1	2	2	2	3	4
35°	1	1	1	1	1	2	2	2	3	3	4



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	1	2	2	3	3	4	4
32.5°	1	1	1	1	2	2	2	3	3	4	5
31.25°	1	1	1	1	2	2	2	3	4	4	5
30°	1	1	1	2	2	2	3	3	4	5	6
28.75°	1	1	1	2	2	2	3	4	4	5	6
27.5°	1	1	1	2	2	3	3	4	5	5	6
26.25°	1	1	1	2	2	3	3	4	5	6	7
25°	1	1	2	2	2	3	4	5	5	6	7
23.75°	1	1	2	2	3	3	4	5	6	6	7
22.5°	1	1	2	2	3	3	4	5	6	7	7
21.25°	1	1	2	2	3	4	4	5	6	7	8
20°	1	2	2	2	3	4	5	6	6	7	8
18.75°	1	2	2	2	3	4	5	6	7	7	8
17.5°	1	2	2	3	3	4	5	6	7	8	8
16.25°	1	2	2	3	4	4	5	6	7	8	8
15°	1	2	2	3	4	5	5	6	7	8	9
13.75°	1	2	2	3	4	5	6	6	7	8	9
12.5°	2	2	2	3	4	5	6	7	7	8	9
11.25°	2	2	2	3	4	5	6	7	8	8	9
10°	2	2	3	3	4	5	6	7	8	8	9
8.75°	2	2	3	3	4	5	6	7	8	8	9
7.5°	2	2	3	3	4	5	6	7	8	9	9
6.25°	2	2	3	3	4	5	6	7	8	9	9
5°	2	2	3	4	4	5	6	7	8	9	9
3.75°	2	2	3	4	5	5	6	7	8	9	9
2.5°	2	2	3	4	5	5	6	7	8	9	9
1.25°	2	2	3	4	5	5	6	7	8	9	9
0°	2	2	3	4	5	6	6	7	8	9	9
-1.25°	2	2	3	4	5	5	6	7	8	9	9
-2.5°	2	2	3	4	5	5	6	7	8	9	9
-3.75°	2	2	3	4	5	5	6	7	8	9	9
-5°	2	2	3	4	4	5	6	7	8	9	9
-6.25°	2	2	3	3	4	5	6	7	8	9	9
-7.5°	2	2	3	3	4	5	6	7	8	9	9
-8.75°	2	2	3	3	4	5	6	7	8	8	9
-10°	2	2	3	3	4	5	6	7	8	8	9
-11.25°	2	2	2	3	4	5	6	7	8	8	9
-12.5°	2	2	2	3	4	5	6	7	7	8	9
-13.75°	1	2	2	3	4	5	6	6	7	8	9
-15°	1	2	2	3	4	5	5	6	7	8	9
-16.25°	1	2	2	3	4	4	5	6	7	8	8
-17.5°	1	2	2	3	3	4	5	6	7	8	8
-18.75°	1	2	2	2	3	4	5	6	7	7	8
-20°	1	2	2	2	3	4	5	6	6	7	8
-21.25°	1	1	2	2	3	4	4	5	6	7	8



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	1	2	2	3	3	4	5	6	7	7
-23.75°	1	1	2	2	3	3	4	5	6	6	7
-25°	1	1	2	2	2	3	4	5	5	6	7
-26.25°	1	1	1	2	2	3	3	4	5	6	7
-27.5°	1	1	1	2	2	3	3	4	5	5	6
-28.75°	1	1	1	2	2	2	3	4	4	5	6
-30°	1	1	1	2	2	2	3	3	4	5	6
-31.25°	1	1	1	1	2	2	2	3	4	4	5
-32.5°	1	1	1	1	2	2	2	3	3	4	5
-33.75°	1	1	1	1	1	2	2	3	3	4	4
-35°	1	1	1	1	1	2	2	2	3	3	4
-36.25°	1	1	1	1	1	1	2	2	2	3	4
-37.5°	1	1	1	1	1	1	2	2	2	3	3
-38.75°	1	1	1	1	1	1	1	2	2	2	3
-40°	1	1	1	1	1	1	1	2	2	2	3
-41.25°	1	1	1	1	1	1	1	1	2	2	2
-42.5°	1	1	1	1	1	1	1	1	2	2	2
-43.75°	1	1	1	1	1	1	1	1	1	2	2
-45°	1	1	1	1	1	1	1	1	1	1	2
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	0	1	1	1	1	1	1	1	1	1	1
-53.75°	0	1	1	1	1	1	1	1	1	1	1
-55°	0	0	1	1	1	1	1	1	1	1	1
-56.25°	0	0	0	1	1	1	1	1	1	1	1
-57.5°	0	0	0	0	1	1	1	1	1	1	1
-58.75°	0	0	0	0	0	1	1	1	1	1	1
-60°	0	0	0	0	0	0	1	1	1	1	1
-61.25°	0	0	0	0	0	0	0	1	1	1	1
-62.5°	0	0	0	0	0	0	0	0	0	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	1	1	1
67.5°	0	0	0	0	0	0	1	1	1	1	1
66.25°	0	0	0	1	1	1	1	1	1	1	1
65°	0	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	2	2
53.75°	1	1	1	1	1	1	1	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	1	2	2	2	2	2	3	3
50°	1	1	1	2	2	2	2	3	3	3	4
48.75°	1	1	2	2	2	2	3	3	3	4	4
47.5°	1	2	2	2	2	3	3	4	4	5	5
46.25°	2	2	2	2	3	3	4	4	5	5	6
45°	2	2	2	3	3	4	4	5	5	6	6
43.75°	2	2	3	3	4	4	5	5	6	6	7
42.5°	2	3	3	4	4	5	5	6	6	7	7
41.25°	3	3	4	4	5	5	6	7	7	8	8
40°	3	4	4	5	5	6	7	7	8	8	8
38.75°	3	4	5	5	6	6	7	8	8	8	9
37.5°	4	5	5	6	6	7	8	8	8	9	9
36.25°	4	5	6	6	7	7	8	8	9	9	10
35°	5	5	6	7	7	8	8	9	9	10	11



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	5	6	6	7	8	8	9	9	10	11	11
32.5°	6	6	7	8	8	9	9	9	10	11	12
31.25°	6	7	7	8	8	9	9	10	11	12	12
30°	6	7	8	8	9	9	10	11	12	12	13
28.75°	7	7	8	8	9	9	10	12	12	12	13
27.5°	7	8	8	9	9	10	11	12	12	13	13
26.25°	7	8	8	9	10	11	12	12	13	13	14
25°	8	8	9	9	10	11	12	12	13	14	14
23.75°	8	8	9	9	11	12	12	13	13	14	15
22.5°	8	9	9	10	11	12	12	13	14	14	15
21.25°	8	9	9	10	12	12	13	13	14	15	15
20°	8	9	10	11	12	12	13	14	14	15	15
18.75°	9	9	10	11	12	13	13	14	15	15	15
17.5°	9	9	11	12	12	13	13	14	15	15	16
16.25°	9	10	11	12	12	13	14	14	15	15	16
15°	9	10	11	12	13	13	14	15	15	16	17
13.75°	9	10	12	12	13	13	14	15	15	16	17
12.5°	9	11	12	12	13	14	14	15	15	16	18
11.25°	9	11	12	12	13	14	15	15	15	17	18
10°	10	11	12	12	13	14	15	15	16	17	18
8.75°	10	11	12	13	13	14	15	15	16	17	18
7.5°	10	11	12	13	13	14	15	15	16	18	19
6.25°	10	12	12	13	13	14	15	15	16	18	19
5°	10	12	12	13	14	14	15	15	17	18	19
3.75°	10	12	12	13	14	15	15	15	17	18	19
2.5°	10	12	12	13	14	15	15	15	17	18	19
1.25°	10	12	12	13	14	15	15	15	17	18	19
0°	11	12	12	13	14	15	15	16	17	18	19
-1.25°	10	12	12	13	14	15	15	15	17	18	19
-2.5°	10	12	12	13	14	15	15	15	17	18	19
-3.75°	10	12	12	13	14	15	15	15	17	18	19
-5°	10	12	12	13	14	14	15	15	17	18	19
-6.25°	10	12	12	13	13	14	15	15	16	18	19
-7.5°	10	11	12	13	13	14	15	15	16	18	19
-8.75°	10	11	12	13	13	14	15	15	16	17	18
-10°	10	11	12	12	13	14	15	15	16	17	18
-11.25°	9	11	12	12	13	14	15	15	15	17	18
-12.5°	9	11	12	12	13	14	14	15	15	16	18
-13.75°	9	10	12	12	13	13	14	15	15	16	17
-15°	9	10	11	12	13	13	14	15	15	16	17
-16.25°	9	10	11	12	12	13	14	14	15	15	16
-17.5°	9	9	11	12	12	13	13	14	15	15	16
-18.75°	9	9	10	11	12	13	13	14	15	15	15
-20°	8	9	10	11	12	12	13	14	14	15	15
-21.25°	8	9	9	10	12	12	13	13	14	15	15



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	8	9	9	10	11	12	12	13	14	14	15
-23.75°	8	8	9	9	11	12	12	13	13	14	15
-25°	8	8	9	9	10	11	12	12	13	14	14
-26.25°	7	8	8	9	10	11	12	12	13	13	14
-27.5°	7	8	8	9	9	10	11	12	12	13	13
-28.75°	7	7	8	8	9	9	10	12	12	12	13
-30°	6	7	8	8	9	9	10	11	12	12	13
-31.25°	6	7	7	8	8	9	9	10	11	12	12
-32.5°	6	6	7	8	8	9	9	9	10	11	12
-33.75°	5	6	6	7	8	8	9	9	10	11	11
-35°	5	5	6	7	7	8	8	9	9	10	11
-36.25°	4	5	6	6	7	7	8	8	9	9	10
-37.5°	4	5	5	6	6	7	8	8	8	9	9
-38.75°	3	4	5	5	6	6	7	8	8	8	9
-40°	3	4	4	5	5	6	7	7	8	8	8
-41.25°	3	3	4	4	5	5	6	7	7	8	8
-42.5°	2	3	3	4	4	5	5	6	6	7	7
-43.75°	2	2	3	3	4	4	5	5	6	6	7
-45°	2	2	2	3	3	4	4	5	5	6	6
-46.25°	2	2	2	2	3	3	4	4	5	5	6
-47.5°	1	2	2	2	2	3	3	4	4	5	5
-48.75°	1	1	2	2	2	2	3	3	3	4	4
-50°	1	1	1	2	2	2	2	3	3	3	4
-51.25°	1	1	1	1	2	2	2	2	2	3	3
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	1	2	2	2	2
-55°	1	1	1	1	1	1	1	1	1	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	0	1	1	1	1	1	1	1	1
-67.5°	0	0	0	0	0	0	1	1	1	1	1
-68.75°	0	0	0	0	0	0	0	0	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	1	1	1	1	1
70°	0	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	2	2	2
58.75°	1	1	1	1	2	2	2	2	2	2	2
57.5°	1	1	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	2	2	2	3	3	3	3	3
55°	2	2	2	2	3	3	3	3	4	4	4
53.75°	2	3	3	3	3	4	4	4	5	5	5
52.5°	3	3	3	4	4	4	5	5	5	6	6
51.25°	3	4	4	4	5	5	5	6	6	6	7
50°	4	4	5	5	6	6	6	7	7	7	7
48.75°	5	5	6	6	6	7	7	7	8	8	8
47.5°	5	6	6	7	7	7	8	8	8	8	9
46.25°	6	6	7	7	8	8	8	8	9	9	9
45°	7	7	8	8	8	8	9	9	9	9	10
43.75°	7	8	8	8	9	9	9	10	10	11	11
42.5°	8	8	9	9	9	9	10	11	11	12	12
41.25°	8	9	9	9	10	10	11	12	12	12	12
40°	9	9	9	10	11	12	12	12	12	13	13
38.75°	9	10	10	11	12	12	12	13	13	13	14
37.5°	10	11	11	12	12	12	13	13	14	14	14
36.25°	11	11	12	12	13	13	13	14	14	15	15
35°	12	12	12	13	13	13	14	14	15	15	15



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	12	12	13	13	14	14	15	15	15	15	16
32.5°	12	13	13	14	14	15	15	15	15	16	17
31.25°	13	13	14	14	15	15	15	16	16	17	18
30°	13	14	14	15	15	15	16	17	17	18	19
28.75°	13	14	15	15	15	16	17	18	18	19	19
27.5°	14	15	15	15	16	17	18	18	19	19	19
26.25°	14	15	15	16	17	18	18	19	19	19	20
25°	15	15	15	16	17	18	19	19	19	20	21
23.75°	15	15	16	17	18	19	19	19	20	21	21
22.5°	15	16	17	18	19	19	19	20	21	21	22
21.25°	15	16	18	18	19	19	20	20	21	22	22
20°	16	17	18	19	19	20	20	21	22	22	23
18.75°	16	18	18	19	19	20	21	21	22	23	24
17.5°	17	18	19	19	20	20	21	22	23	24	25
16.25°	18	18	19	19	20	21	22	22	23	25	26
15°	18	19	19	20	20	21	22	23	24	26	27
13.75°	18	19	19	20	21	22	22	24	25	27	28
12.5°	19	19	20	20	21	22	23	24	26	28	29
11.25°	19	19	20	21	21	22	23	25	27	28	30
10°	19	19	20	21	22	23	24	26	27	29	31
8.75°	19	19	20	21	22	23	25	26	28	30	33
7.5°	19	20	20	21	22	23	25	27	29	31	34
6.25°	19	20	21	21	22	24	26	27	29	31	34
5°	19	20	21	22	23	24	26	28	29	32	35
3.75°	19	20	21	22	23	24	26	28	30	33	36
2.5°	19	20	21	22	23	25	26	28	30	33	36
1.25°	19	20	21	22	23	25	26	28	30	33	36
0°	19	20	21	22	23	25	27	28	30	33	37
-1.25°	19	20	21	22	23	25	26	28	30	33	36
-2.5°	19	20	21	22	23	25	26	28	30	33	36
-3.75°	19	20	21	22	23	24	26	28	30	33	36
-5°	19	20	21	22	23	24	26	28	29	32	35
-6.25°	19	20	21	21	22	24	26	27	29	31	34
-7.5°	19	20	20	21	22	23	25	27	29	31	34
-8.75°	19	19	20	21	22	23	25	26	28	30	33
-10°	19	19	20	21	22	23	24	26	27	29	31
-11.25°	19	19	20	21	21	22	23	25	27	28	30
-12.5°	19	19	20	20	21	22	23	24	26	28	29
-13.75°	18	19	19	20	21	22	22	24	25	27	28
-15°	18	19	19	20	20	21	22	23	24	26	27
-16.25°	18	18	19	19	20	21	22	22	23	25	26
-17.5°	17	18	19	19	20	20	21	22	23	24	25
-18.75°	16	18	18	19	19	20	21	21	22	23	24
-20°	16	17	18	19	19	20	20	21	22	22	23
-21.25°	15	16	18	18	19	19	20	20	21	22	22



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	15	16	17	18	19	19	19	20	21	21	22
-23.75°	15	15	16	17	18	19	19	19	20	21	21
-25°	15	15	15	16	17	18	19	19	19	20	21
-26.25°	14	15	15	16	17	18	18	19	19	19	20
-27.5°	14	15	15	15	16	17	18	18	19	19	19
-28.75°	13	14	15	15	15	16	17	18	18	19	19
-30°	13	14	14	15	15	15	16	17	17	18	19
-31.25°	13	13	14	14	15	15	15	16	16	17	18
-32.5°	12	13	13	14	14	15	15	15	15	16	17
-33.75°	12	12	13	13	14	14	15	15	15	15	16
-35°	12	12	12	13	13	13	14	14	15	15	15
-36.25°	11	11	12	12	13	13	13	14	14	15	15
-37.5°	10	11	11	12	12	12	13	13	14	14	14
-38.75°	9	10	10	11	12	12	12	13	13	13	14
-40°	9	9	9	10	11	12	12	12	12	13	13
-41.25°	8	9	9	9	10	10	11	12	12	12	12
-42.5°	8	8	9	9	9	9	10	11	11	12	12
-43.75°	7	8	8	8	9	9	9	10	10	11	11
-45°	7	7	8	8	8	8	9	9	9	9	10
-46.25°	6	6	7	7	8	8	8	8	9	9	9
-47.5°	5	6	6	7	7	7	8	8	8	8	9
-48.75°	5	5	6	6	6	7	7	7	8	8	8
-50°	4	4	5	5	6	6	6	7	7	7	7
-51.25°	3	4	4	4	5	5	5	6	6	6	7
-52.5°	3	3	3	4	4	4	5	5	5	6	6
-53.75°	2	3	3	3	3	4	4	4	5	5	5
-55°	2	2	2	2	3	3	3	3	4	4	4
-56.25°	2	2	2	2	2	2	3	3	3	3	3
-57.5°	1	1	2	2	2	2	2	2	2	3	3
-58.75°	1	1	1	1	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	1	1	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	1	1	1	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	2	2	2	2
61.25°	1	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	3	3
58.75°	2	2	2	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	4	4	4	4	4	4	4
56.25°	4	4	4	4	4	5	5	5	5	5	5
55°	4	5	5	5	5	5	6	6	6	6	6
53.75°	5	6	6	6	6	6	6	7	7	7	7
52.5°	6	6	7	7	7	7	7	7	8	8	8
51.25°	7	7	7	8	8	8	8	8	8	8	8
50°	8	8	8	8	8	9	9	9	9	9	9
48.75°	8	8	9	9	9	9	9	9	9	10	10
47.5°	9	9	9	9	10	10	10	11	11	11	11
46.25°	9	10	10	11	11	11	12	12	12	12	12
45°	10	11	11	12	12	12	12	12	12	12	13
43.75°	12	12	12	12	12	13	13	13	13	13	13
42.5°	12	12	13	13	13	13	13	14	14	14	14
41.25°	13	13	13	13	14	14	14	14	15	15	15
40°	13	14	14	14	14	15	15	15	15	15	15
38.75°	14	14	15	15	15	15	15	15	15	16	16
37.5°	15	15	15	15	15	16	16	16	17	17	17
36.25°	15	15	15	16	16	17	17	18	18	18	18
35°	15	16	16	17	18	18	18	19	19	19	19



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	16	17	18	18	18	19	19	19	19	19	19
32.5°	18	18	18	19	19	19	19	20	20	20	20
31.25°	18	19	19	19	19	20	20	20	21	21	21
30°	19	19	19	20	20	20	21	21	21	22	22
28.75°	19	20	20	20	21	21	22	22	22	23	23
27.5°	20	20	21	21	22	22	22	23	23	24	25
26.25°	20	21	21	22	22	23	24	24	25	26	26
25°	21	22	22	23	23	24	25	26	27	27	28
23.75°	22	22	23	24	25	26	27	28	28	29	30
22.5°	22	23	24	25	26	27	28	29	30	31	33
21.25°	23	24	26	27	28	29	30	31	33	34	35
20°	24	26	27	28	29	31	32	34	36	38	40
18.75°	26	27	28	29	31	33	35	37	40	43	45
17.5°	27	28	29	31	33	35	38	42	45	48	54
16.25°	28	29	31	33	36	39	43	47	52	60	67
15°	29	31	33	35	39	43	47	55	64	72	80
13.75°	30	32	35	38	43	47	56	66	75	85	94
12.5°	31	34	37	42	47	55	66	76	88	98	108
11.25°	33	36	40	45	52	64	75	88	100	111	132
10°	34	38	43	48	60	72	85	98	111	135	157
8.75°	35	40	45	54	67	80	94	108	132	157	188
7.5°	37	42	48	60	73	88	103	123	151	179	250
6.25°	38	44	52	65	79	95	110	139	168	230	306
5°	40	46	56	70	85	101	122	152	192	274	355
3.75°	41	47	59	73	89	105	131	163	225	311	468
2.5°	42	48	61	76	92	109	138	171	249	337	562
1.25°	42	48	63	77	94	111	143	175	263	354	654
0°	42	48	63	78	95	111	144	177	268	360	692
-1.25°	42	48	63	77	94	111	143	175	263	354	654
-2.5°	42	48	61	76	92	109	138	171	249	337	562
-3.75°	41	47	59	73	89	105	131	163	225	311	468
-5°	40	46	56	70	85	101	122	152	192	274	355
-6.25°	38	44	52	65	79	95	110	139	168	230	306
-7.5°	37	42	48	60	73	88	103	123	151	179	250
-8.75°	35	40	45	54	67	80	94	108	132	157	188
-10°	34	38	43	48	60	72	85	98	111	135	157
-11.25°	33	36	40	45	52	64	75	88	100	111	132
-12.5°	31	34	37	42	47	55	66	76	88	98	108
-13.75°	30	32	35	38	43	47	56	66	75	85	94
-15°	29	31	33	35	39	43	47	55	64	72	80
-16.25°	28	29	31	33	36	39	43	47	52	60	67
-17.5°	27	28	29	31	33	35	38	42	45	48	54
-18.75°	26	27	28	29	31	33	35	37	40	43	45
-20°	24	26	27	28	29	31	32	34	36	38	40
-21.25°	23	24	26	27	28	29	30	31	33	34	35



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	22	23	24	25	26	27	28	29	30	31	33
-23.75°	22	22	23	24	25	26	27	28	28	29	30
-25°	21	22	22	23	23	24	25	26	27	27	28
-26.25°	20	21	21	22	22	23	24	24	25	26	26
-27.5°	20	20	21	21	22	22	22	23	23	24	25
-28.75°	19	20	20	20	21	21	22	22	22	23	23
-30°	19	19	19	20	20	20	21	21	21	22	22
-31.25°	18	19	19	19	19	20	20	20	21	21	21
-32.5°	18	18	18	19	19	19	19	20	20	20	20
-33.75°	16	17	18	18	18	19	19	19	19	19	19
-35°	15	16	16	17	18	18	18	19	19	19	19
-36.25°	15	15	15	16	16	17	17	18	18	18	18
-37.5°	15	15	15	15	15	16	16	16	17	17	17
-38.75°	14	14	15	15	15	15	15	15	15	16	16
-40°	13	14	14	14	14	15	15	15	15	15	15
-41.25°	13	13	13	13	14	14	14	14	15	15	15
-42.5°	12	12	13	13	13	13	13	14	14	14	14
-43.75°	12	12	12	12	12	13	13	13	13	13	13
-45°	10	11	11	12	12	12	12	12	12	12	13
-46.25°	9	10	10	11	11	11	12	12	12	12	12
-47.5°	9	9	9	9	10	10	10	11	11	11	11
-48.75°	8	8	9	9	9	9	9	9	9	10	10
-50°	8	8	8	8	8	9	9	9	9	9	9
-51.25°	7	7	7	8	8	8	8	8	8	8	8
-52.5°	6	6	7	7	7	7	7	7	8	8	8
-53.75°	5	6	6	6	6	6	6	7	7	7	7
-55°	4	5	5	5	5	5	6	6	6	6	6
-56.25°	4	4	4	4	4	5	5	5	5	5	5
-57.5°	3	3	3	3	4	4	4	4	4	4	4
-58.75°	2	2	2	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	2	2	2	2	3	3
-61.25°	1	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	0	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	4	4	4	4	4	4	4	4	4
57.5°	4	4	4	5	5	5	5	5	5	5	4
56.25°	5	5	5	5	5	5	6	5	5	5	5
55°	6	6	6	6	6	6	6	6	6	6	6
53.75°	7	7	7	7	7	7	7	7	7	7	7
52.5°	8	8	8	8	8	8	8	8	8	8	8
51.25°	9	9	9	9	9	9	9	9	9	9	9
50°	9	9	9	9	9	9	9	9	9	9	9
48.75°	10	10	10	10	10	10	11	10	10	10	10
47.5°	11	12	12	12	12	12	12	12	12	12	12
46.25°	12	12	12	12	12	12	12	12	12	12	12
45°	13	13	13	13	13	13	13	13	13	13	13
43.75°	13	13	14	14	14	14	14	14	14	14	14
42.5°	14	14	14	15	15	15	15	15	15	15	14
41.25°	15	15	15	15	15	15	15	15	15	15	15
40°	15	15	15	15	15	15	16	15	15	15	15
38.75°	16	16	17	17	17	17	17	17	17	17	17
37.5°	18	18	18	18	18	18	18	18	18	18	18
36.25°	19	19	19	19	19	19	19	19	19	19	19
35°	19	19	19	19	19	19	19	19	19	19	19



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	20	20	20	20	20	20	20	20	20	20	20
32.5°	20	21	21	21	21	21	21	21	21	21	21
31.25°	21	21	22	22	22	22	22	22	22	22	22
30°	22	22	23	23	23	23	23	23	23	23	23
28.75°	23	24	24	24	25	25	25	25	25	24	24
27.5°	25	26	26	26	26	26	27	26	26	26	26
26.25°	27	27	28	28	28	28	28	28	28	28	28
25°	29	29	29	30	30	30	30	30	30	30	29
23.75°	31	31	32	33	33	33	33	33	33	33	32
22.5°	34	34	35	36	36	36	37	36	36	36	35
21.25°	37	38	40	41	42	42	42	42	42	41	40
20°	42	44	46	47	48	48	48	48	48	47	46
18.75°	48	52	56	59	61	63	63	63	61	59	56
17.5°	60	65	70	73	76	77	78	77	76	73	70
16.25°	73	79	85	89	92	94	95	94	92	89	85
15°	88	95	101	105	109	111	111	111	109	105	101
13.75°	103	110	122	131	138	143	144	143	138	131	122
12.5°	123	139	152	163	171	175	177	175	171	163	152
11.25°	151	168	192	225	249	263	268	263	249	225	192
10°	179	230	274	311	337	354	360	354	337	311	274
8.75°	250	306	355	468	562	654	692	654	562	468	355
7.5°	317	415	582	854	1086	1292	1363	1292	1086	854	582
6.25°	415	657	1021	1511	1918	2196	2293	2196	1918	1511	1021
5°	582	1021	1660	2295	2772	3071	3177	3071	2772	2295	1660
3.75°	854	1511	2295	2969	3452	3753	3835	3753	3452	2969	2295
2.5°	1086	1918	2772	3452	3923	4195	4272	4195	3923	3452	2772
1.25°	1292	2196	3071	3753	4195	4438	4514	4438	4195	3753	3071
0°	1363	2293	3177	3835	4272	4514	4612	4514	4272	3835	3177
-1.25°	1292	2196	3071	3753	4195	4438	4514	4438	4195	3753	3071
-2.5°	1086	1918	2772	3452	3923	4195	4272	4195	3923	3452	2772
-3.75°	854	1511	2295	2969	3452	3753	3835	3753	3452	2969	2295
-5°	582	1021	1660	2295	2772	3071	3177	3071	2772	2295	1660
-6.25°	415	657	1021	1511	1918	2196	2293	2196	1918	1511	1021
-7.5°	317	415	582	854	1086	1292	1363	1292	1086	854	582
-8.75°	250	306	355	468	562	654	692	654	562	468	355
-10°	179	230	274	311	337	354	360	354	337	311	274
-11.25°	151	168	192	225	249	263	268	263	249	225	192
-12.5°	123	139	152	163	171	175	177	175	171	163	152
-13.75°	103	110	122	131	138	143	144	143	138	131	122
-15°	88	95	101	105	109	111	111	111	109	105	101
-16.25°	73	79	85	89	92	94	95	94	92	89	85
-17.5°	60	65	70	73	76	77	78	77	76	73	70
-18.75°	48	52	56	59	61	63	63	63	61	59	56
-20°	42	44	46	47	48	48	48	48	48	47	46
-21.25°	37	38	40	41	42	42	42	42	42	41	40



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	34	34	35	36	36	36	37	36	36	36	35
-23.75°	31	31	32	33	33	33	33	33	33	33	32
-25°	29	29	29	30	30	30	30	30	30	30	29
-26.25°	27	27	28	28	28	28	28	28	28	28	28
-27.5°	25	26	26	26	26	26	27	26	26	26	26
-28.75°	23	24	24	24	25	25	25	25	25	24	24
-30°	22	22	23	23	23	23	23	23	23	23	23
-31.25°	21	21	22	22	22	22	22	22	22	22	22
-32.5°	20	21	21	21	21	21	21	21	21	21	21
-33.75°	20	20	20	20	20	20	20	20	20	20	20
-35°	19	19	19	19	19	19	19	19	19	19	19
-36.25°	19	19	19	19	19	19	19	19	19	19	19
-37.5°	18	18	18	18	18	18	18	18	18	18	18
-38.75°	16	16	17	17	17	17	17	17	17	17	17
-40°	15	15	15	15	15	15	16	15	15	15	15
-41.25°	15	15	15	15	15	15	15	15	15	15	15
-42.5°	14	14	14	15	15	15	15	15	15	15	14
-43.75°	13	13	14	14	14	14	14	14	14	14	14
-45°	13	13	13	13	13	13	13	13	13	13	13
-46.25°	12	12	12	12	12	12	12	12	12	12	12
-47.5°	11	12	12	12	12	12	12	12	12	12	12
-48.75°	10	10	10	10	10	10	11	10	10	10	10
-50°	9	9	9	9	9	9	9	9	9	9	9
-51.25°	9	9	9	9	9	9	9	9	9	9	9
-52.5°	8	8	8	8	8	8	8	8	8	8	8
-53.75°	7	7	7	7	7	7	7	7	7	7	7
-55°	6	6	6	6	6	6	6	6	6	6	6
-56.25°	5	5	5	5	5	5	6	5	5	5	5
-57.5°	4	4	4	5	5	5	5	5	5	5	4
-58.75°	3	3	4	4	4	4	4	4	4	4	4
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	2	2	2	2	2	2	2
58.75°	3	3	3	3	3	3	3	3	3	3	2
57.5°	4	4	4	4	4	4	4	4	4	3	3
56.25°	5	5	5	5	5	5	5	5	4	4	4
55°	6	6	6	6	6	6	6	5	5	5	5
53.75°	7	7	7	7	7	7	6	6	6	6	6
52.5°	8	8	8	8	8	7	7	7	7	7	7
51.25°	9	9	8	8	8	8	8	8	8	8	7
50°	9	9	9	9	9	9	9	9	8	8	8
48.75°	10	10	10	10	9	9	9	9	9	9	9
47.5°	12	11	11	11	11	11	10	10	10	9	9
46.25°	12	12	12	12	12	12	12	11	11	11	10
45°	13	13	13	12	12	12	12	12	12	12	11
43.75°	13	13	13	13	13	13	13	13	12	12	12
42.5°	14	14	14	14	14	14	13	13	13	13	13
41.25°	15	15	15	15	15	14	14	14	14	13	13
40°	15	15	15	15	15	15	15	15	14	14	14
38.75°	16	16	16	16	15	15	15	15	15	15	15
37.5°	18	18	17	17	17	16	16	16	15	15	15
36.25°	19	19	18	18	18	18	17	17	16	16	15
35°	19	19	19	19	19	19	18	18	18	17	16



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	20	20	19	19	19	19	19	19	18	18	18
32.5°	21	20	20	20	20	20	19	19	19	19	18
31.25°	21	21	21	21	21	20	20	20	19	19	19
30°	22	22	22	22	21	21	21	20	20	20	19
28.75°	24	23	23	23	22	22	22	21	21	20	20
27.5°	26	25	25	24	23	23	22	22	22	21	21
26.25°	27	27	26	26	25	24	24	23	22	22	21
25°	29	29	28	27	27	26	25	24	23	23	22
23.75°	31	31	30	29	28	28	27	26	25	24	23
22.5°	34	34	33	31	30	29	28	27	26	25	24
21.25°	38	37	35	34	33	31	30	29	28	27	26
20°	44	42	40	38	36	34	32	31	29	28	27
18.75°	52	48	45	43	40	37	35	33	31	29	28
17.5°	65	60	54	48	45	42	38	35	33	31	29
16.25°	79	73	67	60	52	47	43	39	36	33	31
15°	95	88	80	72	64	55	47	43	39	35	33
13.75°	110	103	94	85	75	66	56	47	43	38	35
12.5°	139	123	108	98	88	76	66	55	47	42	37
11.25°	168	151	132	111	100	88	75	64	52	45	40
10°	230	179	157	135	111	98	85	72	60	48	43
8.75°	306	250	188	157	132	108	94	80	67	54	45
7.5°	415	317	250	179	151	123	103	88	73	60	48
6.25°	657	415	306	230	168	139	110	95	79	65	52
5°	1021	582	355	274	192	152	122	101	85	70	56
3.75°	1511	854	468	311	225	163	131	105	89	73	59
2.5°	1918	1086	562	337	249	171	138	109	92	76	61
1.25°	2196	1292	654	354	263	175	143	111	94	77	63
0°	2293	1363	692	360	268	177	144	111	95	78	63
-1.25°	2196	1292	654	354	263	175	143	111	94	77	63
-2.5°	1918	1086	562	337	249	171	138	109	92	76	61
-3.75°	1511	854	468	311	225	163	131	105	89	73	59
-5°	1021	582	355	274	192	152	122	101	85	70	56
-6.25°	657	415	306	230	168	139	110	95	79	65	52
-7.5°	415	317	250	179	151	123	103	88	73	60	48
-8.75°	306	250	188	157	132	108	94	80	67	54	45
-10°	230	179	157	135	111	98	85	72	60	48	43
-11.25°	168	151	132	111	100	88	75	64	52	45	40
-12.5°	139	123	108	98	88	76	66	55	47	42	37
-13.75°	110	103	94	85	75	66	56	47	43	38	35
-15°	95	88	80	72	64	55	47	43	39	35	33
-16.25°	79	73	67	60	52	47	43	39	36	33	31
-17.5°	65	60	54	48	45	42	38	35	33	31	29
-18.75°	52	48	45	43	40	37	35	33	31	29	28
-20°	44	42	40	38	36	34	32	31	29	28	27
-21.25°	38	37	35	34	33	31	30	29	28	27	26



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	34	34	33	31	30	29	28	27	26	25	24
-23.75°	31	31	30	29	28	28	27	26	25	24	23
-25°	29	29	28	27	27	26	25	24	23	23	22
-26.25°	27	27	26	26	25	24	24	23	22	22	21
-27.5°	26	25	25	24	23	23	22	22	22	21	21
-28.75°	24	23	23	23	22	22	22	21	21	20	20
-30°	22	22	22	22	21	21	21	20	20	20	19
-31.25°	21	21	21	21	21	20	20	20	19	19	19
-32.5°	21	20	20	20	20	20	19	19	19	19	18
-33.75°	20	20	19	19	19	19	19	19	18	18	18
-35°	19	19	19	19	19	19	18	18	18	17	16
-36.25°	19	19	18	18	18	18	17	17	16	16	15
-37.5°	18	18	17	17	17	16	16	16	15	15	15
-38.75°	16	16	16	16	15	15	15	15	15	15	15
-40°	15	15	15	15	15	15	15	15	14	14	14
-41.25°	15	15	15	15	15	14	14	14	14	13	13
-42.5°	14	14	14	14	14	14	13	13	13	13	13
-43.75°	13	13	13	13	13	13	13	13	12	12	12
-45°	13	13	13	12	12	12	12	12	12	12	11
-46.25°	12	12	12	12	12	12	12	11	11	11	10
-47.5°	12	11	11	11	11	11	10	10	10	9	9
-48.75°	10	10	10	10	9	9	9	9	9	9	9
-50°	9	9	9	9	9	9	9	9	8	8	8
-51.25°	9	9	8	8	8	8	8	8	8	8	7
-52.5°	8	8	8	8	8	7	7	7	7	7	7
-53.75°	7	7	7	7	7	7	6	6	6	6	6
-55°	6	6	6	6	6	6	6	5	5	5	5
-56.25°	5	5	5	5	5	5	5	5	4	4	4
-57.5°	4	4	4	4	4	4	4	4	4	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	2
-60°	3	3	3	3	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	0	0	0	0	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	1	1	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	1	1	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	1	1
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	4	4	3	3	3	3	3	2	2	2	2
55°	5	4	4	4	4	3	3	3	3	2	2
53.75°	6	5	5	5	5	4	4	4	3	3	3
52.5°	6	6	6	6	5	5	5	4	4	4	3
51.25°	7	7	7	6	6	6	5	5	5	4	4
50°	8	8	7	7	7	7	6	6	6	5	5
48.75°	8	8	8	8	8	7	7	7	6	6	6
47.5°	9	9	9	8	8	8	8	7	7	7	6
46.25°	10	9	9	9	9	8	8	8	8	7	7
45°	11	10	10	9	9	9	9	8	8	8	8
43.75°	12	12	11	11	10	10	9	9	9	8	8
42.5°	12	12	12	12	11	11	10	9	9	9	9
41.25°	13	13	12	12	12	12	11	10	10	9	9
40°	14	13	13	13	12	12	12	12	11	10	9
38.75°	14	14	14	13	13	13	12	12	12	11	10
37.5°	15	15	14	14	14	13	13	12	12	12	11
36.25°	15	15	15	15	14	14	13	13	13	12	12
35°	16	15	15	15	15	14	14	13	13	13	12



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	17	16	16	15	15	15	15	14	14	13	13
32.5°	18	18	17	16	15	15	15	15	14	14	13
31.25°	19	18	18	17	16	16	15	15	15	14	14
30°	19	19	19	18	17	17	16	15	15	15	14
28.75°	20	19	19	19	18	18	17	16	15	15	15
27.5°	20	20	19	19	19	18	18	17	16	15	15
26.25°	21	20	20	19	19	19	18	18	17	16	15
25°	22	21	21	20	19	19	19	18	17	16	15
23.75°	22	22	21	21	20	19	19	19	18	17	16
22.5°	23	22	22	21	21	20	19	19	19	18	17
21.25°	24	23	22	22	21	20	20	19	19	18	18
20°	26	24	23	22	22	21	20	20	19	19	18
18.75°	27	26	24	23	22	21	21	20	19	19	18
17.5°	28	27	25	24	23	22	21	20	20	19	19
16.25°	29	28	26	25	23	22	22	21	20	19	19
15°	31	29	27	26	24	23	22	21	20	20	19
13.75°	32	30	28	27	25	24	22	22	21	20	19
12.5°	34	31	29	28	26	24	23	22	21	20	20
11.25°	36	33	30	28	27	25	23	22	21	21	20
10°	38	34	31	29	27	26	24	23	22	21	20
8.75°	40	35	33	30	28	26	25	23	22	21	20
7.5°	42	37	34	31	29	27	25	23	22	21	20
6.25°	44	38	34	31	29	27	26	24	22	21	21
5°	46	40	35	32	29	28	26	24	23	22	21
3.75°	47	41	36	33	30	28	26	24	23	22	21
2.5°	48	42	36	33	30	28	26	25	23	22	21
1.25°	48	42	36	33	30	28	26	25	23	22	21
0°	48	42	37	33	30	28	27	25	23	22	21
-1.25°	48	42	36	33	30	28	26	25	23	22	21
-2.5°	48	42	36	33	30	28	26	25	23	22	21
-3.75°	47	41	36	33	30	28	26	24	23	22	21
-5°	46	40	35	32	29	28	26	24	23	22	21
-6.25°	44	38	34	31	29	27	26	24	22	21	21
-7.5°	42	37	34	31	29	27	25	23	22	21	20
-8.75°	40	35	33	30	28	26	25	23	22	21	20
-10°	38	34	31	29	27	26	24	23	22	21	20
-11.25°	36	33	30	28	27	25	23	22	21	21	20
-12.5°	34	31	29	28	26	24	23	22	21	20	20
-13.75°	32	30	28	27	25	24	22	22	21	20	19
-15°	31	29	27	26	24	23	22	21	20	20	19
-16.25°	29	28	26	25	23	22	22	21	20	19	19
-17.5°	28	27	25	24	23	22	21	20	20	19	19
-18.75°	27	26	24	23	22	21	21	20	19	19	18
-20°	26	24	23	22	22	21	20	20	19	19	18
-21.25°	24	23	22	22	21	20	20	19	19	18	18



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	23	22	22	21	21	20	19	19	19	18	17
-23.75°	22	22	21	21	20	19	19	19	18	17	16
-25°	22	21	21	20	19	19	19	18	17	16	15
-26.25°	21	20	20	19	19	19	18	18	17	16	15
-27.5°	20	20	19	19	19	18	18	17	16	15	15
-28.75°	20	19	19	19	18	18	17	16	15	15	15
-30°	19	19	19	18	17	17	16	15	15	15	14
-31.25°	19	18	18	17	16	16	15	15	15	14	14
-32.5°	18	18	17	16	15	15	15	15	14	14	13
-33.75°	17	16	16	15	15	15	15	14	14	13	13
-35°	16	15	15	15	15	14	14	13	13	13	12
-36.25°	15	15	15	15	14	14	13	13	13	12	12
-37.5°	15	15	14	14	14	13	13	12	12	12	11
-38.75°	14	14	14	13	13	13	12	12	12	11	10
-40°	14	13	13	13	12	12	12	12	11	10	9
-41.25°	13	13	12	12	12	12	11	10	10	9	9
-42.5°	12	12	12	12	11	11	10	9	9	9	9
-43.75°	12	12	11	11	10	10	9	9	9	8	8
-45°	11	10	10	9	9	9	9	8	8	8	8
-46.25°	10	9	9	9	9	8	8	8	8	7	7
-47.5°	9	9	9	8	8	8	8	7	7	7	6
-48.75°	8	8	8	8	8	7	7	7	6	6	6
-50°	8	8	7	7	7	7	6	6	6	5	5
-51.25°	7	7	7	6	6	6	5	5	5	4	4
-52.5°	6	6	6	6	5	5	5	4	4	4	3
-53.75°	6	5	5	5	5	4	4	4	3	3	3
-55°	5	4	4	4	4	3	3	3	3	2	2
-56.25°	4	4	3	3	3	3	3	2	2	2	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	1	1
-60°	2	2	2	2	2	1	1	1	1	1	1
-61.25°	2	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	0	0	0	0
-72.5°	1	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	1	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	0	0	0	0	0	0
67.5°	1	1	1	1	1	1	1	0	0	0	0
66.25°	1	1	1	1	1	1	1	1	1	1	0
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	2	1	1	1	1	1	1	1
53.75°	3	2	2	2	2	2	1	1	1	1	1
52.5°	3	3	2	2	2	2	2	2	1	1	1
51.25°	4	3	3	3	2	2	2	2	2	1	1
50°	4	4	4	3	3	3	2	2	2	2	1
48.75°	5	5	4	4	3	3	3	2	2	2	2
47.5°	6	5	5	5	4	4	3	3	2	2	2
46.25°	6	6	6	5	5	4	4	3	3	2	2
45°	7	7	6	6	5	5	4	4	3	3	2
43.75°	8	7	7	6	6	5	5	4	4	3	3
42.5°	8	8	7	7	6	6	5	5	4	4	3
41.25°	9	8	8	8	7	7	6	5	5	4	4
40°	9	9	8	8	8	7	7	6	5	5	4
38.75°	10	9	9	8	8	8	7	6	6	5	5
37.5°	11	10	9	9	8	8	8	7	6	6	5
36.25°	11	11	10	9	9	8	8	7	7	6	6
35°	12	12	11	10	9	9	8	8	7	7	6



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	12	12	11	11	10	9	9	8	8	7	6
32.5°	13	12	12	11	10	9	9	9	8	8	7
31.25°	13	13	12	12	11	10	9	9	8	8	7
30°	14	13	13	12	12	11	10	9	9	8	8
28.75°	14	13	13	12	12	12	10	9	9	8	8
27.5°	15	14	13	13	12	12	11	10	9	9	8
26.25°	15	14	14	13	13	12	12	11	10	9	8
25°	15	15	14	14	13	12	12	11	10	9	9
23.75°	15	15	15	14	13	13	12	12	11	9	9
22.5°	16	15	15	14	14	13	12	12	11	10	9
21.25°	16	15	15	15	14	13	13	12	12	10	9
20°	17	16	15	15	14	14	13	12	12	11	10
18.75°	18	16	15	15	15	14	13	13	12	11	10
17.5°	18	17	16	15	15	14	13	13	12	12	11
16.25°	18	18	16	15	15	14	14	13	12	12	11
15°	19	18	17	16	15	15	14	13	13	12	11
13.75°	19	18	17	16	15	15	14	13	13	12	12
12.5°	19	19	18	16	15	15	14	14	13	12	12
11.25°	19	19	18	17	15	15	15	14	13	12	12
10°	19	19	18	17	16	15	15	14	13	12	12
8.75°	19	19	18	17	16	15	15	14	13	13	12
7.5°	20	19	19	18	16	15	15	14	13	13	12
6.25°	20	19	19	18	16	15	15	14	13	13	12
5°	20	19	19	18	17	15	15	14	14	13	12
3.75°	20	19	19	18	17	15	15	15	14	13	12
2.5°	20	19	19	18	17	15	15	15	14	13	12
1.25°	20	19	19	18	17	15	15	15	14	13	12
0°	20	19	19	18	17	16	15	15	14	13	12
-1.25°	20	19	19	18	17	15	15	15	14	13	12
-2.5°	20	19	19	18	17	15	15	15	14	13	12
-3.75°	20	19	19	18	17	15	15	15	14	13	12
-5°	20	19	19	18	17	15	15	14	14	13	12
-6.25°	20	19	19	18	16	15	15	14	13	13	12
-7.5°	20	19	19	18	16	15	15	14	13	13	12
-8.75°	19	19	18	17	16	15	15	14	13	13	12
-10°	19	19	18	17	16	15	15	14	13	12	12
-11.25°	19	19	18	17	15	15	15	14	13	12	12
-12.5°	19	19	18	16	15	15	14	14	13	12	12
-13.75°	19	18	17	16	15	15	14	13	13	12	12
-15°	19	18	17	16	15	15	14	13	13	12	11
-16.25°	18	18	16	15	15	14	14	13	12	12	11
-17.5°	18	17	16	15	15	14	13	13	12	12	11
-18.75°	18	16	15	15	15	14	13	13	12	11	10
-20°	17	16	15	15	14	14	13	12	12	11	10
-21.25°	16	15	15	15	14	13	13	12	12	10	9



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	16	15	15	14	14	13	12	12	11	10	9
-23.75°	15	15	15	14	13	13	12	12	11	9	9
-25°	15	15	14	14	13	12	12	11	10	9	9
-26.25°	15	14	14	13	13	12	12	11	10	9	8
-27.5°	15	14	13	13	12	12	11	10	9	9	8
-28.75°	14	13	13	12	12	12	10	9	9	8	8
-30°	14	13	13	12	12	11	10	9	9	8	8
-31.25°	13	13	12	12	11	10	9	9	8	8	7
-32.5°	13	12	12	11	10	9	9	9	8	8	7
-33.75°	12	12	11	11	10	9	9	8	8	7	6
-35°	12	12	11	10	9	9	8	8	7	7	6
-36.25°	11	11	10	9	9	8	8	7	7	6	6
-37.5°	11	10	9	9	8	8	8	7	6	6	5
-38.75°	10	9	9	8	8	8	7	6	6	5	5
-40°	9	9	8	8	8	7	7	6	5	5	4
-41.25°	9	8	8	8	7	7	6	5	5	4	4
-42.5°	8	8	7	7	6	6	5	5	4	4	3
-43.75°	8	7	7	6	6	5	5	4	4	3	3
-45°	7	7	6	6	5	5	4	4	3	3	2
-46.25°	6	6	6	5	5	4	4	3	3	2	2
-47.5°	6	5	5	5	4	4	3	3	2	2	2
-48.75°	5	5	4	4	3	3	3	2	2	2	2
-50°	4	4	4	3	3	3	2	2	2	2	1
-51.25°	4	3	3	3	2	2	2	2	2	1	1
-52.5°	3	3	2	2	2	2	2	2	1	1	1
-53.75°	3	2	2	2	2	2	1	1	1	1	1
-55°	2	2	2	2	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	0
-67.5°	1	1	1	1	1	1	1	0	0	0	0
-68.75°	1	1	1	1	1	0	0	0	0	0	0
-70°	1	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	1	0	0	0	0	0	0	0	0
62.5°	1	1	1	1	0	0	0	0	0	0	0
61.25°	1	1	1	1	1	1	0	0	0	0	0
60°	1	1	1	1	1	1	1	0	0	0	0
58.75°	1	1	1	1	1	1	1	1	0	0	0
57.5°	1	1	1	1	1	1	1	1	1	0	0
56.25°	1	1	1	1	1	1	1	1	1	1	0
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	1	1	1	1	1	1	1	1	1	1
46.25°	2	2	1	1	1	1	1	1	1	1	1
45°	2	2	2	1	1	1	1	1	1	1	1
43.75°	2	2	2	2	1	1	1	1	1	1	1
42.5°	3	2	2	2	2	1	1	1	1	1	1
41.25°	3	3	2	2	2	1	1	1	1	1	1
40°	4	3	3	2	2	2	1	1	1	1	1
38.75°	4	3	3	2	2	2	1	1	1	1	1
37.5°	5	4	3	3	2	2	2	1	1	1	1
36.25°	5	4	4	3	2	2	2	1	1	1	1
35°	5	5	4	3	3	2	2	2	1	1	1



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	6	5	4	4	3	3	2	2	1	1	1
32.5°	6	6	5	4	3	3	2	2	2	1	1
31.25°	7	6	5	4	4	3	2	2	2	1	1
30°	7	6	6	5	4	3	3	2	2	2	1
28.75°	7	7	6	5	4	4	3	2	2	2	1
27.5°	8	7	6	5	5	4	3	3	2	2	1
26.25°	8	7	7	6	5	4	3	3	2	2	1
25°	8	8	7	6	5	5	4	3	2	2	2
23.75°	8	8	7	6	6	5	4	3	3	2	2
22.5°	9	8	7	7	6	5	4	3	3	2	2
21.25°	9	8	8	7	6	5	4	4	3	2	2
20°	9	8	8	7	6	6	5	4	3	2	2
18.75°	9	9	8	7	7	6	5	4	3	2	2
17.5°	9	9	8	8	7	6	5	4	3	3	2
16.25°	10	9	8	8	7	6	5	4	4	3	2
15°	10	9	9	8	7	6	5	5	4	3	2
13.75°	10	9	9	8	7	6	6	5	4	3	2
12.5°	11	9	9	8	7	7	6	5	4	3	2
11.25°	11	9	9	8	8	7	6	5	4	3	2
10°	11	10	9	8	8	7	6	5	4	3	3
8.75°	11	10	9	8	8	7	6	5	4	3	3
7.5°	11	10	9	9	8	7	6	5	4	3	3
6.25°	12	10	9	9	8	7	6	5	4	3	3
5°	12	10	9	9	8	7	6	5	4	4	3
3.75°	12	10	9	9	8	7	6	5	5	4	3
2.5°	12	10	9	9	8	7	6	5	5	4	3
1.25°	12	10	9	9	8	7	6	5	5	4	3
0°	12	11	9	9	8	7	6	6	5	4	3
-1.25°	12	10	9	9	8	7	6	5	5	4	3
-2.5°	12	10	9	9	8	7	6	5	5	4	3
-3.75°	12	10	9	9	8	7	6	5	5	4	3
-5°	12	10	9	9	8	7	6	5	4	4	3
-6.25°	12	10	9	9	8	7	6	5	4	3	3
-7.5°	11	10	9	9	8	7	6	5	4	3	3
-8.75°	11	10	9	8	8	7	6	5	4	3	3
-10°	11	10	9	8	8	7	6	5	4	3	3
-11.25°	11	9	9	8	8	7	6	5	4	3	2
-12.5°	11	9	9	8	7	7	6	5	4	3	2
-13.75°	10	9	9	8	7	6	6	5	4	3	2
-15°	10	9	9	8	7	6	5	5	4	3	2
-16.25°	10	9	8	8	7	6	5	4	4	3	2
-17.5°	9	9	8	8	7	6	5	4	3	3	2
-18.75°	9	9	8	7	7	6	5	4	3	2	2
-20°	9	8	8	7	6	6	5	4	3	2	2
-21.25°	9	8	8	7	6	5	4	4	3	2	2



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	9	8	7	7	6	5	4	3	3	2	2
-23.75°	8	8	7	6	6	5	4	3	3	2	2
-25°	8	8	7	6	5	5	4	3	2	2	2
-26.25°	8	7	7	6	5	4	3	3	2	2	1
-27.5°	8	7	6	5	5	4	3	3	2	2	1
-28.75°	7	7	6	5	4	4	3	2	2	2	1
-30°	7	6	6	5	4	3	3	2	2	2	1
-31.25°	7	6	5	4	4	3	2	2	2	1	1
-32.5°	6	6	5	4	3	3	2	2	2	1	1
-33.75°	6	5	4	4	3	3	2	2	1	1	1
-35°	5	5	4	3	3	2	2	2	1	1	1
-36.25°	5	4	4	3	2	2	2	1	1	1	1
-37.5°	5	4	3	3	2	2	2	1	1	1	1
-38.75°	4	3	3	2	2	2	1	1	1	1	1
-40°	4	3	3	2	2	2	1	1	1	1	1
-41.25°	3	3	2	2	2	1	1	1	1	1	1
-42.5°	3	2	2	2	2	1	1	1	1	1	1
-43.75°	2	2	2	2	1	1	1	1	1	1	1
-45°	2	2	2	1	1	1	1	1	1	1	1
-46.25°	2	2	1	1	1	1	1	1	1	1	1
-47.5°	2	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	0
-57.5°	1	1	1	1	1	1	1	1	1	0	0
-58.75°	1	1	1	1	1	1	1	1	0	0	0
-60°	1	1	1	1	1	1	1	0	0	0	0
-61.25°	1	1	1	1	1	1	0	0	0	0	0
-62.5°	1	1	1	1	0	0	0	0	0	0	0
-63.75°	1	1	1	0	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	1	0	0	0	0	0	0	0	0	0	0
52.5°	1	0	0	0	0	0	0	0	0	0	0
51.25°	1	1	0	0	0	0	0	0	0	0	0
50°	1	1	1	0	0	0	0	0	0	0	0
48.75°	1	1	1	0	0	0	0	0	0	0	0
47.5°	1	1	1	1	0	0	0	0	0	0	0
46.25°	1	1	1	1	0	0	0	0	0	0	0
45°	1	1	1	1	1	0	0	0	0	0	0
43.75°	1	1	1	1	1	0	0	0	0	0	0
42.5°	1	1	1	1	1	0	0	0	0	0	0
41.25°	1	1	1	1	1	1	0	0	0	0	0
40°	1	1	1	1	1	1	0	0	0	0	0
38.75°	1	1	1	1	1	1	1	0	0	0	0
37.5°	1	1	1	1	1	1	1	0	0	0	0
36.25°	1	1	1	1	1	1	1	0	0	0	0
35°	1	1	1	1	1	1	1	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	0	0	0
32.5°	1	1	1	1	1	1	1	1	0	0	0
31.25°	1	1	1	1	1	1	1	1	0	0	0
30°	1	1	1	1	1	1	1	1	0	0	0
28.75°	1	1	1	1	1	1	1	1	0	0	0
27.5°	1	1	1	1	1	1	1	1	1	0	0
26.25°	1	1	1	1	1	1	1	1	1	0	0
25°	1	1	1	1	1	1	1	1	1	0	0
23.75°	1	1	1	1	1	1	1	1	1	0	0
22.5°	1	1	1	1	1	1	1	1	1	0	0
21.25°	1	1	1	1	1	1	1	1	1	0	0
20°	2	1	1	1	1	1	1	1	1	1	0
18.75°	2	1	1	1	1	1	1	1	1	1	0
17.5°	2	1	1	1	1	1	1	1	1	1	0
16.25°	2	1	1	1	1	1	1	1	1	1	0
15°	2	1	1	1	1	1	1	1	1	1	0
13.75°	2	1	1	1	1	1	1	1	1	1	0
12.5°	2	2	1	1	1	1	1	1	1	1	0
11.25°	2	2	1	1	1	1	1	1	1	1	0
10°	2	2	1	1	1	1	1	1	1	1	0
8.75°	2	2	1	1	1	1	1	1	1	1	0
7.5°	2	2	1	1	1	1	1	1	1	1	0
6.25°	2	2	1	1	1	1	1	1	1	1	0
5°	2	2	1	1	1	1	1	1	1	1	0
3.75°	2	2	1	1	1	1	1	1	1	1	0
2.5°	2	2	1	1	1	1	1	1	1	1	0
1.25°	2	2	1	1	1	1	1	1	1	1	0
0°	2	2	1	1	1	1	1	1	1	1	0
-1.25°	2	2	1	1	1	1	1	1	1	1	0
-2.5°	2	2	1	1	1	1	1	1	1	1	0
-3.75°	2	2	1	1	1	1	1	1	1	1	0
-5°	2	2	1	1	1	1	1	1	1	1	0
-6.25°	2	2	1	1	1	1	1	1	1	1	0
-7.5°	2	2	1	1	1	1	1	1	1	1	0
-8.75°	2	2	1	1	1	1	1	1	1	1	0
-10°	2	2	1	1	1	1	1	1	1	1	0
-11.25°	2	2	1	1	1	1	1	1	1	1	0
-12.5°	2	2	1	1	1	1	1	1	1	1	0
-13.75°	2	1	1	1	1	1	1	1	1	1	0
-15°	2	1	1	1	1	1	1	1	1	1	0
-16.25°	2	1	1	1	1	1	1	1	1	1	0
-17.5°	2	1	1	1	1	1	1	1	1	1	0
-18.75°	2	1	1	1	1	1	1	1	1	1	0
-20°	2	1	1	1	1	1	1	1	1	1	0
-21.25°	1	1	1	1	1	1	1	1	1	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	1	1	1	1	1	1	1	1	1	0	0
-23.75°	1	1	1	1	1	1	1	1	1	0	0
-25°	1	1	1	1	1	1	1	1	1	0	0
-26.25°	1	1	1	1	1	1	1	1	1	0	0
-27.5°	1	1	1	1	1	1	1	1	1	0	0
-28.75°	1	1	1	1	1	1	1	1	0	0	0
-30°	1	1	1	1	1	1	1	1	0	0	0
-31.25°	1	1	1	1	1	1	1	1	0	0	0
-32.5°	1	1	1	1	1	1	1	1	0	0	0
-33.75°	1	1	1	1	1	1	1	1	0	0	0
-35°	1	1	1	1	1	1	1	0	0	0	0
-36.25°	1	1	1	1	1	1	1	0	0	0	0
-37.5°	1	1	1	1	1	1	1	0	0	0	0
-38.75°	1	1	1	1	1	1	1	0	0	0	0
-40°	1	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-43.75°	1	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	1	1	0	0	0	0	0	0
-46.25°	1	1	1	1	0	0	0	0	0	0	0
-47.5°	1	1	1	1	0	0	0	0	0	0	0
-48.75°	1	1	1	0	0	0	0	0	0	0	0
-50°	1	1	1	0	0	0	0	0	0	0	0
-51.25°	1	1	0	0	0	0	0	0	0	0	0
-52.5°	1	0	0	0	0	0	0	0	0	0	0
-53.75°	1	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: Pxxxxxx (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2710-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)