

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED2725-12-CS-LSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-41)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED2725-12-CS-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, LINEAR SPREAD LENS
Light Source: (1) SORAA 2700K 90 CRI LED
SM16-07-25D-927-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	5H x 4V
Luminaire Lumens:	284.7 lumens	Max Intensity:	724.6 candela
Efficiency:	N/A	Max Intensity Angle:	-18.75°H x 0°V
Efficacy:	38.5 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	55.2°H x 22°V	Field Angle (10%):	72.8°H x 46.1°V
Beam Lumens:	154.1 lumens	Field Lumens:	257.2 lumens
Beam Efficiency:	54.1%	Field Efficiency:	90.4%
Input Watts (W):	7.4		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

Iso-Candela Plot






REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)


CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

Lumen Table




REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

Luminous Intensity Polar Plot



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

Luminous Intensity Plot



Beam:
 H Angle: 55.2°
 V Angle: 22°
 Lumens: 154.1
 Efficiency: 54.1%

Field:
 H Angle: 72.8°
 V Angle: 46.1°
 Lumens: 257.2
 Efficiency: 90.4%

Spill:
 Lumens: 27.4
 Efficiency: 9.6%

— Vertical Distribution through -18.75-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	1
42.5°	0	0	0	0	0	0	0	0	0	0	1
41.25°	0	0	0	0	0	0	0	0	0	0	1
40°	0	0	0	0	0	0	0	0	0	0	1
38.75°	0	0	0	0	0	0	0	0	0	0	1
37.5°	0	0	0	0	0	0	0	0	0	1	1
36.25°	0	0	0	0	0	0	0	0	0	1	1
35°	0	0	0	0	0	0	0	0	0	1	1



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	0	1	1
27.5°	0	0	0	0	0	0	0	0	0	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	0	1	1	1
22.5°	0	0	0	0	0	0	0	0	1	1	1
21.25°	0	0	0	0	0	0	0	0	1	1	1
20°	0	0	0	0	0	0	0	0	1	1	1
18.75°	0	0	0	0	0	0	0	0	1	1	1
17.5°	0	0	0	0	0	0	0	0	1	1	1
16.25°	0	0	0	0	0	0	0	0	1	1	1
15°	0	0	0	0	0	0	0	0	1	1	1
13.75°	0	0	0	0	0	0	0	0	1	1	1
12.5°	0	0	0	0	0	0	0	0	1	1	1
11.25°	0	0	0	0	0	0	0	0	1	1	1
10°	0	0	0	0	0	0	0	0	1	1	1
8.75°	0	0	0	0	0	0	0	0	1	1	1
7.5°	0	0	0	0	0	0	0	0	1	1	1
6.25°	0	0	0	0	0	0	0	0	1	1	1
5°	0	0	0	0	0	0	0	0	1	1	1
3.75°	0	0	0	0	0	0	0	0	1	1	1
2.5°	0	0	0	0	0	0	0	0	1	1	1
1.25°	0	0	0	0	0	0	0	0	1	1	1
0°	0	0	0	0	0	0	0	0	1	1	1
-1.25°	0	0	0	0	0	0	0	0	1	1	1
-2.5°	0	0	0	0	0	0	0	0	1	1	1
-3.75°	0	0	0	0	0	0	0	0	1	1	1
-5°	0	0	0	0	0	0	0	0	1	1	1
-6.25°	0	0	0	0	0	0	0	0	1	1	1
-7.5°	0	0	0	0	0	0	0	0	1	1	1
-8.75°	0	0	0	0	0	0	0	0	1	1	1
-10°	0	0	0	0	0	0	0	0	1	1	1
-11.25°	0	0	0	0	0	0	0	0	1	1	1
-12.5°	0	0	0	0	0	0	0	0	1	1	1
-13.75°	0	0	0	0	0	0	0	0	1	1	1
-15°	0	0	0	0	0	0	0	0	1	1	1
-16.25°	0	0	0	0	0	0	0	0	1	1	1
-17.5°	0	0	0	0	0	0	0	0	1	1	1
-18.75°	0	0	0	0	0	0	0	0	1	1	1
-20°	0	0	0	0	0	0	0	0	1	1	1
-21.25°	0	0	0	0	0	0	0	0	1	1	1



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	1	1	1
-23.75°	0	0	0	0	0	0	0	0	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	0	1	1
-28.75°	0	0	0	0	0	0	0	0	0	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	1	1
-36.25°	0	0	0	0	0	0	0	0	0	1	1
-37.5°	0	0	0	0	0	0	0	0	0	1	1
-38.75°	0	0	0	0	0	0	0	0	0	0	1
-40°	0	0	0	0	0	0	0	0	0	0	1
-41.25°	0	0	0	0	0	0	0	0	0	0	1
-42.5°	0	0	0	0	0	0	0	0	0	0	1
-43.75°	0	0	0	0	0	0	0	0	0	0	1
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	1
67.5°	0	0	0	0	0	0	0	0	0	1	1
66.25°	0	0	0	0	0	0	0	0	1	1	1
65°	0	0	0	0	0	0	0	1	1	1	1
63.75°	0	0	0	0	0	0	1	1	1	1	1
62.5°	0	0	0	0	0	1	1	1	1	1	1
61.25°	0	0	0	0	1	1	1	1	1	1	1
60°	0	0	0	0	1	1	1	1	1	1	1
58.75°	0	0	0	1	1	1	1	1	1	1	1
57.5°	0	0	0	1	1	1	1	1	1	1	1
56.25°	0	0	1	1	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	1	1
53.75°	0	0	1	1	1	1	1	1	1	1	1
52.5°	0	1	1	1	1	1	1	1	1	1	1
51.25°	0	1	1	1	1	1	1	1	1	1	1
50°	0	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	1	1	1	1	1	1	1	1	1	1	1
31.25°	1	1	1	1	1	1	1	1	1	1	1
30°	1	1	1	1	1	1	1	1	1	1	1
28.75°	1	1	1	1	1	1	1	1	1	1	1
27.5°	1	1	1	1	1	1	1	1	1	1	1
26.25°	1	1	1	1	1	1	1	1	1	1	1
25°	1	1	1	1	1	1	1	1	1	1	2
23.75°	1	1	1	1	1	1	1	1	1	1	2
22.5°	1	1	1	1	1	1	1	1	1	1	2
21.25°	1	1	1	1	1	1	1	1	1	2	2
20°	1	1	1	1	1	1	1	1	1	2	2
18.75°	1	1	1	1	1	1	1	1	1	2	2
17.5°	1	1	1	1	1	1	1	1	2	2	2
16.25°	1	1	1	1	1	1	1	1	2	2	2
15°	1	1	1	1	1	1	1	1	2	2	2
13.75°	1	1	1	1	1	1	1	1	2	2	2
12.5°	1	1	1	1	1	1	1	1	2	2	2
11.25°	1	1	1	1	1	1	1	1	2	2	2
10°	1	1	1	1	1	1	1	2	2	2	2
8.75°	1	1	1	1	1	1	1	2	2	2	2
7.5°	1	1	1	1	1	1	1	2	2	2	2
6.25°	1	1	1	1	1	1	1	2	2	2	2
5°	1	1	1	1	1	1	1	2	2	2	2
3.75°	1	1	1	1	1	1	1	2	2	2	2
2.5°	1	1	1	1	1	1	1	2	2	2	2
1.25°	1	1	1	1	1	1	1	2	2	2	2
0°	1	1	1	1	1	1	1	2	2	2	2
-1.25°	1	1	1	1	1	1	1	2	2	2	2
-2.5°	1	1	1	1	1	1	1	2	2	2	2
-3.75°	1	1	1	1	1	1	1	2	2	2	2
-5°	1	1	1	1	1	1	1	2	2	2	2
-6.25°	1	1	1	1	1	1	1	2	2	2	2
-7.5°	1	1	1	1	1	1	1	2	2	2	2
-8.75°	1	1	1	1	1	1	1	2	2	2	2
-10°	1	1	1	1	1	1	1	2	2	2	2
-11.25°	1	1	1	1	1	1	1	1	2	2	2
-12.5°	1	1	1	1	1	1	1	1	2	2	2
-13.75°	1	1	1	1	1	1	1	1	2	2	2
-15°	1	1	1	1	1	1	1	1	2	2	2
-16.25°	1	1	1	1	1	1	1	1	2	2	2
-17.5°	1	1	1	1	1	1	1	1	2	2	2
-18.75°	1	1	1	1	1	1	1	1	1	2	2
-20°	1	1	1	1	1	1	1	1	1	2	2
-21.25°	1	1	1	1	1	1	1	1	1	2	2



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	1	1	2
-23.75°	1	1	1	1	1	1	1	1	1	1	2
-25°	1	1	1	1	1	1	1	1	1	1	2
-26.25°	1	1	1	1	1	1	1	1	1	1	1
-27.5°	1	1	1	1	1	1	1	1	1	1	1
-28.75°	1	1	1	1	1	1	1	1	1	1	1
-30°	1	1	1	1	1	1	1	1	1	1	1
-31.25°	1	1	1	1	1	1	1	1	1	1	1
-32.5°	1	1	1	1	1	1	1	1	1	1	1
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	0	1	1	1	1	1	1	1	1	1	1
-51.25°	0	1	1	1	1	1	1	1	1	1	1
-52.5°	0	1	1	1	1	1	1	1	1	1	1
-53.75°	0	0	1	1	1	1	1	1	1	1	1
-55°	0	0	1	1	1	1	1	1	1	1	1
-56.25°	0	0	1	1	1	1	1	1	1	1	1
-57.5°	0	0	0	1	1	1	1	1	1	1	1
-58.75°	0	0	0	1	1	1	1	1	1	1	1
-60°	0	0	0	0	1	1	1	1	1	1	1
-61.25°	0	0	0	0	1	1	1	1	1	1	1
-62.5°	0	0	0	0	0	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	1	1	1	1	1
-65°	0	0	0	0	0	0	0	1	1	1	1
-66.25°	0	0	0	0	0	0	0	0	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	1	1
-68.75°	0	0	0	0	0	0	0	0	0	0	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	1	1
71.25°	0	0	0	1	1	1	1	1	1	1	1
70°	0	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	2
48.75°	1	1	1	1	1	1	1	1	1	2	2
47.5°	1	1	1	1	1	1	1	1	2	2	2
46.25°	1	1	1	1	1	1	1	1	2	2	2
45°	1	1	1	1	1	1	1	2	2	2	2
43.75°	1	1	1	1	1	1	2	2	2	2	2
42.5°	1	1	1	1	1	2	2	2	2	2	2
41.25°	1	1	1	1	1	2	2	2	2	2	2
40°	1	1	1	1	2	2	2	2	2	2	2
38.75°	1	1	1	1	2	2	2	2	2	2	2
37.5°	1	1	1	2	2	2	2	2	2	2	3
36.25°	1	1	1	2	2	2	2	2	2	3	3
35°	1	1	2	2	2	2	2	2	3	3	3



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	2	2	2	2	2	3	3	3	3
32.5°	1	2	2	2	2	2	2	3	3	3	3
31.25°	1	2	2	2	2	2	2	3	3	3	3
30°	1	2	2	2	2	2	3	3	3	3	3
28.75°	2	2	2	2	2	2	3	3	3	3	3
27.5°	2	2	2	2	2	3	3	3	3	3	4
26.25°	2	2	2	2	2	3	3	3	3	3	4
25°	2	2	2	2	2	3	3	3	3	4	4
23.75°	2	2	2	2	3	3	3	3	3	4	4
22.5°	2	2	2	2	3	3	3	3	3	4	4
21.25°	2	2	2	2	3	3	3	3	4	4	4
20°	2	2	2	2	3	3	3	3	4	4	4
18.75°	2	2	2	2	3	3	3	3	4	4	4
17.5°	2	2	2	3	3	3	3	3	4	4	4
16.25°	2	2	2	3	3	3	3	4	4	4	4
15°	2	2	2	3	3	3	3	4	4	4	4
13.75°	2	2	2	3	3	3	3	4	4	4	4
12.5°	2	2	2	3	3	3	3	4	4	4	4
11.25°	2	2	2	3	3	3	3	4	4	4	5
10°	2	2	3	3	3	3	3	4	4	4	5
8.75°	2	2	3	3	3	3	4	4	4	4	5
7.5°	2	2	3	3	3	3	4	4	4	4	5
6.25°	2	2	3	3	3	3	4	4	4	4	5
5°	2	2	3	3	3	3	4	4	4	4	5
3.75°	2	2	3	3	3	3	4	4	4	4	5
2.5°	2	2	3	3	3	3	4	4	4	5	5
1.25°	2	2	3	3	3	3	4	4	4	5	5
0°	2	2	3	3	3	3	4	4	4	5	5
-1.25°	2	2	3	3	3	3	4	4	4	5	5
-2.5°	2	2	3	3	3	3	4	4	4	5	5
-3.75°	2	2	3	3	3	3	4	4	4	4	5
-5°	2	2	3	3	3	3	4	4	4	4	5
-6.25°	2	2	3	3	3	3	4	4	4	4	5
-7.5°	2	2	3	3	3	3	4	4	4	4	5
-8.75°	2	2	3	3	3	3	4	4	4	4	5
-10°	2	2	3	3	3	3	3	4	4	4	5
-11.25°	2	2	2	3	3	3	3	4	4	4	5
-12.5°	2	2	2	3	3	3	3	4	4	4	4
-13.75°	2	2	2	3	3	3	3	4	4	4	4
-15°	2	2	2	3	3	3	3	4	4	4	4
-16.25°	2	2	2	3	3	3	3	4	4	4	4
-17.5°	2	2	2	3	3	3	3	3	4	4	4
-18.75°	2	2	2	2	3	3	3	3	4	4	4
-20°	2	2	2	2	3	3	3	3	4	4	4
-21.25°	2	2	2	2	3	3	3	3	4	4	4



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	2	2	3	3	3	3	3	4	4
-23.75°	2	2	2	2	3	3	3	3	3	4	4
-25°	2	2	2	2	2	3	3	3	3	4	4
-26.25°	2	2	2	2	2	3	3	3	3	3	4
-27.5°	2	2	2	2	2	3	3	3	3	3	4
-28.75°	2	2	2	2	2	2	3	3	3	3	3
-30°	1	2	2	2	2	2	3	3	3	3	3
-31.25°	1	2	2	2	2	2	2	3	3	3	3
-32.5°	1	2	2	2	2	2	2	3	3	3	3
-33.75°	1	1	2	2	2	2	2	3	3	3	3
-35°	1	1	2	2	2	2	2	2	3	3	3
-36.25°	1	1	1	2	2	2	2	2	2	3	3
-37.5°	1	1	1	2	2	2	2	2	2	2	3
-38.75°	1	1	1	1	2	2	2	2	2	2	2
-40°	1	1	1	1	2	2	2	2	2	2	2
-41.25°	1	1	1	1	1	2	2	2	2	2	2
-42.5°	1	1	1	1	1	2	2	2	2	2	2
-43.75°	1	1	1	1	1	1	2	2	2	2	2
-45°	1	1	1	1	1	1	1	2	2	2	2
-46.25°	1	1	1	1	1	1	1	1	2	2	2
-47.5°	1	1	1	1	1	1	1	1	2	2	2
-48.75°	1	1	1	1	1	1	1	1	1	2	2
-50°	1	1	1	1	1	1	1	1	1	1	2
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	1	1	1	1	1	1	1	1	1	1
-71.25°	0	0	0	1	1	1	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	1	1	1	1
73.75°	0	0	0	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	2
57.5°	1	1	1	1	1	1	1	2	2	2	2
56.25°	1	1	1	1	1	2	2	2	2	2	2
55°	1	1	1	1	2	2	2	2	2	2	2
53.75°	1	1	1	2	2	2	2	2	2	2	2
52.5°	1	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	2	2	2	2	2	2	2	2	2	2	2
48.75°	2	2	2	2	2	2	2	2	2	2	3
47.5°	2	2	2	2	2	2	2	2	2	3	3
46.25°	2	2	2	2	2	2	2	3	3	3	3
45°	2	2	2	2	2	2	3	3	3	3	3
43.75°	2	2	2	2	2	3	3	3	3	3	3
42.5°	2	2	2	3	3	3	3	3	3	3	3
41.25°	2	2	3	3	3	3	3	3	3	3	4
40°	2	3	3	3	3	3	3	3	3	4	4
38.75°	3	3	3	3	3	3	3	3	4	4	4
37.5°	3	3	3	3	3	3	4	4	4	4	5
36.25°	3	3	3	3	3	4	4	4	4	5	5
35°	3	3	3	3	4	4	4	4	4	5	5



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	3	4	4	4	4	4	5	5	5
32.5°	3	3	4	4	4	4	4	5	5	5	5
31.25°	3	4	4	4	4	4	5	5	5	5	6
30°	4	4	4	4	4	4	5	5	5	6	6
28.75°	4	4	4	4	4	5	5	5	6	6	6
27.5°	4	4	4	4	5	5	5	5	6	6	7
26.25°	4	4	4	4	5	5	5	6	6	7	8
25°	4	4	4	5	5	5	6	6	7	8	9
23.75°	4	4	4	5	5	5	6	7	8	8	9
22.5°	4	4	5	5	5	6	7	7	8	9	11
21.25°	4	4	5	5	6	6	7	8	9	10	13
20°	4	5	5	5	6	7	7	8	10	12	15
18.75°	4	5	5	6	6	7	8	9	10	14	17
17.5°	4	5	5	6	6	7	8	10	12	16	20
16.25°	5	5	5	6	7	8	9	10	14	18	24
15°	5	5	6	6	7	8	10	11	16	20	28
13.75°	5	5	6	6	7	9	10	13	17	23	32
12.5°	5	6	6	7	8	9	11	14	19	26	36
11.25°	5	6	6	7	8	10	11	16	20	30	39
10°	5	6	6	7	8	10	12	17	23	33	43
8.75°	5	6	7	7	9	11	14	19	25	36	49
7.5°	6	6	7	8	9	11	15	20	28	38	55
6.25°	6	6	7	8	9	11	16	21	30	41	60
5°	6	6	7	8	10	12	16	22	32	43	64
3.75°	6	6	7	8	10	12	17	23	33	45	68
2.5°	6	6	7	8	10	12	18	23	35	46	72
1.25°	6	6	7	8	10	13	18	24	36	47	74
0°	6	6	7	8	10	13	19	25	36	48	76
-1.25°	6	6	7	8	10	13	18	24	36	47	74
-2.5°	6	6	7	8	10	12	18	23	35	46	72
-3.75°	6	6	7	8	10	12	17	23	33	45	68
-5°	6	6	7	8	10	12	16	22	32	43	64
-6.25°	6	6	7	8	9	11	16	21	30	41	60
-7.5°	6	6	7	8	9	11	15	20	28	38	55
-8.75°	5	6	7	7	9	11	14	19	25	36	49
-10°	5	6	6	7	8	10	12	17	23	33	43
-11.25°	5	6	6	7	8	10	11	16	20	30	39
-12.5°	5	6	6	7	8	9	11	14	19	26	36
-13.75°	5	5	6	6	7	9	10	13	17	23	32
-15°	5	5	6	6	7	8	10	11	16	20	28
-16.25°	5	5	5	6	7	8	9	10	14	18	24
-17.5°	4	5	5	6	6	7	8	10	12	16	20
-18.75°	4	5	5	6	6	7	8	9	10	14	17
-20°	4	5	5	5	6	7	7	8	10	12	15
-21.25°	4	4	5	5	6	6	7	8	9	10	13



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	4	5	5	5	6	7	7	8	9	11
-23.75°	4	4	4	5	5	5	6	7	8	8	9
-25°	4	4	4	5	5	5	6	6	7	8	9
-26.25°	4	4	4	4	5	5	5	6	6	7	8
-27.5°	4	4	4	4	5	5	5	5	6	6	7
-28.75°	4	4	4	4	4	5	5	5	6	6	6
-30°	4	4	4	4	4	4	5	5	5	6	6
-31.25°	3	4	4	4	4	4	5	5	5	5	6
-32.5°	3	3	4	4	4	4	4	5	5	5	5
-33.75°	3	3	3	4	4	4	4	4	5	5	5
-35°	3	3	3	3	4	4	4	4	4	5	5
-36.25°	3	3	3	3	3	4	4	4	4	5	5
-37.5°	3	3	3	3	3	3	4	4	4	4	5
-38.75°	3	3	3	3	3	3	3	3	4	4	4
-40°	2	3	3	3	3	3	3	3	3	4	4
-41.25°	2	2	3	3	3	3	3	3	3	3	4
-42.5°	2	2	2	3	3	3	3	3	3	3	3
-43.75°	2	2	2	2	2	3	3	3	3	3	3
-45°	2	2	2	2	2	2	3	3	3	3	3
-46.25°	2	2	2	2	2	2	2	3	3	3	3
-47.5°	2	2	2	2	2	2	2	2	2	3	3
-48.75°	2	2	2	2	2	2	2	2	2	2	3
-50°	2	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	1	2	2	2	2	2	2	2	2	2	2
-53.75°	1	1	1	2	2	2	2	2	2	2	2
-55°	1	1	1	1	2	2	2	2	2	2	2
-56.25°	1	1	1	1	1	2	2	2	2	2	2
-57.5°	1	1	1	1	1	1	1	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	1	1	2
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	1	1
76.25°	0	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	4	4
47.5°	3	3	3	3	3	3	3	4	4	4	4
46.25°	3	3	3	3	3	4	4	4	4	4	4
45°	3	3	3	4	4	4	4	4	4	4	4
43.75°	3	3	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	4	4	4	5	4	4	4	4	4	5	5
40°	4	4	5	5	4	4	4	5	5	5	5
38.75°	4	5	5	5	5	5	5	5	5	5	6
37.5°	5	5	5	5	5	5	5	5	6	6	6
36.25°	5	5	5	5	5	5	6	6	6	7	7
35°	5	5	5	5	6	6	6	7	7	8	8



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	5	5	6	6	6	7	7	8	8	9	9
32.5°	5	6	6	7	7	8	8	9	9	10	11
31.25°	6	6	7	7	8	9	9	10	11	12	13
30°	6	7	8	8	9	10	11	12	13	14	16
28.75°	7	8	9	10	11	12	14	15	16	18	20
27.5°	8	9	10	12	13	15	17	18	20	22	24
26.25°	9	10	12	14	17	19	21	24	26	27	32
25°	10	12	14	17	21	24	28	31	34	37	40
23.75°	12	14	17	22	25	31	36	40	45	49	51
22.5°	14	17	22	26	33	40	45	52	57	62	67
21.25°	16	21	26	33	42	49	57	65	71	78	84
20°	19	26	31	42	51	61	70	79	88	95	101
18.75°	24	30	40	51	62	74	84	95	105	114	121
17.5°	28	35	49	61	75	88	100	112	123	133	144
16.25°	33	44	59	73	88	102	117	130	143	156	169
15°	37	52	69	85	102	118	134	149	163	181	197
13.75°	43	61	78	97	116	134	151	168	188	209	228
12.5°	50	69	88	108	128	150	169	189	214	238	261
11.25°	57	77	98	119	142	166	188	213	242	270	296
10°	64	85	107	130	156	182	208	238	271	303	334
8.75°	71	93	117	141	171	199	229	264	302	339	375
7.5°	77	101	126	153	185	216	251	290	335	377	416
6.25°	83	108	134	165	199	234	272	317	368	414	457
5°	89	115	142	176	213	250	293	345	400	450	496
3.75°	94	121	149	187	226	267	314	371	432	485	533
2.5°	98	127	155	196	238	282	333	396	462	518	569
1.25°	101	131	161	205	249	296	351	419	490	549	603
0°	104	135	165	212	258	308	366	440	515	577	635
-1.25°	101	131	161	205	249	296	351	419	490	549	603
-2.5°	98	127	155	196	238	282	333	396	462	518	569
-3.75°	94	121	149	187	226	267	314	371	432	485	533
-5°	89	115	142	176	213	250	293	345	400	450	496
-6.25°	83	108	134	165	199	234	272	317	368	414	457
-7.5°	77	101	126	153	185	216	251	290	335	377	416
-8.75°	71	93	117	141	171	199	229	264	302	339	375
-10°	64	85	107	130	156	182	208	238	271	303	334
-11.25°	57	77	98	119	142	166	188	213	242	270	296
-12.5°	50	69	88	108	128	150	169	189	214	238	261
-13.75°	43	61	78	97	116	134	151	168	188	209	228
-15°	37	52	69	85	102	118	134	149	163	181	197
-16.25°	33	44	59	73	88	102	117	130	143	156	169
-17.5°	28	35	49	61	75	88	100	112	123	133	144
-18.75°	24	30	40	51	62	74	84	95	105	114	121
-20°	19	26	31	42	51	61	70	79	88	95	101
-21.25°	16	21	26	33	42	49	57	65	71	78	84



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	14	17	22	26	33	40	45	52	57	62	67
-23.75°	12	14	17	22	25	31	36	40	45	49	51
-25°	10	12	14	17	21	24	28	31	34	37	40
-26.25°	9	10	12	14	17	19	21	24	26	27	32
-27.5°	8	9	10	12	13	15	17	18	20	22	24
-28.75°	7	8	9	10	11	12	14	15	16	18	20
-30°	6	7	8	8	9	10	11	12	13	14	16
-31.25°	6	6	7	7	8	9	9	10	11	12	13
-32.5°	5	6	6	7	7	8	8	9	9	10	11
-33.75°	5	5	6	6	6	7	7	8	8	9	9
-35°	5	5	5	5	6	6	6	7	7	8	8
-36.25°	5	5	5	5	5	5	6	6	6	7	7
-37.5°	5	5	5	5	5	5	5	5	6	6	6
-38.75°	4	5	5	5	5	5	5	5	5	5	6
-40°	4	4	5	5	4	4	4	5	5	5	5
-41.25°	4	4	4	5	4	4	4	4	4	5	5
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	3	3	4	4	4	4	4	4	4	4	4
-45°	3	3	3	4	4	4	4	4	4	4	4
-46.25°	3	3	3	3	3	4	4	4	4	4	4
-47.5°	3	3	3	3	3	3	3	4	4	4	4
-48.75°	3	3	3	3	3	3	3	3	3	4	4
-50°	2	3	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	3	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	1	1



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	1	1
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	5	5	5	5
42.5°	4	4	5	5	5	5	5	5	5	5	5
41.25°	5	5	5	5	5	5	5	5	6	6	6
40°	5	5	5	6	6	6	6	6	6	6	6
38.75°	6	6	6	6	6	7	7	7	7	7	7
37.5°	6	7	7	7	7	7	7	7	8	8	8
36.25°	7	8	8	8	8	8	8	8	8	8	8
35°	8	9	9	9	9	9	9	9	9	10	10



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	10	10	10	10	11	11	11	11	11	11	12
32.5°	12	12	13	13	14	13	13	13	13	13	13
31.25°	14	15	16	16	17	17	16	15	15	15	15
30°	17	19	19	21	21	21	20	18	17	18	19
28.75°	21	23	25	26	26	26	26	24	21	22	22
27.5°	28	30	32	33	35	35	33	31	28	28	29
26.25°	35	38	41	43	44	44	43	41	38	35	37
25°	44	49	52	54	55	55	54	52	50	46	47
23.75°	56	61	65	67	68	69	68	67	63	59	58
22.5°	70	74	78	81	83	84	84	82	78	74	69
21.25°	87	89	94	98	100	101	100	98	95	90	83
20°	106	109	111	115	117	119	118	116	113	108	102
18.75°	128	132	134	133	136	138	138	136	133	129	123
17.5°	153	159	161	158	156	158	159	157	155	152	148
16.25°	180	188	192	191	184	180	180	181	180	178	175
15°	211	221	227	228	221	208	204	207	208	207	204
13.75°	244	258	268	268	262	251	237	235	237	237	233
12.5°	281	299	309	311	305	296	284	269	268	267	266
11.25°	321	343	353	355	351	343	331	318	302	301	301
10°	365	387	399	401	398	390	379	365	351	338	339
8.75°	410	432	445	447	444	437	425	412	400	389	379
7.5°	452	476	489	494	490	482	471	459	448	438	431
6.25°	494	520	531	534	532	526	516	504	493	484	479
5°	536	561	572	573	570	561	552	544	536	528	525
3.75°	576	601	612	611	605	594	582	572	565	564	566
2.5°	615	641	650	648	639	625	610	598	590	587	589
1.25°	652	679	687	684	673	657	638	624	613	609	609
0°	687	717	725	721	708	689	667	650	637	630	627
-1.25°	652	679	687	684	673	657	638	624	613	609	609
-2.5°	615	641	650	648	639	625	610	598	590	587	589
-3.75°	576	601	612	611	605	594	582	572	565	564	566
-5°	536	561	572	573	570	561	552	544	536	528	525
-6.25°	494	520	531	534	532	526	516	504	493	484	479
-7.5°	452	476	489	494	490	482	471	459	448	438	431
-8.75°	410	432	445	447	444	437	425	412	400	389	379
-10°	365	387	399	401	398	390	379	365	351	338	339
-11.25°	321	343	353	355	351	343	331	318	302	301	301
-12.5°	281	299	309	311	305	296	284	269	268	267	266
-13.75°	244	258	268	268	262	251	237	235	237	237	233
-15°	211	221	227	228	221	208	204	207	208	207	204
-16.25°	180	188	192	191	184	180	180	181	180	178	175
-17.5°	153	159	161	158	156	158	159	157	155	152	148
-18.75°	128	132	134	133	136	138	138	136	133	129	123
-20°	106	109	111	115	117	119	118	116	113	108	102
-21.25°	87	89	94	98	100	101	100	98	95	90	83



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	70	74	78	81	83	84	84	82	78	74	69
-23.75°	56	61	65	67	68	69	68	67	63	59	58
-25°	44	49	52	54	55	55	54	52	50	46	47
-26.25°	35	38	41	43	44	44	43	41	38	35	37
-27.5°	28	30	32	33	35	35	33	31	28	28	29
-28.75°	21	23	25	26	26	26	26	24	21	22	22
-30°	17	19	19	21	21	21	20	18	17	18	19
-31.25°	14	15	16	16	17	17	16	15	15	15	15
-32.5°	12	12	13	13	14	13	13	13	13	13	13
-33.75°	10	10	10	10	11	11	11	11	11	11	12
-35°	8	9	9	9	9	9	9	9	9	10	10
-36.25°	7	8	8	8	8	8	8	8	8	8	8
-37.5°	6	7	7	7	7	7	7	7	8	8	8
-38.75°	6	6	6	6	6	7	7	7	7	7	7
-40°	5	5	5	6	6	6	6	6	6	6	6
-41.25°	5	5	5	5	5	5	5	5	6	6	6
-42.5°	4	4	5	5	5	5	5	5	5	5	5
-43.75°	4	4	4	4	4	4	4	5	5	5	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	3	4	4	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	1	0	0	0	0	0	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	5	5	5	5	5	5	5	5	5
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	6	5	5	5	5
41.25°	6	6	6	6	6	6	6	6	6	6	6
40°	7	7	7	7	7	6	6	6	7	7	7
38.75°	7	7	7	7	7	7	7	7	7	7	7
37.5°	8	8	8	7	7	7	7	7	7	7	8
36.25°	9	9	9	9	9	9	9	9	9	9	9
35°	10	10	10	10	10	10	10	10	10	10	10



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	12	12	12	12	12	12	11	12	12	12	12
32.5°	13	14	13	13	13	13	13	13	13	13	13
31.25°	16	16	16	16	16	15	15	15	16	16	16
30°	19	19	19	18	18	17	16	17	18	18	19
28.75°	23	23	23	23	22	21	20	21	22	23	23
27.5°	30	30	30	30	29	28	26	28	29	30	30
26.25°	38	39	39	39	38	36	35	36	38	39	39
25°	48	49	49	49	47	46	44	46	47	49	49
23.75°	59	60	60	59	57	56	53	56	57	59	60
22.5°	71	71	71	71	69	67	64	67	69	71	71
21.25°	84	85	86	85	83	81	78	81	83	85	86
20°	100	101	102	101	99	96	92	96	99	101	102
18.75°	117	119	120	119	117	114	109	114	117	119	120
17.5°	141	141	142	141	139	134	129	134	139	141	142
16.25°	169	164	164	164	161	156	150	156	161	164	164
15°	198	189	189	189	186	181	174	181	186	189	189
13.75°	228	220	217	217	214	208	200	208	214	217	217
12.5°	262	256	248	249	247	242	234	242	247	249	248
11.25°	299	295	288	287	287	283	274	283	287	287	288
10°	339	338	333	330	333	330	320	330	333	330	333
8.75°	382	384	384	381	384	382	374	382	384	381	384
7.5°	427	432	436	436	438	438	430	438	438	436	436
6.25°	478	480	487	490	490	492	485	492	490	490	487
5°	525	529	533	540	542	543	537	543	542	540	533
3.75°	567	572	576	581	586	588	583	588	586	581	576
2.5°	596	607	611	615	619	622	619	622	619	615	611
1.25°	613	621	629	637	643	644	645	644	643	637	629
0°	628	633	639	645	650	652	656	652	650	645	639
-1.25°	613	621	629	637	643	644	645	644	643	637	629
-2.5°	596	607	611	615	619	622	619	622	619	615	611
-3.75°	567	572	576	581	586	588	583	588	586	581	576
-5°	525	529	533	540	542	543	537	543	542	540	533
-6.25°	478	480	487	490	490	492	485	492	490	490	487
-7.5°	427	432	436	436	438	438	430	438	438	436	436
-8.75°	382	384	384	381	384	382	374	382	384	381	384
-10°	339	338	333	330	333	330	320	330	333	330	333
-11.25°	299	295	288	287	287	283	274	283	287	287	288
-12.5°	262	256	248	249	247	242	234	242	247	249	248
-13.75°	228	220	217	217	214	208	200	208	214	217	217
-15°	198	189	189	189	186	181	174	181	186	189	189
-16.25°	169	164	164	164	161	156	150	156	161	164	164
-17.5°	141	141	142	141	139	134	129	134	139	141	142
-18.75°	117	119	120	119	117	114	109	114	117	119	120
-20°	100	101	102	101	99	96	92	96	99	101	102
-21.25°	84	85	86	85	83	81	78	81	83	85	86



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	71	71	71	71	69	67	64	67	69	71	71
-23.75°	59	60	60	59	57	56	53	56	57	59	60
-25°	48	49	49	49	47	46	44	46	47	49	49
-26.25°	38	39	39	39	38	36	35	36	38	39	39
-27.5°	30	30	30	30	29	28	26	28	29	30	30
-28.75°	23	23	23	23	22	21	20	21	22	23	23
-30°	19	19	19	18	18	17	16	17	18	18	19
-31.25°	16	16	16	16	16	15	15	15	16	16	16
-32.5°	13	14	13	13	13	13	13	13	13	13	13
-33.75°	12	12	12	12	12	12	11	12	12	12	12
-35°	10	10	10	10	10	10	10	10	10	10	10
-36.25°	9	9	9	9	9	9	9	9	9	9	9
-37.5°	8	8	8	7	7	7	7	7	7	7	8
-38.75°	7	7	7	7	7	7	7	7	7	7	7
-40°	7	7	7	7	7	6	6	6	7	7	7
-41.25°	6	6	6	6	6	6	6	6	6	6	6
-42.5°	5	5	5	5	5	5	6	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	4	4	5	5	5	5	5	5	5	5	5
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	0	0	0	0	0	1	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	5	5	5	4	4	4	4	4
42.5°	5	5	5	5	5	5	5	5	5	5	5
41.25°	6	6	6	6	6	5	5	5	5	5	5
40°	7	7	6	6	6	6	6	6	6	6	5
38.75°	7	7	7	7	7	7	7	7	6	6	6
37.5°	8	8	8	8	8	7	7	7	7	7	7
36.25°	9	9	8	8	8	8	8	8	8	8	8
35°	10	10	10	10	9	9	9	9	9	9	9



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	12	12	12	11	11	11	11	11	11	10	10
32.5°	14	13	13	13	13	13	13	13	14	13	13
31.25°	16	16	15	15	15	15	16	17	17	16	16
30°	19	19	19	18	17	18	20	21	21	21	19
28.75°	23	23	22	22	21	24	26	26	26	26	25
27.5°	30	30	29	28	28	31	33	35	35	33	32
26.25°	39	38	37	35	38	41	43	44	44	43	41
25°	49	48	47	46	50	52	54	55	55	54	52
23.75°	60	59	58	59	63	67	68	69	68	67	65
22.5°	71	71	69	74	78	82	84	84	83	81	78
21.25°	85	84	83	90	95	98	100	101	100	98	94
20°	101	100	102	108	113	116	118	119	117	115	111
18.75°	119	117	123	129	133	136	138	138	136	133	134
17.5°	141	141	148	152	155	157	159	158	156	158	161
16.25°	164	169	175	178	180	181	180	180	184	191	192
15°	189	198	204	207	208	207	204	208	221	228	227
13.75°	220	228	233	237	237	235	237	251	262	268	268
12.5°	256	262	266	267	268	269	284	296	305	311	309
11.25°	295	299	301	301	302	318	331	343	351	355	353
10°	338	339	339	338	351	365	379	390	398	401	399
8.75°	384	382	379	389	400	412	425	437	444	447	445
7.5°	432	427	431	438	448	459	471	482	490	494	489
6.25°	480	478	479	484	493	504	516	526	532	534	531
5°	529	525	525	528	536	544	552	561	570	573	572
3.75°	572	567	566	564	565	572	582	594	605	611	612
2.5°	607	596	589	587	590	598	610	625	639	648	650
1.25°	621	613	609	609	613	624	638	657	673	684	687
0°	633	628	627	630	637	650	667	689	708	721	725
-1.25°	621	613	609	609	613	624	638	657	673	684	687
-2.5°	607	596	589	587	590	598	610	625	639	648	650
-3.75°	572	567	566	564	565	572	582	594	605	611	612
-5°	529	525	525	528	536	544	552	561	570	573	572
-6.25°	480	478	479	484	493	504	516	526	532	534	531
-7.5°	432	427	431	438	448	459	471	482	490	494	489
-8.75°	384	382	379	389	400	412	425	437	444	447	445
-10°	338	339	339	338	351	365	379	390	398	401	399
-11.25°	295	299	301	301	302	318	331	343	351	355	353
-12.5°	256	262	266	267	268	269	284	296	305	311	309
-13.75°	220	228	233	237	237	235	237	251	262	268	268
-15°	189	198	204	207	208	207	204	208	221	228	227
-16.25°	164	169	175	178	180	181	180	180	184	191	192
-17.5°	141	141	148	152	155	157	159	158	156	158	161
-18.75°	119	117	123	129	133	136	138	138	136	133	134
-20°	101	100	102	108	113	116	118	119	117	115	111
-21.25°	85	84	83	90	95	98	100	101	100	98	94



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	71	71	69	74	78	82	84	84	83	81	78
-23.75°	60	59	58	59	63	67	68	69	68	67	65
-25°	49	48	47	46	50	52	54	55	55	54	52
-26.25°	39	38	37	35	38	41	43	44	44	43	41
-27.5°	30	30	29	28	28	31	33	35	35	33	32
-28.75°	23	23	22	22	21	24	26	26	26	26	25
-30°	19	19	19	18	17	18	20	21	21	21	19
-31.25°	16	16	15	15	15	15	16	17	17	16	16
-32.5°	14	13	13	13	13	13	13	13	14	13	13
-33.75°	12	12	12	11	11	11	11	11	11	10	10
-35°	10	10	10	10	9	9	9	9	9	9	9
-36.25°	9	9	8	8	8	8	8	8	8	8	8
-37.5°	8	8	8	8	8	7	7	7	7	7	7
-38.75°	7	7	7	7	7	7	7	7	6	6	6
-40°	7	7	6	6	6	6	6	6	6	6	5
-41.25°	6	6	6	6	6	5	5	5	5	5	5
-42.5°	5	5	5	5	5	5	5	5	5	5	5
-43.75°	5	5	5	5	5	5	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	0	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	1	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	3	3	3	3	3	3	3	3	3	3	2
50°	4	3	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	4	3	3	3	3	3	3	3
47.5°	4	4	4	4	4	4	3	3	3	3	3
46.25°	4	4	4	4	4	4	4	4	3	3	3
45°	4	4	4	4	4	4	4	4	4	4	3
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	4	4	4
41.25°	5	5	5	5	4	4	4	4	4	5	4
40°	5	5	5	5	5	5	4	4	4	5	5
38.75°	6	6	6	5	5	5	5	5	5	5	5
37.5°	7	6	6	6	6	5	5	5	5	5	5
36.25°	8	7	7	7	6	6	6	5	5	5	5
35°	9	8	8	8	7	7	6	6	6	5	5



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	10	10	9	9	8	8	7	7	6	6	6
32.5°	12	12	11	10	9	9	8	8	7	7	6
31.25°	15	14	13	12	11	10	9	9	8	7	7
30°	19	17	16	14	13	12	11	10	9	8	8
28.75°	23	21	20	18	16	15	14	12	11	10	9
27.5°	30	28	24	22	20	18	17	15	13	12	10
26.25°	38	35	32	27	26	24	21	19	17	14	12
25°	49	44	40	37	34	31	28	24	21	17	14
23.75°	61	56	51	49	45	40	36	31	25	22	17
22.5°	74	70	67	62	57	52	45	40	33	26	22
21.25°	89	87	84	78	71	65	57	49	42	33	26
20°	109	106	101	95	88	79	70	61	51	42	31
18.75°	132	128	121	114	105	95	84	74	62	51	40
17.5°	159	153	144	133	123	112	100	88	75	61	49
16.25°	188	180	169	156	143	130	117	102	88	73	59
15°	221	211	197	181	163	149	134	118	102	85	69
13.75°	258	244	228	209	188	168	151	134	116	97	78
12.5°	299	281	261	238	214	189	169	150	128	108	88
11.25°	343	321	296	270	242	213	188	166	142	119	98
10°	387	365	334	303	271	238	208	182	156	130	107
8.75°	432	410	375	339	302	264	229	199	171	141	117
7.5°	476	452	416	377	335	290	251	216	185	153	126
6.25°	520	494	457	414	368	317	272	234	199	165	134
5°	561	536	496	450	400	345	293	250	213	176	142
3.75°	601	576	533	485	432	371	314	267	226	187	149
2.5°	641	615	569	518	462	396	333	282	238	196	155
1.25°	679	652	603	549	490	419	351	296	249	205	161
0°	717	687	635	577	515	440	366	308	258	212	165
-1.25°	679	652	603	549	490	419	351	296	249	205	161
-2.5°	641	615	569	518	462	396	333	282	238	196	155
-3.75°	601	576	533	485	432	371	314	267	226	187	149
-5°	561	536	496	450	400	345	293	250	213	176	142
-6.25°	520	494	457	414	368	317	272	234	199	165	134
-7.5°	476	452	416	377	335	290	251	216	185	153	126
-8.75°	432	410	375	339	302	264	229	199	171	141	117
-10°	387	365	334	303	271	238	208	182	156	130	107
-11.25°	343	321	296	270	242	213	188	166	142	119	98
-12.5°	299	281	261	238	214	189	169	150	128	108	88
-13.75°	258	244	228	209	188	168	151	134	116	97	78
-15°	221	211	197	181	163	149	134	118	102	85	69
-16.25°	188	180	169	156	143	130	117	102	88	73	59
-17.5°	159	153	144	133	123	112	100	88	75	61	49
-18.75°	132	128	121	114	105	95	84	74	62	51	40
-20°	109	106	101	95	88	79	70	61	51	42	31
-21.25°	89	87	84	78	71	65	57	49	42	33	26



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	74	70	67	62	57	52	45	40	33	26	22
-23.75°	61	56	51	49	45	40	36	31	25	22	17
-25°	49	44	40	37	34	31	28	24	21	17	14
-26.25°	38	35	32	27	26	24	21	19	17	14	12
-27.5°	30	28	24	22	20	18	17	15	13	12	10
-28.75°	23	21	20	18	16	15	14	12	11	10	9
-30°	19	17	16	14	13	12	11	10	9	8	8
-31.25°	15	14	13	12	11	10	9	9	8	7	7
-32.5°	12	12	11	10	9	9	8	8	7	7	6
-33.75°	10	10	9	9	8	8	7	7	6	6	6
-35°	9	8	8	8	7	7	6	6	6	5	5
-36.25°	8	7	7	7	6	6	6	5	5	5	5
-37.5°	7	6	6	6	6	5	5	5	5	5	5
-38.75°	6	6	6	5	5	5	5	5	5	5	5
-40°	5	5	5	5	5	5	4	4	4	5	5
-41.25°	5	5	5	5	4	4	4	4	4	5	4
-42.5°	4	4	4	4	4	4	4	4	4	4	4
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	3
-46.25°	4	4	4	4	4	4	4	4	3	3	3
-47.5°	4	4	4	4	4	4	3	3	3	3	3
-48.75°	4	4	4	4	3	3	3	3	3	3	3
-50°	4	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	1	1	1	1
-61.25°	2	2	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	1	1	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	2	2	2	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	1	1	1	1	1
56.25°	2	2	2	2	2	2	2	2	1	1	1
55°	2	2	2	2	2	2	2	2	2	1	1
53.75°	2	2	2	2	2	2	2	2	2	2	1
52.5°	2	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	3	2	2	2	2	2	2	2	2	2	2
48.75°	3	3	3	2	2	2	2	2	2	2	2
47.5°	3	3	3	3	2	2	2	2	2	2	2
46.25°	3	3	3	3	3	3	2	2	2	2	2
45°	3	3	3	3	3	3	3	2	2	2	2
43.75°	3	3	3	3	3	3	3	3	2	2	2
42.5°	4	4	3	3	3	3	3	3	3	3	2
41.25°	4	4	4	3	3	3	3	3	3	3	3
40°	4	4	4	4	3	3	3	3	3	3	3
38.75°	5	4	4	4	4	3	3	3	3	3	3
37.5°	5	5	5	4	4	4	4	3	3	3	3
36.25°	5	5	5	5	4	4	4	4	3	3	3
35°	5	5	5	5	4	4	4	4	4	3	3



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	5	5	5	5	5	4	4	4	4	4	3
32.5°	6	5	5	5	5	5	4	4	4	4	4
31.25°	6	6	6	5	5	5	5	4	4	4	4
30°	7	6	6	6	5	5	5	4	4	4	4
28.75°	8	7	6	6	6	5	5	5	4	4	4
27.5°	9	8	7	6	6	5	5	5	5	4	4
26.25°	10	9	8	7	6	6	5	5	5	4	4
25°	12	10	9	8	7	6	6	5	5	5	4
23.75°	14	12	9	8	8	7	6	5	5	5	4
22.5°	17	14	11	9	8	7	7	6	5	5	5
21.25°	21	16	13	10	9	8	7	6	6	5	5
20°	26	19	15	12	10	8	7	7	6	5	5
18.75°	30	24	17	14	10	9	8	7	6	6	5
17.5°	35	28	20	16	12	10	8	7	6	6	5
16.25°	44	33	24	18	14	10	9	8	7	6	5
15°	52	37	28	20	16	11	10	8	7	6	6
13.75°	61	43	32	23	17	13	10	9	7	6	6
12.5°	69	50	36	26	19	14	11	9	8	7	6
11.25°	77	57	39	30	20	16	11	10	8	7	6
10°	85	64	43	33	23	17	12	10	8	7	6
8.75°	93	71	49	36	25	19	14	11	9	7	7
7.5°	101	77	55	38	28	20	15	11	9	8	7
6.25°	108	83	60	41	30	21	16	11	9	8	7
5°	115	89	64	43	32	22	16	12	10	8	7
3.75°	121	94	68	45	33	23	17	12	10	8	7
2.5°	127	98	72	46	35	23	18	12	10	8	7
1.25°	131	101	74	47	36	24	18	13	10	8	7
0°	135	104	76	48	36	25	19	13	10	8	7
-1.25°	131	101	74	47	36	24	18	13	10	8	7
-2.5°	127	98	72	46	35	23	18	12	10	8	7
-3.75°	121	94	68	45	33	23	17	12	10	8	7
-5°	115	89	64	43	32	22	16	12	10	8	7
-6.25°	108	83	60	41	30	21	16	11	9	8	7
-7.5°	101	77	55	38	28	20	15	11	9	8	7
-8.75°	93	71	49	36	25	19	14	11	9	7	7
-10°	85	64	43	33	23	17	12	10	8	7	6
-11.25°	77	57	39	30	20	16	11	10	8	7	6
-12.5°	69	50	36	26	19	14	11	9	8	7	6
-13.75°	61	43	32	23	17	13	10	9	7	6	6
-15°	52	37	28	20	16	11	10	8	7	6	6
-16.25°	44	33	24	18	14	10	9	8	7	6	5
-17.5°	35	28	20	16	12	10	8	7	6	6	5
-18.75°	30	24	17	14	10	9	8	7	6	6	5
-20°	26	19	15	12	10	8	7	7	6	5	5
-21.25°	21	16	13	10	9	8	7	6	6	5	5



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	17	14	11	9	8	7	7	6	5	5	5
-23.75°	14	12	9	8	8	7	6	5	5	5	4
-25°	12	10	9	8	7	6	6	5	5	5	4
-26.25°	10	9	8	7	6	6	5	5	5	4	4
-27.5°	9	8	7	6	6	5	5	5	5	4	4
-28.75°	8	7	6	6	6	5	5	5	4	4	4
-30°	7	6	6	6	5	5	5	4	4	4	4
-31.25°	6	6	6	5	5	5	5	4	4	4	4
-32.5°	6	5	5	5	5	5	4	4	4	4	4
-33.75°	5	5	5	5	5	4	4	4	4	4	3
-35°	5	5	5	5	4	4	4	4	4	3	3
-36.25°	5	5	5	5	4	4	4	4	3	3	3
-37.5°	5	5	5	4	4	4	4	3	3	3	3
-38.75°	5	4	4	4	4	3	3	3	3	3	3
-40°	4	4	4	4	3	3	3	3	3	3	3
-41.25°	4	4	4	3	3	3	3	3	3	3	3
-42.5°	4	4	3	3	3	3	3	3	3	3	2
-43.75°	3	3	3	3	3	3	3	3	2	2	2
-45°	3	3	3	3	3	3	3	2	2	2	2
-46.25°	3	3	3	3	3	3	2	2	2	2	2
-47.5°	3	3	3	3	2	2	2	2	2	2	2
-48.75°	3	3	3	2	2	2	2	2	2	2	2
-50°	3	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	2	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	1
-55°	2	2	2	2	2	2	2	2	2	1	1
-56.25°	2	2	2	2	2	2	2	2	1	1	1
-57.5°	2	2	2	2	2	2	1	1	1	1	1
-58.75°	2	2	2	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	0
-75°	1	1	1	1	1	1	0	0	0	0	0
-76.25°	1	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	0	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	1	1	1	0
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	2	1	1	1	1	1	1	1	1	1	1
51.25°	2	2	1	1	1	1	1	1	1	1	1
50°	2	2	2	1	1	1	1	1	1	1	1
48.75°	2	2	2	2	1	1	1	1	1	1	1
47.5°	2	2	2	2	2	1	1	1	1	1	1
46.25°	2	2	2	2	2	1	1	1	1	1	1
45°	2	2	2	2	2	2	1	1	1	1	1
43.75°	2	2	2	2	2	2	2	1	1	1	1
42.5°	2	2	2	2	2	2	2	2	1	1	1
41.25°	2	2	2	2	2	2	2	2	1	1	1
40°	3	2	2	2	2	2	2	2	2	1	1
38.75°	3	3	2	2	2	2	2	2	2	1	1
37.5°	3	3	3	2	2	2	2	2	2	2	1
36.25°	3	3	3	3	2	2	2	2	2	2	1
35°	3	3	3	3	3	2	2	2	2	2	2



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	3	3	3	2	2	2	2	2
32.5°	3	3	3	3	3	3	2	2	2	2	2
31.25°	4	3	3	3	3	3	2	2	2	2	2
30°	4	4	3	3	3	3	3	2	2	2	2
28.75°	4	4	3	3	3	3	3	2	2	2	2
27.5°	4	4	4	3	3	3	3	3	2	2	2
26.25°	4	4	4	3	3	3	3	3	2	2	2
25°	4	4	4	4	3	3	3	3	2	2	2
23.75°	4	4	4	4	3	3	3	3	3	2	2
22.5°	4	4	4	4	3	3	3	3	3	2	2
21.25°	4	4	4	4	4	3	3	3	3	2	2
20°	5	4	4	4	4	3	3	3	3	2	2
18.75°	5	4	4	4	4	3	3	3	3	2	2
17.5°	5	4	4	4	4	3	3	3	3	3	2
16.25°	5	5	4	4	4	4	3	3	3	3	2
15°	5	5	4	4	4	4	3	3	3	3	2
13.75°	5	5	4	4	4	4	3	3	3	3	2
12.5°	6	5	4	4	4	4	3	3	3	3	2
11.25°	6	5	5	4	4	4	3	3	3	3	2
10°	6	5	5	4	4	4	3	3	3	3	3
8.75°	6	5	5	4	4	4	4	3	3	3	3
7.5°	6	6	5	4	4	4	4	3	3	3	3
6.25°	6	6	5	4	4	4	4	3	3	3	3
5°	6	6	5	4	4	4	4	3	3	3	3
3.75°	6	6	5	4	4	4	4	3	3	3	3
2.5°	6	6	5	5	4	4	4	3	3	3	3
1.25°	6	6	5	5	4	4	4	3	3	3	3
0°	6	6	5	5	4	4	4	3	3	3	3
-1.25°	6	6	5	5	4	4	4	3	3	3	3
-2.5°	6	6	5	5	4	4	4	3	3	3	3
-3.75°	6	6	5	4	4	4	4	3	3	3	3
-5°	6	6	5	4	4	4	4	3	3	3	3
-6.25°	6	6	5	4	4	4	4	3	3	3	3
-7.5°	6	6	5	4	4	4	4	3	3	3	3
-8.75°	6	5	5	4	4	4	4	3	3	3	3
-10°	6	5	5	4	4	4	3	3	3	3	3
-11.25°	6	5	5	4	4	4	3	3	3	3	2
-12.5°	6	5	4	4	4	4	3	3	3	3	2
-13.75°	5	5	4	4	4	4	3	3	3	3	2
-15°	5	5	4	4	4	4	3	3	3	3	2
-16.25°	5	5	4	4	4	4	3	3	3	3	2
-17.5°	5	4	4	4	4	3	3	3	3	3	2
-18.75°	5	4	4	4	4	3	3	3	3	2	2
-20°	5	4	4	4	4	3	3	3	3	2	2
-21.25°	4	4	4	4	4	3	3	3	3	2	2



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	4	4	4	3	3	3	3	3	2	2
-23.75°	4	4	4	4	3	3	3	3	3	2	2
-25°	4	4	4	4	3	3	3	3	2	2	2
-26.25°	4	4	4	3	3	3	3	3	2	2	2
-27.5°	4	4	4	3	3	3	3	3	2	2	2
-28.75°	4	4	3	3	3	3	3	2	2	2	2
-30°	4	4	3	3	3	3	3	2	2	2	2
-31.25°	4	3	3	3	3	3	2	2	2	2	2
-32.5°	3	3	3	3	3	3	2	2	2	2	2
-33.75°	3	3	3	3	3	3	2	2	2	2	2
-35°	3	3	3	3	3	2	2	2	2	2	2
-36.25°	3	3	3	3	2	2	2	2	2	2	1
-37.5°	3	3	3	2	2	2	2	2	2	2	1
-38.75°	3	3	2	2	2	2	2	2	2	1	1
-40°	3	2	2	2	2	2	2	2	2	1	1
-41.25°	2	2	2	2	2	2	2	2	1	1	1
-42.5°	2	2	2	2	2	2	2	2	1	1	1
-43.75°	2	2	2	2	2	2	2	1	1	1	1
-45°	2	2	2	2	2	2	1	1	1	1	1
-46.25°	2	2	2	2	2	1	1	1	1	1	1
-47.5°	2	2	2	2	2	1	1	1	1	1	1
-48.75°	2	2	2	2	1	1	1	1	1	1	1
-50°	2	2	2	1	1	1	1	1	1	1	1
-51.25°	2	2	1	1	1	1	1	1	1	1	1
-52.5°	2	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	0
-72.5°	1	1	1	1	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	1	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	0	0	0	0	0	0	0	0
67.5°	1	1	1	1	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	0	0	0	0	0	0
65°	1	1	1	1	1	1	0	0	0	0	0
63.75°	1	1	1	1	1	1	1	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	0	0	0
61.25°	1	1	1	1	1	1	1	1	1	0	0
60°	1	1	1	1	1	1	1	1	1	0	0
58.75°	1	1	1	1	1	1	1	1	1	1	0
57.5°	1	1	1	1	1	1	1	1	1	1	0
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	2	1	1	1	1	1	1	1	1	1	1
31.25°	2	1	1	1	1	1	1	1	1	1	1
30°	2	1	1	1	1	1	1	1	1	1	1
28.75°	2	2	1	1	1	1	1	1	1	1	1
27.5°	2	2	1	1	1	1	1	1	1	1	1
26.25°	2	2	1	1	1	1	1	1	1	1	1
25°	2	2	2	1	1	1	1	1	1	1	1
23.75°	2	2	2	1	1	1	1	1	1	1	1
22.5°	2	2	2	1	1	1	1	1	1	1	1
21.25°	2	2	2	2	1	1	1	1	1	1	1
20°	2	2	2	2	1	1	1	1	1	1	1
18.75°	2	2	2	2	1	1	1	1	1	1	1
17.5°	2	2	2	2	2	1	1	1	1	1	1
16.25°	2	2	2	2	2	1	1	1	1	1	1
15°	2	2	2	2	2	1	1	1	1	1	1
13.75°	2	2	2	2	2	1	1	1	1	1	1
12.5°	2	2	2	2	2	1	1	1	1	1	1
11.25°	2	2	2	2	2	1	1	1	1	1	1
10°	2	2	2	2	2	2	1	1	1	1	1
8.75°	2	2	2	2	2	2	1	1	1	1	1
7.5°	2	2	2	2	2	2	1	1	1	1	1
6.25°	2	2	2	2	2	2	1	1	1	1	1
5°	2	2	2	2	2	2	1	1	1	1	1
3.75°	2	2	2	2	2	2	1	1	1	1	1
2.5°	2	2	2	2	2	2	1	1	1	1	1
1.25°	2	2	2	2	2	2	1	1	1	1	1
0°	2	2	2	2	2	2	1	1	1	1	1
-1.25°	2	2	2	2	2	2	1	1	1	1	1
-2.5°	2	2	2	2	2	2	1	1	1	1	1
-3.75°	2	2	2	2	2	2	1	1	1	1	1
-5°	2	2	2	2	2	2	1	1	1	1	1
-6.25°	2	2	2	2	2	2	1	1	1	1	1
-7.5°	2	2	2	2	2	2	1	1	1	1	1
-8.75°	2	2	2	2	2	2	1	1	1	1	1
-10°	2	2	2	2	2	2	1	1	1	1	1
-11.25°	2	2	2	2	2	1	1	1	1	1	1
-12.5°	2	2	2	2	2	1	1	1	1	1	1
-13.75°	2	2	2	2	2	1	1	1	1	1	1
-15°	2	2	2	2	2	1	1	1	1	1	1
-16.25°	2	2	2	2	2	1	1	1	1	1	1
-17.5°	2	2	2	2	2	1	1	1	1	1	1
-18.75°	2	2	2	2	1	1	1	1	1	1	1
-20°	2	2	2	2	1	1	1	1	1	1	1
-21.25°	2	2	2	2	1	1	1	1	1	1	1



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	1	1	1	1	1	1	1	1
-23.75°	2	2	2	1	1	1	1	1	1	1	1
-25°	2	2	2	1	1	1	1	1	1	1	1
-26.25°	2	2	1	1	1	1	1	1	1	1	1
-27.5°	2	2	1	1	1	1	1	1	1	1	1
-28.75°	2	2	1	1	1	1	1	1	1	1	1
-30°	2	1	1	1	1	1	1	1	1	1	1
-31.25°	2	1	1	1	1	1	1	1	1	1	1
-32.5°	2	1	1	1	1	1	1	1	1	1	1
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	0
-58.75°	1	1	1	1	1	1	1	1	1	1	0
-60°	1	1	1	1	1	1	1	1	1	0	0
-61.25°	1	1	1	1	1	1	1	1	1	0	0
-62.5°	1	1	1	1	1	1	1	1	0	0	0
-63.75°	1	1	1	1	1	1	1	0	0	0	0
-65°	1	1	1	1	1	1	0	0	0	0	0
-66.25°	1	1	1	1	1	0	0	0	0	0	0
-67.5°	1	1	1	1	0	0	0	0	0	0	0
-68.75°	1	1	1	0	0	0	0	0	0	0	0
-70°	1	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	1	0	0	0	0	0	0	0	0	0	0
51.25°	1	0	0	0	0	0	0	0	0	0	0
50°	1	0	0	0	0	0	0	0	0	0	0
48.75°	1	1	0	0	0	0	0	0	0	0	0
47.5°	1	1	0	0	0	0	0	0	0	0	0
46.25°	1	1	0	0	0	0	0	0	0	0	0
45°	1	1	0	0	0	0	0	0	0	0	0
43.75°	1	1	1	0	0	0	0	0	0	0	0
42.5°	1	1	1	0	0	0	0	0	0	0	0
41.25°	1	1	1	0	0	0	0	0	0	0	0
40°	1	1	1	0	0	0	0	0	0	0	0
38.75°	1	1	1	0	0	0	0	0	0	0	0
37.5°	1	1	1	1	0	0	0	0	0	0	0
36.25°	1	1	1	1	0	0	0	0	0	0	0
35°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	0	0	0	0	0	0	0
27.5°	1	1	1	1	0	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	0	0	0	0	0	0
21.25°	1	1	1	1	1	0	0	0	0	0	0
20°	1	1	1	1	1	0	0	0	0	0	0
18.75°	1	1	1	1	1	0	0	0	0	0	0
17.5°	1	1	1	1	1	0	0	0	0	0	0
16.25°	1	1	1	1	1	0	0	0	0	0	0
15°	1	1	1	1	1	0	0	0	0	0	0
13.75°	1	1	1	1	1	0	0	0	0	0	0
12.5°	1	1	1	1	1	0	0	0	0	0	0
11.25°	1	1	1	1	1	0	0	0	0	0	0
10°	1	1	1	1	1	0	0	0	0	0	0
8.75°	1	1	1	1	1	0	0	0	0	0	0
7.5°	1	1	1	1	1	0	0	0	0	0	0
6.25°	1	1	1	1	1	0	0	0	0	0	0
5°	1	1	1	1	1	0	0	0	0	0	0
3.75°	1	1	1	1	1	0	0	0	0	0	0
2.5°	1	1	1	1	1	0	0	0	0	0	0
1.25°	1	1	1	1	1	0	0	0	0	0	0
0°	1	1	1	1	1	0	0	0	0	0	0
-1.25°	1	1	1	1	1	0	0	0	0	0	0
-2.5°	1	1	1	1	1	0	0	0	0	0	0
-3.75°	1	1	1	1	1	0	0	0	0	0	0
-5°	1	1	1	1	1	0	0	0	0	0	0
-6.25°	1	1	1	1	1	0	0	0	0	0	0
-7.5°	1	1	1	1	1	0	0	0	0	0	0
-8.75°	1	1	1	1	1	0	0	0	0	0	0
-10°	1	1	1	1	1	0	0	0	0	0	0
-11.25°	1	1	1	1	1	0	0	0	0	0	0
-12.5°	1	1	1	1	1	0	0	0	0	0	0
-13.75°	1	1	1	1	1	0	0	0	0	0	0
-15°	1	1	1	1	1	0	0	0	0	0	0
-16.25°	1	1	1	1	1	0	0	0	0	0	0
-17.5°	1	1	1	1	1	0	0	0	0	0	0
-18.75°	1	1	1	1	1	0	0	0	0	0	0
-20°	1	1	1	1	1	0	0	0	0	0	0
-21.25°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	0	0	0	0	0	0
-23.75°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	0	0	0	0	0	0	0
-28.75°	1	1	1	1	0	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	1	0	0	0	0	0	0	0
-36.25°	1	1	1	1	0	0	0	0	0	0	0
-37.5°	1	1	1	1	0	0	0	0	0	0	0
-38.75°	1	1	1	0	0	0	0	0	0	0	0
-40°	1	1	1	0	0	0	0	0	0	0	0
-41.25°	1	1	1	0	0	0	0	0	0	0	0
-42.5°	1	1	1	0	0	0	0	0	0	0	0
-43.75°	1	1	1	0	0	0	0	0	0	0	0
-45°	1	1	0	0	0	0	0	0	0	0	0
-46.25°	1	1	0	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	1	0	0	0	0	0	0	0	0	0
-50°	1	0	0	0	0	0	0	0	0	0	0
-51.25°	1	0	0	0	0	0	0	0	0	0	0
-52.5°	1	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P247023 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2725-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)