

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED2736-12-CS-DIFF**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-44)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED2736-12-CS-DIFF  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD SILVER, DIFFUSED LENS  
Light Source: (1) SORAA 2700K 90 CRI LED  
SM16-07-36D-927-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	245.1 lumens	Max Intensity:	458.3 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	31.8 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	40.7°H x 40.7°V	Field Angle (10%):	69.7°H x 69.7°V
Beam Lumens:	131.7 lumens	Field Lumens:	216.6 lumens
Beam Efficiency:	53.7%	Field Efficiency:	88.4%
Input Watts (W):	7.7		
Input Voltage (V):	NR		
Input Current (A <sub>in</sub> ):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

### Iso-Candela Plot






REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)


CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

### Lumen Table




REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

### Luminous Intensity Polar Plot



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

### Luminous Intensity Plot



**Beam:**  
 H Angle: 40.7°  
 V Angle: 40.7°  
 Lumens: 131.7  
 Efficiency: 53.7%

**Field:**  
 H Angle: 69.7°  
 V Angle: 69.7°  
 Lumens: 216.6  
 Efficiency: 88.4%

**Spill:**  
 Lumens: 28.4  
 Efficiency: 11.6%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	1
42.5°	0	0	0	0	0	0	0	0	0	0	1
41.25°	0	0	0	0	0	0	0	0	0	0	1
40°	0	0	0	0	0	0	0	0	0	0	1
38.75°	0	0	0	0	0	0	0	0	0	0	1
37.5°	0	0	0	0	0	0	0	0	0	1	1
36.25°	0	0	0	0	0	0	0	0	0	1	1
35°	0	0	0	0	0	0	0	0	0	1	1



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	0	1	1
27.5°	0	0	0	0	0	0	0	0	0	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	0	1	1	1
22.5°	0	0	0	0	0	0	0	0	1	1	1
21.25°	0	0	0	0	0	0	0	0	1	1	1
20°	0	0	0	0	0	0	0	0	1	1	1
18.75°	0	0	0	0	0	0	0	0	1	1	1
17.5°	0	0	0	0	0	0	0	0	1	1	1
16.25°	0	0	0	0	0	0	0	0	1	1	1
15°	0	0	0	0	0	0	0	0	1	1	1
13.75°	0	0	0	0	0	0	0	0	1	1	1
12.5°	0	0	0	0	0	0	0	0	1	1	1
11.25°	0	0	0	0	0	0	0	0	1	1	1
10°	0	0	0	0	0	0	0	0	1	1	1
8.75°	0	0	0	0	0	0	0	0	1	1	1
7.5°	0	0	0	0	0	0	0	0	1	1	1
6.25°	0	0	0	0	0	0	0	0	1	1	1
5°	0	0	0	0	0	0	0	0	1	1	1
3.75°	0	0	0	0	0	0	0	0	1	1	1
2.5°	0	0	0	0	0	0	0	0	1	1	1
1.25°	0	0	0	0	0	0	0	0	1	1	1
0°	0	0	0	0	0	0	0	0	1	1	1
-1.25°	0	0	0	0	0	0	0	0	1	1	1
-2.5°	0	0	0	0	0	0	0	0	1	1	1
-3.75°	0	0	0	0	0	0	0	0	1	1	1
-5°	0	0	0	0	0	0	0	0	1	1	1
-6.25°	0	0	0	0	0	0	0	0	1	1	1
-7.5°	0	0	0	0	0	0	0	0	1	1	1
-8.75°	0	0	0	0	0	0	0	0	1	1	1
-10°	0	0	0	0	0	0	0	0	1	1	1
-11.25°	0	0	0	0	0	0	0	0	1	1	1
-12.5°	0	0	0	0	0	0	0	0	1	1	1
-13.75°	0	0	0	0	0	0	0	0	1	1	1
-15°	0	0	0	0	0	0	0	0	1	1	1
-16.25°	0	0	0	0	0	0	0	0	1	1	1
-17.5°	0	0	0	0	0	0	0	0	1	1	1
-18.75°	0	0	0	0	0	0	0	0	1	1	1
-20°	0	0	0	0	0	0	0	0	1	1	1
-21.25°	0	0	0	0	0	0	0	0	1	1	1





REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	1	1	1
-23.75°	0	0	0	0	0	0	0	0	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	0	1	1
-28.75°	0	0	0	0	0	0	0	0	0	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	1	1
-36.25°	0	0	0	0	0	0	0	0	0	1	1
-37.5°	0	0	0	0	0	0	0	0	0	1	1
-38.75°	0	0	0	0	0	0	0	0	0	0	1
-40°	0	0	0	0	0	0	0	0	0	0	1
-41.25°	0	0	0	0	0	0	0	0	0	0	1
-42.5°	0	0	0	0	0	0	0	0	0	0	1
-43.75°	0	0	0	0	0	0	0	0	0	0	1
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	1
67.5°	0	0	0	0	0	0	0	0	0	1	1
66.25°	0	0	0	0	0	0	0	0	1	1	1
65°	0	0	0	0	0	0	0	1	1	1	1
63.75°	0	0	0	0	0	0	1	1	1	1	1
62.5°	0	0	0	0	0	1	1	1	1	1	1
61.25°	0	0	0	0	1	1	1	1	1	1	1
60°	0	0	0	0	1	1	1	1	1	1	1
58.75°	0	0	0	1	1	1	1	1	1	1	1
57.5°	0	0	0	1	1	1	1	1	1	1	1
56.25°	0	0	1	1	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	1	1
53.75°	0	0	1	1	1	1	1	1	1	1	1
52.5°	0	1	1	1	1	1	1	1	1	1	1
51.25°	0	1	1	1	1	1	1	1	1	1	1
50°	0	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	2
40°	1	1	1	1	1	1	1	1	1	1	2
38.75°	1	1	1	1	1	1	1	1	1	2	2
37.5°	1	1	1	1	1	1	1	1	1	2	2
36.25°	1	1	1	1	1	1	1	1	1	2	2
35°	1	1	1	1	1	1	1	1	2	2	2



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	2	2	2
32.5°	1	1	1	1	1	1	1	1	2	2	2
31.25°	1	1	1	1	1	1	1	1	2	2	2
30°	1	1	1	1	1	1	1	2	2	2	2
28.75°	1	1	1	1	1	1	1	2	2	2	2
27.5°	1	1	1	1	1	1	1	2	2	2	2
26.25°	1	1	1	1	1	1	1	2	2	2	2
25°	1	1	1	1	1	1	2	2	2	2	2
23.75°	1	1	1	1	1	1	2	2	2	2	2
22.5°	1	1	1	1	1	1	2	2	2	2	2
21.25°	1	1	1	1	1	1	2	2	2	2	2
20°	1	1	1	1	1	1	2	2	2	2	2
18.75°	1	1	1	1	1	1	2	2	2	2	2
17.5°	1	1	1	1	1	1	2	2	2	2	2
16.25°	1	1	1	1	1	2	2	2	2	2	2
15°	1	1	1	1	1	2	2	2	2	2	2
13.75°	1	1	1	1	1	2	2	2	2	2	2
12.5°	1	1	1	1	1	2	2	2	2	2	2
11.25°	1	1	1	1	1	2	2	2	2	2	2
10°	1	1	1	1	1	2	2	2	2	2	2
8.75°	1	1	1	1	1	2	2	2	2	2	2
7.5°	1	1	1	1	1	2	2	2	2	2	2
6.25°	1	1	1	1	1	2	2	2	2	2	2
5°	1	1	1	1	1	2	2	2	2	2	2
3.75°	1	1	1	1	1	2	2	2	2	2	2
2.5°	1	1	1	1	1	2	2	2	2	2	2
1.25°	1	1	1	1	1	2	2	2	2	2	2
0°	1	1	1	1	1	2	2	2	2	2	2
-1.25°	1	1	1	1	1	2	2	2	2	2	2
-2.5°	1	1	1	1	1	2	2	2	2	2	2
-3.75°	1	1	1	1	1	2	2	2	2	2	2
-5°	1	1	1	1	1	2	2	2	2	2	2
-6.25°	1	1	1	1	1	2	2	2	2	2	2
-7.5°	1	1	1	1	1	2	2	2	2	2	2
-8.75°	1	1	1	1	1	2	2	2	2	2	2
-10°	1	1	1	1	1	2	2	2	2	2	2
-11.25°	1	1	1	1	1	2	2	2	2	2	2
-12.5°	1	1	1	1	1	2	2	2	2	2	2
-13.75°	1	1	1	1	1	2	2	2	2	2	2
-15°	1	1	1	1	1	2	2	2	2	2	2
-16.25°	1	1	1	1	1	2	2	2	2	2	2
-17.5°	1	1	1	1	1	1	2	2	2	2	2
-18.75°	1	1	1	1	1	1	2	2	2	2	2
-20°	1	1	1	1	1	1	2	2	2	2	2
-21.25°	1	1	1	1	1	1	2	2	2	2	2



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	2	2	2	2	2
-23.75°	1	1	1	1	1	1	2	2	2	2	2
-25°	1	1	1	1	1	1	2	2	2	2	2
-26.25°	1	1	1	1	1	1	1	2	2	2	2
-27.5°	1	1	1	1	1	1	1	2	2	2	2
-28.75°	1	1	1	1	1	1	1	2	2	2	2
-30°	1	1	1	1	1	1	1	2	2	2	2
-31.25°	1	1	1	1	1	1	1	1	2	2	2
-32.5°	1	1	1	1	1	1	1	1	2	2	2
-33.75°	1	1	1	1	1	1	1	1	2	2	2
-35°	1	1	1	1	1	1	1	1	2	2	2
-36.25°	1	1	1	1	1	1	1	1	1	2	2
-37.5°	1	1	1	1	1	1	1	1	1	2	2
-38.75°	1	1	1	1	1	1	1	1	1	2	2
-40°	1	1	1	1	1	1	1	1	1	1	2
-41.25°	1	1	1	1	1	1	1	1	1	1	2
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	0	1	1	1	1	1	1	1	1	1	1
-51.25°	0	1	1	1	1	1	1	1	1	1	1
-52.5°	0	1	1	1	1	1	1	1	1	1	1
-53.75°	0	0	1	1	1	1	1	1	1	1	1
-55°	0	0	1	1	1	1	1	1	1	1	1
-56.25°	0	0	1	1	1	1	1	1	1	1	1
-57.5°	0	0	0	1	1	1	1	1	1	1	1
-58.75°	0	0	0	1	1	1	1	1	1	1	1
-60°	0	0	0	0	1	1	1	1	1	1	1
-61.25°	0	0	0	0	1	1	1	1	1	1	1
-62.5°	0	0	0	0	0	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	1	1	1	1	1
-65°	0	0	0	0	0	0	0	1	1	1	1
-66.25°	0	0	0	0	0	0	0	0	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	1	1
-68.75°	0	0	0	0	0	0	0	0	0	0	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	1	1	1
73.75°	0	0	0	0	0	1	1	1	1	1	1
72.5°	0	0	0	1	1	1	1	1	1	1	1
71.25°	0	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	2
57.5°	1	1	1	1	1	1	1	1	1	2	2
56.25°	1	1	1	1	1	1	1	2	2	2	2
55°	1	1	1	1	1	1	2	2	2	2	2
53.75°	1	1	1	1	1	2	2	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	1	2	2	2	2	2	2	2
50°	1	1	1	2	2	2	2	2	2	2	2
48.75°	1	1	2	2	2	2	2	2	2	2	2
47.5°	1	1	2	2	2	2	2	2	2	2	2
46.25°	1	2	2	2	2	2	2	2	2	2	2
45°	1	2	2	2	2	2	2	2	2	2	3
43.75°	2	2	2	2	2	2	2	2	2	2	3
42.5°	2	2	2	2	2	2	2	2	2	3	3
41.25°	2	2	2	2	2	2	2	2	3	3	3
40°	2	2	2	2	2	2	2	2	3	3	3
38.75°	2	2	2	2	2	2	2	3	3	3	3
37.5°	2	2	2	2	2	2	3	3	3	3	3
36.25°	2	2	2	2	2	2	3	3	3	3	3
35°	2	2	2	2	2	3	3	3	3	3	3



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	2	3	3	3	3	3	4
32.5°	2	2	2	2	3	3	3	3	3	3	4
31.25°	2	2	2	2	3	3	3	3	3	4	4
30°	2	2	2	2	3	3	3	3	3	4	4
28.75°	2	2	2	3	3	3	3	3	4	4	4
27.5°	2	2	2	3	3	3	3	3	4	4	5
26.25°	2	2	2	3	3	3	3	4	4	4	5
25°	2	2	3	3	3	3	3	4	4	4	5
23.75°	2	2	3	3	3	3	3	4	4	5	5
22.5°	2	2	3	3	3	3	3	4	4	5	5
21.25°	2	2	3	3	3	3	4	4	4	5	5
20°	2	2	3	3	3	3	4	4	5	5	5
18.75°	2	3	3	3	3	3	4	4	5	5	5
17.5°	2	3	3	3	3	3	4	4	5	5	6
16.25°	2	3	3	3	3	4	4	4	5	5	6
15°	2	3	3	3	3	4	4	5	5	5	6
13.75°	2	3	3	3	3	4	4	5	5	5	6
12.5°	2	3	3	3	3	4	4	5	5	6	6
11.25°	2	3	3	3	3	4	4	5	5	6	7
10°	3	3	3	3	3	4	4	5	5	6	7
8.75°	3	3	3	3	4	4	4	5	5	6	7
7.5°	3	3	3	3	4	4	4	5	5	6	7
6.25°	3	3	3	3	4	4	5	5	5	6	7
5°	3	3	3	3	4	4	5	5	5	6	7
3.75°	3	3	3	3	4	4	5	5	5	6	7
2.5°	3	3	3	3	4	4	5	5	5	6	7
1.25°	3	3	3	3	4	4	5	5	5	6	7
0°	3	3	3	3	4	4	5	5	6	6	7
-1.25°	3	3	3	3	4	4	5	5	5	6	7
-2.5°	3	3	3	3	4	4	5	5	5	6	7
-3.75°	3	3	3	3	4	4	5	5	5	6	7
-5°	3	3	3	3	4	4	5	5	5	6	7
-6.25°	3	3	3	3	4	4	5	5	5	6	7
-7.5°	3	3	3	3	4	4	4	5	5	6	7
-8.75°	3	3	3	3	4	4	4	5	5	6	7
-10°	3	3	3	3	3	4	4	5	5	6	7
-11.25°	2	3	3	3	3	4	4	5	5	6	7
-12.5°	2	3	3	3	3	4	4	5	5	6	6
-13.75°	2	3	3	3	3	4	4	5	5	5	6
-15°	2	3	3	3	3	4	4	5	5	5	6
-16.25°	2	3	3	3	3	4	4	4	5	5	6
-17.5°	2	3	3	3	3	3	4	4	5	5	6
-18.75°	2	3	3	3	3	3	4	4	5	5	5
-20°	2	2	3	3	3	3	4	4	5	5	5
-21.25°	2	2	3	3	3	3	4	4	4	5	5





REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	3	3	3	3	3	4	4	5	5
-23.75°	2	2	3	3	3	3	3	4	4	5	5
-25°	2	2	3	3	3	3	3	4	4	4	5
-26.25°	2	2	2	3	3	3	3	4	4	4	5
-27.5°	2	2	2	3	3	3	3	3	4	4	5
-28.75°	2	2	2	3	3	3	3	3	4	4	4
-30°	2	2	2	2	3	3	3	3	3	4	4
-31.25°	2	2	2	2	3	3	3	3	3	4	4
-32.5°	2	2	2	2	3	3	3	3	3	3	4
-33.75°	2	2	2	2	2	3	3	3	3	3	4
-35°	2	2	2	2	2	3	3	3	3	3	3
-36.25°	2	2	2	2	2	2	3	3	3	3	3
-37.5°	2	2	2	2	2	2	3	3	3	3	3
-38.75°	2	2	2	2	2	2	2	3	3	3	3
-40°	2	2	2	2	2	2	2	2	3	3	3
-41.25°	2	2	2	2	2	2	2	2	3	3	3
-42.5°	2	2	2	2	2	2	2	2	2	3	3
-43.75°	2	2	2	2	2	2	2	2	2	2	3
-45°	1	2	2	2	2	2	2	2	2	2	3
-46.25°	1	2	2	2	2	2	2	2	2	2	2
-47.5°	1	1	2	2	2	2	2	2	2	2	2
-48.75°	1	1	2	2	2	2	2	2	2	2	2
-50°	1	1	1	2	2	2	2	2	2	2	2
-51.25°	1	1	1	1	2	2	2	2	2	2	2
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	2	2	2	2	2	2
-55°	1	1	1	1	1	1	2	2	2	2	2
-56.25°	1	1	1	1	1	1	1	2	2	2	2
-57.5°	1	1	1	1	1	1	1	1	1	2	2
-58.75°	1	1	1	1	1	1	1	1	1	1	2
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	0	1	1	1	1	1	1	1	1	1	1
-72.5°	0	0	0	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	0	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	1	1
77.5°	0	0	0	0	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	2	2	2
63.75°	1	1	1	1	1	1	2	2	2	2	2
62.5°	1	1	1	1	2	2	2	2	2	2	2
61.25°	1	1	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	3	3
53.75°	2	2	2	2	2	2	2	2	3	3	3
52.5°	2	2	2	2	2	2	3	3	3	3	3
51.25°	2	2	2	2	2	3	3	3	3	3	3
50°	2	2	2	3	3	3	3	3	3	3	3
48.75°	2	2	3	3	3	3	3	3	3	3	4
47.5°	2	3	3	3	3	3	3	3	3	4	4
46.25°	3	3	3	3	3	3	3	3	4	4	4
45°	3	3	3	3	3	3	4	4	4	4	5
43.75°	3	3	3	3	3	4	4	4	4	5	5
42.5°	3	3	3	3	4	4	4	4	5	5	5
41.25°	3	3	3	4	4	4	4	5	5	5	5
40°	3	3	3	4	4	4	5	5	5	5	6
38.75°	3	3	4	4	4	5	5	5	5	6	7
37.5°	3	4	4	4	5	5	5	5	6	7	7
36.25°	4	4	4	5	5	5	5	6	7	7	8
35°	4	4	4	5	5	5	6	6	7	8	8



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	4	4	5	5	5	6	6	7	8	8	9
32.5°	4	5	5	5	6	6	7	7	8	9	9
31.25°	4	5	5	5	6	7	7	8	9	9	10
30°	5	5	5	6	6	7	8	8	9	10	11
28.75°	5	5	5	6	7	7	8	9	10	11	12
27.5°	5	5	6	6	7	8	9	9	11	12	13
26.25°	5	5	6	7	8	8	9	10	11	12	14
25°	5	6	6	7	8	9	10	11	12	13	15
23.75°	5	6	7	8	8	9	10	11	13	14	16
22.5°	6	6	7	8	9	10	11	12	13	15	17
21.25°	6	7	7	8	9	10	11	13	14	16	19
20°	6	7	8	8	9	11	12	13	15	17	20
18.75°	6	7	8	9	10	11	12	14	16	19	21
17.5°	7	7	8	9	10	12	13	15	17	20	23
16.25°	7	8	8	9	11	12	14	15	18	21	25
15°	7	8	9	10	11	12	14	16	19	22	27
13.75°	7	8	9	10	11	13	15	17	20	24	28
12.5°	7	8	9	10	12	13	15	18	21	25	30
11.25°	8	8	9	11	12	14	16	19	22	26	31
10°	8	9	10	11	12	14	16	19	23	27	32
8.75°	8	9	10	11	13	14	17	20	24	29	34
7.5°	8	9	10	11	13	15	17	20	24	29	35
6.25°	8	9	10	12	13	15	18	21	25	30	36
5°	8	9	10	12	13	15	18	21	26	31	37
3.75°	8	9	10	12	14	15	18	22	26	31	38
2.5°	8	9	10	12	14	15	19	22	27	32	38
1.25°	8	9	10	12	14	15	19	22	27	32	38
0°	8	9	11	12	14	16	19	22	27	32	38
-1.25°	8	9	10	12	14	15	19	22	27	32	38
-2.5°	8	9	10	12	14	15	19	22	27	32	38
-3.75°	8	9	10	12	14	15	18	22	26	31	38
-5°	8	9	10	12	13	15	18	21	26	31	37
-6.25°	8	9	10	12	13	15	18	21	25	30	36
-7.5°	8	9	10	11	13	15	17	20	24	29	35
-8.75°	8	9	10	11	13	14	17	20	24	29	34
-10°	8	9	10	11	12	14	16	19	23	27	32
-11.25°	8	8	9	11	12	14	16	19	22	26	31
-12.5°	7	8	9	10	12	13	15	18	21	25	30
-13.75°	7	8	9	10	11	13	15	17	20	24	28
-15°	7	8	9	10	11	12	14	16	19	22	27
-16.25°	7	8	8	9	11	12	14	15	18	21	25
-17.5°	7	7	8	9	10	12	13	15	17	20	23
-18.75°	6	7	8	9	10	11	12	14	16	19	21
-20°	6	7	8	8	9	11	12	13	15	17	20
-21.25°	6	7	7	8	9	10	11	13	14	16	19



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	6	6	7	8	9	10	11	12	13	15	17
-23.75°	5	6	7	8	8	9	10	11	13	14	16
-25°	5	6	6	7	8	9	10	11	12	13	15
-26.25°	5	5	6	7	8	8	9	10	11	12	14
-27.5°	5	5	6	6	7	8	9	9	11	12	13
-28.75°	5	5	5	6	7	7	8	9	10	11	12
-30°	5	5	5	6	6	7	8	8	9	10	11
-31.25°	4	5	5	5	6	7	7	8	9	9	10
-32.5°	4	5	5	5	6	6	7	7	8	9	9
-33.75°	4	4	5	5	5	6	6	7	8	8	9
-35°	4	4	4	5	5	5	6	6	7	8	8
-36.25°	4	4	4	5	5	5	5	6	7	7	8
-37.5°	3	4	4	4	5	5	5	5	6	7	7
-38.75°	3	3	4	4	4	5	5	5	5	6	7
-40°	3	3	3	4	4	4	5	5	5	5	6
-41.25°	3	3	3	4	4	4	4	5	5	5	5
-42.5°	3	3	3	3	4	4	4	4	5	5	5
-43.75°	3	3	3	3	3	4	4	4	4	5	5
-45°	3	3	3	3	3	3	4	4	4	4	5
-46.25°	3	3	3	3	3	3	3	3	4	4	4
-47.5°	2	3	3	3	3	3	3	3	3	4	4
-48.75°	2	2	3	3	3	3	3	3	3	3	4
-50°	2	2	2	3	3	3	3	3	3	3	3
-51.25°	2	2	2	2	2	3	3	3	3	3	3
-52.5°	2	2	2	2	2	2	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	2	3	3	3
-55°	2	2	2	2	2	2	2	2	2	3	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	2	2	2	2	2
-65°	1	1	1	1	1	1	1	1	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	1	1	1	1	1	1	1



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	1	1
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	2	2	2
67.5°	1	1	1	1	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	3	3	3
58.75°	2	2	2	2	2	3	3	3	3	3	3
57.5°	2	2	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	4	4	4	4
52.5°	3	3	3	3	3	4	4	4	4	4	4
51.25°	3	3	3	4	4	4	4	4	4	5	5
50°	3	4	4	4	4	4	5	5	5	5	5
48.75°	4	4	4	4	5	5	5	5	5	5	6
47.5°	4	4	5	5	5	5	5	5	6	6	6
46.25°	4	5	5	5	5	5	6	6	6	7	7
45°	5	5	5	5	6	6	6	7	7	8	8
43.75°	5	5	6	6	6	7	7	8	8	8	9
42.5°	5	6	6	7	7	7	8	8	9	9	10
41.25°	6	6	7	7	8	8	9	9	10	10	11
40°	6	7	7	8	8	9	9	10	11	11	12
38.75°	7	8	8	9	9	10	11	11	12	13	13
37.5°	8	8	9	9	10	11	12	12	13	14	15
36.25°	8	9	9	10	11	12	13	14	15	16	17
35°	9	10	10	11	12	13	14	15	17	18	20



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	10	10	11	12	13	14	16	17	19	21	23
32.5°	10	11	12	14	15	16	18	20	22	24	27
31.25°	11	12	14	15	16	18	20	22	25	28	31
30°	12	13	15	16	18	20	23	26	29	32	35
28.75°	13	14	16	18	20	23	26	29	33	36	40
27.5°	14	16	18	20	23	26	30	33	37	41	45
26.25°	15	17	20	22	26	29	33	37	42	46	51
25°	17	19	22	25	29	33	37	42	46	52	58
23.75°	18	21	24	28	32	36	41	46	52	58	64
22.5°	20	23	27	31	35	40	45	51	58	64	73
21.25°	21	25	29	34	39	44	50	57	63	72	81
20°	23	27	32	37	42	48	55	62	71	80	89
18.75°	25	30	35	40	45	52	60	68	78	88	98
17.5°	27	32	37	43	49	57	65	75	85	96	107
16.25°	29	34	40	46	53	61	71	81	92	103	116
15°	31	37	42	49	57	66	76	87	99	111	125
13.75°	33	39	45	53	60	71	82	93	106	119	134
12.5°	35	41	48	56	64	76	87	99	112	127	142
11.25°	37	43	50	58	68	80	92	105	119	134	150
10°	38	45	53	61	72	84	96	110	125	141	158
8.75°	40	47	55	64	76	87	101	115	131	147	164
7.5°	41	48	57	67	78	91	104	119	136	153	171
6.25°	42	50	58	69	81	94	108	123	140	158	177
5°	43	51	60	71	83	96	111	127	144	162	181
3.75°	44	52	61	72	85	98	113	129	147	165	185
2.5°	44	53	62	74	86	99	115	131	149	167	188
1.25°	45	53	62	74	86	100	116	132	150	169	189
0°	45	53	62	74	87	101	116	133	151	169	190
-1.25°	45	53	62	74	86	100	116	132	150	169	189
-2.5°	44	53	62	74	86	99	115	131	149	167	188
-3.75°	44	52	61	72	85	98	113	129	147	165	185
-5°	43	51	60	71	83	96	111	127	144	162	181
-6.25°	42	50	58	69	81	94	108	123	140	158	177
-7.5°	41	48	57	67	78	91	104	119	136	153	171
-8.75°	40	47	55	64	76	87	101	115	131	147	164
-10°	38	45	53	61	72	84	96	110	125	141	158
-11.25°	37	43	50	58	68	80	92	105	119	134	150
-12.5°	35	41	48	56	64	76	87	99	112	127	142
-13.75°	33	39	45	53	60	71	82	93	106	119	134
-15°	31	37	42	49	57	66	76	87	99	111	125
-16.25°	29	34	40	46	53	61	71	81	92	103	116
-17.5°	27	32	37	43	49	57	65	75	85	96	107
-18.75°	25	30	35	40	45	52	60	68	78	88	98
-20°	23	27	32	37	42	48	55	62	71	80	89
-21.25°	21	25	29	34	39	44	50	57	63	72	81





REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	20	23	27	31	35	40	45	51	58	64	73
-23.75°	18	21	24	28	32	36	41	46	52	58	64
-25°	17	19	22	25	29	33	37	42	46	52	58
-26.25°	15	17	20	22	26	29	33	37	42	46	51
-27.5°	14	16	18	20	23	26	30	33	37	41	45
-28.75°	13	14	16	18	20	23	26	29	33	36	40
-30°	12	13	15	16	18	20	23	26	29	32	35
-31.25°	11	12	14	15	16	18	20	22	25	28	31
-32.5°	10	11	12	14	15	16	18	20	22	24	27
-33.75°	10	10	11	12	13	14	16	17	19	21	23
-35°	9	10	10	11	12	13	14	15	17	18	20
-36.25°	8	9	9	10	11	12	13	14	15	16	17
-37.5°	8	8	9	9	10	11	12	12	13	14	15
-38.75°	7	8	8	9	9	10	11	11	12	13	13
-40°	6	7	7	8	8	9	9	10	11	11	12
-41.25°	6	6	7	7	8	8	9	9	10	10	11
-42.5°	5	6	6	7	7	7	8	8	9	9	10
-43.75°	5	5	6	6	6	7	7	8	8	8	9
-45°	5	5	5	5	6	6	6	7	7	8	8
-46.25°	4	5	5	5	5	5	6	6	6	7	7
-47.5°	4	4	5	5	5	5	5	5	6	6	6
-48.75°	4	4	4	4	5	5	5	5	5	5	6
-50°	3	4	4	4	4	4	5	5	5	5	5
-51.25°	3	3	3	4	4	4	4	4	4	5	5
-52.5°	3	3	3	3	3	4	4	4	4	4	4
-53.75°	3	3	3	3	3	3	3	4	4	4	4
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	2	2	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	3	3	3	3	3	3
-60°	2	2	2	2	2	2	2	2	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	1	1	1	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	2	2	2
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	0	0	0	0	0	0	0	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	3	3
61.25°	2	2	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	3	3	3	3	3	4
56.25°	3	3	3	3	4	4	4	4	4	4	4
55°	4	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	5	5	5	5	5	5
52.5°	4	5	5	5	5	5	5	5	5	5	5
51.25°	5	5	5	5	5	5	5	6	6	6	6
50°	5	5	5	6	6	6	6	6	7	7	7
48.75°	6	6	6	7	7	7	7	7	8	8	8
47.5°	7	7	7	7	8	8	8	8	8	9	9
46.25°	7	8	8	8	8	9	9	9	9	10	10
45°	8	8	9	9	9	10	10	10	11	11	11
43.75°	9	9	10	10	11	11	11	12	12	12	13
42.5°	10	11	11	12	12	12	13	13	14	14	14
41.25°	11	12	12	13	14	14	15	15	16	16	17
40°	13	13	14	15	15	16	17	18	19	19	20
38.75°	14	15	16	17	18	19	20	21	22	23	24
37.5°	16	17	19	20	21	22	24	25	26	27	29
36.25°	19	20	21	23	25	27	28	30	31	32	34
35°	21	23	25	27	29	31	33	35	37	38	40



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	25	27	30	32	34	37	39	41	43	45	47
32.5°	29	32	35	37	40	42	45	48	50	53	55
31.25°	34	37	40	43	46	49	53	56	58	61	64
30°	39	42	45	49	53	57	60	64	68	72	76
28.75°	44	48	52	57	61	66	71	76	80	84	87
27.5°	50	55	60	65	71	76	82	87	92	96	101
26.25°	57	62	68	75	81	87	93	99	105	110	115
25°	63	71	78	85	92	99	106	112	119	125	131
23.75°	72	80	88	96	103	111	119	127	134	141	147
22.5°	81	89	98	107	116	125	134	142	150	158	164
21.25°	90	99	109	119	129	139	149	158	166	175	183
20°	99	110	120	131	142	153	164	174	184	194	203
18.75°	109	120	132	144	156	168	180	191	202	213	224
17.5°	119	131	144	157	170	183	196	209	222	234	245
16.25°	129	142	156	170	185	199	213	228	242	255	265
15°	139	153	168	183	199	215	231	246	260	273	285
13.75°	149	164	180	196	213	231	248	263	278	291	303
12.5°	158	174	191	209	228	246	263	279	295	308	321
11.25°	166	184	202	222	242	260	278	295	310	324	336
10°	175	194	213	234	255	273	291	308	324	338	350
8.75°	183	203	224	245	265	285	303	321	336	350	364
7.5°	190	211	233	255	275	295	314	331	347	362	375
6.25°	196	218	241	262	283	304	323	340	356	372	385
5°	202	224	247	269	291	311	330	348	364	379	394
3.75°	206	229	253	274	296	317	336	354	371	386	402
2.5°	209	233	256	278	300	321	340	358	375	391	407
1.25°	211	235	258	280	302	323	342	361	378	394	410
0°	212	236	259	281	303	324	343	362	378	395	411
-1.25°	211	235	258	280	302	323	342	361	378	394	410
-2.5°	209	233	256	278	300	321	340	358	375	391	407
-3.75°	206	229	253	274	296	317	336	354	371	386	402
-5°	202	224	247	269	291	311	330	348	364	379	394
-6.25°	196	218	241	262	283	304	323	340	356	372	385
-7.5°	190	211	233	255	275	295	314	331	347	362	375
-8.75°	183	203	224	245	265	285	303	321	336	350	364
-10°	175	194	213	234	255	273	291	308	324	338	350
-11.25°	166	184	202	222	242	260	278	295	310	324	336
-12.5°	158	174	191	209	228	246	263	279	295	308	321
-13.75°	149	164	180	196	213	231	248	263	278	291	303
-15°	139	153	168	183	199	215	231	246	260	273	285
-16.25°	129	142	156	170	185	199	213	228	242	255	265
-17.5°	119	131	144	157	170	183	196	209	222	234	245
-18.75°	109	120	132	144	156	168	180	191	202	213	224
-20°	99	110	120	131	142	153	164	174	184	194	203
-21.25°	90	99	109	119	129	139	149	158	166	175	183



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	81	89	98	107	116	125	134	142	150	158	164
-23.75°	72	80	88	96	103	111	119	127	134	141	147
-25°	63	71	78	85	92	99	106	112	119	125	131
-26.25°	57	62	68	75	81	87	93	99	105	110	115
-27.5°	50	55	60	65	71	76	82	87	92	96	101
-28.75°	44	48	52	57	61	66	71	76	80	84	87
-30°	39	42	45	49	53	57	60	64	68	72	76
-31.25°	34	37	40	43	46	49	53	56	58	61	64
-32.5°	29	32	35	37	40	42	45	48	50	53	55
-33.75°	25	27	30	32	34	37	39	41	43	45	47
-35°	21	23	25	27	29	31	33	35	37	38	40
-36.25°	19	20	21	23	25	27	28	30	31	32	34
-37.5°	16	17	19	20	21	22	24	25	26	27	29
-38.75°	14	15	16	17	18	19	20	21	22	23	24
-40°	13	13	14	15	15	16	17	18	19	19	20
-41.25°	11	12	12	13	14	14	15	15	16	16	17
-42.5°	10	11	11	12	12	12	13	13	14	14	14
-43.75°	9	9	10	10	11	11	11	12	12	12	13
-45°	8	8	9	9	9	10	10	10	11	11	11
-46.25°	7	8	8	8	8	9	9	9	9	10	10
-47.5°	7	7	7	7	8	8	8	8	8	9	9
-48.75°	6	6	6	7	7	7	7	7	8	8	8
-50°	5	5	5	6	6	6	6	6	7	7	7
-51.25°	5	5	5	5	5	5	5	6	6	6	6
-52.5°	4	5	5	5	5	5	5	5	5	5	5
-53.75°	4	4	4	4	4	5	5	5	5	5	5
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	3	3	3	3	4	4	4	4	4	4	4
-57.5°	3	3	3	3	3	3	3	3	3	3	4
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	3	3	3	3	3	3	3	3	3
-62.5°	2	2	2	2	2	2	2	2	2	3	3
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	1	1	1	1	2	2	2	2	2	2	2
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	3	3	3	3	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	4	4	4	4	4	4	4	4	4	4	4
55°	4	5	5	5	5	5	5	5	5	5	5
53.75°	5	5	5	5	5	5	5	5	5	5	5
52.5°	5	5	5	5	5	5	6	5	5	5	5
51.25°	6	6	6	6	6	6	6	6	6	6	6
50°	7	7	7	7	7	7	7	7	7	7	7
48.75°	8	8	8	8	8	8	8	8	8	8	8
47.5°	9	9	9	9	9	9	9	9	9	9	9
46.25°	10	10	10	10	10	10	11	10	10	10	10
45°	11	12	12	12	12	12	12	12	12	12	12
43.75°	13	13	13	14	14	14	14	14	14	14	13
42.5°	15	15	15	15	15	15	16	15	15	15	15
41.25°	17	18	18	18	19	19	19	19	19	18	18
40°	20	21	21	22	22	22	22	22	22	22	21
38.75°	24	25	26	26	27	27	27	27	27	26	26
37.5°	29	30	31	31	32	32	32	32	32	31	31
36.25°	35	36	37	38	38	38	38	38	38	38	37
35°	41	42	43	44	44	45	45	45	44	44	43



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	48	50	51	52	53	53	53	53	53	52	51
32.5°	57	58	60	61	62	62	62	62	62	61	60
31.25°	67	69	71	72	74	74	74	74	74	72	71
30°	78	81	83	85	86	86	87	86	86	85	83
28.75°	91	94	96	98	99	100	101	100	99	98	96
27.5°	104	108	111	113	115	116	116	116	115	113	111
26.25°	119	123	127	129	131	132	133	132	131	129	127
25°	136	140	144	147	149	150	151	150	149	147	144
23.75°	153	158	162	165	167	169	169	169	167	165	162
22.5°	171	177	181	185	188	189	190	189	188	185	181
21.25°	190	196	202	206	209	211	212	211	209	206	202
20°	211	218	224	229	233	235	236	235	233	229	224
18.75°	233	241	247	253	256	258	259	258	256	253	247
17.5°	255	262	269	274	278	280	281	280	278	274	269
16.25°	275	283	291	296	300	302	303	302	300	296	291
15°	295	304	311	317	321	323	324	323	321	317	311
13.75°	314	323	330	336	340	342	343	342	340	336	330
12.5°	331	340	348	354	358	361	362	361	358	354	348
11.25°	347	356	364	371	375	378	378	378	375	371	364
10°	362	372	379	386	391	394	395	394	391	386	379
8.75°	375	385	394	402	407	410	411	410	407	402	394
7.5°	387	398	408	415	421	424	425	424	421	415	408
6.25°	398	410	420	426	431	434	435	434	431	426	420
5°	408	420	428	435	440	443	444	443	440	435	428
3.75°	415	426	435	442	446	448	449	448	446	442	435
2.5°	421	431	440	446	450	452	452	452	450	446	440
1.25°	424	434	443	448	452	454	455	454	452	448	443
0°	425	435	444	449	452	455	458	455	452	449	444
-1.25°	424	434	443	448	452	454	455	454	452	448	443
-2.5°	421	431	440	446	450	452	452	452	450	446	440
-3.75°	415	426	435	442	446	448	449	448	446	442	435
-5°	408	420	428	435	440	443	444	443	440	435	428
-6.25°	398	410	420	426	431	434	435	434	431	426	420
-7.5°	387	398	408	415	421	424	425	424	421	415	408
-8.75°	375	385	394	402	407	410	411	410	407	402	394
-10°	362	372	379	386	391	394	395	394	391	386	379
-11.25°	347	356	364	371	375	378	378	378	375	371	364
-12.5°	331	340	348	354	358	361	362	361	358	354	348
-13.75°	314	323	330	336	340	342	343	342	340	336	330
-15°	295	304	311	317	321	323	324	323	321	317	311
-16.25°	275	283	291	296	300	302	303	302	300	296	291
-17.5°	255	262	269	274	278	280	281	280	278	274	269
-18.75°	233	241	247	253	256	258	259	258	256	253	247
-20°	211	218	224	229	233	235	236	235	233	229	224
-21.25°	190	196	202	206	209	211	212	211	209	206	202





REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	171	177	181	185	188	189	190	189	188	185	181
-23.75°	153	158	162	165	167	169	169	169	167	165	162
-25°	136	140	144	147	149	150	151	150	149	147	144
-26.25°	119	123	127	129	131	132	133	132	131	129	127
-27.5°	104	108	111	113	115	116	116	116	115	113	111
-28.75°	91	94	96	98	99	100	101	100	99	98	96
-30°	78	81	83	85	86	86	87	86	86	85	83
-31.25°	67	69	71	72	74	74	74	74	74	72	71
-32.5°	57	58	60	61	62	62	62	62	62	61	60
-33.75°	48	50	51	52	53	53	53	53	53	52	51
-35°	41	42	43	44	44	45	45	45	44	44	43
-36.25°	35	36	37	38	38	38	38	38	38	38	37
-37.5°	29	30	31	31	32	32	32	32	32	31	31
-38.75°	24	25	26	26	27	27	27	27	27	26	26
-40°	20	21	21	22	22	22	22	22	22	22	21
-41.25°	17	18	18	18	19	19	19	19	19	18	18
-42.5°	15	15	15	15	15	15	16	15	15	15	15
-43.75°	13	13	13	14	14	14	14	14	14	14	13
-45°	11	12	12	12	12	12	12	12	12	12	12
-46.25°	10	10	10	10	10	10	11	10	10	10	10
-47.5°	9	9	9	9	9	9	9	9	9	9	9
-48.75°	8	8	8	8	8	8	8	8	8	8	8
-50°	7	7	7	7	7	7	7	7	7	7	7
-51.25°	6	6	6	6	6	6	6	6	6	6	6
-52.5°	5	5	5	5	5	5	6	5	5	5	5
-53.75°	5	5	5	5	5	5	5	5	5	5	5
-55°	4	5	5	5	5	5	5	5	5	5	5
-56.25°	4	4	4	4	4	4	4	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	4	4	4
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	3	3
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	2	2	2	2	2	2	2	2	2	1	1
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	3	3	3	3	2	2	2	2	2	2	2
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	4	4	4	3	3	3	3	3	3	3	3
56.25°	4	4	4	4	4	4	4	4	4	3	3
55°	5	4	4	4	4	4	4	4	4	4	4
53.75°	5	5	5	5	5	5	5	5	4	4	4
52.5°	5	5	5	5	5	5	5	5	5	5	5
51.25°	6	6	6	6	6	6	5	5	5	5	5
50°	7	7	7	7	7	6	6	6	6	6	5
48.75°	8	8	8	8	8	7	7	7	7	7	6
47.5°	9	9	9	9	8	8	8	8	8	7	7
46.25°	10	10	10	10	9	9	9	9	8	8	8
45°	12	11	11	11	11	10	10	10	9	9	9
43.75°	13	13	13	12	12	12	11	11	11	10	10
42.5°	15	15	14	14	14	13	13	12	12	12	11
41.25°	18	17	17	16	16	15	15	14	14	13	12
40°	21	20	20	19	19	18	17	16	15	15	14
38.75°	25	24	24	23	22	21	20	19	18	17	16
37.5°	30	29	29	27	26	25	24	22	21	20	19
36.25°	36	35	34	32	31	30	28	27	25	23	21
35°	42	41	40	38	37	35	33	31	29	27	25



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	50	48	47	45	43	41	39	37	34	32	30
32.5°	58	57	55	53	50	48	45	42	40	37	35
31.25°	69	67	64	61	58	56	53	49	46	43	40
30°	81	78	76	72	68	64	60	57	53	49	45
28.75°	94	91	87	84	80	76	71	66	61	57	52
27.5°	108	104	101	96	92	87	82	76	71	65	60
26.25°	123	119	115	110	105	99	93	87	81	75	68
25°	140	136	131	125	119	112	106	99	92	85	78
23.75°	158	153	147	141	134	127	119	111	103	96	88
22.5°	177	171	164	158	150	142	134	125	116	107	98
21.25°	196	190	183	175	166	158	149	139	129	119	109
20°	218	211	203	194	184	174	164	153	142	131	120
18.75°	241	233	224	213	202	191	180	168	156	144	132
17.5°	262	255	245	234	222	209	196	183	170	157	144
16.25°	283	275	265	255	242	228	213	199	185	170	156
15°	304	295	285	273	260	246	231	215	199	183	168
13.75°	323	314	303	291	278	263	248	231	213	196	180
12.5°	340	331	321	308	295	279	263	246	228	209	191
11.25°	356	347	336	324	310	295	278	260	242	222	202
10°	372	362	350	338	324	308	291	273	255	234	213
8.75°	385	375	364	350	336	321	303	285	265	245	224
7.5°	398	387	375	362	347	331	314	295	275	255	233
6.25°	410	398	385	372	356	340	323	304	283	262	241
5°	420	408	394	379	364	348	330	311	291	269	247
3.75°	426	415	402	386	371	354	336	317	296	274	253
2.5°	431	421	407	391	375	358	340	321	300	278	256
1.25°	434	424	410	394	378	361	342	323	302	280	258
0°	435	425	411	395	378	362	343	324	303	281	259
-1.25°	434	424	410	394	378	361	342	323	302	280	258
-2.5°	431	421	407	391	375	358	340	321	300	278	256
-3.75°	426	415	402	386	371	354	336	317	296	274	253
-5°	420	408	394	379	364	348	330	311	291	269	247
-6.25°	410	398	385	372	356	340	323	304	283	262	241
-7.5°	398	387	375	362	347	331	314	295	275	255	233
-8.75°	385	375	364	350	336	321	303	285	265	245	224
-10°	372	362	350	338	324	308	291	273	255	234	213
-11.25°	356	347	336	324	310	295	278	260	242	222	202
-12.5°	340	331	321	308	295	279	263	246	228	209	191
-13.75°	323	314	303	291	278	263	248	231	213	196	180
-15°	304	295	285	273	260	246	231	215	199	183	168
-16.25°	283	275	265	255	242	228	213	199	185	170	156
-17.5°	262	255	245	234	222	209	196	183	170	157	144
-18.75°	241	233	224	213	202	191	180	168	156	144	132
-20°	218	211	203	194	184	174	164	153	142	131	120
-21.25°	196	190	183	175	166	158	149	139	129	119	109



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	177	171	164	158	150	142	134	125	116	107	98
-23.75°	158	153	147	141	134	127	119	111	103	96	88
-25°	140	136	131	125	119	112	106	99	92	85	78
-26.25°	123	119	115	110	105	99	93	87	81	75	68
-27.5°	108	104	101	96	92	87	82	76	71	65	60
-28.75°	94	91	87	84	80	76	71	66	61	57	52
-30°	81	78	76	72	68	64	60	57	53	49	45
-31.25°	69	67	64	61	58	56	53	49	46	43	40
-32.5°	58	57	55	53	50	48	45	42	40	37	35
-33.75°	50	48	47	45	43	41	39	37	34	32	30
-35°	42	41	40	38	37	35	33	31	29	27	25
-36.25°	36	35	34	32	31	30	28	27	25	23	21
-37.5°	30	29	29	27	26	25	24	22	21	20	19
-38.75°	25	24	24	23	22	21	20	19	18	17	16
-40°	21	20	20	19	19	18	17	16	15	15	14
-41.25°	18	17	17	16	16	15	15	14	14	13	12
-42.5°	15	15	14	14	14	13	13	12	12	12	11
-43.75°	13	13	13	12	12	12	11	11	11	10	10
-45°	12	11	11	11	11	10	10	10	9	9	9
-46.25°	10	10	10	10	9	9	9	9	8	8	8
-47.5°	9	9	9	9	8	8	8	8	8	7	7
-48.75°	8	8	8	8	8	7	7	7	7	7	6
-50°	7	7	7	7	7	6	6	6	6	6	5
-51.25°	6	6	6	6	6	6	5	5	5	5	5
-52.5°	5	5	5	5	5	5	5	5	5	5	5
-53.75°	5	5	5	5	5	5	5	5	4	4	4
-55°	5	4	4	4	4	4	4	4	4	4	4
-56.25°	4	4	4	4	4	4	4	4	4	3	3
-57.5°	4	4	4	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	0	0	0	0	0
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	2	2	2	2	2	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	1	1
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	2	2	2	2	2	2
58.75°	3	3	3	3	3	3	3	3	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	4	4	3	3	3	3	3	3	3	3	3
53.75°	4	4	4	4	4	4	3	3	3	3	3
52.5°	5	4	4	4	4	4	4	4	3	3	3
51.25°	5	5	5	5	4	4	4	4	4	4	3
50°	5	5	5	5	5	5	5	4	4	4	4
48.75°	6	6	6	5	5	5	5	5	5	4	4
47.5°	7	7	6	6	6	5	5	5	5	5	5
46.25°	8	7	7	7	6	6	6	5	5	5	5
45°	8	8	8	8	7	7	6	6	6	5	5
43.75°	9	9	9	8	8	8	7	7	6	6	6
42.5°	11	10	10	9	9	8	8	7	7	7	6
41.25°	12	11	11	10	10	9	9	8	8	7	7
40°	13	13	12	11	11	10	9	9	8	8	7
38.75°	15	14	13	13	12	11	11	10	9	9	8
37.5°	17	16	15	14	13	12	12	11	10	9	9
36.25°	20	19	17	16	15	14	13	12	11	10	9
35°	23	21	20	18	17	15	14	13	12	11	10



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	27	25	23	21	19	17	16	14	13	12	11
32.5°	32	29	27	24	22	20	18	16	15	14	12
31.25°	37	34	31	28	25	22	20	18	16	15	14
30°	42	39	35	32	29	26	23	20	18	16	15
28.75°	48	44	40	36	33	29	26	23	20	18	16
27.5°	55	50	45	41	37	33	30	26	23	20	18
26.25°	62	57	51	46	42	37	33	29	26	22	20
25°	71	63	58	52	46	42	37	33	29	25	22
23.75°	80	72	64	58	52	46	41	36	32	28	24
22.5°	89	81	73	64	58	51	45	40	35	31	27
21.25°	99	90	81	72	63	57	50	44	39	34	29
20°	110	99	89	80	71	62	55	48	42	37	32
18.75°	120	109	98	88	78	68	60	52	45	40	35
17.5°	131	119	107	96	85	75	65	57	49	43	37
16.25°	142	129	116	103	92	81	71	61	53	46	40
15°	153	139	125	111	99	87	76	66	57	49	42
13.75°	164	149	134	119	106	93	82	71	60	53	45
12.5°	174	158	142	127	112	99	87	76	64	56	48
11.25°	184	166	150	134	119	105	92	80	68	58	50
10°	194	175	158	141	125	110	96	84	72	61	53
8.75°	203	183	164	147	131	115	101	87	76	64	55
7.5°	211	190	171	153	136	119	104	91	78	67	57
6.25°	218	196	177	158	140	123	108	94	81	69	58
5°	224	202	181	162	144	127	111	96	83	71	60
3.75°	229	206	185	165	147	129	113	98	85	72	61
2.5°	233	209	188	167	149	131	115	99	86	74	62
1.25°	235	211	189	169	150	132	116	100	86	74	62
0°	236	212	190	169	151	133	116	101	87	74	62
-1.25°	235	211	189	169	150	132	116	100	86	74	62
-2.5°	233	209	188	167	149	131	115	99	86	74	62
-3.75°	229	206	185	165	147	129	113	98	85	72	61
-5°	224	202	181	162	144	127	111	96	83	71	60
-6.25°	218	196	177	158	140	123	108	94	81	69	58
-7.5°	211	190	171	153	136	119	104	91	78	67	57
-8.75°	203	183	164	147	131	115	101	87	76	64	55
-10°	194	175	158	141	125	110	96	84	72	61	53
-11.25°	184	166	150	134	119	105	92	80	68	58	50
-12.5°	174	158	142	127	112	99	87	76	64	56	48
-13.75°	164	149	134	119	106	93	82	71	60	53	45
-15°	153	139	125	111	99	87	76	66	57	49	42
-16.25°	142	129	116	103	92	81	71	61	53	46	40
-17.5°	131	119	107	96	85	75	65	57	49	43	37
-18.75°	120	109	98	88	78	68	60	52	45	40	35
-20°	110	99	89	80	71	62	55	48	42	37	32
-21.25°	99	90	81	72	63	57	50	44	39	34	29





REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	89	81	73	64	58	51	45	40	35	31	27
-23.75°	80	72	64	58	52	46	41	36	32	28	24
-25°	71	63	58	52	46	42	37	33	29	25	22
-26.25°	62	57	51	46	42	37	33	29	26	22	20
-27.5°	55	50	45	41	37	33	30	26	23	20	18
-28.75°	48	44	40	36	33	29	26	23	20	18	16
-30°	42	39	35	32	29	26	23	20	18	16	15
-31.25°	37	34	31	28	25	22	20	18	16	15	14
-32.5°	32	29	27	24	22	20	18	16	15	14	12
-33.75°	27	25	23	21	19	17	16	14	13	12	11
-35°	23	21	20	18	17	15	14	13	12	11	10
-36.25°	20	19	17	16	15	14	13	12	11	10	9
-37.5°	17	16	15	14	13	12	12	11	10	9	9
-38.75°	15	14	13	13	12	11	11	10	9	9	8
-40°	13	13	12	11	11	10	9	9	8	8	7
-41.25°	12	11	11	10	10	9	9	8	8	7	7
-42.5°	11	10	10	9	9	8	8	7	7	7	6
-43.75°	9	9	9	8	8	8	7	7	6	6	6
-45°	8	8	8	8	7	7	6	6	6	5	5
-46.25°	8	7	7	7	6	6	6	5	5	5	5
-47.5°	7	7	6	6	6	5	5	5	5	5	5
-48.75°	6	6	6	5	5	5	5	5	5	4	4
-50°	5	5	5	5	5	5	5	4	4	4	4
-51.25°	5	5	5	5	4	4	4	4	4	4	3
-52.5°	5	4	4	4	4	4	4	4	3	3	3
-53.75°	4	4	4	4	4	4	3	3	3	3	3
-55°	4	4	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	2	2	2
-60°	3	3	3	3	3	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	1	1
-68.75°	2	2	2	2	2	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	1	1	1	1	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	1	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	1	1	1	1	1	1
63.75°	2	2	2	2	2	2	2	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	3	3	2	2	2	2	2	2	2	2	2
55°	3	3	3	3	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	2	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	2	2	2	2
51.25°	3	3	3	3	3	3	3	3	2	2	2
50°	4	3	3	3	3	3	3	3	3	3	2
48.75°	4	4	4	3	3	3	3	3	3	3	3
47.5°	4	4	4	4	3	3	3	3	3	3	3
46.25°	5	4	4	4	4	3	3	3	3	3	3
45°	5	5	5	4	4	4	4	3	3	3	3
43.75°	5	5	5	5	4	4	4	4	3	3	3
42.5°	6	5	5	5	5	4	4	4	4	3	3
41.25°	6	6	5	5	5	5	4	4	4	4	3
40°	7	6	6	5	5	5	5	4	4	4	3
38.75°	8	7	7	6	5	5	5	5	4	4	4
37.5°	8	8	7	7	6	5	5	5	5	4	4
36.25°	9	8	8	7	7	6	5	5	5	5	4
35°	10	9	8	8	7	6	6	5	5	5	4



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	10	10	9	8	8	7	6	6	5	5	5
32.5°	11	10	9	9	8	7	7	6	6	5	5
31.25°	12	11	10	9	9	8	7	7	6	5	5
30°	13	12	11	10	9	8	8	7	6	6	5
28.75°	14	13	12	11	10	9	8	7	7	6	5
27.5°	16	14	13	12	11	9	9	8	7	6	6
26.25°	17	15	14	12	11	10	9	8	8	7	6
25°	19	17	15	13	12	11	10	9	8	7	6
23.75°	21	18	16	14	13	11	10	9	8	8	7
22.5°	23	20	17	15	13	12	11	10	9	8	7
21.25°	25	21	19	16	14	13	11	10	9	8	7
20°	27	23	20	17	15	13	12	11	9	8	8
18.75°	30	25	21	19	16	14	12	11	10	9	8
17.5°	32	27	23	20	17	15	13	12	10	9	8
16.25°	34	29	25	21	18	15	14	12	11	9	8
15°	37	31	27	22	19	16	14	12	11	10	9
13.75°	39	33	28	24	20	17	15	13	11	10	9
12.5°	41	35	30	25	21	18	15	13	12	10	9
11.25°	43	37	31	26	22	19	16	14	12	11	9
10°	45	38	32	27	23	19	16	14	12	11	10
8.75°	47	40	34	29	24	20	17	14	13	11	10
7.5°	48	41	35	29	24	20	17	15	13	11	10
6.25°	50	42	36	30	25	21	18	15	13	12	10
5°	51	43	37	31	26	21	18	15	13	12	10
3.75°	52	44	38	31	26	22	18	15	14	12	10
2.5°	53	44	38	32	27	22	19	15	14	12	10
1.25°	53	45	38	32	27	22	19	15	14	12	10
0°	53	45	38	32	27	22	19	16	14	12	11
-1.25°	53	45	38	32	27	22	19	15	14	12	10
-2.5°	53	44	38	32	27	22	19	15	14	12	10
-3.75°	52	44	38	31	26	22	18	15	14	12	10
-5°	51	43	37	31	26	21	18	15	13	12	10
-6.25°	50	42	36	30	25	21	18	15	13	12	10
-7.5°	48	41	35	29	24	20	17	15	13	11	10
-8.75°	47	40	34	29	24	20	17	14	13	11	10
-10°	45	38	32	27	23	19	16	14	12	11	10
-11.25°	43	37	31	26	22	19	16	14	12	11	9
-12.5°	41	35	30	25	21	18	15	13	12	10	9
-13.75°	39	33	28	24	20	17	15	13	11	10	9
-15°	37	31	27	22	19	16	14	12	11	10	9
-16.25°	34	29	25	21	18	15	14	12	11	9	8
-17.5°	32	27	23	20	17	15	13	12	10	9	8
-18.75°	30	25	21	19	16	14	12	11	10	9	8
-20°	27	23	20	17	15	13	12	11	9	8	8
-21.25°	25	21	19	16	14	13	11	10	9	8	7



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	23	20	17	15	13	12	11	10	9	8	7
-23.75°	21	18	16	14	13	11	10	9	8	8	7
-25°	19	17	15	13	12	11	10	9	8	7	6
-26.25°	17	15	14	12	11	10	9	8	8	7	6
-27.5°	16	14	13	12	11	9	9	8	7	6	6
-28.75°	14	13	12	11	10	9	8	7	7	6	5
-30°	13	12	11	10	9	8	8	7	6	6	5
-31.25°	12	11	10	9	9	8	7	7	6	5	5
-32.5°	11	10	9	9	8	7	7	6	6	5	5
-33.75°	10	10	9	8	8	7	6	6	5	5	5
-35°	10	9	8	8	7	6	6	5	5	5	4
-36.25°	9	8	8	7	7	6	5	5	5	5	4
-37.5°	8	8	7	7	6	5	5	5	5	4	4
-38.75°	8	7	7	6	5	5	5	5	4	4	4
-40°	7	6	6	5	5	5	5	4	4	4	3
-41.25°	6	6	5	5	5	5	4	4	4	4	3
-42.5°	6	5	5	5	5	4	4	4	4	3	3
-43.75°	5	5	5	5	4	4	4	4	3	3	3
-45°	5	5	5	4	4	4	4	3	3	3	3
-46.25°	5	4	4	4	4	3	3	3	3	3	3
-47.5°	4	4	4	4	3	3	3	3	3	3	3
-48.75°	4	4	4	3	3	3	3	3	3	3	3
-50°	4	3	3	3	3	3	3	3	3	3	2
-51.25°	3	3	3	3	3	3	3	3	2	2	2
-52.5°	3	3	3	3	3	3	3	2	2	2	2
-53.75°	3	3	3	3	3	2	2	2	2	2	2
-55°	3	3	3	3	2	2	2	2	2	2	2
-56.25°	3	3	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	1	1
-63.75°	2	2	2	2	2	2	2	1	1	1	1
-65°	2	2	2	2	2	1	1	1	1	1	1
-66.25°	2	2	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	1	1	1	1	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	0	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	0
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	2	2	1	1	1	1	1	1	1	1	1
58.75°	2	2	2	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	1	1	1	1	1	1	1
56.25°	2	2	2	2	2	2	1	1	1	1	1
55°	2	2	2	2	2	2	2	1	1	1	1
53.75°	2	2	2	2	2	2	2	2	1	1	1
52.5°	2	2	2	2	2	2	2	2	1	1	1
51.25°	2	2	2	2	2	2	2	2	2	1	1
50°	2	2	2	2	2	2	2	2	2	2	1
48.75°	2	2	2	2	2	2	2	2	2	2	2
47.5°	3	2	2	2	2	2	2	2	2	2	2
46.25°	3	3	2	2	2	2	2	2	2	2	2
45°	3	3	3	2	2	2	2	2	2	2	2
43.75°	3	3	3	2	2	2	2	2	2	2	2
42.5°	3	3	3	3	2	2	2	2	2	2	2
41.25°	3	3	3	3	3	2	2	2	2	2	2
40°	3	3	3	3	3	2	2	2	2	2	2
38.75°	3	3	3	3	3	3	2	2	2	2	2
37.5°	4	3	3	3	3	3	3	2	2	2	2
36.25°	4	4	3	3	3	3	3	2	2	2	2
35°	4	4	3	3	3	3	3	3	2	2	2



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	4	4	4	3	3	3	3	3	2	2	2
32.5°	5	4	4	3	3	3	3	3	3	2	2
31.25°	5	4	4	4	3	3	3	3	3	2	2
30°	5	5	4	4	3	3	3	3	3	2	2
28.75°	5	5	4	4	4	3	3	3	3	3	2
27.5°	5	5	5	4	4	3	3	3	3	3	2
26.25°	5	5	5	4	4	4	3	3	3	3	2
25°	6	5	5	4	4	4	3	3	3	3	3
23.75°	6	5	5	5	4	4	3	3	3	3	3
22.5°	6	6	5	5	4	4	3	3	3	3	3
21.25°	7	6	5	5	4	4	4	3	3	3	3
20°	7	6	5	5	5	4	4	3	3	3	3
18.75°	7	6	5	5	5	4	4	3	3	3	3
17.5°	7	7	6	5	5	4	4	3	3	3	3
16.25°	8	7	6	5	5	4	4	4	3	3	3
15°	8	7	6	5	5	5	4	4	3	3	3
13.75°	8	7	6	5	5	5	4	4	3	3	3
12.5°	8	7	6	6	5	5	4	4	3	3	3
11.25°	8	8	7	6	5	5	4	4	3	3	3
10°	9	8	7	6	5	5	4	4	3	3	3
8.75°	9	8	7	6	5	5	4	4	4	3	3
7.5°	9	8	7	6	5	5	4	4	4	3	3
6.25°	9	8	7	6	5	5	5	4	4	3	3
5°	9	8	7	6	5	5	5	4	4	3	3
3.75°	9	8	7	6	5	5	5	4	4	3	3
2.5°	9	8	7	6	5	5	5	4	4	3	3
1.25°	9	8	7	6	5	5	5	4	4	3	3
0°	9	8	7	6	6	5	5	4	4	3	3
-1.25°	9	8	7	6	5	5	5	4	4	3	3
-2.5°	9	8	7	6	5	5	5	4	4	3	3
-3.75°	9	8	7	6	5	5	5	4	4	3	3
-5°	9	8	7	6	5	5	5	4	4	3	3
-6.25°	9	8	7	6	5	5	5	4	4	3	3
-7.5°	9	8	7	6	5	5	4	4	4	3	3
-8.75°	9	8	7	6	5	5	4	4	4	3	3
-10°	9	8	7	6	5	5	4	4	3	3	3
-11.25°	8	8	7	6	5	5	4	4	3	3	3
-12.5°	8	7	6	6	5	5	4	4	3	3	3
-13.75°	8	7	6	5	5	5	4	4	3	3	3
-15°	8	7	6	5	5	5	4	4	3	3	3
-16.25°	8	7	6	5	5	4	4	4	3	3	3
-17.5°	7	7	6	5	5	4	4	3	3	3	3
-18.75°	7	6	5	5	5	4	4	3	3	3	3
-20°	7	6	5	5	5	4	4	3	3	3	3
-21.25°	7	6	5	5	4	4	4	3	3	3	3





REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	6	6	5	5	4	4	3	3	3	3	3
-23.75°	6	5	5	5	4	4	3	3	3	3	3
-25°	6	5	5	4	4	4	3	3	3	3	3
-26.25°	5	5	5	4	4	4	3	3	3	3	2
-27.5°	5	5	5	4	4	3	3	3	3	3	2
-28.75°	5	5	4	4	4	3	3	3	3	3	2
-30°	5	5	4	4	3	3	3	3	3	2	2
-31.25°	5	4	4	4	3	3	3	3	3	2	2
-32.5°	5	4	4	3	3	3	3	3	3	2	2
-33.75°	4	4	4	3	3	3	3	3	2	2	2
-35°	4	4	3	3	3	3	3	3	2	2	2
-36.25°	4	4	3	3	3	3	3	2	2	2	2
-37.5°	4	3	3	3	3	3	3	2	2	2	2
-38.75°	3	3	3	3	3	3	2	2	2	2	2
-40°	3	3	3	3	3	2	2	2	2	2	2
-41.25°	3	3	3	3	3	2	2	2	2	2	2
-42.5°	3	3	3	3	2	2	2	2	2	2	2
-43.75°	3	3	3	2	2	2	2	2	2	2	2
-45°	3	3	3	2	2	2	2	2	2	2	2
-46.25°	3	3	2	2	2	2	2	2	2	2	2
-47.5°	3	2	2	2	2	2	2	2	2	2	2
-48.75°	2	2	2	2	2	2	2	2	2	2	2
-50°	2	2	2	2	2	2	2	2	2	2	1
-51.25°	2	2	2	2	2	2	2	2	2	1	1
-52.5°	2	2	2	2	2	2	2	2	1	1	1
-53.75°	2	2	2	2	2	2	2	2	1	1	1
-55°	2	2	2	2	2	2	2	1	1	1	1
-56.25°	2	2	2	2	2	2	1	1	1	1	1
-57.5°	2	2	2	2	1	1	1	1	1	1	1
-58.75°	2	2	2	1	1	1	1	1	1	1	1
-60°	2	2	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	0
-73.75°	1	1	1	1	1	1	1	1	0	0	0
-75°	1	1	1	1	1	0	0	0	0	0	0
-76.25°	1	1	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	1	0	0	0	0	0	0	0	0	0	0
70°	1	1	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	0	0	0	0	0	0	0	0
67.5°	1	1	1	1	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	0	0	0	0	0	0
65°	1	1	1	1	1	1	0	0	0	0	0
63.75°	1	1	1	1	1	1	1	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	0	0	0
61.25°	1	1	1	1	1	1	1	1	1	0	0
60°	1	1	1	1	1	1	1	1	1	0	0
58.75°	1	1	1	1	1	1	1	1	1	1	0
57.5°	1	1	1	1	1	1	1	1	1	1	0
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	2	1	1	1	1	1	1	1	1	1	1
45°	2	1	1	1	1	1	1	1	1	1	1
43.75°	2	2	1	1	1	1	1	1	1	1	1
42.5°	2	2	1	1	1	1	1	1	1	1	1
41.25°	2	2	2	1	1	1	1	1	1	1	1
40°	2	2	2	1	1	1	1	1	1	1	1
38.75°	2	2	2	2	1	1	1	1	1	1	1
37.5°	2	2	2	2	1	1	1	1	1	1	1
36.25°	2	2	2	2	1	1	1	1	1	1	1
35°	2	2	2	2	2	1	1	1	1	1	1



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	2	2	2	1	1	1	1	1	1
32.5°	2	2	2	2	2	1	1	1	1	1	1
31.25°	2	2	2	2	2	1	1	1	1	1	1
30°	2	2	2	2	2	2	1	1	1	1	1
28.75°	2	2	2	2	2	2	1	1	1	1	1
27.5°	2	2	2	2	2	2	1	1	1	1	1
26.25°	2	2	2	2	2	2	1	1	1	1	1
25°	2	2	2	2	2	2	2	1	1	1	1
23.75°	2	2	2	2	2	2	2	1	1	1	1
22.5°	2	2	2	2	2	2	2	1	1	1	1
21.25°	2	2	2	2	2	2	2	1	1	1	1
20°	2	2	2	2	2	2	2	1	1	1	1
18.75°	3	2	2	2	2	2	2	1	1	1	1
17.5°	3	2	2	2	2	2	2	1	1	1	1
16.25°	3	2	2	2	2	2	2	2	1	1	1
15°	3	2	2	2	2	2	2	2	1	1	1
13.75°	3	2	2	2	2	2	2	2	1	1	1
12.5°	3	2	2	2	2	2	2	2	1	1	1
11.25°	3	2	2	2	2	2	2	2	1	1	1
10°	3	3	2	2	2	2	2	2	1	1	1
8.75°	3	3	2	2	2	2	2	2	1	1	1
7.5°	3	3	2	2	2	2	2	2	1	1	1
6.25°	3	3	2	2	2	2	2	2	1	1	1
5°	3	3	2	2	2	2	2	2	1	1	1
3.75°	3	3	2	2	2	2	2	2	1	1	1
2.5°	3	3	2	2	2	2	2	2	1	1	1
1.25°	3	3	2	2	2	2	2	2	1	1	1
0°	3	3	2	2	2	2	2	2	1	1	1
-1.25°	3	3	2	2	2	2	2	2	1	1	1
-2.5°	3	3	2	2	2	2	2	2	1	1	1
-3.75°	3	3	2	2	2	2	2	2	1	1	1
-5°	3	3	2	2	2	2	2	2	1	1	1
-6.25°	3	3	2	2	2	2	2	2	1	1	1
-7.5°	3	3	2	2	2	2	2	2	1	1	1
-8.75°	3	3	2	2	2	2	2	2	1	1	1
-10°	3	3	2	2	2	2	2	2	1	1	1
-11.25°	3	2	2	2	2	2	2	2	1	1	1
-12.5°	3	2	2	2	2	2	2	2	1	1	1
-13.75°	3	2	2	2	2	2	2	2	1	1	1
-15°	3	2	2	2	2	2	2	2	1	1	1
-16.25°	3	2	2	2	2	2	2	2	1	1	1
-17.5°	3	2	2	2	2	2	2	1	1	1	1
-18.75°	3	2	2	2	2	2	2	1	1	1	1
-20°	2	2	2	2	2	2	2	1	1	1	1
-21.25°	2	2	2	2	2	2	2	1	1	1	1



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	2	2	2	2	1	1	1	1
-23.75°	2	2	2	2	2	2	2	1	1	1	1
-25°	2	2	2	2	2	2	2	1	1	1	1
-26.25°	2	2	2	2	2	2	1	1	1	1	1
-27.5°	2	2	2	2	2	2	1	1	1	1	1
-28.75°	2	2	2	2	2	2	1	1	1	1	1
-30°	2	2	2	2	2	2	1	1	1	1	1
-31.25°	2	2	2	2	2	1	1	1	1	1	1
-32.5°	2	2	2	2	2	1	1	1	1	1	1
-33.75°	2	2	2	2	2	1	1	1	1	1	1
-35°	2	2	2	2	2	1	1	1	1	1	1
-36.25°	2	2	2	2	1	1	1	1	1	1	1
-37.5°	2	2	2	2	1	1	1	1	1	1	1
-38.75°	2	2	2	2	1	1	1	1	1	1	1
-40°	2	2	2	1	1	1	1	1	1	1	1
-41.25°	2	2	2	1	1	1	1	1	1	1	1
-42.5°	2	2	1	1	1	1	1	1	1	1	1
-43.75°	2	2	1	1	1	1	1	1	1	1	1
-45°	2	1	1	1	1	1	1	1	1	1	1
-46.25°	2	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	0
-58.75°	1	1	1	1	1	1	1	1	1	1	0
-60°	1	1	1	1	1	1	1	1	1	0	0
-61.25°	1	1	1	1	1	1	1	1	1	0	0
-62.5°	1	1	1	1	1	1	1	1	0	0	0
-63.75°	1	1	1	1	1	1	1	0	0	0	0
-65°	1	1	1	1	1	1	0	0	0	0	0
-66.25°	1	1	1	1	1	0	0	0	0	0	0
-67.5°	1	1	1	1	0	0	0	0	0	0	0
-68.75°	1	1	1	0	0	0	0	0	0	0	0
-70°	1	1	0	0	0	0	0	0	0	0	0
-71.25°	1	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	1	0	0	0	0	0	0	0	0	0	0
51.25°	1	0	0	0	0	0	0	0	0	0	0
50°	1	0	0	0	0	0	0	0	0	0	0
48.75°	1	1	0	0	0	0	0	0	0	0	0
47.5°	1	1	0	0	0	0	0	0	0	0	0
46.25°	1	1	0	0	0	0	0	0	0	0	0
45°	1	1	0	0	0	0	0	0	0	0	0
43.75°	1	1	1	0	0	0	0	0	0	0	0
42.5°	1	1	1	0	0	0	0	0	0	0	0
41.25°	1	1	1	0	0	0	0	0	0	0	0
40°	1	1	1	0	0	0	0	0	0	0	0
38.75°	1	1	1	0	0	0	0	0	0	0	0
37.5°	1	1	1	1	0	0	0	0	0	0	0
36.25°	1	1	1	1	0	0	0	0	0	0	0
35°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	0	0	0	0	0	0	0
27.5°	1	1	1	1	0	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	0	0	0	0	0	0
21.25°	1	1	1	1	1	0	0	0	0	0	0
20°	1	1	1	1	1	0	0	0	0	0	0
18.75°	1	1	1	1	1	0	0	0	0	0	0
17.5°	1	1	1	1	1	0	0	0	0	0	0
16.25°	1	1	1	1	1	0	0	0	0	0	0
15°	1	1	1	1	1	0	0	0	0	0	0
13.75°	1	1	1	1	1	0	0	0	0	0	0
12.5°	1	1	1	1	1	0	0	0	0	0	0
11.25°	1	1	1	1	1	0	0	0	0	0	0
10°	1	1	1	1	1	0	0	0	0	0	0
8.75°	1	1	1	1	1	0	0	0	0	0	0
7.5°	1	1	1	1	1	0	0	0	0	0	0
6.25°	1	1	1	1	1	0	0	0	0	0	0
5°	1	1	1	1	1	0	0	0	0	0	0
3.75°	1	1	1	1	1	0	0	0	0	0	0
2.5°	1	1	1	1	1	0	0	0	0	0	0
1.25°	1	1	1	1	1	0	0	0	0	0	0
0°	1	1	1	1	1	0	0	0	0	0	0
-1.25°	1	1	1	1	1	0	0	0	0	0	0
-2.5°	1	1	1	1	1	0	0	0	0	0	0
-3.75°	1	1	1	1	1	0	0	0	0	0	0
-5°	1	1	1	1	1	0	0	0	0	0	0
-6.25°	1	1	1	1	1	0	0	0	0	0	0
-7.5°	1	1	1	1	1	0	0	0	0	0	0
-8.75°	1	1	1	1	1	0	0	0	0	0	0
-10°	1	1	1	1	1	0	0	0	0	0	0
-11.25°	1	1	1	1	1	0	0	0	0	0	0
-12.5°	1	1	1	1	1	0	0	0	0	0	0
-13.75°	1	1	1	1	1	0	0	0	0	0	0
-15°	1	1	1	1	1	0	0	0	0	0	0
-16.25°	1	1	1	1	1	0	0	0	0	0	0
-17.5°	1	1	1	1	1	0	0	0	0	0	0
-18.75°	1	1	1	1	1	0	0	0	0	0	0
-20°	1	1	1	1	1	0	0	0	0	0	0
-21.25°	1	1	1	1	1	0	0	0	0	0	0





REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	0	0	0	0	0	0
-23.75°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	0	0	0	0	0	0	0
-28.75°	1	1	1	1	0	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	1	0	0	0	0	0	0	0
-36.25°	1	1	1	1	0	0	0	0	0	0	0
-37.5°	1	1	1	1	0	0	0	0	0	0	0
-38.75°	1	1	1	0	0	0	0	0	0	0	0
-40°	1	1	1	0	0	0	0	0	0	0	0
-41.25°	1	1	1	0	0	0	0	0	0	0	0
-42.5°	1	1	1	0	0	0	0	0	0	0	0
-43.75°	1	1	1	0	0	0	0	0	0	0	0
-45°	1	1	0	0	0	0	0	0	0	0	0
-46.25°	1	1	0	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	1	0	0	0	0	0	0	0	0	0
-50°	1	0	0	0	0	0	0	0	0	0	0
-51.25°	1	0	0	0	0	0	0	0	0	0	0
-52.5°	1	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P247032 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)