

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED2736-12-CS-LSL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-45)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED2736-12-CS-LSL  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD SILVER, LINEAR SPREAD LENS  
Light Source: (1) SORAA 2700K 90 CRI LED  
SM16-07-36D-927-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	5H x 4V
Luminaire Lumens:	289.6 lumens	Max Intensity:	510.3 candela
Efficiency:	N/A	Max Intensity Angle:	-11.25°H x 0°V
Efficacy:	38.1 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	59.6°H x 32.6°V	Field Angle (10%):	78.4°H x 52.6°V
Beam Lumens:	190.1 lumens	Field Lumens:	264.9 lumens
Beam Efficiency:	65.7%	Field Efficiency:	91.5%
Input Watts (W):	7.6		
Input Voltage (V):	NR		
Input Current (A <sub>in</sub> ):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)


CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

### Iso-Candela Plot




REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

### Lumen Table




REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

### Luminous Intensity Polar Plot



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

### Luminous Intensity Plot



**Beam:**  
 H Angle: 59.6°  
 V Angle: 32.6°  
 Lumens: 190.1  
 Efficiency: 65.7%

**Field:**  
 H Angle: 78.4°  
 V Angle: 52.6°  
 Lumens: 264.9  
 Efficiency: 91.5%

**Spill:**  
 Lumens: 24.6  
 Efficiency: 8.5%

— Vertical Distribution through -11.25-Deg  
 - - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	1
57.5°	0	0	0	0	0	0	0	0	0	0	1
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	0	0	0	1	1
52.5°	0	0	0	0	0	0	0	0	0	1	1
51.25°	0	0	0	0	0	0	0	0	0	1	1
50°	0	0	0	0	0	0	0	0	1	1	1
48.75°	0	0	0	0	0	0	0	0	1	1	1
47.5°	0	0	0	0	0	0	0	0	1	1	1
46.25°	0	0	0	0	0	0	0	0	1	1	1
45°	0	0	0	0	0	0	0	0	1	1	1
43.75°	0	0	0	0	0	0	0	0	1	1	1
42.5°	0	0	0	0	0	0	0	1	1	1	1
41.25°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
38.75°	0	0	0	0	0	0	0	1	1	1	1
37.5°	0	0	0	0	0	0	0	1	1	1	1
36.25°	0	0	0	0	0	0	0	1	1	1	1
35°	0	0	0	0	0	0	0	1	1	1	1



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	1	1	1	1
32.5°	0	0	0	0	0	0	0	1	1	1	1
31.25°	0	0	0	0	0	0	1	1	1	1	1
30°	0	0	0	0	0	0	1	1	1	1	1
28.75°	0	0	0	0	0	0	1	1	1	1	1
27.5°	0	0	0	0	0	0	1	1	1	1	1
26.25°	0	0	0	0	0	0	1	1	1	1	1
25°	0	0	0	0	0	0	1	1	1	1	1
23.75°	0	0	0	0	0	0	1	1	1	1	1
22.5°	0	0	0	0	0	0	1	1	1	1	1
21.25°	0	0	0	0	0	0	1	1	1	1	1
20°	0	0	0	0	0	0	1	1	1	1	1
18.75°	0	0	0	0	0	0	1	1	1	1	1
17.5°	0	0	0	0	0	0	1	1	1	1	1
16.25°	0	0	0	0	0	0	1	1	1	1	1
15°	0	0	0	0	0	0	1	1	1	1	1
13.75°	0	0	0	0	0	0	1	1	1	1	1
12.5°	0	0	0	0	0	0	1	1	1	1	1
11.25°	0	0	0	0	0	0	1	1	1	1	1
10°	0	0	0	0	0	0	1	1	1	1	1
8.75°	0	0	0	0	0	0	1	1	1	1	1
7.5°	0	0	0	0	0	0	1	1	1	1	1
6.25°	0	0	0	0	0	0	1	1	1	1	1
5°	0	0	0	0	0	0	1	1	1	1	1
3.75°	0	0	0	0	0	0	1	1	1	1	1
2.5°	0	0	0	0	0	0	1	1	1	1	1
1.25°	0	0	0	0	0	0	1	1	1	1	1
0°	0	0	0	0	0	0	1	1	1	1	1
-1.25°	0	0	0	0	0	0	1	1	1	1	1
-2.5°	0	0	0	0	0	0	1	1	1	1	1
-3.75°	0	0	0	0	0	0	1	1	1	1	1
-5°	0	0	0	0	0	0	1	1	1	1	1
-6.25°	0	0	0	0	0	0	1	1	1	1	1
-7.5°	0	0	0	0	0	0	1	1	1	1	1
-8.75°	0	0	0	0	0	0	1	1	1	1	1
-10°	0	0	0	0	0	0	1	1	1	1	1
-11.25°	0	0	0	0	0	0	1	1	1	1	1
-12.5°	0	0	0	0	0	0	1	1	1	1	1
-13.75°	0	0	0	0	0	0	1	1	1	1	1
-15°	0	0	0	0	0	0	1	1	1	1	1
-16.25°	0	0	0	0	0	0	1	1	1	1	1
-17.5°	0	0	0	0	0	0	1	1	1	1	1
-18.75°	0	0	0	0	0	0	1	1	1	1	1
-20°	0	0	0	0	0	0	1	1	1	1	1
-21.25°	0	0	0	0	0	0	1	1	1	1	1





REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	1	1	1	1	1
-23.75°	0	0	0	0	0	0	1	1	1	1	1
-25°	0	0	0	0	0	0	1	1	1	1	1
-26.25°	0	0	0	0	0	0	1	1	1	1	1
-27.5°	0	0	0	0	0	0	1	1	1	1	1
-28.75°	0	0	0	0	0	0	1	1	1	1	1
-30°	0	0	0	0	0	0	1	1	1	1	1
-31.25°	0	0	0	0	0	0	1	1	1	1	1
-32.5°	0	0	0	0	0	0	0	1	1	1	1
-33.75°	0	0	0	0	0	0	0	1	1	1	1
-35°	0	0	0	0	0	0	0	1	1	1	1
-36.25°	0	0	0	0	0	0	0	1	1	1	1
-37.5°	0	0	0	0	0	0	0	1	1	1	1
-38.75°	0	0	0	0	0	0	0	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	1	1	1	1
-43.75°	0	0	0	0	0	0	0	0	1	1	1
-45°	0	0	0	0	0	0	0	0	1	1	1
-46.25°	0	0	0	0	0	0	0	0	1	1	1
-47.5°	0	0	0	0	0	0	0	0	1	1	1
-48.75°	0	0	0	0	0	0	0	0	1	1	1
-50°	0	0	0	0	0	0	0	0	1	1	1
-51.25°	0	0	0	0	0	0	0	0	0	1	1
-52.5°	0	0	0	0	0	0	0	0	0	1	1
-53.75°	0	0	0	0	0	0	0	0	0	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	1
-58.75°	0	0	0	0	0	0	0	0	0	0	1
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	1	1	1
72.5°	0	0	0	0	0	0	0	1	1	1	1
71.25°	0	0	0	0	0	0	1	1	1	1	1
70°	0	0	0	0	0	1	1	1	1	1	1
68.75°	0	0	0	0	1	1	1	1	1	1	1
67.5°	0	0	0	1	1	1	1	1	1	1	1
66.25°	0	0	1	1	1	1	1	1	1	1	1
65°	0	0	1	1	1	1	1	1	1	1	1
63.75°	0	1	1	1	1	1	1	1	1	1	1
62.5°	0	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	2
40°	1	1	1	1	1	1	1	1	1	1	2
38.75°	1	1	1	1	1	1	1	1	1	2	2
37.5°	1	1	1	1	1	1	1	1	1	2	2
36.25°	1	1	1	1	1	1	1	1	1	2	2
35°	1	1	1	1	1	1	1	1	2	2	2



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	2	2	2
32.5°	1	1	1	1	1	1	1	1	2	2	2
31.25°	1	1	1	1	1	1	1	1	2	2	2
30°	1	1	1	1	1	1	1	2	2	2	2
28.75°	1	1	1	1	1	1	1	2	2	2	2
27.5°	1	1	1	1	1	1	1	2	2	2	2
26.25°	1	1	1	1	1	1	1	2	2	2	2
25°	1	1	1	1	1	1	2	2	2	2	2
23.75°	1	1	1	1	1	1	2	2	2	2	2
22.5°	1	1	1	1	1	1	2	2	2	2	2
21.25°	1	1	1	1	1	1	2	2	2	2	2
20°	1	1	1	1	1	1	2	2	2	2	2
18.75°	1	1	1	1	1	1	2	2	2	2	2
17.5°	1	1	1	1	1	1	2	2	2	2	2
16.25°	1	1	1	1	1	2	2	2	2	2	2
15°	1	1	1	1	1	2	2	2	2	2	2
13.75°	1	1	1	1	1	2	2	2	2	2	2
12.5°	1	1	1	1	1	2	2	2	2	2	2
11.25°	1	1	1	1	1	2	2	2	2	2	2
10°	1	1	1	1	1	2	2	2	2	2	2
8.75°	1	1	1	1	1	2	2	2	2	2	2
7.5°	1	1	1	1	1	2	2	2	2	2	2
6.25°	1	1	1	1	1	2	2	2	2	2	2
5°	1	1	1	1	1	2	2	2	2	2	2
3.75°	1	1	1	1	1	2	2	2	2	2	2
2.5°	1	1	1	1	1	2	2	2	2	2	2
1.25°	1	1	1	1	1	2	2	2	2	2	2
0°	1	1	1	1	1	2	2	2	2	2	2
-1.25°	1	1	1	1	1	2	2	2	2	2	2
-2.5°	1	1	1	1	1	2	2	2	2	2	2
-3.75°	1	1	1	1	1	2	2	2	2	2	2
-5°	1	1	1	1	1	2	2	2	2	2	2
-6.25°	1	1	1	1	1	2	2	2	2	2	2
-7.5°	1	1	1	1	1	2	2	2	2	2	2
-8.75°	1	1	1	1	1	2	2	2	2	2	2
-10°	1	1	1	1	1	2	2	2	2	2	2
-11.25°	1	1	1	1	1	2	2	2	2	2	2
-12.5°	1	1	1	1	1	2	2	2	2	2	2
-13.75°	1	1	1	1	1	2	2	2	2	2	2
-15°	1	1	1	1	1	2	2	2	2	2	2
-16.25°	1	1	1	1	1	2	2	2	2	2	2
-17.5°	1	1	1	1	1	1	2	2	2	2	2
-18.75°	1	1	1	1	1	1	2	2	2	2	2
-20°	1	1	1	1	1	1	2	2	2	2	2
-21.25°	1	1	1	1	1	1	2	2	2	2	2



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	2	2	2	2	2
-23.75°	1	1	1	1	1	1	2	2	2	2	2
-25°	1	1	1	1	1	1	2	2	2	2	2
-26.25°	1	1	1	1	1	1	1	2	2	2	2
-27.5°	1	1	1	1	1	1	1	2	2	2	2
-28.75°	1	1	1	1	1	1	1	2	2	2	2
-30°	1	1	1	1	1	1	1	2	2	2	2
-31.25°	1	1	1	1	1	1	1	1	2	2	2
-32.5°	1	1	1	1	1	1	1	1	2	2	2
-33.75°	1	1	1	1	1	1	1	1	2	2	2
-35°	1	1	1	1	1	1	1	1	2	2	2
-36.25°	1	1	1	1	1	1	1	1	1	2	2
-37.5°	1	1	1	1	1	1	1	1	1	2	2
-38.75°	1	1	1	1	1	1	1	1	1	2	2
-40°	1	1	1	1	1	1	1	1	1	1	2
-41.25°	1	1	1	1	1	1	1	1	1	1	2
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	0	1	1	1	1	1	1	1	1	1	1
-63.75°	0	1	1	1	1	1	1	1	1	1	1
-65°	0	0	1	1	1	1	1	1	1	1	1
-66.25°	0	0	1	1	1	1	1	1	1	1	1
-67.5°	0	0	0	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	1	1	1	1	1	1	1
-70°	0	0	0	0	0	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	1	1	1
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	2	2
53.75°	1	1	1	1	1	1	1	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	1	2	2	2	2	2	2	2
50°	1	1	1	2	2	2	2	2	2	2	2
48.75°	1	1	2	2	2	2	2	2	2	2	2
47.5°	1	1	2	2	2	2	2	2	2	2	2
46.25°	1	2	2	2	2	2	2	2	2	2	2
45°	1	2	2	2	2	2	2	2	2	2	3
43.75°	2	2	2	2	2	2	2	2	2	2	3
42.5°	2	2	2	2	2	2	2	2	2	3	3
41.25°	2	2	2	2	2	2	2	2	3	3	3
40°	2	2	2	2	2	2	2	2	3	3	3
38.75°	2	2	2	2	2	2	2	3	3	3	3
37.5°	2	2	2	2	2	2	3	3	3	3	4
36.25°	2	2	2	2	2	2	3	3	3	4	4
35°	2	2	2	2	2	3	3	3	4	4	4



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	2	3	3	3	4	4	4
32.5°	2	2	2	2	3	3	3	4	4	4	4
31.25°	2	2	2	2	3	3	3	4	4	4	4
30°	2	2	2	2	3	3	4	4	4	4	4
28.75°	2	2	2	3	3	3	4	4	4	4	4
27.5°	2	2	2	3	3	4	4	4	4	4	5
26.25°	2	2	2	3	3	4	4	4	4	4	5
25°	2	2	3	3	3	4	4	4	4	4	5
23.75°	2	2	3	3	3	4	4	4	4	4	5
22.5°	2	2	3	3	4	4	4	4	4	4	5
21.25°	2	2	3	3	4	4	4	4	4	4	5
20°	2	2	3	3	4	4	4	4	4	5	5
18.75°	2	3	3	3	4	4	4	4	4	5	5
17.5°	2	3	3	4	4	4	4	4	4	5	5
16.25°	2	3	3	4	4	4	4	4	4	5	5
15°	2	3	3	4	4	4	4	4	5	5	5
13.75°	2	3	3	4	4	4	4	4	5	5	5
12.5°	2	3	3	4	4	4	4	4	5	5	5
11.25°	2	3	3	4	4	4	4	4	5	5	5
10°	3	3	3	4	4	4	4	4	5	5	5
8.75°	3	3	4	4	4	4	4	4	5	5	5
7.5°	3	3	4	4	4	4	4	4	5	5	6
6.25°	3	3	4	4	4	4	4	5	5	5	6
5°	3	3	4	4	4	4	4	5	5	5	6
3.75°	3	3	4	4	4	4	4	5	5	5	6
2.5°	3	3	4	4	4	4	4	5	5	5	6
1.25°	3	3	4	4	4	4	4	5	5	5	6
0°	3	3	4	4	4	4	4	5	5	5	6
-1.25°	3	3	4	4	4	4	4	5	5	5	6
-2.5°	3	3	4	4	4	4	4	5	5	5	6
-3.75°	3	3	4	4	4	4	4	5	5	5	6
-5°	3	3	4	4	4	4	4	5	5	5	6
-6.25°	3	3	4	4	4	4	4	5	5	5	6
-7.5°	3	3	4	4	4	4	4	5	5	5	6
-8.75°	3	3	4	4	4	4	4	5	5	5	6
-10°	3	3	3	4	4	4	4	5	5	5	6
-11.25°	2	3	3	4	4	4	4	4	5	5	5
-12.5°	2	3	3	4	4	4	4	4	5	5	5
-13.75°	2	3	3	4	4	4	4	4	5	5	5
-15°	2	3	3	4	4	4	4	4	5	5	5
-16.25°	2	3	3	4	4	4	4	4	4	5	5
-17.5°	2	3	3	4	4	4	4	4	4	5	5
-18.75°	2	3	3	3	4	4	4	4	4	5	5
-20°	2	2	3	3	4	4	4	4	4	5	5
-21.25°	2	2	3	3	4	4	4	4	4	5	5





REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	3	3	4	4	4	4	4	5	5
-23.75°	2	2	3	3	3	4	4	4	4	5	5
-25°	2	2	3	3	3	4	4	4	4	4	5
-26.25°	2	2	2	3	3	4	4	4	4	4	5
-27.5°	2	2	2	3	3	4	4	4	4	4	5
-28.75°	2	2	2	3	3	3	4	4	4	4	4
-30°	2	2	2	2	3	3	4	4	4	4	4
-31.25°	2	2	2	2	3	3	3	4	4	4	4
-32.5°	2	2	2	2	3	3	3	4	4	4	4
-33.75°	2	2	2	2	2	3	3	3	4	4	4
-35°	2	2	2	2	2	3	3	3	4	4	4
-36.25°	2	2	2	2	2	2	3	3	3	4	4
-37.5°	2	2	2	2	2	2	3	3	3	3	4
-38.75°	2	2	2	2	2	2	2	3	3	3	3
-40°	2	2	2	2	2	2	2	2	3	3	3
-41.25°	2	2	2	2	2	2	2	2	3	3	3
-42.5°	2	2	2	2	2	2	2	2	2	3	3
-43.75°	2	2	2	2	2	2	2	2	2	2	3
-45°	1	2	2	2	2	2	2	2	2	2	3
-46.25°	1	2	2	2	2	2	2	2	2	2	2
-47.5°	1	1	2	2	2	2	2	2	2	2	2
-48.75°	1	1	2	2	2	2	2	2	2	2	2
-50°	1	1	1	2	2	2	2	2	2	2	2
-51.25°	1	1	1	1	2	2	2	2	2	2	2
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	1	2	2	2	2
-55°	1	1	1	1	1	1	1	1	1	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	2
61.25°	1	1	1	1	1	1	1	1	2	2	2
60°	1	1	1	1	1	2	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	3
53.75°	2	2	2	2	2	2	2	2	3	3	3
52.5°	2	2	2	2	2	2	3	3	3	3	3
51.25°	2	2	2	2	2	3	3	3	3	3	3
50°	2	2	2	3	3	3	3	3	3	3	3
48.75°	2	2	3	3	3	3	3	3	3	3	4
47.5°	2	3	3	3	3	3	3	3	3	4	4
46.25°	3	3	3	3	3	3	3	4	4	4	4
45°	3	3	3	3	3	3	4	4	4	4	4
43.75°	3	3	3	3	3	4	4	4	4	4	4
42.5°	3	3	3	3	4	4	4	4	4	4	4
41.25°	3	3	3	4	4	4	4	4	4	4	5
40°	3	4	4	4	4	4	4	4	4	5	5
38.75°	4	4	4	4	4	4	4	4	5	5	5
37.5°	4	4	4	4	4	4	4	5	5	5	5
36.25°	4	4	4	4	4	4	5	5	5	5	6
35°	4	4	4	4	4	5	5	5	5	6	6



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	4	4	4	4	5	5	5	5	6	6	7
32.5°	4	4	4	5	5	5	5	6	6	7	7
31.25°	4	4	5	5	5	5	5	6	7	7	8
30°	4	5	5	5	5	5	6	6	7	8	8
28.75°	5	5	5	5	5	6	6	7	8	8	9
27.5°	5	5	5	5	5	6	7	7	8	9	11
26.25°	5	5	5	5	6	6	7	8	9	10	12
25°	5	5	5	5	6	7	8	9	10	12	13
23.75°	5	5	5	6	6	7	9	10	11	13	15
22.5°	5	5	5	6	7	8	9	11	13	15	18
21.25°	5	5	6	6	7	9	10	12	14	16	20
20°	5	5	6	7	8	9	11	13	15	19	23
18.75°	5	6	6	7	9	10	12	15	17	22	27
17.5°	5	6	7	7	9	11	13	16	20	25	32
16.25°	6	6	7	8	10	12	14	17	22	28	38
15°	6	6	7	9	11	13	15	19	25	31	43
13.75°	6	7	7	9	11	14	16	21	27	36	49
12.5°	6	7	8	10	12	15	17	23	30	41	54
11.25°	6	7	8	10	13	16	18	26	33	46	59
10°	6	7	9	11	13	16	20	28	36	50	64
8.75°	7	7	9	11	14	17	22	30	40	54	71
7.5°	7	8	9	12	15	18	24	32	44	58	77
6.25°	7	8	10	12	15	19	26	34	47	61	83
5°	7	8	10	13	16	19	27	36	49	64	87
3.75°	7	8	10	13	16	20	28	37	52	67	92
2.5°	7	8	11	13	17	20	29	39	54	69	95
1.25°	7	8	11	14	17	21	30	40	55	71	98
0°	7	8	11	14	17	21	31	41	57	72	100
-1.25°	7	8	11	14	17	21	30	40	55	71	98
-2.5°	7	8	11	13	17	20	29	39	54	69	95
-3.75°	7	8	10	13	16	20	28	37	52	67	92
-5°	7	8	10	13	16	19	27	36	49	64	87
-6.25°	7	8	10	12	15	19	26	34	47	61	83
-7.5°	7	8	9	12	15	18	24	32	44	58	77
-8.75°	7	7	9	11	14	17	22	30	40	54	71
-10°	6	7	9	11	13	16	20	28	36	50	64
-11.25°	6	7	8	10	13	16	18	26	33	46	59
-12.5°	6	7	8	10	12	15	17	23	30	41	54
-13.75°	6	7	7	9	11	14	16	21	27	36	49
-15°	6	6	7	9	11	13	15	19	25	31	43
-16.25°	6	6	7	8	10	12	14	17	22	28	38
-17.5°	5	6	7	7	9	11	13	16	20	25	32
-18.75°	5	6	6	7	9	10	12	15	17	22	27
-20°	5	5	6	7	8	9	11	13	15	19	23
-21.25°	5	5	6	6	7	9	10	12	14	16	20



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	5	5	5	6	7	8	9	11	13	15	18
-23.75°	5	5	5	6	6	7	9	10	11	13	15
-25°	5	5	5	5	6	7	8	9	10	12	13
-26.25°	5	5	5	5	6	6	7	8	9	10	12
-27.5°	5	5	5	5	5	6	7	7	8	9	11
-28.75°	5	5	5	5	5	6	6	7	8	8	9
-30°	4	5	5	5	5	5	6	6	7	8	8
-31.25°	4	4	5	5	5	5	5	6	7	7	8
-32.5°	4	4	4	5	5	5	5	6	6	7	7
-33.75°	4	4	4	4	5	5	5	5	6	6	7
-35°	4	4	4	4	4	5	5	5	5	6	6
-36.25°	4	4	4	4	4	4	5	5	5	5	6
-37.5°	4	4	4	4	4	4	4	5	5	5	5
-38.75°	4	4	4	4	4	4	4	4	5	5	5
-40°	3	4	4	4	4	4	4	4	4	5	5
-41.25°	3	3	3	4	4	4	4	4	4	4	5
-42.5°	3	3	3	3	4	4	4	4	4	4	4
-43.75°	3	3	3	3	3	4	4	4	4	4	4
-45°	3	3	3	3	3	3	4	4	4	4	4
-46.25°	3	3	3	3	3	3	3	4	4	4	4
-47.5°	2	3	3	3	3	3	3	3	3	4	4
-48.75°	2	2	3	3	3	3	3	3	3	3	4
-50°	2	2	2	3	3	3	3	3	3	3	3
-51.25°	2	2	2	2	2	3	3	3	3	3	3
-52.5°	2	2	2	2	2	2	3	3	3	3	3
-53.75°	2	2	2	2	2	2	2	2	3	3	3
-55°	2	2	2	2	2	2	2	2	2	2	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	1	1	1	1	1	1	1



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	2
65°	1	1	1	1	1	2	2	2	2	2	2
63.75°	1	1	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	2	2	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	4	4	4	4
50°	3	3	3	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	5
47.5°	4	4	4	4	4	4	4	5	5	5	5
46.25°	4	4	4	4	4	5	5	5	5	5	5
45°	4	4	4	4	5	5	5	5	5	5	5
43.75°	4	4	5	5	5	5	5	5	5	5	6
42.5°	4	5	5	5	5	5	6	6	6	6	6
41.25°	5	5	5	5	6	6	6	6	6	6	6
40°	5	5	6	6	6	6	6	6	7	7	7
38.75°	5	6	6	6	6	6	7	7	7	7	8
37.5°	6	6	6	6	7	7	7	7	8	8	8
36.25°	6	6	7	7	7	7	8	8	9	9	10
35°	6	7	7	7	8	8	9	9	10	10	11



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	7	7	8	8	9	9	10	11	11	12	12
32.5°	8	8	9	9	10	10	11	12	13	14	15
31.25°	8	9	10	11	11	12	13	14	15	17	18
30°	9	10	11	12	13	14	15	16	18	19	22
28.75°	10	12	13	14	16	17	19	20	21	25	27
27.5°	12	13	15	17	19	22	24	25	27	30	33
26.25°	13	16	18	20	24	27	30	34	36	37	43
25°	15	18	21	26	30	34	39	43	46	51	54
23.75°	18	21	26	32	37	44	49	54	61	65	69
22.5°	21	25	32	39	47	54	61	70	77	82	89
21.25°	24	32	39	48	58	66	76	86	94	103	110
20°	29	39	47	59	69	81	93	103	114	123	131
18.75°	36	46	57	70	82	97	110	123	134	144	154
17.5°	43	53	69	83	99	114	129	143	155	166	177
16.25°	50	64	81	96	115	132	148	163	176	188	201
15°	56	74	92	112	132	151	168	183	197	211	225
13.75°	63	83	102	126	149	169	187	203	219	234	248
12.5°	71	92	114	138	162	185	207	222	240	257	272
11.25°	79	101	125	150	174	198	220	241	262	278	295
10°	87	109	135	160	186	210	232	255	276	297	319
8.75°	94	118	144	170	197	222	244	267	289	311	334
7.5°	101	126	153	180	207	233	256	279	300	324	347
6.25°	107	134	161	189	216	243	266	290	312	335	359
5°	113	140	168	197	225	252	276	299	321	345	370
3.75°	118	146	174	204	233	260	284	307	330	354	379
2.5°	122	151	179	210	240	268	292	315	338	362	387
1.25°	126	155	184	215	246	274	298	321	344	368	393
0°	129	158	187	219	251	280	303	327	350	374	398
-1.25°	126	155	184	215	246	274	298	321	344	368	393
-2.5°	122	151	179	210	240	268	292	315	338	362	387
-3.75°	118	146	174	204	233	260	284	307	330	354	379
-5°	113	140	168	197	225	252	276	299	321	345	370
-6.25°	107	134	161	189	216	243	266	290	312	335	359
-7.5°	101	126	153	180	207	233	256	279	300	324	347
-8.75°	94	118	144	170	197	222	244	267	289	311	334
-10°	87	109	135	160	186	210	232	255	276	297	319
-11.25°	79	101	125	150	174	198	220	241	262	278	295
-12.5°	71	92	114	138	162	185	207	222	240	257	272
-13.75°	63	83	102	126	149	169	187	203	219	234	248
-15°	56	74	92	112	132	151	168	183	197	211	225
-16.25°	50	64	81	96	115	132	148	163	176	188	201
-17.5°	43	53	69	83	99	114	129	143	155	166	177
-18.75°	36	46	57	70	82	97	110	123	134	144	154
-20°	29	39	47	59	69	81	93	103	114	123	131
-21.25°	24	32	39	48	58	66	76	86	94	103	110





REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	21	25	32	39	47	54	61	70	77	82	89
-23.75°	18	21	26	32	37	44	49	54	61	65	69
-25°	15	18	21	26	30	34	39	43	46	51	54
-26.25°	13	16	18	20	24	27	30	34	36	37	43
-27.5°	12	13	15	17	19	22	24	25	27	30	33
-28.75°	10	12	13	14	16	17	19	20	21	25	27
-30°	9	10	11	12	13	14	15	16	18	19	22
-31.25°	8	9	10	11	11	12	13	14	15	17	18
-32.5°	8	8	9	9	10	10	11	12	13	14	15
-33.75°	7	7	8	8	9	9	10	11	11	12	12
-35°	6	7	7	7	8	8	9	9	10	10	11
-36.25°	6	6	7	7	7	7	8	8	9	9	10
-37.5°	6	6	6	6	7	7	7	7	8	8	8
-38.75°	5	6	6	6	6	6	7	7	7	7	8
-40°	5	5	6	6	6	6	6	6	7	7	7
-41.25°	5	5	5	5	6	6	6	6	6	6	6
-42.5°	4	5	5	5	5	5	6	6	6	6	6
-43.75°	4	4	5	5	5	5	5	5	5	5	6
-45°	4	4	4	4	5	5	5	5	5	5	5
-46.25°	4	4	4	4	4	5	5	5	5	5	5
-47.5°	4	4	4	4	4	4	4	5	5	5	5
-48.75°	4	4	4	4	4	4	4	4	4	4	5
-50°	3	3	3	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	3	3	3	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	2	2	2	2	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	2	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	1	2	2	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	2
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	3	3
58.75°	2	2	2	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	4
53.75°	3	3	3	3	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	5	5	5	5	4	4	4	4	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	5	5	5	6	6	6	6	6	6	6	6
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	6	6	6	6	6	7	7	7	7	7	7
41.25°	7	7	7	7	7	7	7	7	7	7	8
40°	7	7	7	7	7	7	8	8	8	8	8
38.75°	8	8	8	8	8	8	9	9	9	9	9
37.5°	9	9	9	9	9	9	10	10	10	10	10
36.25°	10	10	10	11	11	11	11	11	11	12	12
35°	11	12	12	13	13	13	12	13	13	13	14



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	13	14	14	15	15	15	15	14	15	15	16
32.5°	16	16	18	18	18	18	17	17	17	18	18
31.25°	19	21	22	22	22	23	22	20	20	21	21
30°	24	25	27	28	29	29	27	26	25	26	26
28.75°	29	32	35	36	36	37	36	33	30	31	32
27.5°	38	42	44	46	48	48	46	42	39	38	40
26.25°	48	52	56	59	60	60	59	56	52	48	50
25°	60	67	71	74	76	76	75	72	67	62	64
23.75°	76	83	88	92	94	94	94	91	87	81	80
22.5°	95	101	108	112	115	116	116	114	109	103	98
21.25°	116	123	129	135	139	140	140	138	133	128	121
20°	139	146	153	160	164	166	166	164	161	156	150
18.75°	163	172	179	186	190	193	193	193	191	187	183
17.5°	188	197	206	213	218	221	223	224	223	221	217
16.25°	212	223	232	240	246	251	255	257	257	256	253
15°	237	249	259	268	276	283	287	290	290	289	286
13.75°	262	275	287	298	307	314	319	321	321	320	318
12.5°	287	301	316	328	337	344	347	349	350	350	346
11.25°	312	328	345	357	365	371	374	377	378	376	371
10°	337	357	374	384	391	395	399	402	402	399	393
8.75°	358	384	400	409	415	419	423	425	423	419	415
7.5°	373	399	419	432	437	442	445	446	443	440	437
6.25°	386	411	429	442	453	462	466	466	463	459	455
5°	396	420	439	452	463	472	478	482	482	475	469
3.75°	405	429	449	461	472	481	486	490	491	486	482
2.5°	412	438	457	469	480	489	494	497	497	492	488
1.25°	418	445	465	477	487	496	500	503	503	498	494
0°	422	450	471	483	494	503	507	510	510	505	499
-1.25°	418	445	465	477	487	496	500	503	503	498	494
-2.5°	412	438	457	469	480	489	494	497	497	492	488
-3.75°	405	429	449	461	472	481	486	490	491	486	482
-5°	396	420	439	452	463	472	478	482	482	475	469
-6.25°	386	411	429	442	453	462	466	466	463	459	455
-7.5°	373	399	419	432	437	442	445	446	443	440	437
-8.75°	358	384	400	409	415	419	423	425	423	419	415
-10°	337	357	374	384	391	395	399	402	402	399	393
-11.25°	312	328	345	357	365	371	374	377	378	376	371
-12.5°	287	301	316	328	337	344	347	349	350	350	346
-13.75°	262	275	287	298	307	314	319	321	321	320	318
-15°	237	249	259	268	276	283	287	290	290	289	286
-16.25°	212	223	232	240	246	251	255	257	257	256	253
-17.5°	188	197	206	213	218	221	223	224	223	221	217
-18.75°	163	172	179	186	190	193	193	193	191	187	183
-20°	139	146	153	160	164	166	166	164	161	156	150
-21.25°	116	123	129	135	139	140	140	138	133	128	121



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	95	101	108	112	115	116	116	114	109	103	98
-23.75°	76	83	88	92	94	94	94	91	87	81	80
-25°	60	67	71	74	76	76	75	72	67	62	64
-26.25°	48	52	56	59	60	60	59	56	52	48	50
-27.5°	38	42	44	46	48	48	46	42	39	38	40
-28.75°	29	32	35	36	36	37	36	33	30	31	32
-30°	24	25	27	28	29	29	27	26	25	26	26
-31.25°	19	21	22	22	22	23	22	20	20	21	21
-32.5°	16	16	18	18	18	18	17	17	17	18	18
-33.75°	13	14	14	15	15	15	15	14	15	15	16
-35°	11	12	12	13	13	13	12	13	13	13	14
-36.25°	10	10	10	11	11	11	11	11	11	12	12
-37.5°	9	9	9	9	9	9	10	10	10	10	10
-38.75°	8	8	8	8	8	8	9	9	9	9	9
-40°	7	7	7	7	7	7	8	8	8	8	8
-41.25°	7	7	7	7	7	7	7	7	7	7	8
-42.5°	6	6	6	6	6	7	7	7	7	7	7
-43.75°	6	6	6	6	6	6	6	6	6	6	6
-45°	5	5	5	6	6	6	6	6	6	6	6
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	4	4	5	5	5	5	4	4	4	4	5
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	3	3	3	3	4	4	4	4	4	4	4
-55°	3	3	3	3	3	3	3	3	3	3	4
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	2	2	2	2	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	1	1	1	1	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	4	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	5	5	5	5	5	5	5	5	5	5	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	6	6	6	6	6	6	6	6	6	6	6
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	7	7	7	7	7	7	7	7	7	7	7
41.25°	8	8	8	8	8	8	8	8	8	8	8
40°	8	8	8	8	8	8	8	8	8	8	8
38.75°	9	9	9	9	9	9	9	9	9	9	9
37.5°	10	10	10	10	10	10	10	10	10	10	10
36.25°	12	12	12	12	12	12	12	12	12	12	12
35°	14	14	14	14	14	14	14	14	14	14	14



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	16	16	16	16	16	16	16	16	16	16	16
32.5°	18	19	19	18	18	18	17	18	18	18	19
31.25°	22	22	22	22	22	22	21	22	22	22	22
30°	27	27	27	27	26	25	25	25	26	27	27
28.75°	33	33	33	33	32	31	30	31	32	33	33
27.5°	41	41	41	41	40	39	37	39	40	41	41
26.25°	52	53	53	53	52	51	49	51	52	53	53
25°	66	68	68	68	67	65	62	65	67	68	68
23.75°	83	84	85	84	83	81	77	81	83	84	85
22.5°	101	103	104	104	102	99	95	99	102	104	104
21.25°	123	126	127	127	125	122	118	122	125	127	127
20°	148	152	153	153	151	147	142	147	151	153	153
18.75°	177	181	183	183	180	176	169	176	180	183	183
17.5°	212	212	214	213	210	204	196	204	210	213	214
16.25°	248	245	246	244	240	234	226	234	240	244	246
15°	282	275	275	273	269	263	255	263	269	273	275
13.75°	313	306	301	298	293	287	278	287	293	298	301
12.5°	340	333	325	323	319	313	305	313	319	323	325
11.25°	365	358	351	347	343	337	329	337	343	347	351
10°	388	383	376	369	366	360	352	360	366	369	376
8.75°	412	407	400	391	387	381	374	381	387	391	400
7.5°	435	429	421	411	404	399	392	399	404	411	421
6.25°	451	447	438	429	419	414	407	414	419	429	438
5°	465	461	454	442	432	425	420	425	432	442	454
3.75°	479	473	463	452	441	432	428	432	441	452	463
2.5°	489	482	470	458	446	437	434	437	446	458	470
1.25°	492	485	474	462	450	442	438	442	450	462	474
0°	497	489	477	464	451	444	442	444	451	464	477
-1.25°	492	485	474	462	450	442	438	442	450	462	474
-2.5°	489	482	470	458	446	437	434	437	446	458	470
-3.75°	479	473	463	452	441	432	428	432	441	452	463
-5°	465	461	454	442	432	425	420	425	432	442	454
-6.25°	451	447	438	429	419	414	407	414	419	429	438
-7.5°	435	429	421	411	404	399	392	399	404	411	421
-8.75°	412	407	400	391	387	381	374	381	387	391	400
-10°	388	383	376	369	366	360	352	360	366	369	376
-11.25°	365	358	351	347	343	337	329	337	343	347	351
-12.5°	340	333	325	323	319	313	305	313	319	323	325
-13.75°	313	306	301	298	293	287	278	287	293	298	301
-15°	282	275	275	273	269	263	255	263	269	273	275
-16.25°	248	245	246	244	240	234	226	234	240	244	246
-17.5°	212	212	214	213	210	204	196	204	210	213	214
-18.75°	177	181	183	183	180	176	169	176	180	183	183
-20°	148	152	153	153	151	147	142	147	151	153	153
-21.25°	123	126	127	127	125	122	118	122	125	127	127





REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	101	103	104	104	102	99	95	99	102	104	104
-23.75°	83	84	85	84	83	81	77	81	83	84	85
-25°	66	68	68	68	67	65	62	65	67	68	68
-26.25°	52	53	53	53	52	51	49	51	52	53	53
-27.5°	41	41	41	41	40	39	37	39	40	41	41
-28.75°	33	33	33	33	32	31	30	31	32	33	33
-30°	27	27	27	27	26	25	25	25	26	27	27
-31.25°	22	22	22	22	22	22	21	22	22	22	22
-32.5°	18	19	19	18	18	18	17	18	18	18	19
-33.75°	16	16	16	16	16	16	16	16	16	16	16
-35°	14	14	14	14	14	14	14	14	14	14	14
-36.25°	12	12	12	12	12	12	12	12	12	12	12
-37.5°	10	10	10	10	10	10	10	10	10	10	10
-38.75°	9	9	9	9	9	9	9	9	9	9	9
-40°	8	8	8	8	8	8	8	8	8	8	8
-41.25°	8	8	8	8	8	8	8	8	8	8	8
-42.5°	7	7	7	7	7	7	7	7	7	7	7
-43.75°	6	6	6	6	6	6	6	6	6	6	6
-45°	6	6	6	6	6	6	6	6	6	6	6
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	1	1	1
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	2	2	2	2	2	2	2
58.75°	3	3	3	3	3	3	3	3	3	3	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	4	4	4	3	3	3	3	3	3	3	3
53.75°	4	4	4	4	4	4	4	4	4	3	3
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	5	5	5	4	4	4	4	5	5	5	5
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	6	6	6	6	6	6	6	6	6	6	5
43.75°	6	6	6	6	6	6	6	6	6	6	6
42.5°	7	7	7	7	7	7	7	7	6	6	6
41.25°	8	8	8	7	7	7	7	7	7	7	7
40°	8	8	8	8	8	8	8	7	7	7	7
38.75°	9	9	9	9	9	9	9	8	8	8	8
37.5°	10	10	10	10	10	10	10	9	9	9	9
36.25°	12	12	12	12	11	11	11	11	11	11	10
35°	14	14	14	13	13	13	12	13	13	13	12



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	16	16	16	15	15	14	15	15	15	15	14
32.5°	19	18	18	18	17	17	17	18	18	18	18
31.25°	22	22	21	21	20	20	22	23	22	22	22
30°	27	27	26	26	25	26	27	29	29	28	27
28.75°	33	33	32	31	30	33	36	37	36	36	35
27.5°	41	41	40	38	39	42	46	48	48	46	44
26.25°	53	52	50	48	52	56	59	60	60	59	56
25°	68	66	64	62	67	72	75	76	76	74	71
23.75°	84	83	80	81	87	91	94	94	94	92	88
22.5°	103	101	98	103	109	114	116	116	115	112	108
21.25°	126	123	121	128	133	138	140	140	139	135	129
20°	152	148	150	156	161	164	166	166	164	160	153
18.75°	181	177	183	187	191	193	193	193	190	186	179
17.5°	212	212	217	221	223	224	223	221	218	213	206
16.25°	245	248	253	256	257	257	255	251	246	240	232
15°	275	282	286	289	290	290	287	283	276	268	259
13.75°	306	313	318	320	321	321	319	314	307	298	287
12.5°	333	340	346	350	350	349	347	344	337	328	316
11.25°	358	365	371	376	378	377	374	371	365	357	345
10°	383	388	393	399	402	402	399	395	391	384	374
8.75°	407	412	415	419	423	425	423	419	415	409	400
7.5°	429	435	437	440	443	446	445	442	437	432	419
6.25°	447	451	455	459	463	466	466	462	453	442	429
5°	461	465	469	475	482	482	478	472	463	452	439
3.75°	473	479	482	486	491	490	486	481	472	461	449
2.5°	482	489	488	492	497	497	494	489	480	469	457
1.25°	485	492	494	498	503	503	500	496	487	477	465
0°	489	497	499	505	510	510	507	503	494	483	471
-1.25°	485	492	494	498	503	503	500	496	487	477	465
-2.5°	482	489	488	492	497	497	494	489	480	469	457
-3.75°	473	479	482	486	491	490	486	481	472	461	449
-5°	461	465	469	475	482	482	478	472	463	452	439
-6.25°	447	451	455	459	463	466	466	462	453	442	429
-7.5°	429	435	437	440	443	446	445	442	437	432	419
-8.75°	407	412	415	419	423	425	423	419	415	409	400
-10°	383	388	393	399	402	402	399	395	391	384	374
-11.25°	358	365	371	376	378	377	374	371	365	357	345
-12.5°	333	340	346	350	350	349	347	344	337	328	316
-13.75°	306	313	318	320	321	321	319	314	307	298	287
-15°	275	282	286	289	290	290	287	283	276	268	259
-16.25°	245	248	253	256	257	257	255	251	246	240	232
-17.5°	212	212	217	221	223	224	223	221	218	213	206
-18.75°	181	177	183	187	191	193	193	193	190	186	179
-20°	152	148	150	156	161	164	166	166	164	160	153
-21.25°	126	123	121	128	133	138	140	140	139	135	129



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	103	101	98	103	109	114	116	116	115	112	108
-23.75°	84	83	80	81	87	91	94	94	94	92	88
-25°	68	66	64	62	67	72	75	76	76	74	71
-26.25°	53	52	50	48	52	56	59	60	60	59	56
-27.5°	41	41	40	38	39	42	46	48	48	46	44
-28.75°	33	33	32	31	30	33	36	37	36	36	35
-30°	27	27	26	26	25	26	27	29	29	28	27
-31.25°	22	22	21	21	20	20	22	23	22	22	22
-32.5°	19	18	18	18	17	17	17	18	18	18	18
-33.75°	16	16	16	15	15	14	15	15	15	15	14
-35°	14	14	14	13	13	13	12	13	13	13	12
-36.25°	12	12	12	12	11	11	11	11	11	11	10
-37.5°	10	10	10	10	10	10	10	9	9	9	9
-38.75°	9	9	9	9	9	9	9	8	8	8	8
-40°	8	8	8	8	8	8	8	7	7	7	7
-41.25°	8	8	8	7	7	7	7	7	7	7	7
-42.5°	7	7	7	7	7	7	7	7	6	6	6
-43.75°	6	6	6	6	6	6	6	6	6	6	6
-45°	6	6	6	6	6	6	6	6	6	6	5
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	4	4	4	4	5	5	5	5
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	3	3
-55°	4	4	4	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	2
-60°	3	3	3	3	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	2	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	1	1	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	3	3	3	3	3	3	3	3	2	2	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	4	4	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	3
48.75°	5	5	5	4	4	4	4	4	4	4	4
47.5°	5	5	5	5	5	5	4	4	4	4	4
46.25°	5	5	5	5	5	5	5	5	4	4	4
45°	5	5	5	5	5	5	5	5	5	4	4
43.75°	6	6	6	5	5	5	5	5	5	5	5
42.5°	6	6	6	6	6	6	6	5	5	5	5
41.25°	7	7	6	6	6	6	6	6	6	5	5
40°	7	7	7	7	7	6	6	6	6	6	6
38.75°	8	8	8	7	7	7	7	6	6	6	6
37.5°	9	9	8	8	8	7	7	7	7	6	6
36.25°	10	10	10	9	9	8	8	7	7	7	7
35°	12	11	11	10	10	9	9	8	8	7	7



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	14	13	12	12	11	11	10	9	9	8	8
32.5°	16	16	15	14	13	12	11	10	10	9	9
31.25°	21	19	18	17	15	14	13	12	11	11	10
30°	25	24	22	19	18	16	15	14	13	12	11
28.75°	32	29	27	25	21	20	19	17	16	14	13
27.5°	42	38	33	30	27	25	24	22	19	17	15
26.25°	52	48	43	37	36	34	30	27	24	20	18
25°	67	60	54	51	46	43	39	34	30	26	21
23.75°	83	76	69	65	61	54	49	44	37	32	26
22.5°	101	95	89	82	77	70	61	54	47	39	32
21.25°	123	116	110	103	94	86	76	66	58	48	39
20°	146	139	131	123	114	103	93	81	69	59	47
18.75°	172	163	154	144	134	123	110	97	82	70	57
17.5°	197	188	177	166	155	143	129	114	99	83	69
16.25°	223	212	201	188	176	163	148	132	115	96	81
15°	249	237	225	211	197	183	168	151	132	112	92
13.75°	275	262	248	234	219	203	187	169	149	126	102
12.5°	301	287	272	257	240	222	207	185	162	138	114
11.25°	328	312	295	278	262	241	220	198	174	150	125
10°	357	337	319	297	276	255	232	210	186	160	135
8.75°	384	358	334	311	289	267	244	222	197	170	144
7.5°	399	373	347	324	300	279	256	233	207	180	153
6.25°	411	386	359	335	312	290	266	243	216	189	161
5°	420	396	370	345	321	299	276	252	225	197	168
3.75°	429	405	379	354	330	307	284	260	233	204	174
2.5°	438	412	387	362	338	315	292	268	240	210	179
1.25°	445	418	393	368	344	321	298	274	246	215	184
0°	450	422	398	374	350	327	303	280	251	219	187
-1.25°	445	418	393	368	344	321	298	274	246	215	184
-2.5°	438	412	387	362	338	315	292	268	240	210	179
-3.75°	429	405	379	354	330	307	284	260	233	204	174
-5°	420	396	370	345	321	299	276	252	225	197	168
-6.25°	411	386	359	335	312	290	266	243	216	189	161
-7.5°	399	373	347	324	300	279	256	233	207	180	153
-8.75°	384	358	334	311	289	267	244	222	197	170	144
-10°	357	337	319	297	276	255	232	210	186	160	135
-11.25°	328	312	295	278	262	241	220	198	174	150	125
-12.5°	301	287	272	257	240	222	207	185	162	138	114
-13.75°	275	262	248	234	219	203	187	169	149	126	102
-15°	249	237	225	211	197	183	168	151	132	112	92
-16.25°	223	212	201	188	176	163	148	132	115	96	81
-17.5°	197	188	177	166	155	143	129	114	99	83	69
-18.75°	172	163	154	144	134	123	110	97	82	70	57
-20°	146	139	131	123	114	103	93	81	69	59	47
-21.25°	123	116	110	103	94	86	76	66	58	48	39





REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	101	95	89	82	77	70	61	54	47	39	32
-23.75°	83	76	69	65	61	54	49	44	37	32	26
-25°	67	60	54	51	46	43	39	34	30	26	21
-26.25°	52	48	43	37	36	34	30	27	24	20	18
-27.5°	42	38	33	30	27	25	24	22	19	17	15
-28.75°	32	29	27	25	21	20	19	17	16	14	13
-30°	25	24	22	19	18	16	15	14	13	12	11
-31.25°	21	19	18	17	15	14	13	12	11	11	10
-32.5°	16	16	15	14	13	12	11	10	10	9	9
-33.75°	14	13	12	12	11	11	10	9	9	8	8
-35°	12	11	11	10	10	9	9	8	8	7	7
-36.25°	10	10	10	9	9	8	8	7	7	7	7
-37.5°	9	9	8	8	8	7	7	7	7	6	6
-38.75°	8	8	8	7	7	7	7	6	6	6	6
-40°	7	7	7	7	7	6	6	6	6	6	6
-41.25°	7	7	6	6	6	6	6	6	6	5	5
-42.5°	6	6	6	6	6	6	6	5	5	5	5
-43.75°	6	6	6	5	5	5	5	5	5	5	5
-45°	5	5	5	5	5	5	5	5	5	4	4
-46.25°	5	5	5	5	5	5	5	5	4	4	4
-47.5°	5	5	5	5	5	5	4	4	4	4	4
-48.75°	5	5	5	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	3
-51.25°	4	4	4	4	4	4	3	3	3	3	3
-52.5°	4	4	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	2	2	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	1	1	1
-66.25°	2	2	2	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	2	2	2	2	2	2	2	2
53.75°	3	3	3	3	3	2	2	2	2	2	2
52.5°	3	3	3	3	3	3	3	2	2	2	2
51.25°	3	3	3	3	3	3	3	3	2	2	2
50°	3	3	3	3	3	3	3	3	3	3	2
48.75°	4	4	4	3	3	3	3	3	3	3	3
47.5°	4	4	4	4	3	3	3	3	3	3	3
46.25°	4	4	4	4	4	4	3	3	3	3	3
45°	4	4	4	4	4	4	4	3	3	3	3
43.75°	4	4	4	4	4	4	4	4	3	3	3
42.5°	5	4	4	4	4	4	4	4	4	3	3
41.25°	5	5	5	4	4	4	4	4	4	4	3
40°	5	5	5	5	4	4	4	4	4	4	4
38.75°	6	5	5	5	5	4	4	4	4	4	4
37.5°	6	6	5	5	5	5	4	4	4	4	4
36.25°	6	6	6	5	5	5	5	4	4	4	4
35°	7	6	6	6	5	5	5	5	4	4	4



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	7	7	7	6	6	5	5	5	5	4	4
32.5°	8	8	7	7	6	6	5	5	5	5	4
31.25°	9	8	8	7	7	6	5	5	5	5	5
30°	10	9	8	8	7	6	6	5	5	5	5
28.75°	12	10	9	8	8	7	6	6	5	5	5
27.5°	13	12	11	9	8	7	7	6	5	5	5
26.25°	16	13	12	10	9	8	7	6	6	5	5
25°	18	15	13	12	10	9	8	7	6	5	5
23.75°	21	18	15	13	11	10	9	7	6	6	5
22.5°	25	21	18	15	13	11	9	8	7	6	5
21.25°	32	24	20	16	14	12	10	9	7	6	6
20°	39	29	23	19	15	13	11	9	8	7	6
18.75°	46	36	27	22	17	15	12	10	9	7	6
17.5°	53	43	32	25	20	16	13	11	9	7	7
16.25°	64	50	38	28	22	17	14	12	10	8	7
15°	74	56	43	31	25	19	15	13	11	9	7
13.75°	83	63	49	36	27	21	16	14	11	9	7
12.5°	92	71	54	41	30	23	17	15	12	10	8
11.25°	101	79	59	46	33	26	18	16	13	10	8
10°	109	87	64	50	36	28	20	16	13	11	9
8.75°	118	94	71	54	40	30	22	17	14	11	9
7.5°	126	101	77	58	44	32	24	18	15	12	9
6.25°	134	107	83	61	47	34	26	19	15	12	10
5°	140	113	87	64	49	36	27	19	16	13	10
3.75°	146	118	92	67	52	37	28	20	16	13	10
2.5°	151	122	95	69	54	39	29	20	17	13	11
1.25°	155	126	98	71	55	40	30	21	17	14	11
0°	158	129	100	72	57	41	31	21	17	14	11
-1.25°	155	126	98	71	55	40	30	21	17	14	11
-2.5°	151	122	95	69	54	39	29	20	17	13	11
-3.75°	146	118	92	67	52	37	28	20	16	13	10
-5°	140	113	87	64	49	36	27	19	16	13	10
-6.25°	134	107	83	61	47	34	26	19	15	12	10
-7.5°	126	101	77	58	44	32	24	18	15	12	9
-8.75°	118	94	71	54	40	30	22	17	14	11	9
-10°	109	87	64	50	36	28	20	16	13	11	9
-11.25°	101	79	59	46	33	26	18	16	13	10	8
-12.5°	92	71	54	41	30	23	17	15	12	10	8
-13.75°	83	63	49	36	27	21	16	14	11	9	7
-15°	74	56	43	31	25	19	15	13	11	9	7
-16.25°	64	50	38	28	22	17	14	12	10	8	7
-17.5°	53	43	32	25	20	16	13	11	9	7	7
-18.75°	46	36	27	22	17	15	12	10	9	7	6
-20°	39	29	23	19	15	13	11	9	8	7	6
-21.25°	32	24	20	16	14	12	10	9	7	6	6



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	25	21	18	15	13	11	9	8	7	6	5
-23.75°	21	18	15	13	11	10	9	7	6	6	5
-25°	18	15	13	12	10	9	8	7	6	5	5
-26.25°	16	13	12	10	9	8	7	6	6	5	5
-27.5°	13	12	11	9	8	7	7	6	5	5	5
-28.75°	12	10	9	8	8	7	6	6	5	5	5
-30°	10	9	8	8	7	6	6	5	5	5	5
-31.25°	9	8	8	7	7	6	5	5	5	5	5
-32.5°	8	8	7	7	6	6	5	5	5	5	4
-33.75°	7	7	7	6	6	5	5	5	5	4	4
-35°	7	6	6	6	5	5	5	5	4	4	4
-36.25°	6	6	6	5	5	5	5	4	4	4	4
-37.5°	6	6	5	5	5	5	4	4	4	4	4
-38.75°	6	5	5	5	5	4	4	4	4	4	4
-40°	5	5	5	5	4	4	4	4	4	4	4
-41.25°	5	5	5	4	4	4	4	4	4	4	3
-42.5°	5	4	4	4	4	4	4	4	4	3	3
-43.75°	4	4	4	4	4	4	4	4	3	3	3
-45°	4	4	4	4	4	4	4	3	3	3	3
-46.25°	4	4	4	4	4	4	3	3	3	3	3
-47.5°	4	4	4	4	3	3	3	3	3	3	3
-48.75°	4	4	4	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	2
-51.25°	3	3	3	3	3	3	3	3	2	2	2
-52.5°	3	3	3	3	3	3	3	2	2	2	2
-53.75°	3	3	3	3	3	2	2	2	2	2	2
-55°	3	3	3	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	1
-60°	2	2	2	2	2	2	2	2	1	1	1
-61.25°	2	2	2	2	2	1	1	1	1	1	1
-62.5°	2	2	2	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	2	1	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	1	1	1	1	1
52.5°	2	2	2	2	2	2	2	2	1	1	1
51.25°	2	2	2	2	2	2	2	2	2	1	1
50°	2	2	2	2	2	2	2	2	2	2	1
48.75°	2	2	2	2	2	2	2	2	2	2	2
47.5°	3	2	2	2	2	2	2	2	2	2	2
46.25°	3	3	2	2	2	2	2	2	2	2	2
45°	3	3	3	2	2	2	2	2	2	2	2
43.75°	3	3	3	2	2	2	2	2	2	2	2
42.5°	3	3	3	3	2	2	2	2	2	2	2
41.25°	3	3	3	3	3	2	2	2	2	2	2
40°	4	3	3	3	3	2	2	2	2	2	2
38.75°	4	4	3	3	3	3	2	2	2	2	2
37.5°	4	4	4	3	3	3	3	2	2	2	2
36.25°	4	4	4	4	3	3	3	2	2	2	2
35°	4	4	4	4	4	3	3	3	2	2	2



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	4	4	4	4	4	3	3	3	2	2	2
32.5°	4	4	4	4	4	4	3	3	3	2	2
31.25°	4	4	4	4	4	4	3	3	3	2	2
30°	5	4	4	4	4	4	4	3	3	2	2
28.75°	5	5	4	4	4	4	4	3	3	3	2
27.5°	5	5	5	4	4	4	4	4	3	3	2
26.25°	5	5	5	4	4	4	4	4	3	3	2
25°	5	5	5	4	4	4	4	4	3	3	3
23.75°	5	5	5	5	4	4	4	4	3	3	3
22.5°	5	5	5	5	4	4	4	4	4	3	3
21.25°	5	5	5	5	4	4	4	4	4	3	3
20°	5	5	5	5	5	4	4	4	4	3	3
18.75°	6	5	5	5	5	4	4	4	4	3	3
17.5°	6	5	5	5	5	4	4	4	4	4	3
16.25°	6	6	5	5	5	4	4	4	4	4	3
15°	6	6	5	5	5	5	4	4	4	4	3
13.75°	7	6	5	5	5	5	4	4	4	4	3
12.5°	7	6	6	5	5	5	4	4	4	4	3
11.25°	7	6	6	5	5	5	4	4	4	4	3
10°	7	6	6	5	5	5	4	4	4	4	3
8.75°	7	7	6	5	5	5	4	4	4	4	4
7.5°	8	7	6	6	5	5	4	4	4	4	4
6.25°	8	7	6	6	5	5	5	4	4	4	4
5°	8	7	6	6	5	5	5	4	4	4	4
3.75°	8	7	6	6	5	5	5	4	4	4	4
2.5°	8	7	6	6	5	5	5	4	4	4	4
1.25°	8	7	6	6	5	5	5	4	4	4	4
0°	8	7	6	6	5	5	5	4	4	4	4
-1.25°	8	7	6	6	5	5	5	4	4	4	4
-2.5°	8	7	6	6	5	5	5	4	4	4	4
-3.75°	8	7	6	6	5	5	5	4	4	4	4
-5°	8	7	6	6	5	5	5	4	4	4	4
-6.25°	8	7	6	6	5	5	5	4	4	4	4
-7.5°	8	7	6	6	5	5	4	4	4	4	4
-8.75°	7	7	6	5	5	5	4	4	4	4	4
-10°	7	6	6	5	5	5	4	4	4	4	3
-11.25°	7	6	6	5	5	5	4	4	4	4	3
-12.5°	7	6	6	5	5	5	4	4	4	4	3
-13.75°	7	6	5	5	5	5	4	4	4	4	3
-15°	6	6	5	5	5	5	4	4	4	4	3
-16.25°	6	6	5	5	5	4	4	4	4	4	3
-17.5°	6	5	5	5	5	4	4	4	4	4	3
-18.75°	6	5	5	5	5	4	4	4	4	3	3
-20°	5	5	5	5	5	4	4	4	4	3	3
-21.25°	5	5	5	5	4	4	4	4	4	3	3





REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	5	5	5	5	4	4	4	4	4	3	3
-23.75°	5	5	5	5	4	4	4	4	3	3	3
-25°	5	5	5	4	4	4	4	4	3	3	3
-26.25°	5	5	5	4	4	4	4	4	3	3	2
-27.5°	5	5	5	4	4	4	4	4	3	3	2
-28.75°	5	5	4	4	4	4	4	3	3	3	2
-30°	5	4	4	4	4	4	4	3	3	2	2
-31.25°	4	4	4	4	4	4	3	3	3	2	2
-32.5°	4	4	4	4	4	4	3	3	3	2	2
-33.75°	4	4	4	4	4	3	3	3	2	2	2
-35°	4	4	4	4	4	3	3	3	2	2	2
-36.25°	4	4	4	4	3	3	3	2	2	2	2
-37.5°	4	4	4	3	3	3	3	2	2	2	2
-38.75°	4	4	3	3	3	3	2	2	2	2	2
-40°	4	3	3	3	3	2	2	2	2	2	2
-41.25°	3	3	3	3	3	2	2	2	2	2	2
-42.5°	3	3	3	3	2	2	2	2	2	2	2
-43.75°	3	3	3	2	2	2	2	2	2	2	2
-45°	3	3	3	2	2	2	2	2	2	2	2
-46.25°	3	3	2	2	2	2	2	2	2	2	2
-47.5°	3	2	2	2	2	2	2	2	2	2	2
-48.75°	2	2	2	2	2	2	2	2	2	2	2
-50°	2	2	2	2	2	2	2	2	2	2	1
-51.25°	2	2	2	2	2	2	2	2	2	1	1
-52.5°	2	2	2	2	2	2	2	2	1	1	1
-53.75°	2	2	2	2	2	2	1	1	1	1	1
-55°	2	2	2	2	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	0	0	0	0	0	0	0	0	0
73.75°	1	1	1	1	1	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	0	0	0
68.75°	1	1	1	1	1	1	1	1	1	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	0
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	2	1	1	1	1	1	1	1	1	1	1
45°	2	1	1	1	1	1	1	1	1	1	1
43.75°	2	2	1	1	1	1	1	1	1	1	1
42.5°	2	2	1	1	1	1	1	1	1	1	1
41.25°	2	2	2	1	1	1	1	1	1	1	1
40°	2	2	2	1	1	1	1	1	1	1	1
38.75°	2	2	2	2	1	1	1	1	1	1	1
37.5°	2	2	2	2	1	1	1	1	1	1	1
36.25°	2	2	2	2	1	1	1	1	1	1	1
35°	2	2	2	2	2	1	1	1	1	1	1



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	2	2	2	1	1	1	1	1	1
32.5°	2	2	2	2	2	1	1	1	1	1	1
31.25°	2	2	2	2	2	1	1	1	1	1	1
30°	2	2	2	2	2	2	1	1	1	1	1
28.75°	2	2	2	2	2	2	1	1	1	1	1
27.5°	2	2	2	2	2	2	1	1	1	1	1
26.25°	2	2	2	2	2	2	1	1	1	1	1
25°	2	2	2	2	2	2	2	1	1	1	1
23.75°	2	2	2	2	2	2	2	1	1	1	1
22.5°	2	2	2	2	2	2	2	1	1	1	1
21.25°	2	2	2	2	2	2	2	1	1	1	1
20°	2	2	2	2	2	2	2	1	1	1	1
18.75°	3	2	2	2	2	2	2	1	1	1	1
17.5°	3	2	2	2	2	2	2	1	1	1	1
16.25°	3	2	2	2	2	2	2	2	1	1	1
15°	3	2	2	2	2	2	2	2	1	1	1
13.75°	3	2	2	2	2	2	2	2	1	1	1
12.5°	3	2	2	2	2	2	2	2	1	1	1
11.25°	3	2	2	2	2	2	2	2	1	1	1
10°	3	3	2	2	2	2	2	2	1	1	1
8.75°	3	3	2	2	2	2	2	2	1	1	1
7.5°	3	3	2	2	2	2	2	2	1	1	1
6.25°	3	3	2	2	2	2	2	2	1	1	1
5°	3	3	2	2	2	2	2	2	1	1	1
3.75°	3	3	2	2	2	2	2	2	1	1	1
2.5°	3	3	2	2	2	2	2	2	1	1	1
1.25°	3	3	2	2	2	2	2	2	1	1	1
0°	3	3	2	2	2	2	2	2	1	1	1
-1.25°	3	3	2	2	2	2	2	2	1	1	1
-2.5°	3	3	2	2	2	2	2	2	1	1	1
-3.75°	3	3	2	2	2	2	2	2	1	1	1
-5°	3	3	2	2	2	2	2	2	1	1	1
-6.25°	3	3	2	2	2	2	2	2	1	1	1
-7.5°	3	3	2	2	2	2	2	2	1	1	1
-8.75°	3	3	2	2	2	2	2	2	1	1	1
-10°	3	3	2	2	2	2	2	2	1	1	1
-11.25°	3	2	2	2	2	2	2	2	1	1	1
-12.5°	3	2	2	2	2	2	2	2	1	1	1
-13.75°	3	2	2	2	2	2	2	2	1	1	1
-15°	3	2	2	2	2	2	2	2	1	1	1
-16.25°	3	2	2	2	2	2	2	2	1	1	1
-17.5°	3	2	2	2	2	2	2	1	1	1	1
-18.75°	3	2	2	2	2	2	2	1	1	1	1
-20°	2	2	2	2	2	2	2	1	1	1	1
-21.25°	2	2	2	2	2	2	2	1	1	1	1



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	2	2	2	2	1	1	1	1
-23.75°	2	2	2	2	2	2	2	1	1	1	1
-25°	2	2	2	2	2	2	2	1	1	1	1
-26.25°	2	2	2	2	2	2	1	1	1	1	1
-27.5°	2	2	2	2	2	2	1	1	1	1	1
-28.75°	2	2	2	2	2	2	1	1	1	1	1
-30°	2	2	2	2	2	2	1	1	1	1	1
-31.25°	2	2	2	2	2	1	1	1	1	1	1
-32.5°	2	2	2	2	2	1	1	1	1	1	1
-33.75°	2	2	2	2	2	1	1	1	1	1	1
-35°	2	2	2	2	2	1	1	1	1	1	1
-36.25°	2	2	2	2	1	1	1	1	1	1	1
-37.5°	2	2	2	2	1	1	1	1	1	1	1
-38.75°	2	2	2	2	1	1	1	1	1	1	1
-40°	2	2	2	1	1	1	1	1	1	1	1
-41.25°	2	2	2	1	1	1	1	1	1	1	1
-42.5°	2	2	1	1	1	1	1	1	1	1	1
-43.75°	2	2	1	1	1	1	1	1	1	1	1
-45°	2	1	1	1	1	1	1	1	1	1	1
-46.25°	2	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	0
-68.75°	1	1	1	1	1	1	1	1	1	0	0
-70°	1	1	1	1	1	1	1	1	0	0	0
-71.25°	1	1	1	1	1	1	1	0	0	0	0
-72.5°	1	1	1	1	1	1	0	0	0	0	0
-73.75°	1	1	1	1	1	0	0	0	0	0	0
-75°	1	1	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	1	0	0	0	0	0	0	0	0	0	0
62.5°	1	0	0	0	0	0	0	0	0	0	0
61.25°	1	1	0	0	0	0	0	0	0	0	0
60°	1	1	0	0	0	0	0	0	0	0	0
58.75°	1	1	1	0	0	0	0	0	0	0	0
57.5°	1	1	1	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	0	0	0	0	0	0	0
52.5°	1	1	1	1	0	0	0	0	0	0	0
51.25°	1	1	1	1	0	0	0	0	0	0	0
50°	1	1	1	1	1	0	0	0	0	0	0
48.75°	1	1	1	1	1	0	0	0	0	0	0
47.5°	1	1	1	1	1	0	0	0	0	0	0
46.25°	1	1	1	1	1	0	0	0	0	0	0
45°	1	1	1	1	1	0	0	0	0	0	0
43.75°	1	1	1	1	1	0	0	0	0	0	0
42.5°	1	1	1	1	1	1	0	0	0	0	0
41.25°	1	1	1	1	1	1	0	0	0	0	0
40°	1	1	1	1	1	1	0	0	0	0	0
38.75°	1	1	1	1	1	1	0	0	0	0	0
37.5°	1	1	1	1	1	1	0	0	0	0	0
36.25°	1	1	1	1	1	1	0	0	0	0	0
35°	1	1	1	1	1	1	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	1	1	0	0	0	0	0
32.5°	1	1	1	1	1	1	0	0	0	0	0
31.25°	1	1	1	1	1	1	1	0	0	0	0
30°	1	1	1	1	1	1	1	0	0	0	0
28.75°	1	1	1	1	1	1	1	0	0	0	0
27.5°	1	1	1	1	1	1	1	0	0	0	0
26.25°	1	1	1	1	1	1	1	0	0	0	0
25°	1	1	1	1	1	1	1	0	0	0	0
23.75°	1	1	1	1	1	1	1	0	0	0	0
22.5°	1	1	1	1	1	1	1	0	0	0	0
21.25°	1	1	1	1	1	1	1	0	0	0	0
20°	1	1	1	1	1	1	1	0	0	0	0
18.75°	1	1	1	1	1	1	1	0	0	0	0
17.5°	1	1	1	1	1	1	1	0	0	0	0
16.25°	1	1	1	1	1	1	1	0	0	0	0
15°	1	1	1	1	1	1	1	0	0	0	0
13.75°	1	1	1	1	1	1	1	0	0	0	0
12.5°	1	1	1	1	1	1	1	0	0	0	0
11.25°	1	1	1	1	1	1	1	0	0	0	0
10°	1	1	1	1	1	1	1	0	0	0	0
8.75°	1	1	1	1	1	1	1	0	0	0	0
7.5°	1	1	1	1	1	1	1	0	0	0	0
6.25°	1	1	1	1	1	1	1	0	0	0	0
5°	1	1	1	1	1	1	1	0	0	0	0
3.75°	1	1	1	1	1	1	1	0	0	0	0
2.5°	1	1	1	1	1	1	1	0	0	0	0
1.25°	1	1	1	1	1	1	1	0	0	0	0
0°	1	1	1	1	1	1	1	0	0	0	0
-1.25°	1	1	1	1	1	1	1	0	0	0	0
-2.5°	1	1	1	1	1	1	1	0	0	0	0
-3.75°	1	1	1	1	1	1	1	0	0	0	0
-5°	1	1	1	1	1	1	1	0	0	0	0
-6.25°	1	1	1	1	1	1	1	0	0	0	0
-7.5°	1	1	1	1	1	1	1	0	0	0	0
-8.75°	1	1	1	1	1	1	1	0	0	0	0
-10°	1	1	1	1	1	1	1	0	0	0	0
-11.25°	1	1	1	1	1	1	1	0	0	0	0
-12.5°	1	1	1	1	1	1	1	0	0	0	0
-13.75°	1	1	1	1	1	1	1	0	0	0	0
-15°	1	1	1	1	1	1	1	0	0	0	0
-16.25°	1	1	1	1	1	1	1	0	0	0	0
-17.5°	1	1	1	1	1	1	1	0	0	0	0
-18.75°	1	1	1	1	1	1	1	0	0	0	0
-20°	1	1	1	1	1	1	1	0	0	0	0
-21.25°	1	1	1	1	1	1	1	0	0	0	0





REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	1	1	0	0	0	0
-23.75°	1	1	1	1	1	1	1	0	0	0	0
-25°	1	1	1	1	1	1	1	0	0	0	0
-26.25°	1	1	1	1	1	1	1	0	0	0	0
-27.5°	1	1	1	1	1	1	1	0	0	0	0
-28.75°	1	1	1	1	1	1	1	0	0	0	0
-30°	1	1	1	1	1	1	1	0	0	0	0
-31.25°	1	1	1	1	1	1	1	0	0	0	0
-32.5°	1	1	1	1	1	1	0	0	0	0	0
-33.75°	1	1	1	1	1	1	0	0	0	0	0
-35°	1	1	1	1	1	1	0	0	0	0	0
-36.25°	1	1	1	1	1	1	0	0	0	0	0
-37.5°	1	1	1	1	1	1	0	0	0	0	0
-38.75°	1	1	1	1	1	1	0	0	0	0	0
-40°	1	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	1	0	0	0	0	0
-43.75°	1	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	1	1	0	0	0	0	0	0
-46.25°	1	1	1	1	1	0	0	0	0	0	0
-47.5°	1	1	1	1	1	0	0	0	0	0	0
-48.75°	1	1	1	1	1	0	0	0	0	0	0
-50°	1	1	1	1	1	0	0	0	0	0	0
-51.25°	1	1	1	1	0	0	0	0	0	0	0
-52.5°	1	1	1	1	0	0	0	0	0	0	0
-53.75°	1	1	1	1	0	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	1	0	0	0	0	0	0	0	0
-58.75°	1	1	1	0	0	0	0	0	0	0	0
-60°	1	1	0	0	0	0	0	0	0	0	0
-61.25°	1	1	0	0	0	0	0	0	0	0	0
-62.5°	1	0	0	0	0	0	0	0	0	0	0
-63.75°	1	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P247033 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED2736-12-CS-LSL

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)