

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED3010-12-CS-LSL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-37)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3010-12-CS-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER, LINEAR SPREAD LENS
Light Source: (1) SORAA 3000K 95 CRI 10° NSP LED
SM16-07-10D-930-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 2V
Luminaire Lumens:	223.7 lumens	Max Intensity:	1063.8 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	29.8 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	51.1°H x 11.9°V	Field Angle (10%):	61.9°H x 24.8°V
Beam Lumens:	103.8 lumens	Field Lumens:	170.3 lumens
Beam Efficiency:	46.4%	Field Efficiency:	76.1%
Input Watts (W):	7.5		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)


CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

Iso-Candela Plot




REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

Lumen Table




REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

Luminous Intensity Polar Plot



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

Luminous Intensity Plot



Beam:
H Angle: 51.1°
V Angle: 11.9°
Lumens: 103.8
Efficiency: 46.4%

Field:
H Angle: 61.9°
V Angle: 24.8°
Lumens: 170.3
Efficiency: 76.1%

Spill:
Lumens: 53.4
Efficiency: 23.9%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	1
26.25°	0	0	0	0	0	0	0	0	0	0	1
25°	0	0	0	0	0	0	0	0	0	0	1
23.75°	0	0	0	0	0	0	0	0	0	0	1
22.5°	0	0	0	0	0	0	0	0	0	0	1
21.25°	0	0	0	0	0	0	0	0	0	0	1
20°	0	0	0	0	0	0	0	0	0	0	1
18.75°	0	0	0	0	0	0	0	0	0	0	1
17.5°	0	0	0	0	0	0	0	0	0	0	1
16.25°	0	0	0	0	0	0	0	0	0	0	1
15°	0	0	0	0	0	0	0	0	0	0	1
13.75°	0	0	0	0	0	0	0	0	0	0	1
12.5°	0	0	0	0	0	0	0	0	0	0	1
11.25°	0	0	0	0	0	0	0	0	0	0	1
10°	0	0	0	0	0	0	0	0	0	0	1
8.75°	0	0	0	0	0	0	0	0	0	0	1
7.5°	0	0	0	0	0	0	0	0	0	0	1
6.25°	0	0	0	0	0	0	0	0	0	0	1
5°	0	0	0	0	0	0	0	0	0	0	1
3.75°	0	0	0	0	0	0	0	0	0	0	1
2.5°	0	0	0	0	0	0	0	0	0	0	1
1.25°	0	0	0	0	0	0	0	0	0	0	1
0°	0	0	0	0	0	0	0	0	0	0	1
-1.25°	0	0	0	0	0	0	0	0	0	0	1
-2.5°	0	0	0	0	0	0	0	0	0	0	1
-3.75°	0	0	0	0	0	0	0	0	0	0	1
-5°	0	0	0	0	0	0	0	0	0	0	1
-6.25°	0	0	0	0	0	0	0	0	0	0	1
-7.5°	0	0	0	0	0	0	0	0	0	0	1
-8.75°	0	0	0	0	0	0	0	0	0	0	1
-10°	0	0	0	0	0	0	0	0	0	0	1
-11.25°	0	0	0	0	0	0	0	0	0	0	1
-12.5°	0	0	0	0	0	0	0	0	0	0	1
-13.75°	0	0	0	0	0	0	0	0	0	0	1
-15°	0	0	0	0	0	0	0	0	0	0	1
-16.25°	0	0	0	0	0	0	0	0	0	0	1
-17.5°	0	0	0	0	0	0	0	0	0	0	1
-18.75°	0	0	0	0	0	0	0	0	0	0	1
-20°	0	0	0	0	0	0	0	0	0	0	1
-21.25°	0	0	0	0	0	0	0	0	0	0	1



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	1
-23.75°	0	0	0	0	0	0	0	0	0	0	1
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	1
67.5°	0	0	0	0	0	0	0	0	0	1	1
66.25°	0	0	0	0	0	0	0	0	1	1	1
65°	0	0	0	0	0	0	0	1	1	1	1
63.75°	0	0	0	0	0	0	1	1	1	1	1
62.5°	0	0	0	0	0	0	1	1	1	1	1
61.25°	0	0	0	0	0	1	1	1	1	1	1
60°	0	0	0	0	0	1	1	1	1	1	1
58.75°	0	0	0	0	1	1	1	1	1	1	1
57.5°	0	0	0	0	1	1	1	1	1	1	1
56.25°	0	0	0	0	1	1	1	1	1	1	1
55°	0	0	0	1	1	1	1	1	1	1	1
53.75°	0	0	0	1	1	1	1	1	1	1	1
52.5°	0	0	0	1	1	1	1	1	1	1	1
51.25°	0	0	1	1	1	1	1	1	1	1	1
50°	0	0	1	1	1	1	1	1	1	1	1
48.75°	0	0	1	1	1	1	1	1	1	1	1
47.5°	0	0	1	1	1	1	1	1	1	1	1
46.25°	0	0	1	1	1	1	1	1	1	1	1
45°	0	1	1	1	1	1	1	1	1	1	1
43.75°	0	1	1	1	1	1	1	1	1	1	1
42.5°	0	1	1	1	1	1	1	1	1	1	1
41.25°	0	1	1	1	1	1	1	1	1	1	1
40°	0	1	1	1	1	1	1	1	1	1	1
38.75°	0	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	1	1	1	1	1	1	1	1	1	1	2
31.25°	1	1	1	1	1	1	1	1	1	1	2
30°	1	1	1	1	1	1	1	1	1	1	2
28.75°	1	1	1	1	1	1	1	1	1	2	2
27.5°	1	1	1	1	1	1	1	1	1	2	2
26.25°	1	1	1	1	1	1	1	1	1	2	2
25°	1	1	1	1	1	1	1	1	1	2	2
23.75°	1	1	1	1	1	1	1	1	1	2	2
22.5°	1	1	1	1	1	1	1	1	2	2	2
21.25°	1	1	1	1	1	1	1	1	2	2	2
20°	1	1	1	1	1	1	1	1	2	2	2
18.75°	1	1	1	1	1	1	1	1	2	2	2
17.5°	1	1	1	1	1	1	1	1	2	2	2
16.25°	1	1	1	1	1	1	1	1	2	2	2
15°	1	1	1	1	1	1	1	2	2	2	2
13.75°	1	1	1	1	1	1	1	2	2	2	2
12.5°	1	1	1	1	1	1	1	2	2	2	2
11.25°	1	1	1	1	1	1	1	2	2	2	2
10°	1	1	1	1	1	1	1	2	2	2	2
8.75°	1	1	1	1	1	1	1	2	2	2	2
7.5°	1	1	1	1	1	1	1	2	2	2	2
6.25°	1	1	1	1	1	1	1	2	2	2	2
5°	1	1	1	1	1	1	1	2	2	2	2
3.75°	1	1	1	1	1	1	1	2	2	2	2
2.5°	1	1	1	1	1	1	1	2	2	2	2
1.25°	1	1	1	1	1	1	1	2	2	2	2
0°	1	1	1	1	1	1	1	2	2	2	2
-1.25°	1	1	1	1	1	1	1	2	2	2	2
-2.5°	1	1	1	1	1	1	1	2	2	2	2
-3.75°	1	1	1	1	1	1	1	2	2	2	2
-5°	1	1	1	1	1	1	1	2	2	2	2
-6.25°	1	1	1	1	1	1	1	2	2	2	2
-7.5°	1	1	1	1	1	1	1	2	2	2	2
-8.75°	1	1	1	1	1	1	1	2	2	2	2
-10°	1	1	1	1	1	1	1	2	2	2	2
-11.25°	1	1	1	1	1	1	1	2	2	2	2
-12.5°	1	1	1	1	1	1	1	2	2	2	2
-13.75°	1	1	1	1	1	1	1	2	2	2	2
-15°	1	1	1	1	1	1	1	2	2	2	2
-16.25°	1	1	1	1	1	1	1	1	2	2	2
-17.5°	1	1	1	1	1	1	1	1	2	2	2
-18.75°	1	1	1	1	1	1	1	1	2	2	2
-20°	1	1	1	1	1	1	1	1	2	2	2
-21.25°	1	1	1	1	1	1	1	1	2	2	2



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	2	2	2
-23.75°	1	1	1	1	1	1	1	1	1	2	2
-25°	1	1	1	1	1	1	1	1	1	2	2
-26.25°	1	1	1	1	1	1	1	1	1	2	2
-27.5°	1	1	1	1	1	1	1	1	1	2	2
-28.75°	1	1	1	1	1	1	1	1	1	2	2
-30°	1	1	1	1	1	1	1	1	1	1	2
-31.25°	1	1	1	1	1	1	1	1	1	1	2
-32.5°	1	1	1	1	1	1	1	1	1	1	2
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	0	1	1	1	1	1	1	1	1	1	1
-36.25°	0	1	1	1	1	1	1	1	1	1	1
-37.5°	0	1	1	1	1	1	1	1	1	1	1
-38.75°	0	1	1	1	1	1	1	1	1	1	1
-40°	0	1	1	1	1	1	1	1	1	1	1
-41.25°	0	0	1	1	1	1	1	1	1	1	1
-42.5°	0	0	1	1	1	1	1	1	1	1	1
-43.75°	0	0	1	1	1	1	1	1	1	1	1
-45°	0	0	1	1	1	1	1	1	1	1	1
-46.25°	0	0	0	1	1	1	1	1	1	1	1
-47.5°	0	0	0	1	1	1	1	1	1	1	1
-48.75°	0	0	0	1	1	1	1	1	1	1	1
-50°	0	0	0	0	1	1	1	1	1	1	1
-51.25°	0	0	0	0	1	1	1	1	1	1	1
-52.5°	0	0	0	0	0	1	1	1	1	1	1
-53.75°	0	0	0	0	0	1	1	1	1	1	1
-55°	0	0	0	0	0	0	1	1	1	1	1
-56.25°	0	0	0	0	0	0	1	1	1	1	1
-57.5°	0	0	0	0	0	0	0	1	1	1	1
-58.75°	0	0	0	0	0	0	0	1	1	1	1
-60°	0	0	0	0	0	0	0	0	1	1	1
-61.25°	0	0	0	0	0	0	0	0	0	1	1
-62.5°	0	0	0	0	0	0	0	0	0	0	1
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	1	1	1
73.75°	0	0	0	0	0	1	1	1	1	1	1
72.5°	0	0	0	1	1	1	1	1	1	1	1
71.25°	0	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	2	2
52.5°	1	1	1	1	1	1	1	1	2	2	2
51.25°	1	1	1	1	1	1	1	2	2	2	2
50°	1	1	1	1	1	1	1	2	2	2	2
48.75°	1	1	1	1	1	1	2	2	2	2	2
47.5°	1	1	1	1	1	2	2	2	2	2	2
46.25°	1	1	1	1	2	2	2	2	2	2	2
45°	1	1	1	1	2	2	2	2	2	2	2
43.75°	1	1	1	2	2	2	2	2	2	2	2
42.5°	1	1	1	2	2	2	2	2	2	2	3
41.25°	1	1	2	2	2	2	2	2	2	3	3
40°	1	1	2	2	2	2	2	2	3	3	3
38.75°	1	2	2	2	2	2	2	3	3	3	4
37.5°	1	2	2	2	2	2	3	3	3	3	4
36.25°	2	2	2	2	2	2	3	3	3	4	4
35°	2	2	2	2	2	3	3	3	3	4	5



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	2	3	3	3	4	4	5
32.5°	2	2	2	2	3	3	3	3	4	5	6
31.25°	2	2	2	2	3	3	3	4	4	5	6
30°	2	2	2	2	3	3	3	4	5	6	6
28.75°	2	2	2	3	3	3	4	4	5	6	7
27.5°	2	2	2	3	3	3	4	5	5	6	7
26.25°	2	2	2	3	3	3	4	5	6	7	7
25°	2	2	3	3	3	4	4	5	6	7	8
23.75°	2	2	3	3	3	4	5	6	6	7	8
22.5°	2	2	3	3	3	4	5	6	7	8	8
21.25°	2	2	3	3	4	4	5	6	7	8	9
20°	2	2	3	3	4	5	5	6	7	8	9
18.75°	2	3	3	3	4	5	6	7	8	8	9
17.5°	2	3	3	3	4	5	6	7	8	9	9
16.25°	2	3	3	3	4	5	6	7	8	9	10
15°	2	3	3	4	4	5	6	7	8	9	10
13.75°	2	3	3	4	5	5	7	8	8	9	10
12.5°	2	3	3	4	5	6	7	8	9	10	10
11.25°	2	3	3	4	5	6	7	8	9	10	11
10°	3	3	3	4	5	6	7	8	9	10	11
8.75°	3	3	3	4	5	6	7	8	9	10	11
7.5°	3	3	3	4	5	6	7	8	9	10	11
6.25°	3	3	3	4	5	6	8	9	9	10	11
5°	3	3	3	4	5	6	8	9	10	10	11
3.75°	3	3	3	4	5	7	8	9	10	10	11
2.5°	3	3	3	4	5	7	8	9	10	11	11
1.25°	3	3	3	4	5	7	8	9	10	11	11
0°	3	3	4	4	5	7	8	9	10	11	11
-1.25°	3	3	3	4	5	7	8	9	10	11	11
-2.5°	3	3	3	4	5	7	8	9	10	11	11
-3.75°	3	3	3	4	5	7	8	9	10	10	11
-5°	3	3	3	4	5	6	8	9	10	10	11
-6.25°	3	3	3	4	5	6	8	9	9	10	11
-7.5°	2	3	3	4	5	6	7	8	9	10	11
-8.75°	2	3	3	4	5	6	7	8	9	10	11
-10°	2	3	3	4	5	6	7	8	9	10	11
-11.25°	2	3	3	4	5	6	7	8	9	10	11
-12.5°	2	3	3	4	5	6	7	8	9	10	10
-13.75°	2	3	3	4	5	5	7	8	8	9	10
-15°	2	2	3	4	4	5	6	7	8	9	10
-16.25°	2	2	3	3	4	5	6	7	8	9	10
-17.5°	2	2	3	3	4	5	6	7	8	9	9
-18.75°	2	2	3	3	4	5	6	7	8	8	9
-20°	2	2	3	3	4	5	5	6	7	8	9
-21.25°	2	2	2	3	4	4	5	6	7	8	9



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	2	3	3	4	5	6	7	8	8
-23.75°	2	2	2	3	3	4	5	6	6	7	8
-25°	2	2	2	2	3	4	4	5	6	7	8
-26.25°	2	2	2	2	3	3	4	5	6	7	7
-27.5°	2	2	2	2	3	3	4	5	5	6	7
-28.75°	2	2	2	2	2	3	4	4	5	6	7
-30°	2	2	2	2	2	3	3	4	5	6	6
-31.25°	2	2	2	2	2	2	3	4	4	5	6
-32.5°	2	2	2	2	2	2	3	3	4	5	5
-33.75°	2	2	2	2	2	2	2	3	4	4	5
-35°	2	2	2	2	2	2	2	3	3	4	5
-36.25°	2	2	2	2	2	2	2	2	3	4	4
-37.5°	1	2	2	2	2	2	2	2	3	3	4
-38.75°	1	2	2	2	2	2	2	2	2	3	4
-40°	1	1	2	2	2	2	2	2	2	3	3
-41.25°	1	1	2	2	2	2	2	2	2	2	3
-42.5°	1	1	1	2	2	2	2	2	2	2	2
-43.75°	1	1	1	2	2	2	2	2	2	2	2
-45°	1	1	1	1	2	2	2	2	2	2	2
-46.25°	1	1	1	1	1	2	2	2	2	2	2
-47.5°	1	1	1	1	1	2	2	2	2	2	2
-48.75°	1	1	1	1	1	1	2	2	2	2	2
-50°	1	1	1	1	1	1	1	1	2	2	2
-51.25°	1	1	1	1	1	1	1	1	1	2	2
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	1	1	1	1	1	1	1	1	1
-67.5°	0	0	0	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	1	1	1	1	1	1
-70°	0	0	0	0	0	0	0	1	1	1	1
-71.25°	0	0	0	0	0	0	0	0	0	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	2	2	2
60°	1	1	1	1	1	1	2	2	2	2	2
58.75°	1	1	1	1	2	2	2	2	2	2	2
57.5°	1	1	2	2	2	2	2	2	2	2	2
56.25°	1	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	2	2	2	2	2	2	2	2	2	3	3
51.25°	2	2	2	2	2	2	2	3	3	3	4
50°	2	2	2	2	2	2	3	3	4	4	4
48.75°	2	2	2	2	3	3	3	4	4	5	5
47.5°	2	2	2	3	3	3	4	4	5	5	5
46.25°	2	2	3	3	3	4	4	5	5	6	6
45°	2	3	3	4	4	5	5	5	6	6	6
43.75°	3	3	3	4	5	5	5	6	6	6	7
42.5°	3	3	4	5	5	6	6	6	6	7	8
41.25°	3	4	4	5	6	6	6	7	7	8	9
40°	4	4	5	5	6	6	7	7	8	9	9
38.75°	4	5	5	6	6	7	7	8	9	9	10
37.5°	5	5	6	6	7	7	8	9	9	10	10
36.25°	5	6	6	7	7	8	9	9	10	10	10
35°	5	6	7	7	8	9	9	10	10	10	11



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	6	6	7	8	8	9	10	10	10	11	11
32.5°	6	7	7	8	9	9	10	10	11	11	12
31.25°	7	7	8	9	9	10	10	11	11	12	12
30°	7	8	8	9	10	10	11	11	11	12	12
28.75°	7	8	9	9	10	11	11	11	12	12	13
27.5°	8	8	9	10	10	11	11	12	12	13	13
26.25°	8	9	9	10	11	11	11	12	13	13	14
25°	8	9	10	10	11	11	12	12	13	14	14
23.75°	9	9	10	11	11	11	12	13	13	14	15
22.5°	9	10	10	11	11	12	13	13	14	15	15
21.25°	9	10	11	11	12	12	13	14	14	15	16
20°	10	10	11	12	12	13	13	14	15	15	16
18.75°	10	11	11	12	12	13	14	15	15	16	17
17.5°	10	11	12	12	13	14	14	15	16	16	17
16.25°	10	11	12	13	13	14	15	15	16	17	18
15°	11	11	12	13	14	14	15	16	17	17	19
13.75°	11	12	12	13	14	15	16	16	17	18	19
12.5°	11	12	13	14	14	15	16	17	17	19	20
11.25°	11	12	13	14	15	15	16	17	18	19	21
10°	12	12	13	14	15	16	17	17	18	20	21
8.75°	12	13	14	14	15	16	17	18	19	20	22
7.5°	12	13	14	15	16	16	17	18	19	21	23
6.25°	12	13	14	15	16	17	17	18	20	22	24
5°	12	13	14	15	16	17	18	19	20	22	25
3.75°	12	14	15	15	16	17	18	19	21	23	26
2.5°	13	14	15	16	17	17	18	19	21	23	26
1.25°	13	14	15	16	17	18	18	19	21	24	27
0°	13	14	15	16	17	18	19	19	22	24	27
-1.25°	13	14	15	16	17	18	18	19	21	24	27
-2.5°	13	14	15	16	17	17	18	19	21	23	26
-3.75°	13	14	15	16	16	17	18	19	21	23	26
-5°	12	14	15	15	16	17	18	19	20	22	25
-6.25°	12	13	14	15	16	17	18	19	20	22	24
-7.5°	12	13	14	15	16	16	17	18	20	21	23
-8.75°	12	13	14	15	16	16	17	18	19	21	22
-10°	12	13	14	15	15	16	17	18	19	20	21
-11.25°	11	12	14	14	15	16	16	17	18	20	21
-12.5°	11	12	13	14	15	15	16	17	18	19	20
-13.75°	11	12	13	14	15	15	16	16	17	19	20
-15°	11	12	13	13	14	15	15	16	17	18	19
-16.25°	10	11	12	13	14	15	15	16	16	18	18
-17.5°	10	11	12	13	14	14	15	15	16	17	18
-18.75°	10	11	12	12	13	14	15	15	15	16	17
-20°	10	10	11	12	13	14	14	15	15	16	17
-21.25°	9	10	11	12	12	13	14	14	15	15	16



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	9	10	10	11	12	13	13	14	14	15	15
-23.75°	9	9	10	11	12	12	13	14	14	14	15
-25°	8	9	10	10	11	12	13	13	14	14	15
-26.25°	8	9	9	10	11	11	12	13	13	14	14
-27.5°	8	8	9	10	10	11	12	12	13	13	14
-28.75°	7	8	9	9	10	11	11	12	12	13	13
-30°	7	8	8	9	10	10	11	11	12	12	13
-31.25°	7	7	8	8	9	10	10	11	12	12	12
-32.5°	6	7	7	8	9	9	10	10	11	12	12
-33.75°	6	6	7	8	8	9	9	10	10	11	12
-35°	5	6	6	7	8	8	9	9	10	10	11
-36.25°	5	5	6	7	7	8	8	9	9	10	10
-37.5°	4	5	6	6	7	7	8	8	9	9	10
-38.75°	4	5	5	6	6	7	7	8	8	9	9
-40°	4	4	5	5	6	6	7	7	8	8	9
-41.25°	3	4	4	5	5	6	6	7	7	8	8
-42.5°	3	3	4	4	5	5	6	6	6	7	7
-43.75°	2	3	3	4	4	5	5	5	6	6	7
-45°	2	3	3	4	4	4	4	5	5	6	6
-46.25°	2	2	3	3	3	4	4	4	5	5	5
-47.5°	2	2	2	3	3	3	4	4	4	4	5
-48.75°	2	2	2	2	2	3	3	4	4	4	4
-50°	2	2	2	2	2	2	3	3	4	4	4
-51.25°	2	2	2	2	2	2	2	3	3	3	4
-52.5°	2	2	2	2	2	2	2	2	2	3	3
-53.75°	1	1	2	2	2	2	2	2	2	2	2
-55°	1	1	1	2	2	2	2	2	2	2	2
-56.25°	1	1	1	1	1	2	2	2	2	2	2
-57.5°	1	1	1	1	1	1	1	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	1	2	2
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	2
62.5°	1	1	1	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	3
57.5°	2	2	2	2	2	2	2	3	3	3	3
56.25°	2	2	2	2	3	3	3	3	4	4	4
55°	2	2	3	3	3	4	4	4	4	4	4
53.75°	3	3	3	4	4	4	4	5	5	5	5
52.5°	3	4	4	4	5	5	5	5	5	5	6
51.25°	4	4	5	5	5	5	6	6	6	6	6
50°	5	5	5	5	6	6	6	6	7	7	7
48.75°	5	5	6	6	6	6	7	7	7	7	8
47.5°	6	6	6	6	7	7	8	8	8	8	8
46.25°	6	6	7	7	8	8	8	8	9	9	9
45°	7	7	8	8	9	9	9	9	9	9	10
43.75°	8	8	9	9	9	9	9	10	10	10	10
42.5°	9	9	9	9	9	10	10	10	10	11	11
41.25°	9	9	10	10	10	10	11	11	11	11	11
40°	9	10	10	10	11	11	11	11	11	11	11
38.75°	10	10	11	11	11	11	12	12	12	12	12
37.5°	10	11	11	12	12	12	12	12	12	12	13
36.25°	11	11	12	12	12	12	12	13	13	13	13
35°	11	12	12	12	12	13	13	13	13	14	14



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	12	12	12	13	13	13	13	14	14	14	15
32.5°	12	12	13	13	13	13	14	14	15	15	15
31.25°	12	13	13	13	14	14	15	15	15	16	16
30°	13	13	14	14	14	15	15	16	16	16	17
28.75°	13	14	14	15	15	16	16	16	17	17	18
27.5°	14	14	15	15	16	16	17	17	18	18	18
26.25°	14	15	15	16	16	17	18	18	18	19	19
25°	15	15	16	17	17	18	18	19	19	20	20
23.75°	15	16	17	17	18	19	19	20	20	21	21
22.5°	16	16	17	18	19	19	20	21	22	22	23
21.25°	16	17	18	19	20	20	21	22	23	25	25
20°	17	18	19	20	20	22	23	24	26	27	28
18.75°	18	19	19	20	21	23	24	26	28	30	33
17.5°	18	19	20	21	23	25	27	29	32	35	38
16.25°	19	20	21	22	24	26	29	32	36	41	44
15°	20	21	22	24	26	29	32	36	42	47	52
13.75°	21	22	23	26	28	32	36	41	48	54	62
12.5°	21	23	25	29	32	37	39	47	54	63	72
11.25°	22	24	28	32	39	46	54	60	62	74	84
10°	23	25	31	36	47	58	74	87	98	101	101
8.75°	24	28	34	42	57	71	98	119	145	161	173
7.5°	25	30	38	50	68	91	126	160	200	232	260
6.25°	27	33	41	58	80	114	157	207	262	311	355
5°	28	35	45	67	92	138	190	257	327	394	456
3.75°	28	38	48	75	104	162	224	309	396	480	560
2.5°	29	40	52	83	116	186	257	361	464	567	665
1.25°	30	43	55	91	127	208	289	410	531	651	769
0°	31	44	58	97	137	228	318	456	594	731	869
-1.25°	30	43	55	91	127	208	290	412	533	654	773
-2.5°	29	40	52	84	116	186	258	363	467	572	672
-3.75°	28	38	48	75	104	163	225	312	400	487	570
-5°	28	35	45	67	92	139	192	261	333	403	468
-6.25°	27	33	41	58	80	115	160	211	268	320	370
-7.5°	25	30	38	50	68	92	129	164	207	242	276
-8.75°	24	28	34	42	58	72	101	123	153	172	190
-10°	23	25	31	36	48	58	76	91	105	112	117
-11.25°	22	24	28	32	39	47	55	64	68	83	95
-12.5°	21	23	25	29	32	38	40	50	58	70	81
-13.75°	21	22	23	26	28	32	36	43	51	59	68
-15°	20	21	22	24	26	29	33	36	44	50	57
-16.25°	19	20	21	22	24	27	30	33	37	42	47
-17.5°	19	19	20	21	23	25	27	30	32	36	40
-18.75°	18	19	19	20	21	23	25	27	29	31	34
-20°	18	18	19	20	20	22	23	24	26	28	29
-21.25°	17	18	18	19	20	20	22	23	24	25	26



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	16	17	18	18	19	19	20	21	22	23	24
-23.75°	16	16	17	17	18	19	19	20	21	21	22
-25°	15	16	16	17	17	18	18	19	19	20	21
-26.25°	15	15	16	16	17	17	18	18	18	19	19
-27.5°	14	15	15	16	16	16	17	17	18	18	18
-28.75°	14	14	15	15	15	16	16	16	17	17	18
-30°	13	14	14	15	15	15	15	16	16	17	17
-31.25°	13	13	14	14	14	15	15	15	16	16	16
-32.5°	12	13	13	13	14	14	14	15	15	15	16
-33.75°	12	12	13	13	13	14	14	14	14	15	15
-35°	11	12	12	12	13	13	13	14	14	14	14
-36.25°	11	11	12	12	12	12	13	13	13	14	14
-37.5°	10	11	11	12	12	12	12	12	13	13	13
-38.75°	10	10	11	11	11	11	12	12	12	12	13
-40°	9	10	10	10	11	11	11	11	12	12	12
-41.25°	8	9	9	10	10	10	11	11	11	11	11
-42.5°	8	8	9	9	9	10	10	10	10	11	11
-43.75°	7	8	8	8	9	9	9	9	10	10	10
-45°	6	7	7	8	8	8	8	9	9	9	9
-46.25°	6	6	7	7	7	8	8	8	8	8	8
-47.5°	5	6	6	6	7	7	7	7	8	8	8
-48.75°	5	5	5	6	6	6	6	7	7	7	7
-50°	4	4	5	5	5	5	6	6	6	6	7
-51.25°	4	4	4	4	5	5	5	5	5	6	6
-52.5°	3	4	4	4	4	4	4	5	5	5	5
-53.75°	3	3	3	3	4	4	4	4	4	5	5
-55°	2	2	3	3	3	3	3	4	4	4	4
-56.25°	2	2	2	2	2	3	3	3	3	3	3
-57.5°	2	2	2	2	2	2	2	2	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	4
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	4	4	4	4	4	4	4	5	5	5	5
55°	4	5	5	5	5	5	5	5	5	5	5
53.75°	5	5	6	6	6	6	6	6	6	6	6
52.5°	6	6	6	6	6	6	6	6	6	6	6
51.25°	7	7	7	7	7	7	7	7	7	7	7
50°	7	7	7	7	7	8	8	8	8	8	8
48.75°	8	8	8	8	8	8	8	8	8	8	8
47.5°	8	9	9	9	9	9	9	9	9	9	9
46.25°	9	9	9	9	9	9	10	10	10	10	10
45°	10	10	10	10	10	10	10	10	10	10	10
43.75°	10	10	10	10	10	10	10	10	10	11	11
42.5°	11	11	11	11	11	11	11	11	11	11	11
41.25°	11	11	11	11	12	12	12	12	12	12	12
40°	12	12	12	12	12	12	12	12	13	13	13
38.75°	12	12	13	13	13	13	13	13	13	13	13
37.5°	13	13	13	13	13	13	14	14	14	14	14
36.25°	13	14	14	14	14	14	14	15	15	15	15
35°	14	14	15	15	15	15	15	15	15	16	16



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	15	15	15	16	16	16	16	16	16	16	16
32.5°	16	16	16	16	17	17	17	17	17	17	17
31.25°	16	17	17	17	17	18	18	18	18	18	18
30°	17	18	18	18	18	19	19	19	19	19	19
28.75°	18	18	19	19	19	19	20	20	20	20	20
27.5°	19	19	19	20	20	21	21	21	21	21	22
26.25°	20	20	21	21	21	22	22	22	22	22	23
25°	20	21	22	22	23	24	24	24	24	24	25
23.75°	22	23	23	24	25	26	26	27	27	27	27
22.5°	23	24	25	26	27	28	29	29	29	30	30
21.25°	26	26	28	29	30	31	32	33	34	34	34
20°	30	30	30	32	33	34	36	37	38	39	39
18.75°	35	36	36	35	37	39	41	42	44	45	45
17.5°	40	43	43	42	42	44	46	49	50	51	53
16.25°	48	51	53	54	51	50	53	55	58	60	62
15°	57	62	68	70	68	62	60	63	66	69	71
13.75°	68	78	85	90	92	86	74	71	75	78	81
12.5°	83	97	106	117	120	117	105	86	84	88	91
11.25°	102	118	135	148	154	153	144	126	100	98	106
10°	123	143	167	184	194	196	189	172	148	120	124
8.75°	175	174	202	224	238	244	239	226	208	183	151
7.5°	277	285	283	267	287	295	295	288	276	254	245
6.25°	387	408	414	400	383	357	356	357	350	347	343
5°	501	535	543	532	509	476	450	434	433	442	444
3.75°	618	666	672	664	629	587	551	523	517	530	555
2.5°	735	798	801	795	746	694	644	601	593	596	626
1.25°	850	929	929	926	863	799	735	674	661	654	686
0°	963	1057	1057	1057	982	907	828	748	728	707	737
-1.25°	855	935	935	932	870	806	743	682	670	664	697
-2.5°	744	809	813	808	760	708	659	617	610	616	648
-3.75°	631	682	690	683	650	608	573	546	543	559	587
-5°	518	556	568	558	536	504	479	466	464	473	476
-6.25°	407	433	444	432	417	392	389	386	377	375	373
-7.5°	299	313	318	305	322	327	323	313	299	277	270
-8.75°	198	204	235	257	268	271	262	245	226	200	169
-10°	143	167	193	212	219	218	207	187	159	130	136
-11.25°	118	137	155	170	175	170	157	135	106	104	114
-12.5°	95	111	122	133	135	129	114	91	88	92	96
-13.75°	76	88	96	101	102	94	78	74	78	81	84
-15°	63	68	75	77	74	66	62	65	69	71	73
-16.25°	52	55	58	58	54	52	55	57	60	62	63
-17.5°	42	45	45	44	43	46	48	50	52	53	54
-18.75°	36	37	37	36	38	40	42	43	45	46	46
-20°	30	31	30	32	34	35	37	38	39	39	39
-21.25°	26	26	28	29	30	31	32	33	34	34	34



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	24	24	26	27	27	29	29	30	30	30	30
-23.75°	22	23	23	25	25	26	27	27	27	27	27
-25°	21	22	22	23	23	24	25	25	25	25	25
-26.25°	20	21	21	22	22	22	23	23	23	23	24
-27.5°	19	19	20	20	21	21	21	22	22	22	22
-28.75°	18	18	19	19	19	20	20	20	21	21	21
-30°	17	18	18	18	18	19	19	19	19	20	20
-31.25°	17	17	17	17	17	18	18	18	18	18	19
-32.5°	16	16	17	17	17	17	17	17	17	17	18
-33.75°	15	16	16	16	16	16	17	17	17	17	17
-35°	15	15	15	15	16	16	16	16	16	16	16
-36.25°	14	14	14	15	15	15	15	15	16	16	16
-37.5°	13	13	14	14	14	14	14	15	15	15	15
-38.75°	13	13	13	13	13	13	14	14	14	14	14
-40°	12	12	12	12	12	13	13	13	13	13	13
-41.25°	12	12	12	12	12	12	12	12	12	12	12
-42.5°	11	11	11	11	12	12	12	12	12	12	12
-43.75°	10	10	10	11	11	11	11	11	11	11	11
-45°	9	10	10	10	10	10	10	10	10	10	10
-46.25°	9	9	9	9	9	9	9	10	10	10	10
-47.5°	8	8	8	8	8	8	9	9	9	9	9
-48.75°	7	8	8	8	8	8	8	8	8	8	8
-50°	7	7	7	7	7	7	7	7	7	7	7
-51.25°	6	6	6	6	7	7	7	7	7	7	7
-52.5°	5	5	5	6	6	6	6	6	6	6	6
-53.75°	5	5	5	5	5	5	5	5	6	6	6
-55°	4	4	5	5	5	5	5	5	5	5	5
-56.25°	4	4	4	4	4	4	4	4	4	4	4
-57.5°	3	3	3	3	3	3	4	4	4	4	4
-58.75°	2	2	2	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	2	2	2	2	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	4	4	4	4	4	4	4	4	4	4	4
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	5	5	5	5	5	5	5	5	5	5	5
55°	5	5	5	5	5	5	5	5	5	5	5
53.75°	6	6	6	6	6	6	6	6	6	6	6
52.5°	6	6	6	6	6	6	6	6	6	6	6
51.25°	7	7	7	7	7	7	7	7	7	7	7
50°	8	8	8	7	7	7	7	7	7	7	8
48.75°	8	8	8	8	8	8	8	8	8	8	8
47.5°	9	9	9	9	9	9	9	9	9	9	9
46.25°	10	10	10	10	9	9	9	9	9	10	10
45°	10	10	10	10	10	10	10	10	10	10	10
43.75°	11	11	11	10	10	10	10	10	10	10	11
42.5°	11	11	11	11	11	11	11	11	11	11	11
41.25°	12	12	12	12	12	12	12	12	12	12	12
40°	13	13	13	13	13	12	12	12	13	13	13
38.75°	13	13	13	13	13	13	13	13	13	13	13
37.5°	14	14	14	14	14	13	13	13	14	14	14
36.25°	15	15	15	15	14	14	14	14	14	15	15
35°	16	16	16	15	15	15	15	15	15	15	16



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	16	16	16	16	16	16	16	16	16	16	16
32.5°	17	17	17	17	17	17	17	17	17	17	17
31.25°	18	18	18	18	18	18	18	18	18	18	18
30°	19	19	20	20	20	20	20	20	20	20	20
28.75°	21	21	21	21	21	21	21	21	21	21	21
27.5°	22	22	22	22	22	22	22	22	22	22	22
26.25°	23	24	24	24	24	24	24	24	24	24	24
25°	25	26	26	26	26	26	26	26	26	26	26
23.75°	28	28	29	29	29	29	29	29	29	29	29
22.5°	31	32	32	32	32	32	32	32	32	32	32
21.25°	34	36	36	37	37	37	36	37	37	37	36
20°	40	41	42	42	42	42	41	42	42	42	42
18.75°	45	47	49	50	50	50	49	50	50	50	49
17.5°	54	55	57	58	58	58	58	58	58	58	57
16.25°	63	64	66	67	68	69	68	69	68	67	66
15°	72	73	76	77	79	79	79	79	79	77	76
13.75°	83	84	86	89	91	92	91	92	91	89	86
12.5°	95	98	99	103	104	105	104	105	104	103	99
11.25°	112	115	116	121	124	125	123	125	124	121	116
10°	130	144	147	143	146	145	142	145	146	143	147
8.75°	173	187	185	184	191	196	188	196	191	184	185
7.5°	226	247	267	284	295	307	291	307	295	284	267
6.25°	336	348	393	435	461	479	460	479	461	435	393
5°	461	495	543	602	645	668	657	668	645	602	543
3.75°	587	637	693	750	801	829	818	829	801	750	693
2.5°	681	754	817	874	915	949	941	949	915	874	817
1.25°	744	817	893	953	994	1020	1027	1020	994	953	893
0°	792	863	934	986	1026	1052	1064	1052	1026	986	934
-1.25°	757	831	907	967	1008	1033	1039	1033	1008	967	907
-2.5°	707	782	846	903	947	976	972	976	947	903	846
-3.75°	621	673	733	793	841	868	859	868	841	793	733
-5°	497	536	588	645	685	708	696	708	685	645	588
-6.25°	371	389	433	473	496	519	505	519	496	473	433
-7.5°	256	278	298	313	324	341	328	341	324	313	298
-8.75°	194	207	204	202	211	218	211	218	211	202	204
-10°	143	157	158	153	156	155	150	155	156	153	158
-11.25°	120	122	122	126	130	130	128	130	130	126	122
-12.5°	101	103	103	106	107	107	106	107	107	106	103
-13.75°	86	87	90	92	93	93	92	93	93	92	90
-15°	75	76	78	80	80	80	79	80	80	80	78
-16.25°	64	65	67	69	69	69	68	69	69	69	67
-17.5°	55	56	58	59	59	59	58	59	59	59	58
-18.75°	46	48	49	50	50	50	49	50	50	50	49
-20°	40	41	42	42	42	41	40	41	42	42	42
-21.25°	34	35	36	37	37	36	35	36	37	37	36



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	31	32	32	32	32	31	31	31	32	32	32
-23.75°	28	28	29	29	29	29	29	29	29	29	29
-25°	26	26	26	27	27	27	27	27	27	27	26
-26.25°	24	24	25	25	25	25	25	25	25	25	25
-27.5°	23	23	23	23	23	23	23	23	23	23	23
-28.75°	21	22	22	22	22	22	22	22	22	22	22
-30°	20	20	20	20	20	20	20	20	20	20	20
-31.25°	19	19	19	19	19	19	19	19	19	19	19
-32.5°	18	18	18	18	18	18	18	18	18	18	18
-33.75°	17	17	17	17	17	17	17	17	17	17	17
-35°	16	16	16	16	16	16	16	16	16	16	16
-36.25°	15	15	15	15	15	15	15	15	15	15	15
-37.5°	15	15	15	15	14	14	14	14	14	15	15
-38.75°	14	14	14	14	14	13	13	13	14	14	14
-40°	13	13	13	13	13	13	12	13	13	13	13
-41.25°	12	12	12	12	12	12	12	12	12	12	12
-42.5°	12	12	12	12	12	12	12	12	12	12	12
-43.75°	11	11	11	11	11	11	11	11	11	11	11
-45°	10	10	10	10	10	10	10	10	10	10	10
-46.25°	10	10	10	10	10	9	9	9	10	10	10
-47.5°	9	9	9	9	9	9	9	9	9	9	9
-48.75°	8	8	8	8	8	8	8	8	8	8	8
-50°	7	7	7	7	7	7	7	7	7	7	7
-51.25°	7	7	7	7	7	7	7	7	7	7	7
-52.5°	6	6	6	6	6	6	6	6	6	6	6
-53.75°	6	6	6	6	6	6	6	6	6	6	6
-55°	5	5	5	5	5	5	5	5	5	5	5
-56.25°	4	4	4	4	4	4	4	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	4	4	4
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	1	1	1	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	3	3	2	2
58.75°	4	4	4	3	3	3	3	3	3	3	3
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	5	5	5	5	5	5	4	4	4	4	4
55°	5	5	5	5	5	5	5	5	5	5	5
53.75°	6	6	6	6	6	6	6	6	6	6	6
52.5°	6	6	6	6	6	6	6	6	6	6	6
51.25°	7	7	7	7	7	7	7	7	7	7	7
50°	8	8	8	8	8	8	8	8	7	7	7
48.75°	8	8	8	8	8	8	8	8	8	8	8
47.5°	9	9	9	9	9	9	9	9	9	9	9
46.25°	10	10	10	10	10	10	10	9	9	9	9
45°	10	10	10	10	10	10	10	10	10	10	10
43.75°	11	11	11	11	10	10	10	10	10	10	10
42.5°	11	11	11	11	11	11	11	11	11	11	11
41.25°	12	12	12	12	12	12	12	12	12	11	11
40°	13	13	13	13	13	12	12	12	12	12	12
38.75°	13	13	13	13	13	13	13	13	13	13	13
37.5°	14	14	14	14	14	14	14	13	13	13	13
36.25°	15	15	15	15	15	15	14	14	14	14	14
35°	16	16	16	16	15	15	15	15	15	15	15



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	16	16	16	16	16	16	16	16	16	16	15
32.5°	17	17	17	17	17	17	17	17	17	16	16
31.25°	18	18	18	18	18	18	18	18	17	17	17
30°	19	19	19	19	19	19	19	19	18	18	18
28.75°	21	21	20	20	20	20	20	19	19	19	19
27.5°	22	22	22	21	21	21	21	21	20	20	19
26.25°	24	23	23	22	22	22	22	22	21	21	21
25°	26	25	25	24	24	24	24	24	23	22	22
23.75°	28	28	27	27	27	27	26	26	25	24	23
22.5°	32	31	30	30	29	29	29	28	27	26	25
21.25°	36	34	34	34	34	33	32	31	30	29	28
20°	41	40	39	39	38	37	36	34	33	32	30
18.75°	47	45	45	45	44	42	41	39	37	35	36
17.5°	55	54	53	51	50	49	46	44	42	42	43
16.25°	64	63	62	60	58	55	53	50	51	54	53
15°	73	72	71	69	66	63	60	62	68	70	68
13.75°	84	83	81	78	75	71	74	86	92	90	85
12.5°	98	95	91	88	84	86	105	117	120	117	106
11.25°	115	112	106	98	100	126	144	153	154	148	135
10°	144	130	124	120	148	172	189	196	194	184	167
8.75°	187	173	151	183	208	226	239	244	238	224	202
7.5°	247	226	245	254	276	288	295	295	287	267	283
6.25°	348	336	343	347	350	357	356	357	383	400	414
5°	495	461	444	442	433	434	450	476	509	532	543
3.75°	637	587	555	530	517	523	551	587	629	664	672
2.5°	754	681	626	596	593	601	644	694	746	795	801
1.25°	817	744	686	654	661	674	735	799	863	926	929
0°	863	792	737	707	728	748	828	907	982	1057	1057
-1.25°	831	757	697	664	670	682	743	806	870	932	935
-2.5°	782	707	648	616	610	617	659	708	760	808	813
-3.75°	673	621	587	559	543	546	573	608	650	683	690
-5°	536	497	476	473	464	466	479	504	536	558	568
-6.25°	389	371	373	375	377	386	389	392	417	432	444
-7.5°	278	256	270	277	299	313	323	327	322	305	318
-8.75°	207	194	169	200	226	245	262	271	268	257	235
-10°	157	143	136	130	159	187	207	218	219	212	193
-11.25°	122	120	114	104	106	135	157	170	175	170	155
-12.5°	103	101	96	92	88	91	114	129	135	133	122
-13.75°	87	86	84	81	78	74	78	94	102	101	96
-15°	76	75	73	71	69	65	62	66	74	77	75
-16.25°	65	64	63	62	60	57	55	52	54	58	58
-17.5°	56	55	54	53	52	50	48	46	43	44	45
-18.75°	48	46	46	46	45	43	42	40	38	36	37
-20°	41	40	39	39	39	38	37	35	34	32	30
-21.25°	35	34	34	34	34	33	32	31	30	29	28



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	32	31	30	30	30	30	29	29	27	27	26
-23.75°	28	28	27	27	27	27	27	26	25	25	23
-25°	26	26	25	25	25	25	25	24	23	23	22
-26.25°	24	24	24	23	23	23	23	22	22	22	21
-27.5°	23	23	22	22	22	22	21	21	21	20	20
-28.75°	22	21	21	21	21	20	20	20	19	19	19
-30°	20	20	20	20	19	19	19	19	18	18	18
-31.25°	19	19	19	18	18	18	18	18	17	17	17
-32.5°	18	18	18	17	17	17	17	17	17	17	17
-33.75°	17	17	17	17	17	17	17	16	16	16	16
-35°	16	16	16	16	16	16	16	16	16	15	15
-36.25°	15	15	16	16	16	15	15	15	15	15	14
-37.5°	15	15	15	15	15	15	14	14	14	14	14
-38.75°	14	14	14	14	14	14	14	13	13	13	13
-40°	13	13	13	13	13	13	13	13	12	12	12
-41.25°	12	12	12	12	12	12	12	12	12	12	12
-42.5°	12	12	12	12	12	12	12	12	12	11	11
-43.75°	11	11	11	11	11	11	11	11	11	11	10
-45°	10	10	10	10	10	10	10	10	10	10	10
-46.25°	10	10	10	10	10	10	9	9	9	9	9
-47.5°	9	9	9	9	9	9	9	8	8	8	8
-48.75°	8	8	8	8	8	8	8	8	8	8	8
-50°	7	7	7	7	7	7	7	7	7	7	7
-51.25°	7	7	7	7	7	7	7	7	7	6	6
-52.5°	6	6	6	6	6	6	6	6	6	6	5
-53.75°	6	6	6	6	6	5	5	5	5	5	5
-55°	5	5	5	5	5	5	5	5	5	5	5
-56.25°	4	4	4	4	4	4	4	4	4	4	4
-57.5°	4	4	4	4	4	4	4	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	2
-60°	3	3	3	3	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	2	2	2	2	2	2	2
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	2	2	2	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	3	3	3	2	2	2	2	2	2	2	2
57.5°	4	4	3	3	3	3	2	2	2	2	2
56.25°	4	4	4	4	4	3	3	3	3	2	2
55°	5	4	4	4	4	4	4	4	3	3	3
53.75°	5	5	5	5	5	5	4	4	4	4	3
52.5°	6	6	6	5	5	5	5	5	5	4	4
51.25°	7	7	6	6	6	6	6	5	5	5	5
50°	7	7	7	7	7	6	6	6	6	5	5
48.75°	8	8	8	7	7	7	7	6	6	6	6
47.5°	9	8	8	8	8	8	8	7	7	6	6
46.25°	9	9	9	9	9	8	8	8	8	7	7
45°	10	10	10	9	9	9	9	9	9	8	8
43.75°	10	10	10	10	10	10	9	9	9	9	9
42.5°	11	11	11	11	10	10	10	10	9	9	9
41.25°	11	11	11	11	11	11	11	10	10	10	10
40°	12	12	11	11	11	11	11	11	11	10	10
38.75°	12	12	12	12	12	12	12	11	11	11	11
37.5°	13	13	13	12	12	12	12	12	12	12	11
36.25°	14	13	13	13	13	13	12	12	12	12	12
35°	14	14	14	14	13	13	13	13	12	12	12



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	15	15	15	14	14	14	13	13	13	13	12
32.5°	16	16	15	15	15	14	14	13	13	13	13
31.25°	17	16	16	16	15	15	15	14	14	13	13
30°	18	17	17	16	16	16	15	15	14	14	14
28.75°	18	18	18	17	17	16	16	16	15	15	14
27.5°	19	19	18	18	18	17	17	16	16	15	15
26.25°	20	20	19	19	18	18	18	17	16	16	15
25°	21	20	20	20	19	19	18	18	17	17	16
23.75°	23	22	21	21	20	20	19	19	18	17	17
22.5°	24	23	23	22	22	21	20	19	19	18	17
21.25°	26	26	25	25	23	22	21	20	20	19	18
20°	30	30	28	27	26	24	23	22	20	20	19
18.75°	36	35	33	30	28	26	24	23	21	20	19
17.5°	43	40	38	35	32	29	27	25	23	21	20
16.25°	51	48	44	41	36	32	29	26	24	22	21
15°	62	57	52	47	42	36	32	29	26	24	22
13.75°	78	68	62	54	48	41	36	32	28	26	23
12.5°	97	83	72	63	54	47	39	37	32	29	25
11.25°	118	102	84	74	62	60	54	46	39	32	28
10°	143	123	101	101	98	87	74	58	47	36	31
8.75°	174	175	173	161	145	119	98	71	57	42	34
7.5°	285	277	260	232	200	160	126	91	68	50	38
6.25°	408	387	355	311	262	207	157	114	80	58	41
5°	535	501	456	394	327	257	190	138	92	67	45
3.75°	666	618	560	480	396	309	224	162	104	75	48
2.5°	798	735	665	567	464	361	257	186	116	83	52
1.25°	929	850	769	651	531	410	289	208	127	91	55
0°	1057	963	869	731	594	456	318	228	137	97	58
-1.25°	935	855	773	654	533	412	290	208	127	91	55
-2.5°	809	744	672	572	467	363	258	186	116	84	52
-3.75°	682	631	570	487	400	312	225	163	104	75	48
-5°	556	518	468	403	333	261	192	139	92	67	45
-6.25°	433	407	370	320	268	211	160	115	80	58	41
-7.5°	313	299	276	242	207	164	129	92	68	50	38
-8.75°	204	198	190	172	153	123	101	72	58	42	34
-10°	167	143	117	112	105	91	76	58	48	36	31
-11.25°	137	118	95	83	68	64	55	47	39	32	28
-12.5°	111	95	81	70	58	50	40	38	32	29	25
-13.75°	88	76	68	59	51	43	36	32	28	26	23
-15°	68	63	57	50	44	36	33	29	26	24	22
-16.25°	55	52	47	42	37	33	30	27	24	22	21
-17.5°	45	42	40	36	32	30	27	25	23	21	20
-18.75°	37	36	34	31	29	27	25	23	21	20	19
-20°	31	30	29	28	26	24	23	22	20	20	19
-21.25°	26	26	26	25	24	23	22	20	20	19	18



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	24	24	24	23	22	21	20	19	19	18	18
-23.75°	23	22	22	21	21	20	19	19	18	17	17
-25°	22	21	21	20	19	19	18	18	17	17	16
-26.25°	21	20	19	19	18	18	18	17	17	16	16
-27.5°	19	19	18	18	18	17	17	16	16	16	15
-28.75°	18	18	18	17	17	16	16	16	15	15	15
-30°	18	17	17	17	16	16	15	15	15	15	14
-31.25°	17	17	16	16	16	15	15	15	14	14	14
-32.5°	16	16	16	15	15	15	14	14	14	13	13
-33.75°	16	15	15	15	14	14	14	14	13	13	13
-35°	15	15	14	14	14	14	13	13	13	12	12
-36.25°	14	14	14	14	13	13	13	12	12	12	12
-37.5°	13	13	13	13	13	12	12	12	12	12	11
-38.75°	13	13	13	12	12	12	12	11	11	11	11
-40°	12	12	12	12	12	11	11	11	11	10	10
-41.25°	12	12	11	11	11	11	11	10	10	10	9
-42.5°	11	11	11	11	10	10	10	10	9	9	9
-43.75°	10	10	10	10	10	9	9	9	9	8	8
-45°	10	9	9	9	9	9	8	8	8	8	7
-46.25°	9	9	8	8	8	8	8	8	7	7	7
-47.5°	8	8	8	8	8	7	7	7	7	6	6
-48.75°	8	7	7	7	7	7	6	6	6	6	5
-50°	7	7	7	6	6	6	6	5	5	5	5
-51.25°	6	6	6	6	5	5	5	5	5	4	4
-52.5°	5	5	5	5	5	5	4	4	4	4	4
-53.75°	5	5	5	5	4	4	4	4	4	3	3
-55°	4	4	4	4	4	4	3	3	3	3	3
-56.25°	4	4	3	3	3	3	3	3	2	2	2
-57.5°	3	3	3	3	3	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	1
-62.5°	2	2	2	2	2	2	2	1	1	1	1
-63.75°	2	2	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	1	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	3	3	2	2	2	2	2	2	2	2	2
52.5°	4	3	3	3	2	2	2	2	2	2	2
51.25°	4	4	4	3	3	3	2	2	2	2	2
50°	5	5	4	4	4	3	3	2	2	2	2
48.75°	5	5	5	5	4	4	3	3	3	2	2
47.5°	6	6	5	5	5	4	4	3	3	3	2
46.25°	6	6	6	6	5	5	4	4	3	3	3
45°	7	7	6	6	6	5	5	5	4	4	3
43.75°	8	8	7	6	6	6	5	5	5	4	3
42.5°	9	9	8	7	6	6	6	6	5	5	4
41.25°	9	9	9	8	7	7	6	6	6	5	4
40°	10	9	9	9	8	7	7	6	6	5	5
38.75°	10	10	10	9	9	8	7	7	6	6	5
37.5°	11	10	10	10	9	9	8	7	7	6	6
36.25°	11	11	10	10	10	9	9	8	7	7	6
35°	12	11	11	10	10	10	9	9	8	7	7



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	12	12	11	11	10	10	10	9	8	8	7
32.5°	12	12	12	11	11	10	10	9	9	8	7
31.25°	13	12	12	12	11	11	10	10	9	9	8
30°	13	13	12	12	11	11	11	10	10	9	8
28.75°	14	13	13	12	12	11	11	11	10	9	9
27.5°	14	14	13	13	12	12	11	11	10	10	9
26.25°	15	14	14	13	13	12	11	11	11	10	9
25°	15	15	14	14	13	12	12	11	11	10	10
23.75°	16	15	15	14	13	13	12	11	11	11	10
22.5°	16	16	15	15	14	13	13	12	11	11	10
21.25°	17	16	16	15	14	14	13	12	12	11	11
20°	18	17	16	15	15	14	13	13	12	12	11
18.75°	19	18	17	16	15	15	14	13	12	12	11
17.5°	19	18	17	16	16	15	14	14	13	12	12
16.25°	20	19	18	17	16	15	15	14	13	13	12
15°	21	20	19	17	17	16	15	14	14	13	12
13.75°	22	21	19	18	17	16	16	15	14	13	12
12.5°	23	21	20	19	17	17	16	15	14	14	13
11.25°	24	22	21	19	18	17	16	15	15	14	13
10°	25	23	21	20	18	17	17	16	15	14	13
8.75°	28	24	22	20	19	18	17	16	15	14	14
7.5°	30	25	23	21	19	18	17	16	16	15	14
6.25°	33	27	24	22	20	18	17	17	16	15	14
5°	35	28	25	22	20	19	18	17	16	15	14
3.75°	38	28	26	23	21	19	18	17	16	15	15
2.5°	40	29	26	23	21	19	18	17	17	16	15
1.25°	43	30	27	24	21	19	18	18	17	16	15
0°	44	31	27	24	22	19	19	18	17	16	15
-1.25°	43	30	27	24	21	19	18	18	17	16	15
-2.5°	40	29	26	23	21	19	18	17	17	16	15
-3.75°	38	28	26	23	21	19	18	17	16	16	15
-5°	35	28	25	22	20	19	18	17	16	15	15
-6.25°	33	27	24	22	20	19	18	17	16	15	14
-7.5°	30	25	23	21	20	18	17	16	16	15	14
-8.75°	28	24	22	21	19	18	17	16	16	15	14
-10°	25	23	21	20	19	18	17	16	15	15	14
-11.25°	24	22	21	20	18	17	16	16	15	14	14
-12.5°	23	21	20	19	18	17	16	15	15	14	13
-13.75°	22	21	20	19	17	16	16	15	15	14	13
-15°	21	20	19	18	17	16	15	15	14	13	13
-16.25°	20	19	18	18	16	16	15	15	14	13	12
-17.5°	19	19	18	17	16	15	15	14	14	13	12
-18.75°	19	18	17	16	15	15	15	14	13	12	12
-20°	18	18	17	16	15	15	14	14	13	12	11
-21.25°	18	17	16	15	15	14	14	13	12	12	11



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	17	16	15	15	14	14	13	13	12	11	10
-23.75°	16	16	15	14	14	14	13	12	12	11	10
-25°	16	15	15	14	14	13	13	12	11	10	10
-26.25°	15	15	14	14	13	13	12	11	11	10	9
-27.5°	15	14	14	13	13	12	12	11	10	10	9
-28.75°	14	14	13	13	12	12	11	11	10	9	9
-30°	14	13	13	12	12	11	11	10	10	9	8
-31.25°	13	13	12	12	12	11	10	10	9	8	8
-32.5°	13	12	12	12	11	10	10	9	9	8	7
-33.75°	12	12	12	11	10	10	9	9	8	8	7
-35°	12	11	11	10	10	9	9	8	8	7	6
-36.25°	11	11	10	10	9	9	8	8	7	7	6
-37.5°	11	10	10	9	9	8	8	7	7	6	6
-38.75°	10	10	9	9	8	8	7	7	6	6	5
-40°	10	9	9	8	8	7	7	6	6	5	5
-41.25°	9	8	8	8	7	7	6	6	5	5	4
-42.5°	8	8	7	7	6	6	6	5	5	4	4
-43.75°	8	7	7	6	6	5	5	5	4	4	3
-45°	7	6	6	6	5	5	4	4	4	4	3
-46.25°	6	6	5	5	5	4	4	4	3	3	3
-47.5°	6	5	5	4	4	4	4	3	3	3	2
-48.75°	5	5	4	4	4	4	3	3	2	2	2
-50°	4	4	4	4	4	3	3	2	2	2	2
-51.25°	4	4	4	3	3	3	2	2	2	2	2
-52.5°	4	3	3	3	2	2	2	2	2	2	2
-53.75°	3	3	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	1
-56.25°	2	2	2	2	2	2	2	2	1	1	1
-57.5°	2	2	2	2	2	2	1	1	1	1	1
-58.75°	2	2	2	2	1	1	1	1	1	1	1
-60°	2	2	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	0	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	0
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	2	1	1	1	1	1	1	1	1	1	1
55°	2	2	1	1	1	1	1	1	1	1	1
53.75°	2	2	2	2	1	1	1	1	1	1	1
52.5°	2	2	2	2	2	1	1	1	1	1	1
51.25°	2	2	2	2	2	2	1	1	1	1	1
50°	2	2	2	2	2	2	1	1	1	1	1
48.75°	2	2	2	2	2	2	2	1	1	1	1
47.5°	2	2	2	2	2	2	2	2	1	1	1
46.25°	2	2	2	2	2	2	2	2	2	1	1
45°	3	2	2	2	2	2	2	2	2	1	1
43.75°	3	3	2	2	2	2	2	2	2	2	1
42.5°	3	3	3	2	2	2	2	2	2	2	1
41.25°	4	3	3	3	2	2	2	2	2	2	2
40°	4	4	3	3	3	2	2	2	2	2	2
38.75°	5	4	4	3	3	3	2	2	2	2	2
37.5°	5	5	4	3	3	3	3	2	2	2	2
36.25°	6	5	4	4	3	3	3	2	2	2	2
35°	6	5	5	4	3	3	3	3	2	2	2



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	6	6	5	4	4	3	3	3	2	2	2
32.5°	7	6	6	5	4	3	3	3	3	2	2
31.25°	7	7	6	5	4	4	3	3	3	2	2
30°	8	7	6	6	5	4	3	3	3	2	2
28.75°	8	7	7	6	5	4	4	3	3	3	2
27.5°	8	8	7	6	5	5	4	3	3	3	2
26.25°	9	8	7	7	6	5	4	3	3	3	2
25°	9	8	8	7	6	5	4	4	3	3	3
23.75°	9	9	8	7	6	6	5	4	3	3	3
22.5°	10	9	8	8	7	6	5	4	3	3	3
21.25°	10	9	9	8	7	6	5	4	4	3	3
20°	10	10	9	8	7	6	5	5	4	3	3
18.75°	11	10	9	8	8	7	6	5	4	3	3
17.5°	11	10	9	9	8	7	6	5	4	3	3
16.25°	11	10	10	9	8	7	6	5	4	3	3
15°	11	11	10	9	8	7	6	5	4	4	3
13.75°	12	11	10	9	8	8	7	5	5	4	3
12.5°	12	11	10	10	9	8	7	6	5	4	3
11.25°	12	11	11	10	9	8	7	6	5	4	3
10°	12	12	11	10	9	8	7	6	5	4	3
8.75°	13	12	11	10	9	8	7	6	5	4	3
7.5°	13	12	11	10	9	8	7	6	5	4	3
6.25°	13	12	11	10	9	9	8	6	5	4	3
5°	13	12	11	10	10	9	8	6	5	4	3
3.75°	14	12	11	10	10	9	8	7	5	4	3
2.5°	14	13	11	11	10	9	8	7	5	4	3
1.25°	14	13	11	11	10	9	8	7	5	4	3
0°	14	13	11	11	10	9	8	7	5	4	4
-1.25°	14	13	11	11	10	9	8	7	5	4	3
-2.5°	14	13	11	11	10	9	8	7	5	4	3
-3.75°	14	13	11	10	10	9	8	7	5	4	3
-5°	14	12	11	10	10	9	8	6	5	4	3
-6.25°	13	12	11	10	9	9	8	6	5	4	3
-7.5°	13	12	11	10	9	8	7	6	5	4	3
-8.75°	13	12	11	10	9	8	7	6	5	4	3
-10°	13	12	11	10	9	8	7	6	5	4	3
-11.25°	12	11	11	10	9	8	7	6	5	4	3
-12.5°	12	11	10	10	9	8	7	6	5	4	3
-13.75°	12	11	10	9	8	8	7	5	5	4	3
-15°	12	11	10	9	8	7	6	5	4	4	3
-16.25°	11	10	10	9	8	7	6	5	4	3	3
-17.5°	11	10	9	9	8	7	6	5	4	3	3
-18.75°	11	10	9	8	8	7	6	5	4	3	3
-20°	10	10	9	8	7	6	5	5	4	3	3
-21.25°	10	9	9	8	7	6	5	4	4	3	2



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	10	9	8	8	7	6	5	4	3	3	2
-23.75°	9	9	8	7	6	6	5	4	3	3	2
-25°	9	8	8	7	6	5	4	4	3	2	2
-26.25°	9	8	7	7	6	5	4	3	3	2	2
-27.5°	8	8	7	6	5	5	4	3	3	2	2
-28.75°	8	7	7	6	5	4	4	3	2	2	2
-30°	8	7	6	6	5	4	3	3	2	2	2
-31.25°	7	7	6	5	4	4	3	2	2	2	2
-32.5°	7	6	5	5	4	3	3	2	2	2	2
-33.75°	6	6	5	4	4	3	2	2	2	2	2
-35°	6	5	5	4	3	3	2	2	2	2	2
-36.25°	5	5	4	4	3	2	2	2	2	2	2
-37.5°	5	4	4	3	3	2	2	2	2	2	2
-38.75°	5	4	4	3	2	2	2	2	2	2	2
-40°	4	4	3	3	2	2	2	2	2	2	2
-41.25°	4	3	3	2	2	2	2	2	2	2	2
-42.5°	3	3	2	2	2	2	2	2	2	2	1
-43.75°	3	2	2	2	2	2	2	2	2	2	1
-45°	3	2	2	2	2	2	2	2	2	1	1
-46.25°	2	2	2	2	2	2	2	2	1	1	1
-47.5°	2	2	2	2	2	2	2	2	1	1	1
-48.75°	2	2	2	2	2	2	2	1	1	1	1
-50°	2	2	2	2	2	1	1	1	1	1	1
-51.25°	2	2	2	2	1	1	1	1	1	1	1
-52.5°	2	2	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	0
-68.75°	1	1	1	1	1	1	1	1	0	0	0
-70°	1	1	1	1	1	1	0	0	0	0	0
-71.25°	1	1	1	1	0	0	0	0	0	0	0
-72.5°	1	1	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	1	0	0	0	0	0	0	0	0	0	0
70°	1	1	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	0	0	0	0	0	0	0	0
67.5°	1	1	1	1	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	0	0	0	0	0	0
65°	1	1	1	1	1	1	0	0	0	0	0
63.75°	1	1	1	1	1	1	1	0	0	0	0
62.5°	1	1	1	1	1	1	1	0	0	0	0
61.25°	1	1	1	1	1	1	1	1	0	0	0
60°	1	1	1	1	1	1	1	1	0	0	0
58.75°	1	1	1	1	1	1	1	1	1	0	0
57.5°	1	1	1	1	1	1	1	1	1	0	0
56.25°	1	1	1	1	1	1	1	1	1	0	0
55°	1	1	1	1	1	1	1	1	1	1	0
53.75°	1	1	1	1	1	1	1	1	1	1	0
52.5°	1	1	1	1	1	1	1	1	1	1	0
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	2	1	1	1	1	1	1	1	1	1	1
37.5°	2	1	1	1	1	1	1	1	1	1	1
36.25°	2	2	1	1	1	1	1	1	1	1	1
35°	2	2	1	1	1	1	1	1	1	1	1



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	1	1	1	1	1	1	1	1	1
32.5°	2	2	2	1	1	1	1	1	1	1	1
31.25°	2	2	2	1	1	1	1	1	1	1	1
30°	2	2	2	1	1	1	1	1	1	1	1
28.75°	2	2	2	2	1	1	1	1	1	1	1
27.5°	2	2	2	2	1	1	1	1	1	1	1
26.25°	2	2	2	2	1	1	1	1	1	1	1
25°	2	2	2	2	1	1	1	1	1	1	1
23.75°	2	2	2	2	1	1	1	1	1	1	1
22.5°	2	2	2	2	2	1	1	1	1	1	1
21.25°	2	2	2	2	2	1	1	1	1	1	1
20°	2	2	2	2	2	1	1	1	1	1	1
18.75°	3	2	2	2	2	1	1	1	1	1	1
17.5°	3	2	2	2	2	1	1	1	1	1	1
16.25°	3	2	2	2	2	1	1	1	1	1	1
15°	3	2	2	2	2	2	1	1	1	1	1
13.75°	3	2	2	2	2	2	1	1	1	1	1
12.5°	3	2	2	2	2	2	1	1	1	1	1
11.25°	3	2	2	2	2	2	1	1	1	1	1
10°	3	3	2	2	2	2	1	1	1	1	1
8.75°	3	3	2	2	2	2	1	1	1	1	1
7.5°	3	3	2	2	2	2	1	1	1	1	1
6.25°	3	3	2	2	2	2	1	1	1	1	1
5°	3	3	2	2	2	2	1	1	1	1	1
3.75°	3	3	2	2	2	2	1	1	1	1	1
2.5°	3	3	2	2	2	2	1	1	1	1	1
1.25°	3	3	2	2	2	2	1	1	1	1	1
0°	3	3	2	2	2	2	1	1	1	1	1
-1.25°	3	3	2	2	2	2	1	1	1	1	1
-2.5°	3	3	2	2	2	2	1	1	1	1	1
-3.75°	3	3	2	2	2	2	1	1	1	1	1
-5°	3	3	2	2	2	2	1	1	1	1	1
-6.25°	3	3	2	2	2	2	1	1	1	1	1
-7.5°	3	2	2	2	2	2	1	1	1	1	1
-8.75°	3	2	2	2	2	2	1	1	1	1	1
-10°	3	2	2	2	2	2	1	1	1	1	1
-11.25°	3	2	2	2	2	2	1	1	1	1	1
-12.5°	3	2	2	2	2	2	1	1	1	1	1
-13.75°	3	2	2	2	2	2	1	1	1	1	1
-15°	2	2	2	2	2	2	1	1	1	1	1
-16.25°	2	2	2	2	2	1	1	1	1	1	1
-17.5°	2	2	2	2	2	1	1	1	1	1	1
-18.75°	2	2	2	2	2	1	1	1	1	1	1
-20°	2	2	2	2	2	1	1	1	1	1	1
-21.25°	2	2	2	2	2	1	1	1	1	1	1



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	2	2	1	1	1	1	1	1
-23.75°	2	2	2	2	1	1	1	1	1	1	1
-25°	2	2	2	2	1	1	1	1	1	1	1
-26.25°	2	2	2	2	1	1	1	1	1	1	1
-27.5°	2	2	2	2	1	1	1	1	1	1	1
-28.75°	2	2	2	2	1	1	1	1	1	1	1
-30°	2	2	2	1	1	1	1	1	1	1	1
-31.25°	2	2	2	1	1	1	1	1	1	1	1
-32.5°	2	2	2	1	1	1	1	1	1	1	1
-33.75°	2	2	1	1	1	1	1	1	1	1	1
-35°	2	2	1	1	1	1	1	1	1	1	1
-36.25°	2	2	1	1	1	1	1	1	1	1	1
-37.5°	2	1	1	1	1	1	1	1	1	1	1
-38.75°	2	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	0
-47.5°	1	1	1	1	1	1	1	1	1	1	0
-48.75°	1	1	1	1	1	1	1	1	1	1	0
-50°	1	1	1	1	1	1	1	1	1	0	0
-51.25°	1	1	1	1	1	1	1	1	1	0	0
-52.5°	1	1	1	1	1	1	1	1	0	0	0
-53.75°	1	1	1	1	1	1	1	1	0	0	0
-55°	1	1	1	1	1	1	1	0	0	0	0
-56.25°	1	1	1	1	1	1	1	0	0	0	0
-57.5°	1	1	1	1	1	1	0	0	0	0	0
-58.75°	1	1	1	1	1	1	0	0	0	0	0
-60°	1	1	1	1	1	0	0	0	0	0	0
-61.25°	1	1	1	1	0	0	0	0	0	0	0
-62.5°	1	1	1	0	0	0	0	0	0	0	0
-63.75°	1	1	0	0	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	1	0	0	0	0	0	0	0	0	0	0
43.75°	1	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
41.25°	1	0	0	0	0	0	0	0	0	0	0
40°	1	0	0	0	0	0	0	0	0	0	0
38.75°	1	0	0	0	0	0	0	0	0	0	0
37.5°	1	1	0	0	0	0	0	0	0	0	0
36.25°	1	1	0	0	0	0	0	0	0	0	0
35°	1	1	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	0	0	0	0	0	0	0	0	0
32.5°	1	1	0	0	0	0	0	0	0	0	0
31.25°	1	1	0	0	0	0	0	0	0	0	0
30°	1	1	0	0	0	0	0	0	0	0	0
28.75°	1	1	0	0	0	0	0	0	0	0	0
27.5°	1	1	1	0	0	0	0	0	0	0	0
26.25°	1	1	1	0	0	0	0	0	0	0	0
25°	1	1	1	0	0	0	0	0	0	0	0
23.75°	1	1	1	0	0	0	0	0	0	0	0
22.5°	1	1	1	0	0	0	0	0	0	0	0
21.25°	1	1	1	0	0	0	0	0	0	0	0
20°	1	1	1	0	0	0	0	0	0	0	0
18.75°	1	1	1	0	0	0	0	0	0	0	0
17.5°	1	1	1	0	0	0	0	0	0	0	0
16.25°	1	1	1	0	0	0	0	0	0	0	0
15°	1	1	1	0	0	0	0	0	0	0	0
13.75°	1	1	1	0	0	0	0	0	0	0	0
12.5°	1	1	1	0	0	0	0	0	0	0	0
11.25°	1	1	1	0	0	0	0	0	0	0	0
10°	1	1	1	0	0	0	0	0	0	0	0
8.75°	1	1	1	0	0	0	0	0	0	0	0
7.5°	1	1	1	0	0	0	0	0	0	0	0
6.25°	1	1	1	0	0	0	0	0	0	0	0
5°	1	1	1	0	0	0	0	0	0	0	0
3.75°	1	1	1	0	0	0	0	0	0	0	0
2.5°	1	1	1	0	0	0	0	0	0	0	0
1.25°	1	1	1	0	0	0	0	0	0	0	0
0°	1	1	1	0	0	0	0	0	0	0	0
-1.25°	1	1	1	0	0	0	0	0	0	0	0
-2.5°	1	1	1	0	0	0	0	0	0	0	0
-3.75°	1	1	1	0	0	0	0	0	0	0	0
-5°	1	1	1	0	0	0	0	0	0	0	0
-6.25°	1	1	1	0	0	0	0	0	0	0	0
-7.5°	1	1	1	0	0	0	0	0	0	0	0
-8.75°	1	1	1	0	0	0	0	0	0	0	0
-10°	1	1	1	0	0	0	0	0	0	0	0
-11.25°	1	1	1	0	0	0	0	0	0	0	0
-12.5°	1	1	1	0	0	0	0	0	0	0	0
-13.75°	1	1	1	0	0	0	0	0	0	0	0
-15°	1	1	1	0	0	0	0	0	0	0	0
-16.25°	1	1	1	0	0	0	0	0	0	0	0
-17.5°	1	1	1	0	0	0	0	0	0	0	0
-18.75°	1	1	1	0	0	0	0	0	0	0	0
-20°	1	1	1	0	0	0	0	0	0	0	0
-21.25°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	0	0	0	0	0	0	0	0
-23.75°	1	1	1	0	0	0	0	0	0	0	0
-25°	1	1	0	0	0	0	0	0	0	0	0
-26.25°	1	1	0	0	0	0	0	0	0	0	0
-27.5°	1	1	0	0	0	0	0	0	0	0	0
-28.75°	1	1	0	0	0	0	0	0	0	0	0
-30°	1	1	0	0	0	0	0	0	0	0	0
-31.25°	1	1	0	0	0	0	0	0	0	0	0
-32.5°	1	1	0	0	0	0	0	0	0	0	0
-33.75°	1	1	0	0	0	0	0	0	0	0	0
-35°	1	0	0	0	0	0	0	0	0	0	0
-36.25°	1	0	0	0	0	0	0	0	0	0	0
-37.5°	1	0	0	0	0	0	0	0	0	0	0
-38.75°	1	0	0	0	0	0	0	0	0	0	0
-40°	1	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: P246970 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)