

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED3010-12-CS**

Issue Date: 3/3/2020

Test Information


Test Method: LM-79-08
Report Number: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-7)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED3010-12-CS
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER
Light Source: (1) SORAA 3000K 95 CRI 10°NSP LED
SM16-07-10D-930-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	2H x 2V
Luminaire Lumens:	262 lumens	Max Intensity:	4478.6 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	34.9 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	12.5°H x 12.5°V	Field Angle (10%):	19.2°H x 19.2°V
Beam Lumens:	122 lumens	Field Lumens:	181.1 lumens
Beam Efficiency:	46.6%	Field Efficiency:	69.1%
Input Watts (W):	7.5		
Input Voltage (V):	NR		
Input Current (A _{in}):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		

REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS

Iso-Candela Plot






REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
60		0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.1	0.2	0.3	0.3	0.4	0.4	0.3	0.3	0.2	0.1	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.3	0.4	0.5	0.6	0.6	0.5	0.4	0.3	0.1	0.0	0.0		
30	0.0	0.0	0.1	0.2	0.4	0.5	0.7	0.9	0.9	0.7	0.5	0.4	0.2	0.1	0.0	0.0	
20		0.0	0.1	0.2	0.4	0.7	1.4	3.4	3.4	1.4	0.7	0.4	0.2	0.1	0.0		
10	0.0	0.0	0.1	0.3	0.5	0.8	3.3	47.7	47.7	3.3	0.8	0.5	0.3	0.1	0.0	0.0	
0		0.0	0.1	0.3	0.5	0.8	3.3	47.7	47.7	3.3	0.8	0.5	0.3	0.1	0.0		
-10	0.0	0.0	0.1	0.2	0.4	0.7	1.4	3.4	3.4	1.4	0.7	0.4	0.2	0.1	0.0	0.0	
-20		0.0	0.1	0.2	0.4	0.5	0.7	0.9	0.9	0.7	0.5	0.4	0.2	0.1	0.0		
-30	0.0	0.0	0.0	0.1	0.3	0.4	0.5	0.6	0.6	0.5	0.4	0.3	0.1	0.0	0.0	0.0	
-40		0.0	0.0	0.1	0.2	0.3	0.3	0.4	0.4	0.3	0.3	0.2	0.1	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	

REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS


Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS

Luminous Intensity Plot



Beam:
H Angle: 12.5°
V Angle: 12.5°
Lumens: 122
Efficiency: 46.6%

Field:
H Angle: 19.2°
V Angle: 19.2°
Lumens: 181.1
Efficiency: 69.1%

Spill:
Lumens: 80.9
Efficiency: 30.9%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	1
48.75°	0	0	0	0	0	0	0	0	0	0	1
47.5°	0	0	0	0	0	0	0	0	0	1	1
46.25°	0	0	0	0	0	0	0	0	0	1	1
45°	0	0	0	0	0	0	0	0	1	1	1
43.75°	0	0	0	0	0	0	0	0	1	1	1
42.5°	0	0	0	0	0	0	0	0	1	1	1
41.25°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
38.75°	0	0	0	0	0	0	1	1	1	1	1
37.5°	0	0	0	0	0	0	1	1	1	1	1
36.25°	0	0	0	0	0	0	1	1	1	1	1
35°	0	0	0	0	0	0	1	1	1	1	1



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	1	1	1	1	1	1
32.5°	0	0	0	0	0	1	1	1	1	1	1
31.25°	0	0	0	0	0	1	1	1	1	1	1
30°	0	0	0	0	0	1	1	1	1	1	1
28.75°	0	0	0	0	0	1	1	1	1	1	1
27.5°	0	0	0	0	1	1	1	1	1	1	1
26.25°	0	0	0	0	1	1	1	1	1	1	1
25°	0	0	0	0	1	1	1	1	1	1	1
23.75°	0	0	0	0	1	1	1	1	1	1	1
22.5°	0	0	0	0	1	1	1	1	1	1	1
21.25°	0	0	0	0	1	1	1	1	1	1	1
20°	0	0	0	1	1	1	1	1	1	1	1
18.75°	0	0	0	1	1	1	1	1	1	1	1
17.5°	0	0	0	1	1	1	1	1	1	1	1
16.25°	0	0	0	1	1	1	1	1	1	1	1
15°	0	0	0	1	1	1	1	1	1	1	1
13.75°	0	0	0	1	1	1	1	1	1	1	1
12.5°	0	0	0	1	1	1	1	1	1	1	1
11.25°	0	0	0	1	1	1	1	1	1	1	1
10°	0	0	0	1	1	1	1	1	1	1	1
8.75°	0	0	0	1	1	1	1	1	1	1	1
7.5°	0	0	0	1	1	1	1	1	1	1	1
6.25°	0	0	0	1	1	1	1	1	1	1	1
5°	0	0	0	1	1	1	1	1	1	1	1
3.75°	0	0	0	1	1	1	1	1	1	1	1
2.5°	0	0	0	1	1	1	1	1	1	1	1
1.25°	0	0	0	1	1	1	1	1	1	1	1
0°	0	0	0	1	1	1	1	1	1	1	1
-1.25°	0	0	0	1	1	1	1	1	1	1	1
-2.5°	0	0	0	1	1	1	1	1	1	1	1
-3.75°	0	0	0	1	1	1	1	1	1	1	1
-5°	0	0	0	1	1	1	1	1	1	1	1
-6.25°	0	0	0	1	1	1	1	1	1	1	1
-7.5°	0	0	0	1	1	1	1	1	1	1	1
-8.75°	0	0	0	1	1	1	1	1	1	1	1
-10°	0	0	0	1	1	1	1	1	1	1	1
-11.25°	0	0	0	1	1	1	1	1	1	1	1
-12.5°	0	0	0	1	1	1	1	1	1	1	1
-13.75°	0	0	0	1	1	1	1	1	1	1	1
-15°	0	0	0	1	1	1	1	1	1	1	1
-16.25°	0	0	0	1	1	1	1	1	1	1	1
-17.5°	0	0	0	1	1	1	1	1	1	1	1
-18.75°	0	0	0	1	1	1	1	1	1	1	1
-20°	0	0	0	1	1	1	1	1	1	1	1
-21.25°	0	0	0	0	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	1	1	1	1	1	1	1
-23.75°	0	0	0	0	1	1	1	1	1	1	1
-25°	0	0	0	0	1	1	1	1	1	1	1
-26.25°	0	0	0	0	1	1	1	1	1	1	1
-27.5°	0	0	0	0	1	1	1	1	1	1	1
-28.75°	0	0	0	0	0	1	1	1	1	1	1
-30°	0	0	0	0	0	1	1	1	1	1	1
-31.25°	0	0	0	0	0	1	1	1	1	1	1
-32.5°	0	0	0	0	0	1	1	1	1	1	1
-33.75°	0	0	0	0	0	1	1	1	1	1	1
-35°	0	0	0	0	0	0	1	1	1	1	1
-36.25°	0	0	0	0	0	0	1	1	1	1	1
-37.5°	0	0	0	0	0	0	1	1	1	1	1
-38.75°	0	0	0	0	0	0	1	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	0	1	1	1
-43.75°	0	0	0	0	0	0	0	0	1	1	1
-45°	0	0	0	0	0	0	0	0	1	1	1
-46.25°	0	0	0	0	0	0	0	0	0	1	1
-47.5°	0	0	0	0	0	0	0	0	0	1	1
-48.75°	0	0	0	0	0	0	0	0	0	0	1
-50°	0	0	0	0	0	0	0	0	0	0	1
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	1
62.5°	0	0	0	0	0	0	0	0	0	1	1
61.25°	0	0	0	0	0	0	0	1	1	1	1
60°	0	0	0	0	0	0	1	1	1	1	1
58.75°	0	0	0	0	0	1	1	1	1	1	1
57.5°	0	0	0	0	1	1	1	1	1	1	1
56.25°	0	0	0	1	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	1	1
53.75°	0	1	1	1	1	1	1	1	1	1	1
52.5°	0	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	2
43.75°	1	1	1	1	1	1	1	1	1	2	2
42.5°	1	1	1	1	1	1	1	1	2	2	2
41.25°	1	1	1	1	1	1	1	1	2	2	2
40°	1	1	1	1	1	1	1	2	2	2	3
38.75°	1	1	1	1	1	1	1	2	2	2	3
37.5°	1	1	1	1	1	1	2	2	2	3	3
36.25°	1	1	1	1	1	1	2	2	2	3	4
35°	1	1	1	1	1	2	2	2	3	3	4



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	1	2	2	3	3	4	4
32.5°	1	1	1	1	2	2	2	3	3	4	5
31.25°	1	1	1	1	2	2	2	3	4	4	5
30°	1	1	1	2	2	2	3	3	4	5	5
28.75°	1	1	1	2	2	2	3	4	4	5	6
27.5°	1	1	1	2	2	3	3	4	5	5	6
26.25°	1	1	1	2	2	3	3	4	5	6	6
25°	1	1	2	2	2	3	4	4	5	6	7
23.75°	1	1	2	2	3	3	4	5	5	6	7
22.5°	1	1	2	2	3	3	4	5	6	6	7
21.25°	1	1	2	2	3	4	4	5	6	7	7
20°	1	2	2	2	3	4	4	5	6	7	8
18.75°	1	2	2	2	3	4	5	6	6	7	8
17.5°	1	2	2	3	3	4	5	6	7	7	8
16.25°	1	2	2	3	3	4	5	6	7	8	8
15°	1	2	2	3	4	4	5	6	7	8	8
13.75°	1	2	2	3	4	5	5	6	7	8	8
12.5°	2	2	2	3	4	5	6	6	7	8	8
11.25°	2	2	2	3	4	5	6	7	7	8	9
10°	2	2	3	3	4	5	6	7	8	8	9
8.75°	2	2	3	3	4	5	6	7	8	8	9
7.5°	2	2	3	3	4	5	6	7	8	8	9
6.25°	2	2	3	3	4	5	6	7	8	8	9
5°	2	2	3	3	4	5	6	7	8	8	9
3.75°	2	2	3	3	4	5	6	7	8	8	9
2.5°	2	2	3	4	4	5	6	7	8	8	9
1.25°	2	2	3	4	4	5	6	7	8	8	9
0°	2	2	3	4	4	5	6	7	8	8	9
-1.25°	2	2	3	4	4	5	6	7	8	8	9
-2.5°	2	2	3	4	4	5	6	7	8	8	9
-3.75°	2	2	3	3	4	5	6	7	8	8	9
-5°	2	2	3	3	4	5	6	7	8	8	9
-6.25°	2	2	3	3	4	5	6	7	8	8	9
-7.5°	2	2	3	3	4	5	6	7	8	8	9
-8.75°	2	2	3	3	4	5	6	7	8	8	9
-10°	2	2	3	3	4	5	6	7	8	8	9
-11.25°	2	2	2	3	4	5	6	7	7	8	9
-12.5°	2	2	2	3	4	5	6	6	7	8	8
-13.75°	1	2	2	3	4	5	5	6	7	8	8
-15°	1	2	2	3	4	4	5	6	7	8	8
-16.25°	1	2	2	3	3	4	5	6	7	8	8
-17.5°	1	2	2	3	3	4	5	6	7	7	8
-18.75°	1	2	2	2	3	4	5	6	6	7	8
-20°	1	2	2	2	3	4	4	5	6	7	8
-21.25°	1	1	2	2	3	4	4	5	6	7	7



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	1	2	2	3	3	4	5	6	6	7
-23.75°	1	1	2	2	3	3	4	5	5	6	7
-25°	1	1	2	2	2	3	4	4	5	6	7
-26.25°	1	1	1	2	2	3	3	4	5	6	6
-27.5°	1	1	1	2	2	3	3	4	5	5	6
-28.75°	1	1	1	2	2	2	3	4	4	5	6
-30°	1	1	1	2	2	2	3	3	4	5	5
-31.25°	1	1	1	1	2	2	2	3	4	4	5
-32.5°	1	1	1	1	2	2	2	3	3	4	5
-33.75°	1	1	1	1	1	2	2	3	3	4	4
-35°	1	1	1	1	1	2	2	2	3	3	4
-36.25°	1	1	1	1	1	1	2	2	2	3	4
-37.5°	1	1	1	1	1	1	2	2	2	3	3
-38.75°	1	1	1	1	1	1	1	2	2	2	3
-40°	1	1	1	1	1	1	1	2	2	2	3
-41.25°	1	1	1	1	1	1	1	1	2	2	2
-42.5°	1	1	1	1	1	1	1	1	2	2	2
-43.75°	1	1	1	1	1	1	1	1	1	2	2
-45°	1	1	1	1	1	1	1	1	1	1	2
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	0	1	1	1	1	1	1	1	1	1	1
-53.75°	0	1	1	1	1	1	1	1	1	1	1
-55°	0	0	1	1	1	1	1	1	1	1	1
-56.25°	0	0	0	1	1	1	1	1	1	1	1
-57.5°	0	0	0	0	1	1	1	1	1	1	1
-58.75°	0	0	0	0	0	1	1	1	1	1	1
-60°	0	0	0	0	0	0	1	1	1	1	1
-61.25°	0	0	0	0	0	0	0	1	1	1	1
-62.5°	0	0	0	0	0	0	0	0	0	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	1	1	1
67.5°	0	0	0	0	0	0	1	1	1	1	1
66.25°	0	0	0	1	1	1	1	1	1	1	1
65°	0	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	2	2
53.75°	1	1	1	1	1	1	1	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	1	2	2	2	2	2	3	3
50°	1	1	1	2	2	2	2	3	3	3	4
48.75°	1	1	2	2	2	2	3	3	3	4	4
47.5°	1	2	2	2	2	3	3	3	4	4	5
46.25°	2	2	2	2	3	3	4	4	4	5	5
45°	2	2	2	3	3	4	4	5	5	6	6
43.75°	2	2	3	3	4	4	5	5	6	6	7
42.5°	2	3	3	4	4	5	5	6	6	7	7
41.25°	3	3	4	4	5	5	6	6	7	7	8
40°	3	3	4	5	5	6	6	7	7	8	8
38.75°	3	4	4	5	6	6	7	7	8	8	9
37.5°	4	4	5	6	6	7	7	8	8	9	9
36.25°	4	5	5	6	7	7	8	8	9	9	9
35°	5	5	6	6	7	8	8	8	9	9	10



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	5	6	6	7	8	8	8	9	9	10	11
32.5°	5	6	7	7	8	8	9	9	10	11	12
31.25°	6	6	7	8	8	9	9	10	11	12	12
30°	6	7	7	8	8	9	10	11	11	12	12
28.75°	6	7	8	8	9	9	10	11	12	12	12
27.5°	7	8	8	8	9	10	11	12	12	12	13
26.25°	7	8	8	9	9	10	11	12	12	13	13
25°	7	8	8	9	10	11	12	12	12	13	14
23.75°	8	8	9	9	10	11	12	12	13	14	14
22.5°	8	8	9	10	11	12	12	12	13	14	14
21.25°	8	9	9	10	11	12	12	13	14	14	15
20°	8	9	9	11	12	12	12	13	14	14	15
18.75°	8	9	10	11	12	12	13	13	14	15	15
17.5°	9	9	10	11	12	12	13	14	14	15	15
16.25°	9	9	11	12	12	12	13	14	15	15	16
15°	9	10	11	12	12	13	14	14	15	15	16
13.75°	9	10	11	12	12	13	14	14	15	16	17
12.5°	9	10	11	12	12	13	14	15	15	16	17
11.25°	9	10	12	12	12	13	14	15	15	16	17
10°	9	11	12	12	13	14	14	15	15	17	18
8.75°	10	11	12	12	13	14	14	15	16	17	18
7.5°	10	11	12	12	13	14	14	15	16	17	18
6.25°	10	11	12	12	13	14	15	15	16	17	18
5°	10	11	12	12	13	14	15	15	16	17	18
3.75°	10	11	12	12	13	14	15	15	16	18	18
2.5°	10	11	12	12	13	14	15	15	16	18	18
1.25°	10	11	12	12	13	14	15	15	16	18	18
0°	10	12	12	12	13	14	15	15	16	18	18
-1.25°	10	11	12	12	13	14	15	15	16	18	18
-2.5°	10	11	12	12	13	14	15	15	16	18	18
-3.75°	10	11	12	12	13	14	15	15	16	18	18
-5°	10	11	12	12	13	14	15	15	16	17	18
-6.25°	10	11	12	12	13	14	15	15	16	17	18
-7.5°	10	11	12	12	13	14	14	15	16	17	18
-8.75°	10	11	12	12	13	14	14	15	16	17	18
-10°	9	11	12	12	13	14	14	15	15	17	18
-11.25°	9	10	12	12	12	13	14	15	15	16	17
-12.5°	9	10	11	12	12	13	14	15	15	16	17
-13.75°	9	10	11	12	12	13	14	14	15	16	17
-15°	9	10	11	12	12	13	14	14	15	15	16
-16.25°	9	9	11	12	12	12	13	14	15	15	16
-17.5°	9	9	10	11	12	12	13	14	14	15	15
-18.75°	8	9	10	11	12	12	13	13	14	15	15
-20°	8	9	9	11	12	12	12	13	14	14	15
-21.25°	8	9	9	10	11	12	12	13	14	14	15



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	8	8	9	10	11	12	12	12	13	14	14
-23.75°	8	8	9	9	10	11	12	12	13	14	14
-25°	7	8	8	9	10	11	12	12	12	13	14
-26.25°	7	8	8	9	9	10	11	12	12	13	13
-27.5°	7	8	8	8	9	10	11	12	12	12	13
-28.75°	6	7	8	8	9	9	10	11	12	12	12
-30°	6	7	7	8	8	9	10	11	11	12	12
-31.25°	6	6	7	8	8	9	9	10	11	12	12
-32.5°	5	6	7	7	8	8	9	9	10	11	12
-33.75°	5	6	6	7	8	8	8	9	9	10	11
-35°	5	5	6	6	7	8	8	8	9	9	10
-36.25°	4	5	5	6	7	7	8	8	9	9	9
-37.5°	4	4	5	6	6	7	7	8	8	9	9
-38.75°	3	4	4	5	6	6	7	7	8	8	9
-40°	3	3	4	5	5	6	6	7	7	8	8
-41.25°	3	3	4	4	5	5	6	6	7	7	8
-42.5°	2	3	3	4	4	5	5	6	6	7	7
-43.75°	2	2	3	3	4	4	5	5	6	6	7
-45°	2	2	2	3	3	4	4	5	5	6	6
-46.25°	2	2	2	2	3	3	4	4	4	5	5
-47.5°	1	2	2	2	2	3	3	3	4	4	5
-48.75°	1	1	2	2	2	2	3	3	3	4	4
-50°	1	1	1	2	2	2	2	3	3	3	4
-51.25°	1	1	1	1	2	2	2	2	2	3	3
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	1	2	2	2	2
-55°	1	1	1	1	1	1	1	1	1	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	0	1	1	1	1	1	1	1	1
-67.5°	0	0	0	0	0	0	1	1	1	1	1
-68.75°	0	0	0	0	0	0	0	0	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	1	1	1	1	1
70°	0	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	2	2	2
58.75°	1	1	1	1	2	2	2	2	2	2	2
57.5°	1	1	2	2	2	2	2	2	2	3	3
56.25°	2	2	2	2	2	2	3	3	3	3	3
55°	2	2	2	2	3	3	3	3	4	4	4
53.75°	2	3	3	3	3	4	4	4	4	5	5
52.5°	3	3	3	4	4	4	5	5	5	5	6
51.25°	3	4	4	4	5	5	5	6	6	6	6
50°	4	4	5	5	5	6	6	6	7	7	7
48.75°	5	5	5	6	6	6	7	7	7	8	8
47.5°	5	6	6	6	7	7	8	8	8	8	8
46.25°	6	6	7	7	7	8	8	8	8	9	9
45°	6	7	7	8	8	8	8	9	9	9	10
43.75°	7	8	8	8	8	9	9	9	10	10	11
42.5°	8	8	8	9	9	9	10	10	11	11	12
41.25°	8	8	9	9	10	10	11	11	12	12	12
40°	8	9	9	10	11	11	12	12	12	12	12
38.75°	9	9	10	11	11	12	12	12	12	13	13
37.5°	9	10	11	12	12	12	12	13	13	14	14
36.25°	10	11	12	12	12	12	13	13	14	14	14
35°	11	12	12	12	13	13	14	14	14	15	15



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	12	12	12	13	13	14	14	14	15	15	15
32.5°	12	12	13	13	14	14	15	15	15	16	16
31.25°	12	13	13	14	14	15	15	15	16	17	17
30°	13	13	14	14	15	15	15	16	17	18	18
28.75°	13	14	14	15	15	15	16	17	18	18	18
27.5°	14	14	15	15	15	16	17	18	18	18	19
26.25°	14	14	15	15	16	17	18	18	18	19	19
25°	14	15	15	16	17	18	18	18	19	19	20
23.75°	15	15	16	17	18	18	18	19	19	20	21
22.5°	15	15	16	17	18	18	19	19	20	21	21
21.25°	15	16	17	18	18	19	19	20	20	21	22
20°	15	17	18	18	18	19	20	20	21	22	23
18.75°	16	17	18	18	19	19	20	21	22	22	24
17.5°	17	18	18	18	19	20	21	21	22	23	25
16.25°	17	18	18	19	19	20	21	22	23	24	26
15°	17	18	18	19	20	21	21	22	24	25	27
13.75°	18	18	19	19	20	21	22	23	25	26	28
12.5°	18	18	19	20	21	21	22	24	25	27	28
11.25°	18	18	19	20	21	22	23	24	26	28	29
10°	18	19	19	20	21	22	23	25	27	28	30
8.75°	18	19	20	21	21	22	24	26	27	29	32
7.5°	18	19	20	21	22	23	24	26	28	30	33
6.25°	18	19	20	21	22	23	25	27	28	31	33
5°	18	19	20	21	22	23	25	27	29	31	34
3.75°	19	19	20	21	22	24	25	27	29	32	35
2.5°	19	19	20	21	22	24	26	27	29	32	35
1.25°	19	19	20	21	22	24	26	27	29	32	35
0°	19	20	20	21	22	24	26	28	29	32	36
-1.25°	19	19	20	21	22	24	26	27	29	32	35
-2.5°	19	19	20	21	22	24	26	27	29	32	35
-3.75°	19	19	20	21	22	24	25	27	29	32	35
-5°	18	19	20	21	22	23	25	27	29	31	34
-6.25°	18	19	20	21	22	23	25	27	28	31	33
-7.5°	18	19	20	21	22	23	24	26	28	30	33
-8.75°	18	19	20	21	21	22	24	26	27	29	32
-10°	18	19	19	20	21	22	23	25	27	28	30
-11.25°	18	18	19	20	21	22	23	24	26	28	29
-12.5°	18	18	19	20	21	21	22	24	25	27	28
-13.75°	18	18	19	19	20	21	22	23	25	26	28
-15°	17	18	18	19	20	21	21	22	24	25	27
-16.25°	17	18	18	19	19	20	21	22	23	24	26
-17.5°	17	18	18	18	19	20	21	21	22	23	25
-18.75°	16	17	18	18	19	19	20	21	22	22	24
-20°	15	17	18	18	18	19	20	20	21	22	23
-21.25°	15	16	17	18	18	19	19	20	20	21	22



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	15	15	16	17	18	18	19	19	20	21	21
-23.75°	15	15	16	17	18	18	18	19	19	20	21
-25°	14	15	15	16	17	18	18	18	19	19	20
-26.25°	14	14	15	15	16	17	18	18	18	19	19
-27.5°	14	14	15	15	15	16	17	18	18	18	19
-28.75°	13	14	14	15	15	15	16	17	18	18	18
-30°	13	13	14	14	15	15	15	16	17	18	18
-31.25°	12	13	13	14	14	15	15	15	16	17	17
-32.5°	12	12	13	13	14	14	15	15	15	16	16
-33.75°	12	12	12	13	13	14	14	14	15	15	15
-35°	11	12	12	12	13	13	14	14	14	15	15
-36.25°	10	11	12	12	12	12	13	13	14	14	14
-37.5°	9	10	11	12	12	12	12	13	13	14	14
-38.75°	9	9	10	11	11	12	12	12	12	13	13
-40°	8	9	9	10	11	11	12	12	12	12	12
-41.25°	8	8	9	9	10	10	11	11	12	12	12
-42.5°	8	8	8	9	9	9	10	10	11	11	12
-43.75°	7	8	8	8	8	9	9	9	10	10	11
-45°	6	7	7	8	8	8	8	9	9	9	10
-46.25°	6	6	7	7	7	8	8	8	8	9	9
-47.5°	5	6	6	6	7	7	8	8	8	8	8
-48.75°	5	5	5	6	6	6	7	7	7	8	8
-50°	4	4	5	5	5	6	6	6	7	7	7
-51.25°	3	4	4	4	5	5	5	6	6	6	6
-52.5°	3	3	3	4	4	4	5	5	5	5	6
-53.75°	2	3	3	3	3	4	4	4	4	5	5
-55°	2	2	2	2	3	3	3	3	4	4	4
-56.25°	2	2	2	2	2	2	3	3	3	3	3
-57.5°	1	1	2	2	2	2	2	2	2	3	3
-58.75°	1	1	1	1	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	1	1	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	1	1	1	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	2	2	2	2
61.25°	1	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	3	3
58.75°	2	2	2	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	4	4	4	4	4	4
56.25°	4	4	4	4	4	4	5	5	5	5	5
55°	4	4	5	5	5	5	5	6	6	6	6
53.75°	5	5	6	6	6	6	6	6	7	7	7
52.5°	6	6	6	7	7	7	7	7	7	8	8
51.25°	7	7	7	7	8	8	8	8	8	8	8
50°	7	8	8	8	8	8	8	8	9	9	9
48.75°	8	8	8	9	9	9	9	9	9	9	10
47.5°	9	9	9	9	9	10	10	10	10	11	11
46.25°	9	9	10	10	11	11	11	11	12	12	12
45°	10	11	11	11	12	12	12	12	12	12	12
43.75°	11	12	12	12	12	12	12	12	12	13	13
42.5°	12	12	12	12	12	13	13	13	13	14	14
41.25°	12	12	13	13	13	14	14	14	14	14	14
40°	13	13	13	14	14	14	14	15	15	15	15
38.75°	14	14	14	14	15	15	15	15	15	15	16
37.5°	14	14	15	15	15	15	16	16	16	17	17
36.25°	15	15	15	15	16	16	17	17	17	18	18
35°	15	15	16	17	17	17	18	18	18	18	18



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	16	17	17	18	18	18	18	18	18	19	19
32.5°	17	18	18	18	18	18	19	19	19	19	20
31.25°	18	18	18	18	19	19	19	20	20	20	21
30°	18	18	19	19	19	20	20	21	21	21	21
28.75°	19	19	19	20	20	21	21	21	22	22	22
27.5°	19	20	20	21	21	21	22	22	23	23	24
26.25°	20	20	21	21	22	22	23	24	24	25	26
25°	20	21	22	22	23	24	25	25	26	27	27
23.75°	21	22	22	23	24	25	26	27	28	28	29
22.5°	22	23	24	25	26	27	28	28	29	30	32
21.25°	23	24	25	26	27	28	29	31	32	33	34
20°	24	25	26	27	28	30	32	33	35	37	39
18.75°	25	26	27	29	30	32	34	36	39	42	44
17.5°	26	27	29	30	33	35	37	41	44	47	53
16.25°	27	28	30	33	35	38	42	45	51	58	65
15°	28	30	32	35	38	42	46	53	62	70	78
13.75°	29	32	34	37	42	46	54	64	73	83	92
12.5°	31	33	36	41	45	53	64	74	85	96	105
11.25°	32	35	39	44	51	62	73	85	97	108	128
10°	33	37	42	47	58	70	83	96	108	131	153
8.75°	34	39	44	53	65	78	92	105	128	153	183
7.5°	36	41	46	58	71	85	100	120	147	174	243
6.25°	37	43	50	63	77	92	107	135	163	223	297
5°	39	44	54	68	82	98	118	148	186	266	344
3.75°	40	45	57	71	86	102	128	158	218	302	455
2.5°	41	46	59	73	89	106	134	166	241	328	545
1.25°	41	47	61	75	91	108	139	170	256	344	635
0°	41	47	61	75	92	108	140	172	261	349	672
-1.25°	41	47	61	75	91	108	139	170	256	344	635
-2.5°	41	46	59	73	89	106	134	166	241	328	545
-3.75°	40	45	57	71	86	102	128	158	218	302	455
-5°	39	44	54	68	82	98	118	148	186	266	344
-6.25°	37	43	50	63	77	92	107	135	163	223	297
-7.5°	36	41	46	58	71	85	100	120	147	174	243
-8.75°	34	39	44	53	65	78	92	105	128	153	183
-10°	33	37	42	47	58	70	83	96	108	131	153
-11.25°	32	35	39	44	51	62	73	85	97	108	128
-12.5°	31	33	36	41	45	53	64	74	85	96	105
-13.75°	29	32	34	37	42	46	54	64	73	83	92
-15°	28	30	32	35	38	42	46	53	62	70	78
-16.25°	27	28	30	33	35	38	42	45	51	58	65
-17.5°	26	27	29	30	33	35	37	41	44	47	53
-18.75°	25	26	27	29	30	32	34	36	39	42	44
-20°	24	25	26	27	28	30	32	33	35	37	39
-21.25°	23	24	25	26	27	28	29	31	32	33	34



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	22	23	24	25	26	27	28	28	29	30	32
-23.75°	21	22	22	23	24	25	26	27	28	28	29
-25°	20	21	22	22	23	24	25	25	26	27	27
-26.25°	20	20	21	21	22	22	23	24	24	25	26
-27.5°	19	20	20	21	21	21	22	22	23	23	24
-28.75°	19	19	19	20	20	21	21	21	22	22	22
-30°	18	18	19	19	19	20	20	21	21	21	21
-31.25°	18	18	18	18	19	19	19	20	20	20	21
-32.5°	17	18	18	18	18	18	19	19	19	19	20
-33.75°	16	17	17	18	18	18	18	18	18	19	19
-35°	15	15	16	17	17	17	18	18	18	18	18
-36.25°	15	15	15	15	16	16	17	17	17	18	18
-37.5°	14	14	15	15	15	15	16	16	16	17	17
-38.75°	14	14	14	14	15	15	15	15	15	15	16
-40°	13	13	13	14	14	14	14	15	15	15	15
-41.25°	12	12	13	13	13	14	14	14	14	14	14
-42.5°	12	12	12	12	12	13	13	13	13	14	14
-43.75°	11	12	12	12	12	12	12	12	12	13	13
-45°	10	11	11	11	12	12	12	12	12	12	12
-46.25°	9	9	10	10	11	11	11	11	12	12	12
-47.5°	9	9	9	9	9	10	10	10	10	11	11
-48.75°	8	8	8	9	9	9	9	9	9	9	10
-50°	7	8	8	8	8	8	8	8	9	9	9
-51.25°	7	7	7	7	8	8	8	8	8	8	8
-52.5°	6	6	6	7	7	7	7	7	7	8	8
-53.75°	5	5	6	6	6	6	6	6	7	7	7
-55°	4	4	5	5	5	5	5	6	6	6	6
-56.25°	4	4	4	4	4	4	5	5	5	5	5
-57.5°	3	3	3	3	3	4	4	4	4	4	4
-58.75°	2	2	2	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	2	2	2	2	3	3
-61.25°	1	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	0	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	4	4	4	4	4	3	3
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	5	5	5	5	5	5	5	5	5	5	5
55°	6	6	6	6	6	6	6	6	6	6	6
53.75°	7	7	7	7	7	7	7	7	7	7	7
52.5°	8	8	8	8	8	8	8	8	8	8	8
51.25°	8	8	8	8	8	8	8	8	8	8	8
50°	9	9	9	9	9	9	9	9	9	9	9
48.75°	10	10	10	10	10	10	10	10	10	10	10
47.5°	11	11	11	11	11	11	12	11	11	11	11
46.25°	12	12	12	12	12	12	12	12	12	12	12
45°	12	12	12	12	12	12	12	12	12	12	12
43.75°	13	13	13	13	13	13	13	13	13	13	13
42.5°	14	14	14	14	14	14	14	14	14	14	14
41.25°	14	15	15	15	15	15	15	15	15	15	15
40°	15	15	15	15	15	15	15	15	15	15	15
38.75°	16	16	16	16	16	16	16	16	16	16	16
37.5°	17	17	17	18	18	18	18	18	18	18	17
36.25°	18	18	18	18	18	18	18	18	18	18	18
35°	18	18	18	19	19	19	19	19	19	19	18



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	19	19	19	19	19	19	20	19	19	19	19
32.5°	20	20	20	20	20	20	20	20	20	20	20
31.25°	21	21	21	21	21	21	21	21	21	21	21
30°	22	22	22	22	22	22	22	22	22	22	22
28.75°	23	23	23	24	24	24	24	24	24	24	23
27.5°	24	25	25	25	26	26	26	26	26	25	25
26.25°	26	27	27	27	27	27	28	27	27	27	27
25°	28	28	29	29	29	29	29	29	29	29	29
23.75°	30	31	31	32	32	32	32	32	32	32	31
22.5°	33	33	34	35	35	35	36	35	35	35	34
21.25°	36	37	39	40	41	41	41	41	41	40	39
20°	41	43	44	45	46	47	47	47	46	45	44
18.75°	46	50	54	57	59	61	61	61	59	57	54
17.5°	58	63	68	71	73	75	75	75	73	71	68
16.25°	71	77	82	86	89	91	92	91	89	86	82
15°	85	92	98	102	106	108	108	108	106	102	98
13.75°	100	107	118	128	134	139	140	139	134	128	118
12.5°	120	135	148	158	166	170	172	170	166	158	148
11.25°	147	163	186	218	241	256	261	256	241	218	186
10°	174	223	266	302	328	344	349	344	328	302	266
8.75°	243	297	344	455	545	635	672	635	545	455	344
7.5°	307	403	565	829	1055	1255	1324	1255	1055	829	565
6.25°	403	639	992	1467	1862	2133	2227	2133	1862	1467	992
5°	565	992	1613	2229	2691	2982	3085	2982	2691	2229	1613
3.75°	829	1467	2229	2884	3352	3645	3725	3645	3352	2884	2229
2.5°	1055	1862	2691	3352	3810	4073	4149	4073	3810	3352	2691
1.25°	1255	2133	2982	3645	4073	4310	4384	4310	4073	3645	2982
0°	1324	2227	3085	3725	4149	4384	4479	4384	4149	3725	3085
-1.25°	1255	2133	2982	3645	4073	4310	4384	4310	4073	3645	2982
-2.5°	1055	1862	2691	3352	3810	4073	4149	4073	3810	3352	2691
-3.75°	829	1467	2229	2884	3352	3645	3725	3645	3352	2884	2229
-5°	565	992	1613	2229	2691	2982	3085	2982	2691	2229	1613
-6.25°	403	639	992	1467	1862	2133	2227	2133	1862	1467	992
-7.5°	307	403	565	829	1055	1255	1324	1255	1055	829	565
-8.75°	243	297	344	455	545	635	672	635	545	455	344
-10°	174	223	266	302	328	344	349	344	328	302	266
-11.25°	147	163	186	218	241	256	261	256	241	218	186
-12.5°	120	135	148	158	166	170	172	170	166	158	148
-13.75°	100	107	118	128	134	139	140	139	134	128	118
-15°	85	92	98	102	106	108	108	108	106	102	98
-16.25°	71	77	82	86	89	91	92	91	89	86	82
-17.5°	58	63	68	71	73	75	75	75	73	71	68
-18.75°	46	50	54	57	59	61	61	61	59	57	54
-20°	41	43	44	45	46	47	47	47	46	45	44
-21.25°	36	37	39	40	41	41	41	41	41	40	39



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	33	33	34	35	35	35	36	35	35	35	34
-23.75°	30	31	31	32	32	32	32	32	32	32	31
-25°	28	28	29	29	29	29	29	29	29	29	29
-26.25°	26	27	27	27	27	27	28	27	27	27	27
-27.5°	24	25	25	25	26	26	26	26	26	25	25
-28.75°	23	23	23	24	24	24	24	24	24	24	23
-30°	22	22	22	22	22	22	22	22	22	22	22
-31.25°	21	21	21	21	21	21	21	21	21	21	21
-32.5°	20	20	20	20	20	20	20	20	20	20	20
-33.75°	19	19	19	19	19	19	20	19	19	19	19
-35°	18	18	18	19	19	19	19	19	19	19	18
-36.25°	18	18	18	18	18	18	18	18	18	18	18
-37.5°	17	17	17	18	18	18	18	18	18	18	17
-38.75°	16	16	16	16	16	16	16	16	16	16	16
-40°	15	15	15	15	15	15	15	15	15	15	15
-41.25°	14	15	15	15	15	15	15	15	15	15	15
-42.5°	14	14	14	14	14	14	14	14	14	14	14
-43.75°	13	13	13	13	13	13	13	13	13	13	13
-45°	12	12	12	12	12	12	12	12	12	12	12
-46.25°	12	12	12	12	12	12	12	12	12	12	12
-47.5°	11	11	11	11	11	11	12	11	11	11	11
-48.75°	10	10	10	10	10	10	10	10	10	10	10
-50°	9	9	9	9	9	9	9	9	9	9	9
-51.25°	8	8	8	8	8	8	8	8	8	8	8
-52.5°	8	8	8	8	8	8	8	8	8	8	8
-53.75°	7	7	7	7	7	7	7	7	7	7	7
-55°	6	6	6	6	6	6	6	6	6	6	6
-56.25°	5	5	5	5	5	5	5	5	5	5	5
-57.5°	4	4	4	4	4	4	4	4	4	4	4
-58.75°	3	3	3	3	4	4	4	4	4	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	2	2	2	2	2	2	2
58.75°	3	3	3	3	3	3	3	3	3	3	2
57.5°	4	4	4	4	4	4	4	4	3	3	3
56.25°	5	5	5	5	5	5	5	4	4	4	4
55°	6	6	6	6	6	6	5	5	5	5	5
53.75°	7	7	7	7	7	6	6	6	6	6	6
52.5°	8	8	8	8	7	7	7	7	7	7	6
51.25°	8	8	8	8	8	8	8	8	8	7	7
50°	9	9	9	9	9	8	8	8	8	8	8
48.75°	10	10	10	9	9	9	9	9	9	9	8
47.5°	11	11	11	11	10	10	10	10	9	9	9
46.25°	12	12	12	12	12	11	11	11	11	10	10
45°	12	12	12	12	12	12	12	12	12	11	11
43.75°	13	13	13	13	12	12	12	12	12	12	12
42.5°	14	14	14	14	13	13	13	13	12	12	12
41.25°	15	14	14	14	14	14	14	14	13	13	13
40°	15	15	15	15	15	15	14	14	14	14	13
38.75°	16	16	16	15	15	15	15	15	15	14	14
37.5°	17	17	17	17	16	16	16	15	15	15	15
36.25°	18	18	18	18	17	17	17	16	16	15	15
35°	18	18	18	18	18	18	18	17	17	17	16



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	19	19	19	19	18	18	18	18	18	18	17
32.5°	20	20	20	19	19	19	19	18	18	18	18
31.25°	21	21	21	20	20	20	19	19	19	18	18
30°	22	22	21	21	21	21	20	20	19	19	19
28.75°	23	23	22	22	22	21	21	21	20	20	19
27.5°	25	24	24	23	23	22	22	21	21	21	20
26.25°	27	26	26	25	24	24	23	22	22	21	21
25°	28	28	27	27	26	25	25	24	23	22	22
23.75°	31	30	29	28	28	27	26	25	24	23	22
22.5°	33	33	32	30	29	28	28	27	26	25	24
21.25°	37	36	34	33	32	31	29	28	27	26	25
20°	43	41	39	37	35	33	32	30	28	27	26
18.75°	50	46	44	42	39	36	34	32	30	29	27
17.5°	63	58	53	47	44	41	37	35	33	30	29
16.25°	77	71	65	58	51	45	42	38	35	33	30
15°	92	85	78	70	62	53	46	42	38	35	32
13.75°	107	100	92	83	73	64	54	46	42	37	34
12.5°	135	120	105	96	85	74	64	53	45	41	36
11.25°	163	147	128	108	97	85	73	62	51	44	39
10°	223	174	153	131	108	96	83	70	58	47	42
8.75°	297	243	183	153	128	105	92	78	65	53	44
7.5°	403	307	243	174	147	120	100	85	71	58	46
6.25°	639	403	297	223	163	135	107	92	77	63	50
5°	992	565	344	266	186	148	118	98	82	68	54
3.75°	1467	829	455	302	218	158	128	102	86	71	57
2.5°	1862	1055	545	328	241	166	134	106	89	73	59
1.25°	2133	1255	635	344	256	170	139	108	91	75	61
0°	2227	1324	672	349	261	172	140	108	92	75	61
-1.25°	2133	1255	635	344	256	170	139	108	91	75	61
-2.5°	1862	1055	545	328	241	166	134	106	89	73	59
-3.75°	1467	829	455	302	218	158	128	102	86	71	57
-5°	992	565	344	266	186	148	118	98	82	68	54
-6.25°	639	403	297	223	163	135	107	92	77	63	50
-7.5°	403	307	243	174	147	120	100	85	71	58	46
-8.75°	297	243	183	153	128	105	92	78	65	53	44
-10°	223	174	153	131	108	96	83	70	58	47	42
-11.25°	163	147	128	108	97	85	73	62	51	44	39
-12.5°	135	120	105	96	85	74	64	53	45	41	36
-13.75°	107	100	92	83	73	64	54	46	42	37	34
-15°	92	85	78	70	62	53	46	42	38	35	32
-16.25°	77	71	65	58	51	45	42	38	35	33	30
-17.5°	63	58	53	47	44	41	37	35	33	30	29
-18.75°	50	46	44	42	39	36	34	32	30	29	27
-20°	43	41	39	37	35	33	32	30	28	27	26
-21.25°	37	36	34	33	32	31	29	28	27	26	25



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	33	33	32	30	29	28	28	27	26	25	24
-23.75°	31	30	29	28	28	27	26	25	24	23	22
-25°	28	28	27	27	26	25	25	24	23	22	22
-26.25°	27	26	26	25	24	24	23	22	22	21	21
-27.5°	25	24	24	23	23	22	22	21	21	21	20
-28.75°	23	23	22	22	22	21	21	21	20	20	19
-30°	22	22	21	21	21	21	20	20	19	19	19
-31.25°	21	21	21	20	20	20	19	19	19	18	18
-32.5°	20	20	20	19	19	19	19	18	18	18	18
-33.75°	19	19	19	19	18	18	18	18	18	18	17
-35°	18	18	18	18	18	18	18	17	17	17	16
-36.25°	18	18	18	18	17	17	17	16	16	15	15
-37.5°	17	17	17	17	16	16	16	15	15	15	15
-38.75°	16	16	16	15	15	15	15	15	15	14	14
-40°	15	15	15	15	15	15	14	14	14	14	13
-41.25°	15	14	14	14	14	14	14	14	13	13	13
-42.5°	14	14	14	14	13	13	13	13	12	12	12
-43.75°	13	13	13	13	12	12	12	12	12	12	12
-45°	12	12	12	12	12	12	12	12	12	11	11
-46.25°	12	12	12	12	12	11	11	11	11	10	10
-47.5°	11	11	11	11	10	10	10	10	9	9	9
-48.75°	10	10	10	9	9	9	9	9	9	9	8
-50°	9	9	9	9	9	8	8	8	8	8	8
-51.25°	8	8	8	8	8	8	8	8	8	7	7
-52.5°	8	8	8	8	7	7	7	7	7	7	6
-53.75°	7	7	7	7	7	6	6	6	6	6	6
-55°	6	6	6	6	6	6	5	5	5	5	5
-56.25°	5	5	5	5	5	5	5	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	2
-60°	3	3	3	3	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	0	0	0	0	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	1	1	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	1	1	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	1	1
57.5°	3	3	3	3	2	2	2	2	2	2	2
56.25°	4	4	3	3	3	3	3	2	2	2	2
55°	4	4	4	4	4	3	3	3	3	2	2
53.75°	5	5	5	5	4	4	4	4	3	3	3
52.5°	6	6	6	5	5	5	5	4	4	4	3
51.25°	7	7	6	6	6	6	5	5	5	4	4
50°	8	7	7	7	7	6	6	6	5	5	5
48.75°	8	8	8	8	7	7	7	6	6	6	5
47.5°	9	9	8	8	8	8	8	7	7	6	6
46.25°	9	9	9	9	8	8	8	8	7	7	7
45°	11	10	10	9	9	9	8	8	8	8	7
43.75°	12	11	11	10	10	9	9	9	8	8	8
42.5°	12	12	12	11	11	10	10	9	9	9	8
41.25°	12	12	12	12	12	11	11	10	10	9	9
40°	13	13	12	12	12	12	12	11	11	10	9
38.75°	14	14	13	13	12	12	12	12	11	11	10
37.5°	14	14	14	14	13	13	12	12	12	12	11
36.25°	15	15	14	14	14	13	13	12	12	12	12
35°	15	15	15	15	14	14	14	13	13	12	12



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	17	16	15	15	15	14	14	14	13	13	12
32.5°	18	17	16	16	15	15	15	14	14	13	13
31.25°	18	18	17	17	16	15	15	15	14	14	13
30°	18	18	18	18	17	16	15	15	15	14	14
28.75°	19	19	18	18	18	17	16	15	15	15	14
27.5°	20	19	19	18	18	18	17	16	15	15	15
26.25°	20	20	19	19	18	18	18	17	16	15	15
25°	21	20	20	19	19	18	18	18	17	16	15
23.75°	22	21	21	20	19	19	18	18	18	17	16
22.5°	23	22	21	21	20	19	19	18	18	17	16
21.25°	24	23	22	21	20	20	19	19	18	18	17
20°	25	24	23	22	21	20	20	19	18	18	18
18.75°	26	25	24	22	22	21	20	19	19	18	18
17.5°	27	26	25	23	22	21	21	20	19	18	18
16.25°	28	27	26	24	23	22	21	20	19	19	18
15°	30	28	27	25	24	22	21	21	20	19	18
13.75°	32	29	28	26	25	23	22	21	20	19	19
12.5°	33	31	28	27	25	24	22	21	21	20	19
11.25°	35	32	29	28	26	24	23	22	21	20	19
10°	37	33	30	28	27	25	23	22	21	20	19
8.75°	39	34	32	29	27	26	24	22	21	21	20
7.5°	41	36	33	30	28	26	24	23	22	21	20
6.25°	43	37	33	31	28	27	25	23	22	21	20
5°	44	39	34	31	29	27	25	23	22	21	20
3.75°	45	40	35	32	29	27	25	24	22	21	20
2.5°	46	41	35	32	29	27	26	24	22	21	20
1.25°	47	41	35	32	29	27	26	24	22	21	20
0°	47	41	36	32	29	28	26	24	22	21	20
-1.25°	47	41	35	32	29	27	26	24	22	21	20
-2.5°	46	41	35	32	29	27	26	24	22	21	20
-3.75°	45	40	35	32	29	27	25	24	22	21	20
-5°	44	39	34	31	29	27	25	23	22	21	20
-6.25°	43	37	33	31	28	27	25	23	22	21	20
-7.5°	41	36	33	30	28	26	24	23	22	21	20
-8.75°	39	34	32	29	27	26	24	22	21	21	20
-10°	37	33	30	28	27	25	23	22	21	20	19
-11.25°	35	32	29	28	26	24	23	22	21	20	19
-12.5°	33	31	28	27	25	24	22	21	21	20	19
-13.75°	32	29	28	26	25	23	22	21	20	19	19
-15°	30	28	27	25	24	22	21	21	20	19	18
-16.25°	28	27	26	24	23	22	21	20	19	19	18
-17.5°	27	26	25	23	22	21	21	20	19	18	18
-18.75°	26	25	24	22	22	21	20	19	19	18	18
-20°	25	24	23	22	21	20	20	19	18	18	18
-21.25°	24	23	22	21	20	20	19	19	18	18	17



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	23	22	21	21	20	19	19	18	18	17	16
-23.75°	22	21	21	20	19	19	18	18	18	17	16
-25°	21	20	20	19	19	18	18	18	17	16	15
-26.25°	20	20	19	19	18	18	18	17	16	15	15
-27.5°	20	19	19	18	18	18	17	16	15	15	15
-28.75°	19	19	18	18	18	17	16	15	15	15	14
-30°	18	18	18	18	17	16	15	15	15	14	14
-31.25°	18	18	17	17	16	15	15	15	14	14	13
-32.5°	18	17	16	16	15	15	15	14	14	13	13
-33.75°	17	16	15	15	15	14	14	14	13	13	12
-35°	15	15	15	15	14	14	14	13	13	12	12
-36.25°	15	15	14	14	14	13	13	12	12	12	12
-37.5°	14	14	14	14	13	13	12	12	12	12	11
-38.75°	14	14	13	13	12	12	12	12	11	11	10
-40°	13	13	12	12	12	12	12	11	11	10	9
-41.25°	12	12	12	12	12	11	11	10	10	9	9
-42.5°	12	12	12	11	11	10	10	9	9	9	8
-43.75°	12	11	11	10	10	9	9	9	8	8	8
-45°	11	10	10	9	9	9	8	8	8	8	7
-46.25°	9	9	9	9	8	8	8	8	7	7	7
-47.5°	9	9	8	8	8	8	8	7	7	6	6
-48.75°	8	8	8	8	7	7	7	6	6	6	5
-50°	8	7	7	7	7	6	6	6	5	5	5
-51.25°	7	7	6	6	6	6	5	5	5	4	4
-52.5°	6	6	6	5	5	5	5	4	4	4	3
-53.75°	5	5	5	5	4	4	4	4	3	3	3
-55°	4	4	4	4	4	3	3	3	3	2	2
-56.25°	4	4	3	3	3	3	3	2	2	2	2
-57.5°	3	3	3	3	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	1	1
-60°	2	2	2	2	2	1	1	1	1	1	1
-61.25°	2	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	0	0	0	0
-72.5°	1	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	1	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	0	0	0	0	0	0
67.5°	1	1	1	1	1	1	1	0	0	0	0
66.25°	1	1	1	1	1	1	1	1	1	1	0
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	2	1	1	1	1	1	1	1
53.75°	3	2	2	2	2	2	1	1	1	1	1
52.5°	3	3	2	2	2	2	2	2	1	1	1
51.25°	4	3	3	3	2	2	2	2	2	1	1
50°	4	4	4	3	3	3	2	2	2	2	1
48.75°	5	5	4	4	3	3	3	2	2	2	2
47.5°	6	5	5	4	4	3	3	3	2	2	2
46.25°	6	6	5	5	4	4	4	3	3	2	2
45°	7	6	6	6	5	5	4	4	3	3	2
43.75°	8	7	7	6	6	5	5	4	4	3	3
42.5°	8	8	7	7	6	6	5	5	4	4	3
41.25°	8	8	8	7	7	6	6	5	5	4	4
40°	9	8	8	8	7	7	6	6	5	5	4
38.75°	9	9	9	8	8	7	7	6	6	5	4
37.5°	10	9	9	9	8	8	7	7	6	6	5
36.25°	11	10	9	9	9	8	8	7	7	6	5
35°	12	11	10	9	9	8	8	8	7	6	6



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	12	12	11	10	9	9	8	8	8	7	6
32.5°	12	12	12	11	10	9	9	8	8	7	7
31.25°	13	12	12	12	11	10	9	9	8	8	7
30°	13	13	12	12	11	11	10	9	8	8	7
28.75°	14	13	12	12	12	11	10	9	9	8	8
27.5°	14	14	13	12	12	12	11	10	9	8	8
26.25°	14	14	13	13	12	12	11	10	9	9	8
25°	15	14	14	13	12	12	12	11	10	9	8
23.75°	15	15	14	14	13	12	12	11	10	9	9
22.5°	15	15	14	14	13	12	12	12	11	10	9
21.25°	16	15	15	14	14	13	12	12	11	10	9
20°	17	15	15	14	14	13	12	12	12	11	9
18.75°	17	16	15	15	14	13	13	12	12	11	10
17.5°	18	17	15	15	14	14	13	12	12	11	10
16.25°	18	17	16	15	15	14	13	12	12	12	11
15°	18	17	16	15	15	14	14	13	12	12	11
13.75°	18	18	17	16	15	14	14	13	12	12	11
12.5°	18	18	17	16	15	15	14	13	12	12	11
11.25°	18	18	17	16	15	15	14	13	12	12	12
10°	19	18	18	17	15	15	14	14	13	12	12
8.75°	19	18	18	17	16	15	14	14	13	12	12
7.5°	19	18	18	17	16	15	14	14	13	12	12
6.25°	19	18	18	17	16	15	15	14	13	12	12
5°	19	18	18	17	16	15	15	14	13	12	12
3.75°	19	19	18	18	16	15	15	14	13	12	12
2.5°	19	19	18	18	16	15	15	14	13	12	12
1.25°	19	19	18	18	16	15	15	14	13	12	12
0°	20	19	18	18	16	15	15	14	13	12	12
-1.25°	19	19	18	18	16	15	15	14	13	12	12
-2.5°	19	19	18	18	16	15	15	14	13	12	12
-3.75°	19	19	18	18	16	15	15	14	13	12	12
-5°	19	18	18	17	16	15	15	14	13	12	12
-6.25°	19	18	18	17	16	15	15	14	13	12	12
-7.5°	19	18	18	17	16	15	14	14	13	12	12
-8.75°	19	18	18	17	16	15	14	14	13	12	12
-10°	19	18	18	17	15	15	14	14	13	12	12
-11.25°	18	18	17	16	15	15	14	13	12	12	12
-12.5°	18	18	17	16	15	15	14	13	12	12	11
-13.75°	18	18	17	16	15	14	14	13	12	12	11
-15°	18	17	16	15	15	14	14	13	12	12	11
-16.25°	18	17	16	15	15	14	13	12	12	12	11
-17.5°	18	17	15	15	14	14	13	12	12	11	10
-18.75°	17	16	15	15	14	13	13	12	12	11	10
-20°	17	15	15	14	14	13	12	12	12	11	9
-21.25°	16	15	15	14	14	13	12	12	11	10	9



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	15	15	14	14	13	12	12	12	11	10	9
-23.75°	15	15	14	14	13	12	12	11	10	9	9
-25°	15	14	14	13	12	12	12	11	10	9	8
-26.25°	14	14	13	13	12	12	11	10	9	9	8
-27.5°	14	14	13	12	12	12	11	10	9	8	8
-28.75°	14	13	12	12	12	11	10	9	9	8	8
-30°	13	13	12	12	11	11	10	9	8	8	7
-31.25°	13	12	12	12	11	10	9	9	8	8	7
-32.5°	12	12	12	11	10	9	9	8	8	7	7
-33.75°	12	12	11	10	9	9	8	8	8	7	6
-35°	12	11	10	9	9	8	8	8	7	6	6
-36.25°	11	10	9	9	9	8	8	7	7	6	5
-37.5°	10	9	9	9	8	8	7	7	6	6	5
-38.75°	9	9	9	8	8	7	7	6	6	5	4
-40°	9	8	8	8	7	7	6	6	5	5	4
-41.25°	8	8	8	7	7	6	6	5	5	4	4
-42.5°	8	8	7	7	6	6	5	5	4	4	3
-43.75°	8	7	7	6	6	5	5	4	4	3	3
-45°	7	6	6	6	5	5	4	4	3	3	2
-46.25°	6	6	5	5	4	4	4	3	3	2	2
-47.5°	6	5	5	4	4	3	3	3	2	2	2
-48.75°	5	5	4	4	3	3	3	2	2	2	2
-50°	4	4	4	3	3	3	2	2	2	2	1
-51.25°	4	3	3	3	2	2	2	2	2	1	1
-52.5°	3	3	2	2	2	2	2	2	1	1	1
-53.75°	3	2	2	2	2	2	1	1	1	1	1
-55°	2	2	2	2	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	0
-67.5°	1	1	1	1	1	1	1	0	0	0	0
-68.75°	1	1	1	1	1	0	0	0	0	0	0
-70°	1	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	1	0	0	0	0	0	0	0	0
62.5°	1	1	1	1	0	0	0	0	0	0	0
61.25°	1	1	1	1	1	1	0	0	0	0	0
60°	1	1	1	1	1	1	1	0	0	0	0
58.75°	1	1	1	1	1	1	1	1	0	0	0
57.5°	1	1	1	1	1	1	1	1	1	0	0
56.25°	1	1	1	1	1	1	1	1	1	1	0
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	1	1	1	1	1	1	1	1	1	1
46.25°	2	2	1	1	1	1	1	1	1	1	1
45°	2	2	2	1	1	1	1	1	1	1	1
43.75°	2	2	2	2	1	1	1	1	1	1	1
42.5°	3	2	2	2	2	1	1	1	1	1	1
41.25°	3	3	2	2	2	1	1	1	1	1	1
40°	3	3	3	2	2	2	1	1	1	1	1
38.75°	4	3	3	2	2	2	1	1	1	1	1
37.5°	4	4	3	3	2	2	2	1	1	1	1
36.25°	5	4	4	3	2	2	2	1	1	1	1
35°	5	5	4	3	3	2	2	2	1	1	1



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	6	5	4	4	3	3	2	2	1	1	1
32.5°	6	5	5	4	3	3	2	2	2	1	1
31.25°	6	6	5	4	4	3	2	2	2	1	1
30°	7	6	5	5	4	3	3	2	2	2	1
28.75°	7	6	6	5	4	4	3	2	2	2	1
27.5°	8	7	6	5	5	4	3	3	2	2	1
26.25°	8	7	6	6	5	4	3	3	2	2	1
25°	8	7	7	6	5	4	4	3	2	2	2
23.75°	8	8	7	6	5	5	4	3	3	2	2
22.5°	8	8	7	6	6	5	4	3	3	2	2
21.25°	9	8	7	7	6	5	4	4	3	2	2
20°	9	8	8	7	6	5	4	4	3	2	2
18.75°	9	8	8	7	6	6	5	4	3	2	2
17.5°	9	9	8	7	7	6	5	4	3	3	2
16.25°	9	9	8	8	7	6	5	4	3	3	2
15°	10	9	8	8	7	6	5	4	4	3	2
13.75°	10	9	8	8	7	6	5	5	4	3	2
12.5°	10	9	8	8	7	6	6	5	4	3	2
11.25°	10	9	9	8	7	7	6	5	4	3	2
10°	11	9	9	8	8	7	6	5	4	3	3
8.75°	11	10	9	8	8	7	6	5	4	3	3
7.5°	11	10	9	8	8	7	6	5	4	3	3
6.25°	11	10	9	8	8	7	6	5	4	3	3
5°	11	10	9	8	8	7	6	5	4	3	3
3.75°	11	10	9	8	8	7	6	5	4	3	3
2.5°	11	10	9	8	8	7	6	5	4	4	3
1.25°	11	10	9	8	8	7	6	5	4	4	3
0°	12	10	9	8	8	7	6	5	4	4	3
-1.25°	11	10	9	8	8	7	6	5	4	4	3
-2.5°	11	10	9	8	8	7	6	5	4	4	3
-3.75°	11	10	9	8	8	7	6	5	4	3	3
-5°	11	10	9	8	8	7	6	5	4	3	3
-6.25°	11	10	9	8	8	7	6	5	4	3	3
-7.5°	11	10	9	8	8	7	6	5	4	3	3
-8.75°	11	10	9	8	8	7	6	5	4	3	3
-10°	11	9	9	8	8	7	6	5	4	3	3
-11.25°	10	9	9	8	7	7	6	5	4	3	2
-12.5°	10	9	8	8	7	6	6	5	4	3	2
-13.75°	10	9	8	8	7	6	5	5	4	3	2
-15°	10	9	8	8	7	6	5	4	4	3	2
-16.25°	9	9	8	8	7	6	5	4	3	3	2
-17.5°	9	9	8	7	7	6	5	4	3	3	2
-18.75°	9	8	8	7	6	6	5	4	3	2	2
-20°	9	8	8	7	6	5	4	4	3	2	2
-21.25°	9	8	7	7	6	5	4	4	3	2	2



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	8	8	7	6	6	5	4	3	3	2	2
-23.75°	8	8	7	6	5	5	4	3	3	2	2
-25°	8	7	7	6	5	4	4	3	2	2	2
-26.25°	8	7	6	6	5	4	3	3	2	2	1
-27.5°	8	7	6	5	5	4	3	3	2	2	1
-28.75°	7	6	6	5	4	4	3	2	2	2	1
-30°	7	6	5	5	4	3	3	2	2	2	1
-31.25°	6	6	5	4	4	3	2	2	2	1	1
-32.5°	6	5	5	4	3	3	2	2	2	1	1
-33.75°	6	5	4	4	3	3	2	2	1	1	1
-35°	5	5	4	3	3	2	2	2	1	1	1
-36.25°	5	4	4	3	2	2	2	1	1	1	1
-37.5°	4	4	3	3	2	2	2	1	1	1	1
-38.75°	4	3	3	2	2	2	1	1	1	1	1
-40°	3	3	3	2	2	2	1	1	1	1	1
-41.25°	3	3	2	2	2	1	1	1	1	1	1
-42.5°	3	2	2	2	2	1	1	1	1	1	1
-43.75°	2	2	2	2	1	1	1	1	1	1	1
-45°	2	2	2	1	1	1	1	1	1	1	1
-46.25°	2	2	1	1	1	1	1	1	1	1	1
-47.5°	2	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	0
-57.5°	1	1	1	1	1	1	1	1	1	0	0
-58.75°	1	1	1	1	1	1	1	1	0	0	0
-60°	1	1	1	1	1	1	1	0	0	0	0
-61.25°	1	1	1	1	1	1	0	0	0	0	0
-62.5°	1	1	1	1	0	0	0	0	0	0	0
-63.75°	1	1	1	0	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	1	0	0	0	0	0	0	0	0	0	0
52.5°	1	0	0	0	0	0	0	0	0	0	0
51.25°	1	1	0	0	0	0	0	0	0	0	0
50°	1	1	1	0	0	0	0	0	0	0	0
48.75°	1	1	1	0	0	0	0	0	0	0	0
47.5°	1	1	1	1	0	0	0	0	0	0	0
46.25°	1	1	1	1	0	0	0	0	0	0	0
45°	1	1	1	1	1	0	0	0	0	0	0
43.75°	1	1	1	1	1	0	0	0	0	0	0
42.5°	1	1	1	1	1	0	0	0	0	0	0
41.25°	1	1	1	1	1	1	0	0	0	0	0
40°	1	1	1	1	1	1	0	0	0	0	0
38.75°	1	1	1	1	1	1	1	0	0	0	0
37.5°	1	1	1	1	1	1	1	0	0	0	0
36.25°	1	1	1	1	1	1	1	0	0	0	0
35°	1	1	1	1	1	1	1	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	0	0	0
32.5°	1	1	1	1	1	1	1	1	0	0	0
31.25°	1	1	1	1	1	1	1	1	0	0	0
30°	1	1	1	1	1	1	1	1	0	0	0
28.75°	1	1	1	1	1	1	1	1	0	0	0
27.5°	1	1	1	1	1	1	1	1	1	0	0
26.25°	1	1	1	1	1	1	1	1	1	0	0
25°	1	1	1	1	1	1	1	1	1	0	0
23.75°	1	1	1	1	1	1	1	1	1	0	0
22.5°	1	1	1	1	1	1	1	1	1	0	0
21.25°	1	1	1	1	1	1	1	1	1	0	0
20°	2	1	1	1	1	1	1	1	1	1	0
18.75°	2	1	1	1	1	1	1	1	1	1	0
17.5°	2	1	1	1	1	1	1	1	1	1	0
16.25°	2	1	1	1	1	1	1	1	1	1	0
15°	2	1	1	1	1	1	1	1	1	1	0
13.75°	2	1	1	1	1	1	1	1	1	1	0
12.5°	2	2	1	1	1	1	1	1	1	1	0
11.25°	2	2	1	1	1	1	1	1	1	1	0
10°	2	2	1	1	1	1	1	1	1	1	0
8.75°	2	2	1	1	1	1	1	1	1	1	0
7.5°	2	2	1	1	1	1	1	1	1	1	0
6.25°	2	2	1	1	1	1	1	1	1	1	0
5°	2	2	1	1	1	1	1	1	1	1	0
3.75°	2	2	1	1	1	1	1	1	1	1	0
2.5°	2	2	1	1	1	1	1	1	1	1	0
1.25°	2	2	1	1	1	1	1	1	1	1	0
0°	2	2	1	1	1	1	1	1	1	1	0
-1.25°	2	2	1	1	1	1	1	1	1	1	0
-2.5°	2	2	1	1	1	1	1	1	1	1	0
-3.75°	2	2	1	1	1	1	1	1	1	1	0
-5°	2	2	1	1	1	1	1	1	1	1	0
-6.25°	2	2	1	1	1	1	1	1	1	1	0
-7.5°	2	2	1	1	1	1	1	1	1	1	0
-8.75°	2	2	1	1	1	1	1	1	1	1	0
-10°	2	2	1	1	1	1	1	1	1	1	0
-11.25°	2	2	1	1	1	1	1	1	1	1	0
-12.5°	2	2	1	1	1	1	1	1	1	1	0
-13.75°	2	1	1	1	1	1	1	1	1	1	0
-15°	2	1	1	1	1	1	1	1	1	1	0
-16.25°	2	1	1	1	1	1	1	1	1	1	0
-17.5°	2	1	1	1	1	1	1	1	1	1	0
-18.75°	2	1	1	1	1	1	1	1	1	1	0
-20°	2	1	1	1	1	1	1	1	1	1	0
-21.25°	1	1	1	1	1	1	1	1	1	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	1	1	1	1	1	1	1	1	1	0	0
-23.75°	1	1	1	1	1	1	1	1	1	0	0
-25°	1	1	1	1	1	1	1	1	1	0	0
-26.25°	1	1	1	1	1	1	1	1	1	0	0
-27.5°	1	1	1	1	1	1	1	1	1	0	0
-28.75°	1	1	1	1	1	1	1	1	0	0	0
-30°	1	1	1	1	1	1	1	1	0	0	0
-31.25°	1	1	1	1	1	1	1	1	0	0	0
-32.5°	1	1	1	1	1	1	1	1	0	0	0
-33.75°	1	1	1	1	1	1	1	1	0	0	0
-35°	1	1	1	1	1	1	1	0	0	0	0
-36.25°	1	1	1	1	1	1	1	0	0	0	0
-37.5°	1	1	1	1	1	1	1	0	0	0	0
-38.75°	1	1	1	1	1	1	1	0	0	0	0
-40°	1	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-43.75°	1	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	1	1	0	0	0	0	0	0
-46.25°	1	1	1	1	0	0	0	0	0	0	0
-47.5°	1	1	1	1	0	0	0	0	0	0	0
-48.75°	1	1	1	0	0	0	0	0	0	0	0
-50°	1	1	1	0	0	0	0	0	0	0	0
-51.25°	1	1	0	0	0	0	0	0	0	0	0
-52.5°	1	0	0	0	0	0	0	0	0	0	0
-53.75°	1	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED3010-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)