

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4010-12-BK-LSL**

Test Date: 04/06/18

Test Information


Test Method: LM-79-08
Report Number: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-25)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4010-12-BK-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD BLACK, LINEAR SPREAD LENS
Light Source: (1) SORAA 4000K 95 CRI 10°NSP LED
SM16-07-10D-940-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 2V
Luminaire Lumens:	252.8 lumens	Max Intensity:	1299 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	31.6 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	50.8°H x 11.9°V	Field Angle (10%):	61.2°H x 22.1°V
Beam Lumens:	123.5 lumens	Field Lumens:	206.9 lumens
Beam Efficiency:	48.9%	Field Efficiency:	81.9%
Input Watts (W):	8		
Input Voltage (V):	12.0		
Input Current (A _{in}):	0.709		
Voltage Rise (V):	NR		
Power Factor:	0.9468		
Total Harmonic Distortion (THDi):	27.5		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	9 HR		
Ambient Temperature (°C):	24.9		
Test Distance:	25 FT		


REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

Lumen Table




REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

Luminous Intensity Plot



Beam:
 H Angle: 50.8°
 V Angle: 11.9°
 Lumens: 123.5
 Efficiency: 48.9%

Field:
 H Angle: 61.2°
 V Angle: 22.1°
 Lumens: 206.9
 Efficiency: 81.9%

Spill:
 Lumens: 45.9
 Efficiency: 18.1%

— Vertical Distribution through 0-Deg
 - - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	1
40°	0	0	0	0	0	0	0	0	0	0	1
38.75°	0	0	0	0	0	0	0	0	0	1	1
37.5°	0	0	0	0	0	0	0	0	1	1	1
36.25°	0	0	0	0	0	0	0	0	1	1	1
35°	0	0	0	0	0	0	0	1	1	1	2



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	0	0	0	0	0	0	0	1	1	2	2
32.5°	0	0	0	0	0	0	1	1	1	2	2
31.25°	0	0	0	0	0	0	1	1	2	2	3
30°	0	0	0	0	0	1	1	1	2	2	3
28.75°	0	0	0	0	0	1	1	1	2	3	3
27.5°	0	0	0	0	1	1	1	2	2	3	4
26.25°	0	0	0	0	1	1	1	2	3	3	4
25°	0	0	0	1	1	1	2	2	3	4	4
23.75°	0	0	0	1	1	1	2	2	3	4	5
22.5°	0	0	0	1	1	1	2	3	4	4	5
21.25°	0	0	1	1	1	1	2	3	4	5	5
20°	0	0	1	1	1	2	2	3	4	5	5
18.75°	0	0	1	1	1	2	2	3	4	5	5
17.5°	0	1	1	1	1	2	3	4	5	5	6
16.25°	0	1	1	1	1	2	3	4	5	5	6
15°	0	1	1	1	2	2	3	4	5	5	6
13.75°	0	1	1	1	2	2	3	5	5	5	6
12.5°	1	1	1	1	2	2	4	5	5	6	7
11.25°	1	1	1	1	2	3	4	5	5	6	7
10°	1	1	1	1	2	3	4	5	5	6	7
8.75°	1	1	1	1	2	3	4	5	6	6	7
7.5°	1	1	1	1	2	3	4	5	6	6	7
6.25°	1	1	1	1	2	3	5	5	6	7	8
5°	1	1	1	1	2	3	5	5	6	7	8
3.75°	1	1	1	1	2	3	5	5	6	7	8
2.5°	1	1	1	1	2	3	5	5	6	7	8
1.25°	1	1	1	1	2	3	5	5	6	7	8
0°	1	1	1	2	2	3	5	5	6	7	8
-1.25°	1	1	1	1	2	3	5	5	6	7	8
-2.5°	1	1	1	1	2	3	5	5	6	7	8
-3.75°	1	1	1	1	2	3	5	5	6	7	8
-5°	1	1	1	1	2	3	5	5	6	7	8
-6.25°	1	1	1	1	2	3	5	5	6	7	8
-7.5°	1	1	1	1	2	3	4	5	6	6	7
-8.75°	1	1	1	1	2	3	4	5	6	6	7
-10°	1	1	1	1	2	3	4	5	5	6	7
-11.25°	1	1	1	1	2	3	4	5	5	6	7
-12.5°	1	1	1	1	2	2	4	5	5	6	7
-13.75°	1	1	1	1	2	2	3	5	5	5	6
-15°	1	1	1	1	2	2	3	4	5	5	6
-16.25°	1	1	1	1	1	2	3	4	5	5	6
-17.5°	0	1	1	1	1	2	3	4	5	5	6
-18.75°	0	1	1	1	1	2	2	3	4	5	5
-20°	0	1	1	1	1	2	2	3	4	5	5
-21.25°	0	1	1	1	1	1	2	3	4	5	5



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	0	1	1	1	1	1	2	3	4	4	5
-23.75°	0	0	1	1	1	1	2	2	3	4	5
-25°	0	0	1	1	1	1	2	2	3	4	4
-26.25°	0	0	1	1	1	1	1	2	3	3	4
-27.5°	0	0	1	1	1	1	1	2	2	3	4
-28.75°	0	0	0	1	1	1	1	1	2	3	3
-30°	0	0	0	1	1	1	1	1	2	2	3
-31.25°	0	0	0	1	1	1	1	1	2	2	3
-32.5°	0	0	0	0	1	1	1	1	1	2	2
-33.75°	0	0	0	0	1	1	1	1	1	2	2
-35°	0	0	0	0	0	1	1	1	1	1	2
-36.25°	0	0	0	0	0	1	1	1	1	1	2
-37.5°	0	0	0	0	0	0	1	1	1	1	1
-38.75°	0	0	0	0	0	0	1	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	0	1	1	1
-43.75°	0	0	0	0	0	0	0	0	0	1	1
-45°	0	0	0	0	0	0	0	0	0	1	1
-46.25°	0	0	0	0	0	0	0	0	0	0	1
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	1	1
51.25°	0	0	0	0	0	0	0	0	1	1	1
50°	0	0	0	0	0	0	1	1	1	1	1
48.75°	0	0	0	0	0	1	1	1	1	2	2
47.5°	0	0	0	0	1	1	1	1	2	2	2
46.25°	0	0	0	1	1	1	2	2	2	2	3
45°	0	0	1	1	1	2	2	2	2	3	3
43.75°	0	1	1	1	2	2	2	3	3	3	4
42.5°	1	1	1	2	2	2	3	3	3	4	4
41.25°	1	1	2	2	2	3	3	3	4	4	5
40°	1	1	2	2	3	3	3	4	4	5	5
38.75°	1	2	2	3	3	4	4	4	5	5	6
37.5°	2	2	3	3	4	4	4	5	5	6	6
36.25°	2	2	3	3	4	4	5	5	6	6	6
35°	2	3	3	4	4	5	5	6	6	7	7



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	4	4	5	5	6	6	7	7	7
32.5°	3	4	4	5	5	6	6	7	7	7	8
31.25°	3	4	4	5	5	6	7	7	7	8	8
30°	4	4	5	5	6	7	7	7	8	8	9
28.75°	4	5	5	6	6	7	7	8	8	9	9
27.5°	4	5	5	6	7	7	7	8	9	9	10
26.25°	5	5	6	6	7	7	8	8	9	10	10
25°	5	5	6	7	7	8	8	9	10	10	10
23.75°	5	6	6	7	8	8	9	9	10	10	11
22.5°	5	6	7	7	8	8	9	10	10	11	11
21.25°	6	6	7	8	8	9	10	10	11	11	12
20°	6	7	7	8	8	9	10	10	11	12	13
18.75°	6	7	8	8	9	10	10	11	11	12	14
17.5°	7	7	8	8	9	10	11	11	12	13	14
16.25°	7	8	8	9	10	11	11	11	13	14	15
15°	7	8	8	9	10	11	11	12	13	15	15
13.75°	7	8	9	10	10	11	12	13	14	15	16
12.5°	8	8	9	10	11	11	12	13	14	16	17
11.25°	8	8	9	10	11	12	12	14	15	16	17
10°	8	9	9	10	11	12	13	14	16	17	18
8.75°	8	9	10	11	12	12	13	15	16	17	19
7.5°	8	9	10	11	12	13	14	15	17	18	20
6.25°	8	9	10	11	12	13	14	16	17	19	21
5°	9	9	10	11	12	13	14	16	18	19	22
3.75°	9	10	11	12	12	13	15	16	18	20	23
2.5°	9	10	11	12	13	14	15	17	18	20	24
1.25°	9	10	11	12	13	14	15	17	19	21	25
0°	9	10	11	12	13	14	15	17	19	21	25
-1.25°	9	10	11	12	13	14	15	17	19	21	25
-2.5°	9	10	11	12	13	14	15	17	18	20	24
-3.75°	9	10	11	12	12	13	15	16	18	20	23
-5°	9	9	10	11	12	13	14	16	18	19	22
-6.25°	8	9	10	11	12	13	14	16	17	19	21
-7.5°	8	9	10	11	12	13	14	15	17	18	20
-8.75°	8	9	10	11	12	12	13	15	16	17	19
-10°	8	9	9	10	11	12	13	14	16	17	18
-11.25°	8	8	9	10	11	12	12	14	15	16	17
-12.5°	8	8	9	10	11	11	12	13	14	16	17
-13.75°	7	8	9	10	10	11	12	13	14	15	16
-15°	7	8	8	9	10	11	11	12	13	15	15
-16.25°	7	8	8	9	10	11	11	11	13	14	15
-17.5°	7	7	8	8	9	10	11	11	12	13	14
-18.75°	6	7	8	8	9	10	10	11	11	12	14
-20°	6	7	7	8	8	9	10	10	11	12	13
-21.25°	6	6	7	8	8	9	10	10	11	11	12



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	5	6	7	7	8	8	9	10	10	11	11
-23.75°	5	6	6	7	8	8	9	9	10	10	11
-25°	5	5	6	7	7	8	8	9	10	10	10
-26.25°	5	5	6	6	7	7	8	8	9	10	10
-27.5°	4	5	5	6	7	7	7	8	9	9	10
-28.75°	4	5	5	6	6	7	7	8	8	9	9
-30°	4	4	5	5	6	7	7	7	8	8	9
-31.25°	3	4	4	5	5	6	7	7	7	8	8
-32.5°	3	4	4	5	5	6	6	7	7	7	8
-33.75°	3	3	4	4	5	5	6	6	7	7	7
-35°	2	3	4	4	5	5	5	6	6	7	7
-36.25°	2	3	3	4	4	5	5	5	6	6	6
-37.5°	2	2	3	3	4	4	5	5	5	6	6
-38.75°	2	2	2	3	4	4	4	5	5	5	6
-40°	1	2	2	3	3	4	4	4	5	5	5
-41.25°	1	2	2	2	3	3	4	4	4	5	5
-42.5°	1	1	2	2	2	3	3	4	4	4	5
-43.75°	1	1	1	2	2	3	3	3	4	4	4
-45°	1	1	1	2	2	2	3	3	3	4	4
-46.25°	1	1	1	1	2	2	2	3	3	3	4
-47.5°	1	1	1	1	1	2	2	2	3	3	3
-48.75°	0	1	1	1	1	1	2	2	2	3	3
-50°	0	0	1	1	1	1	1	2	2	2	2
-51.25°	0	0	0	1	1	1	1	1	2	2	2
-52.5°	0	0	0	0	0	1	1	1	1	2	2
-53.75°	0	0	0	0	0	0	1	1	1	1	1
-55°	0	0	0	0	0	0	0	0	1	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	1	1	1	1
56.25°	0	0	0	0	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	2	2	2
53.75°	1	1	1	1	1	1	2	2	2	2	2
52.5°	1	1	1	2	2	2	2	2	2	3	3
51.25°	1	2	2	2	2	2	2	3	3	3	3
50°	2	2	2	2	3	3	3	3	3	4	4
48.75°	2	2	3	3	3	3	3	4	4	4	4
47.5°	2	3	3	3	4	4	4	4	5	5	5
46.25°	3	3	3	4	4	5	5	5	5	5	5
45°	3	4	4	5	5	5	5	5	5	6	6
43.75°	4	4	5	5	5	5	6	6	6	6	6
42.5°	5	5	5	5	6	6	6	6	6	6	7
41.25°	5	5	6	6	6	6	6	7	7	7	7
40°	6	6	6	6	6	7	7	7	7	7	7
38.75°	6	6	6	7	7	7	7	7	8	8	8
37.5°	6	7	7	7	7	7	8	8	8	9	9
36.25°	7	7	7	7	8	8	8	9	9	9	9
35°	7	7	8	8	8	9	9	9	10	10	10



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	8	8	8	8	9	9	10	10	10	10	10
32.5°	8	8	9	9	10	10	10	10	11	11	11
31.25°	8	9	9	10	10	11	11	11	11	12	12
30°	9	9	10	10	11	11	11	12	12	13	13
28.75°	9	10	10	11	11	12	12	13	13	13	14
27.5°	10	10	11	12	12	12	13	13	14	14	15
26.25°	10	11	12	12	13	13	14	14	15	15	16
25°	11	12	12	13	14	14	15	16	16	17	17
23.75°	12	12	13	14	14	15	16	17	18	18	19
22.5°	12	13	14	14	15	16	17	19	20	21	22
21.25°	13	14	15	15	17	18	19	21	22	24	25
20°	14	14	15	17	18	20	21	23	26	28	30
18.75°	14	15	16	18	19	22	24	27	30	33	38
17.5°	15	16	18	19	22	24	27	31	35	42	48
16.25°	16	17	19	21	24	26	32	37	44	53	59
15°	16	18	20	23	26	30	37	42	55	65	81
13.75°	17	20	22	26	28	35	42	53	67	83	107
12.5°	19	21	25	29	34	42	48	65	81	108	136
11.25°	20	23	28	33	43	54	68	85	100	137	168
10°	21	24	31	37	53	67	93	118	150	182	213
8.75°	23	27	35	44	64	83	123	156	210	254	303
7.5°	24	30	39	53	76	107	156	206	276	337	404
6.25°	25	33	43	63	89	133	191	262	347	428	510
5°	26	36	47	73	103	161	229	320	421	521	620
3.75°	27	39	51	82	116	189	266	379	496	615	731
2.5°	28	41	55	91	129	215	303	436	570	707	840
1.25°	29	44	58	100	141	240	338	490	641	794	946
0°	30	45	61	106	152	261	370	538	706	876	1046
-1.25°	29	43	58	99	141	239	336	485	633	783	931
-2.5°	28	41	54	91	128	213	300	428	556	685	810
-3.75°	27	38	50	81	115	185	261	367	476	584	687
-5°	26	35	46	72	101	157	222	306	396	483	564
-6.25°	25	32	42	62	87	129	184	247	318	384	446
-7.5°	23	29	38	52	74	103	147	191	246	290	333
-8.75°	22	26	34	43	62	79	114	142	180	206	230
-10°	21	23	30	37	51	63	85	104	123	134	142
-11.25°	20	22	27	32	41	50	61	72	78	98	115
-12.5°	18	21	24	28	33	39	43	55	66	82	97
-13.75°	17	19	21	25	27	33	38	47	56	67	80
-15°	16	18	19	22	25	29	34	39	48	55	64
-16.25°	16	17	18	20	23	25	30	34	40	46	51
-17.5°	15	16	17	19	21	23	26	30	33	38	42
-18.75°	14	15	16	17	19	21	23	26	29	31	35
-20°	14	14	15	16	17	19	21	22	25	27	29
-21.25°	13	14	15	15	16	17	19	20	22	24	25



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	12	13	14	14	15	16	17	18	19	20	22
-23.75°	12	12	13	14	14	15	16	17	18	18	19
-25°	11	12	12	13	14	14	15	15	16	17	17
-26.25°	10	11	12	12	13	13	14	14	15	15	16
-27.5°	10	10	11	12	12	12	13	13	14	14	15
-28.75°	9	10	10	11	11	12	12	13	13	14	14
-30°	9	9	10	10	11	11	11	12	12	13	13
-31.25°	8	9	9	10	10	11	11	11	11	12	12
-32.5°	8	8	9	9	10	10	10	11	11	11	12
-33.75°	8	8	8	8	9	9	10	10	10	11	11
-35°	7	7	8	8	8	9	9	10	10	10	10
-36.25°	7	7	7	7	8	8	8	9	9	10	10
-37.5°	6	7	7	7	7	8	8	8	9	9	9
-38.75°	6	6	6	7	7	7	7	8	8	8	9
-40°	6	6	6	6	6	7	7	7	7	8	8
-41.25°	5	5	6	6	6	6	6	7	7	7	7
-42.5°	5	5	5	5	6	6	6	6	6	6	7
-43.75°	5	5	5	5	5	5	6	6	6	6	6
-45°	4	4	5	5	5	5	5	5	5	6	6
-46.25°	4	4	4	4	4	5	5	5	5	5	5
-47.5°	3	4	4	4	4	4	4	4	5	5	5
-48.75°	3	3	3	4	4	4	4	4	4	4	4
-50°	3	3	3	3	3	3	3	4	4	4	4
-51.25°	2	3	3	3	3	3	3	3	3	3	3
-52.5°	2	2	2	3	3	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	3	3	3	3	3
-55°	1	1	2	2	2	2	2	2	3	3	3
-56.25°	1	1	1	1	2	2	2	2	2	2	2
-57.5°	0	1	1	1	1	1	1	2	2	2	2
-58.75°	0	0	0	1	1	1	1	1	1	1	1
-60°	0	0	0	0	0	0	1	1	1	1	1
-61.25°	0	0	0	0	0	0	0	0	0	0	1
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	2	2	2	2	2	2
56.25°	1	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	3	3	3	3	3
53.75°	2	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	6	6	6	6	6	6	6	6
45°	6	6	6	6	6	6	6	6	6	6	6
43.75°	6	6	6	7	7	7	7	7	7	7	7
42.5°	7	7	7	7	7	7	7	7	7	7	7
41.25°	7	7	7	8	8	8	8	8	8	8	8
40°	8	8	8	8	8	8	8	8	8	8	8
38.75°	8	8	9	9	9	9	9	9	9	9	9
37.5°	9	9	9	9	9	9	9	9	10	10	10
36.25°	9	10	10	10	10	10	10	10	10	11	10
35°	10	10	10	11	11	11	11	11	11	11	11



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	11	11	11	12	12	12	12	12	12	12	12
32.5°	12	12	12	12	12	12	12	12	13	13	13
31.25°	12	13	13	13	13	13	13	13	13	14	14
30°	13	13	14	14	14	14	14	14	14	15	15
28.75°	14	14	15	15	15	16	16	16	15	16	16
27.5°	15	16	16	16	17	17	17	17	17	17	18
26.25°	16	17	18	18	18	18	19	19	19	19	20
25°	18	19	19	20	20	21	21	21	21	21	22
23.75°	19	20	21	22	23	23	24	24	24	24	24
22.5°	22	22	23	24	25	26	27	27	27	27	27
21.25°	25	25	26	27	29	30	31	32	32	31	30
20°	32	31	29	32	33	35	36	37	37	37	36
18.75°	40	41	40	36	38	41	42	43	44	44	43
17.5°	52	58	57	51	45	47	49	51	52	52	52
16.25°	72	79	81	78	64	54	57	59	61	62	63
15°	96	107	116	115	101	77	66	69	72	73	74
13.75°	124	146	159	160	149	125	90	80	83	86	88
12.5°	164	193	211	214	206	182	147	103	97	101	103
11.25°	212	247	268	277	270	245	212	170	123	118	130
10°	265	306	332	347	335	314	282	243	196	158	164
8.75°	344	368	402	415	406	388	357	320	287	251	214
7.5°	459	486	505	486	483	464	436	408	381	349	345
6.25°	574	611	630	609	586	546	520	501	478	471	470
5°	690	739	751	733	700	654	617	595	583	588	591
3.75°	807	868	872	856	811	757	711	675	668	685	715
2.5°	923	997	993	978	920	858	799	746	737	743	780
1.25°	1036	1124	1114	1101	1030	958	884	813	799	791	832
0°	1146	1246	1235	1225	1143	1061	971	881	858	836	874
-1.25°	1017	1100	1090	1076	1004	931	857	785	771	763	800
-2.5°	885	951	944	927	867	804	745	691	681	685	717
-3.75°	752	801	799	778	732	677	630	593	584	598	624
-5°	619	653	654	631	594	547	509	484	478	491	492
-6.25°	489	508	510	483	453	411	399	397	387	384	375
-7.5°	363	369	363	335	345	344	334	322	307	283	267
-8.75°	241	242	269	285	290	287	274	254	233	204	169
-10°	175	202	223	238	239	233	218	195	165	135	137
-11.25°	143	165	182	192	193	184	167	142	111	108	115
-12.5°	114	133	145	152	151	140	121	95	92	95	97
-13.75°	90	104	114	117	113	102	82	78	80	83	85
-15°	73	80	87	88	83	70	65	69	71	73	74
-16.25°	58	63	66	65	58	54	58	61	63	65	65
-17.5°	46	50	50	48	46	48	50	53	55	57	57
-18.75°	37	39	39	38	40	42	44	46	48	49	50
-20°	31	31	30	33	35	37	39	40	41	42	42
-21.25°	26	26	27	29	31	32	33	34	35	36	36



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	22	23	25	26	26	28	29	30	30	30	31
-23.75°	20	21	22	23	24	24	25	26	26	26	26
-25°	18	19	20	21	22	22	22	22	23	23	23
-26.25°	17	17	18	19	20	20	20	21	20	20	21
-27.5°	15	16	16	17	18	18	19	19	19	19	19
-28.75°	14	15	15	16	16	16	17	17	17	18	18
-30°	14	14	14	15	15	15	15	15	16	16	16
-31.25°	13	13	13	14	14	14	14	14	15	15	15
-32.5°	12	12	13	13	13	13	13	13	14	14	14
-33.75°	11	12	12	12	12	13	13	13	13	13	13
-35°	10	11	11	11	12	12	12	12	12	12	12
-36.25°	10	10	10	10	11	11	11	11	12	12	12
-37.5°	10	10	10	10	10	10	10	11	11	11	11
-38.75°	9	9	9	9	10	10	10	10	10	10	10
-40°	8	9	9	9	9	9	9	9	9	9	9
-41.25°	8	8	8	8	9	9	9	9	9	9	9
-42.5°	7	7	7	8	8	8	8	8	8	8	8
-43.75°	6	6	7	7	7	7	8	8	8	8	8
-45°	6	6	6	6	6	6	7	7	7	7	7
-46.25°	5	5	5	6	6	6	6	6	6	6	6
-47.5°	5	5	5	5	5	5	5	6	6	6	6
-48.75°	4	4	5	5	5	5	5	5	5	5	5
-50°	4	4	4	4	4	4	4	5	5	5	5
-51.25°	3	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	4	4	4	4	4	4
-53.75°	3	3	3	3	3	3	3	3	3	4	4
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	3	3	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	0	0	0	0	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	1	0	0	0	0
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	2	1	1	1	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	3	2	2	2	2
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	6	6	6	6	6	6	6	6	6	6	6
45°	6	6	6	6	6	6	6	6	6	6	6
43.75°	7	7	7	7	7	7	7	7	7	7	7
42.5°	7	7	7	7	7	7	7	7	7	7	7
41.25°	8	8	8	8	8	8	8	8	8	8	8
40°	8	8	8	8	8	8	8	8	8	8	8
38.75°	9	9	9	9	9	9	9	9	9	9	9
37.5°	10	10	10	9	9	9	9	9	9	9	10
36.25°	10	10	10	10	10	10	10	10	10	10	10
35°	11	11	11	11	11	11	11	11	11	11	11



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	12	12	12	12	12	12	12	12	12	12	12
32.5°	13	13	13	13	12	12	12	12	12	13	13
31.25°	14	14	14	14	14	14	14	14	14	14	14
30°	15	15	15	15	15	15	15	15	15	15	15
28.75°	16	16	17	17	17	17	17	17	17	17	17
27.5°	18	18	18	18	18	18	18	18	18	18	18
26.25°	20	20	20	20	20	20	20	20	20	20	20
25°	22	22	22	22	22	22	22	22	22	22	22
23.75°	24	25	25	25	25	25	25	25	25	25	25
22.5°	27	28	28	28	28	28	27	28	28	28	28
21.25°	31	32	32	33	33	32	32	32	33	33	32
20°	36	37	38	38	38	37	36	37	38	38	38
18.75°	42	44	45	46	46	46	45	46	46	46	45
17.5°	52	53	55	56	56	55	54	55	56	56	55
16.25°	63	63	64	65	65	64	63	64	65	65	64
15°	75	73	74	75	75	74	72	74	75	75	74
13.75°	88	85	86	88	89	89	87	89	89	88	86
12.5°	107	107	102	104	105	104	101	104	105	104	102
11.25°	136	133	128	133	138	138	133	138	138	133	128
10°	170	187	186	176	178	174	164	174	178	176	186
8.75°	246	262	255	255	271	277	262	277	271	255	255
7.5°	336	360	384	419	445	460	438	460	445	419	384
6.25°	473	495	559	624	668	688	666	688	668	624	559
5°	614	669	743	825	881	908	893	908	881	825	743
3.75°	758	831	915	991	1053	1090	1075	1090	1053	991	915
2.5°	855	958	1045	1118	1171	1212	1204	1212	1171	1118	1045
1.25°	909	1008	1109	1193	1244	1275	1283	1275	1244	1193	1109
0°	943	1033	1127	1204	1253	1284	1299	1284	1253	1204	1127
-1.25°	871	964	1064	1146	1198	1225	1231	1225	1198	1146	1064
-2.5°	782	873	956	1028	1081	1115	1137	1115	1081	1028	956
-3.75°	658	715	786	855	913	945	944	945	913	855	786
-5°	503	532	581	650	692	742	761	742	692	650	581
-6.25°	359	357	400	439	456	508	517	508	456	439	400
-7.5°	237	252	267	276	286	316	320	316	286	276	267
-8.75°	184	192	186	179	188	199	199	199	188	179	186
-10°	141	149	147	140	144	144	142	144	144	140	147
-11.25°	119	118	115	118	121	123	121	123	121	118	115
-12.5°	100	100	97	100	101	101	100	101	101	100	97
-13.75°	86	84	85	88	89	89	88	89	89	88	85
-15°	75	74	75	77	77	77	76	77	77	77	75
-16.25°	65	65	67	68	68	68	68	68	68	68	67
-17.5°	57	58	59	60	60	60	59	60	60	60	59
-18.75°	50	51	52	53	53	53	52	53	53	53	52
-20°	43	45	45	46	46	46	45	46	46	46	45
-21.25°	36	37	38	39	39	38	38	38	39	39	38



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	32	32	32	32	32	31	30	31	32	32	32
-23.75°	27	27	28	28	28	27	27	27	28	28	28
-25°	24	24	24	24	24	23	23	23	24	24	24
-26.25°	21	22	22	22	22	22	22	22	22	22	22
-27.5°	20	20	20	20	20	20	20	20	20	20	20
-28.75°	18	18	18	19	19	19	19	19	19	19	18
-30°	17	17	17	17	17	17	17	17	17	17	17
-31.25°	15	15	15	16	16	16	16	16	16	16	15
-32.5°	14	14	14	14	14	14	14	14	14	14	14
-33.75°	13	13	13	13	13	13	13	13	13	13	13
-35°	12	12	12	12	12	12	12	12	12	12	12
-36.25°	12	12	12	12	12	12	12	12	12	12	12
-37.5°	11	11	11	11	11	11	11	11	11	11	11
-38.75°	10	10	10	10	10	10	10	10	10	10	10
-40°	9	9	9	9	9	9	9	9	9	9	9
-41.25°	9	9	9	9	9	9	9	9	9	9	9
-42.5°	8	8	8	8	8	8	8	8	8	8	8
-43.75°	8	8	8	8	8	8	8	8	8	8	8
-45°	7	7	7	7	7	7	7	7	7	7	7
-46.25°	6	7	7	7	7	7	7	7	7	7	7
-47.5°	6	6	6	6	6	6	6	6	6	6	6
-48.75°	5	5	5	5	5	5	6	5	5	5	5
-50°	5	5	5	5	5	5	5	5	5	5	5
-51.25°	4	4	4	4	4	4	5	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	3	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	2	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	1	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	1	1	1	1	1	1	1	1	0	0	0
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	2	2	1	1	1
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	3	3	2	2	2	2
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	5	5	5	5	5	5	5	5	5	5	5
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	6	6	6	6	6	6	6	6	6	6	5
45°	6	6	6	6	6	6	6	6	6	6	6
43.75°	7	7	7	7	7	7	7	7	7	7	6
42.5°	7	7	7	7	7	7	7	7	7	7	7
41.25°	8	8	8	8	8	8	8	8	8	8	7
40°	8	8	8	8	8	8	8	8	8	8	8
38.75°	9	9	9	9	9	9	9	9	9	9	9
37.5°	10	10	10	10	10	9	9	9	9	9	9
36.25°	10	10	10	11	10	10	10	10	10	10	10
35°	11	11	11	11	11	11	11	11	11	11	10



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	12	12	12	12	12	12	12	12	12	12	11
32.5°	13	13	13	13	13	12	12	12	12	12	12
31.25°	14	14	14	14	13	13	13	13	13	13	13
30°	15	15	15	15	14	14	14	14	14	14	14
28.75°	16	16	16	16	15	16	16	16	15	15	15
27.5°	18	18	18	17	17	17	17	17	17	16	16
26.25°	20	20	20	19	19	19	19	18	18	18	18
25°	22	22	22	21	21	21	21	21	20	20	19
23.75°	25	24	24	24	24	24	24	23	23	22	21
22.5°	28	27	27	27	27	27	27	26	25	24	23
21.25°	32	31	30	31	32	32	31	30	29	27	26
20°	37	36	36	37	37	37	36	35	33	32	29
18.75°	44	42	43	44	44	43	42	41	38	36	40
17.5°	53	52	52	52	52	51	49	47	45	51	57
16.25°	63	63	63	62	61	59	57	54	64	78	81
15°	73	75	74	73	72	69	66	77	101	115	116
13.75°	85	88	88	86	83	80	90	125	149	160	159
12.5°	107	107	103	101	97	103	147	182	206	214	211
11.25°	133	136	130	118	123	170	212	245	270	277	268
10°	187	170	164	158	196	243	282	314	335	347	332
8.75°	262	246	214	251	287	320	357	388	406	415	402
7.5°	360	336	345	349	381	408	436	464	483	486	505
6.25°	495	473	470	471	478	501	520	546	586	609	630
5°	669	614	591	588	583	595	617	654	700	733	751
3.75°	831	758	715	685	668	675	711	757	811	856	872
2.5°	958	855	780	743	737	746	799	858	920	978	993
1.25°	1008	909	832	791	799	813	884	958	1030	1101	1114
0°	1033	943	874	836	858	881	971	1061	1143	1225	1235
-1.25°	964	871	800	763	771	785	857	931	1004	1076	1090
-2.5°	873	782	717	685	681	691	745	804	867	927	944
-3.75°	715	658	624	598	584	593	630	677	732	778	799
-5°	532	503	492	491	478	484	509	547	594	631	654
-6.25°	357	359	375	384	387	397	399	411	453	483	510
-7.5°	252	237	267	283	307	322	334	344	345	335	363
-8.75°	192	184	169	204	233	254	274	287	290	285	269
-10°	149	141	137	135	165	195	218	233	239	238	223
-11.25°	118	119	115	108	111	142	167	184	193	192	182
-12.5°	100	100	97	95	92	95	121	140	151	152	145
-13.75°	84	86	85	83	80	78	82	102	113	117	114
-15°	74	75	74	73	71	69	65	70	83	88	87
-16.25°	65	65	65	65	63	61	58	54	58	65	66
-17.5°	58	57	57	57	55	53	50	48	46	48	50
-18.75°	51	50	50	49	48	46	44	42	40	38	39
-20°	45	43	42	42	41	40	39	37	35	33	30
-21.25°	37	36	36	36	35	34	33	32	31	29	27



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	32	32	31	30	30	30	29	28	26	26	25
-23.75°	27	27	26	26	26	26	25	24	24	23	22
-25°	24	24	23	23	23	22	22	22	22	21	20
-26.25°	22	21	21	20	20	21	20	20	20	19	18
-27.5°	20	20	19	19	19	19	19	18	18	17	16
-28.75°	18	18	18	18	17	17	17	16	16	16	15
-30°	17	17	16	16	16	15	15	15	15	15	14
-31.25°	15	15	15	15	15	14	14	14	14	14	13
-32.5°	14	14	14	14	14	13	13	13	13	13	13
-33.75°	13	13	13	13	13	13	13	13	12	12	12
-35°	12	12	12	12	12	12	12	12	12	11	11
-36.25°	12	12	12	12	12	11	11	11	11	10	10
-37.5°	11	11	11	11	11	11	10	10	10	10	10
-38.75°	10	10	10	10	10	10	10	10	10	9	9
-40°	9	9	9	9	9	9	9	9	9	9	9
-41.25°	9	9	9	9	9	9	9	9	9	8	8
-42.5°	8	8	8	8	8	8	8	8	8	8	7
-43.75°	8	8	8	8	8	8	8	7	7	7	7
-45°	7	7	7	7	7	7	7	6	6	6	6
-46.25°	7	6	6	6	6	6	6	6	6	6	5
-47.5°	6	6	6	6	6	6	5	5	5	5	5
-48.75°	5	5	5	5	5	5	5	5	5	5	5
-50°	5	5	5	5	5	5	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	3	3	3
-53.75°	4	4	4	4	3	3	3	3	3	3	3
-55°	4	4	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	1	1	0	0	0	0	0	0	0	0	0
57.5°	1	1	1	1	1	1	0	0	0	0	0
56.25°	2	1	1	1	1	1	1	1	1	0	0
55°	2	2	2	2	2	1	1	1	1	1	1
53.75°	3	2	2	2	2	2	2	1	1	1	1
52.5°	3	3	3	3	2	2	2	2	2	2	1
51.25°	3	3	3	3	3	3	2	2	2	2	2
50°	4	4	4	4	3	3	3	3	3	2	2
48.75°	4	4	4	4	4	4	3	3	3	3	3
47.5°	5	5	5	5	5	4	4	4	4	3	3
46.25°	5	5	5	5	5	5	5	5	4	4	3
45°	6	6	6	6	5	5	5	5	5	5	4
43.75°	6	6	6	6	6	6	6	5	5	5	5
42.5°	7	7	7	6	6	6	6	6	6	5	5
41.25°	7	7	7	7	7	7	6	6	6	6	6
40°	8	8	7	7	7	7	7	7	6	6	6
38.75°	8	8	8	8	8	7	7	7	7	7	6
37.5°	9	9	9	9	8	8	8	7	7	7	7
36.25°	10	9	9	9	9	9	8	8	8	7	7
35°	10	10	10	10	10	9	9	9	8	8	8



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	11	11	10	10	10	10	10	9	9	8	8
32.5°	12	12	11	11	11	10	10	10	10	9	9
31.25°	13	12	12	12	11	11	11	11	10	10	9
30°	13	13	13	13	12	12	11	11	11	10	10
28.75°	14	14	14	13	13	13	12	12	11	11	10
27.5°	16	15	15	14	14	13	13	12	12	12	11
26.25°	17	16	16	15	15	14	14	13	13	12	12
25°	19	18	17	17	16	16	15	14	14	13	12
23.75°	20	19	19	18	18	17	16	15	14	14	13
22.5°	22	22	22	21	20	19	17	16	15	14	14
21.25°	25	25	25	24	22	21	19	18	17	15	15
20°	31	32	30	28	26	23	21	20	18	17	15
18.75°	41	40	38	33	30	27	24	22	19	18	16
17.5°	58	52	48	42	35	31	27	24	22	19	18
16.25°	79	72	59	53	44	37	32	26	24	21	19
15°	107	96	81	65	55	42	37	30	26	23	20
13.75°	146	124	107	83	67	53	42	35	28	26	22
12.5°	193	164	136	108	81	65	48	42	34	29	25
11.25°	247	212	168	137	100	85	68	54	43	33	28
10°	306	265	213	182	150	118	93	67	53	37	31
8.75°	368	344	303	254	210	156	123	83	64	44	35
7.5°	486	459	404	337	276	206	156	107	76	53	39
6.25°	611	574	510	428	347	262	191	133	89	63	43
5°	739	690	620	521	421	320	229	161	103	73	47
3.75°	868	807	731	615	496	379	266	189	116	82	51
2.5°	997	923	840	707	570	436	303	215	129	91	55
1.25°	1124	1036	946	794	641	490	338	240	141	100	58
0°	1246	1146	1046	876	706	538	370	261	152	106	61
-1.25°	1100	1017	931	783	633	485	336	239	141	99	58
-2.5°	951	885	810	685	556	428	300	213	128	91	54
-3.75°	801	752	687	584	476	367	261	185	115	81	50
-5°	653	619	564	483	396	306	222	157	101	72	46
-6.25°	508	489	446	384	318	247	184	129	87	62	42
-7.5°	369	363	333	290	246	191	147	103	74	52	38
-8.75°	242	241	230	206	180	142	114	79	62	43	34
-10°	202	175	142	134	123	104	85	63	51	37	30
-11.25°	165	143	115	98	78	72	61	50	41	32	27
-12.5°	133	114	97	82	66	55	43	39	33	28	24
-13.75°	104	90	80	67	56	47	38	33	27	25	21
-15°	80	73	64	55	48	39	34	29	25	22	19
-16.25°	63	58	51	46	40	34	30	25	23	20	18
-17.5°	50	46	42	38	33	30	26	23	21	19	17
-18.75°	39	37	35	31	29	26	23	21	19	17	16
-20°	31	31	29	27	25	22	21	19	17	16	15
-21.25°	26	26	25	24	22	20	19	17	16	15	15



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	23	22	22	20	19	18	17	16	15	14	14
-23.75°	21	20	19	18	18	17	16	15	14	14	13
-25°	19	18	17	17	16	15	15	14	14	13	12
-26.25°	17	17	16	15	15	14	14	13	13	12	12
-27.5°	16	15	15	14	14	13	13	12	12	12	11
-28.75°	15	14	14	14	13	13	12	12	11	11	10
-30°	14	14	13	13	12	12	11	11	11	10	10
-31.25°	13	13	12	12	11	11	11	11	10	10	9
-32.5°	12	12	12	11	11	11	10	10	10	9	9
-33.75°	12	11	11	11	10	10	10	9	9	8	8
-35°	11	10	10	10	10	10	9	9	8	8	8
-36.25°	10	10	10	10	9	9	8	8	8	7	7
-37.5°	10	10	9	9	9	8	8	8	7	7	7
-38.75°	9	9	9	8	8	8	7	7	7	7	6
-40°	9	8	8	8	7	7	7	7	6	6	6
-41.25°	8	8	7	7	7	7	6	6	6	6	6
-42.5°	7	7	7	6	6	6	6	6	6	5	5
-43.75°	6	6	6	6	6	6	6	5	5	5	5
-45°	6	6	6	6	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	4	4	4
-47.5°	5	5	5	5	5	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	3
-50°	4	4	4	4	4	4	3	3	3	3	3
-51.25°	4	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	2
-53.75°	3	3	3	3	3	3	3	2	2	2	2
-55°	3	3	3	3	3	2	2	2	2	2	2
-56.25°	3	2	2	2	2	2	2	2	2	1	1
-57.5°	2	2	2	2	2	2	1	1	1	1	1
-58.75°	2	2	1	1	1	1	1	1	1	1	0
-60°	1	1	1	1	1	1	1	0	0	0	0
-61.25°	1	1	1	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	1	1	0	0	0	0	0	0	0	0	0
52.5°	1	1	1	1	0	0	0	0	0	0	0
51.25°	2	1	1	1	1	0	0	0	0	0	0
50°	2	2	1	1	1	1	1	0	0	0	0
48.75°	2	2	2	2	1	1	1	1	0	0	0
47.5°	3	2	2	2	2	1	1	1	1	0	0
46.25°	3	3	3	2	2	2	2	1	1	1	0
45°	4	3	3	3	2	2	2	2	1	1	1
43.75°	4	4	4	3	3	3	2	2	2	1	1
42.5°	5	5	4	4	3	3	3	2	2	2	1
41.25°	5	5	5	4	4	3	3	3	2	2	2
40°	6	6	5	5	4	4	3	3	3	2	2
38.75°	6	6	6	5	5	4	4	4	3	3	2
37.5°	7	6	6	6	5	5	4	4	4	3	3
36.25°	7	7	6	6	6	5	5	4	4	3	3
35°	7	7	7	7	6	6	5	5	4	4	3



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	8	8	7	7	7	6	6	5	5	4	4
32.5°	8	8	8	7	7	7	6	6	5	5	4
31.25°	9	8	8	8	7	7	7	6	5	5	4
30°	9	9	9	8	8	7	7	7	6	5	5
28.75°	10	9	9	9	8	8	7	7	6	6	5
27.5°	10	10	10	9	9	8	7	7	7	6	5
26.25°	11	10	10	10	9	8	8	7	7	6	6
25°	12	11	10	10	10	9	8	8	7	7	6
23.75°	12	12	11	10	10	9	9	8	8	7	6
22.5°	13	12	11	11	10	10	9	8	8	7	7
21.25°	14	13	12	11	11	10	10	9	8	8	7
20°	14	14	13	12	11	10	10	9	8	8	7
18.75°	15	14	14	12	11	11	10	10	9	8	8
17.5°	16	15	14	13	12	11	11	10	9	8	8
16.25°	17	16	15	14	13	11	11	11	10	9	8
15°	18	16	15	15	13	12	11	11	10	9	8
13.75°	20	17	16	15	14	13	12	11	10	10	9
12.5°	21	19	17	16	14	13	12	11	11	10	9
11.25°	23	20	17	16	15	14	12	12	11	10	9
10°	24	21	18	17	16	14	13	12	11	10	9
8.75°	27	23	19	17	16	15	13	12	12	11	10
7.5°	30	24	20	18	17	15	14	13	12	11	10
6.25°	33	25	21	19	17	16	14	13	12	11	10
5°	36	26	22	19	18	16	14	13	12	11	10
3.75°	39	27	23	20	18	16	15	13	12	12	11
2.5°	41	28	24	20	18	17	15	14	13	12	11
1.25°	44	29	25	21	19	17	15	14	13	12	11
0°	45	30	25	21	19	17	15	14	13	12	11
-1.25°	43	29	25	21	19	17	15	14	13	12	11
-2.5°	41	28	24	20	18	17	15	14	13	12	11
-3.75°	38	27	23	20	18	16	15	13	12	12	11
-5°	35	26	22	19	18	16	14	13	12	11	10
-6.25°	32	25	21	19	17	16	14	13	12	11	10
-7.5°	29	23	20	18	17	15	14	13	12	11	10
-8.75°	26	22	19	17	16	15	13	12	12	11	10
-10°	23	21	18	17	16	14	13	12	11	10	9
-11.25°	22	20	17	16	15	14	12	12	11	10	9
-12.5°	21	18	17	16	14	13	12	11	11	10	9
-13.75°	19	17	16	15	14	13	12	11	10	10	9
-15°	18	16	15	15	13	12	11	11	10	9	8
-16.25°	17	16	15	14	13	11	11	11	10	9	8
-17.5°	16	15	14	13	12	11	11	10	9	8	8
-18.75°	15	14	14	12	11	11	10	10	9	8	8
-20°	14	14	13	12	11	10	10	9	8	8	7
-21.25°	14	13	12	11	11	10	10	9	8	8	7



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	13	12	11	11	10	10	9	8	8	7	7
-23.75°	12	12	11	10	10	9	9	8	8	7	6
-25°	12	11	10	10	10	9	8	8	7	7	6
-26.25°	11	10	10	10	9	8	8	7	7	6	6
-27.5°	10	10	10	9	9	8	7	7	7	6	5
-28.75°	10	9	9	9	8	8	7	7	6	6	5
-30°	9	9	9	8	8	7	7	7	6	5	5
-31.25°	9	8	8	8	7	7	7	6	5	5	4
-32.5°	8	8	8	7	7	7	6	6	5	5	4
-33.75°	8	8	7	7	7	6	6	5	5	4	4
-35°	7	7	7	7	6	6	5	5	5	4	4
-36.25°	7	7	6	6	6	5	5	5	4	4	3
-37.5°	7	6	6	6	5	5	5	4	4	3	3
-38.75°	6	6	6	5	5	5	4	4	4	3	2
-40°	6	6	5	5	5	4	4	4	3	3	2
-41.25°	5	5	5	5	4	4	4	3	3	2	2
-42.5°	5	5	5	4	4	4	3	3	2	2	2
-43.75°	5	5	4	4	4	3	3	3	2	2	1
-45°	4	4	4	4	3	3	3	2	2	2	1
-46.25°	4	4	4	3	3	3	2	2	2	1	1
-47.5°	4	3	3	3	3	2	2	2	1	1	1
-48.75°	3	3	3	3	2	2	2	1	1	1	1
-50°	3	3	2	2	2	2	1	1	1	1	1
-51.25°	3	2	2	2	2	1	1	1	1	1	0
-52.5°	2	2	2	2	1	1	1	1	0	0	0
-53.75°	2	2	1	1	1	1	1	0	0	0	0
-55°	1	1	1	1	1	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	1	0	0	0	0	0	0	0	0	0	0
42.5°	1	1	0	0	0	0	0	0	0	0	0
41.25°	1	1	1	0	0	0	0	0	0	0	0
40°	1	1	1	0	0	0	0	0	0	0	0
38.75°	2	1	1	1	0	0	0	0	0	0	0
37.5°	2	2	1	1	1	0	0	0	0	0	0
36.25°	2	2	1	1	1	0	0	0	0	0	0
35°	3	2	2	1	1	1	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	2	2	1	1	0	0	0	0	0
32.5°	4	3	2	2	1	1	1	0	0	0	0
31.25°	4	3	3	2	2	1	1	0	0	0	0
30°	4	4	3	2	2	1	1	1	0	0	0
28.75°	5	4	3	3	2	1	1	1	0	0	0
27.5°	5	4	4	3	2	2	1	1	1	0	0
26.25°	5	5	4	3	3	2	1	1	1	0	0
25°	5	5	4	4	3	2	2	1	1	1	0
23.75°	6	5	5	4	3	2	2	1	1	1	0
22.5°	6	5	5	4	4	3	2	1	1	1	0
21.25°	6	6	5	5	4	3	2	1	1	1	1
20°	7	6	5	5	4	3	2	2	1	1	1
18.75°	7	6	5	5	4	3	2	2	1	1	1
17.5°	7	7	6	5	5	4	3	2	1	1	1
16.25°	8	7	6	5	5	4	3	2	1	1	1
15°	8	7	6	5	5	4	3	2	2	1	1
13.75°	8	7	6	5	5	5	3	2	2	1	1
12.5°	8	8	7	6	5	5	4	2	2	1	1
11.25°	8	8	7	6	5	5	4	3	2	1	1
10°	9	8	7	6	5	5	4	3	2	1	1
8.75°	9	8	7	6	6	5	4	3	2	1	1
7.5°	9	8	7	6	6	5	4	3	2	1	1
6.25°	9	8	8	7	6	5	5	3	2	1	1
5°	9	9	8	7	6	5	5	3	2	1	1
3.75°	10	9	8	7	6	5	5	3	2	1	1
2.5°	10	9	8	7	6	5	5	3	2	1	1
1.25°	10	9	8	7	6	5	5	3	2	1	1
0°	10	9	8	7	6	5	5	3	2	2	1
-1.25°	10	9	8	7	6	5	5	3	2	1	1
-2.5°	10	9	8	7	6	5	5	3	2	1	1
-3.75°	10	9	8	7	6	5	5	3	2	1	1
-5°	9	9	8	7	6	5	5	3	2	1	1
-6.25°	9	8	8	7	6	5	5	3	2	1	1
-7.5°	9	8	7	6	6	5	4	3	2	1	1
-8.75°	9	8	7	6	6	5	4	3	2	1	1
-10°	9	8	7	6	5	5	4	3	2	1	1
-11.25°	8	8	7	6	5	5	4	3	2	1	1
-12.5°	8	8	7	6	5	5	4	2	2	1	1
-13.75°	8	7	6	5	5	5	3	2	2	1	1
-15°	8	7	6	5	5	4	3	2	2	1	1
-16.25°	8	7	6	5	5	4	3	2	1	1	1
-17.5°	7	7	6	5	5	4	3	2	1	1	1
-18.75°	7	6	5	5	4	3	2	2	1	1	1
-20°	7	6	5	5	4	3	2	2	1	1	1
-21.25°	6	6	5	5	4	3	2	1	1	1	1



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	6	5	5	4	4	3	2	1	1	1	1
-23.75°	6	5	5	4	3	2	2	1	1	1	1
-25°	5	5	4	4	3	2	2	1	1	1	1
-26.25°	5	5	4	3	3	2	1	1	1	1	1
-27.5°	5	4	4	3	2	2	1	1	1	1	1
-28.75°	5	4	3	3	2	1	1	1	1	1	0
-30°	4	4	3	2	2	1	1	1	1	1	0
-31.25°	4	3	3	2	2	1	1	1	1	1	0
-32.5°	4	3	2	2	1	1	1	1	1	0	0
-33.75°	3	3	2	2	1	1	1	1	1	0	0
-35°	3	2	2	1	1	1	1	1	0	0	0
-36.25°	3	2	2	1	1	1	1	1	0	0	0
-37.5°	2	2	1	1	1	1	1	0	0	0	0
-38.75°	2	2	1	1	1	1	1	0	0	0	0
-40°	2	1	1	1	1	1	0	0	0	0	0
-41.25°	2	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-43.75°	1	1	1	1	0	0	0	0	0	0	0
-45°	1	1	1	1	0	0	0	0	0	0	0
-46.25°	1	1	1	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
16.25°	1	0	0	0	0	0	0	0	0	0	0
15°	1	0	0	0	0	0	0	0	0	0	0
13.75°	1	0	0	0	0	0	0	0	0	0	0
12.5°	1	1	0	0	0	0	0	0	0	0	0
11.25°	1	1	0	0	0	0	0	0	0	0	0
10°	1	1	0	0	0	0	0	0	0	0	0
8.75°	1	1	0	0	0	0	0	0	0	0	0
7.5°	1	1	0	0	0	0	0	0	0	0	0
6.25°	1	1	0	0	0	0	0	0	0	0	0
5°	1	1	0	0	0	0	0	0	0	0	0
3.75°	1	1	0	0	0	0	0	0	0	0	0
2.5°	1	1	0	0	0	0	0	0	0	0	0
1.25°	1	1	0	0	0	0	0	0	0	0	0
0°	1	1	0	0	0	0	0	0	0	0	0
-1.25°	1	1	0	0	0	0	0	0	0	0	0
-2.5°	1	1	0	0	0	0	0	0	0	0	0
-3.75°	1	1	0	0	0	0	0	0	0	0	0
-5°	1	1	0	0	0	0	0	0	0	0	0
-6.25°	1	1	0	0	0	0	0	0	0	0	0
-7.5°	1	1	0	0	0	0	0	0	0	0	0
-8.75°	1	1	0	0	0	0	0	0	0	0	0
-10°	1	1	0	0	0	0	0	0	0	0	0
-11.25°	1	1	0	0	0	0	0	0	0	0	0
-12.5°	1	1	0	0	0	0	0	0	0	0	0
-13.75°	1	1	0	0	0	0	0	0	0	0	0
-15°	1	1	0	0	0	0	0	0	0	0	0
-16.25°	1	1	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-18.75°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0
-21.25°	1	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	1	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-25 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-BK-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)