

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4010-12-CS-DIFF**

Test Date: 04/05/18

**Test Information**


Test Method: LM-79-08  
Report Number: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-36)  
Test Lab: INNOVATION CENTER(G2)  
Test Date: 04/05/18  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED4010-12-CS-DIFF  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 10 DEGREE SPOT OPTIC,  
REGRESSED HOOD SILVER, DIFFUSED LENS  
Light Source: (1) SORAA 4000K 95 CRI 10° NSP LED  
SM16-07-10D-940-03  
Ballast/Driver: CHROMA POWER SUPPLY IN0004

**Summary**

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	232.6 lumens	Max Intensity:	930 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	31.0 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	22.6°H x 22.6°V	Field Angle (10%):	47.7°H x 47.7°V
Beam Lumens:	79.7 lumens	Field Lumens:	168.5 lumens
Beam Efficiency:	34.3%	Field Efficiency:	72.5%
Input Watts (W):	7.5		
Input Voltage (V):	12.0		
Input Current (A <sub>in</sub> ):	0.656		
Voltage Rise (V):	NR		
Power Factor:	0.9482		
Total Harmonic Distortion (THDi):	27.5%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	9 HR		
Ambient Temperature (°C):	24.7		
Test Distance:	25 FT		

REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF


### Iso-Candela Plot






REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

### Lumen Table




REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

### Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

### Luminous Intensity Plot



**Beam:**  
 H Angle: 22.6°  
 V Angle: 22.6°  
 Lumens: 79.7  
 Efficiency: 34.3%

**Field:**  
 H Angle: 47.7°  
 V Angle: 47.7°  
 Lumens: 168.5  
 Efficiency: 72.5%

**Spill:**  
 Lumens: 64  
 Efficiency: 27.5%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	1
23.75°	0	0	0	0	0	0	0	0	0	0	1
22.5°	0	0	0	0	0	0	0	0	0	0	1
21.25°	0	0	0	0	0	0	0	0	0	0	1
20°	0	0	0	0	0	0	0	0	0	0	1
18.75°	0	0	0	0	0	0	0	0	0	0	1
17.5°	0	0	0	0	0	0	0	0	0	0	1
16.25°	0	0	0	0	0	0	0	0	0	0	1
15°	0	0	0	0	0	0	0	0	0	0	1
13.75°	0	0	0	0	0	0	0	0	0	0	1
12.5°	0	0	0	0	0	0	0	0	0	0	1
11.25°	0	0	0	0	0	0	0	0	0	0	1
10°	0	0	0	0	0	0	0	0	0	0	1
8.75°	0	0	0	0	0	0	0	0	0	0	1
7.5°	0	0	0	0	0	0	0	0	0	0	1
6.25°	0	0	0	0	0	0	0	0	0	0	1
5°	0	0	0	0	0	0	0	0	0	0	1
3.75°	0	0	0	0	0	0	0	0	0	0	1
2.5°	0	0	0	0	0	0	0	0	0	0	1
1.25°	0	0	0	0	0	0	0	0	0	0	1
0°	0	0	0	0	0	0	0	0	0	0	1
-1.25°	0	0	0	0	0	0	0	0	0	0	1
-2.5°	0	0	0	0	0	0	0	0	0	0	1
-3.75°	0	0	0	0	0	0	0	0	0	0	1
-5°	0	0	0	0	0	0	0	0	0	0	1
-6.25°	0	0	0	0	0	0	0	0	0	0	1
-7.5°	0	0	0	0	0	0	0	0	0	0	1
-8.75°	0	0	0	0	0	0	0	0	0	0	1
-10°	0	0	0	0	0	0	0	0	0	0	1
-11.25°	0	0	0	0	0	0	0	0	0	0	1
-12.5°	0	0	0	0	0	0	0	0	0	0	1
-13.75°	0	0	0	0	0	0	0	0	0	0	1
-15°	0	0	0	0	0	0	0	0	0	0	1
-16.25°	0	0	0	0	0	0	0	0	0	0	1
-17.5°	0	0	0	0	0	0	0	0	0	0	1
-18.75°	0	0	0	0	0	0	0	0	0	0	1
-20°	0	0	0	0	0	0	0	0	0	0	1
-21.25°	0	0	0	0	0	0	0	0	0	0	1





REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	1
-23.75°	0	0	0	0	0	0	0	0	0	0	1
-25°	0	0	0	0	0	0	0	0	0	0	1
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	1
62.5°	0	0	0	0	0	0	0	0	0	1	1
61.25°	0	0	0	0	0	0	0	0	0	1	1
60°	0	0	0	0	0	0	0	0	1	1	1
58.75°	0	0	0	0	0	0	0	1	1	1	1
57.5°	0	0	0	0	0	0	0	1	1	1	1
56.25°	0	0	0	0	0	0	1	1	1	1	1
55°	0	0	0	0	0	1	1	1	1	1	1
53.75°	0	0	0	0	0	1	1	1	1	1	1
52.5°	0	0	0	0	1	1	1	1	1	1	1
51.25°	0	0	0	0	1	1	1	1	1	1	1
50°	0	0	0	0	1	1	1	1	1	1	1
48.75°	0	0	0	1	1	1	1	1	1	1	1
47.5°	0	0	0	1	1	1	1	1	1	1	1
46.25°	0	0	0	1	1	1	1	1	1	1	1
45°	0	0	1	1	1	1	1	1	1	1	1
43.75°	0	0	1	1	1	1	1	1	1	1	1
42.5°	0	0	1	1	1	1	1	1	1	1	1
41.25°	0	0	1	1	1	1	1	1	1	1	1
40°	0	1	1	1	1	1	1	1	1	1	1
38.75°	0	1	1	1	1	1	1	1	1	1	1
37.5°	0	1	1	1	1	1	1	1	1	1	1
36.25°	0	1	1	1	1	1	1	1	1	1	1
35°	0	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	2
32.5°	1	1	1	1	1	1	1	1	1	1	2
31.25°	1	1	1	1	1	1	1	1	1	1	2
30°	1	1	1	1	1	1	1	1	1	2	2
28.75°	1	1	1	1	1	1	1	1	1	2	2
27.5°	1	1	1	1	1	1	1	1	1	2	2
26.25°	1	1	1	1	1	1	1	1	1	2	2
25°	1	1	1	1	1	1	1	1	2	2	2
23.75°	1	1	1	1	1	1	1	1	2	2	2
22.5°	1	1	1	1	1	1	1	1	2	2	2
21.25°	1	1	1	1	1	1	1	1	2	2	2
20°	1	1	1	1	1	1	1	1	2	2	2
18.75°	1	1	1	1	1	1	1	1	2	2	2
17.5°	1	1	1	1	1	1	1	2	2	2	2
16.25°	1	1	1	1	1	1	1	2	2	2	2
15°	1	1	1	1	1	1	1	2	2	2	2
13.75°	1	1	1	1	1	1	1	2	2	2	2
12.5°	1	1	1	1	1	1	1	2	2	2	2
11.25°	1	1	1	1	1	1	1	2	2	2	2
10°	1	1	1	1	1	1	1	2	2	2	2
8.75°	1	1	1	1	1	1	1	2	2	2	2
7.5°	1	1	1	1	1	1	1	2	2	2	2
6.25°	1	1	1	1	1	1	1	2	2	2	2
5°	1	1	1	1	1	1	1	2	2	2	2
3.75°	1	1	1	1	1	1	1	2	2	2	2
2.5°	1	1	1	1	1	1	1	2	2	2	2
1.25°	1	1	1	1	1	1	1	2	2	2	2
0°	1	1	1	1	1	1	2	2	2	2	3
-1.25°	1	1	1	1	1	1	1	2	2	2	2
-2.5°	1	1	1	1	1	1	1	2	2	2	2
-3.75°	1	1	1	1	1	1	1	2	2	2	2
-5°	1	1	1	1	1	1	1	2	2	2	2
-6.25°	1	1	1	1	1	1	1	2	2	2	2
-7.5°	1	1	1	1	1	1	1	2	2	2	2
-8.75°	1	1	1	1	1	1	1	2	2	2	2
-10°	1	1	1	1	1	1	1	2	2	2	2
-11.25°	1	1	1	1	1	1	1	2	2	2	2
-12.5°	1	1	1	1	1	1	1	2	2	2	2
-13.75°	1	1	1	1	1	1	1	2	2	2	2
-15°	1	1	1	1	1	1	1	2	2	2	2
-16.25°	1	1	1	1	1	1	1	2	2	2	2
-17.5°	1	1	1	1	1	1	1	2	2	2	2
-18.75°	1	1	1	1	1	1	1	1	2	2	2
-20°	1	1	1	1	1	1	1	1	2	2	2
-21.25°	1	1	1	1	1	1	1	1	2	2	2



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	2	2	2
-23.75°	1	1	1	1	1	1	1	1	2	2	2
-25°	1	1	1	1	1	1	1	1	2	2	2
-26.25°	1	1	1	1	1	1	1	1	1	2	2
-27.5°	1	1	1	1	1	1	1	1	1	2	2
-28.75°	1	1	1	1	1	1	1	1	1	2	2
-30°	1	1	1	1	1	1	1	1	1	2	2
-31.25°	1	1	1	1	1	1	1	1	1	1	2
-32.5°	1	1	1	1	1	1	1	1	1	1	2
-33.75°	1	1	1	1	1	1	1	1	1	1	2
-35°	0	1	1	1	1	1	1	1	1	1	1
-36.25°	0	1	1	1	1	1	1	1	1	1	1
-37.5°	0	1	1	1	1	1	1	1	1	1	1
-38.75°	0	1	1	1	1	1	1	1	1	1	1
-40°	0	1	1	1	1	1	1	1	1	1	1
-41.25°	0	0	1	1	1	1	1	1	1	1	1
-42.5°	0	0	1	1	1	1	1	1	1	1	1
-43.75°	0	0	1	1	1	1	1	1	1	1	1
-45°	0	0	1	1	1	1	1	1	1	1	1
-46.25°	0	0	0	1	1	1	1	1	1	1	1
-47.5°	0	0	0	1	1	1	1	1	1	1	1
-48.75°	0	0	0	1	1	1	1	1	1	1	1
-50°	0	0	0	0	1	1	1	1	1	1	1
-51.25°	0	0	0	0	1	1	1	1	1	1	1
-52.5°	0	0	0	0	1	1	1	1	1	1	1
-53.75°	0	0	0	0	0	1	1	1	1	1	1
-55°	0	0	0	0	0	1	1	1	1	1	1
-56.25°	0	0	0	0	0	0	1	1	1	1	1
-57.5°	0	0	0	0	0	0	0	1	1	1	1
-58.75°	0	0	0	0	0	0	0	1	1	1	1
-60°	0	0	0	0	0	0	0	0	1	1	1
-61.25°	0	0	0	0	0	0	0	0	0	1	1
-62.5°	0	0	0	0	0	0	0	0	0	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	1	1	1
70°	0	0	0	0	0	0	1	1	1	1	1
68.75°	0	0	0	0	0	1	1	1	1	1	1
67.5°	0	0	0	1	1	1	1	1	1	1	1
66.25°	0	0	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	2
53.75°	1	1	1	1	1	1	1	1	1	2	2
52.5°	1	1	1	1	1	1	1	1	2	2	2
51.25°	1	1	1	1	1	1	1	2	2	2	2
50°	1	1	1	1	1	1	2	2	2	2	2
48.75°	1	1	1	1	1	2	2	2	2	2	2
47.5°	1	1	1	1	2	2	2	2	2	2	2
46.25°	1	1	1	1	2	2	2	2	2	2	3
45°	1	1	1	2	2	2	2	2	2	3	3
43.75°	1	1	1	2	2	2	2	2	2	3	3
42.5°	1	1	2	2	2	2	2	2	3	3	3
41.25°	1	1	2	2	2	2	2	3	3	3	4
40°	1	2	2	2	2	2	2	3	3	3	4
38.75°	1	2	2	2	2	2	3	3	3	4	4
37.5°	2	2	2	2	2	2	3	3	4	4	5
36.25°	2	2	2	2	2	3	3	3	4	4	5
35°	2	2	2	2	2	3	3	4	4	5	5



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	3	3	3	4	4	5	6
32.5°	2	2	2	2	3	3	4	4	5	5	6
31.25°	2	2	2	3	3	3	4	4	5	6	7
30°	2	2	2	3	3	4	4	5	5	6	7
28.75°	2	2	2	3	3	4	4	5	6	7	7
27.5°	2	2	3	3	3	4	4	5	6	7	8
26.25°	2	2	3	3	4	4	5	6	6	7	8
25°	2	2	3	3	4	4	5	6	7	8	9
23.75°	2	2	3	3	4	4	5	6	7	8	9
22.5°	2	3	3	3	4	5	6	6	7	8	9
21.25°	2	3	3	4	4	5	6	7	8	9	9
20°	2	3	3	4	4	5	6	7	8	9	10
18.75°	2	3	3	4	4	5	6	7	8	9	10
17.5°	2	3	3	4	5	6	7	7	8	9	10
16.25°	3	3	3	4	5	6	7	8	9	10	10
15°	3	3	4	4	5	6	7	8	9	10	11
13.75°	3	3	4	4	5	6	7	8	9	10	11
12.5°	3	3	4	4	5	6	7	8	9	10	11
11.25°	3	3	4	4	5	6	7	8	9	10	11
10°	3	3	4	5	6	7	8	8	9	10	11
8.75°	3	3	4	5	6	7	8	9	10	11	12
7.5°	3	3	4	5	6	7	8	9	10	11	12
6.25°	3	3	4	5	6	7	8	9	10	11	12
5°	3	3	4	5	6	7	8	9	10	11	12
3.75°	3	3	4	5	6	7	8	9	10	11	12
2.5°	3	3	4	5	6	7	8	9	10	11	12
1.25°	3	3	4	5	6	7	8	9	10	11	12
0°	3	4	4	5	6	7	8	9	10	11	12
-1.25°	3	3	4	5	6	7	8	9	10	11	12
-2.5°	3	3	4	5	6	7	8	9	10	11	12
-3.75°	3	3	4	5	6	7	8	9	10	11	12
-5°	3	3	4	5	6	7	8	9	10	11	12
-6.25°	3	3	4	5	6	7	8	9	10	11	12
-7.5°	3	3	4	5	6	7	8	9	10	11	12
-8.75°	3	3	4	5	6	7	8	9	10	11	12
-10°	3	3	4	5	6	7	8	8	9	10	11
-11.25°	3	3	4	4	5	6	7	8	9	10	11
-12.5°	3	3	4	4	5	6	7	8	9	10	11
-13.75°	3	3	4	4	5	6	7	8	9	10	11
-15°	3	3	4	4	5	6	7	8	9	10	11
-16.25°	3	3	3	4	5	6	7	8	9	10	10
-17.5°	2	3	3	4	5	6	7	7	8	9	10
-18.75°	2	3	3	4	4	5	6	7	8	9	10
-20°	2	3	3	4	4	5	6	7	8	9	10
-21.25°	2	3	3	4	4	5	6	7	8	9	9





REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	3	3	3	4	5	6	6	7	8	9
-23.75°	2	2	3	3	4	4	5	6	7	8	9
-25°	2	2	3	3	4	4	5	6	7	8	9
-26.25°	2	2	3	3	4	4	5	6	6	7	8
-27.5°	2	2	3	3	3	4	4	5	6	7	8
-28.75°	2	2	2	3	3	4	4	5	6	7	7
-30°	2	2	2	3	3	4	4	5	5	6	7
-31.25°	2	2	2	3	3	3	4	4	5	6	7
-32.5°	2	2	2	2	3	3	4	4	5	5	6
-33.75°	2	2	2	2	3	3	3	4	4	5	6
-35°	2	2	2	2	2	3	3	4	4	5	5
-36.25°	2	2	2	2	2	3	3	3	4	4	5
-37.5°	2	2	2	2	2	2	3	3	4	4	5
-38.75°	1	2	2	2	2	2	3	3	3	4	4
-40°	1	2	2	2	2	2	2	3	3	3	4
-41.25°	1	1	2	2	2	2	2	3	3	3	4
-42.5°	1	1	2	2	2	2	2	2	3	3	3
-43.75°	1	1	1	2	2	2	2	2	2	3	3
-45°	1	1	1	2	2	2	2	2	2	3	3
-46.25°	1	1	1	1	2	2	2	2	2	2	3
-47.5°	1	1	1	1	2	2	2	2	2	2	2
-48.75°	1	1	1	1	1	2	2	2	2	2	2
-50°	1	1	1	1	1	1	2	2	2	2	2
-51.25°	1	1	1	1	1	1	1	2	2	2	2
-52.5°	1	1	1	1	1	1	1	1	2	2	2
-53.75°	1	1	1	1	1	1	1	1	1	2	2
-55°	1	1	1	1	1	1	1	1	1	1	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	1	1	1	1	1	1	1	1	1
-67.5°	0	0	0	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	1	1	1	1	1	1
-70°	0	0	0	0	0	0	1	1	1	1	1
-71.25°	0	0	0	0	0	0	0	0	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	1	1	1	1
73.75°	0	0	0	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	2	2
61.25°	1	1	1	1	1	1	1	2	2	2	2
60°	1	1	1	1	1	2	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	3
55°	2	2	2	2	2	2	2	2	3	3	3
53.75°	2	2	2	2	2	2	3	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	4	4
51.25°	2	2	2	3	3	3	3	3	4	4	4
50°	2	2	3	3	3	3	4	4	4	5	5
48.75°	2	3	3	3	3	4	4	4	5	5	6
47.5°	3	3	3	3	4	4	4	5	5	6	6
46.25°	3	3	3	4	4	5	5	6	6	7	7
45°	3	3	4	4	5	5	6	6	7	7	8
43.75°	3	4	4	5	5	6	6	7	7	8	9
42.5°	4	4	5	5	6	6	7	8	8	9	9
41.25°	4	4	5	6	6	7	8	8	9	9	10
40°	4	5	6	6	7	8	8	9	9	10	11
38.75°	5	5	6	7	7	8	9	9	10	11	11
37.5°	5	6	7	7	8	9	9	10	11	11	12
36.25°	6	6	7	8	9	9	10	11	11	12	13
35°	6	7	8	8	9	10	10	11	12	13	14



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	7	7	8	9	10	10	11	12	13	14	15
32.5°	7	8	9	9	10	11	11	12	13	14	15
31.25°	7	8	9	10	11	11	12	13	14	15	16
30°	8	9	9	10	11	12	13	14	15	16	16
28.75°	8	9	10	11	11	12	13	15	16	16	17
27.5°	9	9	10	11	12	13	14	15	16	17	18
26.25°	9	10	11	11	12	14	15	16	17	17	19
25°	9	10	11	12	13	14	15	16	17	18	19
23.75°	10	11	11	12	14	15	16	17	18	19	20
22.5°	10	11	12	13	14	15	16	17	18	20	21
21.25°	10	11	12	13	15	16	17	18	19	20	21
20°	11	12	13	14	15	16	17	18	20	21	22
18.75°	11	12	13	14	16	16	17	19	20	21	23
17.5°	11	12	14	15	16	17	18	19	21	22	23
16.25°	11	13	14	15	16	17	18	20	21	23	24
15°	12	13	14	15	16	17	19	20	22	23	25
13.75°	12	13	15	16	17	18	19	21	22	24	26
12.5°	12	14	15	16	17	18	20	21	23	24	26
11.25°	12	14	15	16	17	19	20	21	23	25	27
10°	13	14	15	16	17	19	20	22	23	25	27
8.75°	13	14	15	16	18	19	21	22	24	26	28
7.5°	13	14	16	17	18	19	21	22	24	26	28
6.25°	13	15	16	17	18	20	21	23	24	26	29
5°	13	15	16	17	18	20	21	23	25	27	29
3.75°	13	15	16	17	18	20	21	23	25	27	29
2.5°	13	15	16	17	18	20	21	23	25	27	29
1.25°	13	15	16	17	18	20	21	23	25	27	29
0°	14	15	16	17	19	20	22	23	25	27	30
-1.25°	13	15	16	17	18	20	21	23	25	27	29
-2.5°	13	15	16	17	18	20	21	23	25	27	29
-3.75°	13	15	16	17	18	20	21	23	25	27	29
-5°	13	15	16	17	18	20	21	23	25	27	29
-6.25°	13	15	16	17	18	20	21	23	24	26	29
-7.5°	13	14	16	17	18	19	21	22	24	26	28
-8.75°	13	14	15	16	18	19	21	22	24	26	28
-10°	13	14	15	16	17	19	20	22	23	25	27
-11.25°	12	14	15	16	17	19	20	21	23	25	27
-12.5°	12	14	15	16	17	18	20	21	23	24	26
-13.75°	12	13	15	16	17	18	19	21	22	24	26
-15°	12	13	14	15	16	17	19	20	22	23	25
-16.25°	11	13	14	15	16	17	18	20	21	23	24
-17.5°	11	12	14	15	16	17	18	19	21	22	23
-18.75°	11	12	13	14	16	16	17	19	20	21	23
-20°	11	12	13	14	15	16	17	18	20	21	22
-21.25°	10	11	12	13	15	16	17	18	19	20	21



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	10	11	12	13	14	15	16	17	18	20	21
-23.75°	10	11	11	12	14	15	16	17	18	19	20
-25°	9	10	11	12	13	14	15	16	17	18	19
-26.25°	9	10	11	11	12	14	15	16	17	17	19
-27.5°	9	9	10	11	12	13	14	15	16	17	18
-28.75°	8	9	10	11	11	12	13	15	16	16	17
-30°	8	9	9	10	11	12	13	14	15	16	16
-31.25°	7	8	9	10	11	11	12	13	14	15	16
-32.5°	7	8	9	9	10	11	11	12	13	14	15
-33.75°	7	7	8	9	10	10	11	12	13	14	15
-35°	6	7	8	8	9	10	10	11	12	13	14
-36.25°	6	6	7	8	9	9	10	11	11	12	13
-37.5°	5	6	7	7	8	9	9	10	11	11	12
-38.75°	5	5	6	7	7	8	9	9	10	11	11
-40°	4	5	6	6	7	8	8	9	9	10	11
-41.25°	4	4	5	6	6	7	8	8	9	9	10
-42.5°	4	4	5	5	6	6	7	8	8	9	9
-43.75°	3	4	4	5	5	6	6	7	7	8	9
-45°	3	3	4	4	5	5	6	6	7	7	8
-46.25°	3	3	3	4	4	5	5	6	6	7	7
-47.5°	3	3	3	3	4	4	4	5	5	6	6
-48.75°	2	3	3	3	3	4	4	4	5	5	6
-50°	2	2	3	3	3	3	4	4	4	5	5
-51.25°	2	2	2	3	3	3	3	3	4	4	4
-52.5°	2	2	2	2	2	3	3	3	3	4	4
-53.75°	2	2	2	2	2	2	3	3	3	3	3
-55°	2	2	2	2	2	2	2	2	3	3	3
-56.25°	2	2	2	2	2	2	2	2	2	2	3
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	2	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	1	1	1
76.25°	0	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	2	2	2
65°	1	1	1	1	2	2	2	2	2	2	2
63.75°	1	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	3
60°	2	2	2	2	2	2	3	3	3	3	3
58.75°	2	2	2	3	3	3	3	3	3	3	3
57.5°	2	3	3	3	3	3	3	4	4	4	4
56.25°	3	3	3	3	4	4	4	4	4	4	5
55°	3	3	4	4	4	4	4	5	5	5	6
53.75°	4	4	4	4	5	5	5	6	6	6	6
52.5°	4	4	5	5	5	6	6	6	7	7	7
51.25°	5	5	5	6	6	7	7	7	8	8	8
50°	5	6	6	7	7	7	8	8	9	9	9
48.75°	6	7	7	7	8	8	9	9	9	10	10
47.5°	7	7	8	8	9	9	9	10	10	11	11
46.25°	8	8	9	9	9	10	10	11	11	11	12
45°	8	9	9	10	10	11	11	11	12	12	13
43.75°	9	10	10	11	11	11	12	12	13	14	14
42.5°	10	10	11	11	12	12	13	14	14	15	15
41.25°	10	11	11	12	13	13	14	15	15	16	16
40°	11	12	12	13	14	15	15	16	16	17	17
38.75°	12	13	13	14	15	16	16	17	17	18	18
37.5°	13	14	14	15	16	16	17	17	18	19	20
36.25°	14	15	15	16	16	17	18	19	19	20	21
35°	15	15	16	17	17	18	19	20	21	21	22



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	15	16	17	17	18	19	20	21	22	22	23
32.5°	16	17	17	18	19	20	21	22	23	24	25
31.25°	17	17	18	19	20	21	22	23	24	25	26
30°	17	18	19	20	21	22	23	25	26	27	28
28.75°	18	19	20	21	22	23	25	26	27	29	30
27.5°	19	20	21	22	23	25	26	27	29	31	32
26.25°	20	21	22	23	25	26	27	29	31	32	34
25°	21	22	23	24	26	27	29	31	33	35	36
23.75°	21	22	24	25	27	29	31	32	35	37	39
22.5°	22	23	25	26	28	30	32	34	36	39	42
21.25°	23	24	26	28	30	32	34	36	39	42	46
20°	24	25	27	29	31	33	36	38	42	45	49
18.75°	24	26	28	30	32	35	37	41	44	48	53
17.5°	25	27	29	31	34	36	39	43	47	52	57
16.25°	26	28	30	32	35	38	42	46	50	55	60
15°	27	29	31	34	36	39	44	48	53	58	65
13.75°	27	30	32	35	37	42	46	51	56	62	71
12.5°	28	31	33	36	39	43	48	53	59	67	75
11.25°	29	31	34	37	41	45	50	56	62	71	80
10°	30	32	35	38	42	47	52	58	66	75	85
8.75°	30	33	36	39	43	48	54	60	69	78	91
7.5°	31	33	36	40	45	50	56	62	72	82	95
6.25°	31	34	37	41	46	51	57	65	74	85	99
5°	31	34	37	42	46	52	58	66	76	89	102
3.75°	32	35	38	42	47	53	59	68	78	91	105
2.5°	32	35	38	43	48	54	59	69	79	93	107
1.25°	32	35	38	43	48	54	60	70	80	94	108
0°	32	35	38	43	48	54	60	70	80	94	108
-1.25°	32	35	38	43	48	54	60	70	80	94	108
-2.5°	32	35	38	43	48	54	59	69	79	93	107
-3.75°	32	35	38	42	47	53	59	68	78	91	105
-5°	31	34	37	42	46	52	58	66	76	89	102
-6.25°	31	34	37	41	46	51	57	65	74	85	99
-7.5°	31	33	36	40	45	50	56	62	72	82	95
-8.75°	30	33	36	39	43	48	54	60	69	78	91
-10°	30	32	35	38	42	47	52	58	66	75	85
-11.25°	29	31	34	37	41	45	50	56	62	71	80
-12.5°	28	31	33	36	39	43	48	53	59	67	75
-13.75°	27	30	32	35	37	42	46	51	56	62	71
-15°	27	29	31	34	36	39	44	48	53	58	65
-16.25°	26	28	30	32	35	38	42	46	50	55	60
-17.5°	25	27	29	31	34	36	39	43	47	52	57
-18.75°	24	26	28	30	32	35	37	41	44	48	53
-20°	24	25	27	29	31	33	36	38	42	45	49
-21.25°	23	24	26	28	30	32	34	36	39	42	46





REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	22	23	25	26	28	30	32	34	36	39	42
-23.75°	21	22	24	25	27	29	31	32	35	37	39
-25°	21	22	23	24	26	27	29	31	33	35	36
-26.25°	20	21	22	23	25	26	27	29	31	32	34
-27.5°	19	20	21	22	23	25	26	27	29	31	32
-28.75°	18	19	20	21	22	23	25	26	27	29	30
-30°	17	18	19	20	21	22	23	25	26	27	28
-31.25°	17	17	18	19	20	21	22	23	24	25	26
-32.5°	16	17	17	18	19	20	21	22	23	24	25
-33.75°	15	16	17	17	18	19	20	21	22	22	23
-35°	15	15	16	17	17	18	19	20	21	21	22
-36.25°	14	15	15	16	16	17	18	19	19	20	21
-37.5°	13	14	14	15	16	16	17	17	18	19	20
-38.75°	12	13	13	14	15	16	16	17	17	18	18
-40°	11	12	12	13	14	15	15	16	16	17	17
-41.25°	10	11	11	12	13	13	14	15	15	16	16
-42.5°	10	10	11	11	12	12	13	14	14	15	15
-43.75°	9	10	10	11	11	11	12	12	13	14	14
-45°	8	9	9	10	10	11	11	11	12	12	13
-46.25°	8	8	9	9	9	10	10	11	11	11	12
-47.5°	7	7	8	8	9	9	9	10	10	11	11
-48.75°	6	7	7	7	8	8	9	9	9	10	10
-50°	5	6	6	7	7	7	8	8	9	9	9
-51.25°	5	5	5	6	6	7	7	7	8	8	8
-52.5°	4	4	5	5	5	6	6	6	7	7	7
-53.75°	4	4	4	4	5	5	5	6	6	6	6
-55°	3	3	4	4	4	4	4	5	5	5	6
-56.25°	3	3	3	3	4	4	4	4	4	4	5
-57.5°	2	3	3	3	3	3	3	4	4	4	4
-58.75°	2	2	2	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	2	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	3
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	2	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	2	2	2	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	2	2	2
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	1	1	1



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	4	4	4	4	4	4
58.75°	4	4	4	4	4	4	4	4	4	5	5
57.5°	4	4	4	5	5	5	5	5	5	6	6
56.25°	5	5	5	6	6	6	6	6	6	7	7
55°	6	6	6	7	7	7	7	7	7	8	8
53.75°	7	7	7	7	8	8	8	8	8	8	9
52.5°	8	8	8	8	9	9	9	9	9	9	10
51.25°	9	9	9	9	10	10	10	10	10	10	11
50°	9	10	10	10	10	11	11	11	11	11	12
48.75°	10	11	11	11	11	12	12	12	12	13	13
47.5°	11	12	12	12	13	13	13	14	14	14	14
46.25°	12	13	13	14	14	14	15	15	15	15	15
45°	13	14	14	15	15	15	16	16	16	16	16
43.75°	15	15	16	16	16	16	17	17	17	17	18
42.5°	16	16	16	17	17	17	18	18	19	19	19
41.25°	17	17	17	18	18	19	19	20	20	20	21
40°	18	18	19	19	20	20	21	21	21	22	22
38.75°	19	20	20	21	21	22	22	23	23	23	24
37.5°	20	21	21	22	23	23	24	24	25	25	26
36.25°	21	22	23	23	24	25	26	26	27	27	28
35°	23	24	24	25	26	27	27	28	29	30	30



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	24	25	26	27	28	29	30	31	31	32	33
32.5°	26	27	28	29	30	31	32	33	34	35	36
31.25°	28	29	30	31	32	34	35	36	37	38	39
30°	30	31	32	34	35	36	37	39	41	42	43
28.75°	32	33	35	36	38	39	42	43	45	47	48
27.5°	34	36	37	39	42	44	46	48	50	52	54
26.25°	36	38	41	43	46	48	51	53	56	58	60
25°	39	42	44	47	50	53	56	59	62	66	69
23.75°	42	45	48	52	55	58	62	67	71	75	78
22.5°	46	49	53	57	60	65	71	75	80	85	91
21.25°	49	53	57	62	68	74	79	86	92	98	103
20°	53	58	63	69	76	82	90	97	104	112	120
18.75°	57	63	70	77	84	93	101	110	120	130	140
17.5°	62	69	77	85	94	104	114	127	138	149	162
16.25°	68	76	84	94	104	117	130	143	158	174	188
15°	74	82	93	104	117	132	146	164	182	199	216
13.75°	79	90	101	114	130	146	166	186	205	229	252
12.5°	86	97	110	127	143	164	186	207	235	262	288
11.25°	92	104	120	138	158	182	205	235	266	295	329
10°	98	112	130	149	174	199	229	262	295	334	371
8.75°	103	120	140	162	188	216	252	288	329	371	412
7.5°	108	128	148	174	201	236	274	315	361	405	455
6.25°	115	135	157	185	214	253	292	341	389	441	493
5°	120	140	165	194	228	268	312	363	414	472	528
3.75°	124	144	171	201	238	280	328	380	437	497	557
2.5°	127	147	176	206	246	288	340	393	454	516	580
1.25°	128	149	179	209	251	293	347	401	464	527	594
0°	129	150	180	210	253	295	350	404	468	531	599
-1.25°	128	149	179	209	251	293	347	401	464	527	594
-2.5°	127	147	176	206	246	288	340	393	454	516	580
-3.75°	124	144	171	201	238	280	328	380	437	497	557
-5°	120	140	165	194	228	268	312	363	414	472	528
-6.25°	115	135	157	185	214	253	292	341	389	441	493
-7.5°	108	128	148	174	201	236	274	315	361	405	455
-8.75°	103	120	140	162	188	216	252	288	329	371	412
-10°	98	112	130	149	174	199	229	262	295	334	371
-11.25°	92	104	120	138	158	182	205	235	266	295	329
-12.5°	86	97	110	127	143	164	186	207	235	262	288
-13.75°	79	90	101	114	130	146	166	186	205	229	252
-15°	74	82	93	104	117	132	146	164	182	199	216
-16.25°	68	76	84	94	104	117	130	143	158	174	188
-17.5°	62	69	77	85	94	104	114	127	138	149	162
-18.75°	57	63	70	77	84	93	101	110	120	130	140
-20°	53	58	63	69	76	82	90	97	104	112	120
-21.25°	49	53	57	62	68	74	79	86	92	98	103



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	46	49	53	57	60	65	71	75	80	85	91
-23.75°	42	45	48	52	55	58	62	67	71	75	78
-25°	39	42	44	47	50	53	56	59	62	66	69
-26.25°	36	38	41	43	46	48	51	53	56	58	60
-27.5°	34	36	37	39	42	44	46	48	50	52	54
-28.75°	32	33	35	36	38	39	42	43	45	47	48
-30°	30	31	32	34	35	36	37	39	41	42	43
-31.25°	28	29	30	31	32	34	35	36	37	38	39
-32.5°	26	27	28	29	30	31	32	33	34	35	36
-33.75°	24	25	26	27	28	29	30	31	31	32	33
-35°	23	24	24	25	26	27	27	28	29	30	30
-36.25°	21	22	23	23	24	25	26	26	27	27	28
-37.5°	20	21	21	22	23	23	24	24	25	25	26
-38.75°	19	20	20	21	21	22	22	23	23	23	24
-40°	18	18	19	19	20	20	21	21	21	22	22
-41.25°	17	17	17	18	18	19	19	20	20	20	21
-42.5°	16	16	16	17	17	17	18	18	19	19	19
-43.75°	15	15	16	16	16	16	17	17	17	17	18
-45°	13	14	14	15	15	15	16	16	16	16	16
-46.25°	12	13	13	14	14	14	15	15	15	15	15
-47.5°	11	12	12	12	13	13	13	14	14	14	14
-48.75°	10	11	11	11	11	12	12	12	12	13	13
-50°	9	10	10	10	10	11	11	11	11	11	12
-51.25°	9	9	9	9	10	10	10	10	10	10	11
-52.5°	8	8	8	8	9	9	9	9	9	9	10
-53.75°	7	7	7	7	8	8	8	8	8	8	9
-55°	6	6	6	7	7	7	7	7	7	8	8
-56.25°	5	5	5	6	6	6	6	6	6	7	7
-57.5°	4	4	4	5	5	5	5	5	5	6	6
-58.75°	4	4	4	4	4	4	4	4	4	5	5
-60°	3	3	3	3	3	4	4	4	4	4	4
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	2	2	2	2	3	3	3	3	3	3	3
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	1	1	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	1	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	2	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	3	2	2	2	2
62.5°	3	3	3	3	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	4	3	3	3	3
60°	4	4	4	4	4	4	4	4	4	4	4
58.75°	5	5	5	5	5	5	5	5	5	5	5
57.5°	6	6	6	6	6	6	6	6	6	6	6
56.25°	7	7	7	7	7	7	7	7	7	7	7
55°	8	8	8	8	8	8	8	8	8	8	8
53.75°	9	9	9	9	9	9	9	9	9	9	9
52.5°	10	10	10	10	10	10	10	10	10	10	10
51.25°	11	11	11	11	11	11	11	11	11	11	11
50°	12	12	12	12	12	12	12	12	12	12	12
48.75°	13	13	13	13	13	13	14	13	13	13	13
47.5°	14	15	15	15	15	15	15	15	15	15	15
46.25°	16	16	16	16	16	16	16	16	16	16	16
45°	17	17	17	17	17	17	17	17	17	17	17
43.75°	18	18	18	18	18	18	19	18	18	18	18
42.5°	19	20	20	20	20	20	20	20	20	20	20
41.25°	21	21	21	21	21	21	22	21	21	21	21
40°	22	23	23	23	23	23	23	23	23	23	23
38.75°	24	24	25	25	25	25	25	25	25	25	25
37.5°	26	26	27	27	27	27	27	27	27	27	27
36.25°	28	29	29	29	29	29	30	29	29	29	29
35°	31	31	31	32	32	32	32	32	32	32	31



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	33	34	34	35	35	35	35	35	35	35	34
32.5°	36	37	37	38	38	38	38	38	38	38	37
31.25°	40	41	42	42	43	43	43	43	43	42	42
30°	45	46	46	47	48	48	48	48	48	47	46
28.75°	50	51	52	53	54	54	54	54	54	53	52
27.5°	56	57	58	59	59	60	60	60	59	59	58
26.25°	62	65	66	68	69	70	70	70	69	68	66
25°	72	74	76	78	79	80	80	80	79	78	76
23.75°	82	85	89	91	93	94	94	94	93	91	89
22.5°	95	99	102	105	107	108	108	108	107	105	102
21.25°	108	115	120	124	127	128	129	128	127	124	120
20°	128	135	140	144	147	149	150	149	147	144	140
18.75°	148	157	165	171	176	179	180	179	176	171	165
17.5°	174	185	194	201	206	209	210	209	206	201	194
16.25°	201	214	228	238	246	251	253	251	246	238	228
15°	236	253	268	280	288	293	295	293	288	280	268
13.75°	274	292	312	328	340	347	350	347	340	328	312
12.5°	315	341	363	380	393	401	404	401	393	380	363
11.25°	361	389	414	437	454	464	468	464	454	437	414
10°	405	441	472	497	516	527	531	527	516	497	472
8.75°	455	493	528	557	580	594	599	594	580	557	528
7.5°	501	544	585	620	646	663	669	663	646	620	585
6.25°	544	595	641	680	710	729	735	729	710	680	641
5°	585	641	692	735	767	787	794	787	767	735	692
3.75°	620	680	735	780	815	838	845	838	815	780	735
2.5°	646	710	767	815	852	877	886	877	852	815	767
1.25°	663	729	787	838	877	905	916	905	877	838	787
0°	669	735	794	845	886	916	930	916	886	845	794
-1.25°	663	729	787	838	877	905	916	905	877	838	787
-2.5°	646	710	767	815	852	877	886	877	852	815	767
-3.75°	620	680	735	780	815	838	845	838	815	780	735
-5°	585	641	692	735	767	787	794	787	767	735	692
-6.25°	544	595	641	680	710	729	735	729	710	680	641
-7.5°	501	544	585	620	646	663	669	663	646	620	585
-8.75°	455	493	528	557	580	594	599	594	580	557	528
-10°	405	441	472	497	516	527	531	527	516	497	472
-11.25°	361	389	414	437	454	464	468	464	454	437	414
-12.5°	315	341	363	380	393	401	404	401	393	380	363
-13.75°	274	292	312	328	340	347	350	347	340	328	312
-15°	236	253	268	280	288	293	295	293	288	280	268
-16.25°	201	214	228	238	246	251	253	251	246	238	228
-17.5°	174	185	194	201	206	209	210	209	206	201	194
-18.75°	148	157	165	171	176	179	180	179	176	171	165
-20°	128	135	140	144	147	149	150	149	147	144	140
-21.25°	108	115	120	124	127	128	129	128	127	124	120





REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	95	99	102	105	107	108	108	108	107	105	102
-23.75°	82	85	89	91	93	94	94	94	93	91	89
-25°	72	74	76	78	79	80	80	80	79	78	76
-26.25°	62	65	66	68	69	70	70	70	69	68	66
-27.5°	56	57	58	59	59	60	60	60	59	59	58
-28.75°	50	51	52	53	54	54	54	54	54	53	52
-30°	45	46	46	47	48	48	48	48	48	47	46
-31.25°	40	41	42	42	43	43	43	43	43	42	42
-32.5°	36	37	37	38	38	38	38	38	38	38	37
-33.75°	33	34	34	35	35	35	35	35	35	35	34
-35°	31	31	31	32	32	32	32	32	32	32	31
-36.25°	28	29	29	29	29	29	30	29	29	29	29
-37.5°	26	26	27	27	27	27	27	27	27	27	27
-38.75°	24	24	25	25	25	25	25	25	25	25	25
-40°	22	23	23	23	23	23	23	23	23	23	23
-41.25°	21	21	21	21	21	21	22	21	21	21	21
-42.5°	19	20	20	20	20	20	20	20	20	20	20
-43.75°	18	18	18	18	18	18	19	18	18	18	18
-45°	17	17	17	17	17	17	17	17	17	17	17
-46.25°	16	16	16	16	16	16	16	16	16	16	16
-47.5°	14	15	15	15	15	15	15	15	15	15	15
-48.75°	13	13	13	13	13	13	14	13	13	13	13
-50°	12	12	12	12	12	12	12	12	12	12	12
-51.25°	11	11	11	11	11	11	11	11	11	11	11
-52.5°	10	10	10	10	10	10	10	10	10	10	10
-53.75°	9	9	9	9	9	9	9	9	9	9	9
-55°	8	8	8	8	8	8	8	8	8	8	8
-56.25°	7	7	7	7	7	7	7	7	7	7	7
-57.5°	6	6	6	6	6	6	6	6	6	6	6
-58.75°	5	5	5	5	5	5	5	5	5	5	5
-60°	4	4	4	4	4	4	4	4	4	4	4
-61.25°	3	3	3	3	3	3	4	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	3	3
-63.75°	2	2	2	2	2	2	3	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	2	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	1	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	1
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	3	3	3	3	3	3	3	3	3	2	2
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	4	4	4	4	4	4	4	4	3	3	3
58.75°	5	5	5	5	4	4	4	4	4	4	4
57.5°	6	6	6	6	5	5	5	5	5	5	4
56.25°	7	7	7	7	6	6	6	6	6	6	5
55°	8	8	8	8	7	7	7	7	7	7	6
53.75°	9	9	9	8	8	8	8	8	8	7	7
52.5°	10	10	10	9	9	9	9	9	9	8	8
51.25°	11	11	11	10	10	10	10	10	10	9	9
50°	12	12	12	11	11	11	11	11	10	10	10
48.75°	13	13	13	13	12	12	12	12	11	11	11
47.5°	15	14	14	14	14	14	13	13	13	12	12
46.25°	16	16	15	15	15	15	15	14	14	14	13
45°	17	17	16	16	16	16	16	15	15	15	14
43.75°	18	18	18	17	17	17	17	16	16	16	16
42.5°	20	19	19	19	19	18	18	17	17	17	16
41.25°	21	21	21	20	20	20	19	19	18	18	17
40°	23	22	22	22	21	21	21	20	20	19	19
38.75°	24	24	24	23	23	23	22	22	21	21	20
37.5°	26	26	26	25	25	24	24	23	23	22	21
36.25°	29	28	28	27	27	26	26	25	24	23	23
35°	31	31	30	30	29	28	27	27	26	25	24



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	34	33	33	32	31	31	30	29	28	27	26
32.5°	37	36	36	35	34	33	32	31	30	29	28
31.25°	41	40	39	38	37	36	35	34	32	31	30
30°	46	45	43	42	41	39	37	36	35	34	32
28.75°	51	50	48	47	45	43	42	39	38	36	35
27.5°	57	56	54	52	50	48	46	44	42	39	37
26.25°	65	62	60	58	56	53	51	48	46	43	41
25°	74	72	69	66	62	59	56	53	50	47	44
23.75°	85	82	78	75	71	67	62	58	55	52	48
22.5°	99	95	91	85	80	75	71	65	60	57	53
21.25°	115	108	103	98	92	86	79	74	68	62	57
20°	135	128	120	112	104	97	90	82	76	69	63
18.75°	157	148	140	130	120	110	101	93	84	77	70
17.5°	185	174	162	149	138	127	114	104	94	85	77
16.25°	214	201	188	174	158	143	130	117	104	94	84
15°	253	236	216	199	182	164	146	132	117	104	93
13.75°	292	274	252	229	205	186	166	146	130	114	101
12.5°	341	315	288	262	235	207	186	164	143	127	110
11.25°	389	361	329	295	266	235	205	182	158	138	120
10°	441	405	371	334	295	262	229	199	174	149	130
8.75°	493	455	412	371	329	288	252	216	188	162	140
7.5°	544	501	455	405	361	315	274	236	201	174	148
6.25°	595	544	493	441	389	341	292	253	214	185	157
5°	641	585	528	472	414	363	312	268	228	194	165
3.75°	680	620	557	497	437	380	328	280	238	201	171
2.5°	710	646	580	516	454	393	340	288	246	206	176
1.25°	729	663	594	527	464	401	347	293	251	209	179
0°	735	669	599	531	468	404	350	295	253	210	180
-1.25°	729	663	594	527	464	401	347	293	251	209	179
-2.5°	710	646	580	516	454	393	340	288	246	206	176
-3.75°	680	620	557	497	437	380	328	280	238	201	171
-5°	641	585	528	472	414	363	312	268	228	194	165
-6.25°	595	544	493	441	389	341	292	253	214	185	157
-7.5°	544	501	455	405	361	315	274	236	201	174	148
-8.75°	493	455	412	371	329	288	252	216	188	162	140
-10°	441	405	371	334	295	262	229	199	174	149	130
-11.25°	389	361	329	295	266	235	205	182	158	138	120
-12.5°	341	315	288	262	235	207	186	164	143	127	110
-13.75°	292	274	252	229	205	186	166	146	130	114	101
-15°	253	236	216	199	182	164	146	132	117	104	93
-16.25°	214	201	188	174	158	143	130	117	104	94	84
-17.5°	185	174	162	149	138	127	114	104	94	85	77
-18.75°	157	148	140	130	120	110	101	93	84	77	70
-20°	135	128	120	112	104	97	90	82	76	69	63
-21.25°	115	108	103	98	92	86	79	74	68	62	57



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	99	95	91	85	80	75	71	65	60	57	53
-23.75°	85	82	78	75	71	67	62	58	55	52	48
-25°	74	72	69	66	62	59	56	53	50	47	44
-26.25°	65	62	60	58	56	53	51	48	46	43	41
-27.5°	57	56	54	52	50	48	46	44	42	39	37
-28.75°	51	50	48	47	45	43	42	39	38	36	35
-30°	46	45	43	42	41	39	37	36	35	34	32
-31.25°	41	40	39	38	37	36	35	34	32	31	30
-32.5°	37	36	36	35	34	33	32	31	30	29	28
-33.75°	34	33	33	32	31	31	30	29	28	27	26
-35°	31	31	30	30	29	28	27	27	26	25	24
-36.25°	29	28	28	27	27	26	26	25	24	23	23
-37.5°	26	26	26	25	25	24	24	23	23	22	21
-38.75°	24	24	24	23	23	23	22	22	21	21	20
-40°	23	22	22	22	21	21	21	20	20	19	19
-41.25°	21	21	21	20	20	20	19	19	18	18	17
-42.5°	20	19	19	19	19	18	18	17	17	17	16
-43.75°	18	18	18	17	17	17	17	16	16	16	16
-45°	17	17	16	16	16	16	16	15	15	15	14
-46.25°	16	16	15	15	15	15	15	14	14	14	13
-47.5°	15	14	14	14	14	14	13	13	13	12	12
-48.75°	13	13	13	13	12	12	12	12	11	11	11
-50°	12	12	12	11	11	11	11	11	10	10	10
-51.25°	11	11	11	10	10	10	10	10	10	9	9
-52.5°	10	10	10	9	9	9	9	9	9	8	8
-53.75°	9	9	9	8	8	8	8	8	8	7	7
-55°	8	8	8	8	7	7	7	7	7	7	6
-56.25°	7	7	7	7	6	6	6	6	6	6	5
-57.5°	6	6	6	6	5	5	5	5	5	5	4
-58.75°	5	5	5	5	4	4	4	4	4	4	4
-60°	4	4	4	4	4	4	4	4	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	2	2	2	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	2	1	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	3	3	3	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	2	2	2	2
58.75°	4	4	3	3	3	3	3	3	3	3	2
57.5°	4	4	4	4	4	4	3	3	3	3	3
56.25°	5	5	5	4	4	4	4	4	4	3	3
55°	6	6	6	5	5	5	4	4	4	4	4
53.75°	7	7	6	6	6	6	5	5	5	4	4
52.5°	8	8	7	7	7	6	6	6	5	5	5
51.25°	9	9	8	8	8	7	7	7	6	6	5
50°	10	9	9	9	9	8	8	7	7	7	6
48.75°	11	10	10	10	9	9	9	8	8	7	7
47.5°	12	11	11	11	10	10	9	9	9	8	8
46.25°	13	12	12	11	11	11	10	10	9	9	9
45°	14	13	13	12	12	11	11	11	10	10	9
43.75°	15	15	14	14	13	12	12	11	11	11	10
42.5°	16	16	15	15	14	14	13	12	12	11	11
41.25°	17	17	16	16	15	15	14	13	13	12	11
40°	18	18	17	17	16	16	15	15	14	13	12
38.75°	20	19	18	18	17	17	16	16	15	14	13
37.5°	21	20	20	19	18	17	17	16	16	15	14
36.25°	22	21	21	20	19	19	18	17	16	16	15
35°	24	23	22	21	21	20	19	18	17	17	16



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	25	24	23	22	22	21	20	19	18	17	17
32.5°	27	26	25	24	23	22	21	20	19	18	17
31.25°	29	28	26	25	24	23	22	21	20	19	18
30°	31	30	28	27	26	25	23	22	21	20	19
28.75°	33	32	30	29	27	26	25	23	22	21	20
27.5°	36	34	32	31	29	27	26	25	23	22	21
26.25°	38	36	34	32	31	29	27	26	25	23	22
25°	42	39	36	35	33	31	29	27	26	24	23
23.75°	45	42	39	37	35	32	31	29	27	25	24
22.5°	49	46	42	39	36	34	32	30	28	26	25
21.25°	53	49	46	42	39	36	34	32	30	28	26
20°	58	53	49	45	42	38	36	33	31	29	27
18.75°	63	57	53	48	44	41	37	35	32	30	28
17.5°	69	62	57	52	47	43	39	36	34	31	29
16.25°	76	68	60	55	50	46	42	38	35	32	30
15°	82	74	65	58	53	48	44	39	36	34	31
13.75°	90	79	71	62	56	51	46	42	37	35	32
12.5°	97	86	75	67	59	53	48	43	39	36	33
11.25°	104	92	80	71	62	56	50	45	41	37	34
10°	112	98	85	75	66	58	52	47	42	38	35
8.75°	120	103	91	78	69	60	54	48	43	39	36
7.5°	128	108	95	82	72	62	56	50	45	40	36
6.25°	135	115	99	85	74	65	57	51	46	41	37
5°	140	120	102	89	76	66	58	52	46	42	37
3.75°	144	124	105	91	78	68	59	53	47	42	38
2.5°	147	127	107	93	79	69	59	54	48	43	38
1.25°	149	128	108	94	80	70	60	54	48	43	38
0°	150	129	108	94	80	70	60	54	48	43	38
-1.25°	149	128	108	94	80	70	60	54	48	43	38
-2.5°	147	127	107	93	79	69	59	54	48	43	38
-3.75°	144	124	105	91	78	68	59	53	47	42	38
-5°	140	120	102	89	76	66	58	52	46	42	37
-6.25°	135	115	99	85	74	65	57	51	46	41	37
-7.5°	128	108	95	82	72	62	56	50	45	40	36
-8.75°	120	103	91	78	69	60	54	48	43	39	36
-10°	112	98	85	75	66	58	52	47	42	38	35
-11.25°	104	92	80	71	62	56	50	45	41	37	34
-12.5°	97	86	75	67	59	53	48	43	39	36	33
-13.75°	90	79	71	62	56	51	46	42	37	35	32
-15°	82	74	65	58	53	48	44	39	36	34	31
-16.25°	76	68	60	55	50	46	42	38	35	32	30
-17.5°	69	62	57	52	47	43	39	36	34	31	29
-18.75°	63	57	53	48	44	41	37	35	32	30	28
-20°	58	53	49	45	42	38	36	33	31	29	27
-21.25°	53	49	46	42	39	36	34	32	30	28	26





REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	49	46	42	39	36	34	32	30	28	26	25
-23.75°	45	42	39	37	35	32	31	29	27	25	24
-25°	42	39	36	35	33	31	29	27	26	24	23
-26.25°	38	36	34	32	31	29	27	26	25	23	22
-27.5°	36	34	32	31	29	27	26	25	23	22	21
-28.75°	33	32	30	29	27	26	25	23	22	21	20
-30°	31	30	28	27	26	25	23	22	21	20	19
-31.25°	29	28	26	25	24	23	22	21	20	19	18
-32.5°	27	26	25	24	23	22	21	20	19	18	17
-33.75°	25	24	23	22	22	21	20	19	18	17	17
-35°	24	23	22	21	21	20	19	18	17	17	16
-36.25°	22	21	21	20	19	19	18	17	16	16	15
-37.5°	21	20	20	19	18	17	17	16	16	15	14
-38.75°	20	19	18	18	17	17	16	16	15	14	13
-40°	18	18	17	17	16	16	15	15	14	13	12
-41.25°	17	17	16	16	15	15	14	13	13	12	11
-42.5°	16	16	15	15	14	14	13	12	12	11	11
-43.75°	15	15	14	14	13	12	12	11	11	11	10
-45°	14	13	13	12	12	11	11	11	10	10	9
-46.25°	13	12	12	11	11	11	10	10	9	9	9
-47.5°	12	11	11	11	10	10	9	9	9	8	8
-48.75°	11	10	10	10	9	9	9	8	8	7	7
-50°	10	9	9	9	9	8	8	7	7	7	6
-51.25°	9	9	8	8	8	7	7	7	6	6	5
-52.5°	8	8	7	7	7	6	6	6	5	5	5
-53.75°	7	7	6	6	6	6	5	5	5	4	4
-55°	6	6	6	5	5	5	4	4	4	4	4
-56.25°	5	5	5	4	4	4	4	4	4	3	3
-57.5°	4	4	4	4	4	4	3	3	3	3	3
-58.75°	4	4	3	3	3	3	3	3	3	3	2
-60°	3	3	3	3	3	3	3	2	2	2	2
-61.25°	3	3	3	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	1	1
-66.25°	2	2	2	2	2	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	1	1	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	2	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	1
57.5°	3	2	2	2	2	2	2	2	2	2	2
56.25°	3	3	3	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	2	2	2	2	2	2
53.75°	4	4	3	3	3	3	3	2	2	2	2
52.5°	4	4	4	4	3	3	3	3	2	2	2
51.25°	5	5	4	4	4	3	3	3	3	3	2
50°	6	5	5	5	4	4	4	3	3	3	3
48.75°	7	6	6	5	5	4	4	4	3	3	3
47.5°	7	7	6	6	5	5	4	4	4	3	3
46.25°	8	8	7	7	6	6	5	5	4	4	3
45°	9	8	8	7	7	6	6	5	5	4	4
43.75°	10	9	9	8	7	7	6	6	5	5	4
42.5°	10	10	9	9	8	8	7	6	6	5	5
41.25°	11	10	10	9	9	8	8	7	6	6	5
40°	12	11	11	10	9	9	8	8	7	6	6
38.75°	13	12	11	11	10	9	9	8	7	7	6
37.5°	14	13	12	11	11	10	9	9	8	7	7
36.25°	15	14	13	12	11	11	10	9	9	8	7
35°	15	15	14	13	12	11	10	10	9	8	8



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	16	15	15	14	13	12	11	10	10	9	8
32.5°	17	16	15	14	13	12	11	11	10	9	9
31.25°	17	17	16	15	14	13	12	11	11	10	9
30°	18	17	16	16	15	14	13	12	11	10	9
28.75°	19	18	17	16	16	15	13	12	11	11	10
27.5°	20	19	18	17	16	15	14	13	12	11	10
26.25°	21	20	19	17	17	16	15	14	12	11	11
25°	22	21	19	18	17	16	15	14	13	12	11
23.75°	22	21	20	19	18	17	16	15	14	12	11
22.5°	23	22	21	20	18	17	16	15	14	13	12
21.25°	24	23	21	20	19	18	17	16	15	13	12
20°	25	24	22	21	20	18	17	16	15	14	13
18.75°	26	24	23	21	20	19	17	16	16	14	13
17.5°	27	25	23	22	21	19	18	17	16	15	14
16.25°	28	26	24	23	21	20	18	17	16	15	14
15°	29	27	25	23	22	20	19	17	16	15	14
13.75°	30	27	26	24	22	21	19	18	17	16	15
12.5°	31	28	26	24	23	21	20	18	17	16	15
11.25°	31	29	27	25	23	21	20	19	17	16	15
10°	32	30	27	25	23	22	20	19	17	16	15
8.75°	33	30	28	26	24	22	21	19	18	16	15
7.5°	33	31	28	26	24	22	21	19	18	17	16
6.25°	34	31	29	26	24	23	21	20	18	17	16
5°	34	31	29	27	25	23	21	20	18	17	16
3.75°	35	32	29	27	25	23	21	20	18	17	16
2.5°	35	32	29	27	25	23	21	20	18	17	16
1.25°	35	32	29	27	25	23	21	20	18	17	16
0°	35	32	30	27	25	23	22	20	19	17	16
-1.25°	35	32	29	27	25	23	21	20	18	17	16
-2.5°	35	32	29	27	25	23	21	20	18	17	16
-3.75°	35	32	29	27	25	23	21	20	18	17	16
-5°	34	31	29	27	25	23	21	20	18	17	16
-6.25°	34	31	29	26	24	23	21	20	18	17	16
-7.5°	33	31	28	26	24	22	21	19	18	17	16
-8.75°	33	30	28	26	24	22	21	19	18	16	15
-10°	32	30	27	25	23	22	20	19	17	16	15
-11.25°	31	29	27	25	23	21	20	19	17	16	15
-12.5°	31	28	26	24	23	21	20	18	17	16	15
-13.75°	30	27	26	24	22	21	19	18	17	16	15
-15°	29	27	25	23	22	20	19	17	16	15	14
-16.25°	28	26	24	23	21	20	18	17	16	15	14
-17.5°	27	25	23	22	21	19	18	17	16	15	14
-18.75°	26	24	23	21	20	19	17	16	16	14	13
-20°	25	24	22	21	20	18	17	16	15	14	13
-21.25°	24	23	21	20	19	18	17	16	15	13	12



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	23	22	21	20	18	17	16	15	14	13	12
-23.75°	22	21	20	19	18	17	16	15	14	12	11
-25°	22	21	19	18	17	16	15	14	13	12	11
-26.25°	21	20	19	17	17	16	15	14	12	11	11
-27.5°	20	19	18	17	16	15	14	13	12	11	10
-28.75°	19	18	17	16	16	15	13	12	11	11	10
-30°	18	17	16	16	15	14	13	12	11	10	9
-31.25°	17	17	16	15	14	13	12	11	11	10	9
-32.5°	17	16	15	14	13	12	11	11	10	9	9
-33.75°	16	15	15	14	13	12	11	10	10	9	8
-35°	15	15	14	13	12	11	10	10	9	8	8
-36.25°	15	14	13	12	11	11	10	9	9	8	7
-37.5°	14	13	12	11	11	10	9	9	8	7	7
-38.75°	13	12	11	11	10	9	9	8	7	7	6
-40°	12	11	11	10	9	9	8	8	7	6	6
-41.25°	11	10	10	9	9	8	8	7	6	6	5
-42.5°	10	10	9	9	8	8	7	6	6	5	5
-43.75°	10	9	9	8	7	7	6	6	5	5	4
-45°	9	8	8	7	7	6	6	5	5	4	4
-46.25°	8	8	7	7	6	6	5	5	4	4	3
-47.5°	7	7	6	6	5	5	4	4	4	3	3
-48.75°	7	6	6	5	5	4	4	4	3	3	3
-50°	6	5	5	5	4	4	4	3	3	3	3
-51.25°	5	5	4	4	4	3	3	3	3	3	2
-52.5°	4	4	4	4	3	3	3	3	2	2	2
-53.75°	4	4	3	3	3	3	3	2	2	2	2
-55°	3	3	3	3	3	2	2	2	2	2	2
-56.25°	3	3	3	2	2	2	2	2	2	2	2
-57.5°	3	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	1
-60°	2	2	2	2	2	2	2	2	1	1	1
-61.25°	2	2	2	2	2	2	1	1	1	1	1
-62.5°	2	2	2	2	1	1	1	1	1	1	1
-63.75°	2	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	0
-75°	1	1	1	1	1	1	0	0	0	0	0
-76.25°	1	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	0	0	0	0	0	0	0	0	0
71.25°	1	1	1	1	1	0	0	0	0	0	0
70°	1	1	1	1	1	1	1	0	0	0	0
68.75°	1	1	1	1	1	1	1	1	0	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	0
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	1	1	1	1	1	1	1	1
53.75°	2	2	2	2	1	1	1	1	1	1	1
52.5°	2	2	2	2	2	1	1	1	1	1	1
51.25°	2	2	2	2	2	2	1	1	1	1	1
50°	2	2	2	2	2	2	2	1	1	1	1
48.75°	3	2	2	2	2	2	2	2	1	1	1
47.5°	3	3	2	2	2	2	2	2	2	1	1
46.25°	3	3	3	2	2	2	2	2	2	1	1
45°	3	3	3	3	2	2	2	2	2	2	1
43.75°	4	3	3	3	2	2	2	2	2	2	1
42.5°	4	4	3	3	3	2	2	2	2	2	2
41.25°	4	4	4	3	3	3	2	2	2	2	2
40°	5	4	4	3	3	3	2	2	2	2	2
38.75°	5	5	4	4	3	3	3	2	2	2	2
37.5°	6	5	5	4	4	3	3	2	2	2	2
36.25°	6	6	5	4	4	3	3	3	2	2	2
35°	7	6	5	5	4	4	3	3	2	2	2



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	7	7	6	5	4	4	3	3	3	2	2
32.5°	8	7	6	5	5	4	4	3	3	2	2
31.25°	8	7	7	6	5	4	4	3	3	3	2
30°	9	8	7	6	5	5	4	4	3	3	2
28.75°	9	8	7	7	6	5	4	4	3	3	2
27.5°	9	9	8	7	6	5	4	4	3	3	3
26.25°	10	9	8	7	6	6	5	4	4	3	3
25°	10	9	9	8	7	6	5	4	4	3	3
23.75°	11	10	9	8	7	6	5	4	4	3	3
22.5°	11	10	9	8	7	6	6	5	4	3	3
21.25°	11	10	9	9	8	7	6	5	4	4	3
20°	12	11	10	9	8	7	6	5	4	4	3
18.75°	12	11	10	9	8	7	6	5	4	4	3
17.5°	12	11	10	9	8	7	7	6	5	4	3
16.25°	13	11	10	10	9	8	7	6	5	4	3
15°	13	12	11	10	9	8	7	6	5	4	4
13.75°	13	12	11	10	9	8	7	6	5	4	4
12.5°	14	12	11	10	9	8	7	6	5	4	4
11.25°	14	12	11	10	9	8	7	6	5	4	4
10°	14	13	11	10	9	8	8	7	6	5	4
8.75°	14	13	12	11	10	9	8	7	6	5	4
7.5°	14	13	12	11	10	9	8	7	6	5	4
6.25°	15	13	12	11	10	9	8	7	6	5	4
5°	15	13	12	11	10	9	8	7	6	5	4
3.75°	15	13	12	11	10	9	8	7	6	5	4
2.5°	15	13	12	11	10	9	8	7	6	5	4
1.25°	15	13	12	11	10	9	8	7	6	5	4
0°	15	14	12	11	10	9	8	7	6	5	4
-1.25°	15	13	12	11	10	9	8	7	6	5	4
-2.5°	15	13	12	11	10	9	8	7	6	5	4
-3.75°	15	13	12	11	10	9	8	7	6	5	4
-5°	15	13	12	11	10	9	8	7	6	5	4
-6.25°	15	13	12	11	10	9	8	7	6	5	4
-7.5°	14	13	12	11	10	9	8	7	6	5	4
-8.75°	14	13	12	11	10	9	8	7	6	5	4
-10°	14	13	11	10	9	8	8	7	6	5	4
-11.25°	14	12	11	10	9	8	7	6	5	4	4
-12.5°	14	12	11	10	9	8	7	6	5	4	4
-13.75°	13	12	11	10	9	8	7	6	5	4	4
-15°	13	12	11	10	9	8	7	6	5	4	4
-16.25°	13	11	10	10	9	8	7	6	5	4	3
-17.5°	12	11	10	9	8	7	7	6	5	4	3
-18.75°	12	11	10	9	8	7	6	5	4	4	3
-20°	12	11	10	9	8	7	6	5	4	4	3
-21.25°	11	10	9	9	8	7	6	5	4	4	3





REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	11	10	9	8	7	6	6	5	4	3	3
-23.75°	11	10	9	8	7	6	5	4	4	3	3
-25°	10	9	9	8	7	6	5	4	4	3	3
-26.25°	10	9	8	7	6	6	5	4	4	3	3
-27.5°	9	9	8	7	6	5	4	4	3	3	3
-28.75°	9	8	7	7	6	5	4	4	3	3	2
-30°	9	8	7	6	5	5	4	4	3	3	2
-31.25°	8	7	7	6	5	4	4	3	3	3	2
-32.5°	8	7	6	5	5	4	4	3	3	2	2
-33.75°	7	7	6	5	4	4	3	3	3	2	2
-35°	7	6	5	5	4	4	3	3	2	2	2
-36.25°	6	6	5	4	4	3	3	3	2	2	2
-37.5°	6	5	5	4	4	3	3	2	2	2	2
-38.75°	5	5	4	4	3	3	3	2	2	2	2
-40°	5	4	4	3	3	3	2	2	2	2	2
-41.25°	4	4	4	3	3	3	2	2	2	2	2
-42.5°	4	4	3	3	3	2	2	2	2	2	2
-43.75°	4	3	3	3	2	2	2	2	2	2	1
-45°	3	3	3	3	2	2	2	2	2	2	1
-46.25°	3	3	3	2	2	2	2	2	2	1	1
-47.5°	3	3	2	2	2	2	2	2	2	1	1
-48.75°	3	2	2	2	2	2	2	2	1	1	1
-50°	2	2	2	2	2	2	2	1	1	1	1
-51.25°	2	2	2	2	2	2	1	1	1	1	1
-52.5°	2	2	2	2	2	1	1	1	1	1	1
-53.75°	2	2	2	2	1	1	1	1	1	1	1
-55°	2	2	2	1	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	0
-68.75°	1	1	1	1	1	1	1	1	0	0	0
-70°	1	1	1	1	1	1	1	0	0	0	0
-71.25°	1	1	1	1	1	0	0	0	0	0	0
-72.5°	1	1	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	1	0	0	0	0	0	0	0	0	0
63.75°	1	1	1	0	0	0	0	0	0	0	0
62.5°	1	1	1	1	0	0	0	0	0	0	0
61.25°	1	1	1	1	0	0	0	0	0	0	0
60°	1	1	1	1	1	0	0	0	0	0	0
58.75°	1	1	1	1	1	1	0	0	0	0	0
57.5°	1	1	1	1	1	1	0	0	0	0	0
56.25°	1	1	1	1	1	1	1	0	0	0	0
55°	1	1	1	1	1	1	1	1	0	0	0
53.75°	1	1	1	1	1	1	1	1	0	0	0
52.5°	1	1	1	1	1	1	1	1	1	0	0
51.25°	1	1	1	1	1	1	1	1	1	0	0
50°	1	1	1	1	1	1	1	1	1	0	0
48.75°	1	1	1	1	1	1	1	1	1	1	0
47.5°	1	1	1	1	1	1	1	1	1	1	0
46.25°	1	1	1	1	1	1	1	1	1	1	0
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	2	1	1	1	1	1	1	1	1	1	1
38.75°	2	1	1	1	1	1	1	1	1	1	1
37.5°	2	2	1	1	1	1	1	1	1	1	1
36.25°	2	2	1	1	1	1	1	1	1	1	1
35°	2	2	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	2	1	1	1	1	1	1	1	1
32.5°	2	2	2	1	1	1	1	1	1	1	1
31.25°	2	2	2	1	1	1	1	1	1	1	1
30°	2	2	2	2	1	1	1	1	1	1	1
28.75°	2	2	2	2	1	1	1	1	1	1	1
27.5°	2	2	2	2	1	1	1	1	1	1	1
26.25°	2	2	2	2	1	1	1	1	1	1	1
25°	2	2	2	2	2	1	1	1	1	1	1
23.75°	2	2	2	2	2	1	1	1	1	1	1
22.5°	3	2	2	2	2	1	1	1	1	1	1
21.25°	3	2	2	2	2	1	1	1	1	1	1
20°	3	2	2	2	2	1	1	1	1	1	1
18.75°	3	2	2	2	2	1	1	1	1	1	1
17.5°	3	2	2	2	2	2	1	1	1	1	1
16.25°	3	3	2	2	2	2	1	1	1	1	1
15°	3	3	2	2	2	2	1	1	1	1	1
13.75°	3	3	2	2	2	2	1	1	1	1	1
12.5°	3	3	2	2	2	2	1	1	1	1	1
11.25°	3	3	2	2	2	2	1	1	1	1	1
10°	3	3	2	2	2	2	1	1	1	1	1
8.75°	3	3	2	2	2	2	1	1	1	1	1
7.5°	3	3	2	2	2	2	1	1	1	1	1
6.25°	3	3	2	2	2	2	1	1	1	1	1
5°	3	3	2	2	2	2	1	1	1	1	1
3.75°	3	3	2	2	2	2	1	1	1	1	1
2.5°	3	3	2	2	2	2	1	1	1	1	1
1.25°	3	3	2	2	2	2	1	1	1	1	1
0°	4	3	3	2	2	2	2	1	1	1	1
-1.25°	3	3	2	2	2	2	1	1	1	1	1
-2.5°	3	3	2	2	2	2	1	1	1	1	1
-3.75°	3	3	2	2	2	2	1	1	1	1	1
-5°	3	3	2	2	2	2	1	1	1	1	1
-6.25°	3	3	2	2	2	2	1	1	1	1	1
-7.5°	3	3	2	2	2	2	1	1	1	1	1
-8.75°	3	3	2	2	2	2	1	1	1	1	1
-10°	3	3	2	2	2	2	1	1	1	1	1
-11.25°	3	3	2	2	2	2	1	1	1	1	1
-12.5°	3	3	2	2	2	2	1	1	1	1	1
-13.75°	3	3	2	2	2	2	1	1	1	1	1
-15°	3	3	2	2	2	2	1	1	1	1	1
-16.25°	3	3	2	2	2	2	1	1	1	1	1
-17.5°	3	2	2	2	2	2	1	1	1	1	1
-18.75°	3	2	2	2	2	1	1	1	1	1	1
-20°	3	2	2	2	2	1	1	1	1	1	1
-21.25°	3	2	2	2	2	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	3	2	2	2	2	1	1	1	1	1	1
-23.75°	2	2	2	2	2	1	1	1	1	1	1
-25°	2	2	2	2	2	1	1	1	1	1	1
-26.25°	2	2	2	2	1	1	1	1	1	1	1
-27.5°	2	2	2	2	1	1	1	1	1	1	1
-28.75°	2	2	2	2	1	1	1	1	1	1	1
-30°	2	2	2	2	1	1	1	1	1	1	1
-31.25°	2	2	2	1	1	1	1	1	1	1	1
-32.5°	2	2	2	1	1	1	1	1	1	1	1
-33.75°	2	2	2	1	1	1	1	1	1	1	1
-35°	2	2	1	1	1	1	1	1	1	1	1
-36.25°	2	2	1	1	1	1	1	1	1	1	1
-37.5°	2	2	1	1	1	1	1	1	1	1	1
-38.75°	2	1	1	1	1	1	1	1	1	1	1
-40°	2	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	0
-47.5°	1	1	1	1	1	1	1	1	1	1	0
-48.75°	1	1	1	1	1	1	1	1	1	1	0
-50°	1	1	1	1	1	1	1	1	1	0	0
-51.25°	1	1	1	1	1	1	1	1	1	0	0
-52.5°	1	1	1	1	1	1	1	1	1	0	0
-53.75°	1	1	1	1	1	1	1	1	0	0	0
-55°	1	1	1	1	1	1	1	1	0	0	0
-56.25°	1	1	1	1	1	1	1	0	0	0	0
-57.5°	1	1	1	1	1	1	0	0	0	0	0
-58.75°	1	1	1	1	1	1	0	0	0	0	0
-60°	1	1	1	1	1	0	0	0	0	0	0
-61.25°	1	1	1	1	0	0	0	0	0	0	0
-62.5°	1	1	1	1	0	0	0	0	0	0	0
-63.75°	1	1	1	0	0	0	0	0	0	0	0
-65°	1	1	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	1	0	0	0	0	0	0	0	0	0	0
38.75°	1	0	0	0	0	0	0	0	0	0	0
37.5°	1	0	0	0	0	0	0	0	0	0	0
36.25°	1	0	0	0	0	0	0	0	0	0	0
35°	1	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	0	0	0	0	0	0	0	0	0
32.5°	1	1	0	0	0	0	0	0	0	0	0
31.25°	1	1	0	0	0	0	0	0	0	0	0
30°	1	1	0	0	0	0	0	0	0	0	0
28.75°	1	1	0	0	0	0	0	0	0	0	0
27.5°	1	1	0	0	0	0	0	0	0	0	0
26.25°	1	1	0	0	0	0	0	0	0	0	0
25°	1	1	1	0	0	0	0	0	0	0	0
23.75°	1	1	1	0	0	0	0	0	0	0	0
22.5°	1	1	1	0	0	0	0	0	0	0	0
21.25°	1	1	1	0	0	0	0	0	0	0	0
20°	1	1	1	0	0	0	0	0	0	0	0
18.75°	1	1	1	0	0	0	0	0	0	0	0
17.5°	1	1	1	0	0	0	0	0	0	0	0
16.25°	1	1	1	0	0	0	0	0	0	0	0
15°	1	1	1	0	0	0	0	0	0	0	0
13.75°	1	1	1	0	0	0	0	0	0	0	0
12.5°	1	1	1	0	0	0	0	0	0	0	0
11.25°	1	1	1	0	0	0	0	0	0	0	0
10°	1	1	1	0	0	0	0	0	0	0	0
8.75°	1	1	1	0	0	0	0	0	0	0	0
7.5°	1	1	1	0	0	0	0	0	0	0	0
6.25°	1	1	1	0	0	0	0	0	0	0	0
5°	1	1	1	0	0	0	0	0	0	0	0
3.75°	1	1	1	0	0	0	0	0	0	0	0
2.5°	1	1	1	0	0	0	0	0	0	0	0
1.25°	1	1	1	0	0	0	0	0	0	0	0
0°	1	1	1	0	0	0	0	0	0	0	0
-1.25°	1	1	1	0	0	0	0	0	0	0	0
-2.5°	1	1	1	0	0	0	0	0	0	0	0
-3.75°	1	1	1	0	0	0	0	0	0	0	0
-5°	1	1	1	0	0	0	0	0	0	0	0
-6.25°	1	1	1	0	0	0	0	0	0	0	0
-7.5°	1	1	1	0	0	0	0	0	0	0	0
-8.75°	1	1	1	0	0	0	0	0	0	0	0
-10°	1	1	1	0	0	0	0	0	0	0	0
-11.25°	1	1	1	0	0	0	0	0	0	0	0
-12.5°	1	1	1	0	0	0	0	0	0	0	0
-13.75°	1	1	1	0	0	0	0	0	0	0	0
-15°	1	1	1	0	0	0	0	0	0	0	0
-16.25°	1	1	1	0	0	0	0	0	0	0	0
-17.5°	1	1	1	0	0	0	0	0	0	0	0
-18.75°	1	1	1	0	0	0	0	0	0	0	0
-20°	1	1	1	0	0	0	0	0	0	0	0
-21.25°	1	1	1	0	0	0	0	0	0	0	0





REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	0	0	0	0	0	0	0	0
-23.75°	1	1	1	0	0	0	0	0	0	0	0
-25°	1	1	1	0	0	0	0	0	0	0	0
-26.25°	1	1	0	0	0	0	0	0	0	0	0
-27.5°	1	1	0	0	0	0	0	0	0	0	0
-28.75°	1	1	0	0	0	0	0	0	0	0	0
-30°	1	1	0	0	0	0	0	0	0	0	0
-31.25°	1	1	0	0	0	0	0	0	0	0	0
-32.5°	1	1	0	0	0	0	0	0	0	0	0
-33.75°	1	1	0	0	0	0	0	0	0	0	0
-35°	1	0	0	0	0	0	0	0	0	0	0
-36.25°	1	0	0	0	0	0	0	0	0	0	0
-37.5°	1	0	0	0	0	0	0	0	0	0	0
-38.75°	1	0	0	0	0	0	0	0	0	0	0
-40°	1	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-36 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4010-12-CS-DIFF

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)