

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4010-12-CS-LSL**

Test Date: 04/05/18

Test Information


Test Method: LM-79-08
Report Number: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-37)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/05/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4010-12-CS-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER, LINEAR SPREAD LENS
Light Source: (1) SORAA 4000K 95 CRI 10° NSP LED
SM16-07-10D-940-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 2V
Luminaire Lumens:	252.3 lumens	Max Intensity:	1200 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	33.6 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	51.1°H x 11.9°V	Field Angle (10%):	61.9°H x 24.8°V
Beam Lumens:	117.1 lumens	Field Lumens:	192.1 lumens
Beam Efficiency:	46.4%	Field Efficiency:	76.1%
Input Watts (W):	7.5		
Input Voltage (V):	12.0		
Input Current (A _{in}):	0.656		
Voltage Rise (V):	NR		
Power Factor:	0.9482		
Total Harmonic Distortion (THDi):	25.7		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	9 HR		
Ambient Temperature (°C):	24.7		
Test Distance:	25 FT		


REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

Lumen Table




REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

Luminous Intensity Plot



Beam:
 H Angle: 51.1°
 V Angle: 11.9°
 Lumens: 117.1
 Efficiency: 46.4%

Field:
 H Angle: 61.9°
 V Angle: 24.8°
 Lumens: 192.1
 Efficiency: 76.1%

Spill:
 Lumens: 60.2
 Efficiency: 23.9%

— Vertical Distribution through 0-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	1
28.75°	0	0	0	0	0	0	0	0	0	0	1
27.5°	0	0	0	0	0	0	0	0	0	0	1
26.25°	0	0	0	0	0	0	0	0	0	0	1
25°	0	0	0	0	0	0	0	0	0	0	1
23.75°	0	0	0	0	0	0	0	0	0	0	1
22.5°	0	0	0	0	0	0	0	0	0	0	1
21.25°	0	0	0	0	0	0	0	0	0	0	1
20°	0	0	0	0	0	0	0	0	0	0	1
18.75°	0	0	0	0	0	0	0	0	0	0	1
17.5°	0	0	0	0	0	0	0	0	0	0	1
16.25°	0	0	0	0	0	0	0	0	0	0	1
15°	0	0	0	0	0	0	0	0	0	0	1
13.75°	0	0	0	0	0	0	0	0	0	0	1
12.5°	0	0	0	0	0	0	0	0	0	0	1
11.25°	0	0	0	0	0	0	0	0	0	0	1
10°	0	0	0	0	0	0	0	0	0	0	1
8.75°	0	0	0	0	0	0	0	0	0	0	1
7.5°	0	0	0	0	0	0	0	0	0	0	1
6.25°	0	0	0	0	0	0	0	0	0	1	1
5°	0	0	0	0	0	0	0	0	0	1	1
3.75°	0	0	0	0	0	0	0	0	0	1	1
2.5°	0	0	0	0	0	0	0	0	0	1	1
1.25°	0	0	0	0	0	0	0	0	0	1	1
0°	0	0	0	0	0	0	0	0	0	1	1
-1.25°	0	0	0	0	0	0	0	0	0	0	1
-2.5°	0	0	0	0	0	0	0	0	0	0	1
-3.75°	0	0	0	0	0	0	0	0	0	0	1
-5°	0	0	0	0	0	0	0	0	0	0	1
-6.25°	0	0	0	0	0	0	0	0	0	0	1
-7.5°	0	0	0	0	0	0	0	0	0	0	1
-8.75°	0	0	0	0	0	0	0	0	0	0	1
-10°	0	0	0	0	0	0	0	0	0	0	1
-11.25°	0	0	0	0	0	0	0	0	0	0	1
-12.5°	0	0	0	0	0	0	0	0	0	0	1
-13.75°	0	0	0	0	0	0	0	0	0	0	1
-15°	0	0	0	0	0	0	0	0	0	0	1
-16.25°	0	0	0	0	0	0	0	0	0	0	1
-17.5°	0	0	0	0	0	0	0	0	0	0	1
-18.75°	0	0	0	0	0	0	0	0	0	0	1
-20°	0	0	0	0	0	0	0	0	0	0	1
-21.25°	0	0	0	0	0	0	0	0	0	0	1



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	1
-23.75°	0	0	0	0	0	0	0	0	0	0	1
-25°	0	0	0	0	0	0	0	0	0	0	1
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	1	1
67.5°	0	0	0	0	0	0	0	0	1	1	1
66.25°	0	0	0	0	0	0	0	1	1	1	1
65°	0	0	0	0	0	0	0	1	1	1	1
63.75°	0	0	0	0	0	0	1	1	1	1	1
62.5°	0	0	0	0	0	1	1	1	1	1	1
61.25°	0	0	0	0	0	1	1	1	1	1	1
60°	0	0	0	0	1	1	1	1	1	1	1
58.75°	0	0	0	0	1	1	1	1	1	1	1
57.5°	0	0	0	0	1	1	1	1	1	1	1
56.25°	0	0	0	1	1	1	1	1	1	1	1
55°	0	0	0	1	1	1	1	1	1	1	1
53.75°	0	0	0	1	1	1	1	1	1	1	1
52.5°	0	0	1	1	1	1	1	1	1	1	1
51.25°	0	0	1	1	1	1	1	1	1	1	1
50°	0	0	1	1	1	1	1	1	1	1	1
48.75°	0	0	1	1	1	1	1	1	1	1	1
47.5°	0	1	1	1	1	1	1	1	1	1	1
46.25°	0	1	1	1	1	1	1	1	1	1	1
45°	0	1	1	1	1	1	1	1	1	1	1
43.75°	0	1	1	1	1	1	1	1	1	1	1
42.5°	0	1	1	1	1	1	1	1	1	1	1
41.25°	0	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	2
32.5°	1	1	1	1	1	1	1	1	1	1	2
31.25°	1	1	1	1	1	1	1	1	1	1	2
30°	1	1	1	1	1	1	1	1	1	2	2
28.75°	1	1	1	1	1	1	1	1	1	2	2
27.5°	1	1	1	1	1	1	1	1	1	2	2
26.25°	1	1	1	1	1	1	1	1	1	2	2
25°	1	1	1	1	1	1	1	1	2	2	2
23.75°	1	1	1	1	1	1	1	1	2	2	2
22.5°	1	1	1	1	1	1	1	1	2	2	2
21.25°	1	1	1	1	1	1	1	1	2	2	2
20°	1	1	1	1	1	1	1	1	2	2	2
18.75°	1	1	1	1	1	1	1	1	2	2	2
17.5°	1	1	1	1	1	1	1	2	2	2	2
16.25°	1	1	1	1	1	1	1	2	2	2	2
15°	1	1	1	1	1	1	1	2	2	2	2
13.75°	1	1	1	1	1	1	1	2	2	2	2
12.5°	1	1	1	1	1	1	1	2	2	2	2
11.25°	1	1	1	1	1	1	1	2	2	2	2
10°	1	1	1	1	1	1	1	2	2	2	2
8.75°	1	1	1	1	1	1	1	2	2	2	2
7.5°	1	1	1	1	1	1	1	2	2	2	2
6.25°	1	1	1	1	1	1	1	2	2	2	2
5°	1	1	1	1	1	1	1	2	2	2	2
3.75°	1	1	1	1	1	1	1	2	2	2	2
2.5°	1	1	1	1	1	1	1	2	2	2	2
1.25°	1	1	1	1	1	1	1	2	2	2	2
0°	1	1	1	1	1	1	2	2	2	2	3
-1.25°	1	1	1	1	1	1	1	2	2	2	2
-2.5°	1	1	1	1	1	1	1	2	2	2	2
-3.75°	1	1	1	1	1	1	1	2	2	2	2
-5°	1	1	1	1	1	1	1	2	2	2	2
-6.25°	1	1	1	1	1	1	1	2	2	2	2
-7.5°	1	1	1	1	1	1	1	2	2	2	2
-8.75°	1	1	1	1	1	1	1	2	2	2	2
-10°	1	1	1	1	1	1	1	2	2	2	2
-11.25°	1	1	1	1	1	1	1	2	2	2	2
-12.5°	1	1	1	1	1	1	1	2	2	2	2
-13.75°	1	1	1	1	1	1	1	2	2	2	2
-15°	1	1	1	1	1	1	1	2	2	2	2
-16.25°	1	1	1	1	1	1	1	2	2	2	2
-17.5°	1	1	1	1	1	1	1	2	2	2	2
-18.75°	1	1	1	1	1	1	1	1	2	2	2
-20°	1	1	1	1	1	1	1	1	2	2	2
-21.25°	1	1	1	1	1	1	1	1	2	2	2



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	2	2	2
-23.75°	1	1	1	1	1	1	1	1	2	2	2
-25°	1	1	1	1	1	1	1	1	2	2	2
-26.25°	1	1	1	1	1	1	1	1	1	2	2
-27.5°	1	1	1	1	1	1	1	1	1	2	2
-28.75°	1	1	1	1	1	1	1	1	1	2	2
-30°	1	1	1	1	1	1	1	1	1	2	2
-31.25°	1	1	1	1	1	1	1	1	1	1	2
-32.5°	1	1	1	1	1	1	1	1	1	1	2
-33.75°	1	1	1	1	1	1	1	1	1	1	2
-35°	0	1	1	1	1	1	1	1	1	1	1
-36.25°	0	1	1	1	1	1	1	1	1	1	1
-37.5°	0	1	1	1	1	1	1	1	1	1	1
-38.75°	0	1	1	1	1	1	1	1	1	1	1
-40°	0	1	1	1	1	1	1	1	1	1	1
-41.25°	0	0	1	1	1	1	1	1	1	1	1
-42.5°	0	0	1	1	1	1	1	1	1	1	1
-43.75°	0	0	1	1	1	1	1	1	1	1	1
-45°	0	0	1	1	1	1	1	1	1	1	1
-46.25°	0	0	0	1	1	1	1	1	1	1	1
-47.5°	0	0	0	1	1	1	1	1	1	1	1
-48.75°	0	0	0	1	1	1	1	1	1	1	1
-50°	0	0	0	0	1	1	1	1	1	1	1
-51.25°	0	0	0	0	1	1	1	1	1	1	1
-52.5°	0	0	0	0	1	1	1	1	1	1	1
-53.75°	0	0	0	0	0	1	1	1	1	1	1
-55°	0	0	0	0	0	1	1	1	1	1	1
-56.25°	0	0	0	0	0	0	1	1	1	1	1
-57.5°	0	0	0	0	0	0	0	1	1	1	1
-58.75°	0	0	0	0	0	0	0	1	1	1	1
-60°	0	0	0	0	0	0	0	0	1	1	1
-61.25°	0	0	0	0	0	0	0	0	0	1	1
-62.5°	0	0	0	0	0	0	0	0	0	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	1
75°	0	0	0	0	0	0	0	1	1	1	1
73.75°	0	0	0	0	0	1	1	1	1	1	1
72.5°	0	0	0	1	1	1	1	1	1	1	1
71.25°	0	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	2
53.75°	1	1	1	1	1	1	1	1	1	2	2
52.5°	1	1	1	1	1	1	1	1	2	2	2
51.25°	1	1	1	1	1	1	1	2	2	2	2
50°	1	1	1	1	1	1	2	2	2	2	2
48.75°	1	1	1	1	1	2	2	2	2	2	2
47.5°	1	1	1	1	2	2	2	2	2	2	2
46.25°	1	1	1	1	2	2	2	2	2	2	2
45°	1	1	1	2	2	2	2	2	2	2	3
43.75°	1	1	1	2	2	2	2	2	2	3	3
42.5°	1	1	2	2	2	2	2	2	3	3	3
41.25°	1	1	2	2	2	2	2	2	3	3	3
40°	1	2	2	2	2	2	2	3	3	3	4
38.75°	1	2	2	2	2	2	3	3	3	4	4
37.5°	2	2	2	2	2	2	3	3	4	4	5
36.25°	2	2	2	2	2	3	3	3	4	4	5
35°	2	2	2	2	2	3	3	4	4	5	5



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	3	3	3	4	4	5	6
32.5°	2	2	2	2	3	3	4	4	5	5	6
31.25°	2	2	2	3	3	3	4	4	5	6	7
30°	2	2	2	3	3	4	4	5	5	6	7
28.75°	2	2	2	3	3	4	4	5	6	7	7
27.5°	2	2	3	3	3	4	4	5	6	7	8
26.25°	2	2	3	3	4	4	5	6	7	7	8
25°	2	2	3	3	4	4	5	6	7	8	9
23.75°	2	2	3	3	4	4	5	6	7	8	9
22.5°	2	3	3	3	4	5	6	7	8	9	9
21.25°	2	3	3	4	4	5	6	7	8	9	10
20°	2	3	3	4	4	5	6	7	8	9	10
18.75°	2	3	3	4	4	5	6	7	9	9	10
17.5°	2	3	3	4	5	6	7	8	9	10	11
16.25°	3	3	3	4	5	6	7	8	9	10	11
15°	3	3	4	4	5	6	7	8	9	10	11
13.75°	3	3	4	4	5	6	7	9	10	10	11
12.5°	3	3	4	4	5	6	8	9	10	11	12
11.25°	3	3	4	4	5	7	8	9	10	11	12
10°	3	3	4	5	6	7	8	9	10	11	12
8.75°	3	3	4	5	6	7	8	9	10	11	12
7.5°	3	3	4	5	6	7	8	9	10	11	12
6.25°	3	3	4	5	6	7	9	10	11	12	13
5°	3	3	4	5	6	7	9	10	11	12	13
3.75°	3	3	4	5	6	7	9	10	11	12	13
2.5°	3	3	4	5	6	7	9	10	11	12	13
1.25°	3	3	4	5	6	7	9	10	11	12	13
0°	3	4	4	5	6	7	9	10	11	12	13
-1.25°	3	3	4	5	6	7	9	10	11	12	13
-2.5°	3	3	4	5	6	7	9	10	11	12	13
-3.75°	3	3	4	5	6	7	9	10	11	12	13
-5°	3	3	4	5	6	7	9	10	11	12	13
-6.25°	3	3	4	5	6	7	9	10	11	12	13
-7.5°	3	3	4	5	6	7	8	9	10	11	12
-8.75°	3	3	4	5	6	7	8	9	10	11	12
-10°	3	3	4	5	6	7	8	9	10	11	12
-11.25°	3	3	4	4	5	7	8	9	10	11	12
-12.5°	3	3	4	4	5	6	8	9	10	11	12
-13.75°	2	3	3	4	5	6	7	9	10	10	11
-15°	2	3	3	4	5	6	7	8	9	10	11
-16.25°	2	3	3	4	5	6	7	8	9	10	11
-17.5°	2	3	3	4	5	6	7	8	9	10	11
-18.75°	2	2	3	4	4	5	6	7	9	9	10
-20°	2	2	3	3	4	5	6	7	8	9	10
-21.25°	2	2	3	3	4	5	6	7	8	9	10



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	2	3	4	5	6	7	8	9	9
-23.75°	2	2	2	3	4	4	5	6	7	8	9
-25°	2	2	2	3	3	4	5	6	7	8	9
-26.25°	2	2	2	2	3	4	5	6	7	7	8
-27.5°	2	2	2	2	3	4	4	5	6	7	8
-28.75°	2	2	2	2	3	3	4	5	6	7	7
-30°	2	2	2	2	2	3	4	5	5	6	7
-31.25°	2	2	2	2	2	3	4	4	5	6	7
-32.5°	2	2	2	2	2	2	3	4	5	5	6
-33.75°	2	2	2	2	2	2	3	4	4	5	6
-35°	2	2	2	2	2	2	2	3	4	5	5
-36.25°	2	2	2	2	2	2	2	3	4	4	5
-37.5°	2	2	2	2	2	2	2	2	3	4	4
-38.75°	1	2	2	2	2	2	2	2	3	3	4
-40°	1	2	2	2	2	2	2	2	2	3	4
-41.25°	1	1	2	2	2	2	2	2	2	2	3
-42.5°	1	1	2	2	2	2	2	2	2	2	3
-43.75°	1	1	1	2	2	2	2	2	2	2	2
-45°	1	1	1	2	2	2	2	2	2	2	2
-46.25°	1	1	1	1	2	2	2	2	2	2	2
-47.5°	1	1	1	1	1	2	2	2	2	2	2
-48.75°	1	1	1	1	1	1	2	2	2	2	2
-50°	1	1	1	1	1	1	1	2	2	2	2
-51.25°	1	1	1	1	1	1	1	1	2	2	2
-52.5°	1	1	1	1	1	1	1	1	1	2	2
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	1	1	1	1	1	1	1	1	1
-67.5°	0	0	0	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	1	1	1	1	1	1
-70°	0	0	0	0	0	0	1	1	1	1	1
-71.25°	0	0	0	0	0	0	0	0	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	2
61.25°	1	1	1	1	1	1	1	2	2	2	2
60°	1	1	1	1	1	2	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	2	2	2
53.75°	2	2	2	2	2	2	2	2	2	2	3
52.5°	2	2	2	2	2	2	2	2	3	3	4
51.25°	2	2	2	2	2	2	3	3	3	4	4
50°	2	2	2	2	2	3	3	4	4	5	5
48.75°	2	2	2	3	3	3	4	4	5	5	6
47.5°	2	2	3	3	3	4	4	5	5	6	6
46.25°	2	3	3	4	4	5	5	6	6	6	7
45°	3	3	4	4	5	5	6	6	6	7	7
43.75°	3	4	4	5	5	6	6	7	7	7	8
42.5°	4	4	5	5	6	6	7	7	7	8	9
41.25°	4	4	5	6	6	7	7	7	8	9	10
40°	4	5	6	6	7	7	8	8	9	10	10
38.75°	5	5	6	7	7	8	8	9	10	10	11
37.5°	5	6	7	7	8	8	9	10	10	11	11
36.25°	6	6	7	7	8	9	10	10	11	11	12
35°	6	7	7	8	9	10	10	11	11	12	12



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	7	7	8	9	9	10	11	11	12	12	13
32.5°	7	8	8	9	10	11	11	12	12	13	13
31.25°	7	8	9	10	10	11	12	12	13	13	14
30°	8	9	9	10	11	12	12	12	13	14	14
28.75°	8	9	10	11	11	12	12	13	13	14	15
27.5°	9	9	10	11	12	12	13	13	14	14	15
26.25°	9	10	11	11	12	12	13	14	14	15	15
25°	9	10	11	12	12	13	13	14	15	15	16
23.75°	10	11	11	12	13	13	14	15	15	16	17
22.5°	10	11	12	12	13	13	14	15	16	16	17
21.25°	11	11	12	13	13	14	15	15	16	17	18
20°	11	12	12	13	14	14	15	16	17	17	18
18.75°	11	12	13	13	14	15	16	16	17	18	19
17.5°	12	12	13	14	15	15	16	17	18	18	19
16.25°	12	13	13	14	15	16	17	17	18	19	20
15°	12	13	14	15	15	16	17	18	19	20	21
13.75°	12	13	14	15	16	17	18	18	19	20	22
12.5°	13	14	14	15	16	17	18	19	20	21	23
11.25°	13	14	15	16	17	17	18	19	20	22	23
10°	13	14	15	16	17	18	19	20	21	22	24
8.75°	13	14	15	16	17	18	19	20	21	23	25
7.5°	14	15	16	17	18	18	19	20	22	24	26
6.25°	14	15	16	17	18	19	20	21	22	24	27
5°	14	15	16	17	18	19	20	21	23	25	28
3.75°	14	15	16	17	18	19	20	21	23	26	29
2.5°	14	16	17	18	19	20	21	22	24	26	30
1.25°	14	16	17	18	19	20	21	22	24	27	30
0°	14	16	17	18	19	20	21	22	24	27	31
-1.25°	14	16	17	18	19	20	21	22	24	27	30
-2.5°	14	16	17	18	19	20	21	22	24	26	30
-3.75°	14	16	17	18	18	19	20	21	24	26	29
-5°	14	15	16	17	18	19	20	21	23	25	28
-6.25°	14	15	16	17	18	19	20	21	23	25	27
-7.5°	14	15	16	17	18	19	20	21	22	24	26
-8.75°	13	15	16	17	18	18	19	20	22	23	25
-10°	13	14	15	16	17	18	19	20	21	23	24
-11.25°	13	14	15	16	17	18	18	19	21	22	23
-12.5°	13	14	15	16	17	17	18	19	20	21	23
-13.75°	12	13	15	16	16	17	18	19	20	21	22
-15°	12	13	14	15	16	17	17	18	19	20	21
-16.25°	12	13	14	15	16	17	17	17	19	20	21
-17.5°	12	12	13	14	15	16	17	17	18	19	20
-18.75°	11	12	13	14	15	16	16	17	17	18	20
-20°	11	12	13	14	14	15	16	16	17	18	19
-21.25°	11	11	12	13	14	15	16	16	17	17	18



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	10	11	12	13	14	14	15	16	16	17	17
-23.75°	10	11	11	12	13	14	15	15	16	16	17
-25°	9	10	11	12	13	13	14	15	16	16	16
-26.25°	9	10	11	11	12	13	14	14	15	16	16
-27.5°	9	9	10	11	12	12	13	14	15	15	16
-28.75°	8	9	10	11	11	12	13	13	14	15	15
-30°	8	9	9	10	11	11	12	13	14	14	15
-31.25°	7	8	9	10	10	11	12	12	13	14	14
-32.5°	7	8	8	9	10	10	11	12	12	13	14
-33.75°	6	7	8	9	9	10	11	11	12	12	13
-35°	6	7	7	8	9	9	10	11	11	12	12
-36.25°	6	6	7	7	8	9	9	10	11	11	12
-37.5°	5	6	6	7	8	8	9	9	10	10	11
-38.75°	5	5	6	6	7	8	8	9	9	10	10
-40°	4	5	5	6	6	7	8	8	9	9	10
-41.25°	4	4	5	5	6	6	7	7	8	8	9
-42.5°	3	4	4	5	5	6	6	7	7	8	8
-43.75°	3	3	4	4	5	5	6	6	7	7	8
-45°	2	3	3	4	4	5	5	5	6	6	7
-46.25°	2	2	3	3	4	4	5	5	5	6	6
-47.5°	2	2	2	3	3	4	4	5	5	5	5
-48.75°	2	2	2	2	3	3	4	4	4	5	5
-50°	2	2	2	2	2	3	3	4	4	4	4
-51.25°	2	2	2	2	2	2	2	3	3	4	4
-52.5°	2	2	2	2	2	2	2	2	3	3	3
-53.75°	2	2	2	2	2	2	2	2	2	2	3
-55°	1	1	2	2	2	2	2	2	2	2	2
-56.25°	1	1	1	1	2	2	2	2	2	2	2
-57.5°	1	1	1	1	1	1	2	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	2	2	2
-60°	1	1	1	1	1	1	1	1	1	1	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	0	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	3	3
57.5°	2	2	2	2	2	2	3	3	3	4	4
56.25°	2	2	2	3	3	3	4	4	4	4	4
55°	2	3	3	3	4	4	4	5	5	5	5
53.75°	3	4	4	4	5	5	5	5	5	5	6
52.5°	4	4	5	5	5	5	6	6	6	6	6
51.25°	5	5	5	6	6	6	6	6	7	7	7
50°	5	6	6	6	6	7	7	7	7	8	8
48.75°	6	6	6	7	7	7	8	8	8	8	9
47.5°	6	7	7	7	8	8	9	9	9	9	9
46.25°	7	7	8	8	9	9	9	10	10	10	10
45°	7	8	9	9	10	10	10	10	10	11	11
43.75°	9	9	10	10	10	10	11	11	11	11	11
42.5°	10	10	10	10	11	11	11	12	12	12	12
41.25°	10	10	11	11	11	12	12	12	12	12	12
40°	11	11	11	12	12	12	13	13	13	13	13
38.75°	11	11	12	12	13	13	13	13	13	13	14
37.5°	12	12	13	13	13	13	13	14	14	14	14
36.25°	12	13	13	13	14	14	14	14	14	15	15
35°	13	13	14	14	14	14	14	15	15	15	16



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	13	14	14	14	14	15	15	15	16	16	16
32.5°	14	14	14	15	15	15	16	16	17	17	17
31.25°	14	14	15	15	15	16	16	17	17	18	18
30°	15	15	15	16	16	17	17	18	18	19	19
28.75°	15	15	16	16	17	18	18	19	19	19	20
27.5°	15	16	17	17	18	18	19	19	20	20	21
26.25°	16	17	17	18	19	19	20	20	21	21	22
25°	17	17	18	19	19	20	21	21	22	22	22
23.75°	17	18	19	20	20	21	22	22	23	23	24
22.5°	18	19	19	20	21	22	23	24	24	25	26
21.25°	18	19	20	21	22	23	24	25	26	28	29
20°	19	20	21	22	23	24	26	27	29	31	32
18.75°	20	21	22	23	24	26	28	30	32	34	37
17.5°	21	22	23	24	26	28	30	33	36	40	43
16.25°	21	23	24	25	28	30	33	37	41	46	50
15°	22	24	25	27	29	33	37	40	47	53	59
13.75°	23	25	26	29	32	36	40	46	54	61	70
12.5°	24	26	29	33	37	42	44	53	61	72	81
11.25°	25	27	32	36	44	52	61	68	70	83	94
10°	26	28	35	41	54	65	83	98	111	114	114
8.75°	28	31	39	47	65	80	111	135	164	182	196
7.5°	29	34	42	56	77	103	143	181	226	261	294
6.25°	30	37	47	65	90	129	177	233	295	350	400
5°	31	40	51	75	104	155	214	290	369	445	514
3.75°	32	43	55	85	117	183	252	348	446	542	631
2.5°	33	46	58	94	131	210	290	407	524	639	750
1.25°	34	48	62	103	144	235	326	463	599	735	868
0°	35	50	65	110	155	257	359	514	670	825	980
-1.25°	34	48	62	103	144	235	327	464	601	737	872
-2.5°	33	46	58	94	131	210	291	409	527	645	758
-3.75°	32	43	55	85	118	184	254	352	451	549	643
-5°	31	40	51	75	104	156	217	294	375	454	528
-6.25°	30	37	47	65	90	130	180	238	302	361	417
-7.5°	29	34	42	56	77	104	145	185	234	273	312
-8.75°	28	31	39	47	65	81	114	139	172	194	214
-10°	26	28	35	41	54	66	86	103	118	126	132
-11.25°	25	27	32	36	44	53	62	72	77	93	108
-12.5°	24	26	29	33	37	42	45	56	66	79	92
-13.75°	23	25	26	29	32	36	41	48	57	66	77
-15°	22	24	25	27	29	33	37	41	49	56	64
-16.25°	22	23	24	25	28	30	34	37	42	48	52
-17.5°	21	22	23	24	26	28	30	34	36	41	45
-18.75°	20	21	22	23	24	26	28	30	33	35	38
-20°	20	20	21	22	23	24	26	28	30	31	32
-21.25°	19	20	21	21	22	23	24	26	27	28	29



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	18	19	20	20	21	22	23	24	25	26	27
-23.75°	18	18	19	20	20	21	22	22	23	24	25
-25°	17	18	18	19	20	20	21	21	22	23	23
-26.25°	16	17	18	18	19	19	20	20	21	21	22
-27.5°	16	16	17	18	18	18	19	19	20	20	21
-28.75°	15	16	16	17	17	18	18	19	19	20	20
-30°	15	15	16	16	17	17	17	18	18	19	19
-31.25°	14	15	15	16	16	17	17	17	17	18	18
-32.5°	14	14	15	15	16	16	16	17	17	17	18
-33.75°	14	14	14	14	15	15	16	16	16	16	17
-35°	13	13	14	14	14	15	15	15	16	16	16
-36.25°	12	13	13	13	14	14	14	15	15	15	15
-37.5°	12	12	13	13	13	13	14	14	14	15	15
-38.75°	11	11	12	12	13	13	13	13	14	14	14
-40°	10	11	11	12	12	12	13	13	13	13	13
-41.25°	9	10	10	11	11	12	12	12	12	13	13
-42.5°	9	9	10	10	10	11	11	11	12	12	12
-43.75°	8	8	9	9	10	10	10	10	11	11	11
-45°	7	8	8	9	9	9	9	10	10	10	10
-46.25°	7	7	7	8	8	9	9	9	9	9	9
-47.5°	6	6	7	7	7	8	8	8	9	9	9
-48.75°	5	6	6	6	7	7	7	7	8	8	8
-50°	5	5	5	6	6	6	6	7	7	7	7
-51.25°	4	4	5	5	5	5	6	6	6	6	7
-52.5°	4	4	4	4	5	5	5	5	6	6	6
-53.75°	3	3	4	4	4	4	4	5	5	5	5
-55°	2	3	3	3	3	4	4	4	4	4	5
-56.25°	2	2	2	3	3	3	3	3	3	4	4
-57.5°	2	2	2	2	2	2	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	3
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	2	2
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	0	0	0	0	0	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	3
60°	2	2	3	3	3	3	3	3	3	3	3
58.75°	3	3	4	4	4	4	4	4	4	4	4
57.5°	4	4	4	4	4	4	4	5	5	5	5
56.25°	5	5	5	5	5	5	5	5	5	5	5
55°	5	5	5	6	6	6	6	6	6	6	6
53.75°	6	6	6	6	7	7	7	7	7	7	7
52.5°	7	7	7	7	7	7	7	7	7	7	7
51.25°	7	8	8	8	8	8	8	8	8	8	8
50°	8	8	8	8	8	9	9	9	9	9	9
48.75°	9	9	9	9	9	9	9	9	9	9	9
47.5°	10	10	10	10	10	10	10	10	10	10	10
46.25°	10	10	11	11	11	11	11	11	11	11	11
45°	11	11	11	11	11	11	11	11	11	11	11
43.75°	12	12	12	12	12	12	12	12	12	12	12
42.5°	12	12	12	12	12	12	12	13	13	13	13
41.25°	13	13	13	13	13	13	13	13	13	13	13
40°	13	13	14	14	14	14	14	14	14	14	14
38.75°	14	14	14	14	15	15	15	15	15	15	15
37.5°	15	15	15	15	15	15	15	15	16	16	16
36.25°	15	15	16	16	16	16	16	16	16	17	17
35°	16	16	16	17	17	17	17	17	17	18	18



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	17	17	17	18	18	18	18	18	18	19	19
32.5°	18	18	18	19	19	19	19	19	19	20	20
31.25°	19	19	19	19	20	20	20	20	20	21	21
30°	19	20	20	20	21	21	21	21	21	22	22
28.75°	20	21	21	21	22	22	22	22	22	23	23
27.5°	21	22	22	22	23	23	23	24	24	24	24
26.25°	22	22	23	24	24	25	25	25	25	25	26
25°	23	24	25	25	26	27	27	27	27	27	28
23.75°	25	25	26	27	28	29	29	30	30	30	30
22.5°	26	27	29	30	31	32	32	33	33	34	34
21.25°	29	30	31	32	34	35	36	37	38	38	38
20°	34	34	34	36	37	39	41	42	43	43	44
18.75°	39	40	40	39	42	44	46	48	49	51	51
17.5°	46	48	48	48	47	50	52	55	57	58	59
16.25°	54	57	60	61	58	56	60	62	65	67	69
15°	65	70	76	79	77	70	67	71	74	77	80
13.75°	76	88	96	102	103	97	83	80	84	88	91
12.5°	94	109	120	132	136	131	119	97	95	99	103
11.25°	115	133	152	167	174	173	163	142	112	110	120
10°	139	162	188	208	219	221	213	195	167	135	140
8.75°	197	196	228	253	269	276	270	255	235	206	170
7.5°	312	322	319	302	324	333	332	325	311	287	277
6.25°	437	460	467	451	432	403	401	402	395	392	387
5°	566	603	613	600	574	536	507	490	488	499	501
3.75°	697	751	758	749	710	662	621	589	584	598	627
2.5°	829	900	903	897	842	783	727	678	668	673	706
1.25°	959	1048	1048	1044	973	902	829	760	746	737	773
0°	1086	1192	1192	1192	1107	1023	933	844	821	798	832
-1.25°	964	1054	1055	1052	981	910	838	769	756	749	786
-2.5°	839	913	917	912	857	799	744	696	688	695	731
-3.75°	712	770	779	771	733	686	646	616	613	631	662
-5°	584	627	640	629	605	568	541	525	523	533	537
-6.25°	459	488	501	487	470	442	438	436	426	423	421
-7.5°	337	353	359	344	363	369	364	353	337	313	305
-8.75°	223	230	265	290	302	306	295	277	255	226	191
-10°	162	189	218	239	247	246	233	211	179	147	153
-11.25°	133	154	175	191	197	192	177	153	119	117	129
-12.5°	107	125	138	150	153	145	129	102	99	104	108
-13.75°	86	99	109	114	115	106	88	84	88	92	95
-15°	71	77	85	87	84	74	70	74	77	80	83
-16.25°	59	62	65	66	61	59	62	65	67	70	72
-17.5°	48	51	51	50	49	51	54	57	58	60	61
-18.75°	40	41	41	40	43	45	47	49	50	52	52
-20°	34	35	34	36	38	40	41	43	43	44	45
-21.25°	30	30	31	33	34	36	36	37	38	38	38



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	27	27	29	30	31	32	33	33	33	34	34
-23.75°	25	26	27	28	29	29	30	30	31	30	31
-25°	24	25	25	26	26	27	28	28	28	28	29
-26.25°	23	23	24	24	25	25	26	26	26	26	27
-27.5°	21	22	22	23	23	24	24	24	25	25	25
-28.75°	20	21	21	22	22	22	23	23	23	24	24
-30°	20	20	20	21	21	21	21	21	22	22	22
-31.25°	19	19	19	20	20	20	20	20	21	21	21
-32.5°	18	18	19	19	19	19	19	19	20	20	20
-33.75°	17	18	18	18	18	19	19	19	19	19	19
-35°	16	17	17	17	18	18	18	18	18	18	18
-36.25°	16	16	16	16	17	17	17	17	17	18	17
-37.5°	15	15	15	16	16	16	16	16	16	17	17
-38.75°	14	14	15	15	15	15	15	15	15	16	16
-40°	14	14	14	14	14	14	14	15	15	15	15
-41.25°	13	13	13	14	14	14	14	14	14	14	14
-42.5°	12	12	13	13	13	13	13	13	13	13	13
-43.75°	11	12	12	12	12	12	12	12	12	12	12
-45°	11	11	11	11	11	11	11	12	12	12	12
-46.25°	10	10	10	10	10	10	11	11	11	11	11
-47.5°	9	9	9	9	9	9	10	10	10	10	10
-48.75°	8	9	9	9	9	9	9	9	9	9	9
-50°	8	8	8	8	8	8	8	8	8	8	8
-51.25°	7	7	7	7	7	8	8	8	8	8	8
-52.5°	6	6	6	6	7	7	7	7	7	7	7
-53.75°	5	6	6	6	6	6	6	6	6	6	6
-55°	5	5	5	5	5	5	5	5	6	6	6
-56.25°	4	4	4	5	5	5	5	5	5	5	5
-57.5°	3	3	3	4	4	4	4	4	4	4	4
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	1	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	2	1	1	1	1
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	4	4	4	4	4	4	4	4	4	4	4
57.5°	5	5	5	5	5	5	5	5	5	5	5
56.25°	6	6	6	6	6	6	6	6	6	6	6
55°	6	6	6	6	6	6	6	6	6	6	6
53.75°	7	7	7	7	7	7	7	7	7	7	7
52.5°	7	7	7	7	7	7	7	7	7	7	7
51.25°	8	8	8	8	8	8	8	8	8	8	8
50°	9	9	8	8	8	8	8	8	8	8	8
48.75°	9	9	9	9	9	9	9	9	9	9	9
47.5°	10	10	10	10	10	10	10	10	10	10	10
46.25°	11	11	11	11	11	11	11	11	11	11	11
45°	11	11	11	11	11	11	11	11	11	11	11
43.75°	12	12	12	12	12	12	12	12	12	12	12
42.5°	13	13	13	12	12	12	12	12	12	12	13
41.25°	13	13	13	13	13	13	13	13	13	13	13
40°	14	14	14	14	14	14	14	14	14	14	14
38.75°	15	15	15	15	15	15	15	15	15	15	15
37.5°	16	16	16	15	15	15	15	15	15	15	16
36.25°	17	17	17	16	16	16	16	16	16	16	17
35°	18	18	18	17	17	17	17	17	17	17	18



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	19	19	19	18	18	18	18	18	18	18	19
32.5°	20	20	20	19	19	19	19	19	19	19	20
31.25°	21	21	21	21	21	21	21	21	21	21	21
30°	22	22	22	22	22	22	22	22	22	22	22
28.75°	23	23	23	24	24	24	24	24	24	24	23
27.5°	25	25	25	25	25	25	25	25	25	25	25
26.25°	26	27	27	27	27	27	27	27	27	27	27
25°	29	29	29	29	29	29	29	29	29	29	29
23.75°	31	32	32	33	33	33	33	33	33	33	32
22.5°	35	36	36	36	36	36	36	36	36	36	36
21.25°	39	40	41	42	42	42	41	42	42	42	41
20°	45	46	47	47	47	47	46	47	47	47	47
18.75°	51	53	55	56	56	56	56	56	56	56	55
17.5°	61	62	64	65	66	66	65	66	66	65	64
16.25°	71	72	74	76	77	78	77	78	77	76	74
15°	82	83	85	87	89	89	89	89	89	87	85
13.75°	93	94	97	101	103	104	103	104	103	101	97
12.5°	107	111	112	116	118	118	117	118	118	116	112
11.25°	126	129	131	136	140	141	139	141	140	136	131
10°	147	163	166	162	165	164	160	164	165	162	166
8.75°	196	210	209	208	216	221	212	221	216	208	209
7.5°	255	278	301	321	333	346	329	346	333	321	301
6.25°	379	393	444	491	520	540	519	540	520	491	444
5°	520	559	612	679	727	754	741	754	727	679	612
3.75°	663	719	782	846	904	935	923	935	904	846	782
2.5°	768	850	922	985	1033	1071	1061	1071	1033	985	922
1.25°	839	921	1007	1075	1121	1151	1158	1151	1121	1075	1007
0°	893	973	1054	1112	1157	1186	1200	1186	1157	1112	1054
-1.25°	853	937	1024	1091	1137	1165	1173	1165	1137	1091	1024
-2.5°	798	882	954	1019	1068	1101	1097	1101	1068	1019	954
-3.75°	701	759	827	895	948	979	969	979	948	895	827
-5°	561	605	664	727	772	799	785	799	772	727	664
-6.25°	418	439	488	533	560	586	570	586	560	533	488
-7.5°	289	313	336	353	366	384	370	384	366	353	336
-8.75°	219	234	231	227	238	245	238	245	238	227	231
-10°	161	177	179	173	176	174	169	174	176	173	179
-11.25°	135	137	137	142	146	147	144	147	146	142	137
-12.5°	113	117	116	119	121	121	119	121	121	119	116
-13.75°	97	99	101	104	105	105	104	105	105	104	101
-15°	85	86	88	90	90	90	89	90	90	90	88
-16.25°	73	74	76	78	78	78	77	78	78	78	76
-17.5°	62	64	65	66	67	66	65	66	67	66	65
-18.75°	52	54	55	56	56	56	55	56	56	56	55
-20°	45	46	47	47	47	46	45	46	47	47	47
-21.25°	39	40	41	41	41	41	40	41	41	41	41



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	35	36	36	36	36	36	35	36	36	36	36
-23.75°	31	32	33	33	33	33	33	33	33	33	33
-25°	29	29	30	30	30	30	30	30	30	30	30
-26.25°	27	28	28	28	28	28	28	28	28	28	28
-27.5°	26	26	26	26	26	26	26	26	26	26	26
-28.75°	24	24	24	25	25	25	25	25	25	25	24
-30°	23	23	23	23	23	23	23	23	23	23	23
-31.25°	21	21	21	22	22	22	22	22	22	22	21
-32.5°	20	20	20	20	20	20	20	20	20	20	20
-33.75°	19	19	19	19	19	19	19	19	19	19	19
-35°	18	18	18	18	18	18	18	18	18	18	18
-36.25°	17	17	17	17	17	17	17	17	17	17	17
-37.5°	17	17	17	16	16	16	16	16	16	16	17
-38.75°	16	16	15	15	15	15	15	15	15	15	15
-40°	15	15	15	14	14	14	14	14	14	14	15
-41.25°	14	14	14	14	14	14	14	14	14	14	14
-42.5°	13	13	13	13	13	13	13	13	13	13	13
-43.75°	12	12	12	12	12	12	12	12	12	12	12
-45°	12	12	12	11	11	11	11	11	11	11	12
-46.25°	11	11	11	11	11	11	11	11	11	11	11
-47.5°	10	10	10	10	10	10	10	10	10	10	10
-48.75°	9	9	9	9	9	9	9	9	9	9	9
-50°	8	8	8	8	8	8	8	8	8	8	8
-51.25°	8	8	8	8	8	8	8	8	8	8	8
-52.5°	7	7	7	7	7	7	7	7	7	7	7
-53.75°	7	7	7	7	7	7	7	7	7	7	7
-55°	6	6	6	6	6	6	6	6	6	6	6
-56.25°	5	5	5	5	5	5	5	5	5	5	5
-57.5°	4	4	4	4	4	4	4	4	4	4	4
-58.75°	4	4	4	4	4	4	4	4	4	4	4
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	3	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	1	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	2	2	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	3	3	3	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	4	4	4	4	4	4	4	4	4	4	4
57.5°	5	5	5	5	5	5	4	4	4	4	4
56.25°	6	6	5	5	5	5	5	5	5	5	5
55°	6	6	6	6	6	6	6	6	6	6	5
53.75°	7	7	7	7	7	7	7	7	7	6	6
52.5°	7	7	7	7	7	7	7	7	7	7	7
51.25°	8	8	8	8	8	8	8	8	8	8	8
50°	9	9	9	9	9	9	9	9	8	8	8
48.75°	9	9	9	9	9	9	9	9	9	9	9
47.5°	10	10	10	10	10	10	10	10	10	10	10
46.25°	11	11	11	11	11	11	11	11	11	11	11
45°	11	11	11	11	11	11	11	11	11	11	11
43.75°	12	12	12	12	12	12	12	12	12	12	12
42.5°	13	13	13	13	13	13	12	12	12	12	12
41.25°	13	13	13	13	13	13	13	13	13	13	13
40°	14	14	14	14	14	14	14	14	14	14	14
38.75°	15	15	15	15	15	15	15	15	15	14	14
37.5°	16	16	16	16	16	15	15	15	15	15	15
36.25°	17	17	17	17	16	16	16	16	16	16	16
35°	18	18	18	18	17	17	17	17	17	17	16



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	19	19	19	19	18	18	18	18	18	18	17
32.5°	20	20	20	20	19	19	19	19	19	19	18
31.25°	21	21	21	21	20	20	20	20	20	19	19
30°	22	22	22	22	21	21	21	21	21	20	20
28.75°	23	23	23	23	22	22	22	22	22	21	21
27.5°	25	25	24	24	24	24	23	23	23	22	22
26.25°	27	26	26	25	25	25	25	25	24	24	23
25°	29	29	28	27	27	27	27	27	26	25	25
23.75°	32	31	30	30	30	30	29	29	28	27	26
22.5°	36	35	34	34	33	33	32	32	31	30	29
21.25°	40	39	38	38	38	37	36	35	34	32	31
20°	46	45	44	43	43	42	41	39	37	36	34
18.75°	53	51	51	51	49	48	46	44	42	39	40
17.5°	62	61	59	58	57	55	52	50	47	48	48
16.25°	72	71	69	67	65	62	60	56	58	61	60
15°	83	82	80	77	74	71	67	70	77	79	76
13.75°	94	93	91	88	84	80	83	97	103	102	96
12.5°	111	107	103	99	95	97	119	131	136	132	120
11.25°	129	126	120	110	112	142	163	173	174	167	152
10°	163	147	140	135	167	195	213	221	219	208	188
8.75°	210	196	170	206	235	255	270	276	269	253	228
7.5°	278	255	277	287	311	325	332	333	324	302	319
6.25°	393	379	387	392	395	402	401	403	432	451	467
5°	559	520	501	499	488	490	507	536	574	600	613
3.75°	719	663	627	598	584	589	621	662	710	749	758
2.5°	850	768	706	673	668	678	727	783	842	897	903
1.25°	921	839	773	737	746	760	829	902	973	1044	1048
0°	973	893	832	798	821	844	933	1023	1107	1192	1192
-1.25°	937	853	786	749	756	769	838	910	981	1052	1055
-2.5°	882	798	731	695	688	696	744	799	857	912	917
-3.75°	759	701	662	631	613	616	646	686	733	771	779
-5°	605	561	537	533	523	525	541	568	605	629	640
-6.25°	439	418	421	423	426	436	438	442	470	487	501
-7.5°	313	289	305	313	337	353	364	369	363	344	359
-8.75°	234	219	191	226	255	277	295	306	302	290	265
-10°	177	161	153	147	179	211	233	246	247	239	218
-11.25°	137	135	129	117	119	153	177	192	197	191	175
-12.5°	117	113	108	104	99	102	129	145	153	150	138
-13.75°	99	97	95	92	88	84	88	106	115	114	109
-15°	86	85	83	80	77	74	70	74	84	87	85
-16.25°	74	73	72	70	67	65	62	59	61	66	65
-17.5°	64	62	61	60	58	57	54	51	49	50	51
-18.75°	54	52	52	52	50	49	47	45	43	40	41
-20°	46	45	45	44	43	43	41	40	38	36	34
-21.25°	40	39	38	38	38	37	36	36	34	33	31



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	36	35	34	34	33	33	33	32	31	30	29
-23.75°	32	31	31	30	31	30	30	29	29	28	27
-25°	29	29	29	28	28	28	28	27	26	26	25
-26.25°	28	27	27	26	26	26	26	25	25	24	24
-27.5°	26	26	25	25	25	24	24	24	23	23	22
-28.75°	24	24	24	24	23	23	23	22	22	22	21
-30°	23	23	22	22	22	21	21	21	21	21	20
-31.25°	21	21	21	21	21	20	20	20	20	20	19
-32.5°	20	20	20	20	20	19	19	19	19	19	19
-33.75°	19	19	19	19	19	19	19	19	18	18	18
-35°	18	18	18	18	18	18	18	18	18	17	17
-36.25°	17	17	17	18	17	17	17	17	17	16	16
-37.5°	17	17	17	17	16	16	16	16	16	16	15
-38.75°	16	16	16	16	15	15	15	15	15	15	15
-40°	15	15	15	15	15	15	14	14	14	14	14
-41.25°	14	14	14	14	14	14	14	14	14	14	13
-42.5°	13	13	13	13	13	13	13	13	13	13	13
-43.75°	12	12	12	12	12	12	12	12	12	12	12
-45°	12	12	12	12	12	12	11	11	11	11	11
-46.25°	11	11	11	11	11	11	11	10	10	10	10
-47.5°	10	10	10	10	10	10	10	9	9	9	9
-48.75°	9	9	9	9	9	9	9	9	9	9	9
-50°	8	8	8	8	8	8	8	8	8	8	8
-51.25°	8	8	8	8	8	8	8	8	7	7	7
-52.5°	7	7	7	7	7	7	7	7	7	6	6
-53.75°	7	7	6	6	6	6	6	6	6	6	6
-55°	6	6	6	6	6	5	5	5	5	5	5
-56.25°	5	5	5	5	5	5	5	5	5	5	4
-57.5°	4	4	4	4	4	4	4	4	4	4	3
-58.75°	4	4	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	2	2	2	2	2	2	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	3	3	3	3	2	2	2	2	2	2	2
57.5°	4	4	4	4	3	3	3	2	2	2	2
56.25°	5	5	4	4	4	4	4	3	3	3	2
55°	5	5	5	5	5	5	4	4	4	3	3
53.75°	6	6	6	5	5	5	5	5	5	4	4
52.5°	7	7	6	6	6	6	6	5	5	5	5
51.25°	8	7	7	7	7	6	6	6	6	6	5
50°	8	8	8	8	7	7	7	7	6	6	6
48.75°	9	9	9	8	8	8	8	7	7	7	6
47.5°	10	10	9	9	9	9	9	8	8	7	7
46.25°	10	10	10	10	10	10	9	9	9	8	8
45°	11	11	11	11	10	10	10	10	10	9	9
43.75°	12	12	11	11	11	11	11	10	10	10	10
42.5°	12	12	12	12	12	12	11	11	11	10	10
41.25°	13	13	12	12	12	12	12	12	11	11	11
40°	13	13	13	13	13	13	13	12	12	12	11
38.75°	14	14	14	13	13	13	13	13	13	12	12
37.5°	15	15	14	14	14	14	13	13	13	13	13
36.25°	15	15	15	15	14	14	14	14	14	13	13
35°	16	16	16	15	15	15	14	14	14	14	14



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	17	17	16	16	16	15	15	15	14	14	14
32.5°	18	18	17	17	17	16	16	15	15	15	14
31.25°	19	19	18	18	17	17	16	16	15	15	15
30°	20	19	19	19	18	18	17	17	16	16	15
28.75°	21	20	20	19	19	19	18	18	17	16	16
27.5°	22	21	21	20	20	19	19	18	18	17	17
26.25°	22	22	22	21	21	20	20	19	19	18	17
25°	24	23	22	22	22	21	21	20	19	19	18
23.75°	25	25	24	23	23	22	22	21	20	20	19
22.5°	27	26	26	25	24	24	23	22	21	20	19
21.25°	30	29	29	28	26	25	24	23	22	21	20
20°	34	34	32	31	29	27	26	24	23	22	21
18.75°	40	39	37	34	32	30	28	26	24	23	22
17.5°	48	46	43	40	36	33	30	28	26	24	23
16.25°	57	54	50	46	41	37	33	30	28	25	24
15°	70	65	59	53	47	40	37	33	29	27	25
13.75°	88	76	70	61	54	46	40	36	32	29	26
12.5°	109	94	81	72	61	53	44	42	37	33	29
11.25°	133	115	94	83	70	68	61	52	44	36	32
10°	162	139	114	114	111	98	83	65	54	41	35
8.75°	196	197	196	182	164	135	111	80	65	47	39
7.5°	322	312	294	261	226	181	143	103	77	56	42
6.25°	460	437	400	350	295	233	177	129	90	65	47
5°	603	566	514	445	369	290	214	155	104	75	51
3.75°	751	697	631	542	446	348	252	183	117	85	55
2.5°	900	829	750	639	524	407	290	210	131	94	58
1.25°	1048	959	868	735	599	463	326	235	144	103	62
0°	1192	1086	980	825	670	514	359	257	155	110	65
-1.25°	1054	964	872	737	601	464	327	235	144	103	62
-2.5°	913	839	758	645	527	409	291	210	131	94	58
-3.75°	770	712	643	549	451	352	254	184	118	85	55
-5°	627	584	528	454	375	294	217	156	104	75	51
-6.25°	488	459	417	361	302	238	180	130	90	65	47
-7.5°	353	337	312	273	234	185	145	104	77	56	42
-8.75°	230	223	214	194	172	139	114	81	65	47	39
-10°	189	162	132	126	118	103	86	66	54	41	35
-11.25°	154	133	108	93	77	72	62	53	44	36	32
-12.5°	125	107	92	79	66	56	45	42	37	33	29
-13.75°	99	86	77	66	57	48	41	36	32	29	26
-15°	77	71	64	56	49	41	37	33	29	27	25
-16.25°	62	59	52	48	42	37	34	30	28	25	24
-17.5°	51	48	45	41	36	34	30	28	26	24	23
-18.75°	41	40	38	35	33	30	28	26	24	23	22
-20°	35	34	32	31	30	28	26	24	23	22	21
-21.25°	30	30	29	28	27	26	24	23	22	21	21



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	27	27	27	26	25	24	23	22	21	20	20
-23.75°	26	25	25	24	23	22	22	21	20	20	19
-25°	25	24	23	23	22	21	21	20	20	19	18
-26.25°	23	23	22	21	21	20	20	19	19	18	18
-27.5°	22	21	21	20	20	19	19	18	18	18	17
-28.75°	21	20	20	20	19	19	18	18	17	17	16
-30°	20	20	19	19	18	18	17	17	17	16	16
-31.25°	19	19	18	18	17	17	17	17	16	16	15
-32.5°	18	18	18	17	17	17	16	16	16	15	15
-33.75°	18	17	17	16	16	16	16	15	15	14	14
-35°	17	16	16	16	16	15	15	15	14	14	14
-36.25°	16	16	15	15	15	15	14	14	14	13	13
-37.5°	15	15	15	15	14	14	14	13	13	13	13
-38.75°	14	14	14	14	14	13	13	13	13	12	12
-40°	14	14	13	13	13	13	13	12	12	12	11
-41.25°	13	13	13	13	12	12	12	12	11	11	10
-42.5°	12	12	12	12	12	11	11	11	10	10	10
-43.75°	12	11	11	11	11	10	10	10	10	9	9
-45°	11	11	10	10	10	10	9	9	9	9	8
-46.25°	10	10	9	9	9	9	9	9	8	8	7
-47.5°	9	9	9	9	9	8	8	8	7	7	7
-48.75°	9	8	8	8	8	7	7	7	7	6	6
-50°	8	8	7	7	7	7	6	6	6	6	5
-51.25°	7	7	7	6	6	6	6	5	5	5	5
-52.5°	6	6	6	6	6	5	5	5	5	4	4
-53.75°	6	5	5	5	5	5	4	4	4	4	4
-55°	5	5	5	4	4	4	4	4	3	3	3
-56.25°	4	4	4	4	3	3	3	3	3	3	2
-57.5°	3	3	3	3	3	3	3	2	2	2	2
-58.75°	3	3	3	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	1	1	1
-63.75°	2	2	2	2	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	0	0	0	0	0	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	3	2	2	2	2	2	2	2	2	2	2
53.75°	4	3	3	2	2	2	2	2	2	2	2
52.5°	4	4	4	3	3	2	2	2	2	2	2
51.25°	5	5	4	4	3	3	3	2	2	2	2
50°	6	5	5	5	4	4	3	3	2	2	2
48.75°	6	6	6	5	5	4	4	3	3	3	2
47.5°	7	6	6	6	5	5	4	4	3	3	3
46.25°	7	7	7	6	6	6	5	5	4	4	3
45°	8	7	7	7	6	6	6	5	5	4	4
43.75°	9	9	8	7	7	7	6	6	5	5	4
42.5°	10	10	9	8	7	7	7	6	6	5	5
41.25°	10	10	10	9	8	7	7	7	6	6	5
40°	11	11	10	10	9	8	8	7	7	6	6
38.75°	11	11	11	10	10	9	8	8	7	7	6
37.5°	12	12	11	11	10	10	9	8	8	7	7
36.25°	13	12	12	11	11	10	10	9	8	7	7
35°	13	13	12	12	11	11	10	10	9	8	7



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	14	13	13	12	12	11	11	10	9	9	8
32.5°	14	14	13	13	12	12	11	11	10	9	8
31.25°	14	14	14	13	13	12	12	11	10	10	9
30°	15	15	14	14	13	12	12	12	11	10	9
28.75°	15	15	15	14	13	13	12	12	11	11	10
27.5°	16	15	15	14	14	13	13	12	12	11	10
26.25°	17	16	15	15	14	14	13	12	12	11	11
25°	17	17	16	15	15	14	13	13	12	12	11
23.75°	18	17	17	16	15	15	14	13	13	12	11
22.5°	19	18	17	16	16	15	14	13	13	12	12
21.25°	19	18	18	17	16	15	15	14	13	13	12
20°	20	19	18	17	17	16	15	14	14	13	12
18.75°	21	20	19	18	17	16	16	15	14	13	13
17.5°	22	21	19	18	18	17	16	15	15	14	13
16.25°	23	21	20	19	18	17	17	16	15	14	13
15°	24	22	21	20	19	18	17	16	15	15	14
13.75°	25	23	22	20	19	18	18	17	16	15	14
12.5°	26	24	23	21	20	19	18	17	16	15	14
11.25°	27	25	23	22	20	19	18	17	17	16	15
10°	28	26	24	22	21	20	19	18	17	16	15
8.75°	31	28	25	23	21	20	19	18	17	16	15
7.5°	34	29	26	24	22	20	19	18	18	17	16
6.25°	37	30	27	24	22	21	20	19	18	17	16
5°	40	31	28	25	23	21	20	19	18	17	16
3.75°	43	32	29	26	23	21	20	19	18	17	16
2.5°	46	33	30	26	24	22	21	20	19	18	17
1.25°	48	34	30	27	24	22	21	20	19	18	17
0°	50	35	31	27	24	22	21	20	19	18	17
-1.25°	48	34	30	27	24	22	21	20	19	18	17
-2.5°	46	33	30	26	24	22	21	20	19	18	17
-3.75°	43	32	29	26	24	21	20	19	18	18	17
-5°	40	31	28	25	23	21	20	19	18	17	16
-6.25°	37	30	27	25	23	21	20	19	18	17	16
-7.5°	34	29	26	24	22	21	20	19	18	17	16
-8.75°	31	28	25	23	22	20	19	18	18	17	16
-10°	28	26	24	23	21	20	19	18	17	16	15
-11.25°	27	25	23	22	21	19	18	18	17	16	15
-12.5°	26	24	23	21	20	19	18	17	17	16	15
-13.75°	25	23	22	21	20	19	18	17	16	16	15
-15°	24	22	21	20	19	18	17	17	16	15	14
-16.25°	23	22	21	20	19	17	17	17	16	15	14
-17.5°	22	21	20	19	18	17	17	16	15	14	13
-18.75°	21	20	20	18	17	17	16	16	15	14	13
-20°	20	20	19	18	17	16	16	15	14	14	13
-21.25°	20	19	18	17	17	16	16	15	14	13	12



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	19	18	17	17	16	16	15	14	14	13	12
-23.75°	18	18	17	16	16	15	15	14	13	12	11
-25°	18	17	16	16	16	15	14	13	13	12	11
-26.25°	17	16	16	16	15	14	14	13	12	11	11
-27.5°	16	16	16	15	15	14	13	12	12	11	10
-28.75°	16	15	15	15	14	13	13	12	11	11	10
-30°	15	15	15	14	14	13	12	11	11	10	9
-31.25°	15	14	14	14	13	12	12	11	10	10	9
-32.5°	14	14	14	13	12	12	11	10	10	9	8
-33.75°	14	14	13	12	12	11	11	10	9	9	8
-35°	13	13	12	12	11	11	10	9	9	8	7
-36.25°	13	12	12	11	11	10	9	9	8	7	7
-37.5°	12	12	11	10	10	9	9	8	8	7	6
-38.75°	11	11	10	10	9	9	8	8	7	6	6
-40°	11	10	10	9	9	8	8	7	6	6	5
-41.25°	10	9	9	8	8	7	7	6	6	5	5
-42.5°	9	9	8	8	7	7	6	6	5	5	4
-43.75°	8	8	8	7	7	6	6	5	5	4	4
-45°	8	7	7	6	6	5	5	5	4	4	3
-46.25°	7	7	6	6	5	5	5	4	4	3	3
-47.5°	6	6	5	5	5	5	4	4	3	3	2
-48.75°	6	5	5	5	4	4	4	3	3	2	2
-50°	5	5	4	4	4	4	3	3	2	2	2
-51.25°	4	4	4	4	3	3	2	2	2	2	2
-52.5°	4	4	3	3	3	2	2	2	2	2	2
-53.75°	3	3	3	2	2	2	2	2	2	2	2
-55°	3	2	2	2	2	2	2	2	2	2	2
-56.25°	2	2	2	2	2	2	2	2	2	1	1
-57.5°	2	2	2	2	2	2	2	1	1	1	1
-58.75°	2	2	2	2	2	1	1	1	1	1	1
-60°	2	2	2	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	0
-75°	1	1	1	1	1	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	0
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	1	1	1	1	1	1	1	1
53.75°	2	2	2	2	1	1	1	1	1	1	1
52.5°	2	2	2	2	2	1	1	1	1	1	1
51.25°	2	2	2	2	2	2	1	1	1	1	1
50°	2	2	2	2	2	2	2	1	1	1	1
48.75°	2	2	2	2	2	2	2	2	1	1	1
47.5°	2	2	2	2	2	2	2	2	2	1	1
46.25°	3	2	2	2	2	2	2	2	2	1	1
45°	3	3	3	2	2	2	2	2	2	2	1
43.75°	4	3	3	3	2	2	2	2	2	2	1
42.5°	4	4	3	3	3	2	2	2	2	2	2
41.25°	4	4	3	3	3	2	2	2	2	2	2
40°	5	4	4	3	3	3	2	2	2	2	2
38.75°	5	5	4	4	3	3	3	2	2	2	2
37.5°	6	5	5	4	4	3	3	2	2	2	2
36.25°	6	6	5	4	4	3	3	3	2	2	2
35°	7	6	5	5	4	4	3	3	2	2	2



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	7	7	6	5	4	4	3	3	3	2	2
32.5°	8	7	6	5	5	4	4	3	3	2	2
31.25°	8	7	7	6	5	4	4	3	3	3	2
30°	9	8	7	6	5	5	4	4	3	3	2
28.75°	9	8	7	7	6	5	4	4	3	3	2
27.5°	9	9	8	7	6	5	4	4	3	3	3
26.25°	10	9	8	7	7	6	5	4	4	3	3
25°	10	9	9	8	7	6	5	4	4	3	3
23.75°	11	10	9	8	7	6	5	4	4	3	3
22.5°	11	10	9	9	8	7	6	5	4	3	3
21.25°	11	11	10	9	8	7	6	5	4	4	3
20°	12	11	10	9	8	7	6	5	4	4	3
18.75°	12	11	10	9	9	7	6	5	4	4	3
17.5°	12	12	11	10	9	8	7	6	5	4	3
16.25°	13	12	11	10	9	8	7	6	5	4	3
15°	13	12	11	10	9	8	7	6	5	4	4
13.75°	13	12	11	10	10	9	7	6	5	4	4
12.5°	14	13	12	11	10	9	8	6	5	4	4
11.25°	14	13	12	11	10	9	8	7	5	4	4
10°	14	13	12	11	10	9	8	7	6	5	4
8.75°	14	13	12	11	10	9	8	7	6	5	4
7.5°	15	14	12	11	10	9	8	7	6	5	4
6.25°	15	14	13	12	11	10	9	7	6	5	4
5°	15	14	13	12	11	10	9	7	6	5	4
3.75°	15	14	13	12	11	10	9	7	6	5	4
2.5°	16	14	13	12	11	10	9	7	6	5	4
1.25°	16	14	13	12	11	10	9	7	6	5	4
0°	16	14	13	12	11	10	9	7	6	5	4
-1.25°	16	14	13	12	11	10	9	7	6	5	4
-2.5°	16	14	13	12	11	10	9	7	6	5	4
-3.75°	16	14	13	12	11	10	9	7	6	5	4
-5°	15	14	13	12	11	10	9	7	6	5	4
-6.25°	15	14	13	12	11	10	9	7	6	5	4
-7.5°	15	14	12	11	10	9	8	7	6	5	4
-8.75°	15	13	12	11	10	9	8	7	6	5	4
-10°	14	13	12	11	10	9	8	7	6	5	4
-11.25°	14	13	12	11	10	9	8	7	5	4	4
-12.5°	14	13	12	11	10	9	8	6	5	4	4
-13.75°	13	12	11	10	10	9	7	6	5	4	3
-15°	13	12	11	10	9	8	7	6	5	4	3
-16.25°	13	12	11	10	9	8	7	6	5	4	3
-17.5°	12	12	11	10	9	8	7	6	5	4	3
-18.75°	12	11	10	9	9	7	6	5	4	4	3
-20°	12	11	10	9	8	7	6	5	4	3	3
-21.25°	11	11	10	9	8	7	6	5	4	3	3



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	11	10	9	9	8	7	6	5	4	3	2
-23.75°	11	10	9	8	7	6	5	4	4	3	2
-25°	10	9	9	8	7	6	5	4	3	3	2
-26.25°	10	9	8	7	7	6	5	4	3	2	2
-27.5°	9	9	8	7	6	5	4	4	3	2	2
-28.75°	9	8	7	7	6	5	4	3	3	2	2
-30°	9	8	7	6	5	5	4	3	2	2	2
-31.25°	8	7	7	6	5	4	4	3	2	2	2
-32.5°	8	7	6	5	5	4	3	2	2	2	2
-33.75°	7	6	6	5	4	4	3	2	2	2	2
-35°	7	6	5	5	4	3	2	2	2	2	2
-36.25°	6	6	5	4	4	3	2	2	2	2	2
-37.5°	6	5	4	4	3	2	2	2	2	2	2
-38.75°	5	5	4	3	3	2	2	2	2	2	2
-40°	5	4	4	3	2	2	2	2	2	2	2
-41.25°	4	4	3	2	2	2	2	2	2	2	2
-42.5°	4	3	3	2	2	2	2	2	2	2	2
-43.75°	3	3	2	2	2	2	2	2	2	2	1
-45°	3	2	2	2	2	2	2	2	2	2	1
-46.25°	2	2	2	2	2	2	2	2	2	1	1
-47.5°	2	2	2	2	2	2	2	2	1	1	1
-48.75°	2	2	2	2	2	2	2	1	1	1	1
-50°	2	2	2	2	2	2	1	1	1	1	1
-51.25°	2	2	2	2	2	1	1	1	1	1	1
-52.5°	2	2	2	2	1	1	1	1	1	1	1
-53.75°	2	2	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	0
-68.75°	1	1	1	1	1	1	1	1	0	0	0
-70°	1	1	1	1	1	1	1	0	0	0	0
-71.25°	1	1	1	1	1	0	0	0	0	0	0
-72.5°	1	1	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	1	0	0	0	0	0	0	0	0	0	0
70°	1	1	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	0	0	0	0	0	0	0
67.5°	1	1	1	1	1	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	0	0	0	0	0
65°	1	1	1	1	1	1	0	0	0	0	0
63.75°	1	1	1	1	1	1	1	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	0	0	0
61.25°	1	1	1	1	1	1	1	1	0	0	0
60°	1	1	1	1	1	1	1	1	1	0	0
58.75°	1	1	1	1	1	1	1	1	1	0	0
57.5°	1	1	1	1	1	1	1	1	1	0	0
56.25°	1	1	1	1	1	1	1	1	1	1	0
55°	1	1	1	1	1	1	1	1	1	1	0
53.75°	1	1	1	1	1	1	1	1	1	1	0
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	2	1	1	1	1	1	1	1	1	1	1
38.75°	2	1	1	1	1	1	1	1	1	1	1
37.5°	2	2	1	1	1	1	1	1	1	1	1
36.25°	2	2	1	1	1	1	1	1	1	1	1
35°	2	2	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	2	1	1	1	1	1	1	1	1
32.5°	2	2	2	1	1	1	1	1	1	1	1
31.25°	2	2	2	1	1	1	1	1	1	1	1
30°	2	2	2	2	1	1	1	1	1	1	1
28.75°	2	2	2	2	1	1	1	1	1	1	1
27.5°	2	2	2	2	1	1	1	1	1	1	1
26.25°	2	2	2	2	1	1	1	1	1	1	1
25°	2	2	2	2	2	1	1	1	1	1	1
23.75°	2	2	2	2	2	1	1	1	1	1	1
22.5°	3	2	2	2	2	1	1	1	1	1	1
21.25°	3	2	2	2	2	1	1	1	1	1	1
20°	3	2	2	2	2	1	1	1	1	1	1
18.75°	3	2	2	2	2	1	1	1	1	1	1
17.5°	3	2	2	2	2	2	1	1	1	1	1
16.25°	3	3	2	2	2	2	1	1	1	1	1
15°	3	3	2	2	2	2	1	1	1	1	1
13.75°	3	3	2	2	2	2	1	1	1	1	1
12.5°	3	3	2	2	2	2	1	1	1	1	1
11.25°	3	3	2	2	2	2	1	1	1	1	1
10°	3	3	2	2	2	2	1	1	1	1	1
8.75°	3	3	2	2	2	2	1	1	1	1	1
7.5°	3	3	2	2	2	2	1	1	1	1	1
6.25°	3	3	2	2	2	2	1	1	1	1	1
5°	3	3	2	2	2	2	1	1	1	1	1
3.75°	3	3	2	2	2	2	1	1	1	1	1
2.5°	3	3	2	2	2	2	1	1	1	1	1
1.25°	3	3	2	2	2	2	1	1	1	1	1
0°	4	3	3	2	2	2	2	1	1	1	1
-1.25°	3	3	2	2	2	2	1	1	1	1	1
-2.5°	3	3	2	2	2	2	1	1	1	1	1
-3.75°	3	3	2	2	2	2	1	1	1	1	1
-5°	3	3	2	2	2	2	1	1	1	1	1
-6.25°	3	3	2	2	2	2	1	1	1	1	1
-7.5°	3	3	2	2	2	2	1	1	1	1	1
-8.75°	3	3	2	2	2	2	1	1	1	1	1
-10°	3	3	2	2	2	2	1	1	1	1	1
-11.25°	3	3	2	2	2	2	1	1	1	1	1
-12.5°	3	3	2	2	2	2	1	1	1	1	1
-13.75°	3	2	2	2	2	2	1	1	1	1	1
-15°	3	2	2	2	2	2	1	1	1	1	1
-16.25°	3	2	2	2	2	2	1	1	1	1	1
-17.5°	3	2	2	2	2	2	1	1	1	1	1
-18.75°	2	2	2	2	2	1	1	1	1	1	1
-20°	2	2	2	2	2	1	1	1	1	1	1
-21.25°	2	2	2	2	2	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	2	2	1	1	1	1	1	1
-23.75°	2	2	2	2	2	1	1	1	1	1	1
-25°	2	2	2	2	2	1	1	1	1	1	1
-26.25°	2	2	2	2	1	1	1	1	1	1	1
-27.5°	2	2	2	2	1	1	1	1	1	1	1
-28.75°	2	2	2	2	1	1	1	1	1	1	1
-30°	2	2	2	2	1	1	1	1	1	1	1
-31.25°	2	2	2	1	1	1	1	1	1	1	1
-32.5°	2	2	2	1	1	1	1	1	1	1	1
-33.75°	2	2	2	1	1	1	1	1	1	1	1
-35°	2	2	1	1	1	1	1	1	1	1	1
-36.25°	2	2	1	1	1	1	1	1	1	1	1
-37.5°	2	2	1	1	1	1	1	1	1	1	1
-38.75°	2	1	1	1	1	1	1	1	1	1	1
-40°	2	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	0
-47.5°	1	1	1	1	1	1	1	1	1	1	0
-48.75°	1	1	1	1	1	1	1	1	1	1	0
-50°	1	1	1	1	1	1	1	1	1	0	0
-51.25°	1	1	1	1	1	1	1	1	1	0	0
-52.5°	1	1	1	1	1	1	1	1	1	0	0
-53.75°	1	1	1	1	1	1	1	1	0	0	0
-55°	1	1	1	1	1	1	1	1	0	0	0
-56.25°	1	1	1	1	1	1	1	0	0	0	0
-57.5°	1	1	1	1	1	1	0	0	0	0	0
-58.75°	1	1	1	1	1	1	0	0	0	0	0
-60°	1	1	1	1	1	0	0	0	0	0	0
-61.25°	1	1	1	1	0	0	0	0	0	0	0
-62.5°	1	1	1	1	0	0	0	0	0	0	0
-63.75°	1	1	1	0	0	0	0	0	0	0	0
-65°	1	1	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	1	0	0	0	0	0	0	0	0	0	0
46.25°	1	0	0	0	0	0	0	0	0	0	0
45°	1	0	0	0	0	0	0	0	0	0	0
43.75°	1	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
41.25°	1	0	0	0	0	0	0	0	0	0	0
40°	1	1	0	0	0	0	0	0	0	0	0
38.75°	1	1	0	0	0	0	0	0	0	0	0
37.5°	1	1	0	0	0	0	0	0	0	0	0
36.25°	1	1	0	0	0	0	0	0	0	0	0
35°	1	1	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	0	0	0	0	0	0	0	0	0
32.5°	1	1	0	0	0	0	0	0	0	0	0
31.25°	1	1	0	0	0	0	0	0	0	0	0
30°	1	1	1	0	0	0	0	0	0	0	0
28.75°	1	1	1	0	0	0	0	0	0	0	0
27.5°	1	1	1	0	0	0	0	0	0	0	0
26.25°	1	1	1	0	0	0	0	0	0	0	0
25°	1	1	1	0	0	0	0	0	0	0	0
23.75°	1	1	1	0	0	0	0	0	0	0	0
22.5°	1	1	1	0	0	0	0	0	0	0	0
21.25°	1	1	1	0	0	0	0	0	0	0	0
20°	1	1	1	0	0	0	0	0	0	0	0
18.75°	1	1	1	0	0	0	0	0	0	0	0
17.5°	1	1	1	0	0	0	0	0	0	0	0
16.25°	1	1	1	0	0	0	0	0	0	0	0
15°	1	1	1	0	0	0	0	0	0	0	0
13.75°	1	1	1	0	0	0	0	0	0	0	0
12.5°	1	1	1	0	0	0	0	0	0	0	0
11.25°	1	1	1	0	0	0	0	0	0	0	0
10°	1	1	1	0	0	0	0	0	0	0	0
8.75°	1	1	1	0	0	0	0	0	0	0	0
7.5°	1	1	1	0	0	0	0	0	0	0	0
6.25°	1	1	1	1	0	0	0	0	0	0	0
5°	1	1	1	1	0	0	0	0	0	0	0
3.75°	1	1	1	1	0	0	0	0	0	0	0
2.5°	1	1	1	1	0	0	0	0	0	0	0
1.25°	1	1	1	1	0	0	0	0	0	0	0
0°	1	1	1	1	0	0	0	0	0	0	0
-1.25°	1	1	1	0	0	0	0	0	0	0	0
-2.5°	1	1	1	0	0	0	0	0	0	0	0
-3.75°	1	1	1	0	0	0	0	0	0	0	0
-5°	1	1	1	0	0	0	0	0	0	0	0
-6.25°	1	1	1	0	0	0	0	0	0	0	0
-7.5°	1	1	1	0	0	0	0	0	0	0	0
-8.75°	1	1	1	0	0	0	0	0	0	0	0
-10°	1	1	1	0	0	0	0	0	0	0	0
-11.25°	1	1	1	0	0	0	0	0	0	0	0
-12.5°	1	1	1	0	0	0	0	0	0	0	0
-13.75°	1	1	1	0	0	0	0	0	0	0	0
-15°	1	1	1	0	0	0	0	0	0	0	0
-16.25°	1	1	1	0	0	0	0	0	0	0	0
-17.5°	1	1	1	0	0	0	0	0	0	0	0
-18.75°	1	1	1	0	0	0	0	0	0	0	0
-20°	1	1	1	0	0	0	0	0	0	0	0
-21.25°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	0	0	0	0	0	0	0	0
-23.75°	1	1	1	0	0	0	0	0	0	0	0
-25°	1	1	1	0	0	0	0	0	0	0	0
-26.25°	1	1	0	0	0	0	0	0	0	0	0
-27.5°	1	1	0	0	0	0	0	0	0	0	0
-28.75°	1	1	0	0	0	0	0	0	0	0	0
-30°	1	1	0	0	0	0	0	0	0	0	0
-31.25°	1	1	0	0	0	0	0	0	0	0	0
-32.5°	1	1	0	0	0	0	0	0	0	0	0
-33.75°	1	1	0	0	0	0	0	0	0	0	0
-35°	1	0	0	0	0	0	0	0	0	0	0
-36.25°	1	0	0	0	0	0	0	0	0	0	0
-37.5°	1	0	0	0	0	0	0	0	0	0	0
-38.75°	1	0	0	0	0	0	0	0	0	0	0
-40°	1	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-37 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)