

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4010-12-CS**

Test Date: 04/05/18

Test Information


Test Method: LM-79-08
Report Number: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-7)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/05/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4010-12-CS
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 10 DEGREE SPOT OPTIC,
REGRESSED HOOD SILVER
Light Source: (1) SORAA 4000K 95 CRI 10°NSP LED
SM16-07-10D-940-03
Ballast/Driver: CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	2H x 2V
Luminaire Lumens:	295.5 lumens	Max Intensity:	5052 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	39.4 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	12.5°H x 12.5°V	Field Angle (10%):	19.2°H x 19.2°V
Beam Lumens:	137.7 lumens	Field Lumens:	204.3 lumens
Beam Efficiency:	46.6%	Field Efficiency:	69.1%
Input Watts (W):	7.5		
Input Voltage (V):	12.0		
Input Current (A _{in}):	0.656		
Voltage Rise (V):	NR		
Power Factor:	0.9482		
Total Harmonic Distortion (THDi):	27.2%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	9 HR		
Ambient Temperature (°C):	24.9		
Test Distance:	25 FT		

REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
60		0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0		
50	0.0	0.0	0.0	0.1	0.2	0.3	0.4	0.4	0.4	0.4	0.3	0.2	0.1	0.0	0.0	
40		0.0	0.0	0.2	0.3	0.4	0.6	0.6	0.6	0.6	0.4	0.3	0.2	0.0		
30	0.0	0.0	0.1	0.2	0.4	0.6	0.8	1.0	1.0	0.8	0.6	0.4	0.2	0.1	0.0	
20		0.0	0.1	0.3	0.5	0.8	1.6	3.8	3.8	1.6	0.8	0.5	0.3	0.1		
10	0.0	0.0	0.1	0.3	0.5	0.9	3.7	53.8	53.8	3.7	0.9	0.5	0.3	0.1	0.0	
0		0.0	0.1	0.3	0.5	0.9	3.7	53.8	53.8	3.7	0.9	0.5	0.3	0.1		
-10	0.0	0.0	0.1	0.3	0.5	0.8	1.6	3.8	3.8	1.6	0.8	0.5	0.3	0.1	0.0	
-20		0.0	0.1	0.2	0.4	0.6	0.8	1.0	1.0	0.8	0.6	0.4	0.2	0.1		
-30	0.0	0.0	0.0	0.2	0.3	0.4	0.6	0.6	0.6	0.6	0.4	0.3	0.2	0.0	0.0	
-40		0.0	0.0	0.1	0.2	0.3	0.4	0.4	0.4	0.4	0.3	0.2	0.1	0.0		
-50	0.0	0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.2	0.2	0.1	0.1	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	

REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS


Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS

Luminous Intensity Plot



Beam:
H Angle: 12.5°
V Angle: 12.5°
Lumens: 137.7
Efficiency: 46.6%

Field:
H Angle: 19.2°
V Angle: 19.2°
Lumens: 204.3
Efficiency: 69.1%

Spill:
Lumens: 91.2
Efficiency: 30.9%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	1
48.75°	0	0	0	0	0	0	0	0	0	0	1
47.5°	0	0	0	0	0	0	0	0	0	1	1
46.25°	0	0	0	0	0	0	0	0	0	1	1
45°	0	0	0	0	0	0	0	0	1	1	1
43.75°	0	0	0	0	0	0	0	0	1	1	1
42.5°	0	0	0	0	0	0	0	1	1	1	1
41.25°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
38.75°	0	0	0	0	0	0	1	1	1	1	1
37.5°	0	0	0	0	0	0	1	1	1	1	1
36.25°	0	0	0	0	0	0	1	1	1	1	1
35°	0	0	0	0	0	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	1	1	1	1	1	1
32.5°	0	0	0	0	0	1	1	1	1	1	1
31.25°	0	0	0	0	0	1	1	1	1	1	1
30°	0	0	0	0	0	1	1	1	1	1	1
28.75°	0	0	0	0	1	1	1	1	1	1	1
27.5°	0	0	0	0	1	1	1	1	1	1	1
26.25°	0	0	0	0	1	1	1	1	1	1	1
25°	0	0	0	0	1	1	1	1	1	1	1
23.75°	0	0	0	0	1	1	1	1	1	1	1
22.5°	0	0	0	0	1	1	1	1	1	1	1
21.25°	0	0	0	1	1	1	1	1	1	1	1
20°	0	0	0	1	1	1	1	1	1	1	1
18.75°	0	0	0	1	1	1	1	1	1	1	1
17.5°	0	0	0	1	1	1	1	1	1	1	1
16.25°	0	0	0	1	1	1	1	1	1	1	1
15°	0	0	0	1	1	1	1	1	1	1	1
13.75°	0	0	0	1	1	1	1	1	1	1	1
12.5°	0	0	0	1	1	1	1	1	1	1	1
11.25°	0	0	0	1	1	1	1	1	1	1	1
10°	0	0	0	1	1	1	1	1	1	1	1
8.75°	0	0	0	1	1	1	1	1	1	1	1
7.5°	0	0	0	1	1	1	1	1	1	1	1
6.25°	0	0	0	1	1	1	1	1	1	1	1
5°	0	0	0	1	1	1	1	1	1	1	1
3.75°	0	0	0	1	1	1	1	1	1	1	1
2.5°	0	0	0	1	1	1	1	1	1	1	1
1.25°	0	0	0	1	1	1	1	1	1	1	1
0°	0	0	1	1	1	1	1	1	1	1	2
-1.25°	0	0	0	1	1	1	1	1	1	1	1
-2.5°	0	0	0	1	1	1	1	1	1	1	1
-3.75°	0	0	0	1	1	1	1	1	1	1	1
-5°	0	0	0	1	1	1	1	1	1	1	1
-6.25°	0	0	0	1	1	1	1	1	1	1	1
-7.5°	0	0	0	1	1	1	1	1	1	1	1
-8.75°	0	0	0	1	1	1	1	1	1	1	1
-10°	0	0	0	1	1	1	1	1	1	1	1
-11.25°	0	0	0	1	1	1	1	1	1	1	1
-12.5°	0	0	0	1	1	1	1	1	1	1	1
-13.75°	0	0	0	1	1	1	1	1	1	1	1
-15°	0	0	0	1	1	1	1	1	1	1	1
-16.25°	0	0	0	1	1	1	1	1	1	1	1
-17.5°	0	0	0	1	1	1	1	1	1	1	1
-18.75°	0	0	0	1	1	1	1	1	1	1	1
-20°	0	0	0	1	1	1	1	1	1	1	1
-21.25°	0	0	0	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	1	1	1	1	1	1	1
-23.75°	0	0	0	0	1	1	1	1	1	1	1
-25°	0	0	0	0	1	1	1	1	1	1	1
-26.25°	0	0	0	0	1	1	1	1	1	1	1
-27.5°	0	0	0	0	1	1	1	1	1	1	1
-28.75°	0	0	0	0	1	1	1	1	1	1	1
-30°	0	0	0	0	0	1	1	1	1	1	1
-31.25°	0	0	0	0	0	1	1	1	1	1	1
-32.5°	0	0	0	0	0	1	1	1	1	1	1
-33.75°	0	0	0	0	0	1	1	1	1	1	1
-35°	0	0	0	0	0	1	1	1	1	1	1
-36.25°	0	0	0	0	0	0	1	1	1	1	1
-37.5°	0	0	0	0	0	0	1	1	1	1	1
-38.75°	0	0	0	0	0	0	1	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-41.25°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	1	1	1	1
-43.75°	0	0	0	0	0	0	0	0	1	1	1
-45°	0	0	0	0	0	0	0	0	1	1	1
-46.25°	0	0	0	0	0	0	0	0	0	1	1
-47.5°	0	0	0	0	0	0	0	0	0	1	1
-48.75°	0	0	0	0	0	0	0	0	0	0	1
-50°	0	0	0	0	0	0	0	0	0	0	1
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	1
62.5°	0	0	0	0	0	0	0	0	1	1	1
61.25°	0	0	0	0	0	0	0	1	1	1	1
60°	0	0	0	0	0	0	1	1	1	1	1
58.75°	0	0	0	0	0	1	1	1	1	1	1
57.5°	0	0	0	0	1	1	1	1	1	1	1
56.25°	0	0	0	1	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	1	1
53.75°	0	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	2
45°	1	1	1	1	1	1	1	1	1	2	2
43.75°	1	1	1	1	1	1	1	1	1	2	2
42.5°	1	1	1	1	1	1	1	1	2	2	2
41.25°	1	1	1	1	1	1	1	2	2	2	3
40°	1	1	1	1	1	1	1	2	2	2	3
38.75°	1	1	1	1	1	1	2	2	2	3	3
37.5°	1	1	1	1	1	1	2	2	3	3	4
36.25°	1	1	1	1	1	2	2	2	3	3	4
35°	1	1	1	1	1	2	2	3	3	4	4



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	2	2	2	3	3	4	5
32.5°	1	1	1	1	2	2	3	3	4	4	5
31.25°	1	1	1	2	2	2	3	3	4	5	6
30°	1	1	1	2	2	3	3	4	4	5	6
28.75°	1	1	1	2	2	3	3	4	5	6	6
27.5°	1	1	2	2	2	3	3	4	5	6	7
26.25°	1	1	2	2	3	3	4	5	5	6	7
25°	1	1	2	2	3	3	4	5	6	7	8
23.75°	1	1	2	2	3	3	4	5	6	7	8
22.5°	1	2	2	2	3	4	5	5	6	7	8
21.25°	1	2	2	3	3	4	5	6	7	8	8
20°	1	2	2	3	3	4	5	6	7	8	9
18.75°	1	2	2	3	3	4	5	6	7	8	9
17.5°	1	2	2	3	4	5	6	6	7	8	9
16.25°	2	2	2	3	4	5	6	7	8	9	9
15°	2	2	3	3	4	5	6	7	8	9	9
13.75°	2	2	3	3	4	5	6	7	8	9	9
12.5°	2	2	3	3	4	5	6	7	8	9	10
11.25°	2	2	3	3	4	5	6	7	8	9	10
10°	2	2	3	4	5	6	7	7	8	9	10
8.75°	2	2	3	4	5	6	7	8	9	9	10
7.5°	2	2	3	4	5	6	7	8	9	9	10
6.25°	2	2	3	4	5	6	7	8	9	9	10
5°	2	2	3	4	5	6	7	8	9	9	10
3.75°	2	2	3	4	5	6	7	8	9	9	10
2.5°	2	2	3	4	5	6	7	8	9	9	10
1.25°	2	2	3	4	5	6	7	8	9	9	10
0°	2	3	3	4	5	6	7	8	9	10	10
-1.25°	2	2	3	4	5	6	7	8	9	9	10
-2.5°	2	2	3	4	5	6	7	8	9	9	10
-3.75°	2	2	3	4	5	6	7	8	9	9	10
-5°	2	2	3	4	5	6	7	8	9	9	10
-6.25°	2	2	3	4	5	6	7	8	9	9	10
-7.5°	2	2	3	4	5	6	7	8	9	9	10
-8.75°	2	2	3	4	5	6	7	8	9	9	10
-10°	2	2	3	4	5	6	7	7	8	9	10
-11.25°	2	2	3	3	4	5	6	7	8	9	10
-12.5°	2	2	3	3	4	5	6	7	8	9	10
-13.75°	2	2	3	3	4	5	6	7	8	9	9
-15°	2	2	3	3	4	5	6	7	8	9	9
-16.25°	2	2	2	3	4	5	6	7	8	9	9
-17.5°	1	2	2	3	4	5	6	6	7	8	9
-18.75°	1	2	2	3	3	4	5	6	7	8	9
-20°	1	2	2	3	3	4	5	6	7	8	9
-21.25°	1	2	2	3	3	4	5	6	7	8	8



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	2	2	2	3	4	5	5	6	7	8
-23.75°	1	1	2	2	3	3	4	5	6	7	8
-25°	1	1	2	2	3	3	4	5	6	7	8
-26.25°	1	1	2	2	3	3	4	5	5	6	7
-27.5°	1	1	2	2	2	3	3	4	5	6	7
-28.75°	1	1	1	2	2	3	3	4	5	6	6
-30°	1	1	1	2	2	3	3	4	4	5	6
-31.25°	1	1	1	2	2	2	3	3	4	5	6
-32.5°	1	1	1	1	2	2	3	3	4	4	5
-33.75°	1	1	1	1	2	2	2	3	3	4	5
-35°	1	1	1	1	1	2	2	3	3	4	4
-36.25°	1	1	1	1	1	2	2	2	3	3	4
-37.5°	1	1	1	1	1	1	2	2	3	3	4
-38.75°	1	1	1	1	1	1	2	2	2	3	3
-40°	1	1	1	1	1	1	1	2	2	2	3
-41.25°	1	1	1	1	1	1	1	2	2	2	3
-42.5°	1	1	1	1	1	1	1	1	2	2	2
-43.75°	1	1	1	1	1	1	1	1	1	2	2
-45°	1	1	1	1	1	1	1	1	1	2	2
-46.25°	1	1	1	1	1	1	1	1	1	1	2
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	0	1	1	1	1	1	1	1	1	1	1
-55°	0	0	1	1	1	1	1	1	1	1	1
-56.25°	0	0	0	1	1	1	1	1	1	1	1
-57.5°	0	0	0	0	1	1	1	1	1	1	1
-58.75°	0	0	0	0	0	1	1	1	1	1	1
-60°	0	0	0	0	0	0	1	1	1	1	1
-61.25°	0	0	0	0	0	0	0	1	1	1	1
-62.5°	0	0	0	0	0	0	0	0	1	1	1
-63.75°	0	0	0	0	0	0	0	0	0	0	1
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	1	1	1
67.5°	0	0	0	0	0	1	1	1	1	1	1
66.25°	0	0	0	1	1	1	1	1	1	1	1
65°	0	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	2
55°	1	1	1	1	1	1	1	1	2	2	2
53.75°	1	1	1	1	1	1	2	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	3	3
51.25°	1	1	1	2	2	2	2	2	3	3	3
50°	1	1	2	2	2	2	3	3	3	4	4
48.75°	1	2	2	2	2	3	3	3	4	4	5
47.5°	2	2	2	2	3	3	3	4	4	5	5
46.25°	2	2	2	3	3	4	4	5	5	6	6
45°	2	2	3	3	4	4	5	5	6	6	7
43.75°	2	3	3	4	4	5	5	6	6	7	8
42.5°	3	3	4	4	5	5	6	7	7	8	8
41.25°	3	3	4	5	5	6	7	7	8	8	9
40°	3	4	5	5	6	7	7	8	8	9	9
38.75°	4	4	5	6	6	7	8	8	9	9	10
37.5°	4	5	6	6	7	8	8	9	9	10	10
36.25°	5	5	6	7	8	8	9	9	10	10	11
35°	5	6	7	7	8	9	9	10	10	11	12



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	6	6	7	8	9	9	9	10	11	12	13
32.5°	6	7	8	8	9	9	10	10	11	12	13
31.25°	6	7	8	9	9	10	10	11	12	13	13
30°	7	8	8	9	9	10	11	12	13	13	14
28.75°	7	8	9	9	10	10	11	13	13	14	14
27.5°	8	8	9	10	10	11	12	13	14	14	15
26.25°	8	9	9	10	10	12	13	13	14	14	15
25°	8	9	10	10	11	12	13	14	14	15	16
23.75°	9	9	10	10	12	13	13	14	14	15	16
22.5°	9	9	10	11	12	13	14	14	15	16	16
21.25°	9	10	10	11	13	13	14	14	15	16	16
20°	9	10	11	12	13	14	14	15	16	16	17
18.75°	9	10	11	12	13	14	14	15	16	16	17
17.5°	10	10	12	13	13	14	15	16	16	17	17
16.25°	10	11	12	13	14	14	15	16	16	17	18
15°	10	11	12	13	14	14	15	16	17	17	18
13.75°	10	11	13	13	14	15	16	16	17	17	19
12.5°	10	12	13	13	14	15	16	16	17	18	19
11.25°	10	12	13	14	14	15	16	16	17	18	20
10°	11	12	13	14	14	15	16	17	17	19	20
8.75°	11	12	13	14	14	15	16	17	18	19	20
7.5°	11	12	13	14	15	16	16	17	18	19	20
6.25°	11	13	13	14	15	16	16	17	18	19	20
5°	11	13	13	14	15	16	16	17	18	20	20
3.75°	11	13	13	14	15	16	16	17	18	20	20
2.5°	11	13	13	14	15	16	16	17	18	20	20
1.25°	11	13	13	14	15	16	16	17	18	20	20
0°	12	13	14	14	15	16	17	17	19	20	21
-1.25°	11	13	13	14	15	16	16	17	18	20	20
-2.5°	11	13	13	14	15	16	16	17	18	20	20
-3.75°	11	13	13	14	15	16	16	17	18	20	20
-5°	11	13	13	14	15	16	16	17	18	20	20
-6.25°	11	13	13	14	15	16	16	17	18	19	20
-7.5°	11	12	13	14	15	16	16	17	18	19	20
-8.75°	11	12	13	14	14	15	16	17	18	19	20
-10°	11	12	13	14	14	15	16	17	17	19	20
-11.25°	10	12	13	14	14	15	16	16	17	18	20
-12.5°	10	12	13	13	14	15	16	16	17	18	19
-13.75°	10	11	13	13	14	15	16	16	17	17	19
-15°	10	11	12	13	14	14	15	16	17	17	18
-16.25°	10	11	12	13	14	14	15	16	16	17	18
-17.5°	10	10	12	13	13	14	15	16	16	17	17
-18.75°	9	10	11	12	13	14	14	15	16	16	17
-20°	9	10	11	12	13	14	14	15	16	16	17
-21.25°	9	10	10	11	13	13	14	14	15	16	16



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	9	9	10	11	12	13	14	14	15	16	16
-23.75°	9	9	10	10	12	13	13	14	14	15	16
-25°	8	9	10	10	11	12	13	14	14	15	16
-26.25°	8	9	9	10	10	12	13	13	14	14	15
-27.5°	8	8	9	10	10	11	12	13	14	14	15
-28.75°	7	8	9	9	10	10	11	13	13	14	14
-30°	7	8	8	9	9	10	11	12	13	13	14
-31.25°	6	7	8	9	9	10	10	11	12	13	13
-32.5°	6	7	8	8	9	9	10	10	11	12	13
-33.75°	6	6	7	8	9	9	9	10	11	12	13
-35°	5	6	7	7	8	9	9	10	10	11	12
-36.25°	5	5	6	7	8	8	9	9	10	10	11
-37.5°	4	5	6	6	7	8	8	9	9	10	10
-38.75°	4	4	5	6	6	7	8	8	9	9	10
-40°	3	4	5	5	6	7	7	8	8	9	9
-41.25°	3	3	4	5	5	6	7	7	8	8	9
-42.5°	3	3	4	4	5	5	6	7	7	8	8
-43.75°	2	3	3	4	4	5	5	6	6	7	8
-45°	2	2	3	3	4	4	5	5	6	6	7
-46.25°	2	2	2	3	3	4	4	5	5	6	6
-47.5°	2	2	2	2	3	3	3	4	4	5	5
-48.75°	1	2	2	2	2	3	3	3	4	4	5
-50°	1	1	2	2	2	2	3	3	3	4	4
-51.25°	1	1	1	2	2	2	2	2	3	3	3
-52.5°	1	1	1	1	1	2	2	2	2	3	3
-53.75°	1	1	1	1	1	1	2	2	2	2	2
-55°	1	1	1	1	1	1	1	1	2	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	2
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	0	1	1	1	1	1	1	1	1	1	1
-66.25°	0	0	0	1	1	1	1	1	1	1	1
-67.5°	0	0	0	0	0	1	1	1	1	1	1
-68.75°	0	0	0	0	0	0	0	0	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	2
60°	1	1	1	1	1	1	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	3	3	3	3
56.25°	2	2	2	2	3	3	3	3	3	3	4
55°	2	2	3	3	3	3	3	4	4	4	5
53.75°	3	3	3	3	4	4	4	5	5	5	5
52.5°	3	3	4	4	4	5	5	5	6	6	6
51.25°	4	4	4	5	5	6	6	6	7	7	7
50°	4	5	5	6	6	6	7	7	8	8	8
48.75°	5	6	6	6	7	7	8	8	8	9	9
47.5°	6	6	7	7	8	8	8	9	9	9	9
46.25°	7	7	8	8	8	9	9	9	10	10	10
45°	7	8	8	9	9	9	10	10	10	10	11
43.75°	8	9	9	9	9	10	10	10	11	12	12
42.5°	9	9	9	10	10	10	11	12	12	13	13
41.25°	9	9	10	10	11	11	12	13	13	13	14
40°	10	10	10	11	12	13	13	13	14	14	14
38.75°	10	11	11	12	13	13	14	14	14	14	15
37.5°	11	12	12	13	13	14	14	14	15	15	16
36.25°	12	13	13	13	14	14	15	15	16	16	16
35°	13	13	13	14	14	15	15	16	16	16	17



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	13	13	14	14	15	15	16	16	17	17	17
32.5°	13	14	14	15	16	16	16	17	17	18	18
31.25°	14	14	15	16	16	16	17	17	18	19	20
30°	14	15	16	16	16	17	17	18	19	20	20
28.75°	15	15	16	16	17	17	18	19	20	20	21
27.5°	15	16	16	17	17	18	19	20	20	21	21
26.25°	16	16	17	17	18	19	20	20	21	21	22
25°	16	17	17	18	19	20	20	21	21	22	22
23.75°	16	17	18	19	20	20	21	21	22	23	23
22.5°	17	17	18	20	20	21	21	22	22	23	24
21.25°	17	18	19	20	21	21	22	22	23	24	25
20°	17	19	20	20	21	21	22	23	24	24	25
18.75°	18	19	20	21	21	22	23	24	24	25	27
17.5°	19	20	20	21	22	22	23	24	25	26	28
16.25°	19	20	21	21	22	23	24	25	26	27	29
15°	20	20	21	22	22	23	24	25	27	28	30
13.75°	20	21	21	22	23	24	25	26	28	29	31
12.5°	20	21	21	22	23	24	25	27	29	30	32
11.25°	20	21	22	23	24	24	26	28	29	31	33
10°	21	21	22	23	24	25	26	28	30	32	34
8.75°	21	21	22	23	24	25	27	29	31	33	36
7.5°	21	21	22	23	24	26	28	29	31	33	37
6.25°	21	22	23	24	25	26	28	30	32	34	38
5°	21	22	23	24	25	26	28	30	32	35	39
3.75°	21	22	23	24	25	27	29	31	33	36	39
2.5°	21	22	23	24	25	27	29	31	33	36	40
1.25°	21	22	23	24	25	27	29	31	33	36	40
0°	21	22	23	24	25	27	29	31	33	37	40
-1.25°	21	22	23	24	25	27	29	31	33	36	40
-2.5°	21	22	23	24	25	27	29	31	33	36	40
-3.75°	21	22	23	24	25	27	29	31	33	36	39
-5°	21	22	23	24	25	26	28	30	32	35	39
-6.25°	21	22	23	24	25	26	28	30	32	34	38
-7.5°	21	21	22	23	24	26	28	29	31	33	37
-8.75°	21	21	22	23	24	25	27	29	31	33	36
-10°	21	21	22	23	24	25	26	28	30	32	34
-11.25°	20	21	22	23	24	24	26	28	29	31	33
-12.5°	20	21	21	22	23	24	25	27	29	30	32
-13.75°	20	21	21	22	23	24	25	26	28	29	31
-15°	20	20	21	22	22	23	24	25	27	28	30
-16.25°	19	20	21	21	22	23	24	25	26	27	29
-17.5°	19	20	20	21	22	22	23	24	25	26	28
-18.75°	18	19	20	21	21	22	23	24	24	25	27
-20°	17	19	20	20	21	21	22	23	24	24	25
-21.25°	17	18	19	20	21	21	22	22	23	24	25



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	17	17	18	20	20	21	21	22	22	23	24
-23.75°	16	17	18	19	20	20	21	21	22	23	23
-25°	16	17	17	18	19	20	20	21	21	22	22
-26.25°	16	16	17	17	18	19	20	20	21	21	22
-27.5°	15	16	16	17	17	18	19	20	20	21	21
-28.75°	15	15	16	16	17	17	18	19	20	20	21
-30°	14	15	16	16	16	17	17	18	19	20	20
-31.25°	14	14	15	16	16	16	17	17	18	19	20
-32.5°	13	14	14	15	16	16	16	17	17	18	18
-33.75°	13	13	14	14	15	15	16	16	17	17	17
-35°	13	13	13	14	14	15	15	16	16	16	17
-36.25°	12	13	13	13	14	14	15	15	16	16	16
-37.5°	11	12	12	13	13	14	14	14	15	15	16
-38.75°	10	11	11	12	13	13	14	14	14	14	15
-40°	10	10	10	11	12	13	13	13	14	14	14
-41.25°	9	9	10	10	11	11	12	13	13	13	14
-42.5°	9	9	9	10	10	10	11	12	12	13	13
-43.75°	8	9	9	9	9	10	10	10	11	12	12
-45°	7	8	8	9	9	9	10	10	10	10	11
-46.25°	7	7	8	8	8	9	9	9	10	10	10
-47.5°	6	6	7	7	8	8	8	9	9	9	9
-48.75°	5	6	6	6	7	7	8	8	8	9	9
-50°	4	5	5	6	6	6	7	7	8	8	8
-51.25°	4	4	4	5	5	6	6	6	7	7	7
-52.5°	3	3	4	4	4	5	5	5	6	6	6
-53.75°	3	3	3	3	4	4	4	5	5	5	5
-55°	2	2	3	3	3	3	3	4	4	4	5
-56.25°	2	2	2	2	3	3	3	3	3	3	4
-57.5°	1	2	2	2	2	2	2	3	3	3	3
-58.75°	1	1	1	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	1	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	4	4
57.5°	3	3	3	4	4	4	4	4	4	5	5
56.25°	4	4	4	5	5	5	5	5	5	6	6
55°	5	5	5	6	6	6	6	6	6	7	7
53.75°	6	6	6	6	7	7	7	7	7	7	8
52.5°	7	7	7	7	8	8	8	8	8	8	9
51.25°	8	8	8	8	9	9	9	9	9	9	9
50°	8	9	9	9	9	9	9	10	10	10	10
48.75°	9	9	9	10	10	10	10	10	10	11	11
47.5°	10	10	10	10	11	11	11	12	12	12	12
46.25°	10	11	11	12	12	12	13	13	13	13	13
45°	11	12	12	13	13	13	13	13	14	14	14
43.75°	13	13	13	13	14	14	14	14	14	14	14
42.5°	13	14	14	14	14	14	15	15	15	15	15
41.25°	14	14	14	15	15	15	16	16	16	16	16
40°	14	15	15	16	16	16	16	16	16	17	17
38.75°	15	16	16	16	16	17	17	17	17	17	18
37.5°	16	16	16	17	17	17	17	18	18	19	19
36.25°	16	17	17	17	18	18	19	19	20	20	20
35°	17	17	18	19	19	20	20	20	20	21	21



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	18	19	19	20	20	20	21	21	21	21	21
32.5°	19	20	20	20	21	21	21	21	22	22	22
31.25°	20	20	21	21	21	22	22	22	23	23	23
30°	21	21	21	22	22	22	23	23	24	24	24
28.75°	21	21	22	22	23	23	24	24	24	25	25
27.5°	22	22	23	23	24	24	25	25	26	26	27
26.25°	22	23	24	24	25	25	26	27	28	28	29
25°	23	24	24	25	26	27	28	29	29	30	31
23.75°	24	24	25	26	27	28	29	30	31	32	33
22.5°	25	25	27	28	29	30	31	32	33	34	36
21.25°	25	27	28	29	31	32	33	34	36	38	39
20°	27	28	30	31	32	34	35	37	39	41	44
18.75°	28	30	31	32	34	36	38	40	44	47	50
17.5°	29	31	32	34	37	39	42	46	49	53	59
16.25°	31	32	34	37	39	43	47	51	57	66	73
15°	32	34	36	39	43	47	52	60	70	79	88
13.75°	33	35	38	42	47	52	61	72	82	93	103
12.5°	34	37	40	46	51	60	72	84	96	108	119
11.25°	36	39	44	49	57	70	82	96	109	122	145
10°	38	41	47	53	66	79	93	108	122	148	172
8.75°	39	44	50	59	73	88	103	119	145	172	206
7.5°	40	46	52	66	80	96	113	135	165	196	274
6.25°	42	48	56	72	87	104	121	152	184	252	335
5°	44	50	61	76	93	110	133	167	210	300	389
3.75°	45	51	64	80	97	115	144	178	246	340	513
2.5°	46	52	67	83	101	119	152	187	272	370	615
1.25°	46	53	68	84	103	121	156	192	289	388	716
0°	47	53	69	85	104	122	158	194	294	394	759
-1.25°	46	53	68	84	103	121	156	192	289	388	716
-2.5°	46	52	67	83	101	119	152	187	272	370	615
-3.75°	45	51	64	80	97	115	144	178	246	340	513
-5°	44	50	61	76	93	110	133	167	210	300	389
-6.25°	42	48	56	72	87	104	121	152	184	252	335
-7.5°	40	46	52	66	80	96	113	135	165	196	274
-8.75°	39	44	50	59	73	88	103	119	145	172	206
-10°	38	41	47	53	66	79	93	108	122	148	172
-11.25°	36	39	44	49	57	70	82	96	109	122	145
-12.5°	34	37	40	46	51	60	72	84	96	108	119
-13.75°	33	35	38	42	47	52	61	72	82	93	103
-15°	32	34	36	39	43	47	52	60	70	79	88
-16.25°	31	32	34	37	39	43	47	51	57	66	73
-17.5°	29	31	32	34	37	39	42	46	49	53	59
-18.75°	28	30	31	32	34	36	38	40	44	47	50
-20°	27	28	30	31	32	34	35	37	39	41	44
-21.25°	25	27	28	29	31	32	33	34	36	38	39



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	25	25	27	28	29	30	31	32	33	34	36
-23.75°	24	24	25	26	27	28	29	30	31	32	33
-25°	23	24	24	25	26	27	28	29	29	30	31
-26.25°	22	23	24	24	25	25	26	27	28	28	29
-27.5°	22	22	23	23	24	24	25	25	26	26	27
-28.75°	21	21	22	22	23	23	24	24	24	25	25
-30°	21	21	21	22	22	22	23	23	24	24	24
-31.25°	20	20	21	21	21	22	22	22	23	23	23
-32.5°	19	20	20	20	21	21	21	21	22	22	22
-33.75°	18	19	19	20	20	20	21	21	21	21	21
-35°	17	17	18	19	19	20	20	20	20	21	21
-36.25°	16	17	17	17	18	18	19	19	20	20	20
-37.5°	16	16	16	17	17	17	17	18	18	19	19
-38.75°	15	16	16	16	16	17	17	17	17	17	18
-40°	14	15	15	16	16	16	16	16	16	17	17
-41.25°	14	14	14	15	15	15	16	16	16	16	16
-42.5°	13	14	14	14	14	14	15	15	15	15	15
-43.75°	13	13	13	13	14	14	14	14	14	14	14
-45°	11	12	12	13	13	13	13	13	14	14	14
-46.25°	10	11	11	12	12	12	13	13	13	13	13
-47.5°	10	10	10	10	11	11	11	12	12	12	12
-48.75°	9	9	9	10	10	10	10	10	10	11	11
-50°	8	9	9	9	9	9	9	10	10	10	10
-51.25°	8	8	8	8	9	9	9	9	9	9	9
-52.5°	7	7	7	7	8	8	8	8	8	8	9
-53.75°	6	6	6	6	7	7	7	7	7	7	8
-55°	5	5	5	6	6	6	6	6	6	7	7
-56.25°	4	4	4	5	5	5	5	5	5	6	6
-57.5°	3	3	3	4	4	4	4	4	4	5	5
-58.75°	3	3	3	3	3	3	3	3	3	4	4
-60°	2	2	2	2	2	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	1	0	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	2	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	3	2	2	2	2
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	4	4	4	4	4	4	4	4	4	4	4
57.5°	5	5	5	5	5	5	5	5	5	5	5
56.25°	6	6	6	6	6	6	6	6	6	6	6
55°	7	7	7	7	7	7	7	7	7	7	7
53.75°	8	8	8	8	8	8	8	8	8	8	8
52.5°	9	9	9	9	9	9	9	9	9	9	9
51.25°	9	9	9	9	9	9	10	9	9	9	9
50°	10	10	10	10	10	10	10	10	10	10	10
48.75°	11	11	11	11	11	11	12	11	11	11	11
47.5°	12	13	13	13	13	13	13	13	13	13	13
46.25°	13	13	13	13	13	13	14	13	13	13	13
45°	14	14	14	14	14	14	14	14	14	14	14
43.75°	15	15	15	15	15	15	15	15	15	15	15
42.5°	16	16	16	16	16	16	16	16	16	16	16
41.25°	16	16	16	16	16	16	17	16	16	16	16
40°	17	17	17	17	17	17	17	17	17	17	17
38.75°	18	18	18	18	18	18	19	18	18	18	18
37.5°	19	19	20	20	20	20	20	20	20	20	20
36.25°	20	20	20	20	20	20	21	20	20	20	20
35°	21	21	21	21	21	21	21	21	21	21	21



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	21	22	22	22	22	22	22	22	22	22	22
32.5°	22	23	23	23	23	23	23	23	23	23	23
31.25°	23	24	24	24	24	24	24	24	24	24	24
30°	24	25	25	25	25	25	25	25	25	25	25
28.75°	26	26	26	27	27	27	27	27	27	27	26
27.5°	28	28	28	29	29	29	29	29	29	29	28
26.25°	29	30	30	31	31	31	31	31	31	31	30
25°	31	32	32	33	33	33	33	33	33	33	32
23.75°	33	34	35	36	36	36	37	36	36	36	35
22.5°	37	38	39	39	40	40	40	40	40	39	39
21.25°	40	42	44	45	46	46	47	46	46	45	44
20°	46	48	50	51	52	53	53	53	52	51	50
18.75°	52	56	61	64	67	68	69	68	67	64	61
17.5°	66	72	76	80	83	84	85	84	83	80	76
16.25°	80	87	93	97	101	103	104	103	101	97	93
15°	96	104	110	115	119	121	122	121	119	115	110
13.75°	113	121	133	144	152	156	158	156	152	144	133
12.5°	135	152	167	178	187	192	194	192	187	178	167
11.25°	165	184	210	246	272	289	294	289	272	246	210
10°	196	252	300	340	370	388	394	388	370	340	300
8.75°	274	335	389	513	615	716	759	716	615	513	389
7.5°	347	455	638	935	1190	1416	1493	1416	1190	935	638
6.25°	455	720	1119	1655	2101	2406	2512	2406	2101	1655	1119
5°	638	1119	1819	2514	3036	3364	3480	3364	3036	2514	1819
3.75°	935	1655	2514	3253	3781	4111	4202	4111	3781	3253	2514
2.5°	1190	2101	3036	3781	4297	4595	4680	4595	4297	3781	3036
1.25°	1416	2406	3364	4111	4595	4861	4945	4861	4595	4111	3364
0°	1493	2512	3480	4202	4680	4945	5052	4945	4680	4202	3480
-1.25°	1416	2406	3364	4111	4595	4861	4945	4861	4595	4111	3364
-2.5°	1190	2101	3036	3781	4297	4595	4680	4595	4297	3781	3036
-3.75°	935	1655	2514	3253	3781	4111	4202	4111	3781	3253	2514
-5°	638	1119	1819	2514	3036	3364	3480	3364	3036	2514	1819
-6.25°	455	720	1119	1655	2101	2406	2512	2406	2101	1655	1119
-7.5°	347	455	638	935	1190	1416	1493	1416	1190	935	638
-8.75°	274	335	389	513	615	716	759	716	615	513	389
-10°	196	252	300	340	370	388	394	388	370	340	300
-11.25°	165	184	210	246	272	289	294	289	272	246	210
-12.5°	135	152	167	178	187	192	194	192	187	178	167
-13.75°	113	121	133	144	152	156	158	156	152	144	133
-15°	96	104	110	115	119	121	122	121	119	115	110
-16.25°	80	87	93	97	101	103	104	103	101	97	93
-17.5°	66	72	76	80	83	84	85	84	83	80	76
-18.75°	52	56	61	64	67	68	69	68	67	64	61
-20°	46	48	50	51	52	53	53	53	52	51	50
-21.25°	40	42	44	45	46	46	47	46	46	45	44



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	37	38	39	39	40	40	40	40	40	39	39
-23.75°	33	34	35	36	36	36	37	36	36	36	35
-25°	31	32	32	33	33	33	33	33	33	33	32
-26.25°	29	30	30	31	31	31	31	31	31	31	30
-27.5°	28	28	28	29	29	29	29	29	29	29	28
-28.75°	26	26	26	27	27	27	27	27	27	27	26
-30°	24	25	25	25	25	25	25	25	25	25	25
-31.25°	23	24	24	24	24	24	24	24	24	24	24
-32.5°	22	23	23	23	23	23	23	23	23	23	23
-33.75°	21	22	22	22	22	22	22	22	22	22	22
-35°	21	21	21	21	21	21	21	21	21	21	21
-36.25°	20	20	20	20	20	20	21	20	20	20	20
-37.5°	19	19	20	20	20	20	20	20	20	20	20
-38.75°	18	18	18	18	18	18	19	18	18	18	18
-40°	17	17	17	17	17	17	17	17	17	17	17
-41.25°	16	16	16	16	16	16	17	16	16	16	16
-42.5°	16	16	16	16	16	16	16	16	16	16	16
-43.75°	15	15	15	15	15	15	15	15	15	15	15
-45°	14	14	14	14	14	14	14	14	14	14	14
-46.25°	13	13	13	13	13	13	14	13	13	13	13
-47.5°	12	13	13	13	13	13	13	13	13	13	13
-48.75°	11	11	11	11	11	11	12	11	11	11	11
-50°	10	10	10	10	10	10	10	10	10	10	10
-51.25°	9	9	9	9	9	9	10	9	9	9	9
-52.5°	9	9	9	9	9	9	9	9	9	9	9
-53.75°	8	8	8	8	8	8	8	8	8	8	8
-55°	7	7	7	7	7	7	7	7	7	7	7
-56.25°	6	6	6	6	6	6	6	6	6	6	6
-57.5°	5	5	5	5	5	5	5	5	5	5	5
-58.75°	4	4	4	4	4	4	4	4	4	4	4
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	2	2	2	2	2	2	3	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	2	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	0	1	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	3	2	2	2
58.75°	4	4	4	4	3	3	3	3	3	3	3
57.5°	5	5	5	5	4	4	4	4	4	4	3
56.25°	6	6	6	6	5	5	5	5	5	5	4
55°	7	7	7	7	6	6	6	6	6	6	5
53.75°	8	8	8	7	7	7	7	7	7	6	6
52.5°	9	9	9	8	8	8	8	8	8	7	7
51.25°	9	9	9	9	9	9	9	9	9	8	8
50°	10	10	10	10	10	10	9	9	9	9	9
48.75°	11	11	11	11	10	10	10	10	10	10	9
47.5°	13	12	12	12	12	12	11	11	11	10	10
46.25°	13	13	13	13	13	13	13	12	12	12	11
45°	14	14	14	14	14	13	13	13	13	13	12
43.75°	15	15	14	14	14	14	14	14	14	13	13
42.5°	16	16	15	15	15	15	15	14	14	14	14
41.25°	16	16	16	16	16	16	16	15	15	15	14
40°	17	17	17	17	16	16	16	16	16	16	15
38.75°	18	18	18	17	17	17	17	17	16	16	16
37.5°	19	19	19	19	18	18	17	17	17	17	16
36.25°	20	20	20	20	20	19	19	18	18	17	17
35°	21	21	21	21	20	20	20	20	19	19	18



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	22	21	21	21	21	21	21	20	20	20	19
32.5°	23	22	22	22	22	21	21	21	21	20	20
31.25°	24	23	23	23	23	22	22	22	21	21	21
30°	25	24	24	24	24	23	23	22	22	22	21
28.75°	26	26	25	25	24	24	24	23	23	22	22
27.5°	28	28	27	26	26	25	25	24	24	23	23
26.25°	30	29	29	28	28	27	26	25	25	24	24
25°	32	31	31	30	29	29	28	27	26	25	24
23.75°	34	33	33	32	31	30	29	28	27	26	25
22.5°	38	37	36	34	33	32	31	30	29	28	27
21.25°	42	40	39	38	36	34	33	32	31	29	28
20°	48	46	44	41	39	37	35	34	32	31	30
18.75°	56	52	50	47	44	40	38	36	34	32	31
17.5°	72	66	59	53	49	46	42	39	37	34	32
16.25°	87	80	73	66	57	51	47	43	39	37	34
15°	104	96	88	79	70	60	52	47	43	39	36
13.75°	121	113	103	93	82	72	61	52	47	42	38
12.5°	152	135	119	108	96	84	72	60	51	46	40
11.25°	184	165	145	122	109	96	82	70	57	49	44
10°	252	196	172	148	122	108	93	79	66	53	47
8.75°	335	274	206	172	145	119	103	88	73	59	50
7.5°	455	347	274	196	165	135	113	96	80	66	52
6.25°	720	455	335	252	184	152	121	104	87	72	56
5°	1119	638	389	300	210	167	133	110	93	76	61
3.75°	1655	935	513	340	246	178	144	115	97	80	64
2.5°	2101	1190	615	370	272	187	152	119	101	83	67
1.25°	2406	1416	716	388	289	192	156	121	103	84	68
0°	2512	1493	759	394	294	194	158	122	104	85	69
-1.25°	2406	1416	716	388	289	192	156	121	103	84	68
-2.5°	2101	1190	615	370	272	187	152	119	101	83	67
-3.75°	1655	935	513	340	246	178	144	115	97	80	64
-5°	1119	638	389	300	210	167	133	110	93	76	61
-6.25°	720	455	335	252	184	152	121	104	87	72	56
-7.5°	455	347	274	196	165	135	113	96	80	66	52
-8.75°	335	274	206	172	145	119	103	88	73	59	50
-10°	252	196	172	148	122	108	93	79	66	53	47
-11.25°	184	165	145	122	109	96	82	70	57	49	44
-12.5°	152	135	119	108	96	84	72	60	51	46	40
-13.75°	121	113	103	93	82	72	61	52	47	42	38
-15°	104	96	88	79	70	60	52	47	43	39	36
-16.25°	87	80	73	66	57	51	47	43	39	37	34
-17.5°	72	66	59	53	49	46	42	39	37	34	32
-18.75°	56	52	50	47	44	40	38	36	34	32	31
-20°	48	46	44	41	39	37	35	34	32	31	30
-21.25°	42	40	39	38	36	34	33	32	31	29	28



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	38	37	36	34	33	32	31	30	29	28	27
-23.75°	34	33	33	32	31	30	29	28	27	26	25
-25°	32	31	31	30	29	29	28	27	26	25	24
-26.25°	30	29	29	28	28	27	26	25	25	24	24
-27.5°	28	28	27	26	26	25	25	24	24	23	23
-28.75°	26	26	25	25	24	24	24	23	23	22	22
-30°	25	24	24	24	24	23	23	22	22	22	21
-31.25°	24	23	23	23	23	22	22	22	21	21	21
-32.5°	23	22	22	22	22	21	21	21	21	20	20
-33.75°	22	21	21	21	21	21	21	20	20	20	19
-35°	21	21	21	21	20	20	20	20	19	19	18
-36.25°	20	20	20	20	20	19	19	18	18	17	17
-37.5°	19	19	19	19	18	18	17	17	17	17	16
-38.75°	18	18	18	17	17	17	17	17	16	16	16
-40°	17	17	17	17	16	16	16	16	16	16	15
-41.25°	16	16	16	16	16	16	16	15	15	15	14
-42.5°	16	16	15	15	15	15	15	14	14	14	14
-43.75°	15	15	14	14	14	14	14	14	14	13	13
-45°	14	14	14	14	14	13	13	13	13	13	12
-46.25°	13	13	13	13	13	13	13	12	12	12	11
-47.5°	13	12	12	12	12	12	11	11	11	10	10
-48.75°	11	11	11	11	10	10	10	10	10	10	9
-50°	10	10	10	10	10	10	9	9	9	9	9
-51.25°	9	9	9	9	9	9	9	9	9	8	8
-52.5°	9	9	9	8	8	8	8	8	8	7	7
-53.75°	8	8	8	7	7	7	7	7	7	6	6
-55°	7	7	7	7	6	6	6	6	6	6	5
-56.25°	6	6	6	6	5	5	5	5	5	5	4
-57.5°	5	5	5	5	4	4	4	4	4	4	3
-58.75°	4	4	4	4	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	0	0	0	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	1	0	0	0
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	1	1	1	1
58.75°	3	3	2	2	2	2	2	2	2	2	1
57.5°	3	3	3	3	3	3	2	2	2	2	2
56.25°	4	4	4	3	3	3	3	3	3	2	2
55°	5	5	5	4	4	4	3	3	3	3	3
53.75°	6	6	5	5	5	5	4	4	4	3	3
52.5°	7	7	6	6	6	5	5	5	4	4	4
51.25°	8	8	7	7	7	6	6	6	5	5	4
50°	9	8	8	8	8	7	7	6	6	6	5
48.75°	9	9	9	9	8	8	8	7	7	6	6
47.5°	10	10	9	9	9	9	8	8	8	7	7
46.25°	11	10	10	10	10	9	9	9	8	8	8
45°	12	11	11	10	10	10	10	9	9	9	8
43.75°	13	13	12	12	11	10	10	10	9	9	9
42.5°	14	13	13	13	12	12	11	10	10	10	9
41.25°	14	14	14	13	13	13	12	11	11	10	10
40°	15	14	14	14	14	13	13	13	12	11	10
38.75°	16	15	15	14	14	14	14	13	13	12	11
37.5°	16	16	16	15	15	14	14	14	13	13	12
36.25°	17	16	16	16	16	15	15	14	14	13	13
35°	17	17	17	16	16	16	15	15	14	14	13



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	19	18	17	17	17	16	16	15	15	14	14
32.5°	20	19	18	18	17	17	16	16	16	15	14
31.25°	20	20	20	19	18	17	17	16	16	16	15
30°	21	21	20	20	19	18	17	17	16	16	16
28.75°	21	21	21	20	20	19	18	17	17	16	16
27.5°	22	22	21	21	20	20	19	18	17	17	16
26.25°	23	22	22	21	21	20	20	19	18	17	17
25°	24	23	22	22	21	21	20	20	19	18	17
23.75°	24	24	23	23	22	21	21	20	20	19	18
22.5°	25	25	24	23	22	22	21	21	20	20	18
21.25°	27	25	25	24	23	22	22	21	21	20	19
20°	28	27	25	24	24	23	22	21	21	20	20
18.75°	30	28	27	25	24	24	23	22	21	21	20
17.5°	31	29	28	26	25	24	23	22	22	21	20
16.25°	32	31	29	27	26	25	24	23	22	21	21
15°	34	32	30	28	27	25	24	23	22	22	21
13.75°	35	33	31	29	28	26	25	24	23	22	21
12.5°	37	34	32	30	29	27	25	24	23	22	21
11.25°	39	36	33	31	29	28	26	24	24	23	22
10°	41	38	34	32	30	28	26	25	24	23	22
8.75°	44	39	36	33	31	29	27	25	24	23	22
7.5°	46	40	37	33	31	29	28	26	24	23	22
6.25°	48	42	38	34	32	30	28	26	25	24	23
5°	50	44	39	35	32	30	28	26	25	24	23
3.75°	51	45	39	36	33	31	29	27	25	24	23
2.5°	52	46	40	36	33	31	29	27	25	24	23
1.25°	53	46	40	36	33	31	29	27	25	24	23
0°	53	47	40	37	33	31	29	27	25	24	23
-1.25°	53	46	40	36	33	31	29	27	25	24	23
-2.5°	52	46	40	36	33	31	29	27	25	24	23
-3.75°	51	45	39	36	33	31	29	27	25	24	23
-5°	50	44	39	35	32	30	28	26	25	24	23
-6.25°	48	42	38	34	32	30	28	26	25	24	23
-7.5°	46	40	37	33	31	29	28	26	24	23	22
-8.75°	44	39	36	33	31	29	27	25	24	23	22
-10°	41	38	34	32	30	28	26	25	24	23	22
-11.25°	39	36	33	31	29	28	26	24	24	23	22
-12.5°	37	34	32	30	29	27	25	24	23	22	21
-13.75°	35	33	31	29	28	26	25	24	23	22	21
-15°	34	32	30	28	27	25	24	23	22	22	21
-16.25°	32	31	29	27	26	25	24	23	22	21	21
-17.5°	31	29	28	26	25	24	23	22	22	21	20
-18.75°	30	28	27	25	24	24	23	22	21	21	20
-20°	28	27	25	24	24	23	22	21	21	20	20
-21.25°	27	25	25	24	23	22	22	21	21	20	19



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	25	25	24	23	22	22	21	21	20	20	18
-23.75°	24	24	23	23	22	21	21	20	20	19	18
-25°	24	23	22	22	21	21	20	20	19	18	17
-26.25°	23	22	22	21	21	20	20	19	18	17	17
-27.5°	22	22	21	21	20	20	19	18	17	17	16
-28.75°	21	21	21	20	20	19	18	17	17	16	16
-30°	21	21	20	20	19	18	17	17	16	16	16
-31.25°	20	20	20	19	18	17	17	16	16	16	15
-32.5°	20	19	18	18	17	17	16	16	16	15	14
-33.75°	19	18	17	17	17	16	16	15	15	14	14
-35°	17	17	17	16	16	16	15	15	14	14	13
-36.25°	17	16	16	16	16	15	15	14	14	13	13
-37.5°	16	16	16	15	15	14	14	14	13	13	12
-38.75°	16	15	15	14	14	14	14	13	13	12	11
-40°	15	14	14	14	14	13	13	13	12	11	10
-41.25°	14	14	14	13	13	13	12	11	11	10	10
-42.5°	14	13	13	13	12	12	11	10	10	10	9
-43.75°	13	13	12	12	11	10	10	10	9	9	9
-45°	12	11	11	10	10	10	10	9	9	9	8
-46.25°	11	10	10	10	10	9	9	9	8	8	8
-47.5°	10	10	9	9	9	9	8	8	8	7	7
-48.75°	9	9	9	9	8	8	8	7	7	6	6
-50°	9	8	8	8	8	7	7	6	6	6	5
-51.25°	8	8	7	7	7	6	6	6	5	5	4
-52.5°	7	7	6	6	6	5	5	5	4	4	4
-53.75°	6	6	5	5	5	5	4	4	4	3	3
-55°	5	5	5	4	4	4	3	3	3	3	3
-56.25°	4	4	4	3	3	3	3	3	3	2	2
-57.5°	3	3	3	3	3	3	2	2	2	2	2
-58.75°	3	3	2	2	2	2	2	2	2	2	1
-60°	2	2	2	2	2	2	2	1	1	1	1
-61.25°	2	2	2	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	0	0	0
-72.5°	1	1	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	1	1	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	0	0	0	0	0	0
67.5°	1	1	1	1	1	1	1	1	0	0	0
66.25°	1	1	1	1	1	1	1	1	1	1	0
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	2	1	1	1	1	1	1	1	1
55°	2	2	2	2	2	1	1	1	1	1	1
53.75°	3	3	2	2	2	2	2	1	1	1	1
52.5°	3	3	3	3	2	2	2	2	1	1	1
51.25°	4	4	3	3	3	2	2	2	2	2	1
50°	5	4	4	4	3	3	3	2	2	2	2
48.75°	6	5	5	4	4	3	3	3	2	2	2
47.5°	6	6	5	5	4	4	3	3	3	2	2
46.25°	7	7	6	6	5	5	4	4	3	3	2
45°	8	7	7	6	6	5	5	4	4	3	3
43.75°	9	8	8	7	6	6	5	5	4	4	3
42.5°	9	9	8	8	7	7	6	5	5	4	4
41.25°	9	9	9	8	8	7	7	6	5	5	4
40°	10	10	9	9	8	8	7	7	6	5	5
38.75°	11	10	10	9	9	8	8	7	6	6	5
37.5°	12	11	10	10	9	9	8	8	7	6	6
36.25°	13	12	11	10	10	9	9	8	8	7	6
35°	13	13	12	11	10	10	9	9	8	7	7



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	13	13	13	12	11	10	9	9	9	8	7
32.5°	14	13	13	12	11	10	10	9	9	8	8
31.25°	14	14	13	13	12	11	10	10	9	9	8
30°	15	14	14	13	13	12	11	10	9	9	8
28.75°	15	15	14	14	13	13	11	10	10	9	9
27.5°	16	15	15	14	14	13	12	11	10	10	9
26.25°	16	16	15	14	14	13	13	12	10	10	9
25°	17	16	16	15	14	14	13	12	11	10	10
23.75°	17	16	16	15	14	14	13	13	12	10	10
22.5°	17	17	16	16	15	14	14	13	12	11	10
21.25°	18	17	16	16	15	14	14	13	13	11	10
20°	19	17	17	16	16	15	14	14	13	12	11
18.75°	19	18	17	16	16	15	14	14	13	12	11
17.5°	20	19	17	17	16	16	15	14	13	13	12
16.25°	20	19	18	17	16	16	15	14	14	13	12
15°	20	20	18	17	17	16	15	14	14	13	12
13.75°	21	20	19	17	17	16	16	15	14	13	13
12.5°	21	20	19	18	17	16	16	15	14	13	13
11.25°	21	20	20	18	17	16	16	15	14	14	13
10°	21	21	20	19	17	17	16	15	14	14	13
8.75°	21	21	20	19	18	17	16	15	14	14	13
7.5°	21	21	20	19	18	17	16	16	15	14	13
6.25°	22	21	20	19	18	17	16	16	15	14	13
5°	22	21	20	20	18	17	16	16	15	14	13
3.75°	22	21	20	20	18	17	16	16	15	14	13
2.5°	22	21	20	20	18	17	16	16	15	14	13
1.25°	22	21	20	20	18	17	16	16	15	14	13
0°	22	21	21	20	19	17	17	16	15	14	14
-1.25°	22	21	20	20	18	17	16	16	15	14	13
-2.5°	22	21	20	20	18	17	16	16	15	14	13
-3.75°	22	21	20	20	18	17	16	16	15	14	13
-5°	22	21	20	20	18	17	16	16	15	14	13
-6.25°	22	21	20	19	18	17	16	16	15	14	13
-7.5°	21	21	20	19	18	17	16	16	15	14	13
-8.75°	21	21	20	19	18	17	16	15	14	14	13
-10°	21	21	20	19	17	17	16	15	14	14	13
-11.25°	21	20	20	18	17	16	16	15	14	14	13
-12.5°	21	20	19	18	17	16	16	15	14	13	13
-13.75°	21	20	19	17	17	16	16	15	14	13	13
-15°	20	20	18	17	17	16	15	14	14	13	12
-16.25°	20	19	18	17	16	16	15	14	14	13	12
-17.5°	20	19	17	17	16	16	15	14	13	13	12
-18.75°	19	18	17	16	16	15	14	14	13	12	11
-20°	19	17	17	16	16	15	14	14	13	12	11
-21.25°	18	17	16	16	15	14	14	13	13	11	10



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	17	17	16	16	15	14	14	13	12	11	10
-23.75°	17	16	16	15	14	14	13	13	12	10	10
-25°	17	16	16	15	14	14	13	12	11	10	10
-26.25°	16	16	15	14	14	13	13	12	10	10	9
-27.5°	16	15	15	14	14	13	12	11	10	10	9
-28.75°	15	15	14	14	13	13	11	10	10	9	9
-30°	15	14	14	13	13	12	11	10	9	9	8
-31.25°	14	14	13	13	12	11	10	10	9	9	8
-32.5°	14	13	13	12	11	10	10	9	9	8	8
-33.75°	13	13	13	12	11	10	9	9	9	8	7
-35°	13	13	12	11	10	10	9	9	8	7	7
-36.25°	13	12	11	10	10	9	9	8	8	7	6
-37.5°	12	11	10	10	9	9	8	8	7	6	6
-38.75°	11	10	10	9	9	8	8	7	6	6	5
-40°	10	10	9	9	8	8	7	7	6	5	5
-41.25°	9	9	9	8	8	7	7	6	5	5	4
-42.5°	9	9	8	8	7	7	6	5	5	4	4
-43.75°	9	8	8	7	6	6	5	5	4	4	3
-45°	8	7	7	6	6	5	5	4	4	3	3
-46.25°	7	7	6	6	5	5	4	4	3	3	2
-47.5°	6	6	5	5	4	4	3	3	3	2	2
-48.75°	6	5	5	4	4	3	3	3	2	2	2
-50°	5	4	4	4	3	3	3	2	2	2	2
-51.25°	4	4	3	3	3	2	2	2	2	2	1
-52.5°	3	3	3	3	2	2	2	2	1	1	1
-53.75°	3	3	2	2	2	2	2	1	1	1	1
-55°	2	2	2	2	2	1	1	1	1	1	1
-56.25°	2	2	2	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	0
-67.5°	1	1	1	1	1	1	1	1	0	0	0
-68.75°	1	1	1	1	1	0	0	0	0	0	0
-70°	1	1	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	1	0	0	0	0	0	0	0	0	0	0
63.75°	1	1	1	0	0	0	0	0	0	0	0
62.5°	1	1	1	1	1	0	0	0	0	0	0
61.25°	1	1	1	1	1	1	0	0	0	0	0
60°	1	1	1	1	1	1	1	0	0	0	0
58.75°	1	1	1	1	1	1	1	1	0	0	0
57.5°	1	1	1	1	1	1	1	1	1	0	0
56.25°	1	1	1	1	1	1	1	1	1	1	0
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	2	1	1	1	1	1	1	1	1	1	1
47.5°	2	2	1	1	1	1	1	1	1	1	1
46.25°	2	2	2	1	1	1	1	1	1	1	1
45°	2	2	2	2	1	1	1	1	1	1	1
43.75°	3	2	2	2	1	1	1	1	1	1	1
42.5°	3	3	2	2	2	1	1	1	1	1	1
41.25°	3	3	3	2	2	2	1	1	1	1	1
40°	4	3	3	2	2	2	1	1	1	1	1
38.75°	4	4	3	3	2	2	2	1	1	1	1
37.5°	5	4	4	3	3	2	2	1	1	1	1
36.25°	5	5	4	3	3	2	2	2	1	1	1
35°	6	5	4	4	3	3	2	2	1	1	1



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	6	6	5	4	3	3	2	2	2	1	1
32.5°	7	6	5	4	4	3	3	2	2	1	1
31.25°	7	6	6	5	4	3	3	2	2	2	1
30°	8	7	6	5	4	4	3	3	2	2	1
28.75°	8	7	6	6	5	4	3	3	2	2	1
27.5°	8	8	7	6	5	4	3	3	2	2	2
26.25°	9	8	7	6	5	5	4	3	3	2	2
25°	9	8	8	7	6	5	4	3	3	2	2
23.75°	9	9	8	7	6	5	4	3	3	2	2
22.5°	9	9	8	7	6	5	5	4	3	2	2
21.25°	10	9	8	8	7	6	5	4	3	3	2
20°	10	9	9	8	7	6	5	4	3	3	2
18.75°	10	9	9	8	7	6	5	4	3	3	2
17.5°	10	10	9	8	7	6	6	5	4	3	2
16.25°	11	10	9	9	8	7	6	5	4	3	2
15°	11	10	9	9	8	7	6	5	4	3	3
13.75°	11	10	9	9	8	7	6	5	4	3	3
12.5°	12	10	10	9	8	7	6	5	4	3	3
11.25°	12	10	10	9	8	7	6	5	4	3	3
10°	12	11	10	9	8	7	7	6	5	4	3
8.75°	12	11	10	9	9	8	7	6	5	4	3
7.5°	12	11	10	9	9	8	7	6	5	4	3
6.25°	13	11	10	9	9	8	7	6	5	4	3
5°	13	11	10	9	9	8	7	6	5	4	3
3.75°	13	11	10	9	9	8	7	6	5	4	3
2.5°	13	11	10	9	9	8	7	6	5	4	3
1.25°	13	11	10	9	9	8	7	6	5	4	3
0°	13	12	10	10	9	8	7	6	5	4	3
-1.25°	13	11	10	9	9	8	7	6	5	4	3
-2.5°	13	11	10	9	9	8	7	6	5	4	3
-3.75°	13	11	10	9	9	8	7	6	5	4	3
-5°	13	11	10	9	9	8	7	6	5	4	3
-6.25°	13	11	10	9	9	8	7	6	5	4	3
-7.5°	12	11	10	9	9	8	7	6	5	4	3
-8.75°	12	11	10	9	9	8	7	6	5	4	3
-10°	12	11	10	9	8	7	7	6	5	4	3
-11.25°	12	10	10	9	8	7	6	5	4	3	3
-12.5°	12	10	10	9	8	7	6	5	4	3	3
-13.75°	11	10	9	9	8	7	6	5	4	3	3
-15°	11	10	9	9	8	7	6	5	4	3	3
-16.25°	11	10	9	9	8	7	6	5	4	3	2
-17.5°	10	10	9	8	7	6	6	5	4	3	2
-18.75°	10	9	9	8	7	6	5	4	3	3	2
-20°	10	9	9	8	7	6	5	4	3	3	2
-21.25°	10	9	8	8	7	6	5	4	3	3	2



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	9	9	8	7	6	5	5	4	3	2	2
-23.75°	9	9	8	7	6	5	4	3	3	2	2
-25°	9	8	8	7	6	5	4	3	3	2	2
-26.25°	9	8	7	6	5	5	4	3	3	2	2
-27.5°	8	8	7	6	5	4	3	3	2	2	2
-28.75°	8	7	6	6	5	4	3	3	2	2	1
-30°	8	7	6	5	4	4	3	3	2	2	1
-31.25°	7	6	6	5	4	3	3	2	2	2	1
-32.5°	7	6	5	4	4	3	3	2	2	1	1
-33.75°	6	6	5	4	3	3	2	2	2	1	1
-35°	6	5	4	4	3	3	2	2	1	1	1
-36.25°	5	5	4	3	3	2	2	2	1	1	1
-37.5°	5	4	4	3	3	2	2	1	1	1	1
-38.75°	4	4	3	3	2	2	2	1	1	1	1
-40°	4	3	3	2	2	2	1	1	1	1	1
-41.25°	3	3	3	2	2	2	1	1	1	1	1
-42.5°	3	3	2	2	2	1	1	1	1	1	1
-43.75°	3	2	2	2	1	1	1	1	1	1	1
-45°	2	2	2	2	1	1	1	1	1	1	1
-46.25°	2	2	2	1	1	1	1	1	1	1	1
-47.5°	2	2	1	1	1	1	1	1	1	1	1
-48.75°	2	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	0
-57.5°	1	1	1	1	1	1	1	1	1	0	0
-58.75°	1	1	1	1	1	1	1	1	0	0	0
-60°	1	1	1	1	1	1	1	0	0	0	0
-61.25°	1	1	1	1	1	1	0	0	0	0	0
-62.5°	1	1	1	1	1	0	0	0	0	0	0
-63.75°	1	1	1	0	0	0	0	0	0	0	0
-65°	1	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	1	0	0	0	0	0	0	0	0	0	0
52.5°	1	1	0	0	0	0	0	0	0	0	0
51.25°	1	1	0	0	0	0	0	0	0	0	0
50°	1	1	1	0	0	0	0	0	0	0	0
48.75°	1	1	1	0	0	0	0	0	0	0	0
47.5°	1	1	1	1	0	0	0	0	0	0	0
46.25°	1	1	1	1	0	0	0	0	0	0	0
45°	1	1	1	1	1	0	0	0	0	0	0
43.75°	1	1	1	1	1	0	0	0	0	0	0
42.5°	1	1	1	1	1	1	0	0	0	0	0
41.25°	1	1	1	1	1	1	0	0	0	0	0
40°	1	1	1	1	1	1	0	0	0	0	0
38.75°	1	1	1	1	1	1	1	0	0	0	0
37.5°	1	1	1	1	1	1	1	0	0	0	0
36.25°	1	1	1	1	1	1	1	0	0	0	0
35°	1	1	1	1	1	1	1	1	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	0	0	0
32.5°	1	1	1	1	1	1	1	1	0	0	0
31.25°	1	1	1	1	1	1	1	1	0	0	0
30°	1	1	1	1	1	1	1	1	0	0	0
28.75°	1	1	1	1	1	1	1	1	1	0	0
27.5°	1	1	1	1	1	1	1	1	1	0	0
26.25°	1	1	1	1	1	1	1	1	1	0	0
25°	1	1	1	1	1	1	1	1	1	0	0
23.75°	1	1	1	1	1	1	1	1	1	0	0
22.5°	2	1	1	1	1	1	1	1	1	0	0
21.25°	2	1	1	1	1	1	1	1	1	1	0
20°	2	1	1	1	1	1	1	1	1	1	0
18.75°	2	1	1	1	1	1	1	1	1	1	0
17.5°	2	1	1	1	1	1	1	1	1	1	0
16.25°	2	2	1	1	1	1	1	1	1	1	0
15°	2	2	1	1	1	1	1	1	1	1	0
13.75°	2	2	1	1	1	1	1	1	1	1	0
12.5°	2	2	1	1	1	1	1	1	1	1	0
11.25°	2	2	1	1	1	1	1	1	1	1	0
10°	2	2	1	1	1	1	1	1	1	1	0
8.75°	2	2	1	1	1	1	1	1	1	1	0
7.5°	2	2	1	1	1	1	1	1	1	1	0
6.25°	2	2	1	1	1	1	1	1	1	1	0
5°	2	2	1	1	1	1	1	1	1	1	0
3.75°	2	2	1	1	1	1	1	1	1	1	0
2.5°	2	2	1	1	1	1	1	1	1	1	0
1.25°	2	2	1	1	1	1	1	1	1	1	0
0°	3	2	2	1	1	1	1	1	1	1	1
-1.25°	2	2	1	1	1	1	1	1	1	1	0
-2.5°	2	2	1	1	1	1	1	1	1	1	0
-3.75°	2	2	1	1	1	1	1	1	1	1	0
-5°	2	2	1	1	1	1	1	1	1	1	0
-6.25°	2	2	1	1	1	1	1	1	1	1	0
-7.5°	2	2	1	1	1	1	1	1	1	1	0
-8.75°	2	2	1	1	1	1	1	1	1	1	0
-10°	2	2	1	1	1	1	1	1	1	1	0
-11.25°	2	2	1	1	1	1	1	1	1	1	0
-12.5°	2	2	1	1	1	1	1	1	1	1	0
-13.75°	2	2	1	1	1	1	1	1	1	1	0
-15°	2	2	1	1	1	1	1	1	1	1	0
-16.25°	2	2	1	1	1	1	1	1	1	1	0
-17.5°	2	1	1	1	1	1	1	1	1	1	0
-18.75°	2	1	1	1	1	1	1	1	1	1	0
-20°	2	1	1	1	1	1	1	1	1	1	0
-21.25°	2	1	1	1	1	1	1	1	1	1	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	1	1	1	1	1	1	1	1	0	0
-23.75°	1	1	1	1	1	1	1	1	1	0	0
-25°	1	1	1	1	1	1	1	1	1	0	0
-26.25°	1	1	1	1	1	1	1	1	1	0	0
-27.5°	1	1	1	1	1	1	1	1	1	0	0
-28.75°	1	1	1	1	1	1	1	1	1	0	0
-30°	1	1	1	1	1	1	1	1	0	0	0
-31.25°	1	1	1	1	1	1	1	1	0	0	0
-32.5°	1	1	1	1	1	1	1	1	0	0	0
-33.75°	1	1	1	1	1	1	1	1	0	0	0
-35°	1	1	1	1	1	1	1	1	0	0	0
-36.25°	1	1	1	1	1	1	1	0	0	0	0
-37.5°	1	1	1	1	1	1	1	0	0	0	0
-38.75°	1	1	1	1	1	1	1	0	0	0	0
-40°	1	1	1	1	1	1	0	0	0	0	0
-41.25°	1	1	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	1	0	0	0	0	0
-43.75°	1	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	1	1	0	0	0	0	0	0
-46.25°	1	1	1	1	0	0	0	0	0	0	0
-47.5°	1	1	1	1	0	0	0	0	0	0	0
-48.75°	1	1	1	0	0	0	0	0	0	0	0
-50°	1	1	1	0	0	0	0	0	0	0	0
-51.25°	1	1	0	0	0	0	0	0	0	0	0
-52.5°	1	1	0	0	0	0	0	0	0	0	0
-53.75°	1	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-7 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4010-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)