

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4025-12-CS-DIFF**

Test Date: 04/05/18

Test Information


Test Method: LM-79-08
Report Number: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-40)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/05/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4025-12-CS-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, DIFFUSED LENS
Light Source: (1) SORAA 4000K 90 CRI LED
SM16-07-25D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	281.2 lumens	Max Intensity:	720 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	36.0 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	31.5°H x 31.5°V	Field Angle (10%):	62.8°H x 62.8°V
Beam Lumens:	120.3 lumens	Field Lumens:	240.7 lumens
Beam Efficiency:	42.8%	Field Efficiency:	85.6%
Input Watts (W):	7.8		
Input Voltage (V):	12.0		
Input Current (A _{in}):	0.684		
Voltage Rise (V):	NR		
Power Factor:	0.9908		
Total Harmonic Distortion (THDi):	27.1%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	3 HR		
Ambient Temperature (°C):	25.0		
Test Distance:	25 FT		

REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

Lumen Table

90	0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0	0.0									
80	0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0	0.0									
70	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0			
60		0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0				
50	0.0	0.0	0.0	0.1	0.1	0.2	0.3	0.4	0.4	0.3	0.2	0.1	0.1	0.0	0.0			
40		0.0	0.1	0.1	0.2	0.5	0.9	1.4	1.4	0.9	0.5	0.2	0.1	0.1				
30	0.0	0.0	0.1	0.2	0.5	1.3	3.0	4.5	4.5	3.0	1.3	0.5	0.2	0.1	0.0			
20		0.0	0.1	0.2	0.8	2.8	6.7	10.8	10.8	6.7	2.8	0.8	0.2	0.1				
10	0.0	0.0	0.1	0.3	1.1	4.1	10.5	17.9	17.9	10.5	4.1	1.1	0.3	0.1	0.0			
0		0.0	0.1	0.3	1.1	4.1	10.5	17.9	17.9	10.5	4.1	1.1	0.3	0.1				
-10	0.0	0.0	0.1	0.3	1.1	4.1	10.5	17.9	17.9	10.5	4.1	1.1	0.3	0.1	0.0			
-20		0.0	0.1	0.2	0.8	2.8	6.7	10.8	10.8	6.7	2.8	0.8	0.2	0.1				
-30	0.0	0.0	0.1	0.2	0.5	1.3	3.0	4.5	4.5	3.0	1.3	0.5	0.2	0.1	0.0			
-40		0.0	0.1	0.1	0.2	0.5	0.9	1.4	1.4	0.9	0.5	0.2	0.1	0.1				
-50	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0			
-60		0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0				
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0			
-80		0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0				
-90	0.0	0.0	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0


REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

Luminous Intensity Plot



Beam:
 H Angle: 31.5°
 V Angle: 31.5°
 Lumens: 120.3
 Efficiency: 42.8%

Field:
 H Angle: 62.8°
 V Angle: 62.8°
 Lumens: 240.7
 Efficiency: 85.6%

Spill:
 Lumens: 40.5
 Efficiency: 14.4%

- Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	1
43.75°	0	0	0	0	0	0	0	0	0	0	1
42.5°	0	0	0	0	0	0	0	0	0	0	1
41.25°	0	0	0	0	0	0	0	0	0	0	1
40°	0	0	0	0	0	0	0	0	0	0	1
38.75°	0	0	0	0	0	0	0	0	0	1	1
37.5°	0	0	0	0	0	0	0	0	0	1	1
36.25°	0	0	0	0	0	0	0	0	0	1	1
35°	0	0	0	0	0	0	0	0	0	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	0	1	1	1
22.5°	0	0	0	0	0	0	0	0	1	1	1
21.25°	0	0	0	0	0	0	0	0	1	1	1
20°	0	0	0	0	0	0	0	0	1	1	1
18.75°	0	0	0	0	0	0	0	0	1	1	1
17.5°	0	0	0	0	0	0	0	0	1	1	1
16.25°	0	0	0	0	0	0	0	0	1	1	1
15°	0	0	0	0	0	0	0	0	1	1	1
13.75°	0	0	0	0	0	0	0	0	1	1	1
12.5°	0	0	0	0	0	0	0	0	1	1	1
11.25°	0	0	0	0	0	0	0	0	1	1	1
10°	0	0	0	0	0	0	0	0	1	1	1
8.75°	0	0	0	0	0	0	0	0	1	1	1
7.5°	0	0	0	0	0	0	0	0	1	1	1
6.25°	0	0	0	0	0	0	0	0	1	1	1
5°	0	0	0	0	0	0	0	0	1	1	1
3.75°	0	0	0	0	0	0	0	0	1	1	1
2.5°	0	0	0	0	0	0	0	0	1	1	1
1.25°	0	0	0	0	0	0	0	0	1	1	1
0°	0	0	0	0	0	0	0	1	1	1	1
-1.25°	0	0	0	0	0	0	0	0	1	1	1
-2.5°	0	0	0	0	0	0	0	0	1	1	1
-3.75°	0	0	0	0	0	0	0	0	1	1	1
-5°	0	0	0	0	0	0	0	0	1	1	1
-6.25°	0	0	0	0	0	0	0	0	1	1	1
-7.5°	0	0	0	0	0	0	0	0	1	1	1
-8.75°	0	0	0	0	0	0	0	0	1	1	1
-10°	0	0	0	0	0	0	0	0	1	1	1
-11.25°	0	0	0	0	0	0	0	0	1	1	1
-12.5°	0	0	0	0	0	0	0	0	1	1	1
-13.75°	0	0	0	0	0	0	0	0	1	1	1
-15°	0	0	0	0	0	0	0	0	1	1	1
-16.25°	0	0	0	0	0	0	0	0	1	1	1
-17.5°	0	0	0	0	0	0	0	0	1	1	1
-18.75°	0	0	0	0	0	0	0	0	1	1	1
-20°	0	0	0	0	0	0	0	0	1	1	1
-21.25°	0	0	0	0	0	0	0	0	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	1	1	1
-23.75°	0	0	0	0	0	0	0	0	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	1	1	1
-28.75°	0	0	0	0	0	0	0	0	1	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	1	1
-36.25°	0	0	0	0	0	0	0	0	0	1	1
-37.5°	0	0	0	0	0	0	0	0	0	1	1
-38.75°	0	0	0	0	0	0	0	0	0	1	1
-40°	0	0	0	0	0	0	0	0	0	0	1
-41.25°	0	0	0	0	0	0	0	0	0	0	1
-42.5°	0	0	0	0	0	0	0	0	0	0	1
-43.75°	0	0	0	0	0	0	0	0	0	0	1
-45°	0	0	0	0	0	0	0	0	0	0	1
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	1	1
67.5°	0	0	0	0	0	0	0	0	1	1	1
66.25°	0	0	0	0	0	0	0	1	1	1	1
65°	0	0	0	0	0	0	1	1	1	1	1
63.75°	0	0	0	0	0	0	1	1	1	1	1
62.5°	0	0	0	0	0	1	1	1	1	1	1
61.25°	0	0	0	0	1	1	1	1	1	1	1
60°	0	0	0	0	1	1	1	1	1	1	1
58.75°	0	0	0	1	1	1	1	1	1	1	1
57.5°	0	0	0	1	1	1	1	1	1	1	1
56.25°	0	0	1	1	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	1	1
53.75°	0	1	1	1	1	1	1	1	1	1	1
52.5°	0	1	1	1	1	1	1	1	1	1	1
51.25°	0	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	2
32.5°	1	1	1	1	1	1	1	1	1	1	2
31.25°	1	1	1	1	1	1	1	1	1	1	2
30°	1	1	1	1	1	1	1	1	1	2	2
28.75°	1	1	1	1	1	1	1	1	1	2	2
27.5°	1	1	1	1	1	1	1	1	1	2	2
26.25°	1	1	1	1	1	1	1	1	1	2	2
25°	1	1	1	1	1	1	1	1	2	2	2
23.75°	1	1	1	1	1	1	1	1	2	2	2
22.5°	1	1	1	1	1	1	1	1	2	2	2
21.25°	1	1	1	1	1	1	1	1	2	2	2
20°	1	1	1	1	1	1	1	1	2	2	2
18.75°	1	1	1	1	1	1	1	1	2	2	2
17.5°	1	1	1	1	1	1	1	2	2	2	2
16.25°	1	1	1	1	1	1	1	2	2	2	2
15°	1	1	1	1	1	1	1	2	2	2	2
13.75°	1	1	1	1	1	1	1	2	2	2	2
12.5°	1	1	1	1	1	1	1	2	2	2	2
11.25°	1	1	1	1	1	1	1	2	2	2	2
10°	1	1	1	1	1	1	1	2	2	2	2
8.75°	1	1	1	1	1	1	1	2	2	2	2
7.5°	1	1	1	1	1	1	1	2	2	2	2
6.25°	1	1	1	1	1	1	1	2	2	2	2
5°	1	1	1	1	1	1	1	2	2	2	2
3.75°	1	1	1	1	1	1	1	2	2	2	2
2.5°	1	1	1	1	1	1	1	2	2	2	2
1.25°	1	1	1	1	1	1	1	2	2	2	2
0°	1	1	1	1	1	1	2	2	2	2	3
-1.25°	1	1	1	1	1	1	1	2	2	2	2
-2.5°	1	1	1	1	1	1	1	2	2	2	2
-3.75°	1	1	1	1	1	1	1	2	2	2	2
-5°	1	1	1	1	1	1	1	2	2	2	2
-6.25°	1	1	1	1	1	1	1	2	2	2	2
-7.5°	1	1	1	1	1	1	1	2	2	2	2
-8.75°	1	1	1	1	1	1	1	2	2	2	2
-10°	1	1	1	1	1	1	1	2	2	2	2
-11.25°	1	1	1	1	1	1	1	2	2	2	2
-12.5°	1	1	1	1	1	1	1	2	2	2	2
-13.75°	1	1	1	1	1	1	1	2	2	2	2
-15°	1	1	1	1	1	1	1	2	2	2	2
-16.25°	1	1	1	1	1	1	1	2	2	2	2
-17.5°	1	1	1	1	1	1	1	2	2	2	2
-18.75°	1	1	1	1	1	1	1	1	2	2	2
-20°	1	1	1	1	1	1	1	1	2	2	2
-21.25°	1	1	1	1	1	1	1	1	2	2	2



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	2	2	2
-23.75°	1	1	1	1	1	1	1	1	2	2	2
-25°	1	1	1	1	1	1	1	1	2	2	2
-26.25°	1	1	1	1	1	1	1	1	1	2	2
-27.5°	1	1	1	1	1	1	1	1	1	2	2
-28.75°	1	1	1	1	1	1	1	1	1	2	2
-30°	1	1	1	1	1	1	1	1	1	2	2
-31.25°	1	1	1	1	1	1	1	1	1	1	2
-32.5°	1	1	1	1	1	1	1	1	1	1	2
-33.75°	1	1	1	1	1	1	1	1	1	1	2
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	0	1	1	1	1	1	1	1	1	1	1
-52.5°	0	1	1	1	1	1	1	1	1	1	1
-53.75°	0	1	1	1	1	1	1	1	1	1	1
-55°	0	0	1	1	1	1	1	1	1	1	1
-56.25°	0	0	1	1	1	1	1	1	1	1	1
-57.5°	0	0	0	1	1	1	1	1	1	1	1
-58.75°	0	0	0	1	1	1	1	1	1	1	1
-60°	0	0	0	0	1	1	1	1	1	1	1
-61.25°	0	0	0	0	1	1	1	1	1	1	1
-62.5°	0	0	0	0	0	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	1	1	1	1	1
-65°	0	0	0	0	0	0	1	1	1	1	1
-66.25°	0	0	0	0	0	0	0	1	1	1	1
-67.5°	0	0	0	0	0	0	0	0	1	1	1
-68.75°	0	0	0	0	0	0	0	0	0	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	1
75°	0	0	0	0	0	0	0	1	1	1	1
73.75°	0	0	0	0	0	1	1	1	1	1	1
72.5°	0	0	0	1	1	1	1	1	1	1	1
71.25°	0	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	2
53.75°	1	1	1	1	1	1	1	1	1	2	2
52.5°	1	1	1	1	1	1	1	1	2	2	2
51.25°	1	1	1	1	1	1	1	2	2	2	2
50°	1	1	1	1	1	1	2	2	2	2	2
48.75°	1	1	1	1	1	2	2	2	2	2	2
47.5°	1	1	1	1	2	2	2	2	2	2	2
46.25°	1	1	1	1	2	2	2	2	2	2	3
45°	1	1	1	2	2	2	2	2	2	3	3
43.75°	1	1	1	2	2	2	2	2	2	3	3
42.5°	1	1	2	2	2	2	2	2	3	3	3
41.25°	1	1	2	2	2	2	2	3	3	3	3
40°	1	2	2	2	2	2	2	3	3	3	3
38.75°	1	2	2	2	2	2	3	3	3	3	3
37.5°	2	2	2	2	2	2	3	3	3	3	3
36.25°	2	2	2	2	2	3	3	3	3	3	3
35°	2	2	2	2	2	3	3	3	3	3	4



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	3	3	3	3	3	4	4
32.5°	2	2	2	2	3	3	3	3	3	4	4
31.25°	2	2	2	3	3	3	3	3	4	4	4
30°	2	2	2	3	3	3	3	3	4	4	5
28.75°	2	2	2	3	3	3	3	3	4	4	5
27.5°	2	2	3	3	3	3	3	4	4	4	5
26.25°	2	2	3	3	3	3	3	4	4	5	5
25°	2	2	3	3	3	3	4	4	4	5	5
23.75°	2	2	3	3	3	3	4	4	5	5	5
22.5°	2	3	3	3	3	3	4	4	5	5	6
21.25°	2	3	3	3	3	3	4	4	5	5	6
20°	2	3	3	3	3	4	4	5	5	5	6
18.75°	2	3	3	3	3	4	4	5	5	6	6
17.5°	2	3	3	3	3	4	4	5	5	6	6
16.25°	3	3	3	3	3	4	4	5	5	6	6
15°	3	3	3	3	4	4	4	5	5	6	6
13.75°	3	3	3	3	4	4	5	5	6	6	6
12.5°	3	3	3	3	4	4	5	5	6	6	7
11.25°	3	3	3	3	4	4	5	5	6	6	7
10°	3	3	3	3	4	4	5	5	6	6	7
8.75°	3	3	3	3	4	4	5	5	6	6	7
7.5°	3	3	3	3	4	4	5	5	6	6	7
6.25°	3	3	3	3	4	4	5	5	6	6	7
5°	3	3	3	3	4	4	5	5	6	6	7
3.75°	3	3	3	3	4	4	5	5	6	6	7
2.5°	3	3	3	3	4	4	5	5	6	6	7
1.25°	3	3	3	3	4	4	5	5	6	6	7
0°	3	3	3	4	4	5	5	6	6	7	7
-1.25°	3	3	3	3	4	4	5	5	6	6	7
-2.5°	3	3	3	3	4	4	5	5	6	6	7
-3.75°	3	3	3	3	4	4	5	5	6	6	7
-5°	3	3	3	3	4	4	5	5	6	6	7
-6.25°	3	3	3	3	4	4	5	5	6	6	7
-7.5°	3	3	3	3	4	4	5	5	6	6	7
-8.75°	3	3	3	3	4	4	5	5	6	6	7
-10°	3	3	3	3	4	4	5	5	6	6	7
-11.25°	3	3	3	3	4	4	5	5	6	6	7
-12.5°	3	3	3	3	4	4	5	5	6	6	7
-13.75°	3	3	3	3	4	4	5	5	6	6	6
-15°	3	3	3	3	4	4	4	5	5	6	6
-16.25°	3	3	3	3	3	4	4	5	5	6	6
-17.5°	2	3	3	3	3	4	4	5	5	6	6
-18.75°	2	3	3	3	3	4	4	5	5	6	6
-20°	2	3	3	3	3	4	4	5	5	5	6
-21.25°	2	3	3	3	3	3	4	4	5	5	6



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	3	3	3	3	3	4	4	5	5	6
-23.75°	2	2	3	3	3	3	4	4	5	5	5
-25°	2	2	3	3	3	3	4	4	4	5	5
-26.25°	2	2	3	3	3	3	3	4	4	5	5
-27.5°	2	2	3	3	3	3	3	4	4	4	5
-28.75°	2	2	2	3	3	3	3	3	4	4	5
-30°	2	2	2	3	3	3	3	3	4	4	5
-31.25°	2	2	2	3	3	3	3	3	4	4	4
-32.5°	2	2	2	2	3	3	3	3	3	4	4
-33.75°	2	2	2	2	3	3	3	3	3	4	4
-35°	2	2	2	2	2	3	3	3	3	3	4
-36.25°	2	2	2	2	2	3	3	3	3	3	3
-37.5°	2	2	2	2	2	2	3	3	3	3	3
-38.75°	1	2	2	2	2	2	3	3	3	3	3
-40°	1	2	2	2	2	2	2	3	3	3	3
-41.25°	1	1	2	2	2	2	2	3	3	3	3
-42.5°	1	1	2	2	2	2	2	2	3	3	3
-43.75°	1	1	1	2	2	2	2	2	2	3	3
-45°	1	1	1	2	2	2	2	2	2	3	3
-46.25°	1	1	1	1	2	2	2	2	2	2	3
-47.5°	1	1	1	1	2	2	2	2	2	2	2
-48.75°	1	1	1	1	1	2	2	2	2	2	2
-50°	1	1	1	1	1	1	2	2	2	2	2
-51.25°	1	1	1	1	1	1	1	2	2	2	2
-52.5°	1	1	1	1	1	1	1	1	2	2	2
-53.75°	1	1	1	1	1	1	1	1	1	2	2
-55°	1	1	1	1	1	1	1	1	1	1	2
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	0	1	1	1	1	1	1	1	1	1	1
-72.5°	0	0	0	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	1	1	1
77.5°	0	0	0	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	2	2
61.25°	1	1	1	1	1	1	1	2	2	2	2
60°	1	1	1	1	1	2	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	3
55°	2	2	2	2	2	2	2	2	3	3	3
53.75°	2	2	2	2	2	2	3	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	2	3	3	3	3	3	3	3	3	3
48.75°	2	3	3	3	3	3	3	3	3	4	4
47.5°	3	3	3	3	3	3	3	3	4	4	4
46.25°	3	3	3	3	3	3	4	4	4	4	5
45°	3	3	3	3	3	4	4	4	4	5	5
43.75°	3	3	3	3	4	4	4	4	5	5	5
42.5°	3	3	3	4	4	4	4	5	5	5	6
41.25°	3	3	4	4	4	4	5	5	5	6	6
40°	3	3	4	4	4	5	5	5	6	6	6
38.75°	3	4	4	4	5	5	5	6	6	6	7
37.5°	4	4	4	5	5	5	6	6	6	7	7
36.25°	4	4	5	5	5	6	6	6	7	7	7
35°	4	4	5	5	6	6	6	7	7	7	8



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	4	5	5	5	6	6	6	7	7	8	9
32.5°	5	5	5	6	6	6	7	7	8	9	9
31.25°	5	5	5	6	6	7	7	8	8	9	10
30°	5	5	6	6	6	7	8	8	9	10	10
28.75°	5	6	6	6	7	7	8	9	10	10	11
27.5°	5	6	6	7	7	8	8	9	10	11	12
26.25°	6	6	6	7	7	8	9	10	11	12	14
25°	6	6	7	7	8	9	9	10	11	13	15
23.75°	6	6	7	7	8	9	10	11	12	14	16
22.5°	6	6	7	8	8	9	10	11	13	15	18
21.25°	6	7	7	8	9	10	11	12	14	16	19
20°	6	7	7	8	9	10	11	13	15	18	20
18.75°	6	7	8	9	10	10	12	14	16	19	21
17.5°	7	7	8	9	10	11	13	15	17	20	23
16.25°	7	7	8	9	10	11	13	16	18	21	25
15°	7	8	9	9	10	12	14	17	19	22	26
13.75°	7	8	9	10	11	12	15	17	20	23	28
12.5°	7	8	9	10	11	13	15	18	21	25	29
11.25°	7	8	9	10	11	14	16	19	22	26	30
10°	7	8	9	10	12	14	17	20	23	27	31
8.75°	8	9	9	10	12	15	17	20	24	28	33
7.5°	8	9	10	11	12	15	18	21	24	29	34
6.25°	8	9	10	11	13	15	18	21	25	29	35
5°	8	9	10	11	13	16	18	21	26	30	36
3.75°	8	9	10	11	13	16	19	22	26	30	36
2.5°	8	9	10	11	13	16	19	22	26	31	37
1.25°	8	9	10	11	13	16	19	22	26	31	37
0°	8	9	10	11	14	16	19	22	27	31	37
-1.25°	8	9	10	11	13	16	19	22	26	31	37
-2.5°	8	9	10	11	13	16	19	22	26	31	37
-3.75°	8	9	10	11	13	16	19	22	26	30	36
-5°	8	9	10	11	13	16	18	21	26	30	36
-6.25°	8	9	10	11	13	15	18	21	25	29	35
-7.5°	8	9	10	11	12	15	18	21	24	29	34
-8.75°	8	9	9	10	12	15	17	20	24	28	33
-10°	7	8	9	10	12	14	17	20	23	27	31
-11.25°	7	8	9	10	11	14	16	19	22	26	30
-12.5°	7	8	9	10	11	13	15	18	21	25	29
-13.75°	7	8	9	10	11	12	15	17	20	23	28
-15°	7	8	9	9	10	12	14	17	19	22	26
-16.25°	7	7	8	9	10	11	13	16	18	21	25
-17.5°	7	7	8	9	10	11	13	15	17	20	23
-18.75°	6	7	8	9	10	10	12	14	16	19	21
-20°	6	7	7	8	9	10	11	13	15	18	20
-21.25°	6	7	7	8	9	10	11	12	14	16	19



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	6	6	7	8	8	9	10	11	13	15	18
-23.75°	6	6	7	7	8	9	10	11	12	14	16
-25°	6	6	7	7	8	9	9	10	11	13	15
-26.25°	6	6	6	7	7	8	9	10	11	12	14
-27.5°	5	6	6	7	7	8	8	9	10	11	12
-28.75°	5	6	6	6	7	7	8	9	10	10	11
-30°	5	5	6	6	6	7	8	8	9	10	10
-31.25°	5	5	5	6	6	7	7	8	8	9	10
-32.5°	5	5	5	6	6	6	7	7	8	9	9
-33.75°	4	5	5	5	6	6	6	7	7	8	9
-35°	4	4	5	5	6	6	6	7	7	7	8
-36.25°	4	4	5	5	5	6	6	6	7	7	7
-37.5°	4	4	4	5	5	5	6	6	6	7	7
-38.75°	3	4	4	4	5	5	5	6	6	6	7
-40°	3	3	4	4	4	5	5	5	6	6	6
-41.25°	3	3	4	4	4	4	5	5	5	6	6
-42.5°	3	3	3	4	4	4	4	5	5	5	6
-43.75°	3	3	3	3	4	4	4	4	5	5	5
-45°	3	3	3	3	3	4	4	4	4	5	5
-46.25°	3	3	3	3	3	3	4	4	4	4	5
-47.5°	3	3	3	3	3	3	3	3	4	4	4
-48.75°	2	3	3	3	3	3	3	3	3	4	4
-50°	2	2	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	3	3	3	3	3
-55°	2	2	2	2	2	2	2	2	3	3	3
-56.25°	2	2	2	2	2	2	2	2	2	2	3
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	2	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	1	1	1
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	2	2	2
65°	1	1	1	1	2	2	2	2	2	2	2
63.75°	1	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	3
60°	2	2	2	2	2	2	3	3	3	3	3
58.75°	2	2	2	3	3	3	3	3	3	3	3
57.5°	2	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	4	4	4
53.75°	3	3	3	3	3	3	4	4	4	4	4
52.5°	3	3	3	4	4	4	4	4	4	5	5
51.25°	3	4	4	4	4	4	4	5	5	5	5
50°	4	4	4	4	5	5	5	5	5	5	6
48.75°	4	4	5	5	5	5	5	6	6	6	6
47.5°	4	5	5	5	5	6	6	6	6	6	6
46.25°	5	5	5	5	6	6	6	6	7	7	7
45°	5	5	6	6	6	6	7	7	7	7	8
43.75°	6	6	6	6	6	7	7	7	8	8	8
42.5°	6	6	6	7	7	7	8	8	9	9	9
41.25°	6	6	7	7	8	8	8	9	9	10	10
40°	7	7	7	8	8	9	9	10	10	11	11
38.75°	7	7	8	8	9	10	10	11	11	12	13
37.5°	7	8	9	9	10	10	11	12	13	14	15
36.25°	8	9	9	10	10	11	12	14	15	16	18
35°	9	9	10	11	11	13	14	16	17	19	20



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	9	10	11	12	13	15	16	18	19	21	23
32.5°	10	11	12	13	15	16	18	20	22	24	26
31.25°	11	12	13	15	17	19	20	22	25	27	30
30°	11	13	15	17	19	21	23	25	28	31	34
28.75°	13	15	16	19	21	23	26	29	32	35	39
27.5°	14	16	18	20	23	26	29	32	36	40	43
26.25°	16	18	20	22	25	29	32	36	40	44	50
25°	17	19	22	25	28	32	36	40	45	51	56
23.75°	19	21	24	27	31	35	40	44	51	57	63
22.5°	20	23	26	30	34	39	43	50	56	63	72
21.25°	21	25	29	33	37	42	48	55	62	71	80
20°	23	27	31	36	40	46	54	61	70	79	89
18.75°	25	29	33	38	44	51	58	67	77	87	98
17.5°	27	31	36	41	48	55	64	74	84	96	108
16.25°	29	33	39	44	52	60	70	80	92	104	117
15°	30	35	41	48	56	65	76	86	99	113	126
13.75°	32	38	43	51	59	70	81	93	107	121	135
12.5°	34	39	46	54	63	75	86	100	114	129	145
11.25°	36	41	49	57	67	79	91	106	121	136	154
10°	37	43	51	60	71	83	96	111	127	143	162
8.75°	38	45	54	63	75	87	101	117	132	150	169
7.5°	40	47	56	66	78	90	105	121	138	157	176
6.25°	41	48	57	68	80	94	109	125	142	162	182
5°	42	50	59	70	82	96	112	128	147	166	188
3.75°	42	51	60	71	84	98	114	131	150	170	192
2.5°	43	51	60	73	85	100	116	133	152	172	195
1.25°	43	52	61	73	86	101	117	134	154	174	197
0°	43	52	61	74	86	101	118	135	154	175	198
-1.25°	43	52	61	73	86	101	117	134	154	174	197
-2.5°	43	51	60	73	85	100	116	133	152	172	195
-3.75°	42	51	60	71	84	98	114	131	150	170	192
-5°	42	50	59	70	82	96	112	128	147	166	188
-6.25°	41	48	57	68	80	94	109	125	142	162	182
-7.5°	40	47	56	66	78	90	105	121	138	157	176
-8.75°	38	45	54	63	75	87	101	117	132	150	169
-10°	37	43	51	60	71	83	96	111	127	143	162
-11.25°	36	41	49	57	67	79	91	106	121	136	154
-12.5°	34	39	46	54	63	75	86	100	114	129	145
-13.75°	32	38	43	51	59	70	81	93	107	121	135
-15°	30	35	41	48	56	65	76	86	99	113	126
-16.25°	29	33	39	44	52	60	70	80	92	104	117
-17.5°	27	31	36	41	48	55	64	74	84	96	108
-18.75°	25	29	33	38	44	51	58	67	77	87	98
-20°	23	27	31	36	40	46	54	61	70	79	89
-21.25°	21	25	29	33	37	42	48	55	62	71	80



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	20	23	26	30	34	39	43	50	56	63	72
-23.75°	19	21	24	27	31	35	40	44	51	57	63
-25°	17	19	22	25	28	32	36	40	45	51	56
-26.25°	16	18	20	22	25	29	32	36	40	44	50
-27.5°	14	16	18	20	23	26	29	32	36	40	43
-28.75°	13	15	16	19	21	23	26	29	32	35	39
-30°	11	13	15	17	19	21	23	25	28	31	34
-31.25°	11	12	13	15	17	19	20	22	25	27	30
-32.5°	10	11	12	13	15	16	18	20	22	24	26
-33.75°	9	10	11	12	13	15	16	18	19	21	23
-35°	9	9	10	11	11	13	14	16	17	19	20
-36.25°	8	9	9	10	10	11	12	14	15	16	18
-37.5°	7	8	9	9	10	10	11	12	13	14	15
-38.75°	7	7	8	8	9	10	10	11	11	12	13
-40°	7	7	7	8	8	9	9	10	10	11	11
-41.25°	6	6	7	7	8	8	8	9	9	10	10
-42.5°	6	6	6	7	7	7	8	8	9	9	9
-43.75°	6	6	6	6	6	7	7	7	8	8	8
-45°	5	5	6	6	6	6	7	7	7	7	8
-46.25°	5	5	5	5	6	6	6	6	7	7	7
-47.5°	4	5	5	5	5	6	6	6	6	6	6
-48.75°	4	4	5	5	5	5	5	6	6	6	6
-50°	4	4	4	4	5	5	5	5	5	5	6
-51.25°	3	4	4	4	4	4	4	5	5	5	5
-52.5°	3	3	3	4	4	4	4	4	4	5	5
-53.75°	3	3	3	3	3	3	4	4	4	4	4
-55°	3	3	3	3	3	3	3	3	4	4	4
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	2	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	2	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	3
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	2	2	2	2	2	2	2	2	2	2
-65°	1	1	1	1	2	2	2	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	2	2	2
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	0	0	0	0	0	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	4	4	4	4	4	4
56.25°	3	4	4	4	4	4	4	4	4	4	4
55°	4	4	4	4	4	4	5	5	5	5	5
53.75°	4	5	5	5	5	5	5	5	5	5	5
52.5°	5	5	5	5	5	5	6	6	6	6	6
51.25°	5	5	6	6	6	6	6	6	6	6	6
50°	6	6	6	6	6	6	6	7	7	7	7
48.75°	6	6	6	7	7	7	7	7	7	7	8
47.5°	7	7	7	7	7	8	8	8	8	8	9
46.25°	7	7	8	8	8	9	9	9	9	9	9
45°	8	8	9	9	9	9	10	10	10	10	10
43.75°	9	9	10	10	10	10	11	11	11	12	12
42.5°	10	10	10	11	11	12	12	13	14	14	15
41.25°	11	11	12	13	13	14	15	15	16	17	17
40°	12	13	14	15	16	17	17	18	19	20	20
38.75°	14	15	16	17	18	19	20	21	22	23	24
37.5°	16	18	19	20	21	22	23	25	26	27	28
36.25°	19	20	21	23	25	26	28	29	30	31	33
35°	21	23	25	27	29	30	32	34	36	37	38



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	25	27	29	31	33	35	38	39	41	43	45
32.5°	29	31	33	36	39	41	43	46	49	51	54
31.25°	33	36	38	41	44	48	51	54	57	60	63
30°	37	40	44	48	52	56	59	63	67	71	75
28.75°	42	46	51	55	60	65	70	75	79	83	87
27.5°	48	54	58	64	70	76	81	86	91	96	101
26.25°	55	61	67	74	80	86	93	100	106	111	117
25°	62	70	77	84	92	99	107	114	121	127	132
23.75°	71	79	87	96	104	113	121	129	136	143	150
22.5°	80	89	98	108	117	126	135	145	154	162	169
21.25°	90	100	110	121	131	141	152	162	171	181	190
20°	100	111	122	133	145	157	168	180	191	203	213
18.75°	110	122	134	147	160	173	186	200	213	225	237
17.5°	121	133	147	161	175	190	206	220	235	249	263
16.25°	131	145	160	175	192	208	225	242	259	276	290
15°	141	157	173	190	208	226	245	265	284	301	318
13.75°	152	168	186	206	225	245	267	288	308	327	346
12.5°	162	180	200	220	242	265	288	310	333	354	376
11.25°	171	191	213	235	259	284	308	333	357	382	404
10°	181	203	225	249	276	301	327	354	382	407	432
8.75°	190	213	237	263	290	318	346	376	404	432	458
7.5°	198	222	248	276	304	333	364	395	425	455	484
6.25°	206	230	258	287	316	347	380	411	444	476	507
5°	212	237	266	296	326	359	393	426	460	494	529
3.75°	217	243	273	303	335	369	403	438	473	509	546
2.5°	220	248	278	309	341	376	411	447	483	521	558
1.25°	222	250	281	312	345	381	416	452	489	529	566
0°	223	251	282	313	346	382	417	454	492	531	569
-1.25°	222	250	281	312	345	381	416	452	489	529	566
-2.5°	220	248	278	309	341	376	411	447	483	521	558
-3.75°	217	243	273	303	335	369	403	438	473	509	546
-5°	212	237	266	296	326	359	393	426	460	494	529
-6.25°	206	230	258	287	316	347	380	411	444	476	507
-7.5°	198	222	248	276	304	333	364	395	425	455	484
-8.75°	190	213	237	263	290	318	346	376	404	432	458
-10°	181	203	225	249	276	301	327	354	382	407	432
-11.25°	171	191	213	235	259	284	308	333	357	382	404
-12.5°	162	180	200	220	242	265	288	310	333	354	376
-13.75°	152	168	186	206	225	245	267	288	308	327	346
-15°	141	157	173	190	208	226	245	265	284	301	318
-16.25°	131	145	160	175	192	208	225	242	259	276	290
-17.5°	121	133	147	161	175	190	206	220	235	249	263
-18.75°	110	122	134	147	160	173	186	200	213	225	237
-20°	100	111	122	133	145	157	168	180	191	203	213
-21.25°	90	100	110	121	131	141	152	162	171	181	190



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	80	89	98	108	117	126	135	145	154	162	169
-23.75°	71	79	87	96	104	113	121	129	136	143	150
-25°	62	70	77	84	92	99	107	114	121	127	132
-26.25°	55	61	67	74	80	86	93	100	106	111	117
-27.5°	48	54	58	64	70	76	81	86	91	96	101
-28.75°	42	46	51	55	60	65	70	75	79	83	87
-30°	37	40	44	48	52	56	59	63	67	71	75
-31.25°	33	36	38	41	44	48	51	54	57	60	63
-32.5°	29	31	33	36	39	41	43	46	49	51	54
-33.75°	25	27	29	31	33	35	38	39	41	43	45
-35°	21	23	25	27	29	30	32	34	36	37	38
-36.25°	19	20	21	23	25	26	28	29	30	31	33
-37.5°	16	18	19	20	21	22	23	25	26	27	28
-38.75°	14	15	16	17	18	19	20	21	22	23	24
-40°	12	13	14	15	16	17	17	18	19	20	20
-41.25°	11	11	12	13	13	14	15	15	16	17	17
-42.5°	10	10	10	11	11	12	12	13	14	14	15
-43.75°	9	9	10	10	10	10	11	11	11	12	12
-45°	8	8	9	9	9	9	10	10	10	10	10
-46.25°	7	7	8	8	8	9	9	9	9	9	9
-47.5°	7	7	7	7	7	8	8	8	8	8	9
-48.75°	6	6	6	7	7	7	7	7	7	7	8
-50°	6	6	6	6	6	6	6	7	7	7	7
-51.25°	5	5	6	6	6	6	6	6	6	6	6
-52.5°	5	5	5	5	5	5	6	6	6	6	6
-53.75°	4	5	5	5	5	5	5	5	5	5	5
-55°	4	4	4	4	4	4	5	5	5	5	5
-56.25°	3	4	4	4	4	4	4	4	4	4	4
-57.5°	3	3	3	3	3	4	4	4	4	4	4
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	2	2	2	2	3	3	3	3	3	3	3
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	1	1	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	1	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	2	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	3	2	2	2	2
62.5°	3	3	3	3	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	4	3	3	3	3
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	4	4	4	4	4	4	5	4	4	4	4
55°	5	5	5	5	5	5	5	5	5	5	5
53.75°	5	5	5	5	5	5	6	5	5	5	5
52.5°	6	6	6	6	6	6	6	6	6	6	6
51.25°	6	6	6	6	6	6	7	6	6	6	6
50°	7	7	7	7	7	7	7	7	7	7	7
48.75°	8	8	8	8	8	8	8	8	8	8	8
47.5°	9	9	9	9	9	9	9	9	9	9	9
46.25°	10	10	10	10	10	10	10	10	10	10	10
45°	11	11	11	11	11	11	11	11	11	11	11
43.75°	12	13	13	13	13	13	14	13	13	13	13
42.5°	15	15	16	16	16	16	16	16	16	16	16
41.25°	18	18	18	19	19	19	19	19	19	19	18
40°	21	21	21	22	22	22	22	22	22	22	21
38.75°	24	25	26	26	26	26	27	26	26	26	26
37.5°	29	29	30	30	31	31	31	31	31	30	30
36.25°	34	35	36	36	37	37	37	37	37	36	36
35°	40	41	42	42	43	43	43	43	43	42	42



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	47	48	50	51	51	52	52	52	51	51	50
32.5°	56	57	59	60	60	61	61	61	60	60	59
31.25°	66	68	70	71	73	73	74	73	73	71	70
30°	78	80	82	84	85	86	86	86	85	84	82
28.75°	90	94	96	98	100	101	101	101	100	98	96
27.5°	105	109	112	114	116	117	118	117	116	114	112
26.25°	121	125	128	131	133	134	135	134	133	131	128
25°	138	142	147	150	152	154	154	154	152	150	147
23.75°	157	162	166	170	172	174	175	174	172	170	166
22.5°	176	182	188	192	195	197	198	197	195	192	188
21.25°	198	206	212	217	220	222	223	222	220	217	212
20°	222	230	237	243	248	250	251	250	248	243	237
18.75°	248	258	266	273	278	281	282	281	278	273	266
17.5°	276	287	296	303	309	312	313	312	309	303	296
16.25°	304	316	326	335	341	345	346	345	341	335	326
15°	333	347	359	369	376	381	382	381	376	369	359
13.75°	364	380	393	403	411	416	417	416	411	403	393
12.5°	395	411	426	438	447	452	454	452	447	438	426
11.25°	425	444	460	473	483	489	492	489	483	473	460
10°	455	476	494	509	521	529	531	529	521	509	494
8.75°	484	507	529	546	558	566	569	566	558	546	529
7.5°	512	538	561	580	594	602	605	602	594	580	561
6.25°	538	566	591	611	626	635	638	635	626	611	591
5°	561	591	617	638	653	662	665	662	653	638	617
3.75°	580	611	638	659	674	684	686	684	674	659	638
2.5°	594	626	653	674	689	698	702	698	689	674	653
1.25°	602	635	662	684	698	709	713	709	698	684	662
0°	605	638	665	686	702	713	720	713	702	686	665
-1.25°	602	635	662	684	698	709	713	709	698	684	662
-2.5°	594	626	653	674	689	698	702	698	689	674	653
-3.75°	580	611	638	659	674	684	686	684	674	659	638
-5°	561	591	617	638	653	662	665	662	653	638	617
-6.25°	538	566	591	611	626	635	638	635	626	611	591
-7.5°	512	538	561	580	594	602	605	602	594	580	561
-8.75°	484	507	529	546	558	566	569	566	558	546	529
-10°	455	476	494	509	521	529	531	529	521	509	494
-11.25°	425	444	460	473	483	489	492	489	483	473	460
-12.5°	395	411	426	438	447	452	454	452	447	438	426
-13.75°	364	380	393	403	411	416	417	416	411	403	393
-15°	333	347	359	369	376	381	382	381	376	369	359
-16.25°	304	316	326	335	341	345	346	345	341	335	326
-17.5°	276	287	296	303	309	312	313	312	309	303	296
-18.75°	248	258	266	273	278	281	282	281	278	273	266
-20°	222	230	237	243	248	250	251	250	248	243	237
-21.25°	198	206	212	217	220	222	223	222	220	217	212



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	176	182	188	192	195	197	198	197	195	192	188
-23.75°	157	162	166	170	172	174	175	174	172	170	166
-25°	138	142	147	150	152	154	154	154	152	150	147
-26.25°	121	125	128	131	133	134	135	134	133	131	128
-27.5°	105	109	112	114	116	117	118	117	116	114	112
-28.75°	90	94	96	98	100	101	101	101	100	98	96
-30°	78	80	82	84	85	86	86	86	85	84	82
-31.25°	66	68	70	71	73	73	74	73	73	71	70
-32.5°	56	57	59	60	60	61	61	61	60	60	59
-33.75°	47	48	50	51	51	52	52	52	51	51	50
-35°	40	41	42	42	43	43	43	43	43	42	42
-36.25°	34	35	36	36	37	37	37	37	37	36	36
-37.5°	29	29	30	30	31	31	31	31	31	30	30
-38.75°	24	25	26	26	26	26	27	26	26	26	26
-40°	21	21	21	22	22	22	22	22	22	22	21
-41.25°	18	18	18	19	19	19	19	19	19	19	18
-42.5°	15	15	16	16	16	16	16	16	16	16	16
-43.75°	12	13	13	13	13	13	14	13	13	13	13
-45°	11	11	11	11	11	11	11	11	11	11	11
-46.25°	10	10	10	10	10	10	10	10	10	10	10
-47.5°	9	9	9	9	9	9	9	9	9	9	9
-48.75°	8	8	8	8	8	8	8	8	8	8	8
-50°	7	7	7	7	7	7	7	7	7	7	7
-51.25°	6	6	6	6	6	6	7	6	6	6	6
-52.5°	6	6	6	6	6	6	6	6	6	6	6
-53.75°	5	5	5	5	5	5	6	5	5	5	5
-55°	5	5	5	5	5	5	5	5	5	5	5
-56.25°	4	4	4	4	4	4	5	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	4	4	4
-58.75°	3	3	3	3	3	3	4	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	3	3
-63.75°	2	2	2	2	2	2	3	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	2	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	1	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	1
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	3	3	3	3	3	3	3	3	3	2	2
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	4	4	4	4	4	4	4	4	3	3	3
56.25°	4	4	4	4	4	4	4	4	4	4	4
55°	5	5	5	5	5	5	5	4	4	4	4
53.75°	5	5	5	5	5	5	5	5	5	5	5
52.5°	6	6	6	6	6	6	6	5	5	5	5
51.25°	6	6	6	6	6	6	6	6	6	6	6
50°	7	7	7	7	7	7	6	6	6	6	6
48.75°	8	8	8	7	7	7	7	7	7	7	6
47.5°	9	9	9	8	8	8	8	8	7	7	7
46.25°	10	10	9	9	9	9	9	9	8	8	8
45°	11	11	10	10	10	10	10	9	9	9	9
43.75°	13	12	12	12	11	11	11	10	10	10	10
42.5°	15	15	15	14	14	13	12	12	11	11	10
41.25°	18	18	17	17	16	15	15	14	13	13	12
40°	21	21	20	20	19	18	17	17	16	15	14
38.75°	25	24	24	23	22	21	20	19	18	17	16
37.5°	29	29	28	27	26	25	23	22	21	20	19
36.25°	35	34	33	31	30	29	28	26	25	23	21
35°	41	40	38	37	36	34	32	30	29	27	25



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	48	47	45	43	41	39	38	35	33	31	29
32.5°	57	56	54	51	49	46	43	41	39	36	33
31.25°	68	66	63	60	57	54	51	48	44	41	38
30°	80	78	75	71	67	63	59	56	52	48	44
28.75°	94	90	87	83	79	75	70	65	60	55	51
27.5°	109	105	101	96	91	86	81	76	70	64	58
26.25°	125	121	117	111	106	100	93	86	80	74	67
25°	142	138	132	127	121	114	107	99	92	84	77
23.75°	162	157	150	143	136	129	121	113	104	96	87
22.5°	182	176	169	162	154	145	135	126	117	108	98
21.25°	206	198	190	181	171	162	152	141	131	121	110
20°	230	222	213	203	191	180	168	157	145	133	122
18.75°	258	248	237	225	213	200	186	173	160	147	134
17.5°	287	276	263	249	235	220	206	190	175	161	147
16.25°	316	304	290	276	259	242	225	208	192	175	160
15°	347	333	318	301	284	265	245	226	208	190	173
13.75°	380	364	346	327	308	288	267	245	225	206	186
12.5°	411	395	376	354	333	310	288	265	242	220	200
11.25°	444	425	404	382	357	333	308	284	259	235	213
10°	476	455	432	407	382	354	327	301	276	249	225
8.75°	507	484	458	432	404	376	346	318	290	263	237
7.5°	538	512	484	455	425	395	364	333	304	276	248
6.25°	566	538	507	476	444	411	380	347	316	287	258
5°	591	561	529	494	460	426	393	359	326	296	266
3.75°	611	580	546	509	473	438	403	369	335	303	273
2.5°	626	594	558	521	483	447	411	376	341	309	278
1.25°	635	602	566	529	489	452	416	381	345	312	281
0°	638	605	569	531	492	454	417	382	346	313	282
-1.25°	635	602	566	529	489	452	416	381	345	312	281
-2.5°	626	594	558	521	483	447	411	376	341	309	278
-3.75°	611	580	546	509	473	438	403	369	335	303	273
-5°	591	561	529	494	460	426	393	359	326	296	266
-6.25°	566	538	507	476	444	411	380	347	316	287	258
-7.5°	538	512	484	455	425	395	364	333	304	276	248
-8.75°	507	484	458	432	404	376	346	318	290	263	237
-10°	476	455	432	407	382	354	327	301	276	249	225
-11.25°	444	425	404	382	357	333	308	284	259	235	213
-12.5°	411	395	376	354	333	310	288	265	242	220	200
-13.75°	380	364	346	327	308	288	267	245	225	206	186
-15°	347	333	318	301	284	265	245	226	208	190	173
-16.25°	316	304	290	276	259	242	225	208	192	175	160
-17.5°	287	276	263	249	235	220	206	190	175	161	147
-18.75°	258	248	237	225	213	200	186	173	160	147	134
-20°	230	222	213	203	191	180	168	157	145	133	122
-21.25°	206	198	190	181	171	162	152	141	131	121	110



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	182	176	169	162	154	145	135	126	117	108	98
-23.75°	162	157	150	143	136	129	121	113	104	96	87
-25°	142	138	132	127	121	114	107	99	92	84	77
-26.25°	125	121	117	111	106	100	93	86	80	74	67
-27.5°	109	105	101	96	91	86	81	76	70	64	58
-28.75°	94	90	87	83	79	75	70	65	60	55	51
-30°	80	78	75	71	67	63	59	56	52	48	44
-31.25°	68	66	63	60	57	54	51	48	44	41	38
-32.5°	57	56	54	51	49	46	43	41	39	36	33
-33.75°	48	47	45	43	41	39	38	35	33	31	29
-35°	41	40	38	37	36	34	32	30	29	27	25
-36.25°	35	34	33	31	30	29	28	26	25	23	21
-37.5°	29	29	28	27	26	25	23	22	21	20	19
-38.75°	25	24	24	23	22	21	20	19	18	17	16
-40°	21	21	20	20	19	18	17	17	16	15	14
-41.25°	18	18	17	17	16	15	15	14	13	13	12
-42.5°	15	15	15	14	14	13	12	12	11	11	10
-43.75°	13	12	12	12	11	11	11	10	10	10	10
-45°	11	11	10	10	10	10	10	9	9	9	9
-46.25°	10	10	9	9	9	9	9	9	8	8	8
-47.5°	9	9	9	8	8	8	8	8	7	7	7
-48.75°	8	8	8	7	7	7	7	7	7	7	6
-50°	7	7	7	7	7	7	6	6	6	6	6
-51.25°	6	6	6	6	6	6	6	6	6	6	6
-52.5°	6	6	6	6	6	6	6	5	5	5	5
-53.75°	5	5	5	5	5	5	5	5	5	5	5
-55°	5	5	5	5	5	5	5	4	4	4	4
-56.25°	4	4	4	4	4	4	4	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	1	1	0	0	0
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	2	2	2	1	1	1	1	1	1
65°	2	2	2	2	2	2	2	2	2	1	1
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	3	3	3	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	2	2	2	2
58.75°	3	3	3	3	3	3	3	3	3	3	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	4	3	3	3	3	3	3	3	3	3	3
55°	4	4	4	4	4	3	3	3	3	3	3
53.75°	5	4	4	4	4	4	4	3	3	3	3
52.5°	5	5	5	5	4	4	4	4	4	4	3
51.25°	5	5	5	5	5	5	4	4	4	4	4
50°	6	6	6	5	5	5	5	5	5	4	4
48.75°	6	6	6	6	6	6	5	5	5	5	5
47.5°	7	7	6	6	6	6	6	6	5	5	5
46.25°	7	7	7	7	7	6	6	6	6	5	5
45°	8	8	8	7	7	7	7	6	6	6	6
43.75°	9	9	8	8	8	7	7	7	6	6	6
42.5°	10	10	9	9	9	8	8	7	7	7	6
41.25°	11	11	10	10	9	9	8	8	8	7	7
40°	13	12	11	11	10	10	9	9	8	8	7
38.75°	15	14	13	12	11	11	10	10	9	8	8
37.5°	18	16	15	14	13	12	11	10	10	9	9
36.25°	20	19	18	16	15	14	12	11	10	10	9
35°	23	21	20	19	17	16	14	13	11	11	10



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	27	25	23	21	19	18	16	15	13	12	11
32.5°	31	29	26	24	22	20	18	16	15	13	12
31.25°	36	33	30	27	25	22	20	19	17	15	13
30°	40	37	34	31	28	25	23	21	19	17	15
28.75°	46	42	39	35	32	29	26	23	21	19	16
27.5°	54	48	43	40	36	32	29	26	23	20	18
26.25°	61	55	50	44	40	36	32	29	25	22	20
25°	70	62	56	51	45	40	36	32	28	25	22
23.75°	79	71	63	57	51	44	40	35	31	27	24
22.5°	89	80	72	63	56	50	43	39	34	30	26
21.25°	100	90	80	71	62	55	48	42	37	33	29
20°	111	100	89	79	70	61	54	46	40	36	31
18.75°	122	110	98	87	77	67	58	51	44	38	33
17.5°	133	121	108	96	84	74	64	55	48	41	36
16.25°	145	131	117	104	92	80	70	60	52	44	39
15°	157	141	126	113	99	86	76	65	56	48	41
13.75°	168	152	135	121	107	93	81	70	59	51	43
12.5°	180	162	145	129	114	100	86	75	63	54	46
11.25°	191	171	154	136	121	106	91	79	67	57	49
10°	203	181	162	143	127	111	96	83	71	60	51
8.75°	213	190	169	150	132	117	101	87	75	63	54
7.5°	222	198	176	157	138	121	105	90	78	66	56
6.25°	230	206	182	162	142	125	109	94	80	68	57
5°	237	212	188	166	147	128	112	96	82	70	59
3.75°	243	217	192	170	150	131	114	98	84	71	60
2.5°	248	220	195	172	152	133	116	100	85	73	60
1.25°	250	222	197	174	154	134	117	101	86	73	61
0°	251	223	198	175	154	135	118	101	86	74	61
-1.25°	250	222	197	174	154	134	117	101	86	73	61
-2.5°	248	220	195	172	152	133	116	100	85	73	60
-3.75°	243	217	192	170	150	131	114	98	84	71	60
-5°	237	212	188	166	147	128	112	96	82	70	59
-6.25°	230	206	182	162	142	125	109	94	80	68	57
-7.5°	222	198	176	157	138	121	105	90	78	66	56
-8.75°	213	190	169	150	132	117	101	87	75	63	54
-10°	203	181	162	143	127	111	96	83	71	60	51
-11.25°	191	171	154	136	121	106	91	79	67	57	49
-12.5°	180	162	145	129	114	100	86	75	63	54	46
-13.75°	168	152	135	121	107	93	81	70	59	51	43
-15°	157	141	126	113	99	86	76	65	56	48	41
-16.25°	145	131	117	104	92	80	70	60	52	44	39
-17.5°	133	121	108	96	84	74	64	55	48	41	36
-18.75°	122	110	98	87	77	67	58	51	44	38	33
-20°	111	100	89	79	70	61	54	46	40	36	31
-21.25°	100	90	80	71	62	55	48	42	37	33	29



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	89	80	72	63	56	50	43	39	34	30	26
-23.75°	79	71	63	57	51	44	40	35	31	27	24
-25°	70	62	56	51	45	40	36	32	28	25	22
-26.25°	61	55	50	44	40	36	32	29	25	22	20
-27.5°	54	48	43	40	36	32	29	26	23	20	18
-28.75°	46	42	39	35	32	29	26	23	21	19	16
-30°	40	37	34	31	28	25	23	21	19	17	15
-31.25°	36	33	30	27	25	22	20	19	17	15	13
-32.5°	31	29	26	24	22	20	18	16	15	13	12
-33.75°	27	25	23	21	19	18	16	15	13	12	11
-35°	23	21	20	19	17	16	14	13	11	11	10
-36.25°	20	19	18	16	15	14	12	11	10	10	9
-37.5°	18	16	15	14	13	12	11	10	10	9	9
-38.75°	15	14	13	12	11	11	10	10	9	8	8
-40°	13	12	11	11	10	10	9	9	8	8	7
-41.25°	11	11	10	10	9	9	8	8	8	7	7
-42.5°	10	10	9	9	9	8	8	7	7	7	6
-43.75°	9	9	8	8	8	7	7	7	6	6	6
-45°	8	8	8	7	7	7	7	6	6	6	6
-46.25°	7	7	7	7	7	6	6	6	6	5	5
-47.5°	7	7	6	6	6	6	6	6	5	5	5
-48.75°	6	6	6	6	6	6	5	5	5	5	5
-50°	6	6	6	5	5	5	5	5	5	4	4
-51.25°	5	5	5	5	5	5	4	4	4	4	4
-52.5°	5	5	5	5	4	4	4	4	4	4	3
-53.75°	5	4	4	4	4	4	4	3	3	3	3
-55°	4	4	4	4	4	3	3	3	3	3	3
-56.25°	4	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	2
-60°	3	3	3	3	3	3	3	2	2	2	2
-61.25°	3	3	3	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	1	1
-66.25°	2	2	2	2	2	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	1	1	1	1	1	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	2	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	1
57.5°	3	2	2	2	2	2	2	2	2	2	2
56.25°	3	3	3	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	3	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	4	3	3	3	3	3	3	3	3	3	2
50°	4	4	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	4	3	3	3	3	3	3	3
47.5°	5	4	4	4	4	3	3	3	3	3	3
46.25°	5	5	5	4	4	4	4	3	3	3	3
45°	5	5	5	5	4	4	4	4	3	3	3
43.75°	6	6	5	5	5	4	4	4	4	3	3
42.5°	6	6	6	5	5	5	4	4	4	4	3
41.25°	6	6	6	6	5	5	5	4	4	4	4
40°	7	7	6	6	6	5	5	5	4	4	4
38.75°	7	7	7	6	6	6	5	5	5	4	4
37.5°	8	7	7	7	6	6	6	5	5	5	4
36.25°	9	8	7	7	7	6	6	6	5	5	5
35°	9	9	8	7	7	7	6	6	6	5	5



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	10	9	9	8	7	7	6	6	6	5	5
32.5°	11	10	9	9	8	7	7	6	6	6	5
31.25°	12	11	10	9	8	8	7	7	6	6	5
30°	13	11	10	10	9	8	8	7	6	6	6
28.75°	15	13	11	10	10	9	8	7	7	6	6
27.5°	16	14	12	11	10	9	8	8	7	7	6
26.25°	18	16	14	12	11	10	9	8	7	7	6
25°	19	17	15	13	11	10	9	9	8	7	7
23.75°	21	19	16	14	12	11	10	9	8	7	7
22.5°	23	20	18	15	13	11	10	9	8	8	7
21.25°	25	21	19	16	14	12	11	10	9	8	7
20°	27	23	20	18	15	13	11	10	9	8	7
18.75°	29	25	21	19	16	14	12	10	10	9	8
17.5°	31	27	23	20	17	15	13	11	10	9	8
16.25°	33	29	25	21	18	16	13	11	10	9	8
15°	35	30	26	22	19	17	14	12	10	9	9
13.75°	38	32	28	23	20	17	15	12	11	10	9
12.5°	39	34	29	25	21	18	15	13	11	10	9
11.25°	41	36	30	26	22	19	16	14	11	10	9
10°	43	37	31	27	23	20	17	14	12	10	9
8.75°	45	38	33	28	24	20	17	15	12	10	9
7.5°	47	40	34	29	24	21	18	15	12	11	10
6.25°	48	41	35	29	25	21	18	15	13	11	10
5°	50	42	36	30	26	21	18	16	13	11	10
3.75°	51	42	36	30	26	22	19	16	13	11	10
2.5°	51	43	37	31	26	22	19	16	13	11	10
1.25°	52	43	37	31	26	22	19	16	13	11	10
0°	52	43	37	31	27	22	19	16	14	11	10
-1.25°	52	43	37	31	26	22	19	16	13	11	10
-2.5°	51	43	37	31	26	22	19	16	13	11	10
-3.75°	51	42	36	30	26	22	19	16	13	11	10
-5°	50	42	36	30	26	21	18	16	13	11	10
-6.25°	48	41	35	29	25	21	18	15	13	11	10
-7.5°	47	40	34	29	24	21	18	15	12	11	10
-8.75°	45	38	33	28	24	20	17	15	12	10	9
-10°	43	37	31	27	23	20	17	14	12	10	9
-11.25°	41	36	30	26	22	19	16	14	11	10	9
-12.5°	39	34	29	25	21	18	15	13	11	10	9
-13.75°	38	32	28	23	20	17	15	12	11	10	9
-15°	35	30	26	22	19	17	14	12	10	9	9
-16.25°	33	29	25	21	18	16	13	11	10	9	8
-17.5°	31	27	23	20	17	15	13	11	10	9	8
-18.75°	29	25	21	19	16	14	12	10	10	9	8
-20°	27	23	20	18	15	13	11	10	9	8	7
-21.25°	25	21	19	16	14	12	11	10	9	8	7



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	23	20	18	15	13	11	10	9	8	8	7
-23.75°	21	19	16	14	12	11	10	9	8	7	7
-25°	19	17	15	13	11	10	9	9	8	7	7
-26.25°	18	16	14	12	11	10	9	8	7	7	6
-27.5°	16	14	12	11	10	9	8	8	7	7	6
-28.75°	15	13	11	10	10	9	8	7	7	6	6
-30°	13	11	10	10	9	8	8	7	6	6	6
-31.25°	12	11	10	9	8	8	7	7	6	6	5
-32.5°	11	10	9	9	8	7	7	6	6	6	5
-33.75°	10	9	9	8	7	7	6	6	6	5	5
-35°	9	9	8	7	7	7	6	6	6	5	5
-36.25°	9	8	7	7	7	6	6	6	5	5	5
-37.5°	8	7	7	7	6	6	6	5	5	5	4
-38.75°	7	7	7	6	6	6	5	5	5	4	4
-40°	7	7	6	6	6	5	5	5	4	4	4
-41.25°	6	6	6	6	5	5	5	4	4	4	4
-42.5°	6	6	6	5	5	5	4	4	4	4	3
-43.75°	6	6	5	5	5	4	4	4	4	3	3
-45°	5	5	5	5	4	4	4	4	3	3	3
-46.25°	5	5	5	4	4	4	4	3	3	3	3
-47.5°	5	4	4	4	4	3	3	3	3	3	3
-48.75°	4	4	4	4	3	3	3	3	3	3	3
-50°	4	4	3	3	3	3	3	3	3	3	3
-51.25°	4	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	3	2	2	2	2
-55°	3	3	3	3	3	2	2	2	2	2	2
-56.25°	3	3	3	2	2	2	2	2	2	2	2
-57.5°	3	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	1
-60°	2	2	2	2	2	2	2	2	1	1	1
-61.25°	2	2	2	2	2	2	1	1	1	1	1
-62.5°	2	2	2	2	1	1	1	1	1	1	1
-63.75°	2	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	1	1	1	1	1	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	0
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	1	1	1	1	1	1	1	1	1
55°	2	2	2	1	1	1	1	1	1	1	1
53.75°	2	2	2	2	1	1	1	1	1	1	1
52.5°	2	2	2	2	2	1	1	1	1	1	1
51.25°	2	2	2	2	2	2	1	1	1	1	1
50°	2	2	2	2	2	2	2	1	1	1	1
48.75°	3	2	2	2	2	2	2	2	1	1	1
47.5°	3	3	2	2	2	2	2	2	2	1	1
46.25°	3	3	3	2	2	2	2	2	2	1	1
45°	3	3	3	3	2	2	2	2	2	2	1
43.75°	3	3	3	3	2	2	2	2	2	2	1
42.5°	3	3	3	3	3	2	2	2	2	2	2
41.25°	3	3	3	3	3	3	2	2	2	2	2
40°	3	3	3	3	3	3	2	2	2	2	2
38.75°	4	3	3	3	3	3	3	2	2	2	2
37.5°	4	4	3	3	3	3	3	2	2	2	2
36.25°	4	4	3	3	3	3	3	3	2	2	2
35°	4	4	4	3	3	3	3	3	2	2	2



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	5	4	4	4	3	3	3	3	3	2	2
32.5°	5	5	4	4	3	3	3	3	3	2	2
31.25°	5	5	4	4	4	3	3	3	3	3	2
30°	5	5	5	4	4	3	3	3	3	3	2
28.75°	6	5	5	4	4	3	3	3	3	3	2
27.5°	6	5	5	4	4	4	3	3	3	3	3
26.25°	6	6	5	5	4	4	3	3	3	3	3
25°	6	6	5	5	4	4	4	3	3	3	3
23.75°	6	6	5	5	5	4	4	3	3	3	3
22.5°	6	6	6	5	5	4	4	3	3	3	3
21.25°	7	6	6	5	5	4	4	3	3	3	3
20°	7	6	6	5	5	5	4	4	3	3	3
18.75°	7	6	6	6	5	5	4	4	3	3	3
17.5°	7	7	6	6	5	5	4	4	3	3	3
16.25°	7	7	6	6	5	5	4	4	3	3	3
15°	8	7	6	6	5	5	4	4	4	3	3
13.75°	8	7	6	6	6	5	5	4	4	3	3
12.5°	8	7	7	6	6	5	5	4	4	3	3
11.25°	8	7	7	6	6	5	5	4	4	3	3
10°	8	7	7	6	6	5	5	4	4	3	3
8.75°	9	8	7	6	6	5	5	4	4	3	3
7.5°	9	8	7	6	6	5	5	4	4	3	3
6.25°	9	8	7	6	6	5	5	4	4	3	3
5°	9	8	7	6	6	5	5	4	4	3	3
3.75°	9	8	7	6	6	5	5	4	4	3	3
2.5°	9	8	7	6	6	5	5	4	4	3	3
1.25°	9	8	7	6	6	5	5	4	4	3	3
0°	9	8	7	7	6	6	5	5	4	4	3
-1.25°	9	8	7	6	6	5	5	4	4	3	3
-2.5°	9	8	7	6	6	5	5	4	4	3	3
-3.75°	9	8	7	6	6	5	5	4	4	3	3
-5°	9	8	7	6	6	5	5	4	4	3	3
-6.25°	9	8	7	6	6	5	5	4	4	3	3
-7.5°	9	8	7	6	6	5	5	4	4	3	3
-8.75°	9	8	7	6	6	5	5	4	4	3	3
-10°	8	7	7	6	6	5	5	4	4	3	3
-11.25°	8	7	7	6	6	5	5	4	4	3	3
-12.5°	8	7	7	6	6	5	5	4	4	3	3
-13.75°	8	7	6	6	6	5	5	4	4	3	3
-15°	8	7	6	6	5	5	4	4	4	3	3
-16.25°	7	7	6	6	5	5	4	4	3	3	3
-17.5°	7	7	6	6	5	5	4	4	3	3	3
-18.75°	7	6	6	6	5	5	4	4	3	3	3
-20°	7	6	6	5	5	5	4	4	3	3	3
-21.25°	7	6	6	5	5	4	4	3	3	3	3



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	6	6	6	5	5	4	4	3	3	3	3
-23.75°	6	6	5	5	5	4	4	3	3	3	3
-25°	6	6	5	5	4	4	4	3	3	3	3
-26.25°	6	6	5	5	4	4	3	3	3	3	3
-27.5°	6	5	5	4	4	4	3	3	3	3	3
-28.75°	6	5	5	4	4	3	3	3	3	3	2
-30°	5	5	5	4	4	3	3	3	3	3	2
-31.25°	5	5	4	4	4	3	3	3	3	3	2
-32.5°	5	5	4	4	3	3	3	3	3	2	2
-33.75°	5	4	4	4	3	3	3	3	3	2	2
-35°	4	4	4	3	3	3	3	3	2	2	2
-36.25°	4	4	3	3	3	3	3	3	2	2	2
-37.5°	4	4	3	3	3	3	3	2	2	2	2
-38.75°	4	3	3	3	3	3	3	2	2	2	2
-40°	3	3	3	3	3	3	2	2	2	2	2
-41.25°	3	3	3	3	3	3	2	2	2	2	2
-42.5°	3	3	3	3	3	2	2	2	2	2	2
-43.75°	3	3	3	3	2	2	2	2	2	2	1
-45°	3	3	3	3	2	2	2	2	2	2	1
-46.25°	3	3	3	2	2	2	2	2	2	1	1
-47.5°	3	3	2	2	2	2	2	2	2	1	1
-48.75°	3	2	2	2	2	2	2	2	1	1	1
-50°	2	2	2	2	2	2	2	1	1	1	1
-51.25°	2	2	2	2	2	2	1	1	1	1	1
-52.5°	2	2	2	2	2	1	1	1	1	1	1
-53.75°	2	2	2	2	1	1	1	1	1	1	1
-55°	2	2	2	1	1	1	1	1	1	1	1
-56.25°	2	2	1	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	0
-73.75°	1	1	1	1	1	1	1	1	0	0	0
-75°	1	1	1	1	1	1	0	0	0	0	0
-76.25°	1	1	1	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	1	0	0	0	0	0	0	0	0	0	0
70°	1	1	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	0	0	0	0	0	0	0
67.5°	1	1	1	1	1	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	0	0	0	0	0
65°	1	1	1	1	1	1	1	0	0	0	0
63.75°	1	1	1	1	1	1	1	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	0	0	0
61.25°	1	1	1	1	1	1	1	1	1	0	0
60°	1	1	1	1	1	1	1	1	1	0	0
58.75°	1	1	1	1	1	1	1	1	1	1	0
57.5°	1	1	1	1	1	1	1	1	1	1	0
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	2	1	1	1	1	1	1	1	1	1	1
38.75°	2	1	1	1	1	1	1	1	1	1	1
37.5°	2	2	1	1	1	1	1	1	1	1	1
36.25°	2	2	1	1	1	1	1	1	1	1	1
35°	2	2	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	2	1	1	1	1	1	1	1	1
32.5°	2	2	2	1	1	1	1	1	1	1	1
31.25°	2	2	2	1	1	1	1	1	1	1	1
30°	2	2	2	2	1	1	1	1	1	1	1
28.75°	2	2	2	2	1	1	1	1	1	1	1
27.5°	2	2	2	2	1	1	1	1	1	1	1
26.25°	2	2	2	2	1	1	1	1	1	1	1
25°	2	2	2	2	2	1	1	1	1	1	1
23.75°	2	2	2	2	2	1	1	1	1	1	1
22.5°	3	2	2	2	2	1	1	1	1	1	1
21.25°	3	2	2	2	2	1	1	1	1	1	1
20°	3	2	2	2	2	1	1	1	1	1	1
18.75°	3	2	2	2	2	1	1	1	1	1	1
17.5°	3	2	2	2	2	2	1	1	1	1	1
16.25°	3	3	2	2	2	2	1	1	1	1	1
15°	3	3	2	2	2	2	1	1	1	1	1
13.75°	3	3	2	2	2	2	1	1	1	1	1
12.5°	3	3	2	2	2	2	1	1	1	1	1
11.25°	3	3	2	2	2	2	1	1	1	1	1
10°	3	3	2	2	2	2	1	1	1	1	1
8.75°	3	3	2	2	2	2	1	1	1	1	1
7.5°	3	3	2	2	2	2	1	1	1	1	1
6.25°	3	3	2	2	2	2	1	1	1	1	1
5°	3	3	2	2	2	2	1	1	1	1	1
3.75°	3	3	2	2	2	2	1	1	1	1	1
2.5°	3	3	2	2	2	2	1	1	1	1	1
1.25°	3	3	2	2	2	2	1	1	1	1	1
0°	3	3	3	2	2	2	2	1	1	1	1
-1.25°	3	3	2	2	2	2	1	1	1	1	1
-2.5°	3	3	2	2	2	2	1	1	1	1	1
-3.75°	3	3	2	2	2	2	1	1	1	1	1
-5°	3	3	2	2	2	2	1	1	1	1	1
-6.25°	3	3	2	2	2	2	1	1	1	1	1
-7.5°	3	3	2	2	2	2	1	1	1	1	1
-8.75°	3	3	2	2	2	2	1	1	1	1	1
-10°	3	3	2	2	2	2	1	1	1	1	1
-11.25°	3	3	2	2	2	2	1	1	1	1	1
-12.5°	3	3	2	2	2	2	1	1	1	1	1
-13.75°	3	3	2	2	2	2	1	1	1	1	1
-15°	3	3	2	2	2	2	1	1	1	1	1
-16.25°	3	3	2	2	2	2	1	1	1	1	1
-17.5°	3	2	2	2	2	2	1	1	1	1	1
-18.75°	3	2	2	2	2	1	1	1	1	1	1
-20°	3	2	2	2	2	1	1	1	1	1	1
-21.25°	3	2	2	2	2	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	3	2	2	2	2	1	1	1	1	1	1
-23.75°	2	2	2	2	2	1	1	1	1	1	1
-25°	2	2	2	2	2	1	1	1	1	1	1
-26.25°	2	2	2	2	1	1	1	1	1	1	1
-27.5°	2	2	2	2	1	1	1	1	1	1	1
-28.75°	2	2	2	2	1	1	1	1	1	1	1
-30°	2	2	2	2	1	1	1	1	1	1	1
-31.25°	2	2	2	1	1	1	1	1	1	1	1
-32.5°	2	2	2	1	1	1	1	1	1	1	1
-33.75°	2	2	2	1	1	1	1	1	1	1	1
-35°	2	2	1	1	1	1	1	1	1	1	1
-36.25°	2	2	1	1	1	1	1	1	1	1	1
-37.5°	2	2	1	1	1	1	1	1	1	1	1
-38.75°	2	1	1	1	1	1	1	1	1	1	1
-40°	2	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	0
-58.75°	1	1	1	1	1	1	1	1	1	1	0
-60°	1	1	1	1	1	1	1	1	1	0	0
-61.25°	1	1	1	1	1	1	1	1	1	0	0
-62.5°	1	1	1	1	1	1	1	1	0	0	0
-63.75°	1	1	1	1	1	1	1	0	0	0	0
-65°	1	1	1	1	1	1	1	0	0	0	0
-66.25°	1	1	1	1	1	1	0	0	0	0	0
-67.5°	1	1	1	1	1	0	0	0	0	0	0
-68.75°	1	1	1	1	0	0	0	0	0	0	0
-70°	1	1	0	0	0	0	0	0	0	0	0
-71.25°	1	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	1	0	0	0	0	0	0	0	0	0	0
52.5°	1	0	0	0	0	0	0	0	0	0	0
51.25°	1	0	0	0	0	0	0	0	0	0	0
50°	1	1	0	0	0	0	0	0	0	0	0
48.75°	1	1	0	0	0	0	0	0	0	0	0
47.5°	1	1	0	0	0	0	0	0	0	0	0
46.25°	1	1	0	0	0	0	0	0	0	0	0
45°	1	1	1	0	0	0	0	0	0	0	0
43.75°	1	1	1	0	0	0	0	0	0	0	0
42.5°	1	1	1	0	0	0	0	0	0	0	0
41.25°	1	1	1	0	0	0	0	0	0	0	0
40°	1	1	1	0	0	0	0	0	0	0	0
38.75°	1	1	1	1	0	0	0	0	0	0	0
37.5°	1	1	1	1	0	0	0	0	0	0	0
36.25°	1	1	1	1	0	0	0	0	0	0	0
35°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	1	0	0	0	0	0	0
27.5°	1	1	1	1	1	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	0	0	0	0	0	0
21.25°	1	1	1	1	1	0	0	0	0	0	0
20°	1	1	1	1	1	0	0	0	0	0	0
18.75°	1	1	1	1	1	0	0	0	0	0	0
17.5°	1	1	1	1	1	0	0	0	0	0	0
16.25°	1	1	1	1	1	0	0	0	0	0	0
15°	1	1	1	1	1	0	0	0	0	0	0
13.75°	1	1	1	1	1	0	0	0	0	0	0
12.5°	1	1	1	1	1	0	0	0	0	0	0
11.25°	1	1	1	1	1	0	0	0	0	0	0
10°	1	1	1	1	1	0	0	0	0	0	0
8.75°	1	1	1	1	1	0	0	0	0	0	0
7.5°	1	1	1	1	1	0	0	0	0	0	0
6.25°	1	1	1	1	1	0	0	0	0	0	0
5°	1	1	1	1	1	0	0	0	0	0	0
3.75°	1	1	1	1	1	0	0	0	0	0	0
2.5°	1	1	1	1	1	0	0	0	0	0	0
1.25°	1	1	1	1	1	0	0	0	0	0	0
0°	1	1	1	1	1	1	0	0	0	0	0
-1.25°	1	1	1	1	1	0	0	0	0	0	0
-2.5°	1	1	1	1	1	0	0	0	0	0	0
-3.75°	1	1	1	1	1	0	0	0	0	0	0
-5°	1	1	1	1	1	0	0	0	0	0	0
-6.25°	1	1	1	1	1	0	0	0	0	0	0
-7.5°	1	1	1	1	1	0	0	0	0	0	0
-8.75°	1	1	1	1	1	0	0	0	0	0	0
-10°	1	1	1	1	1	0	0	0	0	0	0
-11.25°	1	1	1	1	1	0	0	0	0	0	0
-12.5°	1	1	1	1	1	0	0	0	0	0	0
-13.75°	1	1	1	1	1	0	0	0	0	0	0
-15°	1	1	1	1	1	0	0	0	0	0	0
-16.25°	1	1	1	1	1	0	0	0	0	0	0
-17.5°	1	1	1	1	1	0	0	0	0	0	0
-18.75°	1	1	1	1	1	0	0	0	0	0	0
-20°	1	1	1	1	1	0	0	0	0	0	0
-21.25°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	0	0	0	0	0	0
-23.75°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	1	0	0	0	0	0	0
-28.75°	1	1	1	1	1	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	1	0	0	0	0	0	0	0
-36.25°	1	1	1	1	0	0	0	0	0	0	0
-37.5°	1	1	1	1	0	0	0	0	0	0	0
-38.75°	1	1	1	1	0	0	0	0	0	0	0
-40°	1	1	1	0	0	0	0	0	0	0	0
-41.25°	1	1	1	0	0	0	0	0	0	0	0
-42.5°	1	1	1	0	0	0	0	0	0	0	0
-43.75°	1	1	1	0	0	0	0	0	0	0	0
-45°	1	1	1	0	0	0	0	0	0	0	0
-46.25°	1	1	0	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	1	0	0	0	0	0	0	0	0	0
-50°	1	1	0	0	0	0	0	0	0	0	0
-51.25°	1	0	0	0	0	0	0	0	0	0	0
-52.5°	1	0	0	0	0	0	0	0	0	0	0
-53.75°	1	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-40 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)