

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4025-12-CS-LSL**

Test Date: 04/05/18

Test Information


Test Method: LM-79-08
Report Number: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-41)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/05/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4025-12-CS-LSL
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, LINEAR SPREAD LENS
Light Source: (1) SORAA 4000K 90 CRI LED
SM16-07-25D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	5H x 4V
Luminaire Lumens:	311.9 lumens	Max Intensity:	793.7 candela
Efficiency:	N/A	Max Intensity Angle:	-18.75°H x 0°V
Efficacy:	42.1 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	55.2°H x 22°V	Field Angle (10%):	72.8°H x 46.1°V
Beam Lumens:	168.8 lumens	Field Lumens:	281.8 lumens
Beam Efficiency:	54.1%	Field Efficiency:	90.4%
Input Watts (W):	7.4		
Input Voltage (V):	12.0		
Input Current (A _{in}):	0.648		
Voltage Rise (V):	NR		
Power Factor:	0.9912		
Total Harmonic Distortion (THDi):	27.0%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	3 HR		
Ambient Temperature (°C):	25.0		
Test Distance:	25 FT		

REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL


Iso-Candela Plot






REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

Lumen Table




REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

Luminous Intensity Plot



Beam:
 H Angle: 55.2°
 V Angle: 22°
 Lumens: 168.8
 Efficiency: 54.1%

Field:
 H Angle: 72.8°
 V Angle: 46.1°
 Lumens: 281.8
 Efficiency: 90.4%

Spill:
 Lumens: 30.1
 Efficiency: 9.6%

— Vertical Distribution through -18.75-Deg
 - - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	1
43.75°	0	0	0	0	0	0	0	0	0	0	1
42.5°	0	0	0	0	0	0	0	0	0	0	1
41.25°	0	0	0	0	0	0	0	0	0	0	1
40°	0	0	0	0	0	0	0	0	0	0	1
38.75°	0	0	0	0	0	0	0	0	0	1	1
37.5°	0	0	0	0	0	0	0	0	0	1	1
36.25°	0	0	0	0	0	0	0	0	0	1	1
35°	0	0	0	0	0	0	0	0	0	1	1



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	0	1	1	1
22.5°	0	0	0	0	0	0	0	0	1	1	1
21.25°	0	0	0	0	0	0	0	0	1	1	1
20°	0	0	0	0	0	0	0	0	1	1	1
18.75°	0	0	0	0	0	0	0	0	1	1	1
17.5°	0	0	0	0	0	0	0	0	1	1	1
16.25°	0	0	0	0	0	0	0	0	1	1	1
15°	0	0	0	0	0	0	0	0	1	1	1
13.75°	0	0	0	0	0	0	0	0	1	1	1
12.5°	0	0	0	0	0	0	0	0	1	1	1
11.25°	0	0	0	0	0	0	0	0	1	1	1
10°	0	0	0	0	0	0	0	0	1	1	1
8.75°	0	0	0	0	0	0	0	0	1	1	1
7.5°	0	0	0	0	0	0	0	0	1	1	1
6.25°	0	0	0	0	0	0	0	0	1	1	1
5°	0	0	0	0	0	0	0	0	1	1	1
3.75°	0	0	0	0	0	0	0	0	1	1	1
2.5°	0	0	0	0	0	0	0	0	1	1	1
1.25°	0	0	0	0	0	0	0	0	1	1	1
0°	0	0	0	0	0	0	0	1	1	1	1
-1.25°	0	0	0	0	0	0	0	0	1	1	1
-2.5°	0	0	0	0	0	0	0	0	1	1	1
-3.75°	0	0	0	0	0	0	0	0	1	1	1
-5°	0	0	0	0	0	0	0	0	1	1	1
-6.25°	0	0	0	0	0	0	0	0	1	1	1
-7.5°	0	0	0	0	0	0	0	0	1	1	1
-8.75°	0	0	0	0	0	0	0	0	1	1	1
-10°	0	0	0	0	0	0	0	0	1	1	1
-11.25°	0	0	0	0	0	0	0	0	1	1	1
-12.5°	0	0	0	0	0	0	0	0	1	1	1
-13.75°	0	0	0	0	0	0	0	0	1	1	1
-15°	0	0	0	0	0	0	0	0	1	1	1
-16.25°	0	0	0	0	0	0	0	0	1	1	1
-17.5°	0	0	0	0	0	0	0	0	1	1	1
-18.75°	0	0	0	0	0	0	0	0	1	1	1
-20°	0	0	0	0	0	0	0	0	1	1	1
-21.25°	0	0	0	0	0	0	0	0	1	1	1



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	1	1	1
-23.75°	0	0	0	0	0	0	0	0	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	1	1	1
-28.75°	0	0	0	0	0	0	0	0	1	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	1	1
-36.25°	0	0	0	0	0	0	0	0	0	1	1
-37.5°	0	0	0	0	0	0	0	0	0	1	1
-38.75°	0	0	0	0	0	0	0	0	0	1	1
-40°	0	0	0	0	0	0	0	0	0	0	1
-41.25°	0	0	0	0	0	0	0	0	0	0	1
-42.5°	0	0	0	0	0	0	0	0	0	0	1
-43.75°	0	0	0	0	0	0	0	0	0	0	1
-45°	0	0	0	0	0	0	0	0	0	0	1
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	1	1
67.5°	0	0	0	0	0	0	0	0	1	1	1
66.25°	0	0	0	0	0	0	0	1	1	1	1
65°	0	0	0	0	0	0	1	1	1	1	1
63.75°	0	0	0	0	0	0	1	1	1	1	1
62.5°	0	0	0	0	0	1	1	1	1	1	1
61.25°	0	0	0	0	1	1	1	1	1	1	1
60°	0	0	0	0	1	1	1	1	1	1	1
58.75°	0	0	0	1	1	1	1	1	1	1	1
57.5°	0	0	0	1	1	1	1	1	1	1	1
56.25°	0	0	1	1	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	1	1
53.75°	0	1	1	1	1	1	1	1	1	1	1
52.5°	0	1	1	1	1	1	1	1	1	1	1
51.25°	0	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	1	1	1
32.5°	1	1	1	1	1	1	1	1	1	1	1
31.25°	1	1	1	1	1	1	1	1	1	1	1
30°	1	1	1	1	1	1	1	1	1	1	1
28.75°	1	1	1	1	1	1	1	1	1	1	1
27.5°	1	1	1	1	1	1	1	1	1	1	2
26.25°	1	1	1	1	1	1	1	1	1	1	2
25°	1	1	1	1	1	1	1	1	1	2	2
23.75°	1	1	1	1	1	1	1	1	1	2	2
22.5°	1	1	1	1	1	1	1	1	1	2	2
21.25°	1	1	1	1	1	1	1	1	1	2	2
20°	1	1	1	1	1	1	1	1	2	2	2
18.75°	1	1	1	1	1	1	1	1	2	2	2
17.5°	1	1	1	1	1	1	1	1	2	2	2
16.25°	1	1	1	1	1	1	1	1	2	2	2
15°	1	1	1	1	1	1	1	1	2	2	2
13.75°	1	1	1	1	1	1	1	2	2	2	2
12.5°	1	1	1	1	1	1	1	2	2	2	2
11.25°	1	1	1	1	1	1	1	2	2	2	2
10°	1	1	1	1	1	1	1	2	2	2	2
8.75°	1	1	1	1	1	1	1	2	2	2	2
7.5°	1	1	1	1	1	1	1	2	2	2	2
6.25°	1	1	1	1	1	1	1	2	2	2	2
5°	1	1	1	1	1	1	1	2	2	2	2
3.75°	1	1	1	1	1	1	1	2	2	2	2
2.5°	1	1	1	1	1	1	1	2	2	2	2
1.25°	1	1	1	1	1	1	1	2	2	2	2
0°	1	1	1	1	1	1	1	2	2	2	2
-1.25°	1	1	1	1	1	1	1	2	2	2	2
-2.5°	1	1	1	1	1	1	1	2	2	2	2
-3.75°	1	1	1	1	1	1	1	2	2	2	2
-5°	1	1	1	1	1	1	1	2	2	2	2
-6.25°	1	1	1	1	1	1	1	2	2	2	2
-7.5°	1	1	1	1	1	1	1	2	2	2	2
-8.75°	1	1	1	1	1	1	1	2	2	2	2
-10°	1	1	1	1	1	1	1	2	2	2	2
-11.25°	1	1	1	1	1	1	1	2	2	2	2
-12.5°	1	1	1	1	1	1	1	2	2	2	2
-13.75°	1	1	1	1	1	1	1	2	2	2	2
-15°	1	1	1	1	1	1	1	1	2	2	2
-16.25°	1	1	1	1	1	1	1	1	2	2	2
-17.5°	1	1	1	1	1	1	1	1	2	2	2
-18.75°	1	1	1	1	1	1	1	1	2	2	2
-20°	1	1	1	1	1	1	1	1	2	2	2
-21.25°	1	1	1	1	1	1	1	1	1	2	2



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	1	1	1	2	2
-23.75°	1	1	1	1	1	1	1	1	1	2	2
-25°	1	1	1	1	1	1	1	1	1	2	2
-26.25°	1	1	1	1	1	1	1	1	1	1	2
-27.5°	1	1	1	1	1	1	1	1	1	1	2
-28.75°	1	1	1	1	1	1	1	1	1	1	1
-30°	1	1	1	1	1	1	1	1	1	1	1
-31.25°	1	1	1	1	1	1	1	1	1	1	1
-32.5°	1	1	1	1	1	1	1	1	1	1	1
-33.75°	1	1	1	1	1	1	1	1	1	1	1
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	0	1	1	1	1	1	1	1	1	1	1
-52.5°	0	1	1	1	1	1	1	1	1	1	1
-53.75°	0	1	1	1	1	1	1	1	1	1	1
-55°	0	0	1	1	1	1	1	1	1	1	1
-56.25°	0	0	1	1	1	1	1	1	1	1	1
-57.5°	0	0	0	1	1	1	1	1	1	1	1
-58.75°	0	0	0	1	1	1	1	1	1	1	1
-60°	0	0	0	0	1	1	1	1	1	1	1
-61.25°	0	0	0	0	1	1	1	1	1	1	1
-62.5°	0	0	0	0	0	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	1	1	1	1	1
-65°	0	0	0	0	0	0	1	1	1	1	1
-66.25°	0	0	0	0	0	0	0	1	1	1	1
-67.5°	0	0	0	0	0	0	0	0	1	1	1
-68.75°	0	0	0	0	0	0	0	0	0	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	1	1	1
71.25°	0	0	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	2
48.75°	1	1	1	1	1	1	1	1	1	2	2
47.5°	1	1	1	1	1	1	1	1	2	2	2
46.25°	1	1	1	1	1	1	1	2	2	2	2
45°	1	1	1	1	1	1	2	2	2	2	2
43.75°	1	1	1	1	1	1	2	2	2	2	2
42.5°	1	1	1	1	1	2	2	2	2	2	2
41.25°	1	1	1	1	2	2	2	2	2	2	2
40°	1	1	1	1	2	2	2	2	2	2	3
38.75°	1	1	1	2	2	2	2	2	2	3	3
37.5°	1	1	1	2	2	2	2	2	2	3	3
36.25°	1	1	2	2	2	2	2	2	3	3	3
35°	1	1	2	2	2	2	2	3	3	3	3



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	2	2	2	2	2	2	3	3	3	3
32.5°	1	2	2	2	2	2	3	3	3	3	3
31.25°	2	2	2	2	2	2	3	3	3	3	3
30°	2	2	2	2	2	3	3	3	3	3	4
28.75°	2	2	2	2	2	3	3	3	3	3	4
27.5°	2	2	2	2	2	3	3	3	3	3	4
26.25°	2	2	2	2	3	3	3	3	3	4	4
25°	2	2	2	2	3	3	3	3	3	4	4
23.75°	2	2	2	2	3	3	3	3	4	4	4
22.5°	2	2	2	2	3	3	3	3	4	4	4
21.25°	2	2	2	3	3	3	3	3	4	4	4
20°	2	2	2	3	3	3	3	4	4	4	4
18.75°	2	2	2	3	3	3	3	4	4	4	4
17.5°	2	2	2	3	3	3	3	4	4	4	4
16.25°	2	2	2	3	3	3	3	4	4	4	4
15°	2	2	3	3	3	3	3	4	4	4	5
13.75°	2	2	3	3	3	3	4	4	4	4	5
12.5°	2	2	3	3	3	3	4	4	4	4	5
11.25°	2	2	3	3	3	3	4	4	4	4	5
10°	2	2	3	3	3	3	4	4	4	4	5
8.75°	2	2	3	3	3	3	4	4	4	4	5
7.5°	2	2	3	3	3	3	4	4	4	5	5
6.25°	2	2	3	3	3	3	4	4	4	5	6
5°	2	2	3	3	3	3	4	4	4	5	6
3.75°	2	2	3	3	3	3	4	4	4	5	6
2.5°	2	2	3	3	3	3	4	4	4	5	6
1.25°	2	2	3	3	3	3	4	4	4	5	6
0°	2	3	3	3	3	4	4	4	4	5	6
-1.25°	2	2	3	3	3	3	4	4	4	5	6
-2.5°	2	2	3	3	3	3	4	4	4	5	6
-3.75°	2	2	3	3	3	3	4	4	4	5	6
-5°	2	2	3	3	3	3	4	4	4	5	6
-6.25°	2	2	3	3	3	3	4	4	4	5	6
-7.5°	2	2	3	3	3	3	4	4	4	5	5
-8.75°	2	2	3	3	3	3	4	4	4	4	5
-10°	2	2	3	3	3	3	4	4	4	4	5
-11.25°	2	2	3	3	3	3	4	4	4	4	5
-12.5°	2	2	3	3	3	3	4	4	4	4	5
-13.75°	2	2	3	3	3	3	4	4	4	4	5
-15°	2	2	3	3	3	3	3	4	4	4	5
-16.25°	2	2	2	3	3	3	3	4	4	4	4
-17.5°	2	2	2	3	3	3	3	4	4	4	4
-18.75°	2	2	2	3	3	3	3	4	4	4	4
-20°	2	2	2	3	3	3	3	4	4	4	4
-21.25°	2	2	2	3	3	3	3	3	4	4	4



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	2	2	2	3	3	3	3	4	4	4
-23.75°	2	2	2	2	3	3	3	3	4	4	4
-25°	2	2	2	2	3	3	3	3	3	4	4
-26.25°	2	2	2	2	3	3	3	3	3	4	4
-27.5°	2	2	2	2	2	3	3	3	3	3	4
-28.75°	2	2	2	2	2	3	3	3	3	3	4
-30°	2	2	2	2	2	3	3	3	3	3	4
-31.25°	2	2	2	2	2	2	3	3	3	3	3
-32.5°	1	2	2	2	2	2	3	3	3	3	3
-33.75°	1	2	2	2	2	2	2	3	3	3	3
-35°	1	1	2	2	2	2	2	3	3	3	3
-36.25°	1	1	2	2	2	2	2	2	3	3	3
-37.5°	1	1	1	2	2	2	2	2	2	3	3
-38.75°	1	1	1	2	2	2	2	2	2	3	3
-40°	1	1	1	1	2	2	2	2	2	2	3
-41.25°	1	1	1	1	2	2	2	2	2	2	2
-42.5°	1	1	1	1	1	2	2	2	2	2	2
-43.75°	1	1	1	1	1	1	2	2	2	2	2
-45°	1	1	1	1	1	1	2	2	2	2	2
-46.25°	1	1	1	1	1	1	1	2	2	2	2
-47.5°	1	1	1	1	1	1	1	1	2	2	2
-48.75°	1	1	1	1	1	1	1	1	1	2	2
-50°	1	1	1	1	1	1	1	1	1	1	2
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	0	0	1	1	1	1	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	1	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	1	1	1	1
73.75°	0	0	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	2	2	2
57.5°	1	1	1	1	1	1	2	2	2	2	2
56.25°	1	1	1	1	1	2	2	2	2	2	2
55°	1	1	1	2	2	2	2	2	2	2	2
53.75°	1	1	2	2	2	2	2	2	2	2	2
52.5°	1	2	2	2	2	2	2	2	2	2	2
51.25°	2	2	2	2	2	2	2	2	2	2	2
50°	2	2	2	2	2	2	2	2	2	2	2
48.75°	2	2	2	2	2	2	2	2	2	3	3
47.5°	2	2	2	2	2	2	2	3	3	3	3
46.25°	2	2	2	2	2	2	3	3	3	3	3
45°	2	2	2	2	3	3	3	3	3	3	3
43.75°	2	2	3	3	3	3	3	3	3	3	3
42.5°	2	3	3	3	3	3	3	3	3	3	4
41.25°	3	3	3	3	3	3	3	3	4	4	4
40°	3	3	3	3	3	3	3	4	4	4	4
38.75°	3	3	3	3	3	3	4	4	4	4	5
37.5°	3	3	3	3	4	4	4	4	4	5	5
36.25°	3	3	3	4	4	4	4	4	5	5	5
35°	3	3	4	4	4	4	4	5	5	5	5



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	4	4	4	4	4	4	5	5	5	5
32.5°	3	4	4	4	4	4	5	5	5	5	6
31.25°	4	4	4	4	4	5	5	5	5	6	6
30°	4	4	4	4	4	5	5	5	6	6	7
28.75°	4	4	4	4	5	5	5	6	6	7	7
27.5°	4	4	4	5	5	5	6	6	7	7	8
26.25°	4	4	4	5	5	5	6	6	7	8	9
25°	4	4	5	5	5	6	6	7	8	8	9
23.75°	4	4	5	5	6	6	7	7	8	9	10
22.5°	4	5	5	5	6	6	7	8	9	10	12
21.25°	4	5	5	6	6	7	8	9	10	11	14
20°	4	5	5	6	6	7	8	9	10	13	17
18.75°	5	5	6	6	7	8	9	10	11	15	19
17.5°	5	5	6	6	7	8	9	11	13	17	22
16.25°	5	6	6	7	7	8	10	11	15	19	27
15°	5	6	6	7	8	9	10	13	17	21	31
13.75°	5	6	6	7	8	9	11	14	19	25	35
12.5°	6	6	6	7	8	10	12	16	21	29	39
11.25°	6	6	7	8	9	11	12	17	22	32	43
10°	6	6	7	8	9	11	14	19	25	36	47
8.75°	6	6	7	8	10	12	15	20	28	39	54
7.5°	6	7	7	8	10	12	16	22	30	42	60
6.25°	6	7	7	8	10	12	17	23	33	44	65
5°	6	7	8	9	11	13	18	24	35	47	70
3.75°	6	7	8	9	11	13	19	25	37	49	75
2.5°	6	7	8	9	11	14	20	26	38	51	78
1.25°	6	7	8	9	11	14	20	26	39	52	81
0°	6	7	8	9	11	14	20	27	40	53	83
-1.25°	6	7	8	9	11	14	20	26	39	52	81
-2.5°	6	7	8	9	11	14	20	26	38	51	78
-3.75°	6	7	8	9	11	13	19	25	37	49	75
-5°	6	7	8	9	11	13	18	24	35	47	70
-6.25°	6	7	7	8	10	12	17	23	33	44	65
-7.5°	6	7	7	8	10	12	16	22	30	42	60
-8.75°	6	6	7	8	10	12	15	20	28	39	54
-10°	6	6	7	8	9	11	14	19	25	36	47
-11.25°	6	6	7	8	9	11	12	17	22	32	43
-12.5°	6	6	6	7	8	10	12	16	21	29	39
-13.75°	5	6	6	7	8	9	11	14	19	25	35
-15°	5	6	6	7	8	9	10	13	17	21	31
-16.25°	5	6	6	7	7	8	10	11	15	19	27
-17.5°	5	5	6	6	7	8	9	11	13	17	22
-18.75°	5	5	6	6	7	8	9	10	11	15	19
-20°	4	5	5	6	6	7	8	9	10	13	17
-21.25°	4	5	5	6	6	7	8	9	10	11	14



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	5	5	5	6	6	7	8	9	10	12
-23.75°	4	4	5	5	6	6	7	7	8	9	10
-25°	4	4	5	5	5	6	6	7	8	8	9
-26.25°	4	4	4	5	5	5	6	6	7	8	9
-27.5°	4	4	4	5	5	5	6	6	7	7	8
-28.75°	4	4	4	4	5	5	5	6	6	7	7
-30°	4	4	4	4	4	5	5	5	6	6	7
-31.25°	4	4	4	4	4	5	5	5	5	6	6
-32.5°	3	4	4	4	4	4	5	5	5	5	6
-33.75°	3	4	4	4	4	4	4	5	5	5	5
-35°	3	3	4	4	4	4	4	5	5	5	5
-36.25°	3	3	3	4	4	4	4	4	5	5	5
-37.5°	3	3	3	3	4	4	4	4	4	5	5
-38.75°	3	3	3	3	3	3	4	4	4	4	5
-40°	3	3	3	3	3	3	3	4	4	4	4
-41.25°	3	3	3	3	3	3	3	3	4	4	4
-42.5°	2	3	3	3	3	3	3	3	3	3	4
-43.75°	2	2	3	3	3	3	3	3	3	3	3
-45°	2	2	2	2	3	3	3	3	3	3	3
-46.25°	2	2	2	2	2	2	3	3	3	3	3
-47.5°	2	2	2	2	2	2	2	3	3	3	3
-48.75°	2	2	2	2	2	2	2	2	2	3	3
-50°	2	2	2	2	2	2	2	2	2	2	2
-51.25°	2	2	2	2	2	2	2	2	2	2	2
-52.5°	1	2	2	2	2	2	2	2	2	2	2
-53.75°	1	1	2	2	2	2	2	2	2	2	2
-55°	1	1	1	2	2	2	2	2	2	2	2
-56.25°	1	1	1	1	1	2	2	2	2	2	2
-57.5°	1	1	1	1	1	1	2	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	2	2	2
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	1	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	1	1	1
76.25°	0	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	2	2
60°	1	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	3	3	3
53.75°	2	2	2	2	2	2	3	3	3	3	3
52.5°	2	2	2	3	3	3	3	3	3	3	3
51.25°	2	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	4
48.75°	3	3	3	3	3	3	3	4	4	4	4
47.5°	3	3	3	3	3	4	4	4	4	4	4
46.25°	3	3	3	3	4	4	4	4	4	4	4
45°	3	3	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	5	5	5	5	4	4
42.5°	4	4	4	5	5	5	5	5	5	4	5
41.25°	4	4	5	5	5	5	5	5	5	5	5
40°	5	5	5	5	5	5	5	5	5	5	5
38.75°	5	5	5	5	5	5	5	5	6	6	6
37.5°	5	5	5	5	5	5	6	6	6	7	7
36.25°	5	5	5	5	6	6	6	7	7	7	8
35°	5	5	6	6	6	7	7	7	8	8	9



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	6	6	6	6	7	7	8	9	9	10	10
32.5°	6	6	7	7	8	8	9	10	10	11	12
31.25°	6	7	8	8	9	10	10	11	12	13	14
30°	7	8	8	9	10	11	12	13	15	16	17
28.75°	8	9	9	11	12	13	15	16	17	20	22
27.5°	9	9	11	13	14	17	19	20	22	24	26
26.25°	9	11	13	15	18	21	23	27	28	29	35
25°	11	13	15	19	23	26	31	34	37	41	44
23.75°	13	15	19	24	27	34	40	44	49	53	56
22.5°	15	18	24	29	36	43	49	57	63	68	73
21.25°	17	23	29	36	46	54	63	71	78	86	92
20°	21	28	34	46	56	66	77	86	96	104	111
18.75°	26	33	43	56	68	81	92	104	115	124	132
17.5°	31	39	54	67	82	96	109	123	135	146	157
16.25°	36	48	64	80	96	112	128	142	156	171	185
15°	40	57	75	93	111	129	147	163	179	198	216
13.75°	47	66	85	106	127	147	166	184	206	229	250
12.5°	55	75	96	118	141	164	186	207	234	261	286
11.25°	63	84	107	130	156	182	206	234	265	295	324
10°	70	93	118	142	171	199	227	261	297	332	366
8.75°	78	102	128	155	187	218	251	289	331	372	410
7.5°	85	110	138	168	203	237	275	318	367	413	456
6.25°	91	119	147	181	218	256	298	347	403	453	501
5°	97	126	155	193	233	274	321	377	438	493	543
3.75°	102	133	163	205	248	292	344	407	473	532	584
2.5°	107	139	170	215	261	309	365	434	506	568	624
1.25°	111	144	176	224	273	324	384	459	536	601	661
0°	114	147	181	232	283	338	401	481	564	632	695
-1.25°	111	144	176	224	273	324	384	459	536	601	661
-2.5°	107	139	170	215	261	309	365	434	506	568	624
-3.75°	102	133	163	205	248	292	344	407	473	532	584
-5°	97	126	155	193	233	274	321	377	438	493	543
-6.25°	91	119	147	181	218	256	298	347	403	453	501
-7.5°	85	110	138	168	203	237	275	318	367	413	456
-8.75°	78	102	128	155	187	218	251	289	331	372	410
-10°	70	93	118	142	171	199	227	261	297	332	366
-11.25°	63	84	107	130	156	182	206	234	265	295	324
-12.5°	55	75	96	118	141	164	186	207	234	261	286
-13.75°	47	66	85	106	127	147	166	184	206	229	250
-15°	40	57	75	93	111	129	147	163	179	198	216
-16.25°	36	48	64	80	96	112	128	142	156	171	185
-17.5°	31	39	54	67	82	96	109	123	135	146	157
-18.75°	26	33	43	56	68	81	92	104	115	124	132
-20°	21	28	34	46	56	66	77	86	96	104	111
-21.25°	17	23	29	36	46	54	63	71	78	86	92



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	15	18	24	29	36	43	49	57	63	68	73
-23.75°	13	15	19	24	27	34	40	44	49	53	56
-25°	11	13	15	19	23	26	31	34	37	41	44
-26.25°	9	11	13	15	18	21	23	27	28	29	35
-27.5°	9	9	11	13	14	17	19	20	22	24	26
-28.75°	8	9	9	11	12	13	15	16	17	20	22
-30°	7	8	8	9	10	11	12	13	15	16	17
-31.25°	6	7	8	8	9	10	10	11	12	13	14
-32.5°	6	6	7	7	8	8	9	10	10	11	12
-33.75°	6	6	6	6	7	7	8	9	9	10	10
-35°	5	5	6	6	6	7	7	7	8	8	9
-36.25°	5	5	5	5	6	6	6	7	7	7	8
-37.5°	5	5	5	5	5	5	6	6	6	7	7
-38.75°	5	5	5	5	5	5	5	5	6	6	6
-40°	5	5	5	5	5	5	5	5	5	5	5
-41.25°	4	4	5	5	5	5	5	5	5	5	5
-42.5°	4	4	4	5	5	5	5	5	5	4	5
-43.75°	4	4	4	4	4	5	5	5	5	4	4
-45°	3	3	4	4	4	4	4	4	4	4	4
-46.25°	3	3	3	3	4	4	4	4	4	4	4
-47.5°	3	3	3	3	3	4	4	4	4	4	4
-48.75°	3	3	3	3	3	3	3	4	4	4	4
-50°	3	3	3	3	3	3	3	3	3	3	4
-51.25°	2	3	3	3	3	3	3	3	3	3	3
-52.5°	2	2	2	3	3	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	3	3	3	3	3
-55°	2	2	2	2	2	2	2	2	3	3	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	1	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	1	1	1



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	3	3	3	3	3	3
56.25°	2	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	5	5	5
43.75°	4	4	4	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	5	5	6	6	6
41.25°	5	5	5	6	6	6	6	6	6	6	6
40°	6	6	6	6	6	6	6	7	7	7	7
38.75°	6	6	7	7	7	7	7	8	8	8	8
37.5°	7	7	8	8	8	8	8	8	8	8	8
36.25°	8	9	9	9	9	9	9	9	9	9	9
35°	9	10	10	10	10	10	10	10	10	11	11



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	11	11	12	11	12	12	12	12	12	13	13
32.5°	13	13	14	15	15	15	14	14	14	14	15
31.25°	15	16	17	18	18	18	18	16	16	16	17
30°	19	20	21	23	23	23	22	20	19	20	21
28.75°	23	26	28	29	29	29	28	26	23	24	25
27.5°	30	33	35	37	38	38	37	34	31	30	32
26.25°	39	41	45	48	49	48	47	45	41	39	41
25°	48	54	57	60	61	61	60	58	55	50	52
23.75°	62	67	71	73	75	75	75	73	69	65	63
22.5°	77	82	86	89	91	92	92	90	86	81	76
21.25°	96	98	103	107	109	110	110	108	104	98	91
20°	116	120	121	126	129	130	130	128	124	119	112
18.75°	140	145	146	145	149	151	151	149	146	141	135
17.5°	167	174	176	174	171	173	174	172	170	166	162
16.25°	197	206	210	209	202	197	197	198	198	195	191
15°	231	242	249	250	243	228	224	227	228	227	223
13.75°	267	282	293	294	287	275	260	258	260	260	256
12.5°	308	328	339	340	335	325	311	295	293	293	291
11.25°	352	376	387	389	385	376	363	348	330	329	330
10°	400	424	437	440	436	427	415	400	385	371	371
8.75°	449	473	487	490	486	478	466	452	439	426	415
7.5°	495	522	536	541	537	528	516	503	490	479	472
6.25°	541	570	582	585	583	577	565	552	540	530	525
5°	587	614	626	628	624	615	604	596	587	578	575
3.75°	631	658	670	669	663	650	637	626	619	618	620
2.5°	673	702	712	710	700	685	668	655	646	643	645
1.25°	714	744	753	750	738	720	699	684	672	667	667
0°	753	785	794	790	776	755	730	712	697	690	686
-1.25°	714	744	753	750	738	720	699	684	672	667	667
-2.5°	673	702	712	710	700	685	668	655	646	643	645
-3.75°	631	658	670	669	663	650	637	626	619	618	620
-5°	587	614	626	628	624	615	604	596	587	578	575
-6.25°	541	570	582	585	583	577	565	552	540	530	525
-7.5°	495	522	536	541	537	528	516	503	490	479	472
-8.75°	449	473	487	490	486	478	466	452	439	426	415
-10°	400	424	437	440	436	427	415	400	385	371	371
-11.25°	352	376	387	389	385	376	363	348	330	329	330
-12.5°	308	328	339	340	335	325	311	295	293	293	291
-13.75°	267	282	293	294	287	275	260	258	260	260	256
-15°	231	242	249	250	243	228	224	227	228	227	223
-16.25°	197	206	210	209	202	197	197	198	198	195	191
-17.5°	167	174	176	174	171	173	174	172	170	166	162
-18.75°	140	145	146	145	149	151	151	149	146	141	135
-20°	116	120	121	126	129	130	130	128	124	119	112
-21.25°	96	98	103	107	109	110	110	108	104	98	91



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	77	82	86	89	91	92	92	90	86	81	76
-23.75°	62	67	71	73	75	75	75	73	69	65	63
-25°	48	54	57	60	61	61	60	58	55	50	52
-26.25°	39	41	45	48	49	48	47	45	41	39	41
-27.5°	30	33	35	37	38	38	37	34	31	30	32
-28.75°	23	26	28	29	29	29	28	26	23	24	25
-30°	19	20	21	23	23	23	22	20	19	20	21
-31.25°	15	16	17	18	18	18	18	16	16	16	17
-32.5°	13	13	14	15	15	15	14	14	14	14	15
-33.75°	11	11	12	11	12	12	12	12	12	13	13
-35°	9	10	10	10	10	10	10	10	10	11	11
-36.25°	8	9	9	9	9	9	9	9	9	9	9
-37.5°	7	7	8	8	8	8	8	8	8	8	8
-38.75°	6	6	7	7	7	7	7	8	8	8	8
-40°	6	6	6	6	6	6	6	7	7	7	7
-41.25°	5	5	5	6	6	6	6	6	6	6	6
-42.5°	5	5	5	5	5	5	5	5	6	6	6
-43.75°	4	4	4	5	5	5	5	5	5	5	5
-45°	4	4	4	4	4	4	4	4	5	5	5
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	3	3	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	3	3	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	3	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	5	4	4	4	4
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	5	5	5	5	5	5	6	5	5	5	5
42.5°	6	6	6	6	6	6	6	6	6	6	6
41.25°	6	6	7	7	7	7	7	7	7	7	7
40°	7	7	7	7	7	7	7	7	7	7	7
38.75°	8	8	8	8	8	8	8	8	8	8	8
37.5°	8	8	8	8	8	8	8	8	8	8	8
36.25°	9	10	10	10	10	10	10	10	10	10	10
35°	11	11	11	11	11	11	11	11	11	11	11



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	13	13	13	13	13	13	13	13	13	13	13
32.5°	15	15	15	15	15	14	14	14	15	15	15
31.25°	17	17	17	17	17	17	16	17	17	17	17
30°	21	21	21	20	20	19	18	19	20	20	21
28.75°	25	26	25	25	24	23	22	23	24	25	25
27.5°	32	33	33	33	32	31	29	31	32	33	33
26.25°	42	42	43	42	41	40	38	40	41	42	43
25°	53	54	54	53	52	50	48	50	52	53	54
23.75°	65	65	65	64	63	61	58	61	63	64	65
22.5°	77	78	78	77	76	74	71	74	76	77	78
21.25°	92	93	94	93	91	89	85	89	91	93	94
20°	109	111	111	111	109	105	101	105	109	111	111
18.75°	128	131	132	131	128	125	120	125	128	131	132
17.5°	155	154	155	155	152	147	141	147	152	155	155
16.25°	185	179	180	179	176	171	164	171	176	179	180
15°	216	207	207	207	204	199	191	199	204	207	207
13.75°	250	241	237	237	234	228	220	228	234	237	237
12.5°	287	280	271	272	271	265	256	265	271	272	271
11.25°	328	323	315	315	315	310	300	310	315	315	315
10°	372	370	365	362	365	361	351	361	365	362	365
8.75°	418	421	421	417	420	419	410	419	420	417	421
7.5°	468	473	478	478	479	480	471	480	479	478	478
6.25°	524	526	533	537	537	539	531	539	537	537	533
5°	575	579	584	591	594	595	588	595	594	591	584
3.75°	621	626	631	636	642	644	639	644	642	636	631
2.5°	653	664	669	674	678	681	679	681	678	674	669
1.25°	672	681	689	698	704	705	707	705	704	698	689
0°	687	694	700	707	712	714	719	714	712	707	700
-1.25°	672	681	689	698	704	705	707	705	704	698	689
-2.5°	653	664	669	674	678	681	679	681	678	674	669
-3.75°	621	626	631	636	642	644	639	644	642	636	631
-5°	575	579	584	591	594	595	588	595	594	591	584
-6.25°	524	526	533	537	537	539	531	539	537	537	533
-7.5°	468	473	478	478	479	480	471	480	479	478	478
-8.75°	418	421	421	417	420	419	410	419	420	417	421
-10°	372	370	365	362	365	361	351	361	365	362	365
-11.25°	328	323	315	315	315	310	300	310	315	315	315
-12.5°	287	280	271	272	271	265	256	265	271	272	271
-13.75°	250	241	237	237	234	228	220	228	234	237	237
-15°	216	207	207	207	204	199	191	199	204	207	207
-16.25°	185	179	180	179	176	171	164	171	176	179	180
-17.5°	155	154	155	155	152	147	141	147	152	155	155
-18.75°	128	131	132	131	128	125	120	125	128	131	132
-20°	109	111	111	111	109	105	101	105	109	111	111
-21.25°	92	93	94	93	91	89	85	89	91	93	94



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	77	78	78	77	76	74	71	74	76	77	78
-23.75°	65	65	65	64	63	61	58	61	63	64	65
-25°	53	54	54	53	52	50	48	50	52	53	54
-26.25°	42	42	43	42	41	40	38	40	41	42	43
-27.5°	32	33	33	33	32	31	29	31	32	33	33
-28.75°	25	26	25	25	24	23	22	23	24	25	25
-30°	21	21	21	20	20	19	18	19	20	20	21
-31.25°	17	17	17	17	17	17	16	17	17	17	17
-32.5°	15	15	15	15	15	14	14	14	15	15	15
-33.75°	13	13	13	13	13	13	13	13	13	13	13
-35°	11	11	11	11	11	11	11	11	11	11	11
-36.25°	9	10	10	10	10	10	10	10	10	10	10
-37.5°	8	8	8	8	8	8	8	8	8	8	8
-38.75°	8	8	8	8	8	8	8	8	8	8	8
-40°	7	7	7	7	7	7	7	7	7	7	7
-41.25°	6	6	7	7	7	7	7	7	7	7	7
-42.5°	6	6	6	6	6	6	6	6	6	6	6
-43.75°	5	5	5	5	5	5	6	5	5	5	5
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	4	4	4	4	4	4	5	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	3	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	5	5	5	5	5	4	4	4	4	4	4
43.75°	5	5	5	5	5	5	5	5	5	5	4
42.5°	6	6	6	6	6	5	5	5	5	5	5
41.25°	6	6	6	6	6	6	6	6	6	6	5
40°	7	7	7	7	7	7	6	6	6	6	6
38.75°	8	8	8	8	8	8	7	7	7	7	7
37.5°	8	8	8	8	8	8	8	8	8	8	8
36.25°	10	9	9	9	9	9	9	9	9	9	9
35°	11	11	11	11	10	10	10	10	10	10	10



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	13	13	13	13	12	12	12	12	12	11	12
32.5°	15	15	15	14	14	14	14	15	15	15	14
31.25°	17	17	17	16	16	16	18	18	18	18	17
30°	21	21	21	20	19	20	22	23	23	23	21
28.75°	26	25	25	24	23	26	28	29	29	29	28
27.5°	33	32	32	30	31	34	37	38	38	37	35
26.25°	42	42	41	39	41	45	47	48	49	48	45
25°	54	53	52	50	55	58	60	61	61	60	57
23.75°	65	65	63	65	69	73	75	75	75	73	71
22.5°	78	77	76	81	86	90	92	92	91	89	86
21.25°	93	92	91	98	104	108	110	110	109	107	103
20°	111	109	112	119	124	128	130	130	129	126	121
18.75°	131	128	135	141	146	149	151	151	149	145	146
17.5°	154	155	162	166	170	172	174	173	171	174	176
16.25°	179	185	191	195	198	198	197	197	202	209	210
15°	207	216	223	227	228	227	224	228	243	250	249
13.75°	241	250	256	260	260	258	260	275	287	294	293
12.5°	280	287	291	293	293	295	311	325	335	340	339
11.25°	323	328	330	329	330	348	363	376	385	389	387
10°	370	372	371	371	385	400	415	427	436	440	437
8.75°	421	418	415	426	439	452	466	478	486	490	487
7.5°	473	468	472	479	490	503	516	528	537	541	536
6.25°	526	524	525	530	540	552	565	577	583	585	582
5°	579	575	575	578	587	596	604	615	624	628	626
3.75°	626	621	620	618	619	626	637	650	663	669	670
2.5°	664	653	645	643	646	655	668	685	700	710	712
1.25°	681	672	667	667	672	684	699	720	738	750	753
0°	694	687	686	690	697	712	730	755	776	790	794
-1.25°	681	672	667	667	672	684	699	720	738	750	753
-2.5°	664	653	645	643	646	655	668	685	700	710	712
-3.75°	626	621	620	618	619	626	637	650	663	669	670
-5°	579	575	575	578	587	596	604	615	624	628	626
-6.25°	526	524	525	530	540	552	565	577	583	585	582
-7.5°	473	468	472	479	490	503	516	528	537	541	536
-8.75°	421	418	415	426	439	452	466	478	486	490	487
-10°	370	372	371	371	385	400	415	427	436	440	437
-11.25°	323	328	330	329	330	348	363	376	385	389	387
-12.5°	280	287	291	293	293	295	311	325	335	340	339
-13.75°	241	250	256	260	260	258	260	275	287	294	293
-15°	207	216	223	227	228	227	224	228	243	250	249
-16.25°	179	185	191	195	198	198	197	197	202	209	210
-17.5°	154	155	162	166	170	172	174	173	171	174	176
-18.75°	131	128	135	141	146	149	151	151	149	145	146
-20°	111	109	112	119	124	128	130	130	129	126	121
-21.25°	93	92	91	98	104	108	110	110	109	107	103



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	78	77	76	81	86	90	92	92	91	89	86
-23.75°	65	65	63	65	69	73	75	75	75	73	71
-25°	54	53	52	50	55	58	60	61	61	60	57
-26.25°	42	42	41	39	41	45	47	48	49	48	45
-27.5°	33	32	32	30	31	34	37	38	38	37	35
-28.75°	26	25	25	24	23	26	28	29	29	29	28
-30°	21	21	21	20	19	20	22	23	23	23	21
-31.25°	17	17	17	16	16	16	18	18	18	18	17
-32.5°	15	15	15	14	14	14	14	15	15	15	14
-33.75°	13	13	13	13	12	12	12	12	12	11	12
-35°	11	11	11	11	10	10	10	10	10	10	10
-36.25°	10	9	9	9	9	9	9	9	9	9	9
-37.5°	8	8	8	8	8	8	8	8	8	8	8
-38.75°	8	8	8	8	8	8	7	7	7	7	7
-40°	7	7	7	7	7	7	6	6	6	6	6
-41.25°	6	6	6	6	6	6	6	6	6	6	5
-42.5°	6	6	6	6	6	5	5	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	4
-45°	5	5	5	5	5	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	0	0	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	1	1	1	1	1	0	0	0	0	0	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	2	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	3	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	3	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	3	3	2
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	4	4	4	3	3	3	3	3	3	3	3
48.75°	4	4	4	4	4	4	3	3	3	3	3
47.5°	4	4	4	4	4	4	4	4	3	3	3
46.25°	4	4	4	4	4	4	4	4	4	3	3
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	5	5	5	5	4	4	4
42.5°	5	5	5	4	5	5	5	5	5	5	4
41.25°	5	5	5	5	5	5	5	5	5	5	5
40°	6	6	5	5	5	5	5	5	5	5	5
38.75°	6	6	6	6	6	5	5	5	5	5	5
37.5°	7	7	7	7	6	6	6	5	5	5	5
36.25°	9	8	8	7	7	7	6	6	6	5	5
35°	10	9	9	8	8	7	7	7	6	6	6



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	11	11	10	10	9	9	8	7	7	6	6
32.5°	13	13	12	11	10	10	9	8	8	7	7
31.25°	16	15	14	13	12	11	10	10	9	8	8
30°	20	19	17	16	15	13	12	11	10	9	8
28.75°	26	23	22	20	17	16	15	13	12	11	9
27.5°	33	30	26	24	22	20	19	17	14	13	11
26.25°	41	39	35	29	28	27	23	21	18	15	13
25°	54	48	44	41	37	34	31	26	23	19	15
23.75°	67	62	56	53	49	44	40	34	27	24	19
22.5°	82	77	73	68	63	57	49	43	36	29	24
21.25°	98	96	92	86	78	71	63	54	46	36	29
20°	120	116	111	104	96	86	77	66	56	46	34
18.75°	145	140	132	124	115	104	92	81	68	56	43
17.5°	174	167	157	146	135	123	109	96	82	67	54
16.25°	206	197	185	171	156	142	128	112	96	80	64
15°	242	231	216	198	179	163	147	129	111	93	75
13.75°	282	267	250	229	206	184	166	147	127	106	85
12.5°	328	308	286	261	234	207	186	164	141	118	96
11.25°	376	352	324	295	265	234	206	182	156	130	107
10°	424	400	366	332	297	261	227	199	171	142	118
8.75°	473	449	410	372	331	289	251	218	187	155	128
7.5°	522	495	456	413	367	318	275	237	203	168	138
6.25°	570	541	501	453	403	347	298	256	218	181	147
5°	614	587	543	493	438	377	321	274	233	193	155
3.75°	658	631	584	532	473	407	344	292	248	205	163
2.5°	702	673	624	568	506	434	365	309	261	215	170
1.25°	744	714	661	601	536	459	384	324	273	224	176
0°	785	753	695	632	564	481	401	338	283	232	181
-1.25°	744	714	661	601	536	459	384	324	273	224	176
-2.5°	702	673	624	568	506	434	365	309	261	215	170
-3.75°	658	631	584	532	473	407	344	292	248	205	163
-5°	614	587	543	493	438	377	321	274	233	193	155
-6.25°	570	541	501	453	403	347	298	256	218	181	147
-7.5°	522	495	456	413	367	318	275	237	203	168	138
-8.75°	473	449	410	372	331	289	251	218	187	155	128
-10°	424	400	366	332	297	261	227	199	171	142	118
-11.25°	376	352	324	295	265	234	206	182	156	130	107
-12.5°	328	308	286	261	234	207	186	164	141	118	96
-13.75°	282	267	250	229	206	184	166	147	127	106	85
-15°	242	231	216	198	179	163	147	129	111	93	75
-16.25°	206	197	185	171	156	142	128	112	96	80	64
-17.5°	174	167	157	146	135	123	109	96	82	67	54
-18.75°	145	140	132	124	115	104	92	81	68	56	43
-20°	120	116	111	104	96	86	77	66	56	46	34
-21.25°	98	96	92	86	78	71	63	54	46	36	29



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	82	77	73	68	63	57	49	43	36	29	24
-23.75°	67	62	56	53	49	44	40	34	27	24	19
-25°	54	48	44	41	37	34	31	26	23	19	15
-26.25°	41	39	35	29	28	27	23	21	18	15	13
-27.5°	33	30	26	24	22	20	19	17	14	13	11
-28.75°	26	23	22	20	17	16	15	13	12	11	9
-30°	20	19	17	16	15	13	12	11	10	9	8
-31.25°	16	15	14	13	12	11	10	10	9	8	8
-32.5°	13	13	12	11	10	10	9	8	8	7	7
-33.75°	11	11	10	10	9	9	8	7	7	6	6
-35°	10	9	9	8	8	7	7	7	6	6	6
-36.25°	9	8	8	7	7	7	6	6	6	5	5
-37.5°	7	7	7	7	6	6	6	5	5	5	5
-38.75°	6	6	6	6	6	5	5	5	5	5	5
-40°	6	6	5	5	5	5	5	5	5	5	5
-41.25°	5	5	5	5	5	5	5	5	5	5	5
-42.5°	5	5	5	4	5	5	5	5	5	5	4
-43.75°	4	4	4	4	5	5	5	5	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	3	3
-47.5°	4	4	4	4	4	4	4	4	3	3	3
-48.75°	4	4	4	4	4	4	3	3	3	3	3
-50°	4	4	4	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	2
-53.75°	3	3	3	3	3	3	3	2	2	2	2
-55°	3	3	3	3	3	2	2	2	2	2	2
-56.25°	3	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	2	1	1	1	1	1	1	1	1	1	1
58.75°	2	2	2	2	2	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	2	1	1	1	1
56.25°	2	2	2	2	2	2	2	2	1	1	1
55°	2	2	2	2	2	2	2	2	2	2	1
53.75°	2	2	2	2	2	2	2	2	2	2	2
52.5°	2	2	2	2	2	2	2	2	2	2	2
51.25°	3	2	2	2	2	2	2	2	2	2	2
50°	3	3	2	2	2	2	2	2	2	2	2
48.75°	3	3	3	3	2	2	2	2	2	2	2
47.5°	3	3	3	3	3	3	2	2	2	2	2
46.25°	3	3	3	3	3	3	3	2	2	2	2
45°	3	3	3	3	3	3	3	3	3	2	2
43.75°	4	4	3	3	3	3	3	3	3	3	3
42.5°	4	4	4	3	3	3	3	3	3	3	3
41.25°	4	4	4	4	4	3	3	3	3	3	3
40°	5	5	4	4	4	4	3	3	3	3	3
38.75°	5	5	5	4	4	4	4	3	3	3	3
37.5°	5	5	5	5	4	4	4	4	4	3	3
36.25°	5	5	5	5	5	4	4	4	4	4	3
35°	5	5	5	5	5	5	4	4	4	4	4



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	6	6	5	5	5	5	4	4	4	4	4
32.5°	6	6	6	5	5	5	5	4	4	4	4
31.25°	7	6	6	6	5	5	5	5	4	4	4
30°	8	7	7	6	6	5	5	5	4	4	4
28.75°	9	8	7	7	6	6	5	5	5	4	4
27.5°	9	9	8	7	7	6	6	5	5	5	4
26.25°	11	9	9	8	7	6	6	5	5	5	4
25°	13	11	9	8	8	7	6	6	5	5	5
23.75°	15	13	10	9	8	7	7	6	6	5	5
22.5°	18	15	12	10	9	8	7	6	6	5	5
21.25°	23	17	14	11	10	9	8	7	6	6	5
20°	28	21	17	13	10	9	8	7	6	6	5
18.75°	33	26	19	15	11	10	9	8	7	6	6
17.5°	39	31	22	17	13	11	9	8	7	6	6
16.25°	48	36	27	19	15	11	10	8	7	7	6
15°	57	40	31	21	17	13	10	9	8	7	6
13.75°	66	47	35	25	19	14	11	9	8	7	6
12.5°	75	55	39	29	21	16	12	10	8	7	6
11.25°	84	63	43	32	22	17	12	11	9	8	7
10°	93	70	47	36	25	19	14	11	9	8	7
8.75°	102	78	54	39	28	20	15	12	10	8	7
7.5°	110	85	60	42	30	22	16	12	10	8	7
6.25°	119	91	65	44	33	23	17	12	10	8	7
5°	126	97	70	47	35	24	18	13	11	9	8
3.75°	133	102	75	49	37	25	19	13	11	9	8
2.5°	139	107	78	51	38	26	20	14	11	9	8
1.25°	144	111	81	52	39	26	20	14	11	9	8
0°	147	114	83	53	40	27	20	14	11	9	8
-1.25°	144	111	81	52	39	26	20	14	11	9	8
-2.5°	139	107	78	51	38	26	20	14	11	9	8
-3.75°	133	102	75	49	37	25	19	13	11	9	8
-5°	126	97	70	47	35	24	18	13	11	9	8
-6.25°	119	91	65	44	33	23	17	12	10	8	7
-7.5°	110	85	60	42	30	22	16	12	10	8	7
-8.75°	102	78	54	39	28	20	15	12	10	8	7
-10°	93	70	47	36	25	19	14	11	9	8	7
-11.25°	84	63	43	32	22	17	12	11	9	8	7
-12.5°	75	55	39	29	21	16	12	10	8	7	6
-13.75°	66	47	35	25	19	14	11	9	8	7	6
-15°	57	40	31	21	17	13	10	9	8	7	6
-16.25°	48	36	27	19	15	11	10	8	7	7	6
-17.5°	39	31	22	17	13	11	9	8	7	6	6
-18.75°	33	26	19	15	11	10	9	8	7	6	6
-20°	28	21	17	13	10	9	8	7	6	6	5
-21.25°	23	17	14	11	10	9	8	7	6	6	5



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	18	15	12	10	9	8	7	6	6	5	5
-23.75°	15	13	10	9	8	7	7	6	6	5	5
-25°	13	11	9	8	8	7	6	6	5	5	5
-26.25°	11	9	9	8	7	6	6	5	5	5	4
-27.5°	9	9	8	7	7	6	6	5	5	5	4
-28.75°	9	8	7	7	6	6	5	5	5	4	4
-30°	8	7	7	6	6	5	5	5	4	4	4
-31.25°	7	6	6	6	5	5	5	5	4	4	4
-32.5°	6	6	6	5	5	5	5	4	4	4	4
-33.75°	6	6	5	5	5	5	4	4	4	4	4
-35°	5	5	5	5	5	5	4	4	4	4	4
-36.25°	5	5	5	5	5	4	4	4	4	4	3
-37.5°	5	5	5	5	4	4	4	4	4	3	3
-38.75°	5	5	5	4	4	4	4	3	3	3	3
-40°	5	5	4	4	4	4	3	3	3	3	3
-41.25°	4	4	4	4	4	3	3	3	3	3	3
-42.5°	4	4	4	3	3	3	3	3	3	3	3
-43.75°	4	4	3	3	3	3	3	3	3	3	3
-45°	3	3	3	3	3	3	3	3	3	2	2
-46.25°	3	3	3	3	3	3	3	2	2	2	2
-47.5°	3	3	3	3	3	3	2	2	2	2	2
-48.75°	3	3	3	3	2	2	2	2	2	2	2
-50°	3	3	2	2	2	2	2	2	2	2	2
-51.25°	3	2	2	2	2	2	2	2	2	2	2
-52.5°	2	2	2	2	2	2	2	2	2	2	2
-53.75°	2	2	2	2	2	2	2	2	2	2	2
-55°	2	2	2	2	2	2	2	2	2	2	1
-56.25°	2	2	2	2	2	2	2	2	1	1	1
-57.5°	2	2	2	2	2	2	2	1	1	1	1
-58.75°	2	2	2	2	2	1	1	1	1	1	1
-60°	2	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	0	0	0	0	0
-76.25°	1	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	1	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	2	1	1	1	1	1	1	1	1	1	1
51.25°	2	2	1	1	1	1	1	1	1	1	1
50°	2	2	2	1	1	1	1	1	1	1	1
48.75°	2	2	2	2	1	1	1	1	1	1	1
47.5°	2	2	2	2	2	1	1	1	1	1	1
46.25°	2	2	2	2	2	2	1	1	1	1	1
45°	2	2	2	2	2	2	2	1	1	1	1
43.75°	2	2	2	2	2	2	2	1	1	1	1
42.5°	3	2	2	2	2	2	2	2	1	1	1
41.25°	3	3	2	2	2	2	2	2	2	1	1
40°	3	3	3	2	2	2	2	2	2	1	1
38.75°	3	3	3	3	2	2	2	2	2	2	1
37.5°	3	3	3	3	2	2	2	2	2	2	1
36.25°	3	3	3	3	3	2	2	2	2	2	2
35°	3	3	3	3	3	3	2	2	2	2	2



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	4	3	3	3	3	3	2	2	2	2	2
32.5°	4	3	3	3	3	3	3	2	2	2	2
31.25°	4	4	3	3	3	3	3	2	2	2	2
30°	4	4	4	3	3	3	3	3	2	2	2
28.75°	4	4	4	3	3	3	3	3	2	2	2
27.5°	4	4	4	3	3	3	3	3	2	2	2
26.25°	4	4	4	4	3	3	3	3	3	2	2
25°	4	4	4	4	3	3	3	3	3	2	2
23.75°	4	4	4	4	4	3	3	3	3	2	2
22.5°	5	4	4	4	4	3	3	3	3	2	2
21.25°	5	4	4	4	4	3	3	3	3	3	2
20°	5	4	4	4	4	4	3	3	3	3	2
18.75°	5	5	4	4	4	4	3	3	3	3	2
17.5°	5	5	4	4	4	4	3	3	3	3	2
16.25°	6	5	4	4	4	4	3	3	3	3	2
15°	6	5	5	4	4	4	3	3	3	3	3
13.75°	6	5	5	4	4	4	4	3	3	3	3
12.5°	6	6	5	4	4	4	4	3	3	3	3
11.25°	6	6	5	4	4	4	4	3	3	3	3
10°	6	6	5	4	4	4	4	3	3	3	3
8.75°	6	6	5	4	4	4	4	3	3	3	3
7.5°	7	6	5	5	4	4	4	3	3	3	3
6.25°	7	6	6	5	4	4	4	3	3	3	3
5°	7	6	6	5	4	4	4	3	3	3	3
3.75°	7	6	6	5	4	4	4	3	3	3	3
2.5°	7	6	6	5	4	4	4	3	3	3	3
1.25°	7	6	6	5	4	4	4	3	3	3	3
0°	7	6	6	5	4	4	4	4	3	3	3
-1.25°	7	6	6	5	4	4	4	3	3	3	3
-2.5°	7	6	6	5	4	4	4	3	3	3	3
-3.75°	7	6	6	5	4	4	4	3	3	3	3
-5°	7	6	6	5	4	4	4	3	3	3	3
-6.25°	7	6	6	5	4	4	4	3	3	3	3
-7.5°	7	6	5	5	4	4	4	3	3	3	3
-8.75°	6	6	5	4	4	4	4	3	3	3	3
-10°	6	6	5	4	4	4	4	3	3	3	3
-11.25°	6	6	5	4	4	4	4	3	3	3	3
-12.5°	6	6	5	4	4	4	4	3	3	3	3
-13.75°	6	5	5	4	4	4	4	3	3	3	3
-15°	6	5	5	4	4	4	3	3	3	3	3
-16.25°	6	5	4	4	4	4	3	3	3	3	2
-17.5°	5	5	4	4	4	4	3	3	3	3	2
-18.75°	5	5	4	4	4	4	3	3	3	3	2
-20°	5	4	4	4	4	4	3	3	3	3	2
-21.25°	5	4	4	4	4	3	3	3	3	3	2



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	5	4	4	4	4	3	3	3	3	2	2
-23.75°	4	4	4	4	4	3	3	3	3	2	2
-25°	4	4	4	4	3	3	3	3	3	2	2
-26.25°	4	4	4	4	3	3	3	3	3	2	2
-27.5°	4	4	4	3	3	3	3	3	2	2	2
-28.75°	4	4	4	3	3	3	3	3	2	2	2
-30°	4	4	4	3	3	3	3	3	2	2	2
-31.25°	4	4	3	3	3	3	3	2	2	2	2
-32.5°	4	3	3	3	3	3	3	2	2	2	2
-33.75°	4	3	3	3	3	3	2	2	2	2	2
-35°	3	3	3	3	3	3	2	2	2	2	2
-36.25°	3	3	3	3	3	2	2	2	2	2	2
-37.5°	3	3	3	3	2	2	2	2	2	2	1
-38.75°	3	3	3	3	2	2	2	2	2	2	1
-40°	3	3	3	2	2	2	2	2	2	1	1
-41.25°	3	3	2	2	2	2	2	2	2	1	1
-42.5°	3	2	2	2	2	2	2	2	1	1	1
-43.75°	2	2	2	2	2	2	2	1	1	1	1
-45°	2	2	2	2	2	2	2	1	1	1	1
-46.25°	2	2	2	2	2	2	1	1	1	1	1
-47.5°	2	2	2	2	2	1	1	1	1	1	1
-48.75°	2	2	2	2	1	1	1	1	1	1	1
-50°	2	2	2	1	1	1	1	1	1	1	1
-51.25°	2	2	1	1	1	1	1	1	1	1	1
-52.5°	2	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	1	1	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	0	0	0	0	0	0	0
67.5°	1	1	1	1	1	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	0	0	0	0	0
65°	1	1	1	1	1	1	1	0	0	0	0
63.75°	1	1	1	1	1	1	1	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	0	0	0
61.25°	1	1	1	1	1	1	1	1	1	0	0
60°	1	1	1	1	1	1	1	1	1	0	0
58.75°	1	1	1	1	1	1	1	1	1	1	0
57.5°	1	1	1	1	1	1	1	1	1	1	0
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	1
40°	1	1	1	1	1	1	1	1	1	1	1
38.75°	1	1	1	1	1	1	1	1	1	1	1
37.5°	1	1	1	1	1	1	1	1	1	1	1
36.25°	1	1	1	1	1	1	1	1	1	1	1
35°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	1	1	1	1	1	1	1	1	1	1
32.5°	2	1	1	1	1	1	1	1	1	1	1
31.25°	2	2	1	1	1	1	1	1	1	1	1
30°	2	2	1	1	1	1	1	1	1	1	1
28.75°	2	2	1	1	1	1	1	1	1	1	1
27.5°	2	2	2	1	1	1	1	1	1	1	1
26.25°	2	2	2	1	1	1	1	1	1	1	1
25°	2	2	2	2	1	1	1	1	1	1	1
23.75°	2	2	2	2	1	1	1	1	1	1	1
22.5°	2	2	2	2	1	1	1	1	1	1	1
21.25°	2	2	2	2	1	1	1	1	1	1	1
20°	2	2	2	2	2	1	1	1	1	1	1
18.75°	2	2	2	2	2	1	1	1	1	1	1
17.5°	2	2	2	2	2	1	1	1	1	1	1
16.25°	2	2	2	2	2	1	1	1	1	1	1
15°	2	2	2	2	2	1	1	1	1	1	1
13.75°	2	2	2	2	2	2	1	1	1	1	1
12.5°	2	2	2	2	2	2	1	1	1	1	1
11.25°	2	2	2	2	2	2	1	1	1	1	1
10°	2	2	2	2	2	2	1	1	1	1	1
8.75°	2	2	2	2	2	2	1	1	1	1	1
7.5°	2	2	2	2	2	2	1	1	1	1	1
6.25°	2	2	2	2	2	2	1	1	1	1	1
5°	2	2	2	2	2	2	1	1	1	1	1
3.75°	2	2	2	2	2	2	1	1	1	1	1
2.5°	2	2	2	2	2	2	1	1	1	1	1
1.25°	2	2	2	2	2	2	1	1	1	1	1
0°	3	2	2	2	2	2	1	1	1	1	1
-1.25°	2	2	2	2	2	2	1	1	1	1	1
-2.5°	2	2	2	2	2	2	1	1	1	1	1
-3.75°	2	2	2	2	2	2	1	1	1	1	1
-5°	2	2	2	2	2	2	1	1	1	1	1
-6.25°	2	2	2	2	2	2	1	1	1	1	1
-7.5°	2	2	2	2	2	2	1	1	1	1	1
-8.75°	2	2	2	2	2	2	1	1	1	1	1
-10°	2	2	2	2	2	2	1	1	1	1	1
-11.25°	2	2	2	2	2	2	1	1	1	1	1
-12.5°	2	2	2	2	2	2	1	1	1	1	1
-13.75°	2	2	2	2	2	2	1	1	1	1	1
-15°	2	2	2	2	2	1	1	1	1	1	1
-16.25°	2	2	2	2	2	1	1	1	1	1	1
-17.5°	2	2	2	2	2	1	1	1	1	1	1
-18.75°	2	2	2	2	2	1	1	1	1	1	1
-20°	2	2	2	2	2	1	1	1	1	1	1
-21.25°	2	2	2	2	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	2	2	2	1	1	1	1	1	1	1
-23.75°	2	2	2	2	1	1	1	1	1	1	1
-25°	2	2	2	2	1	1	1	1	1	1	1
-26.25°	2	2	2	1	1	1	1	1	1	1	1
-27.5°	2	2	2	1	1	1	1	1	1	1	1
-28.75°	2	2	1	1	1	1	1	1	1	1	1
-30°	2	2	1	1	1	1	1	1	1	1	1
-31.25°	2	2	1	1	1	1	1	1	1	1	1
-32.5°	2	1	1	1	1	1	1	1	1	1	1
-33.75°	2	1	1	1	1	1	1	1	1	1	1
-35°	1	1	1	1	1	1	1	1	1	1	1
-36.25°	1	1	1	1	1	1	1	1	1	1	1
-37.5°	1	1	1	1	1	1	1	1	1	1	1
-38.75°	1	1	1	1	1	1	1	1	1	1	1
-40°	1	1	1	1	1	1	1	1	1	1	1
-41.25°	1	1	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	0
-58.75°	1	1	1	1	1	1	1	1	1	1	0
-60°	1	1	1	1	1	1	1	1	1	0	0
-61.25°	1	1	1	1	1	1	1	1	1	0	0
-62.5°	1	1	1	1	1	1	1	1	0	0	0
-63.75°	1	1	1	1	1	1	1	0	0	0	0
-65°	1	1	1	1	1	1	1	0	0	0	0
-66.25°	1	1	1	1	1	1	0	0	0	0	0
-67.5°	1	1	1	1	1	0	0	0	0	0	0
-68.75°	1	1	1	1	0	0	0	0	0	0	0
-70°	1	1	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	1	0	0	0	0	0	0	0	0	0	0
52.5°	1	0	0	0	0	0	0	0	0	0	0
51.25°	1	0	0	0	0	0	0	0	0	0	0
50°	1	1	0	0	0	0	0	0	0	0	0
48.75°	1	1	0	0	0	0	0	0	0	0	0
47.5°	1	1	0	0	0	0	0	0	0	0	0
46.25°	1	1	0	0	0	0	0	0	0	0	0
45°	1	1	1	0	0	0	0	0	0	0	0
43.75°	1	1	1	0	0	0	0	0	0	0	0
42.5°	1	1	1	0	0	0	0	0	0	0	0
41.25°	1	1	1	0	0	0	0	0	0	0	0
40°	1	1	1	0	0	0	0	0	0	0	0
38.75°	1	1	1	1	0	0	0	0	0	0	0
37.5°	1	1	1	1	0	0	0	0	0	0	0
36.25°	1	1	1	1	0	0	0	0	0	0	0
35°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	1	0	0	0	0	0	0
27.5°	1	1	1	1	1	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	0	0	0	0	0	0
21.25°	1	1	1	1	1	0	0	0	0	0	0
20°	1	1	1	1	1	0	0	0	0	0	0
18.75°	1	1	1	1	1	0	0	0	0	0	0
17.5°	1	1	1	1	1	0	0	0	0	0	0
16.25°	1	1	1	1	1	0	0	0	0	0	0
15°	1	1	1	1	1	0	0	0	0	0	0
13.75°	1	1	1	1	1	0	0	0	0	0	0
12.5°	1	1	1	1	1	0	0	0	0	0	0
11.25°	1	1	1	1	1	0	0	0	0	0	0
10°	1	1	1	1	1	0	0	0	0	0	0
8.75°	1	1	1	1	1	0	0	0	0	0	0
7.5°	1	1	1	1	1	0	0	0	0	0	0
6.25°	1	1	1	1	1	0	0	0	0	0	0
5°	1	1	1	1	1	0	0	0	0	0	0
3.75°	1	1	1	1	1	0	0	0	0	0	0
2.5°	1	1	1	1	1	0	0	0	0	0	0
1.25°	1	1	1	1	1	0	0	0	0	0	0
0°	1	1	1	1	1	1	0	0	0	0	0
-1.25°	1	1	1	1	1	0	0	0	0	0	0
-2.5°	1	1	1	1	1	0	0	0	0	0	0
-3.75°	1	1	1	1	1	0	0	0	0	0	0
-5°	1	1	1	1	1	0	0	0	0	0	0
-6.25°	1	1	1	1	1	0	0	0	0	0	0
-7.5°	1	1	1	1	1	0	0	0	0	0	0
-8.75°	1	1	1	1	1	0	0	0	0	0	0
-10°	1	1	1	1	1	0	0	0	0	0	0
-11.25°	1	1	1	1	1	0	0	0	0	0	0
-12.5°	1	1	1	1	1	0	0	0	0	0	0
-13.75°	1	1	1	1	1	0	0	0	0	0	0
-15°	1	1	1	1	1	0	0	0	0	0	0
-16.25°	1	1	1	1	1	0	0	0	0	0	0
-17.5°	1	1	1	1	1	0	0	0	0	0	0
-18.75°	1	1	1	1	1	0	0	0	0	0	0
-20°	1	1	1	1	1	0	0	0	0	0	0
-21.25°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	0	0	0	0	0	0
-23.75°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	1	0	0	0	0	0	0
-28.75°	1	1	1	1	1	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	1	0	0	0	0	0	0	0
-36.25°	1	1	1	1	0	0	0	0	0	0	0
-37.5°	1	1	1	1	0	0	0	0	0	0	0
-38.75°	1	1	1	1	0	0	0	0	0	0	0
-40°	1	1	1	0	0	0	0	0	0	0	0
-41.25°	1	1	1	0	0	0	0	0	0	0	0
-42.5°	1	1	1	0	0	0	0	0	0	0	0
-43.75°	1	1	1	0	0	0	0	0	0	0	0
-45°	1	1	1	0	0	0	0	0	0	0	0
-46.25°	1	1	0	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	1	0	0	0	0	0	0	0	0	0
-50°	1	1	0	0	0	0	0	0	0	0	0
-51.25°	1	0	0	0	0	0	0	0	0	0	0
-52.5°	1	0	0	0	0	0	0	0	0	0	0
-53.75°	1	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-41 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS-LSL

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)