

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4025-12-CS**

Test Date: 04/05/18

Test Information


Test Method: LM-79-08
Report Number: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-8)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/05/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4025-12-CS
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER
Light Source: (1) SORAA 4000K 90 CRI LED
SM16-07-25D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	360.5 lumens	Max Intensity:	2357 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	49.4 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	18.4°H x 18.4°V	Field Angle (10%):	40.5°H x 40.5°V
Beam Lumens:	131 lumens	Field Lumens:	298.8 lumens
Beam Efficiency:	36.3%	Field Efficiency:	82.9%
Input Watts (W):	7.3		
Input Voltage (V):	12.0		
Input Current (A _{in}):	0.642		
Voltage Rise (V):	NR		
Power Factor:	0.9913		
Total Harmonic Distortion (THDi):	26.9%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	3 HR		
Ambient Temperature (°C):	25.0		
Test Distance:	25 FT		

REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
40		0.0	0.0	0.1	0.1	0.1	0.3	0.4	0.4	0.3	0.1	0.1	0.1	0.0	0.0		
30	0.0	0.0	0.0	0.1	0.1	0.4	1.3	3.0	3.0	1.3	0.4	0.1	0.1	0.0	0.0	0.0	
20		0.0	0.0	0.1	0.2	1.3	6.4	14.5	14.5	6.4	1.3	0.2	0.1	0.0	0.0		
10	0.0	0.0	0.1	0.1	0.3	2.7	14.1	43.4	43.4	14.1	2.7	0.3	0.1	0.1	0.0	0.0	
0		0.0	0.1	0.1	0.3	2.7	14.1	43.4	43.4	14.1	2.7	0.3	0.1	0.1	0.0		
-10	0.0	0.0	0.1	0.1	0.3	2.7	14.1	43.4	43.4	14.1	2.7	0.3	0.1	0.1	0.0	0.0	
-20		0.0	0.0	0.1	0.2	1.3	6.4	14.5	14.5	6.4	1.3	0.2	0.1	0.0	0.0		
-30	0.0	0.0	0.0	0.1	0.1	0.4	1.3	3.0	3.0	1.3	0.4	0.1	0.1	0.0	0.0	0.0	
-40		0.0	0.0	0.1	0.1	0.1	0.3	0.4	0.4	0.3	0.1	0.1	0.1	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0			
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	

REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS


Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

Luminous Intensity Plot



Beam:
 H Angle: 18.4°
 V Angle: 18.4°
 Lumens: 131
 Efficiency: 36.3%

Field:
 H Angle: 40.5°
 V Angle: 40.5°
 Lumens: 298.8
 Efficiency: 82.9%

Spill:
 Lumens: 61.7
 Efficiency: 17.1%

— Vertical Distribution through 0-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	1
41.25°	0	0	0	0	0	0	0	0	0	0	1
40°	0	0	0	0	0	0	0	0	0	1	1
38.75°	0	0	0	0	0	0	0	0	0	1	1
37.5°	0	0	0	0	0	0	0	0	0	1	1
36.25°	0	0	0	0	0	0	0	0	1	1	1
35°	0	0	0	0	0	0	0	0	1	1	1



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	0	0	0	0	0	1	1	1
32.5°	0	0	0	0	0	0	0	1	1	1	1
31.25°	0	0	0	0	0	0	0	1	1	1	1
30°	0	0	0	0	0	0	0	1	1	1	1
28.75°	0	0	0	0	0	0	0	1	1	1	1
27.5°	0	0	0	0	0	0	1	1	1	1	1
26.25°	0	0	0	0	0	0	1	1	1	1	1
25°	0	0	0	0	0	0	1	1	1	1	1
23.75°	0	0	0	0	0	0	1	1	1	1	1
22.5°	0	0	0	0	0	0	1	1	1	1	1
21.25°	0	0	0	0	0	0	1	1	1	1	1
20°	0	0	0	0	0	0	1	1	1	1	1
18.75°	0	0	0	0	0	1	1	1	1	1	1
17.5°	0	0	0	0	0	1	1	1	1	1	1
16.25°	0	0	0	0	0	1	1	1	1	1	1
15°	0	0	0	0	0	1	1	1	1	1	1
13.75°	0	0	0	0	0	1	1	1	1	1	1
12.5°	0	0	0	0	0	1	1	1	1	1	1
11.25°	0	0	0	0	0	1	1	1	1	1	1
10°	0	0	0	0	0	1	1	1	1	1	1
8.75°	0	0	0	0	0	1	1	1	1	1	1
7.5°	0	0	0	0	0	1	1	1	1	1	1
6.25°	0	0	0	0	0	1	1	1	1	1	1
5°	0	0	0	0	0	1	1	1	1	1	1
3.75°	0	0	0	0	0	1	1	1	1	1	1
2.5°	0	0	0	0	0	1	1	1	1	1	1
1.25°	0	0	0	0	0	1	1	1	1	1	1
0°	0	0	0	0	1	1	1	1	1	1	1
-1.25°	0	0	0	0	0	1	1	1	1	1	1
-2.5°	0	0	0	0	0	1	1	1	1	1	1
-3.75°	0	0	0	0	0	1	1	1	1	1	1
-5°	0	0	0	0	0	1	1	1	1	1	1
-6.25°	0	0	0	0	0	1	1	1	1	1	1
-7.5°	0	0	0	0	0	1	1	1	1	1	1
-8.75°	0	0	0	0	0	1	1	1	1	1	1
-10°	0	0	0	0	0	1	1	1	1	1	1
-11.25°	0	0	0	0	0	1	1	1	1	1	1
-12.5°	0	0	0	0	0	1	1	1	1	1	1
-13.75°	0	0	0	0	0	1	1	1	1	1	1
-15°	0	0	0	0	0	1	1	1	1	1	1
-16.25°	0	0	0	0	0	1	1	1	1	1	1
-17.5°	0	0	0	0	0	1	1	1	1	1	1
-18.75°	0	0	0	0	0	1	1	1	1	1	1
-20°	0	0	0	0	0	0	1	1	1	1	1
-21.25°	0	0	0	0	0	0	1	1	1	1	1



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	0	0	0	0	0	1	1	1	1	1
-23.75°	0	0	0	0	0	0	1	1	1	1	1
-25°	0	0	0	0	0	0	1	1	1	1	1
-26.25°	0	0	0	0	0	0	1	1	1	1	1
-27.5°	0	0	0	0	0	0	1	1	1	1	1
-28.75°	0	0	0	0	0	0	0	1	1	1	1
-30°	0	0	0	0	0	0	0	1	1	1	1
-31.25°	0	0	0	0	0	0	0	1	1	1	1
-32.5°	0	0	0	0	0	0	0	1	1	1	1
-33.75°	0	0	0	0	0	0	0	0	1	1	1
-35°	0	0	0	0	0	0	0	0	1	1	1
-36.25°	0	0	0	0	0	0	0	0	1	1	1
-37.5°	0	0	0	0	0	0	0	0	0	1	1
-38.75°	0	0	0	0	0	0	0	0	0	1	1
-40°	0	0	0	0	0	0	0	0	0	1	1
-41.25°	0	0	0	0	0	0	0	0	0	0	1
-42.5°	0	0	0	0	0	0	0	0	0	0	1
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	1	1
57.5°	0	0	0	0	0	0	0	0	1	1	1
56.25°	0	0	0	0	0	0	0	1	1	1	1
55°	0	0	0	0	0	0	1	1	1	1	1
53.75°	0	0	0	0	0	1	1	1	1	1	1
52.5°	0	0	0	0	1	1	1	1	1	1	1
51.25°	0	0	0	1	1	1	1	1	1	1	1
50°	0	0	0	1	1	1	1	1	1	1	1
48.75°	0	0	1	1	1	1	1	1	1	1	1
47.5°	0	1	1	1	1	1	1	1	1	1	1
46.25°	0	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
41.25°	1	1	1	1	1	1	1	1	1	1	2
40°	1	1	1	1	1	1	1	1	1	1	2
38.75°	1	1	1	1	1	1	1	1	1	2	2
37.5°	1	1	1	1	1	1	1	1	2	2	2
36.25°	1	1	1	1	1	1	1	1	2	2	2
35°	1	1	1	1	1	1	1	2	2	2	3



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	1	1	1	2	2	3	3
32.5°	1	1	1	1	1	1	2	2	2	3	3
31.25°	1	1	1	1	1	1	2	2	3	3	3
30°	1	1	1	1	1	2	2	2	3	3	3
28.75°	1	1	1	1	1	2	2	2	3	3	3
27.5°	1	1	1	1	1	2	2	3	3	3	3
26.25°	1	1	1	1	2	2	2	3	3	3	3
25°	1	1	1	1	2	2	3	3	3	3	3
23.75°	1	1	1	1	2	2	3	3	3	3	3
22.5°	1	1	1	1	2	2	3	3	3	3	3
21.25°	1	1	1	2	2	2	3	3	3	3	3
20°	1	1	1	2	2	3	3	3	3	3	3
18.75°	1	1	1	2	2	3	3	3	3	3	3
17.5°	1	1	1	2	2	3	3	3	3	3	3
16.25°	1	1	1	2	2	3	3	3	3	3	3
15°	1	1	2	2	3	3	3	3	3	3	3
13.75°	1	1	2	2	3	3	3	3	3	3	3
12.5°	1	1	2	2	3	3	3	3	3	3	4
11.25°	1	1	2	2	3	3	3	3	3	3	4
10°	1	1	2	2	3	3	3	3	3	3	4
8.75°	1	1	2	2	3	3	3	3	3	3	4
7.5°	1	1	2	2	3	3	3	3	3	3	4
6.25°	1	1	2	2	3	3	3	3	3	3	4
5°	1	1	2	2	3	3	3	3	3	3	4
3.75°	1	1	2	2	3	3	3	3	3	3	4
2.5°	1	1	2	2	3	3	3	3	3	3	4
1.25°	1	1	2	2	3	3	3	3	3	3	4
0°	1	2	2	3	3	3	3	3	3	4	4
-1.25°	1	1	2	2	3	3	3	3	3	3	4
-2.5°	1	1	2	2	3	3	3	3	3	3	4
-3.75°	1	1	2	2	3	3	3	3	3	3	4
-5°	1	1	2	2	3	3	3	3	3	3	4
-6.25°	1	1	2	2	3	3	3	3	3	3	4
-7.5°	1	1	2	2	3	3	3	3	3	3	4
-8.75°	1	1	2	2	3	3	3	3	3	3	4
-10°	1	1	2	2	3	3	3	3	3	3	4
-11.25°	1	1	2	2	3	3	3	3	3	3	4
-12.5°	1	1	2	2	3	3	3	3	3	3	4
-13.75°	1	1	2	2	3	3	3	3	3	3	3
-15°	1	1	2	2	3	3	3	3	3	3	3
-16.25°	1	1	1	2	2	3	3	3	3	3	3
-17.5°	1	1	1	2	2	3	3	3	3	3	3
-18.75°	1	1	1	2	2	3	3	3	3	3	3
-20°	1	1	1	2	2	3	3	3	3	3	3
-21.25°	1	1	1	2	2	2	3	3	3	3	3



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	1	1	1	2	2	3	3	3	3	3
-23.75°	1	1	1	1	2	2	3	3	3	3	3
-25°	1	1	1	1	2	2	3	3	3	3	3
-26.25°	1	1	1	1	2	2	2	3	3	3	3
-27.5°	1	1	1	1	1	2	2	3	3	3	3
-28.75°	1	1	1	1	1	2	2	2	3	3	3
-30°	1	1	1	1	1	2	2	2	3	3	3
-31.25°	1	1	1	1	1	1	2	2	3	3	3
-32.5°	1	1	1	1	1	1	2	2	2	3	3
-33.75°	1	1	1	1	1	1	1	2	2	3	3
-35°	1	1	1	1	1	1	1	2	2	2	3
-36.25°	1	1	1	1	1	1	1	1	2	2	2
-37.5°	1	1	1	1	1	1	1	1	2	2	2
-38.75°	1	1	1	1	1	1	1	1	1	2	2
-40°	1	1	1	1	1	1	1	1	1	1	2
-41.25°	1	1	1	1	1	1	1	1	1	1	2
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	0	1	1	1	1	1	1	1	1	1	1
-47.5°	0	1	1	1	1	1	1	1	1	1	1
-48.75°	0	0	1	1	1	1	1	1	1	1	1
-50°	0	0	0	1	1	1	1	1	1	1	1
-51.25°	0	0	0	1	1	1	1	1	1	1	1
-52.5°	0	0	0	0	1	1	1	1	1	1	1
-53.75°	0	0	0	0	0	1	1	1	1	1	1
-55°	0	0	0	0	0	0	1	1	1	1	1
-56.25°	0	0	0	0	0	0	0	1	1	1	1
-57.5°	0	0	0	0	0	0	0	0	1	1	1
-58.75°	0	0	0	0	0	0	0	0	0	1	1
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	1
65°	0	0	0	0	0	0	0	1	1	1	1
63.75°	0	0	0	0	0	1	1	1	1	1	1
62.5°	0	0	0	1	1	1	1	1	1	1	1
61.25°	0	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	2	2
51.25°	1	1	1	1	1	1	1	1	2	2	2
50°	1	1	1	1	1	1	2	2	2	2	2
48.75°	1	1	1	1	1	2	2	2	2	3	3
47.5°	1	1	1	1	2	2	2	2	3	3	3
46.25°	1	1	1	2	2	2	3	3	3	3	3
45°	1	1	2	2	2	3	3	3	3	3	3
43.75°	1	2	2	2	3	3	3	3	3	3	3
42.5°	2	2	2	3	3	3	3	3	3	3	3
41.25°	2	2	3	3	3	3	3	3	3	3	3
40°	2	2	3	3	3	3	3	3	3	3	3
38.75°	2	3	3	3	3	3	3	3	3	3	4
37.5°	3	3	3	3	3	3	3	3	3	4	4
36.25°	3	3	3	3	3	3	3	3	4	4	4
35°	3	3	3	3	3	3	3	4	4	4	4



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	3	3	3	3	3	3	4	4	4	4
32.5°	3	3	3	3	3	3	4	4	4	4	4
31.25°	3	3	3	3	3	4	4	4	4	4	4
30°	3	3	3	3	3	4	4	4	4	4	4
28.75°	3	3	3	3	4	4	4	4	4	4	4
27.5°	3	3	3	4	4	4	4	4	4	4	4
26.25°	3	3	3	4	4	4	4	4	4	4	5
25°	3	3	4	4	4	4	4	4	4	4	5
23.75°	3	3	4	4	4	4	4	4	4	5	5
22.5°	3	3	4	4	4	4	4	4	4	5	5
21.25°	3	4	4	4	4	4	4	4	5	5	5
20°	3	4	4	4	4	4	4	4	5	5	6
18.75°	3	4	4	4	4	4	4	5	5	5	6
17.5°	4	4	4	4	4	4	4	5	5	6	6
16.25°	4	4	4	4	4	4	4	5	5	6	7
15°	4	4	4	4	4	4	5	5	6	6	7
13.75°	4	4	4	4	4	4	5	5	6	6	7
12.5°	4	4	4	4	4	4	5	5	6	7	8
11.25°	4	4	4	4	4	5	5	5	6	7	8
10°	4	4	4	4	4	5	5	6	6	7	8
8.75°	4	4	4	4	4	5	5	6	6	7	8
7.5°	4	4	4	4	4	5	5	6	7	7	9
6.25°	4	4	4	4	4	5	5	6	7	8	9
5°	4	4	4	4	4	5	5	6	7	8	9
3.75°	4	4	4	4	4	5	5	6	7	8	9
2.5°	4	4	4	4	4	5	5	6	7	8	9
1.25°	4	4	4	4	4	5	5	6	7	8	9
0°	4	4	4	4	5	5	6	6	7	8	10
-1.25°	4	4	4	4	4	5	5	6	7	8	9
-2.5°	4	4	4	4	4	5	5	6	7	8	9
-3.75°	4	4	4	4	4	5	5	6	7	8	9
-5°	4	4	4	4	4	5	5	6	7	8	9
-6.25°	4	4	4	4	4	5	5	6	7	8	9
-7.5°	4	4	4	4	4	5	5	6	7	7	9
-8.75°	4	4	4	4	4	5	5	6	6	7	8
-10°	4	4	4	4	4	5	5	6	6	7	8
-11.25°	4	4	4	4	4	5	5	5	6	7	8
-12.5°	4	4	4	4	4	4	5	5	6	7	8
-13.75°	4	4	4	4	4	4	5	5	6	6	7
-15°	4	4	4	4	4	4	5	5	6	6	7
-16.25°	4	4	4	4	4	4	4	5	5	6	7
-17.5°	4	4	4	4	4	4	4	5	5	6	6
-18.75°	3	4	4	4	4	4	4	5	5	5	6
-20°	3	4	4	4	4	4	4	4	5	5	6
-21.25°	3	4	4	4	4	4	4	4	5	5	5



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	3	3	4	4	4	4	4	4	4	5	5
-23.75°	3	3	4	4	4	4	4	4	4	5	5
-25°	3	3	4	4	4	4	4	4	4	4	5
-26.25°	3	3	3	4	4	4	4	4	4	4	5
-27.5°	3	3	3	4	4	4	4	4	4	4	4
-28.75°	3	3	3	3	4	4	4	4	4	4	4
-30°	3	3	3	3	3	4	4	4	4	4	4
-31.25°	3	3	3	3	3	4	4	4	4	4	4
-32.5°	3	3	3	3	3	3	4	4	4	4	4
-33.75°	3	3	3	3	3	3	3	4	4	4	4
-35°	3	3	3	3	3	3	3	4	4	4	4
-36.25°	3	3	3	3	3	3	3	3	4	4	4
-37.5°	3	3	3	3	3	3	3	3	3	4	4
-38.75°	2	3	3	3	3	3	3	3	3	3	4
-40°	2	2	3	3	3	3	3	3	3	3	3
-41.25°	2	2	3	3	3	3	3	3	3	3	3
-42.5°	2	2	2	3	3	3	3	3	3	3	3
-43.75°	1	2	2	2	3	3	3	3	3	3	3
-45°	1	1	2	2	2	3	3	3	3	3	3
-46.25°	1	1	1	2	2	2	3	3	3	3	3
-47.5°	1	1	1	1	2	2	2	2	3	3	3
-48.75°	1	1	1	1	1	2	2	2	2	3	3
-50°	1	1	1	1	1	1	2	2	2	2	2
-51.25°	1	1	1	1	1	1	1	1	2	2	2
-52.5°	1	1	1	1	1	1	1	1	1	2	2
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	0	1	1	1	1	1	1	1	1	1	1
-62.5°	0	0	0	1	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	1	1	1	1	1	1
-65°	0	0	0	0	0	0	0	1	1	1	1
-66.25°	0	0	0	0	0	0	0	0	0	0	1
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	1	1	1	1	1
67.5°	0	0	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	2	2	2	2
56.25°	1	1	1	1	2	2	2	2	2	2	2
55°	1	1	2	2	2	2	2	2	3	3	3
53.75°	2	2	2	2	2	2	3	3	3	3	3
52.5°	2	2	2	3	3	3	3	3	3	3	3
51.25°	2	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	3	3	3	3	3	3	3	3	3	3	3
46.25°	3	3	3	3	3	3	3	3	4	4	4
45°	3	3	3	3	3	3	4	4	4	4	4
43.75°	3	3	3	3	3	4	4	4	4	4	4
42.5°	3	3	3	4	4	4	4	4	4	4	4
41.25°	3	3	4	4	4	4	4	4	4	4	4
40°	4	4	4	4	4	4	4	4	4	4	4
38.75°	4	4	4	4	4	4	4	4	4	4	4
37.5°	4	4	4	4	4	4	4	4	4	5	5
36.25°	4	4	4	4	4	4	4	5	5	5	5
35°	4	4	4	4	4	4	5	5	5	5	6



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	4	4	4	4	4	5	5	5	6	6	6
32.5°	4	4	4	4	5	5	5	6	6	6	7
31.25°	4	4	4	5	5	5	6	6	7	7	8
30°	4	4	5	5	5	6	6	7	7	8	9
28.75°	4	5	5	5	6	6	7	7	8	9	10
27.5°	5	5	5	6	6	7	8	8	9	10	11
26.25°	5	5	6	6	7	7	8	9	10	11	13
25°	5	6	6	7	7	8	9	10	11	13	15
23.75°	5	6	6	7	8	9	10	11	13	15	17
22.5°	6	6	7	8	9	10	11	13	15	17	20
21.25°	6	7	7	8	10	11	13	14	16	19	22
20°	6	7	8	9	10	12	14	16	19	22	26
18.75°	7	8	9	10	11	13	15	18	21	25	33
17.5°	7	8	9	11	12	14	17	20	23	31	40
16.25°	7	9	10	11	13	16	19	22	28	38	47
15°	8	9	10	12	15	17	21	24	34	44	62
13.75°	8	10	11	13	16	19	22	29	39	53	77
12.5°	9	10	12	14	17	20	24	34	45	66	90
11.25°	9	11	13	15	18	22	28	39	52	77	102
10°	10	11	13	16	19	23	32	43	63	88	114
8.75°	10	12	14	17	20	25	35	46	72	98	124
7.5°	10	12	14	17	21	27	38	53	80	107	134
6.25°	10	12	15	18	22	30	41	60	87	114	142
5°	11	13	15	19	23	32	43	65	93	120	148
3.75°	11	13	16	19	23	33	45	69	97	125	153
2.5°	11	13	16	20	24	35	46	73	100	129	157
1.25°	11	13	16	20	24	35	47	74	102	131	159
0°	11	14	16	20	24	36	47	75	103	132	160
-1.25°	11	13	16	20	24	35	47	74	102	131	159
-2.5°	11	13	16	20	24	35	46	73	100	129	157
-3.75°	11	13	16	19	23	33	45	69	97	125	153
-5°	11	13	15	19	23	32	43	65	93	120	148
-6.25°	10	12	15	18	22	30	41	60	87	114	142
-7.5°	10	12	14	17	21	27	38	53	80	107	134
-8.75°	10	12	14	17	20	25	35	46	72	98	124
-10°	10	11	13	16	19	23	32	43	63	88	114
-11.25°	9	11	13	15	18	22	28	39	52	77	102
-12.5°	9	10	12	14	17	20	24	34	45	66	90
-13.75°	8	10	11	13	16	19	22	29	39	53	77
-15°	8	9	10	12	15	17	21	24	34	44	62
-16.25°	7	9	10	11	13	16	19	22	28	38	47
-17.5°	7	8	9	11	12	14	17	20	23	31	40
-18.75°	7	8	9	10	11	13	15	18	21	25	33
-20°	6	7	8	9	10	12	14	16	19	22	26
-21.25°	6	7	7	8	10	11	13	14	16	19	22



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	6	6	7	8	9	10	11	13	15	17	20
-23.75°	5	6	6	7	8	9	10	11	13	15	17
-25°	5	6	6	7	7	8	9	10	11	13	15
-26.25°	5	5	6	6	7	7	8	9	10	11	13
-27.5°	5	5	5	6	6	7	8	8	9	10	11
-28.75°	4	5	5	5	6	6	7	7	8	9	10
-30°	4	4	5	5	5	6	6	7	7	8	9
-31.25°	4	4	4	5	5	5	6	6	7	7	8
-32.5°	4	4	4	4	5	5	5	6	6	6	7
-33.75°	4	4	4	4	4	5	5	5	6	6	6
-35°	4	4	4	4	4	4	5	5	5	5	6
-36.25°	4	4	4	4	4	4	4	5	5	5	5
-37.5°	4	4	4	4	4	4	4	4	4	5	5
-38.75°	4	4	4	4	4	4	4	4	4	4	4
-40°	4	4	4	4	4	4	4	4	4	4	4
-41.25°	3	3	4	4	4	4	4	4	4	4	4
-42.5°	3	3	3	4	4	4	4	4	4	4	4
-43.75°	3	3	3	3	3	4	4	4	4	4	4
-45°	3	3	3	3	3	3	4	4	4	4	4
-46.25°	3	3	3	3	3	3	3	3	4	4	4
-47.5°	3	3	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	2	3	3	3	3	3	3	3	3	3	3
-52.5°	2	2	2	3	3	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	3	3	3	3	3
-55°	1	1	2	2	2	2	2	2	3	3	3
-56.25°	1	1	1	1	2	2	2	2	2	2	2
-57.5°	1	1	1	1	1	1	1	2	2	2	2
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	0	0	1	1	1	1	1	1	1	1	1
-68.75°	0	0	0	0	0	0	1	1	1	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	3	3	3	3	3	3
56.25°	2	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	4	4	4	4
48.75°	3	3	3	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	4	4	4	4	4	4	4	4	5	5	5
41.25°	4	4	4	4	4	5	5	5	5	5	5
40°	4	4	5	5	5	5	5	5	5	6	6
38.75°	5	5	5	5	5	6	6	6	6	6	6
37.5°	5	5	5	6	6	6	6	7	7	7	7
36.25°	5	6	6	6	7	7	7	8	8	8	8
35°	6	6	7	7	7	8	8	9	9	10	10



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	7	7	8	8	9	9	10	10	11	11	12
32.5°	7	8	9	9	10	10	11	12	13	13	14
31.25°	8	9	10	11	11	12	13	14	15	16	17
30°	10	10	11	12	13	15	16	17	18	19	20
28.75°	11	12	13	14	16	17	19	20	22	23	25
27.5°	13	14	15	17	19	21	22	24	28	32	35
26.25°	14	16	18	20	22	24	29	34	39	43	46
25°	16	19	21	23	28	34	39	45	52	63	72
23.75°	19	22	25	31	38	44	53	66	77	88	98
22.5°	22	26	33	40	47	62	77	90	102	114	124
21.25°	27	34	42	52	69	85	100	114	128	140	151
20°	34	42	55	73	91	107	123	138	152	168	185
18.75°	42	55	74	93	112	129	146	163	185	205	223
17.5°	52	73	93	113	132	151	173	197	220	241	267
16.25°	69	91	112	132	153	178	205	231	259	290	318
15°	85	107	129	151	178	207	236	270	306	338	371
13.75°	100	123	146	173	205	236	274	314	351	393	434
12.5°	114	138	163	197	231	270	314	355	404	451	495
11.25°	128	152	185	220	259	306	351	404	457	507	573
10°	140	168	205	241	290	338	393	451	507	582	652
8.75°	151	185	223	267	318	371	434	495	573	652	735
7.5°	161	200	239	291	344	405	471	546	633	718	847
6.25°	173	213	257	311	367	436	503	595	686	811	948
5°	183	224	273	329	391	461	540	636	742	891	1037
3.75°	191	233	285	342	409	481	571	670	801	957	1125
2.5°	197	239	295	352	423	496	593	695	845	1006	1192
1.25°	201	243	300	358	431	505	607	710	871	1036	1235
0°	202	244	302	360	434	508	612	715	881	1046	1249
-1.25°	201	243	300	358	431	505	607	710	871	1036	1235
-2.5°	197	239	295	352	423	496	593	695	845	1006	1192
-3.75°	191	233	285	342	409	481	571	670	801	957	1125
-5°	183	224	273	329	391	461	540	636	742	891	1037
-6.25°	173	213	257	311	367	436	503	595	686	811	948
-7.5°	161	200	239	291	344	405	471	546	633	718	847
-8.75°	151	185	223	267	318	371	434	495	573	652	735
-10°	140	168	205	241	290	338	393	451	507	582	652
-11.25°	128	152	185	220	259	306	351	404	457	507	573
-12.5°	114	138	163	197	231	270	314	355	404	451	495
-13.75°	100	123	146	173	205	236	274	314	351	393	434
-15°	85	107	129	151	178	207	236	270	306	338	371
-16.25°	69	91	112	132	153	178	205	231	259	290	318
-17.5°	52	73	93	113	132	151	173	197	220	241	267
-18.75°	42	55	74	93	112	129	146	163	185	205	223
-20°	34	42	55	73	91	107	123	138	152	168	185
-21.25°	27	34	42	52	69	85	100	114	128	140	151



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	22	26	33	40	47	62	77	90	102	114	124
-23.75°	19	22	25	31	38	44	53	66	77	88	98
-25°	16	19	21	23	28	34	39	45	52	63	72
-26.25°	14	16	18	20	22	24	29	34	39	43	46
-27.5°	13	14	15	17	19	21	22	24	28	32	35
-28.75°	11	12	13	14	16	17	19	20	22	23	25
-30°	10	10	11	12	13	15	16	17	18	19	20
-31.25°	8	9	10	11	11	12	13	14	15	16	17
-32.5°	7	8	9	9	10	10	11	12	13	13	14
-33.75°	7	7	8	8	9	9	10	10	11	11	12
-35°	6	6	7	7	7	8	8	9	9	10	10
-36.25°	5	6	6	6	7	7	7	8	8	8	8
-37.5°	5	5	5	6	6	6	6	7	7	7	7
-38.75°	5	5	5	5	5	6	6	6	6	6	6
-40°	4	4	5	5	5	5	5	5	5	6	6
-41.25°	4	4	4	4	4	5	5	5	5	5	5
-42.5°	4	4	4	4	4	4	4	4	5	5	5
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	3	3	3	4	4	4	4	4	4	4	4
-50°	3	3	3	3	3	3	3	4	4	4	4
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	2	3	3	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	0	1	1	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	2	1	1	1	1
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	3	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	4	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	5	4	4	4	4
42.5°	5	5	5	5	5	5	5	5	5	5	5
41.25°	5	5	5	5	5	5	6	5	5	5	5
40°	6	6	6	6	6	6	6	6	6	6	6
38.75°	7	7	7	7	7	7	7	7	7	7	7
37.5°	7	8	8	8	8	8	8	8	8	8	8
36.25°	9	9	9	9	9	9	10	9	9	9	9
35°	10	10	11	11	11	11	11	11	11	11	11



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	12	12	13	13	13	13	14	13	13	13	13
32.5°	14	15	15	16	16	16	16	16	16	16	15
31.25°	17	18	19	19	20	20	20	20	20	19	19
30°	21	22	23	23	24	24	24	24	24	23	23
28.75°	27	30	32	33	35	35	36	35	35	33	32
27.5°	38	41	43	45	46	47	47	47	46	45	43
26.25°	53	60	65	69	73	74	75	74	73	69	65
25°	80	87	93	97	100	102	103	102	100	97	93
23.75°	107	114	120	125	129	131	132	131	129	125	120
22.5°	134	142	148	153	157	159	160	159	157	153	148
21.25°	161	173	183	191	197	201	202	201	197	191	183
20°	200	213	224	233	239	243	244	243	239	233	224
18.75°	239	257	273	285	295	300	302	300	295	285	273
17.5°	291	311	329	342	352	358	360	358	352	342	329
16.25°	344	367	391	409	423	431	434	431	423	409	391
15°	405	436	461	481	496	505	508	505	496	481	461
13.75°	471	503	540	571	593	607	612	607	593	571	540
12.5°	546	595	636	670	695	710	715	710	695	670	636
11.25°	633	686	742	801	845	871	881	871	845	801	742
10°	718	811	891	957	1006	1036	1046	1036	1006	957	891
8.75°	847	948	1037	1125	1192	1235	1249	1235	1192	1125	1037
7.5°	968	1086	1207	1310	1389	1441	1459	1441	1389	1310	1207
6.25°	1086	1236	1372	1496	1592	1653	1674	1653	1592	1496	1372
5°	1207	1372	1534	1675	1784	1854	1879	1854	1784	1675	1534
3.75°	1310	1496	1675	1830	1953	2035	2061	2035	1953	1830	1675
2.5°	1389	1592	1784	1953	2089	2178	2207	2178	2089	1953	1784
1.25°	1441	1653	1854	2035	2178	2273	2307	2273	2178	2035	1854
0°	1459	1674	1879	2061	2207	2307	2357	2307	2207	2061	1879
-1.25°	1441	1653	1854	2035	2178	2273	2307	2273	2178	2035	1854
-2.5°	1389	1592	1784	1953	2089	2178	2207	2178	2089	1953	1784
-3.75°	1310	1496	1675	1830	1953	2035	2061	2035	1953	1830	1675
-5°	1207	1372	1534	1675	1784	1854	1879	1854	1784	1675	1534
-6.25°	1086	1236	1372	1496	1592	1653	1674	1653	1592	1496	1372
-7.5°	968	1086	1207	1310	1389	1441	1459	1441	1389	1310	1207
-8.75°	847	948	1037	1125	1192	1235	1249	1235	1192	1125	1037
-10°	718	811	891	957	1006	1036	1046	1036	1006	957	891
-11.25°	633	686	742	801	845	871	881	871	845	801	742
-12.5°	546	595	636	670	695	710	715	710	695	670	636
-13.75°	471	503	540	571	593	607	612	607	593	571	540
-15°	405	436	461	481	496	505	508	505	496	481	461
-16.25°	344	367	391	409	423	431	434	431	423	409	391
-17.5°	291	311	329	342	352	358	360	358	352	342	329
-18.75°	239	257	273	285	295	300	302	300	295	285	273
-20°	200	213	224	233	239	243	244	243	239	233	224
-21.25°	161	173	183	191	197	201	202	201	197	191	183



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	134	142	148	153	157	159	160	159	157	153	148
-23.75°	107	114	120	125	129	131	132	131	129	125	120
-25°	80	87	93	97	100	102	103	102	100	97	93
-26.25°	53	60	65	69	73	74	75	74	73	69	65
-27.5°	38	41	43	45	46	47	47	47	46	45	43
-28.75°	27	30	32	33	35	35	36	35	35	33	32
-30°	21	22	23	23	24	24	24	24	24	23	23
-31.25°	17	18	19	19	20	20	20	20	20	19	19
-32.5°	14	15	15	16	16	16	16	16	16	16	15
-33.75°	12	12	13	13	13	13	14	13	13	13	13
-35°	10	10	11	11	11	11	11	11	11	11	11
-36.25°	9	9	9	9	9	9	10	9	9	9	9
-37.5°	7	8	8	8	8	8	8	8	8	8	8
-38.75°	7	7	7	7	7	7	7	7	7	7	7
-40°	6	6	6	6	6	6	6	6	6	6	6
-41.25°	5	5	5	5	5	5	6	5	5	5	5
-42.5°	5	5	5	5	5	5	5	5	5	5	5
-43.75°	4	4	4	4	4	4	5	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	3	3	3	3	3	3	4	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	3	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	1	1	1	1	1	2	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	2	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	3	3	3
53.75°	3	3	3	3	3	3	3	3	3	3	3
52.5°	3	3	3	3	3	3	3	3	3	3	3
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	4	4	4	4	4	4	3	3	3	3	3
48.75°	4	4	4	4	4	4	4	4	4	4	3
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	4	4
42.5°	5	5	5	5	5	4	4	4	4	4	4
41.25°	5	5	5	5	5	5	5	5	4	4	4
40°	6	6	6	6	5	5	5	5	5	5	5
38.75°	7	7	6	6	6	6	6	6	5	5	5
37.5°	8	7	7	7	7	7	6	6	6	6	5
36.25°	9	9	8	8	8	8	7	7	7	6	6
35°	10	10	10	10	9	9	8	8	7	7	7



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	12	12	12	11	11	10	10	9	9	8	8
32.5°	15	14	14	13	13	12	11	10	10	9	9
31.25°	18	17	17	16	15	14	13	12	11	11	10
30°	22	21	20	19	18	17	16	15	13	12	11
28.75°	30	27	25	23	22	20	19	17	16	14	13
27.5°	41	38	35	32	28	24	22	21	19	17	15
26.25°	60	53	46	43	39	34	29	24	22	20	18
25°	87	80	72	63	52	45	39	34	28	23	21
23.75°	114	107	98	88	77	66	53	44	38	31	25
22.5°	142	134	124	114	102	90	77	62	47	40	33
21.25°	173	161	151	140	128	114	100	85	69	52	42
20°	213	200	185	168	152	138	123	107	91	73	55
18.75°	257	239	223	205	185	163	146	129	112	93	74
17.5°	311	291	267	241	220	197	173	151	132	113	93
16.25°	367	344	318	290	259	231	205	178	153	132	112
15°	436	405	371	338	306	270	236	207	178	151	129
13.75°	503	471	434	393	351	314	274	236	205	173	146
12.5°	595	546	495	451	404	355	314	270	231	197	163
11.25°	686	633	573	507	457	404	351	306	259	220	185
10°	811	718	652	582	507	451	393	338	290	241	205
8.75°	948	847	735	652	573	495	434	371	318	267	223
7.5°	1086	968	847	718	633	546	471	405	344	291	239
6.25°	1236	1086	948	811	686	595	503	436	367	311	257
5°	1372	1207	1037	891	742	636	540	461	391	329	273
3.75°	1496	1310	1125	957	801	670	571	481	409	342	285
2.5°	1592	1389	1192	1006	845	695	593	496	423	352	295
1.25°	1653	1441	1235	1036	871	710	607	505	431	358	300
0°	1674	1459	1249	1046	881	715	612	508	434	360	302
-1.25°	1653	1441	1235	1036	871	710	607	505	431	358	300
-2.5°	1592	1389	1192	1006	845	695	593	496	423	352	295
-3.75°	1496	1310	1125	957	801	670	571	481	409	342	285
-5°	1372	1207	1037	891	742	636	540	461	391	329	273
-6.25°	1236	1086	948	811	686	595	503	436	367	311	257
-7.5°	1086	968	847	718	633	546	471	405	344	291	239
-8.75°	948	847	735	652	573	495	434	371	318	267	223
-10°	811	718	652	582	507	451	393	338	290	241	205
-11.25°	686	633	573	507	457	404	351	306	259	220	185
-12.5°	595	546	495	451	404	355	314	270	231	197	163
-13.75°	503	471	434	393	351	314	274	236	205	173	146
-15°	436	405	371	338	306	270	236	207	178	151	129
-16.25°	367	344	318	290	259	231	205	178	153	132	112
-17.5°	311	291	267	241	220	197	173	151	132	113	93
-18.75°	257	239	223	205	185	163	146	129	112	93	74
-20°	213	200	185	168	152	138	123	107	91	73	55
-21.25°	173	161	151	140	128	114	100	85	69	52	42



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	142	134	124	114	102	90	77	62	47	40	33
-23.75°	114	107	98	88	77	66	53	44	38	31	25
-25°	87	80	72	63	52	45	39	34	28	23	21
-26.25°	60	53	46	43	39	34	29	24	22	20	18
-27.5°	41	38	35	32	28	24	22	21	19	17	15
-28.75°	30	27	25	23	22	20	19	17	16	14	13
-30°	22	21	20	19	18	17	16	15	13	12	11
-31.25°	18	17	17	16	15	14	13	12	11	11	10
-32.5°	15	14	14	13	13	12	11	10	10	9	9
-33.75°	12	12	12	11	11	10	10	9	9	8	8
-35°	10	10	10	10	9	9	8	8	7	7	7
-36.25°	9	9	8	8	8	8	7	7	7	6	6
-37.5°	8	7	7	7	7	7	6	6	6	6	5
-38.75°	7	7	6	6	6	6	6	6	5	5	5
-40°	6	6	6	6	5	5	5	5	5	5	5
-41.25°	5	5	5	5	5	5	5	5	4	4	4
-42.5°	5	5	5	5	5	4	4	4	4	4	4
-43.75°	4	4	4	4	4	4	4	4	4	4	4
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	3
-50°	4	4	4	4	4	4	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	3
-53.75°	3	3	3	3	3	3	3	3	3	3	3
-55°	3	3	3	3	3	3	3	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	1	1	1	0	0	0	0
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	2	2	1	1	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	2	1	1	1	1	1
56.25°	3	2	2	2	2	2	2	2	2	1	1
55°	3	3	3	3	3	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	3	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	3	3	2
51.25°	3	3	3	3	3	3	3	3	3	3	3
50°	3	3	3	3	3	3	3	3	3	3	3
48.75°	3	3	3	3	3	3	3	3	3	3	3
47.5°	4	4	3	3	3	3	3	3	3	3	3
46.25°	4	4	4	4	4	3	3	3	3	3	3
45°	4	4	4	4	4	4	4	3	3	3	3
43.75°	4	4	4	4	4	4	4	4	3	3	3
42.5°	4	4	4	4	4	4	4	4	4	4	3
41.25°	4	4	4	4	4	4	4	4	4	4	4
40°	4	4	4	4	4	4	4	4	4	4	4
38.75°	5	5	4	4	4	4	4	4	4	4	4
37.5°	5	5	5	5	4	4	4	4	4	4	4
36.25°	6	5	5	5	5	5	4	4	4	4	4
35°	6	6	6	5	5	5	5	4	4	4	4



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	7	7	6	6	6	5	5	5	4	4	4
32.5°	8	7	7	6	6	6	5	5	5	4	4
31.25°	9	8	8	7	7	6	6	5	5	5	4
30°	10	10	9	8	7	7	6	6	5	5	5
28.75°	12	11	10	9	8	7	7	6	6	5	5
27.5°	14	13	11	10	9	8	8	7	6	6	5
26.25°	16	14	13	11	10	9	8	7	7	6	6
25°	19	16	15	13	11	10	9	8	7	7	6
23.75°	22	19	17	15	13	11	10	9	8	7	6
22.5°	26	22	20	17	15	13	11	10	9	8	7
21.25°	34	27	22	19	16	14	13	11	10	8	7
20°	42	34	26	22	19	16	14	12	10	9	8
18.75°	55	42	33	25	21	18	15	13	11	10	9
17.5°	73	52	40	31	23	20	17	14	12	11	9
16.25°	91	69	47	38	28	22	19	16	13	11	10
15°	107	85	62	44	34	24	21	17	15	12	10
13.75°	123	100	77	53	39	29	22	19	16	13	11
12.5°	138	114	90	66	45	34	24	20	17	14	12
11.25°	152	128	102	77	52	39	28	22	18	15	13
10°	168	140	114	88	63	43	32	23	19	16	13
8.75°	185	151	124	98	72	46	35	25	20	17	14
7.5°	200	161	134	107	80	53	38	27	21	17	14
6.25°	213	173	142	114	87	60	41	30	22	18	15
5°	224	183	148	120	93	65	43	32	23	19	15
3.75°	233	191	153	125	97	69	45	33	23	19	16
2.5°	239	197	157	129	100	73	46	35	24	20	16
1.25°	243	201	159	131	102	74	47	35	24	20	16
0°	244	202	160	132	103	75	47	36	24	20	16
-1.25°	243	201	159	131	102	74	47	35	24	20	16
-2.5°	239	197	157	129	100	73	46	35	24	20	16
-3.75°	233	191	153	125	97	69	45	33	23	19	16
-5°	224	183	148	120	93	65	43	32	23	19	15
-6.25°	213	173	142	114	87	60	41	30	22	18	15
-7.5°	200	161	134	107	80	53	38	27	21	17	14
-8.75°	185	151	124	98	72	46	35	25	20	17	14
-10°	168	140	114	88	63	43	32	23	19	16	13
-11.25°	152	128	102	77	52	39	28	22	18	15	13
-12.5°	138	114	90	66	45	34	24	20	17	14	12
-13.75°	123	100	77	53	39	29	22	19	16	13	11
-15°	107	85	62	44	34	24	21	17	15	12	10
-16.25°	91	69	47	38	28	22	19	16	13	11	10
-17.5°	73	52	40	31	23	20	17	14	12	11	9
-18.75°	55	42	33	25	21	18	15	13	11	10	9
-20°	42	34	26	22	19	16	14	12	10	9	8
-21.25°	34	27	22	19	16	14	13	11	10	8	7



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	26	22	20	17	15	13	11	10	9	8	7
-23.75°	22	19	17	15	13	11	10	9	8	7	6
-25°	19	16	15	13	11	10	9	8	7	7	6
-26.25°	16	14	13	11	10	9	8	7	7	6	6
-27.5°	14	13	11	10	9	8	8	7	6	6	5
-28.75°	12	11	10	9	8	7	7	6	6	5	5
-30°	10	10	9	8	7	7	6	6	5	5	5
-31.25°	9	8	8	7	7	6	6	5	5	5	4
-32.5°	8	7	7	6	6	6	5	5	5	4	4
-33.75°	7	7	6	6	6	5	5	5	4	4	4
-35°	6	6	6	5	5	5	5	4	4	4	4
-36.25°	6	5	5	5	5	5	4	4	4	4	4
-37.5°	5	5	5	5	4	4	4	4	4	4	4
-38.75°	5	5	4	4	4	4	4	4	4	4	4
-40°	4	4	4	4	4	4	4	4	4	4	4
-41.25°	4	4	4	4	4	4	4	4	4	4	4
-42.5°	4	4	4	4	4	4	4	4	4	4	3
-43.75°	4	4	4	4	4	4	4	4	3	3	3
-45°	4	4	4	4	4	4	4	3	3	3	3
-46.25°	4	4	4	4	4	3	3	3	3	3	3
-47.5°	4	4	3	3	3	3	3	3	3	3	3
-48.75°	3	3	3	3	3	3	3	3	3	3	3
-50°	3	3	3	3	3	3	3	3	3	3	3
-51.25°	3	3	3	3	3	3	3	3	3	3	3
-52.5°	3	3	3	3	3	3	3	3	3	3	2
-53.75°	3	3	3	3	3	3	3	2	2	2	2
-55°	3	3	3	3	3	2	2	2	2	2	2
-56.25°	3	2	2	2	2	2	2	2	2	1	1
-57.5°	2	2	2	2	2	2	1	1	1	1	1
-58.75°	2	2	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	1	1	1	0	0	0	0	0	0	0	0
65°	1	1	1	1	1	1	0	0	0	0	0
63.75°	1	1	1	1	1	1	1	1	0	0	0
62.5°	1	1	1	1	1	1	1	1	1	1	0
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	2	2	1	1	1	1	1	1	1	1	1
52.5°	2	2	2	2	1	1	1	1	1	1	1
51.25°	3	2	2	2	2	1	1	1	1	1	1
50°	3	3	2	2	2	2	2	1	1	1	1
48.75°	3	3	3	3	2	2	2	2	1	1	1
47.5°	3	3	3	3	3	2	2	2	2	1	1
46.25°	3	3	3	3	3	3	3	2	2	2	1
45°	3	3	3	3	3	3	3	3	2	2	2
43.75°	3	3	3	3	3	3	3	3	3	2	2
42.5°	3	3	3	3	3	3	3	3	3	3	2
41.25°	3	3	3	3	3	3	3	3	3	3	3
40°	4	4	3	3	3	3	3	3	3	3	3
38.75°	4	4	4	3	3	3	3	3	3	3	3
37.5°	4	4	4	4	3	3	3	3	3	3	3
36.25°	4	4	4	4	4	3	3	3	3	3	3
35°	4	4	4	4	4	4	3	3	3	3	3



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	4	4	4	4	4	4	3	3	3	3	3
32.5°	4	4	4	4	4	4	4	3	3	3	3
31.25°	4	4	4	4	4	4	4	4	3	3	3
30°	4	4	4	4	4	4	4	4	3	3	3
28.75°	5	4	4	4	4	4	4	4	4	3	3
27.5°	5	5	4	4	4	4	4	4	4	4	3
26.25°	5	5	5	4	4	4	4	4	4	4	3
25°	6	5	5	4	4	4	4	4	4	4	4
23.75°	6	5	5	5	4	4	4	4	4	4	4
22.5°	6	6	5	5	4	4	4	4	4	4	4
21.25°	7	6	5	5	5	4	4	4	4	4	4
20°	7	6	6	5	5	4	4	4	4	4	4
18.75°	8	7	6	5	5	5	4	4	4	4	4
17.5°	8	7	6	6	5	5	4	4	4	4	4
16.25°	9	7	7	6	5	5	4	4	4	4	4
15°	9	8	7	6	6	5	5	4	4	4	4
13.75°	10	8	7	6	6	5	5	4	4	4	4
12.5°	10	9	8	7	6	5	5	4	4	4	4
11.25°	11	9	8	7	6	5	5	5	4	4	4
10°	11	10	8	7	6	6	5	5	4	4	4
8.75°	12	10	8	7	6	6	5	5	4	4	4
7.5°	12	10	9	7	7	6	5	5	4	4	4
6.25°	12	10	9	8	7	6	5	5	4	4	4
5°	13	11	9	8	7	6	5	5	4	4	4
3.75°	13	11	9	8	7	6	5	5	4	4	4
2.5°	13	11	9	8	7	6	5	5	4	4	4
1.25°	13	11	9	8	7	6	5	5	4	4	4
0°	14	11	10	8	7	6	6	5	5	4	4
-1.25°	13	11	9	8	7	6	5	5	4	4	4
-2.5°	13	11	9	8	7	6	5	5	4	4	4
-3.75°	13	11	9	8	7	6	5	5	4	4	4
-5°	13	11	9	8	7	6	5	5	4	4	4
-6.25°	12	10	9	8	7	6	5	5	4	4	4
-7.5°	12	10	9	7	7	6	5	5	4	4	4
-8.75°	12	10	8	7	6	6	5	5	4	4	4
-10°	11	10	8	7	6	6	5	5	4	4	4
-11.25°	11	9	8	7	6	5	5	5	4	4	4
-12.5°	10	9	8	7	6	5	5	4	4	4	4
-13.75°	10	8	7	6	6	5	5	4	4	4	4
-15°	9	8	7	6	6	5	5	4	4	4	4
-16.25°	9	7	7	6	5	5	4	4	4	4	4
-17.5°	8	7	6	6	5	5	4	4	4	4	4
-18.75°	8	7	6	5	5	5	4	4	4	4	4
-20°	7	6	6	5	5	4	4	4	4	4	4
-21.25°	7	6	5	5	5	4	4	4	4	4	4



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	6	6	5	5	4	4	4	4	4	4	4
-23.75°	6	5	5	5	4	4	4	4	4	4	4
-25°	6	5	5	4	4	4	4	4	4	4	4
-26.25°	5	5	5	4	4	4	4	4	4	4	3
-27.5°	5	5	4	4	4	4	4	4	4	4	3
-28.75°	5	4	4	4	4	4	4	4	4	3	3
-30°	4	4	4	4	4	4	4	4	3	3	3
-31.25°	4	4	4	4	4	4	4	4	3	3	3
-32.5°	4	4	4	4	4	4	4	3	3	3	3
-33.75°	4	4	4	4	4	4	3	3	3	3	3
-35°	4	4	4	4	4	4	3	3	3	3	3
-36.25°	4	4	4	4	4	3	3	3	3	3	3
-37.5°	4	4	4	4	3	3	3	3	3	3	3
-38.75°	4	4	4	3	3	3	3	3	3	3	3
-40°	4	4	3	3	3	3	3	3	3	3	3
-41.25°	3	3	3	3	3	3	3	3	3	3	3
-42.5°	3	3	3	3	3	3	3	3	3	3	2
-43.75°	3	3	3	3	3	3	3	3	3	2	2
-45°	3	3	3	3	3	3	3	3	2	2	2
-46.25°	3	3	3	3	3	3	3	2	2	2	1
-47.5°	3	3	3	3	3	2	2	2	2	1	1
-48.75°	3	3	3	3	2	2	2	2	1	1	1
-50°	3	3	2	2	2	2	2	1	1	1	1
-51.25°	3	2	2	2	2	1	1	1	1	1	1
-52.5°	2	2	2	2	1	1	1	1	1	1	1
-53.75°	2	2	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	0
-63.75°	1	1	1	1	1	1	1	1	0	0	0
-65°	1	1	1	1	1	1	0	0	0	0	0
-66.25°	1	1	1	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	1	0	0	0	0	0	0	0	0	0	0
60°	1	1	0	0	0	0	0	0	0	0	0
58.75°	1	1	1	1	0	0	0	0	0	0	0
57.5°	1	1	1	1	1	0	0	0	0	0	0
56.25°	1	1	1	1	1	1	0	0	0	0	0
55°	1	1	1	1	1	1	1	0	0	0	0
53.75°	1	1	1	1	1	1	1	1	0	0	0
52.5°	1	1	1	1	1	1	1	1	1	0	0
51.25°	1	1	1	1	1	1	1	1	1	1	0
50°	1	1	1	1	1	1	1	1	1	1	0
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	2	1	1	1	1	1	1	1	1	1	1
42.5°	2	2	1	1	1	1	1	1	1	1	1
41.25°	2	2	2	1	1	1	1	1	1	1	1
40°	2	2	2	1	1	1	1	1	1	1	1
38.75°	3	2	2	2	1	1	1	1	1	1	1
37.5°	3	3	2	2	2	1	1	1	1	1	1
36.25°	3	3	2	2	2	1	1	1	1	1	1
35°	3	3	3	2	2	2	1	1	1	1	1



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	3	3	3	3	2	2	1	1	1	1	1
32.5°	3	3	3	3	2	2	2	1	1	1	1
31.25°	3	3	3	3	3	2	2	1	1	1	1
30°	3	3	3	3	3	2	2	2	1	1	1
28.75°	3	3	3	3	3	2	2	2	1	1	1
27.5°	3	3	3	3	3	3	2	2	1	1	1
26.25°	3	3	3	3	3	3	2	2	2	1	1
25°	3	3	3	3	3	3	3	2	2	1	1
23.75°	3	3	3	3	3	3	3	2	2	1	1
22.5°	3	3	3	3	3	3	3	2	2	1	1
21.25°	4	3	3	3	3	3	3	2	2	2	1
20°	4	3	3	3	3	3	3	3	2	2	1
18.75°	4	3	3	3	3	3	3	3	2	2	1
17.5°	4	4	3	3	3	3	3	3	2	2	1
16.25°	4	4	3	3	3	3	3	3	2	2	1
15°	4	4	3	3	3	3	3	3	3	2	2
13.75°	4	4	3	3	3	3	3	3	3	2	2
12.5°	4	4	4	3	3	3	3	3	3	2	2
11.25°	4	4	4	3	3	3	3	3	3	2	2
10°	4	4	4	3	3	3	3	3	3	2	2
8.75°	4	4	4	3	3	3	3	3	3	2	2
7.5°	4	4	4	3	3	3	3	3	3	2	2
6.25°	4	4	4	3	3	3	3	3	3	2	2
5°	4	4	4	3	3	3	3	3	3	2	2
3.75°	4	4	4	3	3	3	3	3	3	2	2
2.5°	4	4	4	3	3	3	3	3	3	2	2
1.25°	4	4	4	3	3	3	3	3	3	2	2
0°	4	4	4	4	3	3	3	3	3	3	2
-1.25°	4	4	4	3	3	3	3	3	3	2	2
-2.5°	4	4	4	3	3	3	3	3	3	2	2
-3.75°	4	4	4	3	3	3	3	3	3	2	2
-5°	4	4	4	3	3	3	3	3	3	2	2
-6.25°	4	4	4	3	3	3	3	3	3	2	2
-7.5°	4	4	4	3	3	3	3	3	3	2	2
-8.75°	4	4	4	3	3	3	3	3	3	2	2
-10°	4	4	4	3	3	3	3	3	3	2	2
-11.25°	4	4	4	3	3	3	3	3	3	2	2
-12.5°	4	4	4	3	3	3	3	3	3	2	2
-13.75°	4	4	3	3	3	3	3	3	3	2	2
-15°	4	4	3	3	3	3	3	3	3	2	2
-16.25°	4	4	3	3	3	3	3	3	2	2	1
-17.5°	4	4	3	3	3	3	3	3	2	2	1
-18.75°	4	3	3	3	3	3	3	3	2	2	1
-20°	4	3	3	3	3	3	3	3	2	2	1
-21.25°	4	3	3	3	3	3	3	2	2	2	1



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	3	3	3	3	3	3	3	2	2	1	1
-23.75°	3	3	3	3	3	3	3	2	2	1	1
-25°	3	3	3	3	3	3	3	2	2	1	1
-26.25°	3	3	3	3	3	3	2	2	2	1	1
-27.5°	3	3	3	3	3	3	2	2	1	1	1
-28.75°	3	3	3	3	3	2	2	2	1	1	1
-30°	3	3	3	3	3	2	2	2	1	1	1
-31.25°	3	3	3	3	3	2	2	1	1	1	1
-32.5°	3	3	3	3	2	2	2	1	1	1	1
-33.75°	3	3	3	3	2	2	1	1	1	1	1
-35°	3	3	3	2	2	2	1	1	1	1	1
-36.25°	3	3	2	2	2	1	1	1	1	1	1
-37.5°	3	3	2	2	2	1	1	1	1	1	1
-38.75°	3	2	2	2	1	1	1	1	1	1	1
-40°	2	2	2	1	1	1	1	1	1	1	1
-41.25°	2	2	2	1	1	1	1	1	1	1	1
-42.5°	2	2	1	1	1	1	1	1	1	1	1
-43.75°	2	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	0
-51.25°	1	1	1	1	1	1	1	1	1	1	0
-52.5°	1	1	1	1	1	1	1	1	1	0	0
-53.75°	1	1	1	1	1	1	1	1	0	0	0
-55°	1	1	1	1	1	1	1	0	0	0	0
-56.25°	1	1	1	1	1	1	0	0	0	0	0
-57.5°	1	1	1	1	1	0	0	0	0	0	0
-58.75°	1	1	1	1	0	0	0	0	0	0	0
-60°	1	1	0	0	0	0	0	0	0	0	0
-61.25°	1	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	1	0	0	0	0	0	0	0	0	0	0
46.25°	1	0	0	0	0	0	0	0	0	0	0
45°	1	1	0	0	0	0	0	0	0	0	0
43.75°	1	1	0	0	0	0	0	0	0	0	0
42.5°	1	1	1	0	0	0	0	0	0	0	0
41.25°	1	1	1	0	0	0	0	0	0	0	0
40°	1	1	1	1	0	0	0	0	0	0	0
38.75°	1	1	1	1	0	0	0	0	0	0	0
37.5°	1	1	1	1	0	0	0	0	0	0	0
36.25°	1	1	1	1	1	0	0	0	0	0	0
35°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	0	0	0	0	0	0
32.5°	1	1	1	1	1	1	0	0	0	0	0
31.25°	1	1	1	1	1	1	0	0	0	0	0
30°	1	1	1	1	1	1	0	0	0	0	0
28.75°	1	1	1	1	1	1	0	0	0	0	0
27.5°	1	1	1	1	1	1	1	0	0	0	0
26.25°	1	1	1	1	1	1	1	0	0	0	0
25°	1	1	1	1	1	1	1	0	0	0	0
23.75°	1	1	1	1	1	1	1	0	0	0	0
22.5°	1	1	1	1	1	1	1	0	0	0	0
21.25°	1	1	1	1	1	1	1	0	0	0	0
20°	1	1	1	1	1	1	1	0	0	0	0
18.75°	1	1	1	1	1	1	1	1	0	0	0
17.5°	1	1	1	1	1	1	1	1	0	0	0
16.25°	1	1	1	1	1	1	1	1	0	0	0
15°	1	1	1	1	1	1	1	1	0	0	0
13.75°	1	1	1	1	1	1	1	1	0	0	0
12.5°	1	1	1	1	1	1	1	1	0	0	0
11.25°	1	1	1	1	1	1	1	1	0	0	0
10°	1	1	1	1	1	1	1	1	0	0	0
8.75°	1	1	1	1	1	1	1	1	0	0	0
7.5°	1	1	1	1	1	1	1	1	0	0	0
6.25°	1	1	1	1	1	1	1	1	0	0	0
5°	1	1	1	1	1	1	1	1	0	0	0
3.75°	1	1	1	1	1	1	1	1	0	0	0
2.5°	1	1	1	1	1	1	1	1	0	0	0
1.25°	1	1	1	1	1	1	1	1	0	0	0
0°	2	1	1	1	1	1	1	1	1	0	0
-1.25°	1	1	1	1	1	1	1	1	0	0	0
-2.5°	1	1	1	1	1	1	1	1	0	0	0
-3.75°	1	1	1	1	1	1	1	1	0	0	0
-5°	1	1	1	1	1	1	1	1	0	0	0
-6.25°	1	1	1	1	1	1	1	1	0	0	0
-7.5°	1	1	1	1	1	1	1	1	0	0	0
-8.75°	1	1	1	1	1	1	1	1	0	0	0
-10°	1	1	1	1	1	1	1	1	0	0	0
-11.25°	1	1	1	1	1	1	1	1	0	0	0
-12.5°	1	1	1	1	1	1	1	1	0	0	0
-13.75°	1	1	1	1	1	1	1	1	0	0	0
-15°	1	1	1	1	1	1	1	1	0	0	0
-16.25°	1	1	1	1	1	1	1	1	0	0	0
-17.5°	1	1	1	1	1	1	1	1	0	0	0
-18.75°	1	1	1	1	1	1	1	1	0	0	0
-20°	1	1	1	1	1	1	1	0	0	0	0
-21.25°	1	1	1	1	1	1	1	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	1	1	1	1	1	1	1	0	0	0	0
-23.75°	1	1	1	1	1	1	1	0	0	0	0
-25°	1	1	1	1	1	1	1	0	0	0	0
-26.25°	1	1	1	1	1	1	1	0	0	0	0
-27.5°	1	1	1	1	1	1	1	0	0	0	0
-28.75°	1	1	1	1	1	1	0	0	0	0	0
-30°	1	1	1	1	1	1	0	0	0	0	0
-31.25°	1	1	1	1	1	1	0	0	0	0	0
-32.5°	1	1	1	1	1	1	0	0	0	0	0
-33.75°	1	1	1	1	1	0	0	0	0	0	0
-35°	1	1	1	1	1	0	0	0	0	0	0
-36.25°	1	1	1	1	1	0	0	0	0	0	0
-37.5°	1	1	1	1	0	0	0	0	0	0	0
-38.75°	1	1	1	1	0	0	0	0	0	0	0
-40°	1	1	1	1	0	0	0	0	0	0	0
-41.25°	1	1	1	0	0	0	0	0	0	0	0
-42.5°	1	1	1	0	0	0	0	0	0	0	0
-43.75°	1	1	0	0	0	0	0	0	0	0	0
-45°	1	1	0	0	0	0	0	0	0	0	0
-46.25°	1	0	0	0	0	0	0	0	0	0	0
-47.5°	1	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-8 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4025-12-CS

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)