

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4036-12-CS-DIFF**

Test Date: 04/06/18

Test Information


Test Method: LM-79-08
Report Number: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-44)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-SS-8LED4036-12-CS-DIFF
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD SILVER, DIFFUSED LENS
Light Source: (1) SORAA 4000K 90 CRI LED
SM16-07-36D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	268.5 lumens	Max Intensity:	502 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	34.9 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	40.7°H x 40.7°V	Field Angle (10%):	69.7°H x 69.7°V
Beam Lumens:	144.3 lumens	Field Lumens:	237.5 lumens
Beam Efficiency:	53.7%	Field Efficiency:	88.5%
Input Watts (W):	7.7		
Input Voltage (V):	12.0		
Input Current (A _{in}):	0.674		
Voltage Rise (V):	NR		
Power Factor:	0.9902		
Total Harmonic Distortion (THDi):	27.5%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	3 HR		
Ambient Temperature (°C):	25.2		
Test Distance:	25 FT		


REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

Iso-Candela Plot




REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

Lumen Table




REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

Luminous Intensity Plot



Beam:
 H Angle: 40.7°
 V Angle: 40.7°
 Lumens: 144.3
 Efficiency: 53.7%

Field:
 H Angle: 69.7°
 V Angle: 69.7°
 Lumens: 237.5
 Efficiency: 88.5%

Spill:
 Lumens: 31
 Efficiency: 11.5%

- Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	1
43.75°	0	0	0	0	0	0	0	0	0	0	1
42.5°	0	0	0	0	0	0	0	0	0	0	1
41.25°	0	0	0	0	0	0	0	0	0	0	1
40°	0	0	0	0	0	0	0	0	0	0	1
38.75°	0	0	0	0	0	0	0	0	0	1	1
37.5°	0	0	0	0	0	0	0	0	0	1	1
36.25°	0	0	0	0	0	0	0	0	0	1	1
35°	0	0	0	0	0	0	0	0	0	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
31.25°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	0	1	1
28.75°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	1
26.25°	0	0	0	0	0	0	0	0	1	1	1
25°	0	0	0	0	0	0	0	0	1	1	1
23.75°	0	0	0	0	0	0	0	0	1	1	1
22.5°	0	0	0	0	0	0	0	0	1	1	1
21.25°	0	0	0	0	0	0	0	0	1	1	1
20°	0	0	0	0	0	0	0	0	1	1	1
18.75°	0	0	0	0	0	0	0	0	1	1	1
17.5°	0	0	0	0	0	0	0	0	1	1	1
16.25°	0	0	0	0	0	0	0	0	1	1	1
15°	0	0	0	0	0	0	0	0	1	1	1
13.75°	0	0	0	0	0	0	0	0	1	1	1
12.5°	0	0	0	0	0	0	0	0	1	1	1
11.25°	0	0	0	0	0	0	0	0	1	1	1
10°	0	0	0	0	0	0	0	0	1	1	1
8.75°	0	0	0	0	0	0	0	0	1	1	1
7.5°	0	0	0	0	0	0	0	0	1	1	1
6.25°	0	0	0	0	0	0	0	0	1	1	1
5°	0	0	0	0	0	0	0	0	1	1	1
3.75°	0	0	0	0	0	0	0	0	1	1	1
2.5°	0	0	0	0	0	0	0	0	1	1	1
1.25°	0	0	0	0	0	0	0	0	1	1	1
0°	0	0	0	0	0	0	0	1	1	1	1
-1.25°	0	0	0	0	0	0	0	0	1	1	1
-2.5°	0	0	0	0	0	0	0	0	1	1	1
-3.75°	0	0	0	0	0	0	0	0	1	1	1
-5°	0	0	0	0	0	0	0	0	1	1	1
-6.25°	0	0	0	0	0	0	0	0	1	1	1
-7.5°	0	0	0	0	0	0	0	0	1	1	1
-8.75°	0	0	0	0	0	0	0	0	1	1	1
-10°	0	0	0	0	0	0	0	0	1	1	1
-11.25°	0	0	0	0	0	0	0	0	1	1	1
-12.5°	0	0	0	0	0	0	0	0	1	1	1
-13.75°	0	0	0	0	0	0	0	0	1	1	1
-15°	0	0	0	0	0	0	0	0	1	1	1
-16.25°	0	0	0	0	0	0	0	0	1	1	1
-17.5°	0	0	0	0	0	0	0	0	1	1	1
-18.75°	0	0	0	0	0	0	0	0	1	1	1
-20°	0	0	0	0	0	0	0	0	1	1	1
-21.25°	0	0	0	0	0	0	0	0	1	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	1	1	1
-23.75°	0	0	0	0	0	0	0	0	1	1	1
-25°	0	0	0	0	0	0	0	0	1	1	1
-26.25°	0	0	0	0	0	0	0	0	1	1	1
-27.5°	0	0	0	0	0	0	0	0	1	1	1
-28.75°	0	0	0	0	0	0	0	0	1	1	1
-30°	0	0	0	0	0	0	0	0	0	1	1
-31.25°	0	0	0	0	0	0	0	0	0	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-33.75°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	1	1
-36.25°	0	0	0	0	0	0	0	0	0	1	1
-37.5°	0	0	0	0	0	0	0	0	0	1	1
-38.75°	0	0	0	0	0	0	0	0	0	1	1
-40°	0	0	0	0	0	0	0	0	0	0	1
-41.25°	0	0	0	0	0	0	0	0	0	0	1
-42.5°	0	0	0	0	0	0	0	0	0	0	1
-43.75°	0	0	0	0	0	0	0	0	0	0	1
-45°	0	0	0	0	0	0	0	0	0	0	1
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	1	1
67.5°	0	0	0	0	0	0	0	0	1	1	1
66.25°	0	0	0	0	0	0	0	1	1	1	1
65°	0	0	0	0	0	0	1	1	1	1	1
63.75°	0	0	0	0	0	0	1	1	1	1	1
62.5°	0	0	0	0	0	1	1	1	1	1	1
61.25°	0	0	0	0	1	1	1	1	1	1	1
60°	0	0	0	0	1	1	1	1	1	1	1
58.75°	0	0	0	1	1	1	1	1	1	1	1
57.5°	0	0	0	1	1	1	1	1	1	1	1
56.25°	0	0	1	1	1	1	1	1	1	1	1
55°	0	0	1	1	1	1	1	1	1	1	1
53.75°	0	1	1	1	1	1	1	1	1	1	1
52.5°	0	1	1	1	1	1	1	1	1	1	1
51.25°	0	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
43.75°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	2
41.25°	1	1	1	1	1	1	1	1	1	1	2
40°	1	1	1	1	1	1	1	1	1	2	2
38.75°	1	1	1	1	1	1	1	1	1	2	2
37.5°	1	1	1	1	1	1	1	1	1	2	2
36.25°	1	1	1	1	1	1	1	1	2	2	2
35°	1	1	1	1	1	1	1	1	2	2	2



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	1	1	1	1	1	1	1	1	2	2	2
32.5°	1	1	1	1	1	1	1	2	2	2	2
31.25°	1	1	1	1	1	1	1	2	2	2	2
30°	1	1	1	1	1	1	1	2	2	2	2
28.75°	1	1	1	1	1	1	1	2	2	2	2
27.5°	1	1	1	1	1	1	2	2	2	2	2
26.25°	1	1	1	1	1	1	2	2	2	2	2
25°	1	1	1	1	1	1	2	2	2	2	2
23.75°	1	1	1	1	1	1	2	2	2	2	2
22.5°	1	1	1	1	1	1	2	2	2	2	2
21.25°	1	1	1	1	1	1	2	2	2	2	2
20°	1	1	1	1	1	1	2	2	2	2	2
18.75°	1	1	1	1	1	2	2	2	2	2	2
17.5°	1	1	1	1	1	2	2	2	2	2	2
16.25°	1	1	1	1	1	2	2	2	2	2	2
15°	1	1	1	1	1	2	2	2	2	2	2
13.75°	1	1	1	1	1	2	2	2	2	2	2
12.5°	1	1	1	1	1	2	2	2	2	2	2
11.25°	1	1	1	1	1	2	2	2	2	2	2
10°	1	1	1	1	1	2	2	2	2	2	2
8.75°	1	1	1	1	1	2	2	2	2	2	2
7.5°	1	1	1	1	1	2	2	2	2	2	2
6.25°	1	1	1	1	1	2	2	2	2	2	2
5°	1	1	1	1	1	2	2	2	2	2	2
3.75°	1	1	1	1	1	2	2	2	2	2	2
2.5°	1	1	1	1	1	2	2	2	2	2	2
1.25°	1	1	1	1	1	2	2	2	2	2	2
0°	1	1	1	1	2	2	2	2	2	2	3
-1.25°	1	1	1	1	1	2	2	2	2	2	2
-2.5°	1	1	1	1	1	2	2	2	2	2	2
-3.75°	1	1	1	1	1	2	2	2	2	2	2
-5°	1	1	1	1	1	2	2	2	2	2	2
-6.25°	1	1	1	1	1	2	2	2	2	2	2
-7.5°	1	1	1	1	1	2	2	2	2	2	2
-8.75°	1	1	1	1	1	2	2	2	2	2	2
-10°	1	1	1	1	1	2	2	2	2	2	2
-11.25°	1	1	1	1	1	2	2	2	2	2	2
-12.5°	1	1	1	1	1	2	2	2	2	2	2
-13.75°	1	1	1	1	1	2	2	2	2	2	2
-15°	1	1	1	1	1	2	2	2	2	2	2
-16.25°	1	1	1	1	1	2	2	2	2	2	2
-17.5°	1	1	1	1	1	2	2	2	2	2	2
-18.75°	1	1	1	1	1	2	2	2	2	2	2
-20°	1	1	1	1	1	1	2	2	2	2	2
-21.25°	1	1	1	1	1	1	2	2	2	2	2



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	1	1	1	1	1	1	2	2	2	2	2
-23.75°	1	1	1	1	1	1	2	2	2	2	2
-25°	1	1	1	1	1	1	2	2	2	2	2
-26.25°	1	1	1	1	1	1	2	2	2	2	2
-27.5°	1	1	1	1	1	1	2	2	2	2	2
-28.75°	1	1	1	1	1	1	1	2	2	2	2
-30°	1	1	1	1	1	1	1	2	2	2	2
-31.25°	1	1	1	1	1	1	1	2	2	2	2
-32.5°	1	1	1	1	1	1	1	2	2	2	2
-33.75°	1	1	1	1	1	1	1	1	2	2	2
-35°	1	1	1	1	1	1	1	1	2	2	2
-36.25°	1	1	1	1	1	1	1	1	2	2	2
-37.5°	1	1	1	1	1	1	1	1	1	2	2
-38.75°	1	1	1	1	1	1	1	1	1	2	2
-40°	1	1	1	1	1	1	1	1	1	2	2
-41.25°	1	1	1	1	1	1	1	1	1	1	2
-42.5°	1	1	1	1	1	1	1	1	1	1	2
-43.75°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-46.25°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	0	1	1	1	1	1	1	1	1	1	1
-52.5°	0	1	1	1	1	1	1	1	1	1	1
-53.75°	0	1	1	1	1	1	1	1	1	1	1
-55°	0	0	1	1	1	1	1	1	1	1	1
-56.25°	0	0	1	1	1	1	1	1	1	1	1
-57.5°	0	0	0	1	1	1	1	1	1	1	1
-58.75°	0	0	0	1	1	1	1	1	1	1	1
-60°	0	0	0	0	1	1	1	1	1	1	1
-61.25°	0	0	0	0	1	1	1	1	1	1	1
-62.5°	0	0	0	0	0	1	1	1	1	1	1
-63.75°	0	0	0	0	0	0	1	1	1	1	1
-65°	0	0	0	0	0	0	1	1	1	1	1
-66.25°	0	0	0	0	0	0	0	1	1	1	1
-67.5°	0	0	0	0	0	0	0	0	1	1	1
-68.75°	0	0	0	0	0	0	0	0	0	1	1
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	1
75°	0	0	0	0	0	0	0	1	1	1	1
73.75°	0	0	0	0	0	1	1	1	1	1	1
72.5°	0	0	0	1	1	1	1	1	1	1	1
71.25°	0	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	2	2
57.5°	1	1	1	1	1	1	1	1	2	2	2
56.25°	1	1	1	1	1	1	1	2	2	2	2
55°	1	1	1	1	1	1	2	2	2	2	2
53.75°	1	1	1	1	1	2	2	2	2	2	2
52.5°	1	1	1	1	2	2	2	2	2	2	2
51.25°	1	1	1	2	2	2	2	2	2	2	2
50°	1	1	1	2	2	2	2	2	2	2	2
48.75°	1	1	2	2	2	2	2	2	2	2	2
47.5°	1	2	2	2	2	2	2	2	2	2	2
46.25°	1	2	2	2	2	2	2	2	2	2	3
45°	2	2	2	2	2	2	2	2	2	3	3
43.75°	2	2	2	2	2	2	2	2	2	3	3
42.5°	2	2	2	2	2	2	2	2	3	3	3
41.25°	2	2	2	2	2	2	2	3	3	3	3
40°	2	2	2	2	2	2	2	3	3	3	3
38.75°	2	2	2	2	2	2	3	3	3	3	3
37.5°	2	2	2	2	2	2	3	3	3	3	3
36.25°	2	2	2	2	2	3	3	3	3	3	3
35°	2	2	2	2	2	3	3	3	3	3	4



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	2	2	2	2	3	3	3	3	3	4	4
32.5°	2	2	2	2	3	3	3	3	3	4	4
31.25°	2	2	2	3	3	3	3	3	4	4	4
30°	2	2	2	3	3	3	3	3	4	4	5
28.75°	2	2	2	3	3	3	3	3	4	4	5
27.5°	2	2	3	3	3	3	3	4	4	4	5
26.25°	2	2	3	3	3	3	3	4	4	5	5
25°	2	2	3	3	3	3	4	4	4	5	5
23.75°	2	2	3	3	3	3	4	4	5	5	5
22.5°	2	3	3	3	3	3	4	4	5	5	6
21.25°	2	3	3	3	3	3	4	4	5	5	6
20°	2	3	3	3	3	4	4	5	5	5	6
18.75°	2	3	3	3	3	4	4	5	5	6	6
17.5°	2	3	3	3	3	4	4	5	5	6	6
16.25°	3	3	3	3	3	4	4	5	5	6	6
15°	3	3	3	3	4	4	4	5	5	6	7
13.75°	3	3	3	3	4	4	5	5	6	6	7
12.5°	3	3	3	3	4	4	5	5	6	6	7
11.25°	3	3	3	3	4	4	5	5	6	6	7
10°	3	3	3	3	4	4	5	5	6	6	7
8.75°	3	3	3	3	4	4	5	5	6	7	8
7.5°	3	3	3	3	4	4	5	5	6	7	8
6.25°	3	3	3	3	4	4	5	5	6	7	8
5°	3	3	3	3	4	4	5	5	6	7	8
3.75°	3	3	3	3	4	4	5	5	6	7	8
2.5°	3	3	3	3	4	4	5	5	6	7	8
1.25°	3	3	3	3	4	4	5	5	6	7	8
0°	3	3	3	4	4	5	5	6	6	7	8
-1.25°	3	3	3	3	4	4	5	5	6	7	8
-2.5°	3	3	3	3	4	4	5	5	6	7	8
-3.75°	3	3	3	3	4	4	5	5	6	7	8
-5°	3	3	3	3	4	4	5	5	6	7	8
-6.25°	3	3	3	3	4	4	5	5	6	7	8
-7.5°	3	3	3	3	4	4	5	5	6	7	8
-8.75°	3	3	3	3	4	4	5	5	6	7	8
-10°	3	3	3	3	4	4	5	5	6	6	7
-11.25°	3	3	3	3	4	4	5	5	6	6	7
-12.5°	3	3	3	3	4	4	5	5	6	6	7
-13.75°	3	3	3	3	4	4	5	5	6	6	7
-15°	3	3	3	3	4	4	4	5	5	6	7
-16.25°	3	3	3	3	3	4	4	5	5	6	6
-17.5°	2	3	3	3	3	4	4	5	5	6	6
-18.75°	2	3	3	3	3	4	4	5	5	6	6
-20°	2	3	3	3	3	4	4	5	5	5	6
-21.25°	2	3	3	3	3	3	4	4	5	5	6



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	2	3	3	3	3	3	4	4	5	5	6
-23.75°	2	2	3	3	3	3	4	4	5	5	5
-25°	2	2	3	3	3	3	4	4	4	5	5
-26.25°	2	2	3	3	3	3	3	4	4	5	5
-27.5°	2	2	3	3	3	3	3	4	4	4	5
-28.75°	2	2	2	3	3	3	3	3	4	4	5
-30°	2	2	2	3	3	3	3	3	4	4	5
-31.25°	2	2	2	3	3	3	3	3	4	4	4
-32.5°	2	2	2	2	3	3	3	3	3	4	4
-33.75°	2	2	2	2	3	3	3	3	3	4	4
-35°	2	2	2	2	2	3	3	3	3	3	4
-36.25°	2	2	2	2	2	3	3	3	3	3	3
-37.5°	2	2	2	2	2	2	3	3	3	3	3
-38.75°	2	2	2	2	2	2	3	3	3	3	3
-40°	2	2	2	2	2	2	2	3	3	3	3
-41.25°	2	2	2	2	2	2	2	3	3	3	3
-42.5°	2	2	2	2	2	2	2	2	3	3	3
-43.75°	2	2	2	2	2	2	2	2	2	3	3
-45°	2	2	2	2	2	2	2	2	2	3	3
-46.25°	1	2	2	2	2	2	2	2	2	2	3
-47.5°	1	2	2	2	2	2	2	2	2	2	2
-48.75°	1	1	2	2	2	2	2	2	2	2	2
-50°	1	1	1	2	2	2	2	2	2	2	2
-51.25°	1	1	1	2	2	2	2	2	2	2	2
-52.5°	1	1	1	1	2	2	2	2	2	2	2
-53.75°	1	1	1	1	1	2	2	2	2	2	2
-55°	1	1	1	1	1	1	2	2	2	2	2
-56.25°	1	1	1	1	1	1	1	2	2	2	2
-57.5°	1	1	1	1	1	1	1	1	2	2	2
-58.75°	1	1	1	1	1	1	1	1	1	2	2
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	0	1	1	1	1	1	1	1	1	1	1
-72.5°	0	0	0	1	1	1	1	1	1	1	1
-73.75°	0	0	0	0	0	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	1
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	1	1	1
77.5°	0	0	0	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	2
65°	1	1	1	1	1	1	1	2	2	2	2
63.75°	1	1	1	1	1	2	2	2	2	2	2
62.5°	1	1	1	2	2	2	2	2	2	2	2
61.25°	1	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	3
55°	2	2	2	2	2	2	2	2	3	3	3
53.75°	2	2	2	2	2	2	3	3	3	3	3
52.5°	2	2	2	2	2	3	3	3	3	3	3
51.25°	2	2	2	3	3	3	3	3	3	3	3
50°	2	2	3	3	3	3	3	3	3	3	3
48.75°	2	3	3	3	3	3	3	3	3	4	4
47.5°	3	3	3	3	3	3	3	3	4	4	4
46.25°	3	3	3	3	3	3	4	4	4	4	5
45°	3	3	3	3	3	4	4	4	4	5	5
43.75°	3	3	3	3	4	4	4	4	5	5	5
42.5°	3	3	3	4	4	4	4	5	5	5	6
41.25°	3	3	4	4	4	4	5	5	5	6	6
40°	3	3	4	4	4	5	5	5	6	6	7
38.75°	3	4	4	4	5	5	5	6	6	7	7
37.5°	4	4	4	5	5	5	6	6	7	7	8
36.25°	4	4	5	5	5	6	6	7	7	8	8
35°	4	4	5	5	6	6	6	7	8	8	9



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	4	5	5	5	6	6	7	8	8	9	10
32.5°	5	5	5	6	6	7	7	8	9	10	10
31.25°	5	5	5	6	7	7	8	9	9	10	11
30°	5	5	6	6	7	8	9	9	10	11	12
28.75°	5	6	6	7	7	8	9	10	11	12	13
27.5°	5	6	6	7	8	9	9	10	12	13	14
26.25°	6	6	7	7	8	9	10	11	12	14	15
25°	6	6	7	8	9	10	11	12	13	15	16
23.75°	6	7	7	8	9	10	11	12	14	16	17
22.5°	6	7	8	9	9	11	12	13	15	16	19
21.25°	6	7	8	9	10	11	12	14	16	18	20
20°	7	8	8	9	10	12	13	15	16	19	22
18.75°	7	8	9	10	11	12	14	15	17	20	23
17.5°	7	8	9	10	11	13	14	16	19	22	25
16.25°	7	8	9	10	12	13	15	17	20	23	27
15°	8	9	10	11	12	14	16	18	21	24	29
13.75°	8	9	10	11	12	14	16	19	22	26	31
12.5°	8	9	10	11	13	15	17	20	23	27	33
11.25°	8	9	10	12	13	15	17	20	24	29	34
10°	8	9	11	12	14	15	18	21	25	30	35
8.75°	9	10	11	12	14	16	18	22	26	31	37
7.5°	9	10	11	12	14	16	19	22	27	32	38
6.25°	9	10	11	13	14	16	19	23	28	33	39
5°	9	10	11	13	15	17	20	23	28	34	40
3.75°	9	10	11	13	15	17	20	24	29	34	41
2.5°	9	10	11	13	15	17	20	24	29	35	42
1.25°	9	10	11	13	15	17	20	24	29	35	42
0°	9	10	12	13	15	17	21	24	30	35	42
-1.25°	9	10	11	13	15	17	20	24	29	35	42
-2.5°	9	10	11	13	15	17	20	24	29	35	42
-3.75°	9	10	11	13	15	17	20	24	29	34	41
-5°	9	10	11	13	15	17	20	23	28	34	40
-6.25°	9	10	11	13	14	16	19	23	28	33	39
-7.5°	9	10	11	12	14	16	19	22	27	32	38
-8.75°	9	10	11	12	14	16	18	22	26	31	37
-10°	8	9	11	12	14	15	18	21	25	30	35
-11.25°	8	9	10	12	13	15	17	20	24	29	34
-12.5°	8	9	10	11	13	15	17	20	23	27	33
-13.75°	8	9	10	11	12	14	16	19	22	26	31
-15°	8	9	10	11	12	14	16	18	21	24	29
-16.25°	7	8	9	10	12	13	15	17	20	23	27
-17.5°	7	8	9	10	11	13	14	16	19	22	25
-18.75°	7	8	9	10	11	12	14	15	17	20	23
-20°	7	8	8	9	10	12	13	15	16	19	22
-21.25°	6	7	8	9	10	11	12	14	16	18	20



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	6	7	8	9	9	11	12	13	15	16	19
-23.75°	6	7	7	8	9	10	11	12	14	16	17
-25°	6	6	7	8	9	10	11	12	13	15	16
-26.25°	6	6	7	7	8	9	10	11	12	14	15
-27.5°	5	6	6	7	8	9	9	10	12	13	14
-28.75°	5	6	6	7	7	8	9	10	11	12	13
-30°	5	5	6	6	7	8	9	9	10	11	12
-31.25°	5	5	5	6	7	7	8	9	9	10	11
-32.5°	5	5	5	6	6	7	7	8	9	10	10
-33.75°	4	5	5	5	6	6	7	8	8	9	10
-35°	4	4	5	5	6	6	6	7	8	8	9
-36.25°	4	4	5	5	5	6	6	7	7	8	8
-37.5°	4	4	4	5	5	5	6	6	7	7	8
-38.75°	3	4	4	4	5	5	5	6	6	7	7
-40°	3	3	4	4	4	5	5	5	6	6	7
-41.25°	3	3	4	4	4	4	5	5	5	6	6
-42.5°	3	3	3	4	4	4	4	5	5	5	6
-43.75°	3	3	3	3	4	4	4	4	5	5	5
-45°	3	3	3	3	3	4	4	4	4	5	5
-46.25°	3	3	3	3	3	3	4	4	4	4	5
-47.5°	3	3	3	3	3	3	3	3	4	4	4
-48.75°	2	3	3	3	3	3	3	3	3	4	4
-50°	2	2	3	3	3	3	3	3	3	3	3
-51.25°	2	2	2	3	3	3	3	3	3	3	3
-52.5°	2	2	2	2	2	3	3	3	3	3	3
-53.75°	2	2	2	2	2	2	3	3	3	3	3
-55°	2	2	2	2	2	2	2	2	3	3	3
-56.25°	2	2	2	2	2	2	2	2	2	2	3
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	1	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	2	2	2	2	2	2
-65°	1	1	1	1	1	1	1	2	2	2	2
-66.25°	1	1	1	1	1	1	1	1	1	1	2
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	0	0	0	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	1	1	1
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	2	2	2	2	2
67.5°	1	1	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	3
60°	2	2	2	2	2	2	3	3	3	3	3
58.75°	2	2	2	3	3	3	3	3	3	3	3
57.5°	2	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	3	3	4	4	4
53.75°	3	3	3	3	3	3	4	4	4	4	4
52.5°	3	3	3	4	4	4	4	4	4	5	5
51.25°	3	4	4	4	4	4	4	5	5	5	5
50°	4	4	4	4	5	5	5	5	5	5	6
48.75°	4	4	5	5	5	5	5	6	6	6	6
47.5°	4	5	5	5	5	6	6	6	6	7	7
46.25°	5	5	5	5	6	6	6	7	7	7	8
45°	5	5	6	6	6	7	7	7	8	8	9
43.75°	6	6	6	7	7	7	8	8	9	9	9
42.5°	6	6	7	7	8	8	9	9	10	10	11
41.25°	6	7	7	8	9	9	9	10	11	11	12
40°	7	8	8	9	9	10	10	11	12	12	13
38.75°	8	8	9	9	10	11	12	12	13	14	15
37.5°	8	9	10	10	11	12	13	14	15	16	16
36.25°	9	10	10	11	12	13	14	15	16	17	19
35°	10	11	11	12	13	14	16	17	18	20	22



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	11	11	12	13	15	16	17	19	21	23	25
32.5°	11	12	14	15	16	18	20	22	24	26	29
31.25°	12	13	15	16	18	20	22	24	27	31	34
30°	13	15	16	18	20	22	25	28	32	35	39
28.75°	14	16	18	20	22	25	29	32	36	40	44
27.5°	16	17	20	22	25	29	32	36	41	45	49
26.25°	17	19	22	24	28	32	36	41	45	50	56
25°	18	21	24	27	32	36	41	45	51	57	63
23.75°	20	23	26	31	35	40	45	50	57	64	71
22.5°	22	25	29	34	39	44	49	56	63	71	80
21.25°	23	28	32	37	42	48	55	62	69	79	89
20°	25	30	35	40	46	53	60	68	78	88	98
18.75°	28	33	38	44	50	58	65	75	85	96	107
17.5°	30	35	41	47	54	62	71	82	93	105	117
16.25°	32	38	44	50	58	67	78	89	101	113	127
15°	34	40	46	54	62	72	84	95	108	122	137
13.75°	36	43	49	58	66	78	90	102	116	131	146
12.5°	38	45	52	61	70	83	95	109	123	139	156
11.25°	40	47	55	64	75	87	100	115	130	147	165
10°	42	49	58	67	79	92	105	121	137	154	173
8.75°	44	51	60	70	83	96	110	126	143	161	180
7.5°	45	53	62	73	86	99	114	131	149	168	187
6.25°	46	55	64	75	89	103	118	135	153	173	193
5°	47	56	65	78	91	105	121	139	158	177	199
3.75°	48	57	67	79	93	107	124	142	161	181	203
2.5°	49	58	67	81	94	109	126	144	163	183	206
1.25°	49	58	68	81	95	110	127	145	165	185	207
0°	49	59	68	82	95	110	127	145	165	186	208
-1.25°	49	58	68	81	95	110	127	145	165	185	207
-2.5°	49	58	67	81	94	109	126	144	163	183	206
-3.75°	48	57	67	79	93	107	124	142	161	181	203
-5°	47	56	65	78	91	105	121	139	158	177	199
-6.25°	46	55	64	75	89	103	118	135	153	173	193
-7.5°	45	53	62	73	86	99	114	131	149	168	187
-8.75°	44	51	60	70	83	96	110	126	143	161	180
-10°	42	49	58	67	79	92	105	121	137	154	173
-11.25°	40	47	55	64	75	87	100	115	130	147	165
-12.5°	38	45	52	61	70	83	95	109	123	139	156
-13.75°	36	43	49	58	66	78	90	102	116	131	146
-15°	34	40	46	54	62	72	84	95	108	122	137
-16.25°	32	38	44	50	58	67	78	89	101	113	127
-17.5°	30	35	41	47	54	62	71	82	93	105	117
-18.75°	28	33	38	44	50	58	65	75	85	96	107
-20°	25	30	35	40	46	53	60	68	78	88	98
-21.25°	23	28	32	37	42	48	55	62	69	79	89



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	22	25	29	34	39	44	49	56	63	71	80
-23.75°	20	23	26	31	35	40	45	50	57	64	71
-25°	18	21	24	27	32	36	41	45	51	57	63
-26.25°	17	19	22	24	28	32	36	41	45	50	56
-27.5°	16	17	20	22	25	29	32	36	41	45	49
-28.75°	14	16	18	20	22	25	29	32	36	40	44
-30°	13	15	16	18	20	22	25	28	32	35	39
-31.25°	12	13	15	16	18	20	22	24	27	31	34
-32.5°	11	12	14	15	16	18	20	22	24	26	29
-33.75°	11	11	12	13	15	16	17	19	21	23	25
-35°	10	11	11	12	13	14	16	17	18	20	22
-36.25°	9	10	10	11	12	13	14	15	16	17	19
-37.5°	8	9	10	10	11	12	13	14	15	16	16
-38.75°	8	8	9	9	10	11	12	12	13	14	15
-40°	7	8	8	9	9	10	10	11	12	12	13
-41.25°	6	7	7	8	9	9	9	10	11	11	12
-42.5°	6	6	7	7	8	8	9	9	10	10	11
-43.75°	6	6	6	7	7	7	8	8	9	9	9
-45°	5	5	6	6	6	7	7	7	8	8	9
-46.25°	5	5	5	5	6	6	6	7	7	7	8
-47.5°	4	5	5	5	5	6	6	6	6	7	7
-48.75°	4	4	5	5	5	5	5	6	6	6	6
-50°	4	4	4	4	5	5	5	5	5	5	6
-51.25°	3	4	4	4	4	4	4	5	5	5	5
-52.5°	3	3	3	4	4	4	4	4	4	5	5
-53.75°	3	3	3	3	3	3	4	4	4	4	4
-55°	3	3	3	3	3	3	3	3	4	4	4
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	2	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	3	3	3	3	3	3	3	3
-60°	2	2	2	2	2	2	3	3	3	3	3
-61.25°	2	2	2	2	2	2	2	2	2	2	3
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	1	1	2	2	2	2	2	2	2	2	2
-68.75°	1	1	1	1	1	1	2	2	2	2	2
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	0	0	0	0	0	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	3	3	3	3	3	4	4	4	4	4	4
56.25°	3	4	4	4	4	4	4	4	4	4	4
55°	4	4	4	4	4	4	5	5	5	5	5
53.75°	4	5	5	5	5	5	5	5	5	5	5
52.5°	5	5	5	5	5	5	6	6	6	6	6
51.25°	5	5	6	6	6	6	6	6	6	6	7
50°	6	6	6	6	6	7	7	7	7	7	8
48.75°	6	7	7	7	7	8	8	8	8	8	9
47.5°	7	8	8	8	8	9	9	9	9	9	10
46.25°	8	8	9	9	9	10	10	10	10	11	11
45°	9	9	10	10	10	11	11	11	12	12	12
43.75°	10	10	11	11	12	12	12	13	13	14	14
42.5°	11	12	12	13	13	14	14	15	15	15	16
41.25°	12	13	14	14	15	16	16	17	17	18	18
40°	14	15	15	16	17	18	19	20	20	21	22
38.75°	16	16	17	19	20	21	22	23	24	25	26
37.5°	18	19	20	22	23	24	26	27	29	30	31
36.25°	20	22	23	25	27	29	31	33	34	35	37
35°	23	25	28	30	32	34	36	38	40	42	44



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	28	30	33	35	38	40	43	45	47	49	51
32.5°	32	35	38	41	44	46	49	52	55	58	60
31.25°	37	40	44	47	50	54	58	61	64	67	70
30°	42	46	50	54	58	62	66	70	75	79	83
28.75°	48	53	58	62	67	72	78	83	87	92	96
27.5°	55	60	65	71	78	84	90	95	100	105	110
26.25°	62	68	75	82	89	95	102	109	115	121	126
25°	69	78	85	93	101	108	116	123	130	137	143
23.75°	79	88	96	105	113	122	131	139	147	154	161
22.5°	89	98	107	117	127	137	146	156	165	173	180
21.25°	99	109	119	130	141	152	163	173	182	192	201
20°	109	120	132	144	156	168	179	191	202	212	222
18.75°	119	132	145	158	171	184	197	210	222	234	245
17.5°	130	144	158	172	186	201	215	229	243	256	268
16.25°	141	156	171	186	202	217	234	250	265	279	290
15°	152	168	184	201	217	235	253	270	285	299	312
13.75°	163	179	197	215	234	253	272	288	304	319	332
12.5°	173	191	210	229	250	270	288	306	323	338	351
11.25°	182	202	222	243	265	285	304	323	340	355	368
10°	192	212	234	256	279	299	319	338	355	370	384
8.75°	201	222	245	268	290	312	332	351	368	384	398
7.5°	208	231	255	279	301	323	344	363	380	396	411
6.25°	215	239	264	288	310	333	354	373	390	407	422
5°	221	246	271	295	318	341	362	381	399	416	432
3.75°	226	251	277	300	324	347	368	387	406	423	440
2.5°	229	255	281	305	329	351	372	392	411	428	446
1.25°	231	257	283	307	331	354	375	395	414	432	449
0°	232	258	284	308	332	355	376	396	415	433	450
-1.25°	231	257	283	307	331	354	375	395	414	432	449
-2.5°	229	255	281	305	329	351	372	392	411	428	446
-3.75°	226	251	277	300	324	347	368	387	406	423	440
-5°	221	246	271	295	318	341	362	381	399	416	432
-6.25°	215	239	264	288	310	333	354	373	390	407	422
-7.5°	208	231	255	279	301	323	344	363	380	396	411
-8.75°	201	222	245	268	290	312	332	351	368	384	398
-10°	192	212	234	256	279	299	319	338	355	370	384
-11.25°	182	202	222	243	265	285	304	323	340	355	368
-12.5°	173	191	210	229	250	270	288	306	323	338	351
-13.75°	163	179	197	215	234	253	272	288	304	319	332
-15°	152	168	184	201	217	235	253	270	285	299	312
-16.25°	141	156	171	186	202	217	234	250	265	279	290
-17.5°	130	144	158	172	186	201	215	229	243	256	268
-18.75°	119	132	145	158	171	184	197	210	222	234	245
-20°	109	120	132	144	156	168	179	191	202	212	222
-21.25°	99	109	119	130	141	152	163	173	182	192	201



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	89	98	107	117	127	137	146	156	165	173	180
-23.75°	79	88	96	105	113	122	131	139	147	154	161
-25°	69	78	85	93	101	108	116	123	130	137	143
-26.25°	62	68	75	82	89	95	102	109	115	121	126
-27.5°	55	60	65	71	78	84	90	95	100	105	110
-28.75°	48	53	58	62	67	72	78	83	87	92	96
-30°	42	46	50	54	58	62	66	70	75	79	83
-31.25°	37	40	44	47	50	54	58	61	64	67	70
-32.5°	32	35	38	41	44	46	49	52	55	58	60
-33.75°	28	30	33	35	38	40	43	45	47	49	51
-35°	23	25	28	30	32	34	36	38	40	42	44
-36.25°	20	22	23	25	27	29	31	33	34	35	37
-37.5°	18	19	20	22	23	24	26	27	29	30	31
-38.75°	16	16	17	19	20	21	22	23	24	25	26
-40°	14	15	15	16	17	18	19	20	20	21	22
-41.25°	12	13	14	14	15	16	16	17	17	18	18
-42.5°	11	12	12	13	13	14	14	15	15	15	16
-43.75°	10	10	11	11	12	12	12	13	13	14	14
-45°	9	9	10	10	10	11	11	11	12	12	12
-46.25°	8	8	9	9	9	10	10	10	10	11	11
-47.5°	7	8	8	8	8	9	9	9	9	9	10
-48.75°	6	7	7	7	7	8	8	8	8	8	9
-50°	6	6	6	6	6	7	7	7	7	7	8
-51.25°	5	5	6	6	6	6	6	6	6	6	7
-52.5°	5	5	5	5	5	5	6	6	6	6	6
-53.75°	4	5	5	5	5	5	5	5	5	5	5
-55°	4	4	4	4	4	4	5	5	5	5	5
-56.25°	3	4	4	4	4	4	4	4	4	4	4
-57.5°	3	3	3	3	3	4	4	4	4	4	4
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	2	2	2	2	3	3	3	3	3	3	3
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	1	1	2	2	2	2	2	2	2	2	2
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	1	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	2	1	1	1	1
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	3	2	2	2	2
62.5°	3	3	3	3	3	3	3	3	3	3	3
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	4	3	3	3	3
57.5°	4	4	4	4	4	4	4	4	4	4	4
56.25°	4	4	4	4	4	4	5	4	4	4	4
55°	5	5	5	5	5	5	5	5	5	5	5
53.75°	5	5	5	5	5	5	6	5	5	5	5
52.5°	6	6	6	6	6	6	6	6	6	6	6
51.25°	7	7	7	7	7	7	7	7	7	7	7
50°	8	8	8	8	8	8	8	8	8	8	8
48.75°	9	9	9	9	9	9	9	9	9	9	9
47.5°	10	10	10	10	10	10	10	10	10	10	10
46.25°	11	11	11	11	11	11	12	11	11	11	11
45°	12	13	13	13	13	13	13	13	13	13	13
43.75°	14	14	15	15	15	15	15	15	15	15	15
42.5°	16	16	17	17	17	17	17	17	17	17	17
41.25°	19	19	20	20	20	20	21	20	20	20	20
40°	22	23	23	24	24	24	24	24	24	24	23
38.75°	27	28	28	29	29	29	30	29	29	29	28
37.5°	32	33	34	34	35	35	35	35	35	34	34
36.25°	38	39	40	41	42	42	42	42	42	41	40
35°	45	46	47	48	49	49	49	49	49	48	47



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	53	55	56	57	58	58	59	58	58	57	56
32.5°	62	64	65	67	67	68	68	68	67	67	65
31.25°	73	75	78	79	81	81	82	81	81	79	78
30°	86	89	91	93	94	95	95	95	94	93	91
28.75°	99	103	105	107	109	110	110	110	109	107	105
27.5°	114	118	121	124	126	127	127	127	126	124	121
26.25°	131	135	139	142	144	145	145	145	144	142	139
25°	149	153	158	161	163	165	165	165	163	161	158
23.75°	168	173	177	181	183	185	186	185	183	181	177
22.5°	187	193	199	203	206	207	208	207	206	203	199
21.25°	208	215	221	226	229	231	232	231	229	226	221
20°	231	239	246	251	255	257	258	257	255	251	246
18.75°	255	264	271	277	281	283	284	283	281	277	271
17.5°	279	288	295	300	305	307	308	307	305	300	295
16.25°	301	310	318	324	329	331	332	331	329	324	318
15°	323	333	341	347	351	354	355	354	351	347	341
13.75°	344	354	362	368	372	375	376	375	372	368	362
12.5°	363	373	381	387	392	395	396	395	392	387	381
11.25°	380	390	399	406	411	414	415	414	411	406	399
10°	396	407	416	423	428	432	433	432	428	423	416
8.75°	411	422	432	440	446	449	450	449	446	440	432
7.5°	424	436	447	455	461	464	465	464	461	455	447
6.25°	436	449	460	467	472	476	477	476	472	467	460
5°	447	460	469	477	482	485	486	485	482	477	469
3.75°	455	467	477	484	488	491	492	491	488	484	477
2.5°	461	472	482	488	492	495	496	495	492	488	482
1.25°	464	476	485	491	495	497	499	497	495	491	485
0°	465	477	486	492	496	499	502	499	496	492	486
-1.25°	464	476	485	491	495	497	499	497	495	491	485
-2.5°	461	472	482	488	492	495	496	495	492	488	482
-3.75°	455	467	477	484	488	491	492	491	488	484	477
-5°	447	460	469	477	482	485	486	485	482	477	469
-6.25°	436	449	460	467	472	476	477	476	472	467	460
-7.5°	424	436	447	455	461	464	465	464	461	455	447
-8.75°	411	422	432	440	446	449	450	449	446	440	432
-10°	396	407	416	423	428	432	433	432	428	423	416
-11.25°	380	390	399	406	411	414	415	414	411	406	399
-12.5°	363	373	381	387	392	395	396	395	392	387	381
-13.75°	344	354	362	368	372	375	376	375	372	368	362
-15°	323	333	341	347	351	354	355	354	351	347	341
-16.25°	301	310	318	324	329	331	332	331	329	324	318
-17.5°	279	288	295	300	305	307	308	307	305	300	295
-18.75°	255	264	271	277	281	283	284	283	281	277	271
-20°	231	239	246	251	255	257	258	257	255	251	246
-21.25°	208	215	221	226	229	231	232	231	229	226	221



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	187	193	199	203	206	207	208	207	206	203	199
-23.75°	168	173	177	181	183	185	186	185	183	181	177
-25°	149	153	158	161	163	165	165	165	163	161	158
-26.25°	131	135	139	142	144	145	145	145	144	142	139
-27.5°	114	118	121	124	126	127	127	127	126	124	121
-28.75°	99	103	105	107	109	110	110	110	109	107	105
-30°	86	89	91	93	94	95	95	95	94	93	91
-31.25°	73	75	78	79	81	81	82	81	81	79	78
-32.5°	62	64	65	67	67	68	68	68	67	67	65
-33.75°	53	55	56	57	58	58	59	58	58	57	56
-35°	45	46	47	48	49	49	49	49	49	48	47
-36.25°	38	39	40	41	42	42	42	42	42	41	40
-37.5°	32	33	34	34	35	35	35	35	35	34	34
-38.75°	27	28	28	29	29	29	30	29	29	29	28
-40°	22	23	23	24	24	24	24	24	24	24	23
-41.25°	19	19	20	20	20	20	21	20	20	20	20
-42.5°	16	16	17	17	17	17	17	17	17	17	17
-43.75°	14	14	15	15	15	15	15	15	15	15	15
-45°	12	13	13	13	13	13	13	13	13	13	13
-46.25°	11	11	11	11	11	11	12	11	11	11	11
-47.5°	10	10	10	10	10	10	10	10	10	10	10
-48.75°	9	9	9	9	9	9	9	9	9	9	9
-50°	8	8	8	8	8	8	8	8	8	8	8
-51.25°	7	7	7	7	7	7	7	7	7	7	7
-52.5°	6	6	6	6	6	6	6	6	6	6	6
-53.75°	5	5	5	5	5	5	6	5	5	5	5
-55°	5	5	5	5	5	5	5	5	5	5	5
-56.25°	4	4	4	4	4	4	5	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	4	4	4
-58.75°	3	3	3	3	3	3	4	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	3	3
-63.75°	2	2	2	2	2	2	3	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	1	1	1	1	1	1	2	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	1	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	1	1	1	1	1
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	2	2	2	2	2	2	2	2	2	2	2
68.75°	2	2	2	2	2	2	2	2	2	2	2
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	3	3	3	3	3	3	3	3	3	2	2
61.25°	3	3	3	3	3	3	3	3	3	3	3
60°	3	3	3	3	3	3	3	3	3	3	3
58.75°	3	3	3	3	3	3	3	3	3	3	3
57.5°	4	4	4	4	4	4	4	4	3	3	3
56.25°	4	4	4	4	4	4	4	4	4	4	4
55°	5	5	5	5	5	5	5	4	4	4	4
53.75°	5	5	5	5	5	5	5	5	5	5	5
52.5°	6	6	6	6	6	6	6	5	5	5	5
51.25°	7	7	7	6	6	6	6	6	6	6	6
50°	8	8	8	7	7	7	7	7	6	6	6
48.75°	9	9	9	8	8	8	8	8	7	7	7
47.5°	10	10	10	9	9	9	9	9	8	8	8
46.25°	11	11	11	11	10	10	10	10	9	9	9
45°	13	12	12	12	12	11	11	11	10	10	10
43.75°	14	14	14	14	13	13	12	12	12	11	11
42.5°	16	16	16	15	15	15	14	14	13	13	12
41.25°	19	19	18	18	17	17	16	16	15	14	14
40°	23	22	22	21	20	20	19	18	17	16	15
38.75°	28	27	26	25	24	23	22	21	20	19	17
37.5°	33	32	31	30	29	27	26	24	23	22	20
36.25°	39	38	37	35	34	33	31	29	27	25	23
35°	46	45	44	42	40	38	36	34	32	30	28



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	55	53	51	49	47	45	43	40	38	35	33
32.5°	64	62	60	58	55	52	49	46	44	41	38
31.25°	75	73	70	67	64	61	58	54	50	47	44
30°	89	86	83	79	75	70	66	62	58	54	50
28.75°	103	99	96	92	87	83	78	72	67	62	58
27.5°	118	114	110	105	100	95	90	84	78	71	65
26.25°	135	131	126	121	115	109	102	95	89	82	75
25°	153	149	143	137	130	123	116	108	101	93	85
23.75°	173	168	161	154	147	139	131	122	113	105	96
22.5°	193	187	180	173	165	156	146	137	127	117	107
21.25°	215	208	201	192	182	173	163	152	141	130	119
20°	239	231	222	212	202	191	179	168	156	144	132
18.75°	264	255	245	234	222	210	197	184	171	158	145
17.5°	288	279	268	256	243	229	215	201	186	172	158
16.25°	310	301	290	279	265	250	234	217	202	186	171
15°	333	323	312	299	285	270	253	235	217	201	184
13.75°	354	344	332	319	304	288	272	253	234	215	197
12.5°	373	363	351	338	323	306	288	270	250	229	210
11.25°	390	380	368	355	340	323	304	285	265	243	222
10°	407	396	384	370	355	338	319	299	279	256	234
8.75°	422	411	398	384	368	351	332	312	290	268	245
7.5°	436	424	411	396	380	363	344	323	301	279	255
6.25°	449	436	422	407	390	373	354	333	310	288	264
5°	460	447	432	416	399	381	362	341	318	295	271
3.75°	467	455	440	423	406	387	368	347	324	300	277
2.5°	472	461	446	428	411	392	372	351	329	305	281
1.25°	476	464	449	432	414	395	375	354	331	307	283
0°	477	465	450	433	415	396	376	355	332	308	284
-1.25°	476	464	449	432	414	395	375	354	331	307	283
-2.5°	472	461	446	428	411	392	372	351	329	305	281
-3.75°	467	455	440	423	406	387	368	347	324	300	277
-5°	460	447	432	416	399	381	362	341	318	295	271
-6.25°	449	436	422	407	390	373	354	333	310	288	264
-7.5°	436	424	411	396	380	363	344	323	301	279	255
-8.75°	422	411	398	384	368	351	332	312	290	268	245
-10°	407	396	384	370	355	338	319	299	279	256	234
-11.25°	390	380	368	355	340	323	304	285	265	243	222
-12.5°	373	363	351	338	323	306	288	270	250	229	210
-13.75°	354	344	332	319	304	288	272	253	234	215	197
-15°	333	323	312	299	285	270	253	235	217	201	184
-16.25°	310	301	290	279	265	250	234	217	202	186	171
-17.5°	288	279	268	256	243	229	215	201	186	172	158
-18.75°	264	255	245	234	222	210	197	184	171	158	145
-20°	239	231	222	212	202	191	179	168	156	144	132
-21.25°	215	208	201	192	182	173	163	152	141	130	119



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	193	187	180	173	165	156	146	137	127	117	107
-23.75°	173	168	161	154	147	139	131	122	113	105	96
-25°	153	149	143	137	130	123	116	108	101	93	85
-26.25°	135	131	126	121	115	109	102	95	89	82	75
-27.5°	118	114	110	105	100	95	90	84	78	71	65
-28.75°	103	99	96	92	87	83	78	72	67	62	58
-30°	89	86	83	79	75	70	66	62	58	54	50
-31.25°	75	73	70	67	64	61	58	54	50	47	44
-32.5°	64	62	60	58	55	52	49	46	44	41	38
-33.75°	55	53	51	49	47	45	43	40	38	35	33
-35°	46	45	44	42	40	38	36	34	32	30	28
-36.25°	39	38	37	35	34	33	31	29	27	25	23
-37.5°	33	32	31	30	29	27	26	24	23	22	20
-38.75°	28	27	26	25	24	23	22	21	20	19	17
-40°	23	22	22	21	20	20	19	18	17	16	15
-41.25°	19	19	18	18	17	17	16	16	15	14	14
-42.5°	16	16	16	15	15	15	14	14	13	13	12
-43.75°	14	14	14	14	13	13	12	12	12	11	11
-45°	13	12	12	12	12	11	11	11	10	10	10
-46.25°	11	11	11	11	10	10	10	10	9	9	9
-47.5°	10	10	10	9	9	9	9	9	8	8	8
-48.75°	9	9	9	8	8	8	8	8	7	7	7
-50°	8	8	8	7	7	7	7	7	6	6	6
-51.25°	7	7	7	6	6	6	6	6	6	6	6
-52.5°	6	6	6	6	6	6	6	5	5	5	5
-53.75°	5	5	5	5	5	5	5	5	5	5	5
-55°	5	5	5	5	5	5	5	4	4	4	4
-56.25°	4	4	4	4	4	4	4	4	4	4	4
-57.5°	4	4	4	4	4	4	4	4	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	3
-60°	3	3	3	3	3	3	3	3	3	3	3
-61.25°	3	3	3	3	3	3	3	3	3	3	3
-62.5°	3	3	3	3	3	3	3	3	3	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	2	2	2	2
-70°	2	2	2	2	2	2	2	2	2	2	2
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	1	1	1
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	1	1	1	1	1	1	1	1	0	0	0
78.75°	1	1	1	1	1	1	1	1	1	1	1
77.5°	1	1	1	1	1	1	1	1	1	1	1
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	2	2	2	2	2	2	2	1	1	1	1
67.5°	2	2	2	2	2	2	2	2	2	2	2
66.25°	2	2	2	2	2	2	2	2	2	2	2
65°	2	2	2	2	2	2	2	2	2	2	2
63.75°	2	2	2	2	2	2	2	2	2	2	2
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	3	3	3	2	2	2	2	2	2	2	2
60°	3	3	3	3	3	3	3	2	2	2	2
58.75°	3	3	3	3	3	3	3	3	3	3	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	4	3	3	3	3	3	3	3	3	3	3
55°	4	4	4	4	4	3	3	3	3	3	3
53.75°	5	4	4	4	4	4	4	3	3	3	3
52.5°	5	5	5	5	4	4	4	4	4	4	3
51.25°	5	5	5	5	5	5	4	4	4	4	4
50°	6	6	6	5	5	5	5	5	5	4	4
48.75°	7	6	6	6	6	6	5	5	5	5	5
47.5°	8	7	7	7	6	6	6	6	5	5	5
46.25°	8	8	8	7	7	7	6	6	6	5	5
45°	9	9	9	8	8	7	7	7	6	6	6
43.75°	10	10	9	9	9	8	8	7	7	7	6
42.5°	12	11	11	10	10	9	9	8	8	7	7
41.25°	13	12	12	11	11	10	9	9	9	8	7
40°	15	14	13	12	12	11	10	10	9	9	8
38.75°	16	16	15	14	13	12	12	11	10	9	9
37.5°	19	18	16	16	15	14	13	12	11	10	10
36.25°	22	20	19	17	16	15	14	13	12	11	10
35°	25	23	22	20	18	17	16	14	13	12	11



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	30	28	25	23	21	19	17	16	15	13	12
32.5°	35	32	29	26	24	22	20	18	16	15	14
31.25°	40	37	34	31	27	24	22	20	18	16	15
30°	46	42	39	35	32	28	25	22	20	18	16
28.75°	53	48	44	40	36	32	29	25	22	20	18
27.5°	60	55	49	45	41	36	32	29	25	22	20
26.25°	68	62	56	50	45	41	36	32	28	24	22
25°	78	69	63	57	51	45	41	36	32	27	24
23.75°	88	79	71	64	57	50	45	40	35	31	26
22.5°	98	89	80	71	63	56	49	44	39	34	29
21.25°	109	99	89	79	69	62	55	48	42	37	32
20°	120	109	98	88	78	68	60	53	46	40	35
18.75°	132	119	107	96	85	75	65	58	50	44	38
17.5°	144	130	117	105	93	82	71	62	54	47	41
16.25°	156	141	127	113	101	89	78	67	58	50	44
15°	168	152	137	122	108	95	84	72	62	54	46
13.75°	179	163	146	131	116	102	90	78	66	58	49
12.5°	191	173	156	139	123	109	95	83	70	61	52
11.25°	202	182	165	147	130	115	100	87	75	64	55
10°	212	192	173	154	137	121	105	92	79	67	58
8.75°	222	201	180	161	143	126	110	96	83	70	60
7.5°	231	208	187	168	149	131	114	99	86	73	62
6.25°	239	215	193	173	153	135	118	103	89	75	64
5°	246	221	199	177	158	139	121	105	91	78	65
3.75°	251	226	203	181	161	142	124	107	93	79	67
2.5°	255	229	206	183	163	144	126	109	94	81	67
1.25°	257	231	207	185	165	145	127	110	95	81	68
0°	258	232	208	186	165	145	127	110	95	82	68
-1.25°	257	231	207	185	165	145	127	110	95	81	68
-2.5°	255	229	206	183	163	144	126	109	94	81	67
-3.75°	251	226	203	181	161	142	124	107	93	79	67
-5°	246	221	199	177	158	139	121	105	91	78	65
-6.25°	239	215	193	173	153	135	118	103	89	75	64
-7.5°	231	208	187	168	149	131	114	99	86	73	62
-8.75°	222	201	180	161	143	126	110	96	83	70	60
-10°	212	192	173	154	137	121	105	92	79	67	58
-11.25°	202	182	165	147	130	115	100	87	75	64	55
-12.5°	191	173	156	139	123	109	95	83	70	61	52
-13.75°	179	163	146	131	116	102	90	78	66	58	49
-15°	168	152	137	122	108	95	84	72	62	54	46
-16.25°	156	141	127	113	101	89	78	67	58	50	44
-17.5°	144	130	117	105	93	82	71	62	54	47	41
-18.75°	132	119	107	96	85	75	65	58	50	44	38
-20°	120	109	98	88	78	68	60	53	46	40	35
-21.25°	109	99	89	79	69	62	55	48	42	37	32



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	98	89	80	71	63	56	49	44	39	34	29
-23.75°	88	79	71	64	57	50	45	40	35	31	26
-25°	78	69	63	57	51	45	41	36	32	27	24
-26.25°	68	62	56	50	45	41	36	32	28	24	22
-27.5°	60	55	49	45	41	36	32	29	25	22	20
-28.75°	53	48	44	40	36	32	29	25	22	20	18
-30°	46	42	39	35	32	28	25	22	20	18	16
-31.25°	40	37	34	31	27	24	22	20	18	16	15
-32.5°	35	32	29	26	24	22	20	18	16	15	14
-33.75°	30	28	25	23	21	19	17	16	15	13	12
-35°	25	23	22	20	18	17	16	14	13	12	11
-36.25°	22	20	19	17	16	15	14	13	12	11	10
-37.5°	19	18	16	16	15	14	13	12	11	10	10
-38.75°	16	16	15	14	13	12	12	11	10	9	9
-40°	15	14	13	12	12	11	10	10	9	9	8
-41.25°	13	12	12	11	11	10	9	9	9	8	7
-42.5°	12	11	11	10	10	9	9	8	8	7	7
-43.75°	10	10	9	9	9	8	8	7	7	7	6
-45°	9	9	9	8	8	7	7	7	6	6	6
-46.25°	8	8	8	7	7	7	6	6	6	5	5
-47.5°	8	7	7	7	6	6	6	6	5	5	5
-48.75°	7	6	6	6	6	6	5	5	5	5	5
-50°	6	6	6	5	5	5	5	5	5	4	4
-51.25°	5	5	5	5	5	5	4	4	4	4	4
-52.5°	5	5	5	5	4	4	4	4	4	4	3
-53.75°	5	4	4	4	4	4	4	3	3	3	3
-55°	4	4	4	4	4	3	3	3	3	3	3
-56.25°	4	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	3	3	3	3	3	3	3	3	3	3	2
-60°	3	3	3	3	3	3	3	2	2	2	2
-61.25°	3	3	3	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	2	2	2	2	2	2	2	2	2	2	2
-65°	2	2	2	2	2	2	2	2	2	2	2
-66.25°	2	2	2	2	2	2	2	2	2	2	2
-67.5°	2	2	2	2	2	2	2	2	2	2	2
-68.75°	2	2	2	2	2	2	2	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	1	1	1	1	1	1	1	1	1	1	1
-80°	1	1	1	1	1	1	1	1	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	1	1	1	1	1	0	0	0	0	0	0
77.5°	1	1	1	1	1	1	1	1	1	1	0
76.25°	1	1	1	1	1	1	1	1	1	1	1
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	2	2	2	1	1	1	1	1	1	1	1
65°	2	2	2	2	2	2	1	1	1	1	1
63.75°	2	2	2	2	2	2	2	2	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	2	2	2	2	2	2	2	2	2	2
56.25°	3	3	3	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	2	2	2	2	2	2
53.75°	3	3	3	3	3	3	3	2	2	2	2
52.5°	3	3	3	3	3	3	3	3	2	2	2
51.25°	4	3	3	3	3	3	3	3	3	3	2
50°	4	4	3	3	3	3	3	3	3	3	3
48.75°	4	4	4	4	3	3	3	3	3	3	3
47.5°	5	4	4	4	4	3	3	3	3	3	3
46.25°	5	5	5	4	4	4	4	3	3	3	3
45°	5	5	5	5	4	4	4	4	3	3	3
43.75°	6	6	5	5	5	4	4	4	4	3	3
42.5°	6	6	6	5	5	5	4	4	4	4	3
41.25°	7	6	6	6	5	5	5	4	4	4	4
40°	8	7	7	6	6	5	5	5	4	4	4
38.75°	8	8	7	7	6	6	5	5	5	4	4
37.5°	9	8	8	7	7	6	6	5	5	5	4
36.25°	10	9	8	8	7	7	6	6	5	5	5
35°	11	10	9	8	8	7	6	6	6	5	5



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	11	11	10	9	8	8	7	6	6	5	5
32.5°	12	11	10	10	9	8	7	7	6	6	5
31.25°	13	12	11	10	9	9	8	7	7	6	5
30°	15	13	12	11	10	9	9	8	7	6	6
28.75°	16	14	13	12	11	10	9	8	7	7	6
27.5°	17	16	14	13	12	10	9	9	8	7	6
26.25°	19	17	15	14	12	11	10	9	8	7	7
25°	21	18	16	15	13	12	11	10	9	8	7
23.75°	23	20	17	16	14	12	11	10	9	8	7
22.5°	25	22	19	16	15	13	12	11	9	9	8
21.25°	28	23	20	18	16	14	12	11	10	9	8
20°	30	25	22	19	16	15	13	12	10	9	8
18.75°	33	28	23	20	17	15	14	12	11	10	9
17.5°	35	30	25	22	19	16	14	13	11	10	9
16.25°	38	32	27	23	20	17	15	13	12	10	9
15°	40	34	29	24	21	18	16	14	12	11	10
13.75°	43	36	31	26	22	19	16	14	12	11	10
12.5°	45	38	33	27	23	20	17	15	13	11	10
11.25°	47	40	34	29	24	20	17	15	13	12	10
10°	49	42	35	30	25	21	18	15	14	12	11
8.75°	51	44	37	31	26	22	18	16	14	12	11
7.5°	53	45	38	32	27	22	19	16	14	12	11
6.25°	55	46	39	33	28	23	19	16	14	13	11
5°	56	47	40	34	28	23	20	17	15	13	11
3.75°	57	48	41	34	29	24	20	17	15	13	11
2.5°	58	49	42	35	29	24	20	17	15	13	11
1.25°	58	49	42	35	29	24	20	17	15	13	11
0°	59	49	42	35	30	24	21	17	15	13	12
-1.25°	58	49	42	35	29	24	20	17	15	13	11
-2.5°	58	49	42	35	29	24	20	17	15	13	11
-3.75°	57	48	41	34	29	24	20	17	15	13	11
-5°	56	47	40	34	28	23	20	17	15	13	11
-6.25°	55	46	39	33	28	23	19	16	14	13	11
-7.5°	53	45	38	32	27	22	19	16	14	12	11
-8.75°	51	44	37	31	26	22	18	16	14	12	11
-10°	49	42	35	30	25	21	18	15	14	12	11
-11.25°	47	40	34	29	24	20	17	15	13	12	10
-12.5°	45	38	33	27	23	20	17	15	13	11	10
-13.75°	43	36	31	26	22	19	16	14	12	11	10
-15°	40	34	29	24	21	18	16	14	12	11	10
-16.25°	38	32	27	23	20	17	15	13	12	10	9
-17.5°	35	30	25	22	19	16	14	13	11	10	9
-18.75°	33	28	23	20	17	15	14	12	11	10	9
-20°	30	25	22	19	16	15	13	12	10	9	8
-21.25°	28	23	20	18	16	14	12	11	10	9	8



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	25	22	19	16	15	13	12	11	9	9	8
-23.75°	23	20	17	16	14	12	11	10	9	8	7
-25°	21	18	16	15	13	12	11	10	9	8	7
-26.25°	19	17	15	14	12	11	10	9	8	7	7
-27.5°	17	16	14	13	12	10	9	9	8	7	6
-28.75°	16	14	13	12	11	10	9	8	7	7	6
-30°	15	13	12	11	10	9	9	8	7	6	6
-31.25°	13	12	11	10	9	9	8	7	7	6	5
-32.5°	12	11	10	10	9	8	7	7	6	6	5
-33.75°	11	11	10	9	8	8	7	6	6	5	5
-35°	11	10	9	8	8	7	6	6	6	5	5
-36.25°	10	9	8	8	7	7	6	6	5	5	5
-37.5°	9	8	8	7	7	6	6	5	5	5	4
-38.75°	8	8	7	7	6	6	5	5	5	4	4
-40°	8	7	7	6	6	5	5	5	4	4	4
-41.25°	7	6	6	6	5	5	5	4	4	4	4
-42.5°	6	6	6	5	5	5	4	4	4	4	3
-43.75°	6	6	5	5	5	4	4	4	4	3	3
-45°	5	5	5	5	4	4	4	4	3	3	3
-46.25°	5	5	5	4	4	4	4	3	3	3	3
-47.5°	5	4	4	4	4	3	3	3	3	3	3
-48.75°	4	4	4	4	3	3	3	3	3	3	3
-50°	4	4	3	3	3	3	3	3	3	3	3
-51.25°	4	3	3	3	3	3	3	3	3	3	2
-52.5°	3	3	3	3	3	3	3	3	2	2	2
-53.75°	3	3	3	3	3	3	3	2	2	2	2
-55°	3	3	3	3	3	2	2	2	2	2	2
-56.25°	3	3	3	2	2	2	2	2	2	2	2
-57.5°	3	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	1
-63.75°	2	2	2	2	2	2	2	2	1	1	1
-65°	2	2	2	2	2	2	1	1	1	1	1
-66.25°	2	2	2	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	1	1	1	1	1	1	1	1	1	1	1
-77.5°	1	1	1	1	1	1	1	1	1	1	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	1	1	1	1	1	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	1	1	1	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	0	0	0
72.5°	1	1	1	1	1	1	1	1	1	1	0
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	1	1	1	1	1	1	1	1	1	1
60°	2	2	1	1	1	1	1	1	1	1	1
58.75°	2	2	2	2	1	1	1	1	1	1	1
57.5°	2	2	2	2	2	1	1	1	1	1	1
56.25°	2	2	2	2	2	2	1	1	1	1	1
55°	2	2	2	2	2	2	2	1	1	1	1
53.75°	2	2	2	2	2	2	2	2	1	1	1
52.5°	2	2	2	2	2	2	2	2	2	1	1
51.25°	2	2	2	2	2	2	2	2	2	2	1
50°	2	2	2	2	2	2	2	2	2	2	1
48.75°	3	2	2	2	2	2	2	2	2	2	2
47.5°	3	3	2	2	2	2	2	2	2	2	2
46.25°	3	3	3	2	2	2	2	2	2	2	2
45°	3	3	3	3	2	2	2	2	2	2	2
43.75°	3	3	3	3	2	2	2	2	2	2	2
42.5°	3	3	3	3	3	2	2	2	2	2	2
41.25°	3	3	3	3	3	3	2	2	2	2	2
40°	3	3	3	3	3	3	2	2	2	2	2
38.75°	4	3	3	3	3	3	3	2	2	2	2
37.5°	4	4	3	3	3	3	3	2	2	2	2
36.25°	4	4	3	3	3	3	3	3	2	2	2
35°	4	4	4	3	3	3	3	3	2	2	2



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	5	4	4	4	3	3	3	3	3	2	2
32.5°	5	5	4	4	3	3	3	3	3	2	2
31.25°	5	5	4	4	4	3	3	3	3	3	2
30°	5	5	5	4	4	3	3	3	3	3	2
28.75°	6	5	5	4	4	3	3	3	3	3	2
27.5°	6	5	5	4	4	4	3	3	3	3	3
26.25°	6	6	5	5	4	4	3	3	3	3	3
25°	6	6	5	5	4	4	4	3	3	3	3
23.75°	7	6	5	5	5	4	4	3	3	3	3
22.5°	7	6	6	5	5	4	4	3	3	3	3
21.25°	7	6	6	5	5	4	4	3	3	3	3
20°	8	7	6	5	5	5	4	4	3	3	3
18.75°	8	7	6	6	5	5	4	4	3	3	3
17.5°	8	7	6	6	5	5	4	4	3	3	3
16.25°	8	7	6	6	5	5	4	4	3	3	3
15°	9	8	7	6	5	5	4	4	4	3	3
13.75°	9	8	7	6	6	5	5	4	4	3	3
12.5°	9	8	7	6	6	5	5	4	4	3	3
11.25°	9	8	7	6	6	5	5	4	4	3	3
10°	9	8	7	6	6	5	5	4	4	3	3
8.75°	10	9	8	7	6	5	5	4	4	3	3
7.5°	10	9	8	7	6	5	5	4	4	3	3
6.25°	10	9	8	7	6	5	5	4	4	3	3
5°	10	9	8	7	6	5	5	4	4	3	3
3.75°	10	9	8	7	6	5	5	4	4	3	3
2.5°	10	9	8	7	6	5	5	4	4	3	3
1.25°	10	9	8	7	6	5	5	4	4	3	3
0°	10	9	8	7	6	6	5	5	4	4	3
-1.25°	10	9	8	7	6	5	5	4	4	3	3
-2.5°	10	9	8	7	6	5	5	4	4	3	3
-3.75°	10	9	8	7	6	5	5	4	4	3	3
-5°	10	9	8	7	6	5	5	4	4	3	3
-6.25°	10	9	8	7	6	5	5	4	4	3	3
-7.5°	10	9	8	7	6	5	5	4	4	3	3
-8.75°	10	9	8	7	6	5	5	4	4	3	3
-10°	9	8	7	6	6	5	5	4	4	3	3
-11.25°	9	8	7	6	6	5	5	4	4	3	3
-12.5°	9	8	7	6	6	5	5	4	4	3	3
-13.75°	9	8	7	6	6	5	5	4	4	3	3
-15°	9	8	7	6	5	5	4	4	4	3	3
-16.25°	8	7	6	6	5	5	4	4	3	3	3
-17.5°	8	7	6	6	5	5	4	4	3	3	3
-18.75°	8	7	6	6	5	5	4	4	3	3	3
-20°	8	7	6	5	5	5	4	4	3	3	3
-21.25°	7	6	6	5	5	4	4	3	3	3	3



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	7	6	6	5	5	4	4	3	3	3	3
-23.75°	7	6	5	5	5	4	4	3	3	3	3
-25°	6	6	5	5	4	4	4	3	3	3	3
-26.25°	6	6	5	5	4	4	3	3	3	3	3
-27.5°	6	5	5	4	4	4	3	3	3	3	3
-28.75°	6	5	5	4	4	3	3	3	3	3	2
-30°	5	5	5	4	4	3	3	3	3	3	2
-31.25°	5	5	4	4	4	3	3	3	3	3	2
-32.5°	5	5	4	4	3	3	3	3	3	2	2
-33.75°	5	4	4	4	3	3	3	3	3	2	2
-35°	4	4	4	3	3	3	3	3	2	2	2
-36.25°	4	4	3	3	3	3	3	3	2	2	2
-37.5°	4	4	3	3	3	3	3	2	2	2	2
-38.75°	4	3	3	3	3	3	3	2	2	2	2
-40°	3	3	3	3	3	3	2	2	2	2	2
-41.25°	3	3	3	3	3	3	2	2	2	2	2
-42.5°	3	3	3	3	3	2	2	2	2	2	2
-43.75°	3	3	3	3	2	2	2	2	2	2	2
-45°	3	3	3	3	2	2	2	2	2	2	2
-46.25°	3	3	3	2	2	2	2	2	2	2	2
-47.5°	3	3	2	2	2	2	2	2	2	2	2
-48.75°	3	2	2	2	2	2	2	2	2	2	2
-50°	2	2	2	2	2	2	2	2	2	2	1
-51.25°	2	2	2	2	2	2	2	2	2	2	1
-52.5°	2	2	2	2	2	2	2	2	2	1	1
-53.75°	2	2	2	2	2	2	2	2	1	1	1
-55°	2	2	2	2	2	2	2	1	1	1	1
-56.25°	2	2	2	2	2	2	1	1	1	1	1
-57.5°	2	2	2	2	2	1	1	1	1	1	1
-58.75°	2	2	2	2	1	1	1	1	1	1	1
-60°	2	2	1	1	1	1	1	1	1	1	1
-61.25°	2	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	0
-73.75°	1	1	1	1	1	1	1	1	0	0	0
-75°	1	1	1	1	1	1	0	0	0	0	0
-76.25°	1	1	1	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	1	0	0	0	0	0	0	0	0	0	0
70°	1	1	0	0	0	0	0	0	0	0	0
68.75°	1	1	1	1	0	0	0	0	0	0	0
67.5°	1	1	1	1	1	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	0	0	0	0	0
65°	1	1	1	1	1	1	1	0	0	0	0
63.75°	1	1	1	1	1	1	1	0	0	0	0
62.5°	1	1	1	1	1	1	1	1	0	0	0
61.25°	1	1	1	1	1	1	1	1	1	0	0
60°	1	1	1	1	1	1	1	1	1	0	0
58.75°	1	1	1	1	1	1	1	1	1	1	0
57.5°	1	1	1	1	1	1	1	1	1	1	0
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	1	1	1	1	1	1	1	1	1	1
46.25°	2	1	1	1	1	1	1	1	1	1	1
45°	2	2	1	1	1	1	1	1	1	1	1
43.75°	2	2	1	1	1	1	1	1	1	1	1
42.5°	2	2	2	1	1	1	1	1	1	1	1
41.25°	2	2	2	1	1	1	1	1	1	1	1
40°	2	2	2	2	1	1	1	1	1	1	1
38.75°	2	2	2	2	1	1	1	1	1	1	1
37.5°	2	2	2	2	1	1	1	1	1	1	1
36.25°	2	2	2	2	2	1	1	1	1	1	1
35°	2	2	2	2	2	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	2	2	2	2	2	1	1	1	1	1	1
32.5°	2	2	2	2	2	2	1	1	1	1	1
31.25°	2	2	2	2	2	2	1	1	1	1	1
30°	2	2	2	2	2	2	1	1	1	1	1
28.75°	2	2	2	2	2	2	1	1	1	1	1
27.5°	2	2	2	2	2	2	2	1	1	1	1
26.25°	2	2	2	2	2	2	2	1	1	1	1
25°	2	2	2	2	2	2	2	1	1	1	1
23.75°	2	2	2	2	2	2	2	1	1	1	1
22.5°	3	2	2	2	2	2	2	1	1	1	1
21.25°	3	2	2	2	2	2	2	1	1	1	1
20°	3	2	2	2	2	2	2	1	1	1	1
18.75°	3	2	2	2	2	2	2	2	1	1	1
17.5°	3	2	2	2	2	2	2	2	1	1	1
16.25°	3	3	2	2	2	2	2	2	1	1	1
15°	3	3	2	2	2	2	2	2	1	1	1
13.75°	3	3	2	2	2	2	2	2	1	1	1
12.5°	3	3	2	2	2	2	2	2	1	1	1
11.25°	3	3	2	2	2	2	2	2	1	1	1
10°	3	3	2	2	2	2	2	2	1	1	1
8.75°	3	3	2	2	2	2	2	2	1	1	1
7.5°	3	3	2	2	2	2	2	2	1	1	1
6.25°	3	3	2	2	2	2	2	2	1	1	1
5°	3	3	2	2	2	2	2	2	1	1	1
3.75°	3	3	2	2	2	2	2	2	1	1	1
2.5°	3	3	2	2	2	2	2	2	1	1	1
1.25°	3	3	2	2	2	2	2	2	1	1	1
0°	3	3	3	2	2	2	2	2	2	1	1
-1.25°	3	3	2	2	2	2	2	2	1	1	1
-2.5°	3	3	2	2	2	2	2	2	1	1	1
-3.75°	3	3	2	2	2	2	2	2	1	1	1
-5°	3	3	2	2	2	2	2	2	1	1	1
-6.25°	3	3	2	2	2	2	2	2	1	1	1
-7.5°	3	3	2	2	2	2	2	2	1	1	1
-8.75°	3	3	2	2	2	2	2	2	1	1	1
-10°	3	3	2	2	2	2	2	2	1	1	1
-11.25°	3	3	2	2	2	2	2	2	1	1	1
-12.5°	3	3	2	2	2	2	2	2	1	1	1
-13.75°	3	3	2	2	2	2	2	2	1	1	1
-15°	3	3	2	2	2	2	2	2	1	1	1
-16.25°	3	3	2	2	2	2	2	2	1	1	1
-17.5°	3	2	2	2	2	2	2	2	1	1	1
-18.75°	3	2	2	2	2	2	2	2	1	1	1
-20°	3	2	2	2	2	2	2	1	1	1	1
-21.25°	3	2	2	2	2	2	2	1	1	1	1



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	3	2	2	2	2	2	2	1	1	1	1
-23.75°	2	2	2	2	2	2	2	1	1	1	1
-25°	2	2	2	2	2	2	2	1	1	1	1
-26.25°	2	2	2	2	2	2	2	1	1	1	1
-27.5°	2	2	2	2	2	2	2	1	1	1	1
-28.75°	2	2	2	2	2	2	1	1	1	1	1
-30°	2	2	2	2	2	2	1	1	1	1	1
-31.25°	2	2	2	2	2	2	1	1	1	1	1
-32.5°	2	2	2	2	2	2	1	1	1	1	1
-33.75°	2	2	2	2	2	1	1	1	1	1	1
-35°	2	2	2	2	2	1	1	1	1	1	1
-36.25°	2	2	2	2	2	1	1	1	1	1	1
-37.5°	2	2	2	2	1	1	1	1	1	1	1
-38.75°	2	2	2	2	1	1	1	1	1	1	1
-40°	2	2	2	2	1	1	1	1	1	1	1
-41.25°	2	2	2	1	1	1	1	1	1	1	1
-42.5°	2	2	2	1	1	1	1	1	1	1	1
-43.75°	2	2	1	1	1	1	1	1	1	1	1
-45°	2	2	1	1	1	1	1	1	1	1	1
-46.25°	2	1	1	1	1	1	1	1	1	1	1
-47.5°	2	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	0
-58.75°	1	1	1	1	1	1	1	1	1	1	0
-60°	1	1	1	1	1	1	1	1	1	0	0
-61.25°	1	1	1	1	1	1	1	1	1	0	0
-62.5°	1	1	1	1	1	1	1	1	0	0	0
-63.75°	1	1	1	1	1	1	1	0	0	0	0
-65°	1	1	1	1	1	1	1	0	0	0	0
-66.25°	1	1	1	1	1	1	0	0	0	0	0
-67.5°	1	1	1	1	1	0	0	0	0	0	0
-68.75°	1	1	1	1	0	0	0	0	0	0	0
-70°	1	1	0	0	0	0	0	0	0	0	0
-71.25°	1	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	1	0	0	0	0	0	0	0	0	0	0
52.5°	1	0	0	0	0	0	0	0	0	0	0
51.25°	1	0	0	0	0	0	0	0	0	0	0
50°	1	1	0	0	0	0	0	0	0	0	0
48.75°	1	1	0	0	0	0	0	0	0	0	0
47.5°	1	1	0	0	0	0	0	0	0	0	0
46.25°	1	1	0	0	0	0	0	0	0	0	0
45°	1	1	1	0	0	0	0	0	0	0	0
43.75°	1	1	1	0	0	0	0	0	0	0	0
42.5°	1	1	1	0	0	0	0	0	0	0	0
41.25°	1	1	1	0	0	0	0	0	0	0	0
40°	1	1	1	0	0	0	0	0	0	0	0
38.75°	1	1	1	1	0	0	0	0	0	0	0
37.5°	1	1	1	1	0	0	0	0	0	0	0
36.25°	1	1	1	1	0	0	0	0	0	0	0
35°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	1	1	1	1	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
31.25°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
28.75°	1	1	1	1	1	0	0	0	0	0	0
27.5°	1	1	1	1	1	0	0	0	0	0	0
26.25°	1	1	1	1	1	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
23.75°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	0	0	0	0	0	0
21.25°	1	1	1	1	1	0	0	0	0	0	0
20°	1	1	1	1	1	0	0	0	0	0	0
18.75°	1	1	1	1	1	0	0	0	0	0	0
17.5°	1	1	1	1	1	0	0	0	0	0	0
16.25°	1	1	1	1	1	0	0	0	0	0	0
15°	1	1	1	1	1	0	0	0	0	0	0
13.75°	1	1	1	1	1	0	0	0	0	0	0
12.5°	1	1	1	1	1	0	0	0	0	0	0
11.25°	1	1	1	1	1	0	0	0	0	0	0
10°	1	1	1	1	1	0	0	0	0	0	0
8.75°	1	1	1	1	1	0	0	0	0	0	0
7.5°	1	1	1	1	1	0	0	0	0	0	0
6.25°	1	1	1	1	1	0	0	0	0	0	0
5°	1	1	1	1	1	0	0	0	0	0	0
3.75°	1	1	1	1	1	0	0	0	0	0	0
2.5°	1	1	1	1	1	0	0	0	0	0	0
1.25°	1	1	1	1	1	0	0	0	0	0	0
0°	1	1	1	1	1	1	0	0	0	0	0
-1.25°	1	1	1	1	1	0	0	0	0	0	0
-2.5°	1	1	1	1	1	0	0	0	0	0	0
-3.75°	1	1	1	1	1	0	0	0	0	0	0
-5°	1	1	1	1	1	0	0	0	0	0	0
-6.25°	1	1	1	1	1	0	0	0	0	0	0
-7.5°	1	1	1	1	1	0	0	0	0	0	0
-8.75°	1	1	1	1	1	0	0	0	0	0	0
-10°	1	1	1	1	1	0	0	0	0	0	0
-11.25°	1	1	1	1	1	0	0	0	0	0	0
-12.5°	1	1	1	1	1	0	0	0	0	0	0
-13.75°	1	1	1	1	1	0	0	0	0	0	0
-15°	1	1	1	1	1	0	0	0	0	0	0
-16.25°	1	1	1	1	1	0	0	0	0	0	0
-17.5°	1	1	1	1	1	0	0	0	0	0	0
-18.75°	1	1	1	1	1	0	0	0	0	0	0
-20°	1	1	1	1	1	0	0	0	0	0	0
-21.25°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	1	1	1	1	0	0	0	0	0	0
-23.75°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-26.25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	1	0	0	0	0	0	0
-28.75°	1	1	1	1	1	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-31.25°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-33.75°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	1	0	0	0	0	0	0	0
-36.25°	1	1	1	1	0	0	0	0	0	0	0
-37.5°	1	1	1	1	0	0	0	0	0	0	0
-38.75°	1	1	1	1	0	0	0	0	0	0	0
-40°	1	1	1	0	0	0	0	0	0	0	0
-41.25°	1	1	1	0	0	0	0	0	0	0	0
-42.5°	1	1	1	0	0	0	0	0	0	0	0
-43.75°	1	1	1	0	0	0	0	0	0	0	0
-45°	1	1	1	0	0	0	0	0	0	0	0
-46.25°	1	1	0	0	0	0	0	0	0	0	0
-47.5°	1	1	0	0	0	0	0	0	0	0	0
-48.75°	1	1	0	0	0	0	0	0	0	0	0
-50°	1	1	0	0	0	0	0	0	0	0	0
-51.25°	1	0	0	0	0	0	0	0	0	0	0
-52.5°	1	0	0	0	0	0	0	0	0	0	0
-53.75°	1	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-44 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-SS-8LED4036-12-CS-DIFF

CANDELA DISTRIBUTION (continued):

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)