

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-SS-8LED4036-12-CS**

Test Date: 04/05/18

**Test Information**


Test Method: LM-79-08  
Report Number: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-9)  
Test Lab: INNOVATION CENTER(G2)  
Test Date: 04/05/18  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-SS-8LED4036-12-CS  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD SILVER  
Light Source: (1) SORAA 4000K 90 CRI LED  
SM16-07-36D-940-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

**Summary**

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	371.4 lumens	Max Intensity:	1080 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	48.9 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	35.1°H x 35.1°V	Field Angle (10%):	52.2°H x 52.2°V
Beam Lumens:	238.8 lumens	Field Lumens:	338.2 lumens
Beam Efficiency:	64.3%	Field Efficiency:	91.0%
Input Watts (W):	7.6		
Input Voltage (V):	12.0		
Input Current (A <sub>in</sub> ):	0.667		
Voltage Rise (V):	NR		
Power Factor:	0.9902		
Total Harmonic Distortion (THDi):	27.4%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	3 HR		
Ambient Temperature (°C):	25.3		
Test Distance:	25 FT		

REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4036-12-CS

### Iso-Candela Plot






REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

### Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	
50	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.1	0.0	0.0	0.0
40		0.0	0.0	0.1	0.1	0.2	0.3	0.5	0.5	0.3	0.2	0.1	0.1	0.0	0.0	
30	0.0	0.0	0.0	0.1	0.2	0.5	1.9	4.4	4.4	1.9	0.5	0.2	0.1	0.0	0.0	0.0
20		0.0	0.1	0.1	0.3	1.8	9.6	18.8	18.8	9.6	1.8	0.3	0.1	0.1	0.0	
10	0.0	0.0	0.1	0.1	0.4	4.0	18.2	29.8	29.8	18.2	4.0	0.4	0.1	0.1	0.0	0.0
0		0.0	0.1	0.1	0.4	4.0	18.2	29.8	29.8	18.2	4.0	0.4	0.1	0.1	0.0	
-10	0.0	0.0	0.1	0.1	0.3	1.8	9.6	18.8	18.8	9.6	1.8	0.3	0.1	0.1	0.0	0.0
-20		0.0	0.0	0.1	0.2	0.5	1.9	4.4	4.4	1.9	0.5	0.2	0.1	0.0	0.0	
-30	0.0	0.0	0.0	0.1	0.1	0.2	0.3	0.5	0.5	0.3	0.2	0.1	0.1	0.0	0.0	0.0
-40		0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1	0.1	0.1	0.0	0.0	
-50	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0


REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4036-12-CS

### Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

### Luminous Intensity Plot



**Beam:**  
 H Angle: 35.1°  
 V Angle: 35.1°  
 Lumens: 238.8  
 Efficiency: 64.3%

**Field:**  
 H Angle: 52.2°  
 V Angle: 52.2°  
 Lumens: 338.2  
 Efficiency: 91.0%

**Spill:**  
 Lumens: 33.2  
 Efficiency: 9.0%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
21.25°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
18.75°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
16.25°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
13.75°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
11.25°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
8.75°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
6.25°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
3.75°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
1.25°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-1.25°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-3.75°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-6.25°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-8.75°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-11.25°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-13.75°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-16.25°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-18.75°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0
-21.25°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-90°	-88.75°	-87.5°	-86.25°	-85°	-83.75°	-82.5°	-81.25°	-80°	-78.75°	-77.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	1
55°	0	0	0	0	0	0	0	0	0	1	1
53.75°	0	0	0	0	0	0	0	0	1	1	1
52.5°	0	0	0	0	0	0	0	0	1	1	1
51.25°	0	0	0	0	0	0	0	1	1	1	1
50°	0	0	0	0	0	0	0	1	1	1	1
48.75°	0	0	0	0	0	0	1	1	1	1	1
47.5°	0	0	0	0	0	0	1	1	1	1	1
46.25°	0	0	0	0	0	0	1	1	1	1	1
45°	0	0	0	0	0	1	1	1	1	1	1
43.75°	0	0	0	0	0	1	1	1	1	1	1
42.5°	0	0	0	0	0	1	1	1	1	1	1
41.25°	0	0	0	0	1	1	1	1	1	1	1
40°	0	0	0	0	1	1	1	1	1	1	1
38.75°	0	0	0	0	1	1	1	1	1	1	1
37.5°	0	0	0	1	1	1	1	1	1	1	1
36.25°	0	0	0	1	1	1	1	1	1	1	1
35°	0	0	0	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
33.75°	0	0	0	1	1	1	1	1	1	1	1
32.5°	0	0	0	1	1	1	1	1	1	1	1
31.25°	0	0	1	1	1	1	1	1	1	1	1
30°	0	0	1	1	1	1	1	1	1	1	1
28.75°	0	0	1	1	1	1	1	1	1	1	1
27.5°	0	0	1	1	1	1	1	1	1	1	1
26.25°	0	0	1	1	1	1	1	1	1	1	1
25°	0	0	1	1	1	1	1	1	1	1	1
23.75°	0	0	1	1	1	1	1	1	1	1	1
22.5°	0	1	1	1	1	1	1	1	1	1	1
21.25°	0	1	1	1	1	1	1	1	1	1	1
20°	0	1	1	1	1	1	1	1	1	1	1
18.75°	0	1	1	1	1	1	1	1	1	1	1
17.5°	0	1	1	1	1	1	1	1	1	1	1
16.25°	0	1	1	1	1	1	1	1	1	1	1
15°	0	1	1	1	1	1	1	1	1	1	1
13.75°	0	1	1	1	1	1	1	1	1	1	1
12.5°	0	1	1	1	1	1	1	1	1	1	1
11.25°	0	1	1	1	1	1	1	1	1	1	1
10°	0	1	1	1	1	1	1	1	1	1	1
8.75°	0	1	1	1	1	1	1	1	1	1	1
7.5°	0	1	1	1	1	1	1	1	1	1	1
6.25°	0	1	1	1	1	1	1	1	1	1	1
5°	0	1	1	1	1	1	1	1	1	1	1
3.75°	0	1	1	1	1	1	1	1	1	1	1
2.5°	0	1	1	1	1	1	1	1	1	1	1
1.25°	0	1	1	1	1	1	1	1	1	1	1
0°	1	1	1	1	1	1	1	1	1	1	2
-1.25°	0	1	1	1	1	1	1	1	1	1	1
-2.5°	0	1	1	1	1	1	1	1	1	1	1
-3.75°	0	1	1	1	1	1	1	1	1	1	1
-5°	0	1	1	1	1	1	1	1	1	1	1
-6.25°	0	1	1	1	1	1	1	1	1	1	1
-7.5°	0	1	1	1	1	1	1	1	1	1	1
-8.75°	0	1	1	1	1	1	1	1	1	1	1
-10°	0	1	1	1	1	1	1	1	1	1	1
-11.25°	0	1	1	1	1	1	1	1	1	1	1
-12.5°	0	1	1	1	1	1	1	1	1	1	1
-13.75°	0	1	1	1	1	1	1	1	1	1	1
-15°	0	1	1	1	1	1	1	1	1	1	1
-16.25°	0	1	1	1	1	1	1	1	1	1	1
-17.5°	0	1	1	1	1	1	1	1	1	1	1
-18.75°	0	1	1	1	1	1	1	1	1	1	1
-20°	0	1	1	1	1	1	1	1	1	1	1
-21.25°	0	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-22.5°	0	1	1	1	1	1	1	1	1	1	1
-23.75°	0	0	1	1	1	1	1	1	1	1	1
-25°	0	0	1	1	1	1	1	1	1	1	1
-26.25°	0	0	1	1	1	1	1	1	1	1	1
-27.5°	0	0	1	1	1	1	1	1	1	1	1
-28.75°	0	0	1	1	1	1	1	1	1	1	1
-30°	0	0	1	1	1	1	1	1	1	1	1
-31.25°	0	0	1	1	1	1	1	1	1	1	1
-32.5°	0	0	0	1	1	1	1	1	1	1	1
-33.75°	0	0	0	1	1	1	1	1	1	1	1
-35°	0	0	0	1	1	1	1	1	1	1	1
-36.25°	0	0	0	1	1	1	1	1	1	1	1
-37.5°	0	0	0	1	1	1	1	1	1	1	1
-38.75°	0	0	0	0	1	1	1	1	1	1	1
-40°	0	0	0	0	1	1	1	1	1	1	1
-41.25°	0	0	0	0	1	1	1	1	1	1	1
-42.5°	0	0	0	0	0	1	1	1	1	1	1
-43.75°	0	0	0	0	0	1	1	1	1	1	1
-45°	0	0	0	0	0	1	1	1	1	1	1
-46.25°	0	0	0	0	0	0	1	1	1	1	1
-47.5°	0	0	0	0	0	0	1	1	1	1	1
-48.75°	0	0	0	0	0	0	1	1	1	1	1
-50°	0	0	0	0	0	0	0	1	1	1	1
-51.25°	0	0	0	0	0	0	0	1	1	1	1
-52.5°	0	0	0	0	0	0	0	0	1	1	1
-53.75°	0	0	0	0	0	0	0	0	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-56.25°	0	0	0	0	0	0	0	0	0	0	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-76.25°	-75°	-73.75°	-72.5°	-71.25°	-70°	-68.75°	-67.5°	-66.25°	-65°	-63.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	1	1
66.25°	0	0	0	0	0	0	0	1	1	1	1
65°	0	0	0	0	0	0	1	1	1	1	1
63.75°	0	0	0	0	0	1	1	1	1	1	1
62.5°	0	0	0	1	1	1	1	1	1	1	1
61.25°	0	0	1	1	1	1	1	1	1	1	1
60°	0	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
46.25°	1	1	1	1	1	1	1	1	1	1	2
45°	1	1	1	1	1	1	1	1	1	2	2
43.75°	1	1	1	1	1	1	1	1	1	2	2
42.5°	1	1	1	1	1	1	1	1	2	2	2
41.25°	1	1	1	1	1	1	1	2	2	2	2
40°	1	1	1	1	1	1	1	2	2	2	2
38.75°	1	1	1	1	1	1	2	2	2	2	2
37.5°	1	1	1	1	1	1	2	2	2	2	2
36.25°	1	1	1	1	1	2	2	2	2	2	2
35°	1	1	1	1	1	2	2	2	2	2	3



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
33.75°	1	1	1	1	2	2	2	2	2	3	3
32.5°	1	1	1	1	2	2	2	2	2	3	3
31.25°	1	1	1	2	2	2	2	2	3	3	3
30°	1	1	1	2	2	2	2	2	3	3	4
28.75°	1	1	1	2	2	2	2	2	3	3	4
27.5°	1	1	2	2	2	2	2	3	3	3	4
26.25°	1	1	2	2	2	2	2	3	3	4	4
25°	1	1	2	2	2	2	3	3	3	4	4
23.75°	1	1	2	2	2	2	3	3	4	4	4
22.5°	1	2	2	2	2	2	3	3	4	4	4
21.25°	1	2	2	2	2	2	3	3	4	4	4
20°	1	2	2	2	2	3	3	4	4	4	4
18.75°	1	2	2	2	2	3	3	4	4	4	4
17.5°	1	2	2	2	2	3	3	4	4	4	4
16.25°	2	2	2	2	2	3	3	4	4	4	4
15°	2	2	2	2	3	3	3	4	4	4	4
13.75°	2	2	2	2	3	3	4	4	4	4	4
12.5°	2	2	2	2	3	3	4	4	4	4	4
11.25°	2	2	2	2	3	3	4	4	4	4	4
10°	2	2	2	2	3	3	4	4	4	4	4
8.75°	2	2	2	2	3	3	4	4	4	4	4
7.5°	2	2	2	2	3	3	4	4	4	4	4
6.25°	2	2	2	2	3	3	4	4	4	4	4
5°	2	2	2	2	3	3	4	4	4	4	4
3.75°	2	2	2	2	3	3	4	4	4	4	4
2.5°	2	2	2	2	3	3	4	4	4	4	4
1.25°	2	2	2	2	3	3	4	4	4	4	4
0°	2	2	2	3	3	4	4	4	4	4	4
-1.25°	2	2	2	2	3	3	4	4	4	4	4
-2.5°	2	2	2	2	3	3	4	4	4	4	4
-3.75°	2	2	2	2	3	3	4	4	4	4	4
-5°	2	2	2	2	3	3	4	4	4	4	4
-6.25°	2	2	2	2	3	3	4	4	4	4	4
-7.5°	2	2	2	2	3	3	4	4	4	4	4
-8.75°	2	2	2	2	3	3	4	4	4	4	4
-10°	2	2	2	2	3	3	4	4	4	4	4
-11.25°	2	2	2	2	3	3	4	4	4	4	4
-12.5°	2	2	2	2	3	3	4	4	4	4	4
-13.75°	2	2	2	2	3	3	4	4	4	4	4
-15°	2	2	2	2	3	3	3	4	4	4	4
-16.25°	2	2	2	2	2	3	3	4	4	4	4
-17.5°	1	2	2	2	2	3	3	4	4	4	4
-18.75°	1	2	2	2	2	3	3	4	4	4	4
-20°	1	2	2	2	2	3	3	4	4	4	4
-21.25°	1	2	2	2	2	2	3	3	4	4	4





REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-22.5°	1	2	2	2	2	2	3	3	4	4	4
-23.75°	1	1	2	2	2	2	3	3	4	4	4
-25°	1	1	2	2	2	2	3	3	3	4	4
-26.25°	1	1	2	2	2	2	2	3	3	4	4
-27.5°	1	1	2	2	2	2	2	3	3	3	4
-28.75°	1	1	1	2	2	2	2	2	3	3	4
-30°	1	1	1	2	2	2	2	2	3	3	4
-31.25°	1	1	1	2	2	2	2	2	3	3	3
-32.5°	1	1	1	1	2	2	2	2	2	3	3
-33.75°	1	1	1	1	2	2	2	2	2	3	3
-35°	1	1	1	1	1	2	2	2	2	2	3
-36.25°	1	1	1	1	1	2	2	2	2	2	2
-37.5°	1	1	1	1	1	1	2	2	2	2	2
-38.75°	1	1	1	1	1	1	2	2	2	2	2
-40°	1	1	1	1	1	1	1	2	2	2	2
-41.25°	1	1	1	1	1	1	1	2	2	2	2
-42.5°	1	1	1	1	1	1	1	1	2	2	2
-43.75°	1	1	1	1	1	1	1	1	1	2	2
-45°	1	1	1	1	1	1	1	1	1	2	2
-46.25°	1	1	1	1	1	1	1	1	1	1	2
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-48.75°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	0	1	1	1	1	1	1	1	1	1	1
-61.25°	0	0	1	1	1	1	1	1	1	1	1
-62.5°	0	0	0	1	1	1	1	1	1	1	1
-63.75°	0	0	0	0	0	1	1	1	1	1	1
-65°	0	0	0	0	0	0	1	1	1	1	1
-66.25°	0	0	0	0	0	0	0	1	1	1	1
-67.5°	0	0	0	0	0	0	0	0	0	1	1
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-61.25°	-60°	-58.75°	-57.5°	-56.25°	-55°	-53.75°	-52.5°	-51.25°	-50°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	1	1
71.25°	0	0	0	0	0	0	1	1	1	1	1
70°	0	0	0	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	2
55°	1	1	1	1	1	1	1	1	2	2	2
53.75°	1	1	1	1	1	1	2	2	2	2	2
52.5°	1	1	1	1	1	2	2	2	2	2	2
51.25°	1	1	1	2	2	2	2	2	2	2	2
50°	1	1	2	2	2	2	2	2	2	2	2
48.75°	1	2	2	2	2	2	2	2	2	3	3
47.5°	2	2	2	2	2	2	2	2	3	3	3
46.25°	2	2	2	2	2	2	3	3	3	3	4
45°	2	2	2	2	2	3	3	3	3	4	4
43.75°	2	2	2	2	3	3	3	3	4	4	4
42.5°	2	2	2	3	3	3	3	4	4	4	4
41.25°	2	2	3	3	3	3	4	4	4	4	4
40°	2	2	3	3	3	4	4	4	4	4	4
38.75°	2	3	3	3	4	4	4	4	4	4	4
37.5°	3	3	3	4	4	4	4	4	4	4	4
36.25°	3	3	4	4	4	4	4	4	4	4	4
35°	3	3	4	4	4	4	4	4	4	4	5



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
33.75°	3	4	4	4	4	4	4	4	4	5	5
32.5°	4	4	4	4	4	4	4	4	4	5	5
31.25°	4	4	4	4	4	4	4	4	5	5	5
30°	4	4	4	4	4	4	4	5	5	5	5
28.75°	4	4	4	4	4	4	4	5	5	5	5
27.5°	4	4	4	4	4	4	5	5	5	5	5
26.25°	4	4	4	4	4	5	5	5	5	5	6
25°	4	4	4	4	4	5	5	5	5	5	6
23.75°	4	4	4	4	5	5	5	5	5	6	6
22.5°	4	4	4	4	5	5	5	5	5	6	7
21.25°	4	4	4	4	5	5	5	5	6	6	7
20°	4	4	4	5	5	5	5	5	6	7	7
18.75°	4	4	4	5	5	5	5	6	6	7	8
17.5°	4	4	5	5	5	5	5	6	6	7	8
16.25°	4	4	5	5	5	5	5	6	7	8	9
15°	4	4	5	5	5	5	6	6	7	8	9
13.75°	4	4	5	5	5	5	6	6	7	8	10
12.5°	4	5	5	5	5	5	6	7	8	9	10
11.25°	4	5	5	5	5	6	6	7	8	9	11
10°	4	5	5	5	5	6	6	7	8	10	11
8.75°	4	5	5	5	5	6	6	7	9	10	12
7.5°	4	5	5	5	5	6	7	8	9	10	12
6.25°	4	5	5	5	5	6	7	8	9	10	12
5°	4	5	5	5	5	6	7	8	9	11	13
3.75°	4	5	5	5	5	6	7	8	9	11	13
2.5°	4	5	5	5	5	6	7	8	9	11	13
1.25°	4	5	5	5	5	6	7	8	9	11	13
0°	5	5	5	5	6	6	7	8	10	11	13
-1.25°	4	5	5	5	5	6	7	8	9	11	13
-2.5°	4	5	5	5	5	6	7	8	9	11	13
-3.75°	4	5	5	5	5	6	7	8	9	11	13
-5°	4	5	5	5	5	6	7	8	9	11	13
-6.25°	4	5	5	5	5	6	7	8	9	10	12
-7.5°	4	5	5	5	5	6	7	8	9	10	12
-8.75°	4	5	5	5	5	6	6	7	9	10	12
-10°	4	5	5	5	5	6	6	7	8	10	11
-11.25°	4	5	5	5	5	6	6	7	8	9	11
-12.5°	4	5	5	5	5	5	6	7	8	9	10
-13.75°	4	4	5	5	5	5	6	6	7	8	10
-15°	4	4	5	5	5	5	6	6	7	8	9
-16.25°	4	4	5	5	5	5	5	6	7	8	9
-17.5°	4	4	5	5	5	5	5	6	6	7	8
-18.75°	4	4	4	5	5	5	5	6	6	7	8
-20°	4	4	4	5	5	5	5	5	6	7	7
-21.25°	4	4	4	4	5	5	5	5	6	6	7



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-22.5°	4	4	4	4	5	5	5	5	5	6	7
-23.75°	4	4	4	4	5	5	5	5	5	6	6
-25°	4	4	4	4	4	5	5	5	5	5	6
-26.25°	4	4	4	4	4	5	5	5	5	5	6
-27.5°	4	4	4	4	4	4	5	5	5	5	5
-28.75°	4	4	4	4	4	4	4	5	5	5	5
-30°	4	4	4	4	4	4	4	5	5	5	5
-31.25°	4	4	4	4	4	4	4	4	5	5	5
-32.5°	4	4	4	4	4	4	4	4	4	5	5
-33.75°	3	4	4	4	4	4	4	4	4	5	5
-35°	3	3	4	4	4	4	4	4	4	4	5
-36.25°	3	3	4	4	4	4	4	4	4	4	4
-37.5°	3	3	3	4	4	4	4	4	4	4	4
-38.75°	2	3	3	3	4	4	4	4	4	4	4
-40°	2	2	3	3	3	4	4	4	4	4	4
-41.25°	2	2	3	3	3	3	4	4	4	4	4
-42.5°	2	2	2	3	3	3	3	4	4	4	4
-43.75°	2	2	2	2	3	3	3	3	4	4	4
-45°	2	2	2	2	2	3	3	3	3	4	4
-46.25°	2	2	2	2	2	2	3	3	3	3	4
-47.5°	2	2	2	2	2	2	2	2	3	3	3
-48.75°	1	2	2	2	2	2	2	2	2	3	3
-50°	1	1	2	2	2	2	2	2	2	2	2
-51.25°	1	1	1	2	2	2	2	2	2	2	2
-52.5°	1	1	1	1	1	2	2	2	2	2	2
-53.75°	1	1	1	1	1	1	2	2	2	2	2
-55°	1	1	1	1	1	1	1	1	2	2	2
-56.25°	1	1	1	1	1	1	1	1	1	1	2
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	0	0	0	1	1	1	1	1	1	1	1
-71.25°	0	0	0	0	0	0	1	1	1	1	1
-72.5°	0	0	0	0	0	0	0	0	0	1	1
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-48.75°	-47.5°	-46.25°	-45°	-43.75°	-42.5°	-41.25°	-40°	-38.75°	-37.5°	-36.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	1
73.75°	0	0	0	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	2
60°	1	1	1	1	1	1	2	2	2	2	2
58.75°	1	1	1	2	2	2	2	2	2	2	2
57.5°	1	2	2	2	2	2	2	2	2	2	2
56.25°	2	2	2	2	2	2	2	2	2	2	2
55°	2	2	2	2	2	2	2	2	3	3	3
53.75°	2	2	2	2	2	2	3	3	3	3	3
52.5°	2	2	2	3	3	3	3	3	3	4	4
51.25°	2	3	3	3	3	3	3	4	4	4	4
50°	3	3	3	3	4	4	4	4	4	4	4
48.75°	3	3	4	4	4	4	4	4	4	4	4
47.5°	3	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	4	4	4	4	4	4	4	4	4	4	4
43.75°	4	4	4	4	4	4	4	4	4	5	5
42.5°	4	4	4	4	4	4	4	5	5	5	5
41.25°	4	4	4	4	4	4	5	5	5	5	5
40°	4	4	4	4	5	5	5	5	5	5	5
38.75°	4	4	4	5	5	5	5	5	5	5	5
37.5°	4	5	5	5	5	5	5	5	5	6	6
36.25°	5	5	5	5	5	5	5	6	6	6	7
35°	5	5	5	5	5	5	6	6	6	7	7



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
33.75°	5	5	5	5	5	6	6	7	7	8	8
32.5°	5	5	5	5	6	6	7	7	8	9	9
31.25°	5	5	5	6	6	7	7	8	9	10	11
30°	5	5	6	6	7	8	8	9	10	11	12
28.75°	5	6	6	7	8	8	9	10	11	12	14
27.5°	6	6	7	7	8	9	10	11	13	14	15
26.25°	6	7	7	8	9	10	11	13	14	16	18
25°	6	7	8	9	10	11	13	14	16	18	21
23.75°	7	8	9	10	11	12	14	16	18	21	24
22.5°	7	8	9	11	12	14	15	18	21	24	29
21.25°	8	9	10	12	13	15	17	20	24	29	34
20°	8	10	11	13	14	17	20	23	28	33	40
18.75°	9	10	12	13	15	19	22	27	32	38	48
17.5°	10	11	13	14	17	21	25	30	36	46	60
16.25°	10	12	14	16	19	22	28	34	42	55	73
15°	11	12	14	17	21	25	31	37	49	66	88
13.75°	11	13	15	19	22	28	34	44	58	78	104
12.5°	12	14	16	20	24	31	37	50	68	92	124
11.25°	13	14	18	21	27	33	42	57	78	105	143
10°	13	15	19	23	29	35	47	64	88	121	161
8.75°	13	16	20	24	31	38	52	72	99	136	177
7.5°	14	17	21	26	32	41	57	78	108	150	192
6.25°	14	17	21	27	34	44	61	85	119	161	206
5°	15	18	22	28	35	46	65	91	128	171	217
3.75°	15	18	22	29	36	48	68	96	135	178	228
2.5°	15	19	23	29	36	50	71	100	140	184	236
1.25°	15	19	23	30	37	51	72	102	143	188	240
0°	15	19	23	30	37	52	73	103	144	189	242
-1.25°	15	19	23	30	37	51	72	102	143	188	240
-2.5°	15	19	23	29	36	50	71	100	140	184	236
-3.75°	15	18	22	29	36	48	68	96	135	178	228
-5°	15	18	22	28	35	46	65	91	128	171	217
-6.25°	14	17	21	27	34	44	61	85	119	161	206
-7.5°	14	17	21	26	32	41	57	78	108	150	192
-8.75°	13	16	20	24	31	38	52	72	99	136	177
-10°	13	15	19	23	29	35	47	64	88	121	161
-11.25°	13	14	18	21	27	33	42	57	78	105	143
-12.5°	12	14	16	20	24	31	37	50	68	92	124
-13.75°	11	13	15	19	22	28	34	44	58	78	104
-15°	11	12	14	17	21	25	31	37	49	66	88
-16.25°	10	12	14	16	19	22	28	34	42	55	73
-17.5°	10	11	13	14	17	21	25	30	36	46	60
-18.75°	9	10	12	13	15	19	22	27	32	38	48
-20°	8	10	11	13	14	17	20	23	28	33	40
-21.25°	8	9	10	12	13	15	17	20	24	29	34





REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-22.5°	7	8	9	11	12	14	15	18	21	24	29
-23.75°	7	8	9	10	11	12	14	16	18	21	24
-25°	6	7	8	9	10	11	13	14	16	18	21
-26.25°	6	7	7	8	9	10	11	13	14	16	18
-27.5°	6	6	7	7	8	9	10	11	13	14	15
-28.75°	5	6	6	7	8	8	9	10	11	12	14
-30°	5	5	6	6	7	8	8	9	10	11	12
-31.25°	5	5	5	6	6	7	7	8	9	10	11
-32.5°	5	5	5	5	6	6	7	7	8	9	9
-33.75°	5	5	5	5	5	6	6	7	7	8	8
-35°	5	5	5	5	5	5	6	6	6	7	7
-36.25°	5	5	5	5	5	5	5	6	6	6	7
-37.5°	4	5	5	5	5	5	5	5	5	6	6
-38.75°	4	4	4	5	5	5	5	5	5	5	5
-40°	4	4	4	4	5	5	5	5	5	5	5
-41.25°	4	4	4	4	4	4	5	5	5	5	5
-42.5°	4	4	4	4	4	4	4	5	5	5	5
-43.75°	4	4	4	4	4	4	4	4	4	5	5
-45°	4	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	3	4	4	4	4	4	4	4	4	4	4
-48.75°	3	3	4	4	4	4	4	4	4	4	4
-50°	3	3	3	3	4	4	4	4	4	4	4
-51.25°	2	3	3	3	3	3	3	4	4	4	4
-52.5°	2	2	2	3	3	3	3	3	3	4	4
-53.75°	2	2	2	2	2	2	3	3	3	3	3
-55°	2	2	2	2	2	2	2	2	3	3	3
-56.25°	2	2	2	2	2	2	2	2	2	2	2
-57.5°	1	2	2	2	2	2	2	2	2	2	2
-58.75°	1	1	1	2	2	2	2	2	2	2	2
-60°	1	1	1	1	1	1	2	2	2	2	2
-61.25°	1	1	1	1	1	1	1	1	1	1	2
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	0	0	0	1	1	1	1	1	1	1	1
-75°	0	0	0	0	0	0	0	0	0	0	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-35°	-33.75°	-32.5°	-31.25°	-30°	-28.75°	-27.5°	-26.25°	-25°	-23.75°	-22.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	2	2	2	2	2	3	3	3	3	3	3
56.25°	2	3	3	3	3	3	3	3	3	3	3
55°	3	3	3	3	3	3	4	4	4	4	4
53.75°	3	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	5	5	5	5
46.25°	4	4	4	5	5	5	5	5	5	5	5
45°	4	5	5	5	5	5	5	5	5	5	5
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	5	5	5	5	5	5	5	5	6	6	6
41.25°	5	5	5	5	5	6	6	6	6	6	6
40°	5	5	6	6	6	6	6	7	7	7	7
38.75°	6	6	6	6	7	7	7	8	8	8	9
37.5°	6	7	7	7	8	8	8	9	9	10	10
36.25°	7	7	8	8	9	9	10	10	11	11	12
35°	8	8	9	10	10	11	11	12	13	13	13



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
33.75°	9	10	10	11	12	12	13	14	14	15	16
32.5°	10	11	12	13	14	14	15	16	18	19	20
31.25°	12	13	13	14	16	17	19	20	21	23	24
30°	13	14	15	17	19	21	22	24	27	29	31
28.75°	15	17	19	21	22	25	28	31	33	35	38
27.5°	17	20	22	25	28	31	34	37	42	47	52
26.25°	20	23	27	30	34	37	44	50	57	64	72
25°	24	28	32	36	42	49	58	68	78	88	99
23.75°	29	33	38	46	55	66	78	92	105	121	136
22.5°	34	40	48	60	73	88	104	124	143	161	177
21.25°	40	50	62	78	95	116	139	161	182	203	223
20°	50	63	80	100	124	151	175	201	226	253	279
18.75°	62	80	102	129	157	185	214	246	279	311	343
17.5°	78	100	129	160	190	223	260	299	338	376	413
16.25°	95	124	157	190	226	267	311	357	402	444	485
15°	116	151	185	223	267	315	366	417	467	513	556
13.75°	139	175	214	260	311	366	423	478	531	580	623
12.5°	161	201	246	299	357	417	478	537	592	640	681
11.25°	182	226	279	338	402	467	531	592	646	693	732
10°	203	253	311	376	444	513	580	640	693	738	779
8.75°	223	279	343	413	485	556	623	681	732	779	823
7.5°	243	303	372	445	521	593	658	716	768	817	860
6.25°	261	325	398	475	552	624	689	745	799	849	893
5°	277	345	421	499	578	649	712	770	825	875	921
3.75°	290	361	438	519	597	668	731	790	845	896	943
2.5°	299	372	451	533	611	682	744	804	860	911	959
1.25°	305	379	459	541	620	690	753	813	868	921	968
0°	307	381	462	544	623	693	755	816	871	924	971
-1.25°	305	379	459	541	620	690	753	813	868	921	968
-2.5°	299	372	451	533	611	682	744	804	860	911	959
-3.75°	290	361	438	519	597	668	731	790	845	896	943
-5°	277	345	421	499	578	649	712	770	825	875	921
-6.25°	261	325	398	475	552	624	689	745	799	849	893
-7.5°	243	303	372	445	521	593	658	716	768	817	860
-8.75°	223	279	343	413	485	556	623	681	732	779	823
-10°	203	253	311	376	444	513	580	640	693	738	779
-11.25°	182	226	279	338	402	467	531	592	646	693	732
-12.5°	161	201	246	299	357	417	478	537	592	640	681
-13.75°	139	175	214	260	311	366	423	478	531	580	623
-15°	116	151	185	223	267	315	366	417	467	513	556
-16.25°	95	124	157	190	226	267	311	357	402	444	485
-17.5°	78	100	129	160	190	223	260	299	338	376	413
-18.75°	62	80	102	129	157	185	214	246	279	311	343
-20°	50	63	80	100	124	151	175	201	226	253	279
-21.25°	40	50	62	78	95	116	139	161	182	203	223



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-22.5°	34	40	48	60	73	88	104	124	143	161	177
-23.75°	29	33	38	46	55	66	78	92	105	121	136
-25°	24	28	32	36	42	49	58	68	78	88	99
-26.25°	20	23	27	30	34	37	44	50	57	64	72
-27.5°	17	20	22	25	28	31	34	37	42	47	52
-28.75°	15	17	19	21	22	25	28	31	33	35	38
-30°	13	14	15	17	19	21	22	24	27	29	31
-31.25°	12	13	13	14	16	17	19	20	21	23	24
-32.5°	10	11	12	13	14	14	15	16	18	19	20
-33.75°	9	10	10	11	12	12	13	14	14	15	16
-35°	8	8	9	10	10	11	11	12	13	13	13
-36.25°	7	7	8	8	9	9	10	10	11	11	12
-37.5°	6	7	7	7	8	8	8	9	9	10	10
-38.75°	6	6	6	6	7	7	7	8	8	8	9
-40°	5	5	6	6	6	6	6	7	7	7	7
-41.25°	5	5	5	5	5	6	6	6	6	6	6
-42.5°	5	5	5	5	5	5	5	5	6	6	6
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	4	5	5	5	5	5	5	5	5	5	5
-46.25°	4	4	4	5	5	5	5	5	5	5	5
-47.5°	4	4	4	4	4	4	4	5	5	5	5
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	3	4	4	4	4	4	4	4	4	4	4
-55°	3	3	3	3	3	3	4	4	4	4	4
-56.25°	2	3	3	3	3	3	3	3	3	3	3
-57.5°	2	2	2	2	2	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	1	1	1	1	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-21.25°	-20°	-18.75°	-17.5°	-16.25°	-15°	-13.75°	-12.5°	-11.25°	-10°	-8.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	1	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	2	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	2	2
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	3	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	3	3	3
56.25°	3	3	3	3	3	3	4	3	3	3	3
55°	4	4	4	4	4	4	4	4	4	4	4
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	5	4	4	4	4
47.5°	5	5	5	5	5	5	5	5	5	5	5
46.25°	5	5	5	5	5	5	5	5	5	5	5
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	5	5	5	5	5	5	6	5	5	5	5
42.5°	6	6	6	6	6	6	6	6	6	6	6
41.25°	7	7	7	7	7	7	7	7	7	7	7
40°	8	8	8	8	8	8	8	8	8	8	8
38.75°	9	9	9	9	9	9	10	9	9	9	9
37.5°	10	10	11	11	11	11	11	11	11	11	11
36.25°	12	12	13	13	13	13	13	13	13	13	13
35°	14	14	15	15	15	15	15	15	15	15	15



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
33.75°	17	17	18	18	19	19	19	19	19	18	18
32.5°	21	21	22	22	23	23	23	23	23	22	22
31.25°	26	27	28	29	29	30	30	30	29	29	28
30°	32	34	35	36	36	37	37	37	36	36	35
28.75°	41	44	46	48	50	51	52	51	50	48	46
27.5°	57	61	65	68	71	72	73	72	71	68	65
26.25°	78	85	91	96	100	102	103	102	100	96	91
25°	108	119	128	135	140	143	144	143	140	135	128
23.75°	150	161	171	178	184	188	189	188	184	178	171
22.5°	192	206	217	228	236	240	242	240	236	228	217
21.25°	243	261	277	290	299	305	307	305	299	290	277
20°	303	325	345	361	372	379	381	379	372	361	345
18.75°	372	398	421	438	451	459	462	459	451	438	421
17.5°	445	475	499	519	533	541	544	541	533	519	499
16.25°	521	552	578	597	611	620	623	620	611	597	578
15°	593	624	649	668	682	690	693	690	682	668	649
13.75°	658	689	712	731	744	753	755	753	744	731	712
12.5°	716	745	770	790	804	813	816	813	804	790	770
11.25°	768	799	825	845	860	868	871	868	860	845	825
10°	817	849	875	896	911	921	924	921	911	896	875
8.75°	860	893	921	943	959	968	971	968	959	943	921
7.5°	899	934	963	983	999	1007	1010	1007	999	983	963
6.25°	934	969	996	1016	1029	1036	1038	1036	1029	1016	996
5°	963	996	1022	1038	1048	1053	1055	1053	1048	1038	1022
3.75°	983	1016	1038	1051	1059	1063	1064	1063	1059	1051	1038
2.5°	999	1029	1048	1059	1065	1068	1069	1068	1065	1059	1048
1.25°	1007	1036	1053	1063	1068	1071	1075	1071	1068	1063	1053
0°	1010	1038	1055	1064	1069	1075	1080	1075	1069	1064	1055
-1.25°	1007	1036	1053	1063	1068	1071	1075	1071	1068	1063	1053
-2.5°	999	1029	1048	1059	1065	1068	1069	1068	1065	1059	1048
-3.75°	983	1016	1038	1051	1059	1063	1064	1063	1059	1051	1038
-5°	963	996	1022	1038	1048	1053	1055	1053	1048	1038	1022
-6.25°	934	969	996	1016	1029	1036	1038	1036	1029	1016	996
-7.5°	899	934	963	983	999	1007	1010	1007	999	983	963
-8.75°	860	893	921	943	959	968	971	968	959	943	921
-10°	817	849	875	896	911	921	924	921	911	896	875
-11.25°	768	799	825	845	860	868	871	868	860	845	825
-12.5°	716	745	770	790	804	813	816	813	804	790	770
-13.75°	658	689	712	731	744	753	755	753	744	731	712
-15°	593	624	649	668	682	690	693	690	682	668	649
-16.25°	521	552	578	597	611	620	623	620	611	597	578
-17.5°	445	475	499	519	533	541	544	541	533	519	499
-18.75°	372	398	421	438	451	459	462	459	451	438	421
-20°	303	325	345	361	372	379	381	379	372	361	345
-21.25°	243	261	277	290	299	305	307	305	299	290	277





REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-22.5°	192	206	217	228	236	240	242	240	236	228	217
-23.75°	150	161	171	178	184	188	189	188	184	178	171
-25°	108	119	128	135	140	143	144	143	140	135	128
-26.25°	78	85	91	96	100	102	103	102	100	96	91
-27.5°	57	61	65	68	71	72	73	72	71	68	65
-28.75°	41	44	46	48	50	51	52	51	50	48	46
-30°	32	34	35	36	36	37	37	37	36	36	35
-31.25°	26	27	28	29	29	30	30	30	29	29	28
-32.5°	21	21	22	22	23	23	23	23	23	22	22
-33.75°	17	17	18	18	19	19	19	19	19	18	18
-35°	14	14	15	15	15	15	15	15	15	15	15
-36.25°	12	12	13	13	13	13	13	13	13	13	13
-37.5°	10	10	11	11	11	11	11	11	11	11	11
-38.75°	9	9	9	9	9	9	10	9	9	9	9
-40°	8	8	8	8	8	8	8	8	8	8	8
-41.25°	7	7	7	7	7	7	7	7	7	7	7
-42.5°	6	6	6	6	6	6	6	6	6	6	6
-43.75°	5	5	5	5	5	5	6	5	5	5	5
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	5	5
-47.5°	5	5	5	5	5	5	5	5	5	5	5
-48.75°	4	4	4	4	4	4	5	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	4	4	4	4
-56.25°	3	3	3	3	3	3	4	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	3	3	3
-58.75°	2	2	2	2	2	2	3	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	2	2
-63.75°	1	1	1	1	1	1	2	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	1	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-6.25°	-5°	-3.75°	-2.5°	-1.25°	0°	1.25°	2.5°	3.75°	5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	1	1	1	1	1	1	1	1
73.75°	1	1	1	1	1	1	1	1	1	1	1
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	2	2	2	2	2	2	2	2	2	1	1
61.25°	2	2	2	2	2	2	2	2	2	2	2
60°	2	2	2	2	2	2	2	2	2	2	2
58.75°	2	2	2	2	2	2	2	2	2	2	2
57.5°	3	3	3	3	3	3	3	3	2	2	2
56.25°	3	3	3	3	3	3	3	3	3	3	3
55°	4	4	4	4	4	4	4	3	3	3	3
53.75°	4	4	4	4	4	4	4	4	4	4	4
52.5°	4	4	4	4	4	4	4	4	4	4	4
51.25°	4	4	4	4	4	4	4	4	4	4	4
50°	4	4	4	4	4	4	4	4	4	4	4
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	5	5	5	5	5	5	4	4	4	4	4
46.25°	5	5	5	5	5	5	5	5	5	5	4
45°	5	5	5	5	5	5	5	5	5	5	5
43.75°	5	5	5	5	5	5	5	5	5	5	5
42.5°	6	6	6	6	6	5	5	5	5	5	5
41.25°	7	7	6	6	6	6	6	6	5	5	5
40°	8	8	7	7	7	7	6	6	6	6	6
38.75°	9	9	9	8	8	8	7	7	7	6	6
37.5°	10	10	10	10	9	9	8	8	8	7	7
36.25°	12	12	12	11	11	10	10	9	9	8	8
35°	14	14	13	13	13	12	11	11	10	10	9



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
33.75°	17	17	16	15	14	14	13	12	12	11	10
32.5°	21	21	20	19	18	16	15	14	14	13	12
31.25°	27	26	24	23	21	20	19	17	16	14	13
30°	34	32	31	29	27	24	22	21	19	17	15
28.75°	44	41	38	35	33	31	28	25	22	21	19
27.5°	61	57	52	47	42	37	34	31	28	25	22
26.25°	85	78	72	64	57	50	44	37	34	30	27
25°	119	108	99	88	78	68	58	49	42	36	32
23.75°	161	150	136	121	105	92	78	66	55	46	38
22.5°	206	192	177	161	143	124	104	88	73	60	48
21.25°	261	243	223	203	182	161	139	116	95	78	62
20°	325	303	279	253	226	201	175	151	124	100	80
18.75°	398	372	343	311	279	246	214	185	157	129	102
17.5°	475	445	413	376	338	299	260	223	190	160	129
16.25°	552	521	485	444	402	357	311	267	226	190	157
15°	624	593	556	513	467	417	366	315	267	223	185
13.75°	689	658	623	580	531	478	423	366	311	260	214
12.5°	745	716	681	640	592	537	478	417	357	299	246
11.25°	799	768	732	693	646	592	531	467	402	338	279
10°	849	817	779	738	693	640	580	513	444	376	311
8.75°	893	860	823	779	732	681	623	556	485	413	343
7.5°	934	899	860	817	768	716	658	593	521	445	372
6.25°	969	934	893	849	799	745	689	624	552	475	398
5°	996	963	921	875	825	770	712	649	578	499	421
3.75°	1016	983	943	896	845	790	731	668	597	519	438
2.5°	1029	999	959	911	860	804	744	682	611	533	451
1.25°	1036	1007	968	921	868	813	753	690	620	541	459
0°	1038	1010	971	924	871	816	755	693	623	544	462
-1.25°	1036	1007	968	921	868	813	753	690	620	541	459
-2.5°	1029	999	959	911	860	804	744	682	611	533	451
-3.75°	1016	983	943	896	845	790	731	668	597	519	438
-5°	996	963	921	875	825	770	712	649	578	499	421
-6.25°	969	934	893	849	799	745	689	624	552	475	398
-7.5°	934	899	860	817	768	716	658	593	521	445	372
-8.75°	893	860	823	779	732	681	623	556	485	413	343
-10°	849	817	779	738	693	640	580	513	444	376	311
-11.25°	799	768	732	693	646	592	531	467	402	338	279
-12.5°	745	716	681	640	592	537	478	417	357	299	246
-13.75°	689	658	623	580	531	478	423	366	311	260	214
-15°	624	593	556	513	467	417	366	315	267	223	185
-16.25°	552	521	485	444	402	357	311	267	226	190	157
-17.5°	475	445	413	376	338	299	260	223	190	160	129
-18.75°	398	372	343	311	279	246	214	185	157	129	102
-20°	325	303	279	253	226	201	175	151	124	100	80
-21.25°	261	243	223	203	182	161	139	116	95	78	62



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-22.5°	206	192	177	161	143	124	104	88	73	60	48
-23.75°	161	150	136	121	105	92	78	66	55	46	38
-25°	119	108	99	88	78	68	58	49	42	36	32
-26.25°	85	78	72	64	57	50	44	37	34	30	27
-27.5°	61	57	52	47	42	37	34	31	28	25	22
-28.75°	44	41	38	35	33	31	28	25	22	21	19
-30°	34	32	31	29	27	24	22	21	19	17	15
-31.25°	27	26	24	23	21	20	19	17	16	14	13
-32.5°	21	21	20	19	18	16	15	14	14	13	12
-33.75°	17	17	16	15	14	14	13	12	12	11	10
-35°	14	14	13	13	13	12	11	11	10	10	9
-36.25°	12	12	12	11	11	10	10	9	9	8	8
-37.5°	10	10	10	10	9	9	8	8	8	7	7
-38.75°	9	9	9	8	8	8	7	7	7	6	6
-40°	8	8	7	7	7	7	6	6	6	6	6
-41.25°	7	7	6	6	6	6	6	6	5	5	5
-42.5°	6	6	6	6	6	5	5	5	5	5	5
-43.75°	5	5	5	5	5	5	5	5	5	5	5
-45°	5	5	5	5	5	5	5	5	5	5	5
-46.25°	5	5	5	5	5	5	5	5	5	5	4
-47.5°	5	5	5	5	5	5	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	4	4
-51.25°	4	4	4	4	4	4	4	4	4	4	4
-52.5°	4	4	4	4	4	4	4	4	4	4	4
-53.75°	4	4	4	4	4	4	4	4	4	4	4
-55°	4	4	4	4	4	4	4	3	3	3	3
-56.25°	3	3	3	3	3	3	3	3	3	3	3
-57.5°	3	3	3	3	3	3	3	3	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	2
-60°	2	2	2	2	2	2	2	2	2	2	2
-61.25°	2	2	2	2	2	2	2	2	2	2	2
-62.5°	2	2	2	2	2	2	2	2	2	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	1
-75°	1	1	1	1	1	1	1	1	1	1	1
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	6.25°	7.5°	8.75°	10°	11.25°	12.5°	13.75°	15°	16.25°	17.5°	18.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	1	1	1	0	0	0	0	0	0	0	0
73.75°	1	1	1	1	1	1	1	1	1	1	0
72.5°	1	1	1	1	1	1	1	1	1	1	1
71.25°	1	1	1	1	1	1	1	1	1	1	1
70°	1	1	1	1	1	1	1	1	1	1	1
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	2	2	2	1	1	1	1	1	1	1	1
60°	2	2	2	2	2	2	2	1	1	1	1
58.75°	2	2	2	2	2	2	2	2	2	2	1
57.5°	2	2	2	2	2	2	2	2	2	2	2
56.25°	3	2	2	2	2	2	2	2	2	2	2
55°	3	3	3	3	3	2	2	2	2	2	2
53.75°	4	3	3	3	3	3	3	2	2	2	2
52.5°	4	4	4	4	3	3	3	3	3	3	2
51.25°	4	4	4	4	4	4	3	3	3	3	3
50°	4	4	4	4	4	4	4	4	4	3	3
48.75°	4	4	4	4	4	4	4	4	4	4	4
47.5°	4	4	4	4	4	4	4	4	4	4	4
46.25°	4	4	4	4	4	4	4	4	4	4	4
45°	5	4	4	4	4	4	4	4	4	4	4
43.75°	5	5	5	5	4	4	4	4	4	4	4
42.5°	5	5	5	5	5	5	4	4	4	4	4
41.25°	5	5	5	5	5	5	5	4	4	4	4
40°	5	5	5	5	5	5	5	5	5	4	4
38.75°	6	6	5	5	5	5	5	5	5	5	4
37.5°	7	6	6	6	5	5	5	5	5	5	5
36.25°	7	7	7	6	6	6	5	5	5	5	5
35°	8	8	7	7	6	6	6	5	5	5	5



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
33.75°	10	9	8	8	7	7	6	6	5	5	5
32.5°	11	10	9	9	8	7	7	6	6	5	5
31.25°	13	12	11	10	9	8	7	7	6	6	5
30°	14	13	12	11	10	9	8	8	7	6	6
28.75°	17	15	14	12	11	10	9	8	8	7	6
27.5°	20	17	15	14	13	11	10	9	8	7	7
26.25°	23	20	18	16	14	13	11	10	9	8	7
25°	28	24	21	18	16	14	13	11	10	9	8
23.75°	33	29	24	21	18	16	14	12	11	10	9
22.5°	40	34	29	24	21	18	15	14	12	11	9
21.25°	50	40	34	29	24	20	17	15	13	12	10
20°	63	50	40	33	28	23	20	17	14	13	11
18.75°	80	62	48	38	32	27	22	19	15	13	12
17.5°	100	78	60	46	36	30	25	21	17	14	13
16.25°	124	95	73	55	42	34	28	22	19	16	14
15°	151	116	88	66	49	37	31	25	21	17	14
13.75°	175	139	104	78	58	44	34	28	22	19	15
12.5°	201	161	124	92	68	50	37	31	24	20	16
11.25°	226	182	143	105	78	57	42	33	27	21	18
10°	253	203	161	121	88	64	47	35	29	23	19
8.75°	279	223	177	136	99	72	52	38	31	24	20
7.5°	303	243	192	150	108	78	57	41	32	26	21
6.25°	325	261	206	161	119	85	61	44	34	27	21
5°	345	277	217	171	128	91	65	46	35	28	22
3.75°	361	290	228	178	135	96	68	48	36	29	22
2.5°	372	299	236	184	140	100	71	50	36	29	23
1.25°	379	305	240	188	143	102	72	51	37	30	23
0°	381	307	242	189	144	103	73	52	37	30	23
-1.25°	379	305	240	188	143	102	72	51	37	30	23
-2.5°	372	299	236	184	140	100	71	50	36	29	23
-3.75°	361	290	228	178	135	96	68	48	36	29	22
-5°	345	277	217	171	128	91	65	46	35	28	22
-6.25°	325	261	206	161	119	85	61	44	34	27	21
-7.5°	303	243	192	150	108	78	57	41	32	26	21
-8.75°	279	223	177	136	99	72	52	38	31	24	20
-10°	253	203	161	121	88	64	47	35	29	23	19
-11.25°	226	182	143	105	78	57	42	33	27	21	18
-12.5°	201	161	124	92	68	50	37	31	24	20	16
-13.75°	175	139	104	78	58	44	34	28	22	19	15
-15°	151	116	88	66	49	37	31	25	21	17	14
-16.25°	124	95	73	55	42	34	28	22	19	16	14
-17.5°	100	78	60	46	36	30	25	21	17	14	13
-18.75°	80	62	48	38	32	27	22	19	15	13	12
-20°	63	50	40	33	28	23	20	17	14	13	11
-21.25°	50	40	34	29	24	20	17	15	13	12	10





REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-22.5°	40	34	29	24	21	18	15	14	12	11	9
-23.75°	33	29	24	21	18	16	14	12	11	10	9
-25°	28	24	21	18	16	14	13	11	10	9	8
-26.25°	23	20	18	16	14	13	11	10	9	8	7
-27.5°	20	17	15	14	13	11	10	9	8	7	7
-28.75°	17	15	14	12	11	10	9	8	8	7	6
-30°	14	13	12	11	10	9	8	8	7	6	6
-31.25°	13	12	11	10	9	8	7	7	6	6	5
-32.5°	11	10	9	9	8	7	7	6	6	5	5
-33.75°	10	9	8	8	7	7	6	6	5	5	5
-35°	8	8	7	7	6	6	6	5	5	5	5
-36.25°	7	7	7	6	6	6	5	5	5	5	5
-37.5°	7	6	6	6	5	5	5	5	5	5	5
-38.75°	6	6	5	5	5	5	5	5	5	5	4
-40°	5	5	5	5	5	5	5	5	5	4	4
-41.25°	5	5	5	5	5	5	5	4	4	4	4
-42.5°	5	5	5	5	5	5	4	4	4	4	4
-43.75°	5	5	5	5	4	4	4	4	4	4	4
-45°	5	4	4	4	4	4	4	4	4	4	4
-46.25°	4	4	4	4	4	4	4	4	4	4	4
-47.5°	4	4	4	4	4	4	4	4	4	4	4
-48.75°	4	4	4	4	4	4	4	4	4	4	4
-50°	4	4	4	4	4	4	4	4	4	3	3
-51.25°	4	4	4	4	4	4	3	3	3	3	3
-52.5°	4	4	4	4	3	3	3	3	3	3	2
-53.75°	4	3	3	3	3	3	3	2	2	2	2
-55°	3	3	3	3	3	2	2	2	2	2	2
-56.25°	3	2	2	2	2	2	2	2	2	2	2
-57.5°	2	2	2	2	2	2	2	2	2	2	2
-58.75°	2	2	2	2	2	2	2	2	2	2	1
-60°	2	2	2	2	2	2	2	1	1	1	1
-61.25°	2	2	2	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	1
-71.25°	1	1	1	1	1	1	1	1	1	1	1
-72.5°	1	1	1	1	1	1	1	1	1	1	1
-73.75°	1	1	1	1	1	1	1	1	1	1	0
-75°	1	1	1	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	20°	21.25°	22.5°	23.75°	25°	26.25°	27.5°	28.75°	30°	31.25°	32.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	1	1	1	1	0	0	0	0	0	0	0
71.25°	1	1	1	1	1	1	1	0	0	0	0
70°	1	1	1	1	1	1	1	1	1	1	0
68.75°	1	1	1	1	1	1	1	1	1	1	1
67.5°	1	1	1	1	1	1	1	1	1	1	1
66.25°	1	1	1	1	1	1	1	1	1	1	1
65°	1	1	1	1	1	1	1	1	1	1	1
63.75°	1	1	1	1	1	1	1	1	1	1	1
62.5°	1	1	1	1	1	1	1	1	1	1	1
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	2	1	1	1	1	1	1	1	1	1	1
56.25°	2	2	2	1	1	1	1	1	1	1	1
55°	2	2	2	2	2	1	1	1	1	1	1
53.75°	2	2	2	2	2	2	2	1	1	1	1
52.5°	2	2	2	2	2	2	2	2	1	1	1
51.25°	3	2	2	2	2	2	2	2	2	2	1
50°	3	3	2	2	2	2	2	2	2	2	2
48.75°	3	3	3	3	2	2	2	2	2	2	2
47.5°	4	3	3	3	3	2	2	2	2	2	2
46.25°	4	4	4	3	3	3	3	2	2	2	2
45°	4	4	4	4	3	3	3	3	2	2	2
43.75°	4	4	4	4	4	3	3	3	3	2	2
42.5°	4	4	4	4	4	4	3	3	3	3	2
41.25°	4	4	4	4	4	4	4	3	3	3	3
40°	4	4	4	4	4	4	4	4	3	3	3
38.75°	4	4	4	4	4	4	4	4	4	3	3
37.5°	5	4	4	4	4	4	4	4	4	4	3
36.25°	5	5	4	4	4	4	4	4	4	4	4
35°	5	5	5	4	4	4	4	4	4	4	4



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
33.75°	5	5	5	5	4	4	4	4	4	4	4
32.5°	5	5	5	5	4	4	4	4	4	4	4
31.25°	5	5	5	5	5	4	4	4	4	4	4
30°	5	5	5	5	5	5	4	4	4	4	4
28.75°	6	5	5	5	5	5	4	4	4	4	4
27.5°	6	6	5	5	5	5	5	4	4	4	4
26.25°	7	6	6	5	5	5	5	5	4	4	4
25°	7	6	6	5	5	5	5	5	4	4	4
23.75°	8	7	6	6	5	5	5	5	5	4	4
22.5°	8	7	7	6	5	5	5	5	5	4	4
21.25°	9	8	7	6	6	5	5	5	5	4	4
20°	10	8	7	7	6	5	5	5	5	5	4
18.75°	10	9	8	7	6	6	5	5	5	5	4
17.5°	11	10	8	7	6	6	5	5	5	5	5
16.25°	12	10	9	8	7	6	5	5	5	5	5
15°	12	11	9	8	7	6	6	5	5	5	5
13.75°	13	11	10	8	7	6	6	5	5	5	5
12.5°	14	12	10	9	8	7	6	5	5	5	5
11.25°	14	13	11	9	8	7	6	6	5	5	5
10°	15	13	11	10	8	7	6	6	5	5	5
8.75°	16	13	12	10	9	7	6	6	5	5	5
7.5°	17	14	12	10	9	8	7	6	5	5	5
6.25°	17	14	12	10	9	8	7	6	5	5	5
5°	18	15	13	11	9	8	7	6	5	5	5
3.75°	18	15	13	11	9	8	7	6	5	5	5
2.5°	19	15	13	11	9	8	7	6	5	5	5
1.25°	19	15	13	11	9	8	7	6	5	5	5
0°	19	15	13	11	10	8	7	6	6	5	5
-1.25°	19	15	13	11	9	8	7	6	5	5	5
-2.5°	19	15	13	11	9	8	7	6	5	5	5
-3.75°	18	15	13	11	9	8	7	6	5	5	5
-5°	18	15	13	11	9	8	7	6	5	5	5
-6.25°	17	14	12	10	9	8	7	6	5	5	5
-7.5°	17	14	12	10	9	8	7	6	5	5	5
-8.75°	16	13	12	10	9	7	6	6	5	5	5
-10°	15	13	11	10	8	7	6	6	5	5	5
-11.25°	14	13	11	9	8	7	6	6	5	5	5
-12.5°	14	12	10	9	8	7	6	5	5	5	5
-13.75°	13	11	10	8	7	6	6	5	5	5	5
-15°	12	11	9	8	7	6	6	5	5	5	5
-16.25°	12	10	9	8	7	6	5	5	5	5	5
-17.5°	11	10	8	7	6	6	5	5	5	5	5
-18.75°	10	9	8	7	6	6	5	5	5	5	4
-20°	10	8	7	7	6	5	5	5	5	5	4
-21.25°	9	8	7	6	6	5	5	5	5	4	4



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-22.5°	8	7	7	6	5	5	5	5	5	4	4
-23.75°	8	7	6	6	5	5	5	5	5	4	4
-25°	7	6	6	5	5	5	5	5	4	4	4
-26.25°	7	6	6	5	5	5	5	5	4	4	4
-27.5°	6	6	5	5	5	5	5	4	4	4	4
-28.75°	6	5	5	5	5	5	4	4	4	4	4
-30°	5	5	5	5	5	5	4	4	4	4	4
-31.25°	5	5	5	5	5	4	4	4	4	4	4
-32.5°	5	5	5	5	4	4	4	4	4	4	4
-33.75°	5	5	5	5	4	4	4	4	4	4	4
-35°	5	5	5	4	4	4	4	4	4	4	4
-36.25°	5	5	4	4	4	4	4	4	4	4	4
-37.5°	5	4	4	4	4	4	4	4	4	4	3
-38.75°	4	4	4	4	4	4	4	4	4	3	3
-40°	4	4	4	4	4	4	4	4	3	3	3
-41.25°	4	4	4	4	4	4	4	3	3	3	3
-42.5°	4	4	4	4	4	4	3	3	3	3	2
-43.75°	4	4	4	4	4	3	3	3	3	2	2
-45°	4	4	4	4	3	3	3	3	2	2	2
-46.25°	4	4	4	3	3	3	3	2	2	2	2
-47.5°	4	3	3	3	3	2	2	2	2	2	2
-48.75°	3	3	3	3	2	2	2	2	2	2	2
-50°	3	3	2	2	2	2	2	2	2	2	2
-51.25°	3	2	2	2	2	2	2	2	2	2	1
-52.5°	2	2	2	2	2	2	2	2	1	1	1
-53.75°	2	2	2	2	2	2	2	1	1	1	1
-55°	2	2	2	2	2	1	1	1	1	1	1
-56.25°	2	2	2	1	1	1	1	1	1	1	1
-57.5°	2	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	1
-63.75°	1	1	1	1	1	1	1	1	1	1	1
-65°	1	1	1	1	1	1	1	1	1	1	1
-66.25°	1	1	1	1	1	1	1	1	1	1	1
-67.5°	1	1	1	1	1	1	1	1	1	1	1
-68.75°	1	1	1	1	1	1	1	1	1	1	1
-70°	1	1	1	1	1	1	1	1	1	1	0
-71.25°	1	1	1	1	1	1	1	0	0	0	0
-72.5°	1	1	1	1	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	33.75°	35°	36.25°	37.5°	38.75°	40°	41.25°	42.5°	43.75°	45°	46.25°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	1	1	0	0	0	0	0	0	0	0	0
67.5°	1	1	1	1	0	0	0	0	0	0	0
66.25°	1	1	1	1	1	1	0	0	0	0	0
65°	1	1	1	1	1	1	1	0	0	0	0
63.75°	1	1	1	1	1	1	1	1	0	0	0
62.5°	1	1	1	1	1	1	1	1	1	1	0
61.25°	1	1	1	1	1	1	1	1	1	1	1
60°	1	1	1	1	1	1	1	1	1	1	1
58.75°	1	1	1	1	1	1	1	1	1	1	1
57.5°	1	1	1	1	1	1	1	1	1	1	1
56.25°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
53.75°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
51.25°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
48.75°	2	1	1	1	1	1	1	1	1	1	1
47.5°	2	2	1	1	1	1	1	1	1	1	1
46.25°	2	2	2	1	1	1	1	1	1	1	1
45°	2	2	2	2	1	1	1	1	1	1	1
43.75°	2	2	2	2	1	1	1	1	1	1	1
42.5°	2	2	2	2	2	1	1	1	1	1	1
41.25°	2	2	2	2	2	2	1	1	1	1	1
40°	2	2	2	2	2	2	1	1	1	1	1
38.75°	3	2	2	2	2	2	2	1	1	1	1
37.5°	3	3	2	2	2	2	2	1	1	1	1
36.25°	3	3	2	2	2	2	2	2	1	1	1
35°	3	3	3	2	2	2	2	2	1	1	1



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
33.75°	4	3	3	3	2	2	2	2	2	1	1
32.5°	4	4	3	3	2	2	2	2	2	1	1
31.25°	4	4	3	3	3	2	2	2	2	2	1
30°	4	4	4	3	3	2	2	2	2	2	1
28.75°	4	4	4	3	3	2	2	2	2	2	1
27.5°	4	4	4	3	3	3	2	2	2	2	2
26.25°	4	4	4	4	3	3	2	2	2	2	2
25°	4	4	4	4	3	3	3	2	2	2	2
23.75°	4	4	4	4	4	3	3	2	2	2	2
22.5°	4	4	4	4	4	3	3	2	2	2	2
21.25°	4	4	4	4	4	3	3	2	2	2	2
20°	4	4	4	4	4	4	3	3	2	2	2
18.75°	4	4	4	4	4	4	3	3	2	2	2
17.5°	4	4	4	4	4	4	3	3	2	2	2
16.25°	4	4	4	4	4	4	3	3	2	2	2
15°	4	4	4	4	4	4	3	3	3	2	2
13.75°	4	4	4	4	4	4	4	3	3	2	2
12.5°	5	4	4	4	4	4	4	3	3	2	2
11.25°	5	4	4	4	4	4	4	3	3	2	2
10°	5	4	4	4	4	4	4	3	3	2	2
8.75°	5	4	4	4	4	4	4	3	3	2	2
7.5°	5	4	4	4	4	4	4	3	3	2	2
6.25°	5	4	4	4	4	4	4	3	3	2	2
5°	5	4	4	4	4	4	4	3	3	2	2
3.75°	5	4	4	4	4	4	4	3	3	2	2
2.5°	5	4	4	4	4	4	4	3	3	2	2
1.25°	5	4	4	4	4	4	4	3	3	2	2
0°	5	5	4	4	4	4	4	4	3	3	2
-1.25°	5	4	4	4	4	4	4	3	3	2	2
-2.5°	5	4	4	4	4	4	4	3	3	2	2
-3.75°	5	4	4	4	4	4	4	3	3	2	2
-5°	5	4	4	4	4	4	4	3	3	2	2
-6.25°	5	4	4	4	4	4	4	3	3	2	2
-7.5°	5	4	4	4	4	4	4	3	3	2	2
-8.75°	5	4	4	4	4	4	4	3	3	2	2
-10°	5	4	4	4	4	4	4	3	3	2	2
-11.25°	5	4	4	4	4	4	4	3	3	2	2
-12.5°	5	4	4	4	4	4	4	3	3	2	2
-13.75°	4	4	4	4	4	4	4	3	3	2	2
-15°	4	4	4	4	4	4	3	3	3	2	2
-16.25°	4	4	4	4	4	4	3	3	2	2	2
-17.5°	4	4	4	4	4	4	3	3	2	2	2
-18.75°	4	4	4	4	4	4	3	3	2	2	2
-20°	4	4	4	4	4	4	3	3	2	2	2
-21.25°	4	4	4	4	4	3	3	2	2	2	2





REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-22.5°	4	4	4	4	4	3	3	2	2	2	2
-23.75°	4	4	4	4	4	3	3	2	2	2	2
-25°	4	4	4	4	3	3	3	2	2	2	2
-26.25°	4	4	4	4	3	3	2	2	2	2	2
-27.5°	4	4	4	3	3	3	2	2	2	2	2
-28.75°	4	4	4	3	3	2	2	2	2	2	1
-30°	4	4	4	3	3	2	2	2	2	2	1
-31.25°	4	4	3	3	3	2	2	2	2	2	1
-32.5°	4	4	3	3	2	2	2	2	2	1	1
-33.75°	4	3	3	3	2	2	2	2	2	1	1
-35°	3	3	3	2	2	2	2	2	1	1	1
-36.25°	3	3	2	2	2	2	2	2	1	1	1
-37.5°	3	3	2	2	2	2	2	1	1	1	1
-38.75°	3	2	2	2	2	2	2	1	1	1	1
-40°	2	2	2	2	2	2	1	1	1	1	1
-41.25°	2	2	2	2	2	2	1	1	1	1	1
-42.5°	2	2	2	2	2	1	1	1	1	1	1
-43.75°	2	2	2	2	1	1	1	1	1	1	1
-45°	2	2	2	2	1	1	1	1	1	1	1
-46.25°	2	2	2	1	1	1	1	1	1	1	1
-47.5°	2	2	1	1	1	1	1	1	1	1	1
-48.75°	2	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-51.25°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-53.75°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-56.25°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-58.75°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	1	1
-61.25°	1	1	1	1	1	1	1	1	1	1	1
-62.5°	1	1	1	1	1	1	1	1	1	1	0
-63.75°	1	1	1	1	1	1	1	1	0	0	0
-65°	1	1	1	1	1	1	1	0	0	0	0
-66.25°	1	1	1	1	1	1	0	0	0	0	0
-67.5°	1	1	1	1	0	0	0	0	0	0	0
-68.75°	1	1	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	47.5°	48.75°	50°	51.25°	52.5°	53.75°	55°	56.25°	57.5°	58.75°	60°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	1	0	0	0	0	0	0	0	0	0	0
58.75°	1	1	0	0	0	0	0	0	0	0	0
57.5°	1	1	0	0	0	0	0	0	0	0	0
56.25°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	0	0	0	0	0	0	0
53.75°	1	1	1	1	1	0	0	0	0	0	0
52.5°	1	1	1	1	1	0	0	0	0	0	0
51.25°	1	1	1	1	1	1	0	0	0	0	0
50°	1	1	1	1	1	1	0	0	0	0	0
48.75°	1	1	1	1	1	1	1	0	0	0	0
47.5°	1	1	1	1	1	1	1	0	0	0	0
46.25°	1	1	1	1	1	1	1	0	0	0	0
45°	1	1	1	1	1	1	1	1	0	0	0
43.75°	1	1	1	1	1	1	1	1	0	0	0
42.5°	1	1	1	1	1	1	1	1	0	0	0
41.25°	1	1	1	1	1	1	1	1	1	0	0
40°	1	1	1	1	1	1	1	1	1	0	0
38.75°	1	1	1	1	1	1	1	1	1	0	0
37.5°	1	1	1	1	1	1	1	1	1	1	0
36.25°	1	1	1	1	1	1	1	1	1	1	0
35°	1	1	1	1	1	1	1	1	1	1	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
33.75°	1	1	1	1	1	1	1	1	1	1	0
32.5°	1	1	1	1	1	1	1	1	1	1	0
31.25°	1	1	1	1	1	1	1	1	1	1	1
30°	1	1	1	1	1	1	1	1	1	1	1
28.75°	1	1	1	1	1	1	1	1	1	1	1
27.5°	1	1	1	1	1	1	1	1	1	1	1
26.25°	1	1	1	1	1	1	1	1	1	1	1
25°	1	1	1	1	1	1	1	1	1	1	1
23.75°	1	1	1	1	1	1	1	1	1	1	1
22.5°	2	1	1	1	1	1	1	1	1	1	1
21.25°	2	1	1	1	1	1	1	1	1	1	1
20°	2	1	1	1	1	1	1	1	1	1	1
18.75°	2	1	1	1	1	1	1	1	1	1	1
17.5°	2	1	1	1	1	1	1	1	1	1	1
16.25°	2	2	1	1	1	1	1	1	1	1	1
15°	2	2	1	1	1	1	1	1	1	1	1
13.75°	2	2	1	1	1	1	1	1	1	1	1
12.5°	2	2	1	1	1	1	1	1	1	1	1
11.25°	2	2	1	1	1	1	1	1	1	1	1
10°	2	2	1	1	1	1	1	1	1	1	1
8.75°	2	2	1	1	1	1	1	1	1	1	1
7.5°	2	2	1	1	1	1	1	1	1	1	1
6.25°	2	2	1	1	1	1	1	1	1	1	1
5°	2	2	1	1	1	1	1	1	1	1	1
3.75°	2	2	1	1	1	1	1	1	1	1	1
2.5°	2	2	1	1	1	1	1	1	1	1	1
1.25°	2	2	1	1	1	1	1	1	1	1	1
0°	2	2	2	1	1	1	1	1	1	1	1
-1.25°	2	2	1	1	1	1	1	1	1	1	1
-2.5°	2	2	1	1	1	1	1	1	1	1	1
-3.75°	2	2	1	1	1	1	1	1	1	1	1
-5°	2	2	1	1	1	1	1	1	1	1	1
-6.25°	2	2	1	1	1	1	1	1	1	1	1
-7.5°	2	2	1	1	1	1	1	1	1	1	1
-8.75°	2	2	1	1	1	1	1	1	1	1	1
-10°	2	2	1	1	1	1	1	1	1	1	1
-11.25°	2	2	1	1	1	1	1	1	1	1	1
-12.5°	2	2	1	1	1	1	1	1	1	1	1
-13.75°	2	2	1	1	1	1	1	1	1	1	1
-15°	2	2	1	1	1	1	1	1	1	1	1
-16.25°	2	2	1	1	1	1	1	1	1	1	1
-17.5°	2	1	1	1	1	1	1	1	1	1	1
-18.75°	2	1	1	1	1	1	1	1	1	1	1
-20°	2	1	1	1	1	1	1	1	1	1	1
-21.25°	2	1	1	1	1	1	1	1	1	1	1



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-22.5°	2	1	1	1	1	1	1	1	1	1	1
-23.75°	1	1	1	1	1	1	1	1	1	1	1
-25°	1	1	1	1	1	1	1	1	1	1	1
-26.25°	1	1	1	1	1	1	1	1	1	1	1
-27.5°	1	1	1	1	1	1	1	1	1	1	1
-28.75°	1	1	1	1	1	1	1	1	1	1	1
-30°	1	1	1	1	1	1	1	1	1	1	1
-31.25°	1	1	1	1	1	1	1	1	1	1	1
-32.5°	1	1	1	1	1	1	1	1	1	1	0
-33.75°	1	1	1	1	1	1	1	1	1	1	0
-35°	1	1	1	1	1	1	1	1	1	1	0
-36.25°	1	1	1	1	1	1	1	1	1	1	0
-37.5°	1	1	1	1	1	1	1	1	1	1	0
-38.75°	1	1	1	1	1	1	1	1	1	0	0
-40°	1	1	1	1	1	1	1	1	1	0	0
-41.25°	1	1	1	1	1	1	1	1	1	0	0
-42.5°	1	1	1	1	1	1	1	1	0	0	0
-43.75°	1	1	1	1	1	1	1	1	0	0	0
-45°	1	1	1	1	1	1	1	1	0	0	0
-46.25°	1	1	1	1	1	1	1	0	0	0	0
-47.5°	1	1	1	1	1	1	1	0	0	0	0
-48.75°	1	1	1	1	1	1	1	0	0	0	0
-50°	1	1	1	1	1	1	0	0	0	0	0
-51.25°	1	1	1	1	1	1	0	0	0	0	0
-52.5°	1	1	1	1	1	0	0	0	0	0	0
-53.75°	1	1	1	1	1	0	0	0	0	0	0
-55°	1	1	1	1	0	0	0	0	0	0	0
-56.25°	1	1	1	0	0	0	0	0	0	0	0
-57.5°	1	1	0	0	0	0	0	0	0	0	0
-58.75°	1	1	0	0	0	0	0	0	0	0	0
-60°	1	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	61.25°	62.5°	63.75°	65°	66.25°	67.5°	68.75°	70°	71.25°	72.5°	73.75°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
90°	0	0	0	0	0	0	0	0	0	0	0
88.75°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
86.25°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
83.75°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
81.25°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
78.75°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
76.25°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
73.75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
71.25°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
68.75°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
66.25°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
63.75°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
61.25°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
58.75°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
56.25°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
53.75°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
51.25°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
48.75°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
46.25°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
43.75°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
41.25°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
38.75°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
36.25°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
33.75°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
31.25°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
28.75°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
26.25°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
23.75°	0	0	0	0	0	0	0	0	0	0	0
22.5°	1	0	0	0	0	0	0	0	0	0	0
21.25°	1	0	0	0	0	0	0	0	0	0	0
20°	1	0	0	0	0	0	0	0	0	0	0
18.75°	1	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
16.25°	1	0	0	0	0	0	0	0	0	0	0
15°	1	0	0	0	0	0	0	0	0	0	0
13.75°	1	0	0	0	0	0	0	0	0	0	0
12.5°	1	0	0	0	0	0	0	0	0	0	0
11.25°	1	0	0	0	0	0	0	0	0	0	0
10°	1	0	0	0	0	0	0	0	0	0	0
8.75°	1	0	0	0	0	0	0	0	0	0	0
7.5°	1	0	0	0	0	0	0	0	0	0	0
6.25°	1	0	0	0	0	0	0	0	0	0	0
5°	1	0	0	0	0	0	0	0	0	0	0
3.75°	1	0	0	0	0	0	0	0	0	0	0
2.5°	1	0	0	0	0	0	0	0	0	0	0
1.25°	1	0	0	0	0	0	0	0	0	0	0
0°	1	1	0	0	0	0	0	0	0	0	0
-1.25°	1	0	0	0	0	0	0	0	0	0	0
-2.5°	1	0	0	0	0	0	0	0	0	0	0
-3.75°	1	0	0	0	0	0	0	0	0	0	0
-5°	1	0	0	0	0	0	0	0	0	0	0
-6.25°	1	0	0	0	0	0	0	0	0	0	0
-7.5°	1	0	0	0	0	0	0	0	0	0	0
-8.75°	1	0	0	0	0	0	0	0	0	0	0
-10°	1	0	0	0	0	0	0	0	0	0	0
-11.25°	1	0	0	0	0	0	0	0	0	0	0
-12.5°	1	0	0	0	0	0	0	0	0	0	0
-13.75°	1	0	0	0	0	0	0	0	0	0	0
-15°	1	0	0	0	0	0	0	0	0	0	0
-16.25°	1	0	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-18.75°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0
-21.25°	1	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-22.5°	1	0	0	0	0	0	0	0	0	0	0
-23.75°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-26.25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-28.75°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-31.25°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-33.75°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-36.25°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-38.75°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-41.25°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-43.75°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-46.25°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-48.75°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-51.25°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-53.75°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-56.25°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-58.75°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-61.25°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-63.75°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-66.25°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-68.75°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-71.25°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-73.75°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-76.25°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	75°	76.25°	77.5°	78.75°	80°	81.25°	82.5°	83.75°	85°	86.25°	87.5°
-78.75°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-81.25°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-83.75°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-86.25°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-88.75°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
90°	0	0
88.75°	0	0
87.5°	0	0
86.25°	0	0
85°	0	0
83.75°	0	0
82.5°	0	0
81.25°	0	0
80°	0	0
78.75°	0	0
77.5°	0	0
76.25°	0	0
75°	0	0
73.75°	0	0
72.5°	0	0
71.25°	0	0
70°	0	0
68.75°	0	0
67.5°	0	0
66.25°	0	0
65°	0	0
63.75°	0	0
62.5°	0	0
61.25°	0	0
60°	0	0
58.75°	0	0
57.5°	0	0
56.25°	0	0
55°	0	0
53.75°	0	0
52.5°	0	0
51.25°	0	0
50°	0	0
48.75°	0	0
47.5°	0	0
46.25°	0	0
45°	0	0
43.75°	0	0
42.5°	0	0
41.25°	0	0
40°	0	0
38.75°	0	0
37.5°	0	0
36.25°	0	0
35°	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
33.75°	0	0
32.5°	0	0
31.25°	0	0
30°	0	0
28.75°	0	0
27.5°	0	0
26.25°	0	0
25°	0	0
23.75°	0	0
22.5°	0	0
21.25°	0	0
20°	0	0
18.75°	0	0
17.5°	0	0
16.25°	0	0
15°	0	0
13.75°	0	0
12.5°	0	0
11.25°	0	0
10°	0	0
8.75°	0	0
7.5°	0	0
6.25°	0	0
5°	0	0
3.75°	0	0
2.5°	0	0
1.25°	0	0
0°	0	0
-1.25°	0	0
-2.5°	0	0
-3.75°	0	0
-5°	0	0
-6.25°	0	0
-7.5°	0	0
-8.75°	0	0
-10°	0	0
-11.25°	0	0
-12.5°	0	0
-13.75°	0	0
-15°	0	0
-16.25°	0	0
-17.5°	0	0
-18.75°	0	0
-20°	0	0
-21.25°	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-22.5°	0	0
-23.75°	0	0
-25°	0	0
-26.25°	0	0
-27.5°	0	0
-28.75°	0	0
-30°	0	0
-31.25°	0	0
-32.5°	0	0
-33.75°	0	0
-35°	0	0
-36.25°	0	0
-37.5°	0	0
-38.75°	0	0
-40°	0	0
-41.25°	0	0
-42.5°	0	0
-43.75°	0	0
-45°	0	0
-46.25°	0	0
-47.5°	0	0
-48.75°	0	0
-50°	0	0
-51.25°	0	0
-52.5°	0	0
-53.75°	0	0
-55°	0	0
-56.25°	0	0
-57.5°	0	0
-58.75°	0	0
-60°	0	0
-61.25°	0	0
-62.5°	0	0
-63.75°	0	0
-65°	0	0
-66.25°	0	0
-67.5°	0	0
-68.75°	0	0
-70°	0	0
-71.25°	0	0
-72.5°	0	0
-73.75°	0	0
-75°	0	0
-76.25°	0	0
-77.5°	0	0



REPORT NUMBER: G2-1802-569-9 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-SS-8LED4036-12-CS

**CANDELA DISTRIBUTION (continued):**

	88.75°	90°
-78.75°	0	0
-80°	0	0
-81.25°	0	0
-82.5°	0	0
-83.75°	0	0
-85°	0	0
-86.25°	0	0
-87.5°	0	0
-88.75°	0	0
-90°	0	0

(END OF REPORT)