

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220313

Luminaire Tested: **9002-W1-[RW, RI]-LED2790-M-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29410)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W1-[RW, RI]-LED2790-M-WT-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 2700K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 745.8 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.37
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220313

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-M-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220313

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-M-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	93
3	108	103	99	96	106	102	98	96	99	96	94	97	95	93	95	93	91	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87
5	102	96	92	89	100	95	91	88	93	90	88	92	89	87	90	88	86	85
6	99	93	89	86	98	92	88	85	91	87	85	90	87	84	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	81
8	94	88	84	81	93	87	83	81	86	83	80	85	82	80	85	82	80	79
9	92	85	82	79	91	85	81	79	84	81	79	84	80	78	83	80	78	77
10	90	83	80	77	89	83	79	77	82	79	77	82	79	77	81	78	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2058725
5°	1844512
10°	1295512
15°	516862
20°	177780
25°	98969
30°	24156
35°	13251
40°	9725
45°	9001
50°	8750
55°	9118
60°	8980
65°	8873
70°	8800
75°	8578
80°	8524
85°	8491



TEST NUMBER: P220313

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-M-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	318.7	42.7
10°-20°	302.1	40.5
20°-30°	76.6	10.3
30°-40°	14.9	2.0
40°-50°	10.0	1.3
50°-60°	9.4	1.3
60°-70°	7.5	1.0
70°-80°	5.0	0.7
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	697.4	93.5
0°-40°	712.3	95.5
0°-60°	731.7	98.1
0°-90°	745.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	745.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4173	
5°	3724	319
15°	1012	302
25°	182	77
35°	22	15
45°	13	10
55°	11	9
65°	8	8
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P220313

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-M-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4172.7
1°	4143.9
2°	4084.1
3°	3997.8
4°	3878.8
5°	3724.3
6°	3542.5
7°	3336.5
8°	3106.3
9°	2854.0
10°	2585.9
11°	2295.0
12°	1973.1
13°	1638.3
14°	1305.8
15°	1011.9
16°	775.6
17°	602.9
18°	481.7
19°	397.7
20°	338.6
22.5°	246.2
25°	181.8
26°	146.2
27°	103.0
28°	68.9
29°	51.5
30°	42.4
32.5°	28.8
35°	22.0
37.5°	17.4
40°	15.1
42.5°	13.6
45°	12.9
47.5°	12.1
50°	11.4
52.5°	11.4
55°	10.6
57.5°	9.8
60°	9.1
62.5°	8.3
65°	7.6
67.5°	6.8
70°	6.1
72.5°	5.3



TEST NUMBER: P220313

CATALOG NUMBER: 9002-W1-[RW, RI]-LED2790-M-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
75°	4.5
77.5°	4.5
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)