

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220306

Luminaire Tested: **9002-W1-[RW, RI]-LED3090-S-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29409)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W1-[RW, RI]-LED3090-S-WT-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 375.8 lumens
Efficiency: N/A
Efficacy: 37.6 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.24
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220306

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-S-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220306

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-S-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	98	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94	94	94	94
4	107	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93	93	93	93
5	105	100	97	95	104	100	97	94	98	95	93	97	94	93	95	94	92	91	91	91	91
6	103	98	95	92	102	98	94	92	96	94	92	95	93	91	94	92	91	90	90	90	90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88	88	88	88
8	100	95	91	89	99	94	91	89	93	91	89	93	90	88	92	90	88	87	87	87	87
9	98	93	90	88	97	93	90	88	92	89	87	91	89	87	91	89	87	86	86	86	86
10	97	92	89	87	96	91	88	86	91	88	86	90	88	86	90	87	86	85	85	85	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2364966
5°	1632836
10°	588514
15°	120085
20°	56862
25°	27981
30°	10084
35°	5300
40°	3607
45°	3349
50°	3070
55°	2753
60°	2368
65°	1868
70°	2308
75°	1525
80°	2273
85°	0



TEST NUMBER: P220306

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-S-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.2	65.5
10°-20°	89.7	23.9
20°-30°	24.6	6.5
30°-40°	6.0	1.6
40°-50°	3.5	0.9
50°-60°	2.9	0.8
60°-70°	1.7	0.4
70°-80°	1.0	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.5	95.9
0°-40°	366.4	97.5
0°-60°	372.8	99.2
0°-90°	375.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	375.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4793	
5°	3297	246
15°	235	90
25°	51	25
35°	9	6
45°	5	4
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220306

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-S-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4793.4
1°	4694.7
2°	4468.4
3°	4130.6
4°	3721.4
5°	3296.9
6°	2874.9
7°	2449.6
8°	2013.1
9°	1579.9
10°	1174.7
11°	830.5
12°	576.9
13°	406.8
14°	301.7
15°	235.1
17.5°	150.0
20°	108.3
22.5°	79.4
25°	51.4
27.5°	29.7
30°	17.7
32.5°	11.2
35°	8.8
37.5°	7.2
40°	5.6
42.5°	4.8
45°	4.8
47.5°	4.0
50°	4.0
52.5°	4.0
55°	3.2
57.5°	2.4
60°	2.4
62.5°	1.6
65°	1.6
67.5°	1.6
70°	1.6
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0



TEST NUMBER: P220306

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)