

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220362

Luminaire Tested: **9002-W1-[RW, RI]-LED3090-W-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29416)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W1-[RW, RI]-LED3090-W-BK-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 725.5 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.86
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220362

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-W-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220362

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-W-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81
4	98	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66
7	84	74	68	64	82	74	68	64	73	67	64	71	67	63	70	66	63	62
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	417251
5°	427215
10°	415672
15°	376652
20°	321852
25°	275622
30°	211190
35°	144975
40°	91457
45°	53168
50°	11053
55°	688
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P220362

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-W-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	11.2
10°-20°	203.5	28.1
20°-30°	228.6	31.5
30°-40°	152.1	21.0
40°-50°	57.6	7.9
50°-60°	2.3	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	513.6	70.8
0°-40°	665.7	91.8
0°-60°	725.5	100.0
0°-90°	725.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	725.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	846	
5°	863	81
15°	737	204
25°	506	229
35°	241	152
45°	76	58
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220362

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-W-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	845.7
1°	843.3
2°	844.9
3°	850.5
4°	856.9
5°	862.6
6°	865.8
7°	863.4
8°	855.3
9°	843.3
10°	829.7
11°	813.6
12°	796.8
13°	779.1
14°	759.0
15°	737.4
16°	711.7
17°	685.2
18°	659.6
19°	636.3
20°	613.0
21°	592.2
22°	570.5
23°	548.8
24°	528.0
25°	506.3
26°	483.8
27°	459.0
28°	431.7
29°	400.4
30°	370.7
32.5°	302.5
35°	240.7
37.5°	187.0
40°	142.0
42.5°	106.7
45°	76.2
47.5°	43.3
50°	14.4
52.5°	1.6
55°	0.8
57.5°	0.8
60°	0.0
62.5°	0.0
65°	0.0



TEST NUMBER: P220362

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3090-W-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)