

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220347

Luminaire Tested: **9002-W1-[RW, RI]-LED3590-M-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29414)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W1-[RW, RI]-LED3590-M-BK-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 830.7 lumens
Efficiency: N/A
Efficacy: 83.1 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.37
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220347

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3590-M-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220347

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3590-M-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95
3	109	105	101	99	107	103	100	98	101	99	96	99	97	95	97	95	94	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	90	94	92	90	93	91	89	88
6	101	95	91	89	100	95	91	89	93	90	88	92	89	87	91	89	87	86
7	98	93	89	86	97	92	89	86	91	88	86	90	87	85	89	87	85	84
8	96	90	87	84	95	90	86	84	89	86	84	88	85	83	87	85	83	82
9	94	88	85	82	93	88	84	82	87	84	82	86	84	82	86	83	81	81
10	92	86	83	80	91	86	82	80	85	82	80	85	82	80	84	82	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2406015
5°	2153211
10°	1507932
15°	600325
20°	205240
25°	113014
30°	24269
35°	10480
40°	5603
45°	2442
50°	1305
55°	774
60°	888
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P220347

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3590-M-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	371.4	44.7
10°-20°	355.3	42.8
20°-30°	87.4	10.5
30°-40°	12.2	1.5
40°-50°	3.3	0.4
50°-60°	0.9	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.2	98.0
0°-40°	826.4	99.5
0°-60°	830.6	100.0
0°-90°	830.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	830.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4877	
5°	4348	371
15°	1175	355
25°	208	87
35°	17	12
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220347

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3590-M-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4876.6
1°	4841.0
2°	4769.8
3°	4668.1
4°	4529.1
5°	4347.6
6°	4129.6
7°	3885.5
8°	3610.1
9°	3321.7
10°	3009.9
11°	2667.6
12°	2290.6
13°	1904.1
14°	1520.1
15°	1175.3
17.5°	624.6
20°	390.9
22.5°	282.3
25°	207.6
27.5°	91.2
30°	42.6
32.5°	26.1
35°	17.4
37.5°	11.3
40°	8.7
42.5°	6.1
45°	3.5
47.5°	2.6
50°	1.7
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P220347

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3590-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0.0}$

(END OF REPORT)