

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220359

Luminaire Tested: **9002-W1-[RW, RI]-LED3597-F-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220359  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29415)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9002-W1-[RW, RI]-LED3597-F-BK-L1-UNV  
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 800.7 lumens  
Efficiency: N/A  
Efficacy: 80.1 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.63  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220359

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3597-F-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220359

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3597-F-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83
5	98	91	86	83	96	90	86	83	89	85	82	87	84	81	86	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	73
8	88	80	75	72	86	79	75	71	78	74	71	77	74	71	77	73	71	70
9	84	77	72	69	84	76	72	68	75	71	68	75	71	68	74	70	68	67
10	82	74	69	66	81	73	69	66	73	68	66	72	68	65	71	68	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	849057
5°	851904
10°	790914
15°	657379
20°	453060
25°	267184
30°	119410
35°	50895
40°	20417
45°	7396
50°	2533
55°	688
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P220359

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3597-F-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	159.8	20.0
10°-20°	346.5	43.3
20°-30°	224.6	28.0
30°-40°	59.0	7.4
40°-50°	9.9	1.2
50°-60°	1.1	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	730.8	91.3
0°-40°	789.8	98.6
0°-60°	800.7	100.0
0°-90°	800.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	800.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1721	
5°	1720	160
15°	1287	347
25°	491	225
35°	84	59
45°	11	10
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220359

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3597-F-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1720.9
1°	1715.2
2°	1713.6
3°	1716.9
4°	1720.9
5°	1720.1
6°	1710.4
7°	1690.9
8°	1659.2
9°	1621.8
10°	1578.7
11°	1531.6
12°	1480.4
13°	1424.4
14°	1359.4
15°	1287.0
16°	1207.4
17°	1122.9
18°	1036.0
19°	947.4
20°	862.9
22.5°	667.1
25°	490.8
26°	425.8
27°	360.8
28°	302.3
29°	251.9
30°	209.6
32.5°	131.6
35°	84.5
37.5°	52.0
40°	31.7
42.5°	18.7
45°	10.6
47.5°	5.7
50°	3.3
52.5°	1.6
55°	0.8
57.5°	0.8
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P220359

CATALOG NUMBER: 9002-W1-[RW, RI]-LED3597-F-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)