

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P29409

Luminaire Tested: **9002-W1-[RW, RI]-LED4080-S-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P29409
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W1-[RW, RI]-LED4080-S-WT-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC,
WHITE HOUSING.
Light Source: (1) 4000K CCT, 80 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 468.4 lumens
Efficiency: N/A
Efficacy: 46.8 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.24
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P29409

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4080-S-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P29409

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4080-S-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	94
4	107	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93
5	105	100	97	95	104	100	97	94	98	95	93	97	94	93	95	93	92	91
6	103	98	95	92	102	98	94	92	96	94	92	95	93	91	94	92	91	90
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88
8	100	95	91	89	99	94	91	89	93	91	89	92	90	88	92	90	88	87
9	98	93	90	88	97	93	90	88	92	89	87	91	89	87	91	89	87	86
10	97	92	89	87	96	91	88	86	91	88	86	90	88	86	90	87	86	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2947449
5°	2035041
10°	733450
15°	149660
20°	70881
25°	34841
30°	12534
35°	6625
40°	4508
45°	4186
50°	3838
55°	3441
60°	2960
65°	2335
70°	2885
75°	1906
80°	2841
85°	0



TEST NUMBER: P29409

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4080-S-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.8	65.5
10°-20°	111.8	23.9
20°-30°	30.6	6.5
30°-40°	7.5	1.6
40°-50°	4.4	0.9
50°-60°	3.6	0.8
60°-70°	2.1	0.4
70°-80°	1.2	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	449.3	95.9
0°-40°	456.7	97.5
0°-60°	464.7	99.2
0°-90°	468.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	468.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5974	
5°	4109	307
15°	293	112
25°	64	31
35°	11	7
45°	6	4
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P29409

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4080-S-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	5974
1°	5851
2°	5569
3°	5148
4°	4638
5°	4109
6°	3583
7°	3053
8°	2509
9°	1969
10°	1464
11°	1035
12°	719
13°	507
14°	376
15°	293
17.5°	187
20°	135
22.5°	99
25°	64
27.5°	37
30°	22
32.5°	14
35°	11
37.5°	9
40°	7
42.5°	6
45°	6
47.5°	5
50°	5
52.5°	5
55°	4
57.5°	3
60°	3
62.5°	2
65°	2
67.5°	2
70°	2
72.5°	1
75°	1
77.5°	1
80°	1
82.5°	1
85°	0
87.5°	0



TEST NUMBER: P29409

CATALOG NUMBER: 9002-W1-[RW, RI]-LED4080-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

90° | $\frac{0^\circ}{0}$

(END OF REPORT)