

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220382

Luminaire Tested: **9002-W1-FL-LED3097-M-WT-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220382  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29418)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9002-W1-FL-LED3097-M-WT-L1-UNV  
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.  
Light Source: (1) 3000K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 784.2 lumens  
Efficiency: N/A  
Efficacy: 78.4 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.36  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220382

CATALOG NUMBER: 9002-W1-FL-LED3097-M-WT-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220382

CATALOG NUMBER: 9002-W1-FL-LED3097-M-WT-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96
2	111	107	104	102	109	106	103	101	103	100	99	100	98	97	97	96	95	93
3	108	103	99	96	106	102	98	96	99	96	94	97	95	93	95	93	91	90
4	104	99	95	92	103	98	94	91	96	93	90	94	92	89	92	90	88	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82
7	96	90	86	83	95	89	85	82	88	85	82	87	84	82	86	83	81	80
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	78
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	80	78	76	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2112454
5°	1889433
10°	1319109
15°	520489
20°	187021
25°	105556
30°	60275
35°	32585
40°	12946
45°	8652
50°	5910
55°	5333
60°	5328
65°	6304
70°	6636
75°	7434
80°	4262
85°	4529



TEST NUMBER: P220382

CATALOG NUMBER: 9002-W1-FL-LED3097-M-WT-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	325.8	41.5
10°-20°	306.1	39.0
20°-30°	92.4	11.8
30°-40°	34.2	4.4
40°-50°	9.9	1.3
50°-60°	5.8	0.7
60°-70°	5.3	0.7
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	724.4	92.4
0°-40°	758.6	96.7
0°-60°	774.3	98.7
0°-90°	784.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	784.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4282	
5°	3815	326
15°	1019	306
25°	194	92
35°	54	34
45°	12	10
55°	6	6
65°	5	5
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P220382

CATALOG NUMBER: 9002-W1-FL-LED3097-M-WT-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4281.6
1°	4251.5
2°	4188.9
3°	4098.5
4°	3975.7
5°	3815.0
6°	3623.4
7°	3410.2
8°	3168.4
9°	2909.5
10°	2633.0
11°	2331.6
12°	2002.5
13°	1658.0
14°	1319.6
15°	1019.0
16°	778.8
17°	603.4
18°	487.5
19°	410.2
20°	356.2
22.5°	261.9
25°	193.9
26°	171.5
27°	152.2
28°	135.2
29°	119.7
30°	105.8
32.5°	77.3
35°	54.1
37.5°	30.1
40°	20.1
42.5°	15.5
45°	12.4
47.5°	10.0
50°	7.7
52.5°	7.0
55°	6.2
57.5°	6.2
60°	5.4
62.5°	5.4
65°	5.4
67.5°	5.4
70°	4.6
72.5°	3.9



TEST NUMBER: P220382

CATALOG NUMBER: 9002-W1-FL-LED3097-M-WT-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
75°	3.9
77.5°	3.1
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)