

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220427

Luminaire Tested: **9002-W1-FL-LED3590-W-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220427  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29424)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9002-W1-FL-LED3590-W-BK-L1-UNV  
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, FLUSH LENS, WIDE FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 822.4 lumens  
Efficiency: N/A  
Efficacy: 82.2 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.88  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220427

CATALOG NUMBER: 9002-W1-FL-LED3590-W-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220427

CATALOG NUMBER: 9002-W1-FL-LED3590-W-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81	78	75	74
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		76	73	70	68
6	86	77	71	67	85	76	71	66	75	70	66		73	69	65		72	68	65	63
7	82	72	66	62	81	72	66	62	70	65	61		69	64	61		68	64	61	59
8	78	68	62	58	77	67	62	57	66	61	57		65	60	57		64	60	57	55
9	74	64	58	54	73	64	58	54	63	57	54		62	57	53		61	56	53	52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58	53	50	49

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	436296
5°	448264
10°	437365
15°	397543
20°	343904
25°	293641
30°	236029
35°	163767
40°	105755
45°	64262
50°	37304
55°	20902
60°	11150
65°	6071
70°	2452
75°	0
80°	0
85°	0



TEST NUMBER: P220427

CATALOG NUMBER: 9002-W1-FL-LED3590-W-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	85.5	10.4
10°-20°	215.6	26.2
20°-30°	245.8	29.9
30°-40°	172.1	20.9
40°-50°	74.2	9.0
50°-60°	23.3	2.8
60°-70°	5.4	0.7
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	546.9	66.5
0°-40°	719.0	87.4
0°-60°	816.6	99.3
0°-90°	822.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	822.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	884	
5°	905	86
15°	778	216
25°	539	246
35°	272	172
45°	92	74
55°	24	23
65°	5	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220427

CATALOG NUMBER: 9002-W1-FL-LED3590-W-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	884.3
1°	883.4
2°	884.3
3°	891.2
4°	899.1
5°	905.1
6°	908.6
7°	907.7
8°	899.9
9°	887.8
10°	873.0
11°	855.6
12°	839.1
13°	820.0
14°	800.0
15°	778.3
16°	754.9
17°	728.8
18°	703.6
19°	679.3
20°	655.0
21°	632.4
22°	608.9
23°	585.5
24°	562.9
25°	539.4
26°	516.8
27°	493.4
28°	468.2
29°	442.1
30°	414.3
32.5°	340.5
35°	271.9
37.5°	213.7
40°	164.2
42.5°	124.2
45°	92.1
47.5°	66.9
50°	48.6
52.5°	34.7
55°	24.3
57.5°	16.5
60°	11.3
62.5°	7.8
65°	5.2



TEST NUMBER: P220427

CATALOG NUMBER: 9002-W1-FL-LED3590-W-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	2.6
70°	1.7
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)