

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221238

Luminaire Tested: **9002-W2-[RW, RI]-LED3090-S-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29409)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W2-[RW, RI]-LED3090-S-WT-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, WHITE HOUSING.
Light Source: (1) 3000K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 751.6 lumens
Efficiency: N/A
Efficacy: 37.6 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.24
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221238

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3090-S-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221238

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3090-S-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	101	98	96	93	94	91	89	87	78	77	75		66	65	64		55	54	54	49
2	96	91	87	83	89	85	81	79	74	71	69		63	62	61		54	53	52	48
3	91	85	80	76	85	79	75	72	70	67	65		61	59	58		52	51	51	47
4	86	79	74	70	81	75	70	67	66	63	61		59	57	55		51	50	49	46
5	83	75	69	66	77	71	66	63	64	60	58		57	55	53		50	49	48	46
6	79	71	66	62	74	68	63	60	61	58	55		55	53	51		49	48	47	45
7	76	68	62	59	72	65	60	57	59	56	53		54	51	50		49	47	46	44
8	73	65	60	56	69	62	58	55	57	54	52		52	50	48		48	46	45	44
9	71	62	57	54	67	60	56	53	55	52	50		51	49	47		47	46	45	43
10	68	60	55	52	65	58	54	51	54	51	49		50	48	46		46	45	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2364966
5°	1632836
10°	588514
15°	120085
20°	56862
25°	27981
30°	10084
35°	5300
40°	3607
45°	3349
50°	3070
55°	2753
60°	2368
65°	1868
70°	2308
75°	1525
80°	2273
85°	0



TEST NUMBER: P221238

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3090-S-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.2	32.8
10°-20°	89.7	11.9
20°-30°	24.6	3.3
30°-40°	6.0	0.8
40°-50°	3.5	0.5
50°-60°	2.9	0.4
60°-70°	1.7	0.2
70°-80°	1.0	0.1
80°-90°	0.3	0.0
90°-100°	0.5	0.1
100°-110°	1.0	0.1
110°-120°	1.7	0.2
120°-130°	2.9	0.4
130°-140°	3.5	0.5
140°-150°	6.0	0.8
150°-160°	24.6	3.3
160°-170°	89.7	11.9
170°-180°	246.2	32.8
0°-30°	360.5	48.0
0°-40°	366.4	48.8
0°-60°	372.8	49.6
0°-90°	375.8	50.0
90°-120°	3.2	0.4
90°-150°	15.5	2.1
90°-180°	376.0	50.0
0°-180°	751.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4793	
5°	3297	246
15°	235	90
25°	51	25
35°	9	6
45°	5	4
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	0
95°	0	0
105°	1	1
115°	2	2
125°	3	3
135°	5	4
145°	9	6
155°	51	25
165°	235	90
175°	3297	246
180°	4793	



TEST NUMBER: P221238

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3090-S-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4793.4
1°	4694.7
2°	4468.4
3°	4130.6
4°	3721.4
5°	3296.9
6°	2874.9
7°	2449.6
8°	2013.1
9°	1579.9
10°	1174.7
11°	830.5
12°	576.9
13°	406.8
14°	301.7
15°	235.1
17.5°	150.0
20°	108.3
22.5°	79.4
25°	51.4
27.5°	29.7
30°	17.7
32.5°	11.2
35°	8.8
37.5°	7.2
40°	5.6
42.5°	4.8
45°	4.8
47.5°	4.0
50°	4.0
52.5°	4.0
55°	3.2
57.5°	2.4
60°	2.4
62.5°	1.6
65°	1.6
67.5°	1.6
70°	1.6
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0



TEST NUMBER: P221238

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3090-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.8
100°	0.8
102.5°	0.8
105°	0.8
107.5°	0.8
110°	1.6
112.5°	1.6
115°	1.6
117.5°	1.6
120°	2.4
122.5°	2.4
125°	3.2
127.5°	4.0
130°	4.0
132.5°	4.0
135°	4.8
137.5°	4.8
140°	5.6
142.5°	7.2
145°	8.8
147.5°	11.2
150°	17.7
152.5°	29.7
155°	51.4
157.5°	79.4
160°	108.3
162.5°	150.0
165°	235.1
166°	301.7
167°	406.8
168°	576.9
169°	830.5
170°	1174.7
171°	1579.9
172°	2013.1
173°	2449.6
174°	2874.9
175°	3296.9
176°	3721.4
177°	4130.6
178°	4468.4
179°	4694.7



TEST NUMBER: P221238

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3090-S-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

180° $\overbrace{\hspace{1.5cm}}^{0^\circ}$
4793.4

(END OF REPORT)