

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P221259

Luminaire Tested: **9002-W2-[RW, RI]-LED3597-M-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P221259
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29414)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9002-W2-[RW, RI]-LED3597-M-BK-L1-UNV
Description: LUMIERE LANTERRA 9002 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3500K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1553.9 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.37
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 20
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P221259

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-M-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P221259

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-M-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	101	98	95	93	93	91	89	87	78	76	75		66	65	64		55	54	54	49
2	95	90	86	83	89	84	81	78	73	71	69		63	61	60		53	52	52	47
3	90	84	79	75	84	79	75	71	69	66	64		60	58	57		52	51	50	46
4	86	78	73	69	80	74	69	66	66	62	60		58	56	54		50	49	48	45
5	82	74	68	64	76	70	65	61	62	59	56		56	53	51		49	48	47	44
6	78	70	64	60	73	66	61	58	60	56	54		54	51	49		48	46	45	43
7	74	66	60	57	70	63	58	55	57	54	51		52	49	48		47	45	44	42
8	71	63	57	54	67	60	55	52	55	52	49		50	48	46		46	44	43	41
9	69	60	55	51	65	58	53	50	53	50	47		49	46	45		45	43	42	40
10	66	58	53	49	63	55	51	48	51	48	46		47	45	43		44	42	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2250551
5°	2014091
10°	1410489
15°	561505
20°	191956
25°	105719
30°	22674
35°	9818
40°	5217
45°	2303
50°	1228
55°	688
60°	789
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P221259

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-M-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.4	22.4
10°-20°	332.4	21.4
20°-30°	81.8	5.3
30°-40°	11.4	0.7
40°-50°	3.1	0.2
50°-60°	0.8	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.1	0.0
120°-130°	0.8	0.1
130°-140°	3.1	0.2
140°-150°	11.4	0.7
150°-160°	81.8	5.3
160°-170°	332.4	21.4
170°-180°	347.4	22.4
0°-30°	761.5	49.0
0°-40°	773.0	49.7
0°-60°	776.9	50.0
0°-90°	777.0	50.0
90°-120°	0.1	0.0
90°-150°	15.4	1.0
90°-180°	777.0	50.0
0°-180°	1553.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4562	
5°	4067	347
15°	1099	332
25°	194	82
35°	16	11
45°	3	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	1	1
135°	3	3
145°	16	11
155°	194	82
165°	1099	332
175°	4067	347
180°	4562	



TEST NUMBER: P221259

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	4561.5
1°	4528.2
2°	4461.6
3°	4366.5
4°	4236.5
5°	4066.7
6°	3862.8
7°	3634.4
8°	3376.9
9°	3107.1
10°	2815.4
11°	2495.3
12°	2142.6
13°	1781.1
14°	1421.9
15°	1099.3
17.5°	584.2
20°	365.6
22.5°	264.1
25°	194.2
27.5°	85.3
30°	39.8
32.5°	24.4
35°	16.3
37.5°	10.6
40°	8.1
42.5°	5.7
45°	3.3
47.5°	2.4
50°	1.6
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P221259

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.8
122.5°	0.8
125°	0.8
127.5°	0.8
130°	1.6
132.5°	2.4
135°	3.3
137.5°	5.7
140°	8.1
142.5°	10.6
145°	16.3
147.5°	24.4
150°	39.8
152.5°	85.3
155°	194.2
157.5°	264.1
160°	365.6
162.5°	584.2
165°	1099.3
166°	1421.9
167°	1781.1
168°	2142.6
169°	2495.3
170°	2815.4
171°	3107.1
172°	3376.9
173°	3634.4
174°	3862.8
175°	4066.7
176°	4236.5
177°	4366.5
178°	4461.6
179°	4528.2



TEST NUMBER: P221259

CATALOG NUMBER: 9002-W2-[RW, RI]-LED3597-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

180° $\overbrace{\hspace{1.5cm}}^{0^\circ}$
4561.5

(END OF REPORT)