

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220552

Luminaire Tested: **9003-W1-[RW, RI]-LED2790-W-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220552  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29475)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED2790-W-BK-L1-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 2700K CCT, 90 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 559.8 lumens  
Efficiency: N/A  
Efficacy: 57.1 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220552

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2790-W-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220552

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2790-W-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	77	71	68	84	76	71	68	75	71	67	74	70	67	73	69	67	66
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63
10	78	70	65	61	78	70	65	61	69	64	61	68	64	61	67	64	61	60

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	219083
5°	220008
10°	205786
15°	175824
20°	149416
25°	88795
30°	40411
35°	25618
40°	14513
45°	5334
50°	1672
55°	1262
60°	1096
65°	623
70°	256
75°	339
80°	0
85°	0



TEST NUMBER: P220552

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2790-W-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.1	16.6
10°-20°	216.5	38.7
20°-30°	168.0	30.0
30°-40°	61.3	10.9
40°-50°	16.2	2.9
50°-60°	3.0	0.5
60°-70°	1.3	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.6	85.3
0°-40°	538.8	96.3
0°-60°	558.1	99.7
0°-90°	559.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	559.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	999	
5°	1000	93
15°	774	216
25°	367	168
35°	96	61
45°	17	16
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220552

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2790-W-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	999.1
1°	996.2
2°	996.2
3°	999.1
4°	1000.7
5°	999.5
6°	994.6
7°	984.3
8°	968.4
9°	947.5
10°	924.2
11°	897.2
12°	867.3
13°	835.8
14°	803.5
15°	774.5
16°	748.3
17°	720.4
18°	693.9
19°	666.9
20°	640.3
21°	610.8
22°	564.2
23°	502.8
24°	436.1
25°	367.0
26°	301.9
27°	243.8
28°	200.1
29°	175.1
30°	159.6
32.5°	125.6
35°	95.7
37.5°	72.0
40°	50.7
42.5°	33.5
45°	17.2
47.5°	7.8
50°	4.9
52.5°	3.7
55°	3.3
57.5°	2.9
60°	2.5
62.5°	1.6
65°	1.2



TEST NUMBER: P220552

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2790-W-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.2
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)