

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220524

Luminaire Tested: **9003-W1-[RW, RI]-LED3097-M-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220524
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29473)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-[RW, RI]-LED3097-M-BK-L1-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 3000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 552.1 lumens
Efficiency: N/A
Efficacy: 56.3 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220524

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3097-M-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220524

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3097-M-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	88	93	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	85	91	87	85	89	87	84	88	86	84	83
7	96	90	86	83	95	89	85	83	88	85	82	87	84	82	86	83	81	80
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	78
9	91	85	81	78	90	84	80	78	83	80	78	83	80	77	82	79	77	76
10	89	82	78	76	88	82	78	76	81	78	76	81	78	75	80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	580480
5°	520184
10°	365457
15°	196119
20°	103166
25°	46116
30°	8913
35°	3266
40°	1861
45°	1551
50°	1296
55°	1032
60°	833
65°	571
70°	256
75°	0
80°	0
85°	0



TEST NUMBER: P220524

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3097-M-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.2	36.6
10°-20°	243.7	44.1
20°-30°	88.9	16.1
30°-40°	9.8	1.8
40°-50°	3.9	0.7
50°-60°	2.4	0.4
60°-70°	1.1	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	534.7	96.9
0°-40°	544.5	98.6
0°-60°	550.8	99.8
0°-90°	552.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	552.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2647	
5°	2363	202
15°	864	244
25°	191	89
35°	12	10
45°	5	4
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220524

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3097-M-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2647.2
1°	2625.7
2°	2588.2
3°	2533.1
4°	2456.9
5°	2363.2
6°	2251.0
7°	2119.3
8°	1970.1
9°	1808.2
10°	1641.3
11°	1473.2
12°	1306.7
13°	1149.4
14°	999.4
15°	863.9
16°	739.5
17°	638.1
18°	555.8
19°	490.7
20°	442.1
21°	402.3
22°	356.7
23°	302.8
24°	246.5
25°	190.6
26°	137.4
27°	89.9
28°	56.6
29°	41.3
30°	35.2
32.5°	23.7
35°	12.2
37.5°	8.0
40°	6.5
42.5°	5.7
45°	5.0
47.5°	4.2
50°	3.8
52.5°	3.1
55°	2.7
57.5°	2.3
60°	1.9
62.5°	1.5
65°	1.1



TEST NUMBER: P220524

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3097-M-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)