

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220486

Luminaire Tested: **9003-W1-[RW, RI]-LED3590-W-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220486
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29471)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-[RW, RI]-LED3590-W-WT-L1-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 3500K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 746.0 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220486

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-W-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220486

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-W-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78
4	96	88	82	78	94	87	82	77	85	80	76	83	79	76	81	77	75	73
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	68
6	87	78	72	67	85	77	71	67	76	70	67	74	70	66	73	69	66	64
7	83	74	67	63	82	73	67	63	72	66	63	70	66	62	69	65	62	61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54
10	73	63	57	54	72	63	57	53	62	57	53	61	56	53	60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	242897
5°	242768
10°	227807
15°	195938
20°	168271
25°	103627
30°	51729
35°	36246
40°	25219
45°	16188
50°	13168
55°	13419
60°	13639
65°	13179
70°	11797
75°	11184
80°	12123
85°	12077



TEST NUMBER: P220486

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-W-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.8	13.8
10°-20°	241.5	32.4
20°-30°	196.0	26.3
30°-40°	86.7	11.6
40°-50°	43.5	5.8
50°-60°	31.3	4.2
60°-70°	24.8	3.3
70°-80°	14.1	1.9
80°-90°	5.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	540.4	72.4
0°-40°	627.1	84.1
0°-60°	701.8	94.1
0°-90°	746.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	746.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1108	
5°	1103	103
15°	863	242
25°	428	196
35°	135	87
45°	52	43
55°	35	31
65°	25	25
75°	13	14
85°	5	5
90°	0	



TEST NUMBER: P220486

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-W-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1107.7
1°	1104.6
2°	1103.7
3°	1105.5
4°	1105.5
5°	1102.9
6°	1097.2
7°	1085.8
8°	1069.1
9°	1047.6
10°	1023.1
11°	994.6
12°	963.0
13°	928.8
14°	895.1
15°	863.1
16°	835.5
17°	806.5
18°	777.6
19°	748.7
20°	721.1
21°	689.1
22°	638.7
23°	573.8
24°	502.8
25°	428.3
26°	358.1
27°	295.9
28°	248.5
29°	221.4
30°	204.3
32.5°	167.4
35°	135.4
37.5°	111.8
40°	88.1
42.5°	69.7
45°	52.2
47.5°	42.1
50°	38.6
52.5°	36.8
55°	35.1
57.5°	32.9
60°	31.1
62.5°	28.5
65°	25.4



TEST NUMBER: P220486

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3590-W-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	21.5
70°	18.4
72.5°	14.9
75°	13.2
77.5°	11.4
80°	9.6
82.5°	7.5
85°	4.8
87.5°	2.2
90°	0.0

(END OF REPORT)