

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-8LED2725-12-BK-LVR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-30)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-8LED2725-12-BK-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD BLACK, HEX CELL LOUVER
Light Source: (1) SORAA 2700K 95 CRI LED
SM16-07-25D-927-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	247.3 lumens	Max Intensity:	2094.2 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	30.9 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	16.2°H x 16.2°V	Field Angle (10%):	35.4°H x 35.4°V
Beam Lumens:	88.3 lumens	Field Lumens:	203.8 lumens
Beam Efficiency:	35.7%	Field Efficiency:	82.4%

Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED2725-12-BK-LVR

Iso-Candela Plot





REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR


Lumen Table

90	0.0															
80	0.0															
70	0.0															
60	0.0															
50	0.0															
40	0.0															
30	0.0															
20	0.0															
10	0.0															
0	0.0															
-10	0.0															
-20	0.0															
-30	0.0															
-40	0.0															
-50	0.0															
-60	0.0															
-70	0.0															
-80	0.0															
-90	0.0															

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30	0.0	0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
20	0.0	0.0	0.0	0.1	0.2	0.7	1.6	1.6	0.7	0.2	0.1	0.0	0.0	0.0	0.0	0.0
10	0.0	0.0	0.0	0.1	0.7	3.7	9.4	9.4	3.7	0.7	0.1	0.0	0.0	0.0	0.0	0.0
0	0.0	0.0	0.0	0.2	1.5	9.2	34.1	34.1	9.2	1.5	0.2	0.0	0.0	0.0	0.0	0.0
-10	0.0	0.0	0.0	0.2	1.5	9.2	34.1	34.1	9.2	1.5	0.2	0.0	0.0	0.0	0.0	0.0
-20	0.0	0.0	0.0	0.1	0.7	3.7	9.4	9.4	3.7	0.7	0.1	0.0	0.0	0.0	0.0	0.0
-30	0.0	0.0	0.0	0.1	0.2	0.7	1.6	1.6	0.7	0.2	0.1	0.0	0.0	0.0	0.0	0.0
-40	0.0	0.0	0.0	0.0	0.1	0.1	0.2	0.2	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-60	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED2725-12-BK-LVR


Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED2725-12-BK-LVR

Luminous Intensity Plot



Beam:
H Angle: 16.2°
V Angle: 16.2°
Lumens: 88.3
Efficiency: 35.7%

Field:
H Angle: 35.4°
V Angle: 35.4°
Lumens: 203.8
Efficiency: 82.4%

Spill:
Lumens: 43.5
Efficiency: 17.6%

— Vertical Distribution through 0-Deg
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	1
35°	0	0	0	0	0	0	0	0	0	0	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	2
25°	0	0	0	0	0	0	0	1	1	1	2
22.5°	0	0	0	0	0	0	0	1	1	2	2
20°	0	0	0	0	0	0	1	1	1	2	2
17.5°	0	0	0	0	0	0	1	1	2	2	2
15°	0	0	0	0	0	0	1	1	2	2	3
12.5°	0	0	0	0	0	0	1	1	2	2	3
10°	0	0	0	0	0	1	1	1	2	2	3
7.5°	0	0	0	0	0	1	1	2	2	2	3
5°	0	0	0	0	0	1	1	2	2	3	4
2.5°	0	0	0	0	0	1	1	2	2	3	4
0°	0	0	0	0	0	1	1	2	2	3	4
-2.5°	0	0	0	0	0	1	1	2	2	3	4
-5°	0	0	0	0	0	1	1	2	2	3	4
-7.5°	0	0	0	0	0	1	1	2	2	2	3
-10°	0	0	0	0	0	1	1	1	2	2	3
-12.5°	0	0	0	0	0	0	1	1	2	2	3
-15°	0	0	0	0	0	0	1	1	2	2	3
-17.5°	0	0	0	0	0	0	1	1	2	2	2
-20°	0	0	0	0	0	0	1	1	1	2	2



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	0	0	0	0	0	1	1	2	2
-25°	0	0	0	0	0	0	0	1	1	1	2
-27.5°	0	0	0	0	0	0	0	0	1	1	2
-30°	0	0	0	0	0	0	0	0	1	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	0	1
-37.5°	0	0	0	0	0	0	0	0	0	0	1
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	1
47.5°	0	0	0	0	0	0	1	1	1	1	1
45°	0	0	0	0	1	1	1	1	1	1	1
42.5°	0	0	1	1	1	1	1	2	2	2	2
40°	0	1	1	1	1	2	2	2	2	2	2
37.5°	1	1	1	2	2	2	2	2	3	3	3
35°	1	1	2	2	2	2	3	3	4	4	5
32.5°	1	2	2	2	3	3	4	4	5	6	7
30°	2	2	2	3	3	4	5	6	7	9	10
27.5°	2	2	3	3	4	6	7	9	11	14	18
25°	2	3	3	4	6	8	10	13	19	25	33
22.5°	2	3	4	6	8	11	15	23	33	44	56
20°	3	4	5	7	10	15	24	37	52	72	91
17.5°	3	4	6	9	13	23	37	56	80	109	137
15°	4	5	7	11	19	33	52	80	116	156	201
12.5°	4	6	9	14	25	44	72	109	156	212	281
10°	5	7	10	18	33	56	91	137	201	281	381
7.5°	5	7	12	22	40	69	111	170	248	352	490
5°	5	8	13	24	45	78	126	195	288	425	636
2.5°	5	8	13	26	48	84	136	210	314	471	733
0°	6	8	14	27	49	86	139	215	322	488	767
-2.5°	5	8	13	26	48	84	136	210	314	471	733
-5°	5	8	13	24	45	78	126	195	288	425	636
-7.5°	5	7	12	22	40	69	111	170	248	352	490
-10°	5	7	10	18	33	56	91	137	201	281	381
-12.5°	4	6	9	14	25	44	72	109	156	212	281
-15°	4	5	7	11	19	33	52	80	116	156	201
-17.5°	3	4	6	9	13	23	37	56	80	109	137
-20°	3	4	5	7	10	15	24	37	52	72	91



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	2	3	4	6	8	11	15	23	33	44	56
-25°	2	3	3	4	6	8	10	13	19	25	33
-27.5°	2	2	3	3	4	6	7	9	11	14	18
-30°	2	2	2	3	3	4	5	6	7	9	10
-32.5°	1	2	2	2	3	3	4	4	5	6	7
-35°	1	1	2	2	2	2	3	3	4	4	5
-37.5°	1	1	1	2	2	2	2	2	3	3	3
-40°	0	1	1	1	1	2	2	2	2	2	2
-42.5°	0	0	1	1	1	1	1	2	2	2	2
-45°	0	0	0	0	1	1	1	1	1	1	1
-47.5°	0	0	0	0	0	0	1	1	1	1	1
-50°	0	0	0	0	0	0	0	0	0	0	1
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	1	1	1	1	1	1	1	1	0	0	0
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	2	2	2	2	2	2	2	1	1	1	1
42.5°	2	2	2	2	2	2	2	2	2	2	2
40°	2	3	3	3	3	3	2	2	2	2	2
37.5°	3	4	4	4	4	4	3	3	3	3	2
35°	5	5	5	6	5	5	5	5	4	4	3
32.5°	7	8	8	8	8	8	7	7	6	5	4
30°	12	13	13	14	13	13	12	10	9	7	6
27.5°	22	24	26	27	26	24	22	18	14	11	9
25°	40	45	48	49	48	45	40	33	25	19	13
22.5°	69	78	84	86	84	78	69	56	44	33	23
20°	111	126	136	139	136	126	111	91	72	52	37
17.5°	170	195	210	215	210	195	170	137	109	80	56
15°	248	288	314	322	314	288	248	201	156	116	80
12.5°	352	425	471	488	471	425	352	281	212	156	109
10°	490	636	733	767	733	636	490	381	281	201	137
7.5°	701	907	1074	1139	1074	907	701	490	352	248	170
5°	907	1210	1445	1536	1445	1210	907	636	425	288	195
2.5°	1074	1445	1765	1902	1765	1445	1074	733	471	314	210
0°	1139	1536	1902	2094	1902	1536	1139	767	488	322	215
-2.5°	1074	1445	1765	1902	1765	1445	1074	733	471	314	210
-5°	907	1210	1445	1536	1445	1210	907	636	425	288	195
-7.5°	701	907	1074	1139	1074	907	701	490	352	248	170
-10°	490	636	733	767	733	636	490	381	281	201	137
-12.5°	352	425	471	488	471	425	352	281	212	156	109
-15°	248	288	314	322	314	288	248	201	156	116	80
-17.5°	170	195	210	215	210	195	170	137	109	80	56
-20°	111	126	136	139	136	126	111	91	72	52	37



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	69	78	84	86	84	78	69	56	44	33	23
-25°	40	45	48	49	48	45	40	33	25	19	13
-27.5°	22	24	26	27	26	24	22	18	14	11	9
-30°	12	13	13	14	13	13	12	10	9	7	6
-32.5°	7	8	8	8	8	8	7	7	6	5	4
-35°	5	5	5	6	5	5	5	5	4	4	3
-37.5°	3	4	4	4	4	4	3	3	3	3	2
-40°	2	3	3	3	3	3	2	2	2	2	2
-42.5°	2	2	2	2	2	2	2	2	2	2	2
-45°	2	2	2	2	2	2	2	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	1	0	0	0	0	0	0	0	0	0	0
45°	1	1	1	0	0	0	0	0	0	0	0
42.5°	1	1	1	1	1	0	0	0	0	0	0
40°	2	2	1	1	1	1	0	0	0	0	0
37.5°	2	2	2	2	1	1	1	1	0	0	0
35°	3	2	2	2	2	1	1	1	0	0	0
32.5°	4	3	3	2	2	2	1	1	1	0	0
30°	5	4	3	3	2	2	2	1	1	1	0
27.5°	7	6	4	3	3	2	2	2	1	1	0
25°	10	8	6	4	3	3	2	2	1	1	1
22.5°	15	11	8	6	4	3	2	2	2	1	1
20°	24	15	10	7	5	4	3	2	2	1	1
17.5°	37	23	13	9	6	4	3	2	2	2	1
15°	52	33	19	11	7	5	4	3	2	2	1
12.5°	72	44	25	14	9	6	4	3	2	2	1
10°	91	56	33	18	10	7	5	3	2	2	1
7.5°	111	69	40	22	12	7	5	3	2	2	2
5°	126	78	45	24	13	8	5	4	3	2	2
2.5°	136	84	48	26	13	8	5	4	3	2	2
0°	139	86	49	27	14	8	6	4	3	2	2
-2.5°	136	84	48	26	13	8	5	4	3	2	2
-5°	126	78	45	24	13	8	5	4	3	2	2
-7.5°	111	69	40	22	12	7	5	3	2	2	2
-10°	91	56	33	18	10	7	5	3	2	2	1
-12.5°	72	44	25	14	9	6	4	3	2	2	1
-15°	52	33	19	11	7	5	4	3	2	2	1
-17.5°	37	23	13	9	6	4	3	2	2	2	1
-20°	24	15	10	7	5	4	3	2	2	1	1



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	15	11	8	6	4	3	2	2	2	1	1
-25°	10	8	6	4	3	3	2	2	1	1	1
-27.5°	7	6	4	3	3	2	2	2	1	1	0
-30°	5	4	3	3	2	2	2	1	1	1	0
-32.5°	4	3	3	2	2	2	1	1	1	0	0
-35°	3	2	2	2	2	1	1	1	0	0	0
-37.5°	2	2	2	2	1	1	1	1	0	0	0
-40°	2	2	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	0	0	0	0	0	0	0	0
-47.5°	1	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	1	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
15°	1	0	0	0	0	0	0	0	0	0	0
12.5°	1	0	0	0	0	0	0	0	0	0	0
10°	1	1	0	0	0	0	0	0	0	0	0
7.5°	1	1	0	0	0	0	0	0	0	0	0
5°	1	1	0	0	0	0	0	0	0	0	0
2.5°	1	1	0	0	0	0	0	0	0	0	0
0°	1	1	0	0	0	0	0	0	0	0	0
-2.5°	1	1	0	0	0	0	0	0	0	0	0
-5°	1	1	0	0	0	0	0	0	0	0	0
-7.5°	1	1	0	0	0	0	0	0	0	0	0
-10°	1	1	0	0	0	0	0	0	0	0	0
-12.5°	1	0	0	0	0	0	0	0	0	0	0
-15°	1	0	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: P247019 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-8LED2725-12-BK-LVR

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)