

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220542

Luminaire Tested: **9003-W1-[RW, RI]-LED3597-F-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220542  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29474)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED3597-F-BK-L1-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 707.2 lumens  
Efficiency: N/A  
Efficacy: 72.2 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220542

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-F-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220542

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-F-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	86	99	93	89	86	91	88	85	90	87	85	89	86	84	83
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	80	78	77
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	452201
5°	442460
10°	389973
15°	301296
20°	187126
25°	69319
30°	14509
35°	5461
40°	1975
45°	1333
50°	1194
55°	994
60°	746
65°	467
70°	256
75°	0
80°	0
85°	0



TEST NUMBER: P220542

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-F-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.6	26.0
10°-20°	356.1	50.4
20°-30°	145.1	20.5
30°-40°	15.3	2.2
40°-50°	3.6	0.5
50°-60°	2.3	0.3
60°-70°	1.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	684.8	96.8
0°-40°	700.1	99.0
0°-60°	706.0	99.8
0°-90°	707.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	707.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2062	
5°	2010	184
15°	1327	356
25°	286	145
35°	20	15
45°	4	4
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220542

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-F-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2062.2
1°	2057.0
2°	2050.9
3°	2045.3
4°	2034.0
5°	2010.1
6°	1977.6
7°	1935.0
8°	1880.8
9°	1819.1
10°	1751.4
11°	1677.1
12°	1598.1
13°	1515.6
14°	1425.3
15°	1327.2
16°	1227.4
17°	1116.6
18°	1013.3
19°	905.6
20°	801.9
21°	700.7
22°	593.5
23°	484.1
24°	380.3
25°	286.5
26°	205.4
27°	139.8
28°	92.5
29°	68.6
30°	57.3
32.5°	37.8
35°	20.4
37.5°	11.3
40°	6.9
42.5°	5.2
45°	4.3
47.5°	3.9
50°	3.5
52.5°	3.0
55°	2.6
57.5°	2.2
60°	1.7
62.5°	1.3
65°	0.9



TEST NUMBER: P220542

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-F-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.9
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)