

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-8LED2725-12-CS-LVR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-42)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-8LED2725-12-CS-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, HEX CELL LOUVER
Light Source: (1) SORAA 2700K 90 CRI LED
SM16-07-25D-927-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

Summary


Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	230.7 lumens	Max Intensity:	1909.8 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	32.0 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	16.3°H x 16.3°V	Field Angle (10%):	36°H x 36°V
Beam Lumens:	80.8 lumens	Field Lumens:	187.6 lumens
Beam Efficiency:	35.0%	Field Efficiency:	81.3%
Input Watts (W):	7.2		
Input Voltage (V):	NR		
Input Current (A _{in}):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-8LED2725-12-CS-LVR

Iso-Candela Plot






REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

Lumen Table

90	0.0															
80	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0	
70	0.0															
60	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0	
50	0.0															
40	0.0		0.0		0.0		0.1		0.1		0.0		0.0		0.0	
30	0.0															
20	0.0		0.0		0.1		0.2		0.7		1.5		1.5		0.7	
10	0.0		0.0		0.1		0.7		3.5		8.8		8.8		3.5	
0	0.0		0.0		0.2		1.4		8.5		31.2		31.2		8.5	
-10	0.0		0.0		0.2		1.4		8.5		31.2		31.2		8.5	
-20	0.0		0.0		0.1		0.7		3.5		8.8		8.8		3.5	
-30	0.0															
-40	0.0		0.0		0.0		0.1		0.1		0.2		0.2		0.1	
-50	0.0															
-60	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0	
-70	0.0															
-80	0.0		0.0		0.0		0.0		0.0		0.0		0.0		0.0	
-90	0.0															


REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED2725-12-CS-LVR

Luminous Intensity Polar Plot



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

Luminous Intensity Plot



Beam:
 H Angle: 16.3°
 V Angle: 16.3°
 Lumens: 80.8
 Efficiency: 35.0%

Field:
 H Angle: 36°
 V Angle: 36°
 Lumens: 187.6
 Efficiency: 81.3%

Spill:
 Lumens: 43.1
 Efficiency: 18.7%

— Vertical Distribution through 0-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	1
42.5°	0	0	0	0	0	0	0	0	0	1	1
40°	0	0	0	0	0	0	0	0	1	1	1
37.5°	0	0	0	0	0	0	0	1	1	1	1
35°	0	0	0	0	0	0	0	1	1	1	1
32.5°	0	0	0	0	0	0	1	1	1	1	1
30°	0	0	0	0	0	0	1	1	1	1	1
27.5°	0	0	0	0	0	1	1	1	1	1	2
25°	0	0	0	0	0	1	1	1	1	1	2
22.5°	0	0	0	0	1	1	1	1	1	2	3
20°	0	0	0	0	1	1	1	1	1	2	3
17.5°	0	0	0	0	1	1	1	1	2	2	3
15°	0	0	0	0	1	1	1	1	2	3	4
12.5°	0	0	0	1	1	1	1	1	2	3	4
10°	0	0	0	1	1	1	1	1	2	3	4
7.5°	0	0	0	1	1	1	1	2	3	3	4
5°	0	0	0	1	1	1	1	2	3	4	4
2.5°	0	0	0	1	1	1	1	2	3	4	5
0°	0	0	0	1	1	1	1	2	3	4	5
-2.5°	0	0	0	1	1	1	1	2	3	4	5
-5°	0	0	0	1	1	1	1	2	3	4	4
-7.5°	0	0	0	1	1	1	1	2	3	3	4
-10°	0	0	0	1	1	1	1	1	2	3	4
-12.5°	0	0	0	1	1	1	1	1	2	3	4
-15°	0	0	0	0	1	1	1	1	2	3	4
-17.5°	0	0	0	0	1	1	1	1	2	2	3
-20°	0	0	0	0	1	1	1	1	1	2	3



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	0	0	1	1	1	1	1	2	3
-25°	0	0	0	0	0	1	1	1	1	1	2
-27.5°	0	0	0	0	0	1	1	1	1	1	2
-30°	0	0	0	0	0	0	1	1	1	1	1
-32.5°	0	0	0	0	0	0	1	1	1	1	1
-35°	0	0	0	0	0	0	0	1	1	1	1
-37.5°	0	0	0	0	0	0	0	1	1	1	1
-40°	0	0	0	0	0	0	0	0	1	1	1
-42.5°	0	0	0	0	0	0	0	0	0	1	1
-45°	0	0	0	0	0	0	0	0	0	0	1
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	1	1
52.5°	0	0	0	0	0	1	1	1	1	1	1
50°	0	0	0	1	1	1	1	1	1	1	1
47.5°	0	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	2	2	2	2
40°	1	1	1	1	1	2	2	2	3	3	3
37.5°	1	1	1	2	2	3	3	3	4	4	4
35°	1	1	2	2	3	3	4	4	5	5	6
32.5°	1	2	2	3	4	4	5	5	6	7	8
30°	2	2	3	4	4	5	6	7	9	10	12
27.5°	2	3	4	4	5	6	9	10	12	14	17
25°	3	4	4	5	7	9	11	13	18	24	31
22.5°	3	4	5	6	9	12	15	21	30	41	55
20°	4	5	6	9	11	15	22	34	51	69	87
17.5°	4	5	7	10	13	21	34	54	77	105	133
15°	5	6	9	12	18	30	51	77	112	149	190
12.5°	5	7	10	14	24	41	69	105	149	202	262
10°	6	8	12	17	31	55	87	133	190	262	348
7.5°	6	9	12	20	36	67	107	160	233	326	459
5°	6	10	13	23	43	75	122	184	269	389	577
2.5°	6	10	14	25	47	80	131	200	294	438	674
0°	6	10	14	26	48	82	134	206	303	457	709
-2.5°	6	10	14	25	47	80	131	200	294	438	674
-5°	6	10	13	23	43	75	122	184	269	389	577
-7.5°	6	9	12	20	36	67	107	160	233	326	459
-10°	6	8	12	17	31	55	87	133	190	262	348
-12.5°	5	7	10	14	24	41	69	105	149	202	262
-15°	5	6	9	12	18	30	51	77	112	149	190
-17.5°	4	5	7	10	13	21	34	54	77	105	133
-20°	4	5	6	9	11	15	22	34	51	69	87



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	3	4	5	6	9	12	15	21	30	41	55
-25°	3	4	4	5	7	9	11	13	18	24	31
-27.5°	2	3	4	4	5	6	9	10	12	14	17
-30°	2	2	3	4	4	5	6	7	9	10	12
-32.5°	1	2	2	3	4	4	5	5	6	7	8
-35°	1	1	2	2	3	3	4	4	5	5	6
-37.5°	1	1	1	2	2	3	3	3	4	4	4
-40°	1	1	1	1	1	2	2	2	3	3	3
-42.5°	1	1	1	1	1	1	1	2	2	2	2
-45°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	0	1	1	1	1	1	1	1	1	1	1
-50°	0	0	0	1	1	1	1	1	1	1	1
-52.5°	0	0	0	0	0	1	1	1	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	1	1	1	1	1	1	1	1	1	0	0
52.5°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	2	2	2	2	2	2	2	1	1	1	1
42.5°	3	3	3	3	3	3	3	2	2	2	2
40°	3	4	4	4	4	4	3	3	3	3	2
37.5°	4	4	5	5	5	4	4	4	4	4	3
35°	6	6	6	6	6	6	6	6	5	5	4
32.5°	9	10	10	10	10	10	9	8	7	6	5
30°	12	13	14	14	14	13	12	12	10	9	7
27.5°	20	23	25	26	25	23	20	17	14	12	10
25°	36	43	47	48	47	43	36	31	24	18	13
22.5°	67	75	80	82	80	75	67	55	41	30	21
20°	107	122	131	134	131	122	107	87	69	51	34
17.5°	160	184	200	206	200	184	160	133	105	77	54
15°	233	269	294	303	294	269	233	190	149	112	77
12.5°	326	389	438	457	438	389	326	262	202	149	105
10°	459	577	674	709	674	577	459	348	262	190	133
7.5°	641	835	988	1045	988	835	641	459	326	233	160
5°	835	1107	1322	1409	1322	1107	835	577	389	269	184
2.5°	988	1322	1610	1734	1610	1322	988	674	438	294	200
0°	1045	1409	1734	1910	1734	1409	1045	709	457	303	206
-2.5°	988	1322	1610	1734	1610	1322	988	674	438	294	200
-5°	835	1107	1322	1409	1322	1107	835	577	389	269	184
-7.5°	641	835	988	1045	988	835	641	459	326	233	160
-10°	459	577	674	709	674	577	459	348	262	190	133
-12.5°	326	389	438	457	438	389	326	262	202	149	105
-15°	233	269	294	303	294	269	233	190	149	112	77
-17.5°	160	184	200	206	200	184	160	133	105	77	54
-20°	107	122	131	134	131	122	107	87	69	51	34



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	67	75	80	82	80	75	67	55	41	30	21
-25°	36	43	47	48	47	43	36	31	24	18	13
-27.5°	20	23	25	26	25	23	20	17	14	12	10
-30°	12	13	14	14	14	13	12	12	10	9	7
-32.5°	9	10	10	10	10	10	9	8	7	6	5
-35°	6	6	6	6	6	6	6	6	5	5	4
-37.5°	4	4	5	5	5	4	4	4	4	4	3
-40°	3	4	4	4	4	4	3	3	3	3	2
-42.5°	3	3	3	3	3	3	3	2	2	2	2
-45°	2	2	2	2	2	2	2	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	1	1	0	0	0	0	0	0	0	0	0
50°	1	1	1	1	0	0	0	0	0	0	0
47.5°	1	1	1	1	1	1	0	0	0	0	0
45°	1	1	1	1	1	1	1	1	0	0	0
42.5°	1	1	1	1	1	1	1	1	1	0	0
40°	2	2	1	1	1	1	1	1	1	1	0
37.5°	3	3	2	2	1	1	1	1	1	1	1
35°	4	3	3	2	2	1	1	1	1	1	1
32.5°	5	4	4	3	2	2	1	1	1	1	1
30°	6	5	4	4	3	2	2	1	1	1	1
27.5°	9	6	5	4	4	3	2	2	1	1	1
25°	11	9	7	5	4	4	3	2	1	1	1
22.5°	15	12	9	6	5	4	3	3	2	1	1
20°	22	15	11	9	6	5	4	3	2	1	1
17.5°	34	21	13	10	7	5	4	3	2	2	1
15°	51	30	18	12	9	6	5	4	3	2	1
12.5°	69	41	24	14	10	7	5	4	3	2	1
10°	87	55	31	17	12	8	6	4	3	2	1
7.5°	107	67	36	20	12	9	6	4	3	3	2
5°	122	75	43	23	13	10	6	4	4	3	2
2.5°	131	80	47	25	14	10	6	5	4	3	2
0°	134	82	48	26	14	10	6	5	4	3	2
-2.5°	131	80	47	25	14	10	6	5	4	3	2
-5°	122	75	43	23	13	10	6	4	4	3	2
-7.5°	107	67	36	20	12	9	6	4	3	3	2
-10°	87	55	31	17	12	8	6	4	3	2	1
-12.5°	69	41	24	14	10	7	5	4	3	2	1
-15°	51	30	18	12	9	6	5	4	3	2	1
-17.5°	34	21	13	10	7	5	4	3	2	2	1
-20°	22	15	11	9	6	5	4	3	2	1	1



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	15	12	9	6	5	4	3	3	2	1	1
-25°	11	9	7	5	4	4	3	2	1	1	1
-27.5°	9	6	5	4	4	3	2	2	1	1	1
-30°	6	5	4	4	3	2	2	1	1	1	1
-32.5°	5	4	4	3	2	2	1	1	1	1	1
-35°	4	3	3	2	2	1	1	1	1	1	1
-37.5°	3	3	2	2	1	1	1	1	1	1	1
-40°	2	2	1	1	1	1	1	1	1	1	0
-42.5°	1	1	1	1	1	1	1	1	1	0	0
-45°	1	1	1	1	1	1	1	1	0	0	0
-47.5°	1	1	1	1	1	1	0	0	0	0	0
-50°	1	1	1	1	0	0	0	0	0	0	0
-52.5°	1	1	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	1	0	0	0	0	0	0	0	0	0	0
30°	1	0	0	0	0	0	0	0	0	0	0
27.5°	1	1	0	0	0	0	0	0	0	0	0
25°	1	1	0	0	0	0	0	0	0	0	0
22.5°	1	1	1	0	0	0	0	0	0	0	0
20°	1	1	1	0	0	0	0	0	0	0	0
17.5°	1	1	1	0	0	0	0	0	0	0	0
15°	1	1	1	0	0	0	0	0	0	0	0
12.5°	1	1	1	1	0	0	0	0	0	0	0
10°	1	1	1	1	0	0	0	0	0	0	0
7.5°	1	1	1	1	0	0	0	0	0	0	0
5°	1	1	1	1	0	0	0	0	0	0	0
2.5°	1	1	1	1	0	0	0	0	0	0	0
0°	1	1	1	1	0	0	0	0	0	0	0
-2.5°	1	1	1	1	0	0	0	0	0	0	0
-5°	1	1	1	1	0	0	0	0	0	0	0
-7.5°	1	1	1	1	0	0	0	0	0	0	0
-10°	1	1	1	1	0	0	0	0	0	0	0
-12.5°	1	1	1	1	0	0	0	0	0	0	0
-15°	1	1	1	0	0	0	0	0	0	0	0
-17.5°	1	1	1	0	0	0	0	0	0	0	0
-20°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	1	1	1	0	0	0	0	0	0	0	0
-25°	1	1	0	0	0	0	0	0	0	0	0
-27.5°	1	1	0	0	0	0	0	0	0	0	0
-30°	1	0	0	0	0	0	0	0	0	0	0
-32.5°	1	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: P247024 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED2725-12-CS-LVR

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)