

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220525

Luminaire Tested: **9003-W1-[RW, RI]-LED3597-M-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220525  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29473)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED3597-M-BK-L1-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, MEDIUM FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 3500K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 626.2 lumens  
Efficiency: N/A  
Efficacy: 63.9 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.4  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220525

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-M-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220525

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-M-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	88	93	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	85	91	87	85	89	87	84	88	86	84	83
7	96	90	86	83	95	89	85	83	88	85	82	87	84	82	86	83	81	80
8	94	87	83	80	93	87	83	80	86	82	80	85	82	80	84	81	79	78
9	91	85	81	78	90	84	80	78	83	80	78	83	80	77	82	79	77	76
10	89	82	78	76	88	82	78	76	81	78	76	81	78	75	80	77	75	74

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	658412
5°	590027
10°	414533
15°	222453
20°	117004
25°	52309
30°	10103
35°	3721
40°	2118
45°	1737
50°	1467
55°	1147
60°	965
65°	675
70°	256
75°	0
80°	0
85°	0



TEST NUMBER: P220525

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-M-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	229.3	36.6
10°-20°	276.4	44.1
20°-30°	100.8	16.1
30°-40°	11.1	1.8
40°-50°	4.4	0.7
50°-60°	2.8	0.4
60°-70°	1.3	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	606.5	96.9
0°-40°	617.7	98.6
0°-60°	624.8	99.8
0°-90°	626.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	626.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3003	
5°	2680	229
15°	980	276
25°	216	101
35°	14	11
45°	6	4
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220525

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-M-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3002.6
1°	2978.3
2°	2935.7
3°	2873.2
4°	2786.8
5°	2680.5
6°	2553.3
7°	2403.9
8°	2234.6
9°	2050.9
10°	1861.7
11°	1671.1
12°	1482.2
13°	1303.8
14°	1133.6
15°	979.9
16°	838.8
17°	723.7
18°	630.4
19°	556.6
20°	501.4
21°	456.3
22°	404.6
23°	343.4
24°	279.6
25°	216.2
26°	155.9
27°	102.0
28°	64.3
29°	46.9
30°	39.9
32.5°	26.9
35°	13.9
37.5°	9.1
40°	7.4
42.5°	6.5
45°	5.6
47.5°	4.8
50°	4.3
52.5°	3.5
55°	3.0
57.5°	2.6
60°	2.2
62.5°	1.7
65°	1.3



TEST NUMBER: P220525

CATALOG NUMBER: 9003-W1-[RW, RI]-LED3597-M-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.9
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)