

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-8LED2736-12-BK-OSL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-35)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-8LED2736-12-BK-OSL  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD BLACK, OVERALL SPREAD LENS  
Light Source: (1) SORAA 2700K 95 CRI LED  
SM16-07-36D-927-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	308.1 lumens	Max Intensity:	850.8 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	40.0 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	34.5°H x 34.5°V	Field Angle (10%):	58°H x 58°V
Beam Lumens:	172.8 lumens	Field Lumens:	285.3 lumens
Beam Efficiency:	56.1%	Field Efficiency:	92.6%
Input Watts (W):	7.7		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-8LED2736-12-BK-OSL

### Iso-Candela Plot






REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

### Lumen Table

90	0.0															
80	0.0															
70	0.0															
60	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50	0.0															
40	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30	0.0															
20	0.0	0.0	0.0	0.1	0.7	2.7	5.0	5.0	2.7	0.7	0.1	0.0	0.0	0.0	0.0	0.0
10	0.0															
0	0.0	0.0	0.1	0.6	4.6	13.8	22.4	22.4	13.8	4.6	0.6	0.1	0.0	0.0	0.0	0.0
-10	0.0															
-20	0.0	0.0	0.0	0.3	2.6	8.5	14.2	14.2	8.5	2.6	0.3	0.0	0.0	0.0	0.0	0.0
-30	0.0															
-40	0.0	0.0	0.0	0.0	0.1	0.4	0.7	0.7	0.4	0.1	0.0	0.0	0.0	0.0	0.0	0.0
-50	0.0															
-60	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-70	0.0															
-80	0.0															
-90	0.0															

REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-8LED2736-12-BK-OSL


### Luminous Intensity Polar Plot



— Vertical Distribution Through 0-Deg      - - - Horizontal Distribution Through 0-Deg

REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

### Luminous Intensity Plot



**Beam:**  
 H Angle: 34.5°  
 V Angle: 34.5°  
 Lumens: 172.8  
 Efficiency: 56.1%

**Field:**  
 H Angle: 58°  
 V Angle: 58°  
 Lumens: 285.3  
 Efficiency: 92.6%

**Spill:**  
 Lumens: 22.7  
 Efficiency: 7.4%

- Vertical Distribution through 0-Deg
- - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	1
45°	0	0	0	0	0	0	0	0	1	1	1
42.5°	0	0	0	0	0	0	0	1	1	1	1
40°	0	0	0	0	0	0	0	1	1	1	1
37.5°	0	0	0	0	0	0	1	1	1	1	1
35°	0	0	0	0	0	1	1	1	1	1	1
32.5°	0	0	0	0	0	1	1	1	1	1	2
30°	0	0	0	0	1	1	1	1	1	1	2
27.5°	0	0	0	0	1	1	1	1	1	2	3
25°	0	0	0	0	1	1	1	1	2	2	3
22.5°	0	0	0	1	1	1	1	1	2	3	4
20°	0	0	0	1	1	1	1	1	2	3	4
17.5°	0	0	0	1	1	1	1	2	3	3	6
15°	0	0	0	1	1	1	1	2	3	4	6
12.5°	0	0	1	1	1	1	1	2	3	5	8
10°	0	0	1	1	1	1	2	2	3	5	8
7.5°	0	0	1	1	1	1	2	3	3	6	9
5°	0	0	1	1	1	1	2	3	4	6	10
2.5°	0	0	1	1	1	1	2	3	4	6	10
0°	0	0	1	1	1	1	2	3	4	6	10
-2.5°	0	0	1	1	1	1	2	3	4	6	10
-5°	0	0	1	1	1	1	2	3	4	6	10
-7.5°	0	0	1	1	1	1	2	3	3	6	9
-10°	0	0	1	1	1	1	2	2	3	5	8
-12.5°	0	0	1	1	1	1	1	2	3	5	8
-15°	0	0	0	1	1	1	1	2	3	4	6
-17.5°	0	0	0	1	1	1	1	2	3	3	6
-20°	0	0	0	1	1	1	1	1	2	3	4



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	0	1	1	1	1	1	2	3	4
-25°	0	0	0	0	1	1	1	1	2	2	3
-27.5°	0	0	0	0	1	1	1	1	1	2	3
-30°	0	0	0	0	1	1	1	1	1	1	2
-32.5°	0	0	0	0	0	1	1	1	1	1	2
-35°	0	0	0	0	0	1	1	1	1	1	1
-37.5°	0	0	0	0	0	0	1	1	1	1	1
-40°	0	0	0	0	0	0	0	1	1	1	1
-42.5°	0	0	0	0	0	0	0	1	1	1	1
-45°	0	0	0	0	0	0	0	0	1	1	1
-47.5°	0	0	0	0	0	0	0	0	0	0	1
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	1	1
55°	0	0	0	0	0	1	1	1	1	1	1
52.5°	0	0	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	2
45°	1	1	1	1	1	1	1	2	2	2	2
42.5°	1	1	1	1	2	2	2	3	3	3	3
40°	1	1	1	2	2	3	3	3	4	5	5
37.5°	1	2	2	3	3	4	4	6	6	8	8
35°	2	2	3	3	4	6	7	8	10	12	14
32.5°	2	3	3	5	6	8	10	13	17	21	25
30°	3	3	5	7	9	12	17	22	29	36	46
27.5°	3	5	7	9	13	18	27	37	52	66	80
25°	4	6	9	13	20	29	45	63	84	107	129
22.5°	6	8	12	18	29	47	70	98	128	157	184
20°	7	10	17	27	45	70	102	139	176	213	250
17.5°	8	13	22	37	63	98	139	183	230	278	322
15°	10	17	29	52	84	128	176	230	287	346	399
12.5°	12	21	36	66	107	157	213	278	346	412	471
10°	14	25	46	80	129	184	250	322	399	471	538
7.5°	16	28	55	94	146	207	281	362	443	522	600
5°	17	31	61	104	160	226	305	391	477	563	647
2.5°	18	32	64	111	168	238	320	410	498	590	677
0°	18	33	66	113	171	242	325	416	506	599	687
-2.5°	18	32	64	111	168	238	320	410	498	590	677
-5°	17	31	61	104	160	226	305	391	477	563	647
-7.5°	16	28	55	94	146	207	281	362	443	522	600
-10°	14	25	46	80	129	184	250	322	399	471	538
-12.5°	12	21	36	66	107	157	213	278	346	412	471
-15°	10	17	29	52	84	128	176	230	287	346	399
-17.5°	8	13	22	37	63	98	139	183	230	278	322
-20°	7	10	17	27	45	70	102	139	176	213	250



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	6	8	12	18	29	47	70	98	128	157	184
-25°	4	6	9	13	20	29	45	63	84	107	129
-27.5°	3	5	7	9	13	18	27	37	52	66	80
-30°	3	3	5	7	9	12	17	22	29	36	46
-32.5°	2	3	3	5	6	8	10	13	17	21	25
-35°	2	2	3	3	4	6	7	8	10	12	14
-37.5°	1	2	2	3	3	4	4	6	6	8	8
-40°	1	1	1	2	2	3	3	3	4	5	5
-42.5°	1	1	1	1	2	2	2	3	3	3	3
-45°	1	1	1	1	1	1	1	2	2	2	2
-47.5°	1	1	1	1	1	1	1	1	1	1	2
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	0	0	1	1	1	1	1	1	1	1	1
-55°	0	0	0	0	0	1	1	1	1	1	1
-57.5°	0	0	0	0	0	0	0	0	0	1	1
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	1	1	1	1	1	1	1	0	0
55°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	2	2	2	2	2	2	2	2	1	1	1
45°	3	3	3	3	3	3	3	2	2	2	2
42.5°	3	4	4	4	4	4	3	3	3	3	3
40°	6	6	6	6	6	6	6	5	5	4	3
37.5°	9	10	10	10	10	10	9	8	8	6	6
35°	16	17	18	18	18	17	16	14	12	10	8
32.5°	28	31	32	33	32	31	28	25	21	17	13
30°	55	61	64	66	64	61	55	46	36	29	22
27.5°	94	104	111	113	111	104	94	80	66	52	37
25°	146	160	168	171	168	160	146	129	107	84	63
22.5°	207	226	238	242	238	226	207	184	157	128	98
20°	281	305	320	325	320	305	281	250	213	176	139
17.5°	362	391	410	416	410	391	362	322	278	230	183
15°	443	477	498	506	498	477	443	399	346	287	230
12.5°	522	563	590	599	590	563	522	471	412	346	278
10°	600	647	677	687	677	647	600	538	471	399	322
7.5°	667	718	751	761	751	718	667	600	522	443	362
5°	718	772	801	810	801	772	718	647	563	477	391
2.5°	751	801	824	832	824	801	751	677	590	498	410
0°	761	810	832	851	832	810	761	687	599	506	416
-2.5°	751	801	824	832	824	801	751	677	590	498	410
-5°	718	772	801	810	801	772	718	647	563	477	391
-7.5°	667	718	751	761	751	718	667	600	522	443	362
-10°	600	647	677	687	677	647	600	538	471	399	322
-12.5°	522	563	590	599	590	563	522	471	412	346	278
-15°	443	477	498	506	498	477	443	399	346	287	230
-17.5°	362	391	410	416	410	391	362	322	278	230	183
-20°	281	305	320	325	320	305	281	250	213	176	139



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	207	226	238	242	238	226	207	184	157	128	98
-25°	146	160	168	171	168	160	146	129	107	84	63
-27.5°	94	104	111	113	111	104	94	80	66	52	37
-30°	55	61	64	66	64	61	55	46	36	29	22
-32.5°	28	31	32	33	32	31	28	25	21	17	13
-35°	16	17	18	18	18	17	16	14	12	10	8
-37.5°	9	10	10	10	10	10	9	8	8	6	6
-40°	6	6	6	6	6	6	6	5	5	4	3
-42.5°	3	4	4	4	4	4	3	3	3	3	3
-45°	3	3	3	3	3	3	3	2	2	2	2
-47.5°	2	2	2	2	2	2	2	2	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	1	1	0	0	0	0	0	0	0	0	0
52.5°	1	1	1	1	1	0	0	0	0	0	0
50°	1	1	1	1	1	1	1	0	0	0	0
47.5°	1	1	1	1	1	1	1	1	0	0	0
45°	1	1	1	1	1	1	1	1	1	1	0
42.5°	2	2	2	1	1	1	1	1	1	1	1
40°	3	3	2	2	1	1	1	1	1	1	1
37.5°	4	4	3	3	2	2	1	1	1	1	1
35°	7	6	4	3	3	2	2	1	1	1	1
32.5°	10	8	6	5	3	3	2	2	1	1	1
30°	17	12	9	7	5	3	3	2	1	1	1
27.5°	27	18	13	9	7	5	3	3	2	1	1
25°	45	29	20	13	9	6	4	3	2	2	1
22.5°	70	47	29	18	12	8	6	4	3	2	1
20°	102	70	45	27	17	10	7	4	3	2	1
17.5°	139	98	63	37	22	13	8	6	3	3	2
15°	176	128	84	52	29	17	10	6	4	3	2
12.5°	213	157	107	66	36	21	12	8	5	3	2
10°	250	184	129	80	46	25	14	8	5	3	2
7.5°	281	207	146	94	55	28	16	9	6	3	3
5°	305	226	160	104	61	31	17	10	6	4	3
2.5°	320	238	168	111	64	32	18	10	6	4	3
0°	325	242	171	113	66	33	18	10	6	4	3
-2.5°	320	238	168	111	64	32	18	10	6	4	3
-5°	305	226	160	104	61	31	17	10	6	4	3
-7.5°	281	207	146	94	55	28	16	9	6	3	3
-10°	250	184	129	80	46	25	14	8	5	3	2
-12.5°	213	157	107	66	36	21	12	8	5	3	2
-15°	176	128	84	52	29	17	10	6	4	3	2
-17.5°	139	98	63	37	22	13	8	6	3	3	2
-20°	102	70	45	27	17	10	7	4	3	2	1



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	70	47	29	18	12	8	6	4	3	2	1
-25°	45	29	20	13	9	6	4	3	2	2	1
-27.5°	27	18	13	9	7	5	3	3	2	1	1
-30°	17	12	9	7	5	3	3	2	1	1	1
-32.5°	10	8	6	5	3	3	2	2	1	1	1
-35°	7	6	4	3	3	2	2	1	1	1	1
-37.5°	4	4	3	3	2	2	1	1	1	1	1
-40°	3	3	2	2	1	1	1	1	1	1	1
-42.5°	2	2	2	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	0
-47.5°	1	1	1	1	1	1	1	1	0	0	0
-50°	1	1	1	1	1	1	1	0	0	0	0
-52.5°	1	1	1	1	1	0	0	0	0	0	0
-55°	1	1	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	1	0	0	0	0	0	0	0	0	0	0
35°	1	1	0	0	0	0	0	0	0	0	0
32.5°	1	1	0	0	0	0	0	0	0	0	0
30°	1	1	1	0	0	0	0	0	0	0	0
27.5°	1	1	1	0	0	0	0	0	0	0	0
25°	1	1	1	0	0	0	0	0	0	0	0
22.5°	1	1	1	1	0	0	0	0	0	0	0
20°	1	1	1	1	0	0	0	0	0	0	0
17.5°	1	1	1	1	0	0	0	0	0	0	0
15°	1	1	1	1	0	0	0	0	0	0	0
12.5°	1	1	1	1	1	0	0	0	0	0	0
10°	2	1	1	1	1	0	0	0	0	0	0
7.5°	2	1	1	1	1	0	0	0	0	0	0
5°	2	1	1	1	1	0	0	0	0	0	0
2.5°	2	1	1	1	1	0	0	0	0	0	0
0°	2	1	1	1	1	0	0	0	0	0	0
-2.5°	2	1	1	1	1	0	0	0	0	0	0
-5°	2	1	1	1	1	0	0	0	0	0	0
-7.5°	2	1	1	1	1	0	0	0	0	0	0
-10°	2	1	1	1	1	0	0	0	0	0	0
-12.5°	1	1	1	1	1	0	0	0	0	0	0
-15°	1	1	1	1	0	0	0	0	0	0	0
-17.5°	1	1	1	1	0	0	0	0	0	0	0
-20°	1	1	1	1	0	0	0	0	0	0	0



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	1	1	1	1	0	0	0	0	0	0	0
-25°	1	1	1	0	0	0	0	0	0	0	0
-27.5°	1	1	1	0	0	0	0	0	0	0	0
-30°	1	1	1	0	0	0	0	0	0	0	0
-32.5°	1	1	0	0	0	0	0	0	0	0	0
-35°	1	1	0	0	0	0	0	0	0	0	0
-37.5°	1	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: P247030 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-8LED2736-12-BK-OSL

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)