

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220504

Luminaire Tested: **9003-W1-[RW, RI]-LED4080-S-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220504  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29472)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED4080-S-BK-L1-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, SPOT OPTIC, BLACK HOUSING.  
Light Source: (1) 4000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 823.3 lumens  
Efficiency: N/A  
Efficacy: 84.0 lumens/watt  
Spacing Criteria (0/90/45): 0.27 / 0.27 / 0.27  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220504

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-S-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220504

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-S-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	102	104	102	100	101	100	98	99	97	96	95
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	97	95	94	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88
6	101	95	92	89	100	95	91	89	93	90	88	92	90	88	91	89	87	86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84
8	96	91	87	84	95	90	87	84	89	86	84	88	86	84	88	85	83	82
9	94	88	85	82	94	88	85	82	87	84	82	87	84	82	86	84	82	81
10	92	87	83	81	92	86	83	81	86	83	80	85	82	80	84	82	80	79

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1547508
5°	1185535
10°	497341
15°	209899
20°	136535
25°	59834
30°	8103
35°	3052
40°	2176
45°	1675
50°	1467
55°	1453
60°	1184
65°	830
70°	321
75°	0
80°	0
85°	0



TEST NUMBER: P220504

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-S-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	405.5	49.2
10°-20°	282.7	34.3
20°-30°	116.5	14.2
30°-40°	9.2	1.1
40°-50°	4.4	0.5
50°-60°	3.2	0.4
60°-70°	1.6	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	804.7	97.7
0°-40°	813.9	98.9
0°-60°	821.5	99.8
0°-90°	823.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	823.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7057	
5°	5386	405
15°	925	283
25°	247	117
35°	11	9
45°	5	4
55°	4	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220504

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-S-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7057.2
1°	6967.1
2°	6756.2
3°	6412.9
4°	5954.7
5°	5385.9
6°	4753.0
7°	4089.8
8°	3407.7
9°	2782.4
10°	2233.6
11°	1799.3
12°	1477.7
13°	1240.7
14°	1067.7
15°	924.6
16°	809.1
17°	733.7
18°	675.7
19°	624.7
20°	585.1
21°	548.8
22°	493.5
23°	418.1
24°	332.4
25°	247.3
26°	171.9
27°	103.0
28°	57.5
29°	38.5
30°	32.0
32.5°	20.6
35°	11.4
37.5°	8.7
40°	7.6
42.5°	6.5
45°	5.4
47.5°	4.9
50°	4.3
52.5°	3.8
55°	3.8
57.5°	3.3
60°	2.7
62.5°	2.2
65°	1.6



TEST NUMBER: P220504

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4080-S-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.1
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)