

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-8LED3036-12-BK**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-6)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 203-8LED3036-12-BK
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK
Light Source: (1) SORAA 3000K 95 CRI LED
SM16-07-36D-930-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	327 lumens	Max Intensity:	997.3 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	41.9 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	34.9°H x 34.9°V	Field Angle (10%):	52.3°H x 52.3°V
Beam Lumens:	209.2 lumens	Field Lumens:	302.5 lumens
Beam Efficiency:	64.0%	Field Efficiency:	92.5%
Input Watts (W):	7.8		
Input Voltage (V):	NR		
Input Current (Ain):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED3036-12-BK

Iso-Candela Plot



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK


Lumen Table

90	0.0														
80	0.0														
70	0.0														
60	0.0														
50	0.0														
40	0.0														
30	0.0														
20	0.0														
10	0.0														
0	0.0														
-10	0.0														
-20	0.0														
-30	0.0														
-40	0.0														
-50	0.0														
-60	0.0														
-70	0.0														
-80	0.0														
-90	0.0														

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40	0.0	0.0	0.0	0.0	0.1	0.2	0.3	0.3	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30	0.0	0.0	0.0	0.1	0.3	1.7	4.0	4.0	1.7	0.3	0.1	0.0	0.0	0.0	0.0	0.0	0.0
20	0.0	0.0	0.0	0.2	1.6	8.7	16.9	16.9	8.7	1.6	0.2	0.0	0.0	0.0	0.0	0.0	0.0
10	0.0	0.0	0.0	0.3	3.7	16.4	26.9	26.9	16.4	3.7	0.3	0.0	0.0	0.0	0.0	0.0	0.0
0	0.0	0.0	0.0	0.3	3.7	16.4	26.9	26.9	16.4	3.7	0.3	0.0	0.0	0.0	0.0	0.0	0.0
-10	0.0	0.0	0.0	0.3	3.7	16.4	26.9	26.9	16.4	3.7	0.3	0.0	0.0	0.0	0.0	0.0	0.0
-20	0.0	0.0	0.0	0.2	1.6	8.7	16.9	16.9	8.7	1.6	0.2	0.0	0.0	0.0	0.0	0.0	0.0
-30	0.0	0.0	0.0	0.1	0.3	1.7	4.0	4.0	1.7	0.3	0.1	0.0	0.0	0.0	0.0	0.0	0.0
-40	0.0	0.0	0.0	0.0	0.1	0.2	0.3	0.3	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-60	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0


REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED3036-12-BK

Luminous Intensity Polar Plot



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

Luminous Intensity Plot



Beam:
 H Angle: 34.9°
 V Angle: 34.9°
 Lumens: 209.2
 Efficiency: 64.0%

Field:
 H Angle: 52.3°
 V Angle: 52.3°
 Lumens: 302.5
 Efficiency: 92.5%

Spill:
 Lumens: 24.4
 Efficiency: 7.5%

— Vertical Distribution through 0-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	1	1
47.5°	0	0	0	0	0	0	0	0	1	1	1
45°	0	0	0	0	0	0	0	1	1	1	1
42.5°	0	0	0	0	0	0	1	1	1	1	1
40°	0	0	0	0	0	1	1	1	1	1	1
37.5°	0	0	0	0	0	1	1	1	1	1	1
35°	0	0	0	0	1	1	1	1	1	1	1
32.5°	0	0	0	1	1	1	1	1	1	1	1
30°	0	0	0	1	1	1	1	1	1	1	1
27.5°	0	0	0	1	1	1	1	1	1	1	2
25°	0	0	1	1	1	1	1	1	1	1	2
22.5°	0	0	1	1	1	1	1	1	1	2	3
20°	0	0	1	1	1	1	1	1	1	2	3
17.5°	0	0	1	1	1	1	1	1	2	2	3
15°	0	0	1	1	1	1	1	1	2	3	4
12.5°	0	1	1	1	1	1	1	1	2	3	4
10°	0	1	1	1	1	1	1	1	2	3	4
7.5°	0	1	1	1	1	1	1	2	3	3	5
5°	0	1	1	1	1	1	1	2	3	3	5
2.5°	0	1	1	1	1	1	1	2	3	3	5
0°	0	1	1	1	1	1	1	2	3	4	5
-2.5°	0	1	1	1	1	1	1	2	3	3	5
-5°	0	1	1	1	1	1	1	2	3	3	5
-7.5°	0	1	1	1	1	1	1	2	3	3	5
-10°	0	1	1	1	1	1	1	1	2	3	4
-12.5°	0	1	1	1	1	1	1	1	2	3	4
-15°	0	0	1	1	1	1	1	1	2	3	4
-17.5°	0	0	1	1	1	1	1	1	2	2	3
-20°	0	0	1	1	1	1	1	1	1	2	3



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	1	1	1	1	1	1	1	2	3
-25°	0	0	1	1	1	1	1	1	1	1	2
-27.5°	0	0	0	1	1	1	1	1	1	1	2
-30°	0	0	0	1	1	1	1	1	1	1	1
-32.5°	0	0	0	1	1	1	1	1	1	1	1
-35°	0	0	0	0	1	1	1	1	1	1	1
-37.5°	0	0	0	0	0	1	1	1	1	1	1
-40°	0	0	0	0	0	1	1	1	1	1	1
-42.5°	0	0	0	0	0	0	1	1	1	1	1
-45°	0	0	0	0	0	0	0	1	1	1	1
-47.5°	0	0	0	0	0	0	0	0	1	1	1
-50°	0	0	0	0	0	0	0	0	0	1	1
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	1	1
57.5°	0	0	0	0	1	1	1	1	1	1	1
55°	0	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	2	2	2	2
40°	1	1	1	1	1	2	2	2	3	3	3
37.5°	1	1	1	2	2	3	3	3	4	4	4
35°	1	1	2	2	3	3	4	4	5	6	8
32.5°	1	2	2	3	3	4	5	7	9	11	13
30°	2	2	3	4	5	6	9	11	14	17	21
27.5°	2	3	4	5	7	10	13	17	24	29	39
25°	3	3	5	7	10	14	21	28	42	60	80
22.5°	3	4	6	10	14	22	32	52	79	114	143
20°	4	5	9	13	21	32	56	93	134	179	229
17.5°	4	7	11	17	28	52	93	142	200	272	343
15°	5	9	14	24	42	79	134	200	288	381	468
12.5°	6	11	17	29	60	114	179	272	381	489	577
10°	8	13	21	39	80	143	229	343	468	577	664
7.5°	9	14	25	49	102	171	277	406	538	644	735
5°	9	15	27	57	117	194	315	456	585	693	789
2.5°	10	16	29	63	126	212	339	485	614	724	824
0°	10	16	29	65	129	218	348	495	624	734	836
-2.5°	10	16	29	63	126	212	339	485	614	724	824
-5°	9	15	27	57	117	194	315	456	585	693	789
-7.5°	9	14	25	49	102	171	277	406	538	644	735
-10°	8	13	21	39	80	143	229	343	468	577	664
-12.5°	6	11	17	29	60	114	179	272	381	489	577
-15°	5	9	14	24	42	79	134	200	288	381	468
-17.5°	4	7	11	17	28	52	93	142	200	272	343
-20°	4	5	9	13	21	32	56	93	134	179	229



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	3	4	6	10	14	22	32	52	79	114	143
-25°	3	3	5	7	10	14	21	28	42	60	80
-27.5°	2	3	4	5	7	10	13	17	24	29	39
-30°	2	2	3	4	5	6	9	11	14	17	21
-32.5°	1	2	2	3	3	4	5	7	9	11	13
-35°	1	1	2	2	3	3	4	4	5	6	8
-37.5°	1	1	1	2	2	3	3	3	4	4	4
-40°	1	1	1	1	1	2	2	2	3	3	3
-42.5°	1	1	1	1	1	1	1	2	2	2	2
-45°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-55°	0	1	1	1	1	1	1	1	1	1	1
-57.5°	0	0	0	0	1	1	1	1	1	1	1
-60°	0	0	0	0	0	0	0	0	0	1	1
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	1	1	1	1	1	1	1	1	1	0	0
57.5°	1	1	1	1	1	1	1	1	1	1	1
55°	1	1	1	1	1	1	1	1	1	1	1
52.5°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	2	2	2	2	2	2	2	1	1	1	1
42.5°	3	3	3	3	3	3	3	2	2	2	2
40°	3	3	3	4	3	3	3	3	3	3	2
37.5°	5	5	5	5	5	5	5	4	4	4	3
35°	9	9	10	10	10	9	9	8	6	5	4
32.5°	14	15	16	16	16	15	14	13	11	9	7
30°	25	27	29	29	29	27	25	21	17	14	11
27.5°	49	57	63	65	63	57	49	39	29	24	17
25°	102	117	126	129	126	117	102	80	60	42	28
22.5°	171	194	212	218	212	194	171	143	114	79	52
20°	277	315	339	348	339	315	277	229	179	134	93
17.5°	406	456	485	495	485	456	406	343	272	200	142
15°	538	585	614	624	614	585	538	468	381	288	200
12.5°	644	693	724	734	724	693	644	577	489	381	272
10°	735	789	824	836	824	789	735	664	577	468	343
7.5°	812	869	903	913	903	869	812	735	644	538	406
5°	869	924	949	957	949	924	869	789	693	585	456
2.5°	903	949	971	979	971	949	903	824	724	614	485
0°	913	957	979	997	979	957	913	836	734	624	495
-2.5°	903	949	971	979	971	949	903	824	724	614	485
-5°	869	924	949	957	949	924	869	789	693	585	456
-7.5°	812	869	903	913	903	869	812	735	644	538	406
-10°	735	789	824	836	824	789	735	664	577	468	343
-12.5°	644	693	724	734	724	693	644	577	489	381	272
-15°	538	585	614	624	614	585	538	468	381	288	200
-17.5°	406	456	485	495	485	456	406	343	272	200	142
-20°	277	315	339	348	339	315	277	229	179	134	93



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	171	194	212	218	212	194	171	143	114	79	52
-25°	102	117	126	129	126	117	102	80	60	42	28
-27.5°	49	57	63	65	63	57	49	39	29	24	17
-30°	25	27	29	29	29	27	25	21	17	14	11
-32.5°	14	15	16	16	16	15	14	13	11	9	7
-35°	9	9	10	10	10	9	9	8	6	5	4
-37.5°	5	5	5	5	5	5	5	4	4	4	3
-40°	3	3	3	4	3	3	3	3	3	3	2
-42.5°	3	3	3	3	3	3	3	2	2	2	2
-45°	2	2	2	2	2	2	2	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	1	1
-57.5°	1	1	1	1	1	1	1	1	1	1	1
-60°	1	1	1	1	1	1	1	1	1	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	1	1	1	0	0	0	0	0	0	0	0
55°	1	1	1	1	1	1	0	0	0	0	0
52.5°	1	1	1	1	1	1	1	0	0	0	0
50°	1	1	1	1	1	1	1	1	1	0	0
47.5°	1	1	1	1	1	1	1	1	1	1	0
45°	1	1	1	1	1	1	1	1	1	1	1
42.5°	1	1	1	1	1	1	1	1	1	1	1
40°	2	2	1	1	1	1	1	1	1	1	1
37.5°	3	3	2	2	1	1	1	1	1	1	1
35°	4	3	3	2	2	1	1	1	1	1	1
32.5°	5	4	3	3	2	2	1	1	1	1	1
30°	9	6	5	4	3	2	2	1	1	1	1
27.5°	13	10	7	5	4	3	2	2	1	1	1
25°	21	14	10	7	5	3	3	2	1	1	1
22.5°	32	22	14	10	6	4	3	3	2	1	1
20°	56	32	21	13	9	5	4	3	2	1	1
17.5°	93	52	28	17	11	7	4	3	2	2	1
15°	134	79	42	24	14	9	5	4	3	2	1
12.5°	179	114	60	29	17	11	6	4	3	2	1
10°	229	143	80	39	21	13	8	4	3	2	1
7.5°	277	171	102	49	25	14	9	5	3	3	2
5°	315	194	117	57	27	15	9	5	3	3	2
2.5°	339	212	126	63	29	16	10	5	3	3	2
0°	348	218	129	65	29	16	10	5	4	3	2
-2.5°	339	212	126	63	29	16	10	5	3	3	2
-5°	315	194	117	57	27	15	9	5	3	3	2
-7.5°	277	171	102	49	25	14	9	5	3	3	2
-10°	229	143	80	39	21	13	8	4	3	2	1
-12.5°	179	114	60	29	17	11	6	4	3	2	1
-15°	134	79	42	24	14	9	5	4	3	2	1
-17.5°	93	52	28	17	11	7	4	3	2	2	1
-20°	56	32	21	13	9	5	4	3	2	1	1



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	32	22	14	10	6	4	3	3	2	1	1
-25°	21	14	10	7	5	3	3	2	1	1	1
-27.5°	13	10	7	5	4	3	2	2	1	1	1
-30°	9	6	5	4	3	2	2	1	1	1	1
-32.5°	5	4	3	3	2	2	1	1	1	1	1
-35°	4	3	3	2	2	1	1	1	1	1	1
-37.5°	3	3	2	2	1	1	1	1	1	1	1
-40°	2	2	1	1	1	1	1	1	1	1	1
-42.5°	1	1	1	1	1	1	1	1	1	1	1
-45°	1	1	1	1	1	1	1	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	0
-50°	1	1	1	1	1	1	1	1	1	0	0
-52.5°	1	1	1	1	1	1	1	0	0	0	0
-55°	1	1	1	1	1	1	0	0	0	0	0
-57.5°	1	1	1	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	1	0	0	0	0	0	0	0	0	0	0
40°	1	1	0	0	0	0	0	0	0	0	0
37.5°	1	1	0	0	0	0	0	0	0	0	0
35°	1	1	1	0	0	0	0	0	0	0	0
32.5°	1	1	1	1	0	0	0	0	0	0	0
30°	1	1	1	1	0	0	0	0	0	0	0
27.5°	1	1	1	1	0	0	0	0	0	0	0
25°	1	1	1	1	1	0	0	0	0	0	0
22.5°	1	1	1	1	1	0	0	0	0	0	0
20°	1	1	1	1	1	0	0	0	0	0	0
17.5°	1	1	1	1	1	0	0	0	0	0	0
15°	1	1	1	1	1	0	0	0	0	0	0
12.5°	1	1	1	1	1	1	0	0	0	0	0
10°	1	1	1	1	1	1	0	0	0	0	0
7.5°	1	1	1	1	1	1	0	0	0	0	0
5°	1	1	1	1	1	1	0	0	0	0	0
2.5°	1	1	1	1	1	1	0	0	0	0	0
0°	1	1	1	1	1	1	0	0	0	0	0
-2.5°	1	1	1	1	1	1	0	0	0	0	0
-5°	1	1	1	1	1	1	0	0	0	0	0
-7.5°	1	1	1	1	1	1	0	0	0	0	0
-10°	1	1	1	1	1	1	0	0	0	0	0
-12.5°	1	1	1	1	1	1	0	0	0	0	0
-15°	1	1	1	1	1	0	0	0	0	0	0
-17.5°	1	1	1	1	1	0	0	0	0	0	0
-20°	1	1	1	1	1	0	0	0	0	0	0



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	1	1	1	1	1	0	0	0	0	0	0
-25°	1	1	1	1	1	0	0	0	0	0	0
-27.5°	1	1	1	1	0	0	0	0	0	0	0
-30°	1	1	1	1	0	0	0	0	0	0	0
-32.5°	1	1	1	1	0	0	0	0	0	0	0
-35°	1	1	1	0	0	0	0	0	0	0	0
-37.5°	1	1	0	0	0	0	0	0	0	0	0
-40°	1	1	0	0	0	0	0	0	0	0	0
-42.5°	1	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: P246983 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 203-8LED3036-12-BK

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)