

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **203-8LED4025-12-CS-LVR**

Test Date: 04/05/18

**Test Information**

Test Method: LM-79-08  
Report Number: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
Test Lab: INNOVATION CENTER(G2)  
Test Date: 04/05/18  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 203-8LED4025-12-CS-LVR  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 25 DEGREE NARROW OPTIC, REGRESSED HOOD SILVER, HEX CELL LOUVER  
Light Source: (1) SORAA 4000K 90 CRI LED  
SM16-07-25D-940-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	3H x 3V
Luminaire Lumens:	252.7 lumens	Max Intensity:	2092 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	35.1 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	16.3°H x 16.3°V	Field Angle (10%):	36°H x 36°V
Beam Lumens:	88.5 lumens	Field Lumens:	205.5 lumens
Beam Efficiency:	35.0%	Field Efficiency:	81.3%
Input Watts (W):	7.2		
Input Voltage (V):	12.0		
Input Current (Ain):	0.629		
Voltage Rise (V):	NR		
Power Factor:	0.9913		
Total Harmonic Distortion (THDi):	26.9%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	3 HR		
Ambient Temperature (°C):	25.2		
Test Distance:	25 FT		



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-8LED4025-12-CS-LVR

### Iso-Candela Plot






REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

### Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40		0.0	0.0	0.0	0.0	0.1	0.2	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0		
30	0.0	0.0	0.0	0.0	0.1	0.2	0.8	1.7	1.7	0.8	0.2	0.1	0.0	0.0	0.0	0.0	0.0
20		0.0	0.0	0.0	0.1	0.7	3.8	9.6	9.6	3.8	0.7	0.1	0.0	0.0	0.0		
10	0.0	0.0	0.0	0.0	0.2	1.5	9.3	34.2	34.2	9.3	1.5	0.2	0.0	0.0	0.0	0.0	0.0
0		0.0	0.0	0.0	0.2	1.5	9.3	34.2	34.2	9.3	1.5	0.2	0.0	0.0	0.0		
-10	0.0	0.0	0.0	0.0	0.1	0.7	3.8	9.6	9.6	3.8	0.7	0.1	0.0	0.0	0.0	0.0	0.0
-20		0.0	0.0	0.0	0.1	0.2	0.8	1.7	1.7	0.8	0.2	0.1	0.0	0.0	0.0		
-30	0.0	0.0	0.0	0.0	0.0	0.1	0.2	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0
-40		0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0


REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-8LED4025-12-CS-LVR

### Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-8LED4025-12-CS-LVR

### Luminous Intensity Plot



**Beam:**  
H Angle: 16.3°  
V Angle: 16.3°  
Lumens: 88.5  
Efficiency: 35.0%

**Field:**  
H Angle: 36°  
V Angle: 36°  
Lumens: 205.5  
Efficiency: 81.3%

**Spill:**  
Lumens: 47.2  
Efficiency: 18.7%

— Vertical Distribution through 0-Deg  
- - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	1
42.5°	0	0	0	0	0	0	0	0	0	1	1
40°	0	0	0	0	0	0	0	0	1	1	1
37.5°	0	0	0	0	0	0	0	1	1	1	1
35°	0	0	0	0	0	0	0	1	1	1	1
32.5°	0	0	0	0	0	0	1	1	1	1	1
30°	0	0	0	0	0	1	1	1	1	1	1
27.5°	0	0	0	0	0	1	1	1	1	1	2
25°	0	0	0	0	0	1	1	1	1	2	2
22.5°	0	0	0	0	1	1	1	1	1	2	3
20°	0	0	0	0	1	1	1	1	2	2	3
17.5°	0	0	0	0	1	1	1	1	2	3	4
15°	0	0	0	0	1	1	1	1	2	3	4
12.5°	0	0	0	1	1	1	1	1	2	3	4
10°	0	0	0	1	1	1	1	2	3	4	5
7.5°	0	0	0	1	1	1	1	2	3	4	5
5°	0	0	0	1	1	1	1	2	3	4	5
2.5°	0	0	0	1	1	1	1	2	3	4	5
0°	0	0	0	1	1	1	1	2	3	4	5
-2.5°	0	0	0	1	1	1	1	2	3	4	5
-5°	0	0	0	1	1	1	1	2	3	4	5
-7.5°	0	0	0	1	1	1	1	2	3	4	5
-10°	0	0	0	1	1	1	1	2	3	4	5
-12.5°	0	0	0	1	1	1	1	1	2	3	4
-15°	0	0	0	0	1	1	1	1	2	3	4
-17.5°	0	0	0	0	1	1	1	1	2	3	4
-20°	0	0	0	0	1	1	1	1	2	2	3



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	0	0	1	1	1	1	1	2	3
-25°	0	0	0	0	0	1	1	1	1	2	2
-27.5°	0	0	0	0	0	1	1	1	1	1	2
-30°	0	0	0	0	0	1	1	1	1	1	1
-32.5°	0	0	0	0	0	0	1	1	1	1	1
-35°	0	0	0	0	0	0	0	1	1	1	1
-37.5°	0	0	0	0	0	0	0	1	1	1	1
-40°	0	0	0	0	0	0	0	0	1	1	1
-42.5°	0	0	0	0	0	0	0	0	0	1	1
-45°	0	0	0	0	0	0	0	0	0	0	1
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	1	1
52.5°	0	0	0	0	0	1	1	1	1	1	1
50°	0	0	1	1	1	1	1	1	1	1	1
47.5°	0	1	1	1	1	1	1	1	1	1	1
45°	1	1	1	1	1	1	1	1	1	1	2
42.5°	1	1	1	1	1	1	2	2	2	2	3
40°	1	1	1	1	2	2	2	3	3	3	4
37.5°	1	1	1	2	2	3	3	4	4	4	5
35°	1	1	2	3	3	4	4	5	5	5	6
32.5°	1	2	3	3	4	4	5	6	7	8	9
30°	2	3	3	4	5	6	7	8	10	11	13
27.5°	3	3	4	5	6	7	9	11	13	15	18
25°	3	4	5	6	7	10	12	15	19	26	34
22.5°	4	4	6	7	10	13	16	23	33	45	60
20°	4	5	7	9	12	16	24	37	56	76	95
17.5°	5	6	8	11	15	23	37	60	84	115	145
15°	5	7	10	13	19	33	56	84	122	163	208
12.5°	5	8	11	15	26	45	76	115	163	222	287
10°	6	9	13	18	34	60	95	145	208	287	381
7.5°	6	10	14	22	40	73	117	175	255	357	502
5°	7	10	14	25	47	82	134	201	295	426	632
2.5°	7	11	15	27	51	88	144	219	322	479	738
0°	7	11	15	28	53	90	147	226	332	501	777
-2.5°	7	11	15	27	51	88	144	219	322	479	738
-5°	7	10	14	25	47	82	134	201	295	426	632
-7.5°	6	10	14	22	40	73	117	175	255	357	502
-10°	6	9	13	18	34	60	95	145	208	287	381
-12.5°	5	8	11	15	26	45	76	115	163	222	287
-15°	5	7	10	13	19	33	56	84	122	163	208
-17.5°	5	6	8	11	15	23	37	60	84	115	145
-20°	4	5	7	9	12	16	24	37	56	76	95



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	4	4	6	7	10	13	16	23	33	45	60
-25°	3	4	5	6	7	10	12	15	19	26	34
-27.5°	3	3	4	5	6	7	9	11	13	15	18
-30°	2	3	3	4	5	6	7	8	10	11	13
-32.5°	1	2	3	3	4	4	5	6	7	8	9
-35°	1	1	2	3	3	4	4	5	5	5	6
-37.5°	1	1	1	2	2	3	3	4	4	4	5
-40°	1	1	1	1	2	2	2	3	3	3	4
-42.5°	1	1	1	1	1	1	2	2	2	2	3
-45°	1	1	1	1	1	1	1	1	1	1	2
-47.5°	0	1	1	1	1	1	1	1	1	1	1
-50°	0	0	1	1	1	1	1	1	1	1	1
-52.5°	0	0	0	0	0	1	1	1	1	1	1
-55°	0	0	0	0	0	0	0	0	0	1	1
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	1	1	1	1	1	1	1	1	1	0	0
52.5°	1	1	1	1	1	1	1	1	1	1	1
50°	1	1	1	1	1	1	1	1	1	1	1
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	2	2	2	2	2	2	2	2	1	1	1
42.5°	3	3	3	3	3	3	3	3	2	2	2
40°	4	4	4	4	4	4	4	4	3	3	3
37.5°	5	5	5	5	5	5	5	5	4	4	4
35°	6	7	7	7	7	7	6	6	5	5	5
32.5°	10	10	11	11	11	10	10	9	8	7	6
30°	14	14	15	15	15	14	14	13	11	10	8
27.5°	22	25	27	28	27	25	22	18	15	13	11
25°	40	47	51	53	51	47	40	34	26	19	15
22.5°	73	82	88	90	88	82	73	60	45	33	23
20°	117	134	144	147	144	134	117	95	76	56	37
17.5°	175	201	219	226	219	201	175	145	115	84	60
15°	255	295	322	332	322	295	255	208	163	122	84
12.5°	357	426	479	501	479	426	357	287	222	163	115
10°	502	632	738	777	738	632	502	381	287	208	145
7.5°	702	915	1082	1145	1082	915	702	502	357	255	175
5°	915	1213	1448	1543	1448	1213	915	632	426	295	201
2.5°	1082	1448	1764	1899	1764	1448	1082	738	479	322	219
0°	1145	1543	1899	2092	1899	1543	1145	777	501	332	226
-2.5°	1082	1448	1764	1899	1764	1448	1082	738	479	322	219
-5°	915	1213	1448	1543	1448	1213	915	632	426	295	201
-7.5°	702	915	1082	1145	1082	915	702	502	357	255	175
-10°	502	632	738	777	738	632	502	381	287	208	145
-12.5°	357	426	479	501	479	426	357	287	222	163	115
-15°	255	295	322	332	322	295	255	208	163	122	84
-17.5°	175	201	219	226	219	201	175	145	115	84	60
-20°	117	134	144	147	144	134	117	95	76	56	37



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	73	82	88	90	88	82	73	60	45	33	23
-25°	40	47	51	53	51	47	40	34	26	19	15
-27.5°	22	25	27	28	27	25	22	18	15	13	11
-30°	14	14	15	15	15	14	14	13	11	10	8
-32.5°	10	10	11	11	11	10	10	9	8	7	6
-35°	6	7	7	7	7	7	6	6	5	5	5
-37.5°	5	5	5	5	5	5	5	5	4	4	4
-40°	4	4	4	4	4	4	4	4	3	3	3
-42.5°	3	3	3	3	3	3	3	3	2	2	2
-45°	2	2	2	2	2	2	2	2	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	1	1
-52.5°	1	1	1	1	1	1	1	1	1	1	1
-55°	1	1	1	1	1	1	1	1	1	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	1	1	0	0	0	0	0	0	0	0	0
50°	1	1	1	1	1	0	0	0	0	0	0
47.5°	1	1	1	1	1	1	0	0	0	0	0
45°	1	1	1	1	1	1	1	1	0	0	0
42.5°	2	1	1	1	1	1	1	1	1	0	0
40°	2	2	2	1	1	1	1	1	1	1	0
37.5°	3	3	2	2	1	1	1	1	1	1	1
35°	4	4	3	3	2	1	1	1	1	1	1
32.5°	5	4	4	3	3	2	1	1	1	1	1
30°	7	6	5	4	3	3	2	1	1	1	1
27.5°	9	7	6	5	4	3	3	2	1	1	1
25°	12	10	7	6	5	4	3	2	2	1	1
22.5°	16	13	10	7	6	4	4	3	2	1	1
20°	24	16	12	9	7	5	4	3	2	2	1
17.5°	37	23	15	11	8	6	5	4	3	2	1
15°	56	33	19	13	10	7	5	4	3	2	1
12.5°	76	45	26	15	11	8	5	4	3	2	1
10°	95	60	34	18	13	9	6	5	4	3	2
7.5°	117	73	40	22	14	10	6	5	4	3	2
5°	134	82	47	25	14	10	7	5	4	3	2
2.5°	144	88	51	27	15	11	7	5	4	3	2
0°	147	90	53	28	15	11	7	5	4	3	2
-2.5°	144	88	51	27	15	11	7	5	4	3	2
-5°	134	82	47	25	14	10	7	5	4	3	2
-7.5°	117	73	40	22	14	10	6	5	4	3	2
-10°	95	60	34	18	13	9	6	5	4	3	2
-12.5°	76	45	26	15	11	8	5	4	3	2	1
-15°	56	33	19	13	10	7	5	4	3	2	1
-17.5°	37	23	15	11	8	6	5	4	3	2	1
-20°	24	16	12	9	7	5	4	3	2	2	1



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	16	13	10	7	6	4	4	3	2	1	1
-25°	12	10	7	6	5	4	3	2	2	1	1
-27.5°	9	7	6	5	4	3	3	2	1	1	1
-30°	7	6	5	4	3	3	2	1	1	1	1
-32.5°	5	4	4	3	3	2	1	1	1	1	1
-35°	4	4	3	3	2	1	1	1	1	1	1
-37.5°	3	3	2	2	1	1	1	1	1	1	1
-40°	2	2	2	1	1	1	1	1	1	1	0
-42.5°	2	1	1	1	1	1	1	1	1	0	0
-45°	1	1	1	1	1	1	1	1	0	0	0
-47.5°	1	1	1	1	1	1	0	0	0	0	0
-50°	1	1	1	1	1	0	0	0	0	0	0
-52.5°	1	1	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	1	0	0	0	0	0	0	0	0	0	0
30°	1	1	0	0	0	0	0	0	0	0	0
27.5°	1	1	0	0	0	0	0	0	0	0	0
25°	1	1	0	0	0	0	0	0	0	0	0
22.5°	1	1	1	0	0	0	0	0	0	0	0
20°	1	1	1	0	0	0	0	0	0	0	0
17.5°	1	1	1	0	0	0	0	0	0	0	0
15°	1	1	1	0	0	0	0	0	0	0	0
12.5°	1	1	1	1	0	0	0	0	0	0	0
10°	1	1	1	1	0	0	0	0	0	0	0
7.5°	1	1	1	1	0	0	0	0	0	0	0
5°	1	1	1	1	0	0	0	0	0	0	0
2.5°	1	1	1	1	0	0	0	0	0	0	0
0°	1	1	1	1	0	0	0	0	0	0	0
-2.5°	1	1	1	1	0	0	0	0	0	0	0
-5°	1	1	1	1	0	0	0	0	0	0	0
-7.5°	1	1	1	1	0	0	0	0	0	0	0
-10°	1	1	1	1	0	0	0	0	0	0	0
-12.5°	1	1	1	1	0	0	0	0	0	0	0
-15°	1	1	1	0	0	0	0	0	0	0	0
-17.5°	1	1	1	0	0	0	0	0	0	0	0
-20°	1	1	1	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	1	1	1	0	0	0	0	0	0	0	0
-25°	1	1	0	0	0	0	0	0	0	0	0
-27.5°	1	1	0	0	0	0	0	0	0	0	0
-30°	1	1	0	0	0	0	0	0	0	0	0
-32.5°	1	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-42 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 203-8LED4025-12-CS-LVR

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)