

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P220560

Luminaire Tested: **9003-W1-[RW, RI]-LED4097-W-BK-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29475)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-[RW, RI]-LED4097-W-BK-L1-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, WIDE FLOOD OPTIC, BLACK HOUSING.
Light Source: (1) 4000K CCT, 97 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 588.3 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220560

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-W-BK-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220560

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-W-BK-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	90	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	77	71	68	84	76	71	68	75	71	67	74	70	67	73	69	67	66
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63
10	78	70	65	61	78	70	65	61	69	64	61	68	64	61	67	64	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230245
5°	231212
10°	216273
15°	184768
20°	157024
25°	93320
30°	42462
35°	26930
40°	15257
45°	5613
50°	1774
55°	1300
60°	1140
65°	675
70°	256
75°	339
80°	0
85°	0



TEST NUMBER: P220560

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-W-BK-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.8	16.6
10°-20°	227.5	38.7
20°-30°	176.6	30.0
30°-40°	64.4	10.9
40°-50°	17.1	2.9
50°-60°	3.2	0.5
60°-70°	1.4	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.9	85.3
0°-40°	566.3	96.3
0°-60°	586.5	99.7
0°-90°	588.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	588.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1050	
5°	1050	98
15°	814	227
25°	386	177
35°	101	64
45°	18	17
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220560

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-W-BK-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	1050.0
1°	1047.0
2°	1047.0
3°	1050.0
4°	1051.7
5°	1050.4
6°	1045.3
7°	1034.5
8°	1017.7
9°	995.8
10°	971.3
11°	942.9
12°	911.5
13°	878.4
14°	844.5
15°	813.9
16°	786.4
17°	757.2
18°	729.2
19°	700.9
20°	672.9
21°	641.9
22°	592.9
23°	528.4
24°	458.4
25°	385.7
26°	317.3
27°	256.3
28°	210.3
29°	184.0
30°	167.7
32.5°	132.0
35°	100.6
37.5°	75.7
40°	53.3
42.5°	35.3
45°	18.1
47.5°	8.2
50°	5.2
52.5°	3.9
55°	3.4
57.5°	3.0
60°	2.6
62.5°	1.7
65°	1.3



TEST NUMBER: P220560

CATALOG NUMBER: 9003-W1-[RW, RI]-LED4097-W-BK-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.3
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)