

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P220539

Luminaire Tested: **9003-W1-[RW, RI]-LED5080-F-BK-L1-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220539  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29474)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED5080-F-BK-L1-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 5000K CCT, 80 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 917.6 lumens  
Efficiency: N/A  
Efficacy: 93.6 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220539

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-F-BK-L1-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220539

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-F-BK-L1-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	86	99	93	89	86	91	88	85	90	87	85	89	86	84	83
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	80	78	77
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	586751
5°	574113
10°	506003
15°	390944
20°	242804
25°	89957
30°	18838
35°	7094
40°	2576
45°	1737
50°	1535
55°	1300
60°	1009
65°	571
70°	385
75°	0
80°	0
85°	0



TEST NUMBER: P220539

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-F-BK-L1-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	238.2	26.0
10°-20°	462.1	50.4
20°-30°	188.3	20.5
30°-40°	19.9	2.2
40°-50°	4.7	0.5
50°-60°	3.0	0.3
60°-70°	1.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	888.5	96.8
0°-40°	908.4	99.0
0°-60°	916.1	99.8
0°-90°	917.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	917.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2676	
5°	2608	238
15°	1722	462
25°	372	188
35°	26	20
45°	6	5
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220539

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-F-BK-L1-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2675.8
1°	2669.1
2°	2661.2
3°	2653.9
4°	2639.2
5°	2608.2
6°	2566.0
7°	2510.8
8°	2440.4
9°	2360.4
10°	2272.5
11°	2176.2
12°	2073.6
13°	1966.6
14°	1849.4
15°	1722.1
16°	1592.5
17°	1448.9
18°	1314.8
19°	1175.1
20°	1040.5
21°	909.2
22°	770.1
23°	628.1
24°	493.5
25°	371.8
26°	266.5
27°	181.4
28°	120.0
29°	89.0
30°	74.4
32.5°	49.0
35°	26.5
37.5°	14.6
40°	9.0
42.5°	6.8
45°	5.6
47.5°	5.1
50°	4.5
52.5°	3.9
55°	3.4
57.5°	2.8
60°	2.3
62.5°	1.7
65°	1.1



TEST NUMBER: P220539

CATALOG NUMBER: 9003-W1-[RW, RI]-LED5080-F-BK-L1-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.1
70°	0.6
72.5°	0.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)