

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **206-8LED2736-12-XX-LVR**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-34)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 206-8LED2736-12-XX-LVR  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 2700K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD BLACK, HEX CELL LOUVER  
Light Source: (1) SORAA 2700K 95 CRI LED  
SM16-07-36D-927-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


**Summary**

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	229.9 lumens	Max Intensity:	909.2 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	29.5 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	28.7°H x 28.7°V	Field Angle (10%):	48°H x 48°V
Beam Lumens:	133.3 lumens	Field Lumens:	209.5 lumens
Beam Efficiency:	58.0%	Field Efficiency:	91.1%
Input Watts (W):	7.8		
Input Voltage (V):	NR		
Input Current (A <sub>in</sub> ):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 206-8LED2736-12-XX-LVR

### Iso-Candela Plot






REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

### Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40		0.0	0.0	0.0	0.0	0.1	0.2	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0		
30	0.0	0.0	0.0	0.0	0.1	0.2	0.9	2.2	2.2	0.9	0.2	0.1	0.0	0.0	0.0	0.0	0.0
20		0.0	0.0	0.0	0.1	0.9	5.3	11.5	11.5	5.3	0.9	0.1	0.0	0.0	0.0		
10	0.0	0.0	0.0	0.0	0.2	2.1	11.2	21.9	21.9	11.2	2.1	0.2	0.0	0.0	0.0	0.0	0.0
0		0.0	0.0	0.0	0.2	2.1	11.2	21.9	21.9	11.2	2.1	0.2	0.0	0.0	0.0		
-10	0.0	0.0	0.0	0.0	0.1	0.9	5.3	11.5	11.5	5.3	0.9	0.1	0.0	0.0	0.0	0.0	0.0
-20		0.0	0.0	0.0	0.1	0.2	0.9	2.2	2.2	0.9	0.2	0.1	0.0	0.0	0.0		
-30	0.0	0.0	0.0	0.0	0.0	0.1	0.2	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0
-40		0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0


REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 206-8LED2736-12-XX-LVR

### Luminous Intensity Polar Plot



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

### Luminous Intensity Plot



**Beam:**  
 H Angle: 28.7°  
 V Angle: 28.7°  
 Lumens: 133.3  
 Efficiency: 58.0%

**Field:**  
 H Angle: 48°  
 V Angle: 48°  
 Lumens: 209.5  
 Efficiency: 91.1%

**Spill:**  
 Lumens: 20.4  
 Efficiency: 8.9%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	1
35°	0	0	0	0	0	0	0	0	0	0	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	2
25°	0	0	0	0	0	0	0	1	1	1	2
22.5°	0	0	0	0	0	0	0	1	1	2	3
20°	0	0	0	0	0	0	1	1	1	2	3
17.5°	0	0	0	0	0	0	1	1	2	2	3
15°	0	0	0	0	0	0	1	1	2	3	4
12.5°	0	0	0	0	0	0	1	1	2	3	4
10°	0	0	0	0	0	1	1	1	2	3	4
7.5°	0	0	0	0	0	1	1	2	3	3	4
5°	0	0	0	0	0	1	1	2	3	4	4
2.5°	0	0	0	0	0	1	1	2	3	4	5
0°	0	0	0	0	0	1	1	2	3	4	5
-2.5°	0	0	0	0	0	1	1	2	3	4	5
-5°	0	0	0	0	0	1	1	2	3	4	4
-7.5°	0	0	0	0	0	1	1	2	3	3	4
-10°	0	0	0	0	0	1	1	1	2	3	4
-12.5°	0	0	0	0	0	0	1	1	2	3	4
-15°	0	0	0	0	0	0	1	1	2	3	4
-17.5°	0	0	0	0	0	0	1	1	2	2	3
-20°	0	0	0	0	0	0	1	1	1	2	3



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	0	0	0	0	0	1	1	2	3
-25°	0	0	0	0	0	0	0	1	1	1	2
-27.5°	0	0	0	0	0	0	0	0	1	1	2
-30°	0	0	0	0	0	0	0	0	1	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	0	1
-37.5°	0	0	0	0	0	0	0	0	0	0	1
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	1
47.5°	0	0	0	0	0	0	1	1	1	1	1
45°	0	0	0	0	1	1	1	1	1	1	1
42.5°	0	0	1	1	1	1	1	2	2	2	2
40°	0	1	1	1	1	2	2	2	3	3	3
37.5°	1	1	1	2	2	3	3	3	4	4	4
35°	1	1	2	2	3	3	4	4	5	5	6
32.5°	1	2	2	3	4	4	5	6	7	8	9
30°	2	2	3	4	4	5	7	8	10	12	14
27.5°	2	3	4	4	6	7	9	12	15	18	22
25°	3	4	4	6	8	10	14	18	24	33	42
22.5°	3	4	5	7	10	14	19	29	42	59	77
20°	4	5	7	9	14	19	31	48	71	101	133
17.5°	4	6	8	12	18	29	48	76	115	161	209
15°	5	7	10	15	24	42	71	115	170	236	298
12.5°	5	8	12	18	33	59	101	161	236	314	385
10°	6	9	14	22	42	77	133	209	298	385	463
7.5°	7	10	16	27	52	96	163	254	352	444	535
5°	7	10	17	32	61	112	189	289	392	492	595
2.5°	7	11	18	34	66	123	206	311	417	523	634
0°	7	11	18	35	68	126	212	319	425	534	647
-2.5°	7	11	18	34	66	123	206	311	417	523	634
-5°	7	10	17	32	61	112	189	289	392	492	595
-7.5°	7	10	16	27	52	96	163	254	352	444	535
-10°	6	9	14	22	42	77	133	209	298	385	463
-12.5°	5	8	12	18	33	59	101	161	236	314	385
-15°	5	7	10	15	24	42	71	115	170	236	298
-17.5°	4	6	8	12	18	29	48	76	115	161	209
-20°	4	5	7	9	14	19	31	48	71	101	133



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	3	4	5	7	10	14	19	29	42	59	77
-25°	3	4	4	6	8	10	14	18	24	33	42
-27.5°	2	3	4	4	6	7	9	12	15	18	22
-30°	2	2	3	4	4	5	7	8	10	12	14
-32.5°	1	2	2	3	4	4	5	6	7	8	9
-35°	1	1	2	2	3	3	4	4	5	5	6
-37.5°	1	1	1	2	2	3	3	3	4	4	4
-40°	0	1	1	1	1	2	2	2	3	3	3
-42.5°	0	0	1	1	1	1	1	2	2	2	2
-45°	0	0	0	0	1	1	1	1	1	1	1
-47.5°	0	0	0	0	0	0	1	1	1	1	1
-50°	0	0	0	0	0	0	0	0	0	0	1
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	1	1	1	1	1	1	1	1	0	0	0
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	2	2	2	2	2	2	2	1	1	1	1
42.5°	3	3	3	3	3	3	3	2	2	2	2
40°	3	4	4	4	4	4	3	3	3	3	2
37.5°	4	4	5	5	5	4	4	4	4	4	3
35°	7	7	7	7	7	7	7	6	5	5	4
32.5°	10	10	11	11	11	10	10	9	8	7	6
30°	16	17	18	18	18	17	16	14	12	10	8
27.5°	27	32	34	35	34	32	27	22	18	15	12
25°	52	61	66	68	66	61	52	42	33	24	18
22.5°	96	112	123	126	123	112	96	77	59	42	29
20°	163	189	206	212	206	189	163	133	101	71	48
17.5°	254	289	311	319	311	289	254	209	161	115	76
15°	352	392	417	425	417	392	352	298	236	170	115
12.5°	444	492	523	534	523	492	444	385	314	236	161
10°	535	595	634	647	634	595	535	463	385	298	209
7.5°	621	688	731	746	731	688	621	535	444	352	254
5°	688	762	804	819	804	762	688	595	492	392	289
2.5°	731	804	850	871	850	804	731	634	523	417	311
0°	746	819	871	909	871	819	746	647	534	425	319
-2.5°	731	804	850	871	850	804	731	634	523	417	311
-5°	688	762	804	819	804	762	688	595	492	392	289
-7.5°	621	688	731	746	731	688	621	535	444	352	254
-10°	535	595	634	647	634	595	535	463	385	298	209
-12.5°	444	492	523	534	523	492	444	385	314	236	161
-15°	352	392	417	425	417	392	352	298	236	170	115
-17.5°	254	289	311	319	311	289	254	209	161	115	76
-20°	163	189	206	212	206	189	163	133	101	71	48



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	96	112	123	126	123	112	96	77	59	42	29
-25°	52	61	66	68	66	61	52	42	33	24	18
-27.5°	27	32	34	35	34	32	27	22	18	15	12
-30°	16	17	18	18	18	17	16	14	12	10	8
-32.5°	10	10	11	11	11	10	10	9	8	7	6
-35°	7	7	7	7	7	7	7	6	5	5	4
-37.5°	4	4	5	5	5	4	4	4	4	4	3
-40°	3	4	4	4	4	4	3	3	3	3	2
-42.5°	3	3	3	3	3	3	3	2	2	2	2
-45°	2	2	2	2	2	2	2	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	1	0	0	0	0	0	0	0	0	0	0
45°	1	1	1	0	0	0	0	0	0	0	0
42.5°	1	1	1	1	1	0	0	0	0	0	0
40°	2	2	1	1	1	1	0	0	0	0	0
37.5°	3	3	2	2	1	1	1	1	0	0	0
35°	4	3	3	2	2	1	1	1	0	0	0
32.5°	5	4	4	3	2	2	1	1	1	0	0
30°	7	5	4	4	3	2	2	1	1	1	0
27.5°	9	7	6	4	4	3	2	2	1	1	0
25°	14	10	8	6	4	4	3	2	1	1	1
22.5°	19	14	10	7	5	4	3	3	2	1	1
20°	31	19	14	9	7	5	4	3	2	1	1
17.5°	48	29	18	12	8	6	4	3	2	2	1
15°	71	42	24	15	10	7	5	4	3	2	1
12.5°	101	59	33	18	12	8	5	4	3	2	1
10°	133	77	42	22	14	9	6	4	3	2	1
7.5°	163	96	52	27	16	10	7	4	3	3	2
5°	189	112	61	32	17	10	7	4	4	3	2
2.5°	206	123	66	34	18	11	7	5	4	3	2
0°	212	126	68	35	18	11	7	5	4	3	2
-2.5°	206	123	66	34	18	11	7	5	4	3	2
-5°	189	112	61	32	17	10	7	4	4	3	2
-7.5°	163	96	52	27	16	10	7	4	3	3	2
-10°	133	77	42	22	14	9	6	4	3	2	1
-12.5°	101	59	33	18	12	8	5	4	3	2	1
-15°	71	42	24	15	10	7	5	4	3	2	1
-17.5°	48	29	18	12	8	6	4	3	2	2	1
-20°	31	19	14	9	7	5	4	3	2	1	1



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	19	14	10	7	5	4	3	3	2	1	1
-25°	14	10	8	6	4	4	3	2	1	1	1
-27.5°	9	7	6	4	4	3	2	2	1	1	0
-30°	7	5	4	4	3	2	2	1	1	1	0
-32.5°	5	4	4	3	2	2	1	1	1	0	0
-35°	4	3	3	2	2	1	1	1	0	0	0
-37.5°	3	3	2	2	1	1	1	1	0	0	0
-40°	2	2	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	0	0	0	0	0	0	0	0
-47.5°	1	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	1	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
15°	1	0	0	0	0	0	0	0	0	0	0
12.5°	1	0	0	0	0	0	0	0	0	0	0
10°	1	1	0	0	0	0	0	0	0	0	0
7.5°	1	1	0	0	0	0	0	0	0	0	0
5°	1	1	0	0	0	0	0	0	0	0	0
2.5°	1	1	0	0	0	0	0	0	0	0	0
0°	1	1	0	0	0	0	0	0	0	0	0
-2.5°	1	1	0	0	0	0	0	0	0	0	0
-5°	1	1	0	0	0	0	0	0	0	0	0
-7.5°	1	1	0	0	0	0	0	0	0	0	0
-10°	1	1	0	0	0	0	0	0	0	0	0
-12.5°	1	0	0	0	0	0	0	0	0	0	0
-15°	1	0	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: P247029 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 206-8LED2736-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)