

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220587

Luminaire Tested: **9003-W1-FL-LED2790-M-WT-L1-UNV**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P220587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29477)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 9003-W1-FL-LED2790-M-WT-L1-UNV
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, FLUSH LENS, MEDIUM FLOOD OPTIC, WHITE HOUSING.
Light Source: (1) 2700K CCT, 90 CRI LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 664.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct


Input Watts (W): 9.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P220587

CATALOG NUMBER: 9003-W1-FL-LED2790-M-WT-L1-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P220587

CATALOG NUMBER: 9003-W1-FL-LED2790-M-WT-L1-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97	95	94	93
3	107	102	99	96	105	101	98	95	98	96	93		96	94	92		94	92	91	89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	84	81	80
7	94	88	83	80	93	87	83	80	86	82	80		85	82	79		84	81	79	78
8	92	85	80	77	91	84	80	77	83	80	77		82	79	77		82	79	76	75
9	89	82	78	75	88	82	78	75	81	77	75		80	77	74		79	76	74	73
10	86	79	75	73	86	79	75	72	78	75	72		78	74	72		77	74	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	616047
5°	559761
10°	395628
15°	213804
20°	113713
25°	83642
30°	33777
35°	6451
40°	3406
45°	1520
50°	1262
55°	1109
60°	877
65°	830
70°	769
75°	678
80°	505
85°	1006



TEST NUMBER: P220587

CATALOG NUMBER: 9003-W1-FL-LED2790-M-WT-L1-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.9	32.8
10°-20°	265.8	40.0
20°-30°	146.3	22.0
30°-40°	24.3	3.7
40°-50°	4.4	0.7
50°-60°	2.6	0.4
60°-70°	1.6	0.2
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	630.0	94.9
0°-40°	654.3	98.5
0°-60°	661.3	99.6
0°-90°	664.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	664.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2809	
5°	2543	218
15°	942	266
25°	346	146
35°	24	24
45°	5	4
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P220587

CATALOG NUMBER: 9003-W1-FL-LED2790-M-WT-L1-UNV

CANDELA DISTRIBUTION (FULL):

0°	
0°	2809.4
1°	2792.2
2°	2763.1
3°	2717.3
4°	2639.6
5°	2543.0
6°	2426.4
7°	2287.8
8°	2129.8
9°	1956.8
10°	1776.8
11°	1595.1
12°	1416.8
13°	1246.2
14°	1088.6
15°	941.8
16°	815.0
17°	700.8
18°	611.6
19°	540.4
20°	487.3
21°	446.8
22°	417.3
23°	396.4
24°	375.6
25°	345.7
26°	308.5
27°	266.7
28°	221.3
29°	176.7
30°	133.4
32.5°	48.3
35°	24.1
37.5°	17.2
40°	11.9
42.5°	6.1
45°	4.9
47.5°	4.5
50°	3.7
52.5°	3.3
55°	2.9
57.5°	2.5
60°	2.0
62.5°	2.0
65°	1.6



TEST NUMBER: P220587

CATALOG NUMBER: 9003-W1-FL-LED2790-M-WT-L1-UNV

CANDELA DISTRIBUTION (continued):

	0°
67.5°	1.2
70°	1.2
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)