

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: LUMIERE

Report Number: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **206-8LED3036-12-XX-LVR**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1802-569-34)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 206-8LED3036-12-XX-LVR  
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 3000K CCT, 36 DEGREE WIDE OPTIC,  
REGRESSED HOOD BLACK, HEX CELL LOUVER  
Light Source: (1) SORAA 3000K 95 CRI LED  
SM16-07-36D-930-03  
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004

**Summary**


Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	223.2 lumens	Max Intensity:	882.9 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	28.6 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	28.7°H x 28.7°V	Field Angle (10%):	48°H x 48°V
Beam Lumens:	129.5 lumens	Field Lumens:	203.5 lumens
Beam Efficiency:	58.0%	Field Efficiency:	91.1%
Input Watts (W):	7.8		
Input Voltage (V):	NR		
Input Current (A <sub>in</sub> ):	NR		
Voltage Rise (V):	NR		
Power Factor:	NR		
Total Harmonic Distortion (THDi):	NR		
Frequency (hertz):	60		
Stabilization Time:	NR		
Operation Time:	NR		
Ambient Temperature (°C):	NR		
Test Distance:	25 FT		



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 206-8LED3036-12-XX-LVR

### Iso-Candela Plot






REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

### Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40		0.0	0.0	0.0	0.0	0.1	0.2	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0		
30	0.0	0.0	0.0	0.0	0.1	0.2	0.9	2.2	2.2	0.9	0.2	0.1	0.0	0.0	0.0	0.0	0.0
20		0.0	0.0	0.0	0.1	0.9	5.2	11.2	11.2	5.2	0.9	0.1	0.0	0.0	0.0		
10	0.0	0.0	0.0	0.0	0.2	2.0	10.9	21.2	21.2	10.9	2.0	0.2	0.0	0.0	0.0	0.0	0.0
0		0.0	0.0	0.0	0.2	2.0	10.9	21.2	21.2	10.9	2.0	0.2	0.0	0.0	0.0		
-10	0.0	0.0	0.0	0.0	0.1	0.9	5.2	11.2	11.2	5.2	0.9	0.1	0.0	0.0	0.0	0.0	0.0
-20		0.0	0.0	0.0	0.1	0.2	0.9	2.2	2.2	0.9	0.2	0.1	0.0	0.0	0.0		
-30	0.0	0.0	0.0	0.0	0.0	0.1	0.2	0.2	0.2	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0
-40		0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0


REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
CATALOG NUMBER: 206-8LED3036-12-XX-LVR

### Luminous Intensity Polar Plot



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

### Luminous Intensity Plot



**Beam:**  
 H Angle: 28.7°  
 V Angle: 28.7°  
 Lumens: 129.5  
 Efficiency: 58.0%

**Field:**  
 H Angle: 48°  
 V Angle: 48°  
 Lumens: 203.5  
 Efficiency: 91.1%

**Spill:**  
 Lumens: 19.8  
 Efficiency: 8.9%

— Vertical Distribution through 0-Deg  
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

FIELD  
 BEAM

**CANDELA DISTRIBUTION:**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	1
35°	0	0	0	0	0	0	0	0	0	0	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	0	1	1	2
25°	0	0	0	0	0	0	0	1	1	1	2
22.5°	0	0	0	0	0	0	0	1	1	2	3
20°	0	0	0	0	0	0	1	1	1	2	3
17.5°	0	0	0	0	0	0	1	1	2	2	3
15°	0	0	0	0	0	0	1	1	2	3	4
12.5°	0	0	0	0	0	0	1	1	2	3	4
10°	0	0	0	0	0	1	1	1	2	3	4
7.5°	0	0	0	0	0	1	1	2	3	3	4
5°	0	0	0	0	0	1	1	2	3	3	4
2.5°	0	0	0	0	0	1	1	2	3	3	4
0°	0	0	0	0	0	1	1	2	3	4	4
-2.5°	0	0	0	0	0	1	1	2	3	3	4
-5°	0	0	0	0	0	1	1	2	3	3	4
-7.5°	0	0	0	0	0	1	1	2	3	3	4
-10°	0	0	0	0	0	1	1	1	2	3	4
-12.5°	0	0	0	0	0	0	1	1	2	3	4
-15°	0	0	0	0	0	0	1	1	2	3	4
-17.5°	0	0	0	0	0	0	1	1	2	2	3
-20°	0	0	0	0	0	0	1	1	1	2	3



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	0	0	0	0	0	1	1	2	3
-25°	0	0	0	0	0	0	0	1	1	1	2
-27.5°	0	0	0	0	0	0	0	0	1	1	2
-30°	0	0	0	0	0	0	0	0	1	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	0	1
-37.5°	0	0	0	0	0	0	0	0	0	0	1
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	1
47.5°	0	0	0	0	0	0	1	1	1	1	1
45°	0	0	0	0	1	1	1	1	1	1	1
42.5°	0	0	1	1	1	1	1	2	2	2	2
40°	0	1	1	1	1	2	2	2	3	3	3
37.5°	1	1	1	2	2	3	3	3	4	4	4
35°	1	1	2	2	3	3	4	4	4	5	6
32.5°	1	2	2	3	3	4	4	6	7	8	9
30°	2	2	3	4	4	5	7	8	10	11	14
27.5°	2	3	4	4	5	7	9	11	15	18	22
25°	3	3	4	5	7	10	13	17	23	32	41
22.5°	3	4	5	7	10	14	19	28	40	57	75
20°	4	4	7	9	13	19	30	47	69	98	129
17.5°	4	6	8	11	17	28	47	74	112	156	203
15°	4	7	10	15	23	40	69	112	166	229	290
12.5°	5	8	11	18	32	57	98	156	229	305	374
10°	6	9	14	22	41	75	129	203	290	374	450
7.5°	6	10	15	27	51	93	159	247	342	432	519
5°	7	10	17	31	59	108	184	281	381	477	577
2.5°	7	10	17	33	64	119	200	302	405	508	615
0°	7	11	18	34	66	123	206	309	413	518	629
-2.5°	7	10	17	33	64	119	200	302	405	508	615
-5°	7	10	17	31	59	108	184	281	381	477	577
-7.5°	6	10	15	27	51	93	159	247	342	432	519
-10°	6	9	14	22	41	75	129	203	290	374	450
-12.5°	5	8	11	18	32	57	98	156	229	305	374
-15°	4	7	10	15	23	40	69	112	166	229	290
-17.5°	4	6	8	11	17	28	47	74	112	156	203
-20°	4	4	7	9	13	19	30	47	69	98	129



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	3	4	5	7	10	14	19	28	40	57	75
-25°	3	3	4	5	7	10	13	17	23	32	41
-27.5°	2	3	4	4	5	7	9	11	15	18	22
-30°	2	2	3	4	4	5	7	8	10	11	14
-32.5°	1	2	2	3	3	4	4	6	7	8	9
-35°	1	1	2	2	3	3	4	4	4	5	6
-37.5°	1	1	1	2	2	3	3	3	4	4	4
-40°	0	1	1	1	1	2	2	2	3	3	3
-42.5°	0	0	1	1	1	1	1	2	2	2	2
-45°	0	0	0	0	1	1	1	1	1	1	1
-47.5°	0	0	0	0	0	0	1	1	1	1	1
-50°	0	0	0	0	0	0	0	0	0	0	1
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	1	1	1	1	1	1	1	1	0	0	0
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	2	2	2	2	2	2	2	1	1	1	1
42.5°	3	3	3	3	3	3	3	2	2	2	2
40°	3	3	3	4	3	3	3	3	3	3	2
37.5°	4	4	4	4	4	4	4	4	4	4	3
35°	6	7	7	7	7	7	6	6	5	4	4
32.5°	10	10	10	11	10	10	10	9	8	7	6
30°	15	17	17	18	17	17	15	14	11	10	8
27.5°	27	31	33	34	33	31	27	22	18	15	11
25°	51	59	64	66	64	59	51	41	32	23	17
22.5°	93	108	119	123	119	108	93	75	57	40	28
20°	159	184	200	206	200	184	159	129	98	69	47
17.5°	247	281	302	309	302	281	247	203	156	112	74
15°	342	381	405	413	405	381	342	290	229	166	112
12.5°	432	477	508	518	508	477	432	374	305	229	156
10°	519	577	615	629	615	577	519	450	374	290	203
7.5°	603	668	710	724	710	668	603	519	432	342	247
5°	668	740	781	795	781	740	668	577	477	381	281
2.5°	710	781	826	846	826	781	710	615	508	405	302
0°	724	795	846	883	846	795	724	629	518	413	309
-2.5°	710	781	826	846	826	781	710	615	508	405	302
-5°	668	740	781	795	781	740	668	577	477	381	281
-7.5°	603	668	710	724	710	668	603	519	432	342	247
-10°	519	577	615	629	615	577	519	450	374	290	203
-12.5°	432	477	508	518	508	477	432	374	305	229	156
-15°	342	381	405	413	405	381	342	290	229	166	112
-17.5°	247	281	302	309	302	281	247	203	156	112	74
-20°	159	184	200	206	200	184	159	129	98	69	47



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	93	108	119	123	119	108	93	75	57	40	28
-25°	51	59	64	66	64	59	51	41	32	23	17
-27.5°	27	31	33	34	33	31	27	22	18	15	11
-30°	15	17	17	18	17	17	15	14	11	10	8
-32.5°	10	10	10	11	10	10	10	9	8	7	6
-35°	6	7	7	7	7	7	6	6	5	4	4
-37.5°	4	4	4	4	4	4	4	4	4	4	3
-40°	3	3	3	4	3	3	3	3	3	3	2
-42.5°	3	3	3	3	3	3	3	2	2	2	2
-45°	2	2	2	2	2	2	2	1	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	1	0	0	0	0	0	0	0	0	0	0
45°	1	1	1	0	0	0	0	0	0	0	0
42.5°	1	1	1	1	1	0	0	0	0	0	0
40°	2	2	1	1	1	1	0	0	0	0	0
37.5°	3	3	2	2	1	1	1	1	0	0	0
35°	4	3	3	2	2	1	1	1	0	0	0
32.5°	4	4	3	3	2	2	1	1	1	0	0
30°	7	5	4	4	3	2	2	1	1	1	0
27.5°	9	7	5	4	4	3	2	2	1	1	0
25°	13	10	7	5	4	3	3	2	1	1	1
22.5°	19	14	10	7	5	4	3	3	2	1	1
20°	30	19	13	9	7	4	4	3	2	1	1
17.5°	47	28	17	11	8	6	4	3	2	2	1
15°	69	40	23	15	10	7	4	4	3	2	1
12.5°	98	57	32	18	11	8	5	4	3	2	1
10°	129	75	41	22	14	9	6	4	3	2	1
7.5°	159	93	51	27	15	10	6	4	3	3	2
5°	184	108	59	31	17	10	7	4	3	3	2
2.5°	200	119	64	33	17	10	7	4	3	3	2
0°	206	123	66	34	18	11	7	4	4	3	2
-2.5°	200	119	64	33	17	10	7	4	3	3	2
-5°	184	108	59	31	17	10	7	4	3	3	2
-7.5°	159	93	51	27	15	10	6	4	3	3	2
-10°	129	75	41	22	14	9	6	4	3	2	1
-12.5°	98	57	32	18	11	8	5	4	3	2	1
-15°	69	40	23	15	10	7	4	4	3	2	1
-17.5°	47	28	17	11	8	6	4	3	2	2	1
-20°	30	19	13	9	7	4	4	3	2	1	1



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	19	14	10	7	5	4	3	3	2	1	1
-25°	13	10	7	5	4	3	3	2	1	1	1
-27.5°	9	7	5	4	4	3	2	2	1	1	0
-30°	7	5	4	4	3	2	2	1	1	1	0
-32.5°	4	4	3	3	2	2	1	1	1	0	0
-35°	4	3	3	2	2	1	1	1	0	0	0
-37.5°	3	3	2	2	1	1	1	1	0	0	0
-40°	2	2	1	1	1	1	0	0	0	0	0
-42.5°	1	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	0	0	0	0	0	0	0	0
-47.5°	1	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0





REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	1	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
15°	1	0	0	0	0	0	0	0	0	0	0
12.5°	1	0	0	0	0	0	0	0	0	0	0
10°	1	1	0	0	0	0	0	0	0	0	0
7.5°	1	1	0	0	0	0	0	0	0	0	0
5°	1	1	0	0	0	0	0	0	0	0	0
2.5°	1	1	0	0	0	0	0	0	0	0	0
0°	1	1	0	0	0	0	0	0	0	0	0
-2.5°	1	1	0	0	0	0	0	0	0	0	0
-5°	1	1	0	0	0	0	0	0	0	0	0
-7.5°	1	1	0	0	0	0	0	0	0	0	0
-10°	1	1	0	0	0	0	0	0	0	0	0
-12.5°	1	0	0	0	0	0	0	0	0	0	0
-15°	1	0	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)  
 CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: P246986 (CONVERTED FROM TYPE C PHOTOMETRY)

CATALOG NUMBER: 206-8LED3036-12-XX-LVR

**CANDELA DISTRIBUTION (continued):**

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)