

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: LUMIERE

Report Number: P220548

Luminaire Tested: **9003-W1-[RW, RI]-LED2797-F-BK-L2-UNV**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P220548  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29474)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: LUMIERE  
Catalog Number: 9003-W1-[RW, RI]-LED2797-F-BK-L2-UNV  
Description: LUMIERE LANTERRA 9003 LED WALL LUMINAIRE, RECESSED LENS, FLOOD OPTIC, BLACK HOUSING.  
Light Source: (1) 2700K CCT, 97 CRI LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1139.0 lumens  
Efficiency: N/A  
Efficacy: 56.7 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.56  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P220548

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-F-BK-L2-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P220548

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-F-BK-L2-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	86	99	93	89	86	91	88	85	90	87	85	89	86	84	83
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	80	78	77
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	728319
5°	712633
10°	628089
15°	485270
20°	301376
25°	111660
30°	23371
35°	8807
40°	3206
45°	2171
50°	1910
55°	1606
60°	1228
65°	726
70°	449
75°	0
80°	0
85°	0



TEST NUMBER: P220548

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-F-BK-L2-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	295.6	26.0
10°-20°	573.6	50.4
20°-30°	233.7	20.5
30°-40°	24.7	2.2
40°-50°	5.8	0.5
50°-60°	3.7	0.3
60°-70°	1.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1102.9	96.8
0°-40°	1127.6	99.0
0°-60°	1137.1	99.8
0°-90°	1139.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1139.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3321	
5°	3238	296
15°	2138	574
25°	462	234
35°	33	25
45°	7	6
55°	4	4
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P220548

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-F-BK-L2-UNV

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3321.4
1°	3313.0
2°	3303.3
3°	3294.2
4°	3276.0
5°	3237.5
6°	3185.1
7°	3116.6
8°	3029.1
9°	2929.9
10°	2820.8
11°	2701.2
12°	2573.9
13°	2441.1
14°	2295.6
15°	2137.6
16°	1976.8
17°	1798.5
18°	1632.0
19°	1458.6
20°	1291.5
21°	1128.6
22°	955.9
23°	779.7
24°	612.5
25°	461.5
26°	330.7
27°	225.2
28°	148.9
29°	110.5
30°	92.3
32.5°	60.8
35°	32.9
37.5°	18.2
40°	11.2
42.5°	8.4
45°	7.0
47.5°	6.3
50°	5.6
52.5°	4.9
55°	4.2
57.5°	3.5
60°	2.8
62.5°	2.1
65°	1.4



TEST NUMBER: P220548

CATALOG NUMBER: 9003-W1-[RW, RI]-LED2797-F-BK-L2-UNV

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.4
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)