

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)

Luminaire Tested: **206-8LED4036-12-XX-LVR**

Test Date: 04/06/18

Test Information

Test Method: LM-79-08
Report Number: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
Test Lab: INNOVATION CENTER(G2)
Test Date: 04/06/18
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 206-8LED4036-12-XX-LVR
Description: CAMBRIA 203 LED LUMINAIRE, 8 WATT, 4000K CCT, 36 DEGREE WIDE OPTIC,
REGRESSED HOOD BLACK, HEX CELL LOUVER
Light Source: (1) SORAA 4000K 95 CRI LED
SM16-07-36D-940-03
Ballast/Driver: (1) CHROMA POWER SUPPLY IN0004


Summary

Lumens per Lamp:	N/A	NEMA Type:	4H x 4V
Luminaire Lumens:	251.8 lumens	Max Intensity:	996 candela
Efficiency:	N/A	Max Intensity Angle:	0°H x 0°V
Efficacy:	32.3 lumens/watt		
Luminous Opening:	Circular (Dia: 0.17' x H: 0')		
Beam Angle (50%):	28.6°H x 28.6°V	Field Angle (10%):	48°H x 48°V
Beam Lumens:	146.1 lumens	Field Lumens:	229.5 lumens
Beam Efficiency:	58.0%	Field Efficiency:	91.1%
Input Watts (W):	7.8		
Input Voltage (V):	12.0		
Input Current (Ain):	0.680		
Voltage Rise (V):	NR		
Power Factor:	0.9908		
Total Harmonic Distortion (THDi):	27.3%		
Frequency (hertz):	60		
Stabilization Time:	0.5 HR		
Operation Time:	3 HR		
Ambient Temperature (°C):	24.9		
Test Distance:	25 FT		



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 206-8LED4036-12-XX-LVR

Iso-Candela Plot






REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

Lumen Table

90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40		0.0	0.0	0.0	0.0	0.1	0.2	0.3	0.3	0.2	0.1	0.0	0.0	0.0	0.0		
30	0.0	0.0	0.0	0.0	0.1	0.3	1.0	2.5	2.5	1.0	0.3	0.1	0.0	0.0	0.0	0.0	0.0
20		0.0	0.0	0.0	0.1	1.0	5.8	12.6	12.6	5.8	1.0	0.1	0.0	0.0	0.0		
10	0.0	0.0	0.0	0.0	0.2	2.3	12.3	24.0	24.0	12.3	2.3	0.2	0.0	0.0	0.0	0.0	0.0
0		0.0	0.0	0.0	0.2	2.3	12.3	24.0	24.0	12.3	2.3	0.2	0.0	0.0	0.0		
-10	0.0	0.0	0.0	0.0	0.1	1.0	5.8	12.6	12.6	5.8	1.0	0.1	0.0	0.0	0.0	0.0	0.0
-20		0.0	0.0	0.0	0.1	0.3	1.0	2.5	2.5	1.0	0.3	0.1	0.0	0.0	0.0		
-30	0.0	0.0	0.0	0.0	0.0	0.1	0.2	0.3	0.3	0.2	0.1	0.0	0.0	0.0	0.0	0.0	0.0
-40		0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0		
-50	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-60		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-70	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
-80		0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0		
-90	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0


REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 206-8LED4036-12-XX-LVR

Luminous Intensity Polar Plot



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

Luminous Intensity Plot



Beam:
 H Angle: 28.6°
 V Angle: 28.6°
 Lumens: 146.1
 Efficiency: 58.0%

Field:
 H Angle: 48°
 V Angle: 48°
 Lumens: 229.5
 Efficiency: 91.1%

Spill:
 Lumens: 22.3
 Efficiency: 8.9%

— Vertical Distribution through 0-Deg
 - - Horizontal Distribution through 0-Deg



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

FIELD
 BEAM

CANDELA DISTRIBUTION:

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	-90°	-87.5°	-85°	-82.5°	-80°	-77.5°	-75°	-72.5°	-70°	-67.5°	-65°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	1
35°	0	0	0	0	0	0	0	0	0	1	1
32.5°	0	0	0	0	0	0	0	0	0	1	1
30°	0	0	0	0	0	0	0	0	1	1	1
27.5°	0	0	0	0	0	0	0	1	1	1	2
25°	0	0	0	0	0	0	0	1	1	2	2
22.5°	0	0	0	0	0	0	0	1	1	2	3
20°	0	0	0	0	0	0	1	1	2	2	3
17.5°	0	0	0	0	0	0	1	1	2	3	4
15°	0	0	0	0	0	0	1	1	2	3	4
12.5°	0	0	0	0	0	1	1	1	2	3	4
10°	0	0	0	0	0	1	1	2	3	4	5
7.5°	0	0	0	0	0	1	1	2	3	4	5
5°	0	0	0	0	0	1	1	2	3	4	5
2.5°	0	0	0	0	0	1	1	2	3	4	5
0°	0	0	0	0	0	1	1	2	3	4	5
-2.5°	0	0	0	0	0	1	1	2	3	4	5
-5°	0	0	0	0	0	1	1	2	3	4	5
-7.5°	0	0	0	0	0	1	1	2	3	4	5
-10°	0	0	0	0	0	1	1	2	3	4	5
-12.5°	0	0	0	0	0	1	1	1	2	3	4
-15°	0	0	0	0	0	0	1	1	2	3	4
-17.5°	0	0	0	0	0	0	1	1	2	3	4
-20°	0	0	0	0	0	0	1	1	2	2	3



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	-62.5°	-60°	-57.5°	-55°	-52.5°	-50°	-47.5°	-45°	-42.5°	-40°	-37.5°
-22.5°	0	0	0	0	0	0	0	1	1	2	3
-25°	0	0	0	0	0	0	0	1	1	2	2
-27.5°	0	0	0	0	0	0	0	1	1	1	2
-30°	0	0	0	0	0	0	0	0	1	1	1
-32.5°	0	0	0	0	0	0	0	0	0	1	1
-35°	0	0	0	0	0	0	0	0	0	1	1
-37.5°	0	0	0	0	0	0	0	0	0	0	1
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	1	1
47.5°	0	0	0	0	0	0	1	1	1	1	1
45°	0	0	0	1	1	1	1	1	1	1	2
42.5°	0	0	1	1	1	1	2	2	2	2	3
40°	1	1	1	1	2	2	2	3	3	3	4
37.5°	1	1	1	2	2	3	3	4	4	4	5
35°	1	1	2	3	3	4	4	5	5	6	7
32.5°	1	2	3	3	4	4	5	6	7	9	10
30°	2	3	3	4	5	6	7	9	11	13	15
27.5°	3	3	4	5	6	8	10	13	17	20	24
25°	3	4	5	6	8	11	15	19	26	36	46
22.5°	4	4	6	8	11	16	21	32	46	65	84
20°	4	5	7	10	15	21	34	53	78	110	146
17.5°	5	6	9	13	19	32	53	83	126	176	229
15°	5	7	11	17	26	46	78	126	187	258	327
12.5°	6	9	13	20	36	65	110	176	258	344	422
10°	7	10	15	24	46	84	146	229	327	422	507
7.5°	7	11	17	30	58	105	179	278	386	487	586
5°	8	11	19	35	67	122	207	317	430	538	651
2.5°	8	12	20	38	72	134	226	341	457	573	694
0°	8	12	20	39	74	139	232	349	466	585	709
-2.5°	8	12	20	38	72	134	226	341	457	573	694
-5°	8	11	19	35	67	122	207	317	430	538	651
-7.5°	7	11	17	30	58	105	179	278	386	487	586
-10°	7	10	15	24	46	84	146	229	327	422	507
-12.5°	6	9	13	20	36	65	110	176	258	344	422
-15°	5	7	11	17	26	46	78	126	187	258	327
-17.5°	5	6	9	13	19	32	53	83	126	176	229
-20°	4	5	7	10	15	21	34	53	78	110	146



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	-35°	-32.5°	-30°	-27.5°	-25°	-22.5°	-20°	-17.5°	-15°	-12.5°	-10°
-22.5°	4	4	6	8	11	16	21	32	46	65	84
-25°	3	4	5	6	8	11	15	19	26	36	46
-27.5°	3	3	4	5	6	8	10	13	17	20	24
-30°	2	3	3	4	5	6	7	9	11	13	15
-32.5°	1	2	3	3	4	4	5	6	7	9	10
-35°	1	1	2	3	3	4	4	5	5	6	7
-37.5°	1	1	1	2	2	3	3	4	4	4	5
-40°	1	1	1	1	2	2	2	3	3	3	4
-42.5°	0	0	1	1	1	1	2	2	2	2	3
-45°	0	0	0	1	1	1	1	1	1	1	2
-47.5°	0	0	0	0	0	0	1	1	1	1	1
-50°	0	0	0	0	0	0	0	0	0	1	1
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	1	1	1	1	1	1	1	1	1	0	0
47.5°	1	1	1	1	1	1	1	1	1	1	1
45°	2	2	2	2	2	2	2	2	1	1	1
42.5°	3	3	3	3	3	3	3	3	2	2	2
40°	4	4	4	4	4	4	4	4	3	3	3
37.5°	5	5	5	5	5	5	5	5	4	4	4
35°	7	8	8	8	8	8	7	7	6	5	5
32.5°	11	11	12	12	12	11	11	10	9	7	6
30°	17	19	20	20	20	19	17	15	13	11	9
27.5°	30	35	38	39	38	35	30	24	20	17	13
25°	58	67	72	74	72	67	58	46	36	26	19
22.5°	105	122	134	139	134	122	105	84	65	46	32
20°	179	207	226	232	226	207	179	146	110	78	53
17.5°	278	317	341	349	341	317	278	229	176	126	83
15°	386	430	457	466	457	430	386	327	258	187	126
12.5°	487	538	573	585	573	538	487	422	344	258	176
10°	586	651	694	709	694	651	586	507	422	327	229
7.5°	680	754	801	817	801	754	680	586	487	386	278
5°	754	834	881	897	881	834	754	651	538	430	317
2.5°	801	881	931	954	931	881	801	694	573	457	341
0°	817	897	954	996	954	897	817	709	585	466	349
-2.5°	801	881	931	954	931	881	801	694	573	457	341
-5°	754	834	881	897	881	834	754	651	538	430	317
-7.5°	680	754	801	817	801	754	680	586	487	386	278
-10°	586	651	694	709	694	651	586	507	422	327	229
-12.5°	487	538	573	585	573	538	487	422	344	258	176
-15°	386	430	457	466	457	430	386	327	258	187	126
-17.5°	278	317	341	349	341	317	278	229	176	126	83
-20°	179	207	226	232	226	207	179	146	110	78	53



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	-7.5°	-5°	-2.5°	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°
-22.5°	105	122	134	139	134	122	105	84	65	46	32
-25°	58	67	72	74	72	67	58	46	36	26	19
-27.5°	30	35	38	39	38	35	30	24	20	17	13
-30°	17	19	20	20	20	19	17	15	13	11	9
-32.5°	11	11	12	12	12	11	11	10	9	7	6
-35°	7	8	8	8	8	8	7	7	6	5	5
-37.5°	5	5	5	5	5	5	5	5	4	4	4
-40°	4	4	4	4	4	4	4	4	3	3	3
-42.5°	3	3	3	3	3	3	3	3	2	2	2
-45°	2	2	2	2	2	2	2	2	1	1	1
-47.5°	1	1	1	1	1	1	1	1	1	1	1
-50°	1	1	1	1	1	1	1	1	1	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	1	0	0	0	0	0	0	0	0	0	0
45°	1	1	1	1	0	0	0	0	0	0	0
42.5°	2	1	1	1	1	0	0	0	0	0	0
40°	2	2	2	1	1	1	1	0	0	0	0
37.5°	3	3	2	2	1	1	1	1	0	0	0
35°	4	4	3	3	2	1	1	1	1	0	0
32.5°	5	4	4	3	3	2	1	1	1	0	0
30°	7	6	5	4	3	3	2	1	1	1	0
27.5°	10	8	6	5	4	3	3	2	1	1	1
25°	15	11	8	6	5	4	3	2	2	1	1
22.5°	21	16	11	8	6	4	4	3	2	1	1
20°	34	21	15	10	7	5	4	3	2	2	1
17.5°	53	32	19	13	9	6	5	4	3	2	1
15°	78	46	26	17	11	7	5	4	3	2	1
12.5°	110	65	36	20	13	9	6	4	3	2	1
10°	146	84	46	24	15	10	7	5	4	3	2
7.5°	179	105	58	30	17	11	7	5	4	3	2
5°	207	122	67	35	19	11	8	5	4	3	2
2.5°	226	134	72	38	20	12	8	5	4	3	2
0°	232	139	74	39	20	12	8	5	4	3	2
-2.5°	226	134	72	38	20	12	8	5	4	3	2
-5°	207	122	67	35	19	11	8	5	4	3	2
-7.5°	179	105	58	30	17	11	7	5	4	3	2
-10°	146	84	46	24	15	10	7	5	4	3	2
-12.5°	110	65	36	20	13	9	6	4	3	2	1
-15°	78	46	26	17	11	7	5	4	3	2	1
-17.5°	53	32	19	13	9	6	5	4	3	2	1
-20°	34	21	15	10	7	5	4	3	2	2	1



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	20°	22.5°	25°	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°
-22.5°	21	16	11	8	6	4	4	3	2	1	1
-25°	15	11	8	6	5	4	3	2	2	1	1
-27.5°	10	8	6	5	4	3	3	2	1	1	1
-30°	7	6	5	4	3	3	2	1	1	1	0
-32.5°	5	4	4	3	3	2	1	1	1	0	0
-35°	4	4	3	3	2	1	1	1	1	0	0
-37.5°	3	3	2	2	1	1	1	1	0	0	0
-40°	2	2	2	1	1	1	1	0	0	0	0
-42.5°	2	1	1	1	1	0	0	0	0	0	0
-45°	1	1	1	1	0	0	0	0	0	0	0
-47.5°	1	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
90°	0	0	0	0	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0	0	0	0	0
20°	1	0	0	0	0	0	0	0	0	0	0
17.5°	1	0	0	0	0	0	0	0	0	0	0
15°	1	0	0	0	0	0	0	0	0	0	0
12.5°	1	1	0	0	0	0	0	0	0	0	0
10°	1	1	0	0	0	0	0	0	0	0	0
7.5°	1	1	0	0	0	0	0	0	0	0	0
5°	1	1	0	0	0	0	0	0	0	0	0
2.5°	1	1	0	0	0	0	0	0	0	0	0
0°	1	1	0	0	0	0	0	0	0	0	0
-2.5°	1	1	0	0	0	0	0	0	0	0	0
-5°	1	1	0	0	0	0	0	0	0	0	0
-7.5°	1	1	0	0	0	0	0	0	0	0	0
-10°	1	1	0	0	0	0	0	0	0	0	0
-12.5°	1	1	0	0	0	0	0	0	0	0	0
-15°	1	0	0	0	0	0	0	0	0	0	0
-17.5°	1	0	0	0	0	0	0	0	0	0	0
-20°	1	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	47.5°	50°	52.5°	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°
-22.5°	0	0	0	0	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
 CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
90°	0	0	0	0	0	0	0
87.5°	0	0	0	0	0	0	0
85°	0	0	0	0	0	0	0
82.5°	0	0	0	0	0	0	0
80°	0	0	0	0	0	0	0
77.5°	0	0	0	0	0	0	0
75°	0	0	0	0	0	0	0
72.5°	0	0	0	0	0	0	0
70°	0	0	0	0	0	0	0
67.5°	0	0	0	0	0	0	0
65°	0	0	0	0	0	0	0
62.5°	0	0	0	0	0	0	0
60°	0	0	0	0	0	0	0
57.5°	0	0	0	0	0	0	0
55°	0	0	0	0	0	0	0
52.5°	0	0	0	0	0	0	0
50°	0	0	0	0	0	0	0
47.5°	0	0	0	0	0	0	0
45°	0	0	0	0	0	0	0
42.5°	0	0	0	0	0	0	0
40°	0	0	0	0	0	0	0
37.5°	0	0	0	0	0	0	0
35°	0	0	0	0	0	0	0
32.5°	0	0	0	0	0	0	0
30°	0	0	0	0	0	0	0
27.5°	0	0	0	0	0	0	0
25°	0	0	0	0	0	0	0
22.5°	0	0	0	0	0	0	0
20°	0	0	0	0	0	0	0
17.5°	0	0	0	0	0	0	0
15°	0	0	0	0	0	0	0
12.5°	0	0	0	0	0	0	0
10°	0	0	0	0	0	0	0
7.5°	0	0	0	0	0	0	0
5°	0	0	0	0	0	0	0
2.5°	0	0	0	0	0	0	0
0°	0	0	0	0	0	0	0
-2.5°	0	0	0	0	0	0	0
-5°	0	0	0	0	0	0	0
-7.5°	0	0	0	0	0	0	0
-10°	0	0	0	0	0	0	0
-12.5°	0	0	0	0	0	0	0
-15°	0	0	0	0	0	0	0
-17.5°	0	0	0	0	0	0	0
-20°	0	0	0	0	0	0	0



REPORT NUMBER: G2-1802-569-34 (CONVERTED FROM TYPE C PHOTOMETRY)
CATALOG NUMBER: 206-8LED4036-12-XX-LVR

CANDELA DISTRIBUTION (continued):

	75°	77.5°	80°	82.5°	85°	87.5°	90°
-22.5°	0	0	0	0	0	0	0
-25°	0	0	0	0	0	0	0
-27.5°	0	0	0	0	0	0	0
-30°	0	0	0	0	0	0	0
-32.5°	0	0	0	0	0	0	0
-35°	0	0	0	0	0	0	0
-37.5°	0	0	0	0	0	0	0
-40°	0	0	0	0	0	0	0
-42.5°	0	0	0	0	0	0	0
-45°	0	0	0	0	0	0	0
-47.5°	0	0	0	0	0	0	0
-50°	0	0	0	0	0	0	0
-52.5°	0	0	0	0	0	0	0
-55°	0	0	0	0	0	0	0
-57.5°	0	0	0	0	0	0	0
-60°	0	0	0	0	0	0	0
-62.5°	0	0	0	0	0	0	0
-65°	0	0	0	0	0	0	0
-67.5°	0	0	0	0	0	0	0
-70°	0	0	0	0	0	0	0
-72.5°	0	0	0	0	0	0	0
-75°	0	0	0	0	0	0	0
-77.5°	0	0	0	0	0	0	0
-80°	0	0	0	0	0	0	0
-82.5°	0	0	0	0	0	0	0
-85°	0	0	0	0	0	0	0
-87.5°	0	0	0	0	0	0	0
-90°	0	0	0	0	0	0	0

(END OF REPORT)