

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: LUMIERE

Report Number: P253136

Luminaire Tested: **3002A-25LED2700-MFL-UNV-NBR**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P253136
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P22981)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: LUMIERE
Catalog Number: 3002A-25LED2700-MFL-UNV-NBR
Description: LUMIERE MONACO INGRADE TEST FIXTURE WITH MEDIUM FLOOD OPTICS
Light Source: (7) 2700K CCT, 90 CRI LEDS
LBA-8057XPG2-2K
Ballast/Driver: -
ESS030W-1000-24-CPL

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 846.2 lumens
Efficiency: N/A
Efficacy: 33.7 lumens/watt
N/A
Luminous Opening: Circular (Dia: 0.44' x H: 0')
CIE Type: Indirect


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P253136

CATALOG NUMBER: 3002A-25LED2700-MFL-UNV-NBR

Luminous Intensity Polar Plot





TEST NUMBER: P253136

CATALOG NUMBER: 3002A-25LED2700-MFL-UNV-NBR

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°
95°	0
100°	0
105°	277
110°	209
115°	169
120°	0
125°	125
130°	0
135°	1337
140°	2112
145°	4781
150°	10062
155°	23085
160°	51875
165°	96596
170°	160899
175°	247898



TEST NUMBER: P253136

CATALOG NUMBER: 3002A-25LED2700-MFL-UNV-NBR

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.5	0.1
100°-110°	0.7	0.1
110°-120°	1.3	0.2
120°-130°	0.7	0.1
130°-140°	6.9	0.8
140°-150°	35.9	4.2
150°-160°	148.0	17.5
160°-170°	363.6	43.0
170°-180°	289.0	34.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2.5	0.3
90°-150°	45.9	5.4
90°-180°	847.0	100.1
0°-180°	846.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
90°	0	
95°	0	1
105°	1	1
115°	1	1
125°	1	1
135°	13	7
145°	55	36
155°	292	148
165°	1303	364
175°	3449	289
180°	4171	



TEST NUMBER: P253136

CATALOG NUMBER: 3002A-25LED2700-MFL-UNV-NBR

CANDELA DISTRIBUTION (FULL):

	0°
90°	0.0
92.5°	0.0
95°	0.0
97.5°	1.0
100°	0.0
102.5°	1.0
105°	1.0
107.5°	0.0
110°	1.0
112.5°	2.8
115°	1.0
117.5°	1.0
120°	0.0
122.5°	1.0
125°	1.0
127.5°	1.0
130°	0.0
132.5°	0.0
135°	13.2
137.5°	12.3
140°	22.6
142.5°	28.3
145°	54.7
147.5°	81.1
150°	121.7
152.5°	191.4
155°	292.2
157.5°	458.2
160°	680.8
162.5°	974.0
165°	1303.1
167.5°	1715.1
170°	2213.0
172.5°	2813.6
175°	3449.0
175.5°	3566.0
176°	3684.8
176.5°	3789.5
177°	3896.0
177.5°	3986.6
178°	4043.1
178.5°	4094.9
179°	4136.4
179.5°	4166.6
180°	4171.4

(END OF REPORT)